

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P633597

Luminaire Tested: GWS-SA2F-722-U-T2R-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P633597
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA2F-722-U-T2R-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (2) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II ROADWAY OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (32) 2200K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8010.3 lumens
Efficiency: N/A
Efficacy: 64.3 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B1 - U0 - G0


Input Watts (W): 124.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P633597
 CATALOG NUMBER: GWS-SA2F-722-U-T2R-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 29.4 fc
 Type II - Short - N/A

REPORT NUMBER: P633597
CATALOG NUMBER: GWS-SA2F-722-U-T2R-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 58-Deg Lateral - - - Horizontal Cone Through 50-Deg Vertical

REPORT NUMBER: P633597
 CATALOG NUMBER: GWS-SA2F-722-U-T2R-W-GRSBK


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1121.9 | 0.0 | 1121.9 |
| | % Fixture | 14.0 | 0.0 | 14.0 |
| Street Side | Lumens | 6888.3 | 0.0 | 6888.3 |
| | % Fixture | 86.0 | 0.0 | 86.0 |
| Total | Lumens | 8010.3 | 0.0 | 8010.3 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 118.5 | 1.5 |
| 10°-20° | 469.2 | 5.9 |
| 20°-30° | 949.5 | 11.9 |
| 30°-40° | 1679.8 | 21.0 |
| 40°-50° | 2448.8 | 30.6 |
| 50°-60° | 1962.8 | 24.5 |
| 60°-70° | 353.6 | 4.4 |
| 70°-80° | 27.9 | 0.3 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 8010.3 | 100.0 |
| 0°-180° | 8010.3 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P633597

CATALOG NUMBER: GWS-SA2F-722-U-T2R-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 1191.9 | 14.9 | | | |
| FM (30°-60°) | 5394.7 | 67.3 | | | |
| FH (60°-80°) | 301.7 | 3.8 | | | G0/660 |
| FVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| BL (0°-30°) | 345.4 | 4.3 | B1/500 | | |
| BM (30°-60°) | 696.8 | 8.7 | B1/1000 | | |
| BH (60°-80°) | 79.7 | 1.0 | B0/110 | | G0/110 |
| BVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G0
 Type II Short





REPORT NUMBER: P633597

CATALOG NUMBER: GWS-SA2F-722-U-T2R-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 58° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 956.8 | 956.8 | 956.8 | 956.8 | 956.8 | 956.8 | 956.8 | 956.8 | 956.8 | 956.8 | 956.8 |
| 2.5° | 1416.0 | 1393.7 | 1380.8 | 1370.6 | 1325.2 | 1253.2 | 1206.1 | 1181.2 | 1140.1 | 1070.7 | 1010.8 |
| 5° | 1847.7 | 1831.4 | 1801.4 | 1780.9 | 1722.6 | 1620.7 | 1515.3 | 1473.3 | 1380.0 | 1223.2 | 1082.7 |
| 7.5° | 2133.8 | 2121.8 | 2110.7 | 2083.2 | 2028.4 | 1935.9 | 1819.4 | 1775.7 | 1631.8 | 1409.1 | 1178.7 |
| 10° | 2353.9 | 2344.5 | 2331.7 | 2330.8 | 2288.0 | 2204.9 | 2090.9 | 2045.5 | 1889.6 | 1611.3 | 1291.7 |
| 12.5° | 2547.5 | 2539.8 | 2537.2 | 2561.2 | 2533.8 | 2472.1 | 2348.8 | 2292.2 | 2126.9 | 1817.7 | 1416.8 |
| 15° | 2680.3 | 2678.6 | 2689.7 | 2736.8 | 2752.2 | 2724.0 | 2620.3 | 2559.5 | 2369.3 | 2025.0 | 1554.7 |
| 17.5° | 2741.1 | 2746.2 | 2767.7 | 2849.0 | 2917.6 | 2941.5 | 2861.9 | 2810.5 | 2610.0 | 2234.9 | 1702.1 |
| 20° | 2844.8 | 2843.0 | 2855.9 | 2933.0 | 3016.9 | 3102.6 | 3078.6 | 3034.9 | 2853.3 | 2456.7 | 1865.7 |
| 22.5° | 3136.9 | 3112.0 | 3084.6 | 3096.6 | 3126.6 | 3226.8 | 3271.3 | 3249.1 | 3104.3 | 2684.6 | 2034.4 |
| 25° | 3585.7 | 3560.0 | 3471.8 | 3386.1 | 3329.6 | 3375.0 | 3435.8 | 3446.9 | 3353.6 | 2918.4 | 2210.9 |
| 27.5° | 4062.0 | 4038.8 | 3939.5 | 3811.0 | 3649.1 | 3570.3 | 3615.7 | 3638.0 | 3598.6 | 3196.8 | 2398.5 |
| 30° | 4508.3 | 4477.4 | 4368.6 | 4209.3 | 4021.7 | 3900.9 | 3849.5 | 3865.0 | 3888.1 | 3526.6 | 2618.6 |
| 32.5° | 4895.4 | 4872.3 | 4742.1 | 4574.2 | 4393.5 | 4267.6 | 4147.6 | 4173.3 | 4229.9 | 3930.1 | 2900.4 |
| 35° | 5223.5 | 5211.5 | 5073.6 | 4906.6 | 4715.6 | 4651.3 | 4548.5 | 4553.7 | 4610.2 | 4417.5 | 3243.9 |
| 37.5° | 5508.8 | 5488.2 | 5363.1 | 5208.1 | 5056.5 | 5046.2 | 5017.9 | 5020.5 | 5049.6 | 4985.4 | 3638.8 |
| 40° | 5688.6 | 5669.8 | 5580.7 | 5484.8 | 5376.8 | 5378.6 | 5525.0 | 5536.2 | 5502.8 | 5543.0 | 4056.0 |
| 42.5° | 5756.3 | 5742.6 | 5694.6 | 5695.5 | 5684.4 | 5734.9 | 6009.9 | 6030.4 | 5910.5 | 5980.7 | 4412.3 |
| 45° | 5639.0 | 5633.0 | 5636.4 | 5759.7 | 5893.4 | 6049.3 | 6406.5 | 6442.5 | 6272.8 | 6271.1 | 4690.7 |
| 47.5° | 5260.3 | 5248.4 | 5348.6 | 5558.4 | 5867.7 | 6170.9 | 6646.3 | 6702.0 | 6526.4 | 6437.3 | 4865.5 |
| 50° | 4518.5 | 4552.8 | 4711.3 | 5026.5 | 5496.8 | 6003.9 | 6643.8 | 6740.5 | 6535.8 | 6422.7 | 4836.3 |
| 52.5° | 3273.0 | 3266.2 | 3613.1 | 4046.6 | 4618.8 | 5469.4 | 6290.8 | 6432.2 | 6307.1 | 6279.7 | 4771.2 |
| 55° | 1780.9 | 1843.4 | 2077.2 | 2651.2 | 3365.6 | 4457.7 | 5484.8 | 5793.2 | 5937.9 | 6227.4 | 4888.6 |
| 57.5° | 654.4 | 681.8 | 828.3 | 1234.4 | 1781.7 | 2771.9 | 4189.6 | 4654.7 | 5101.9 | 6081.8 | 4868.9 |
| 60° | 263.8 | 269.0 | 327.2 | 454.0 | 748.7 | 1410.8 | 2513.2 | 2926.1 | 3347.6 | 4655.6 | 3736.5 |
| 62.5° | 191.9 | 198.7 | 221.9 | 265.5 | 378.6 | 616.7 | 1083.6 | 1260.1 | 1377.4 | 2306.0 | 1840.8 |
| 65° | 155.0 | 160.2 | 179.0 | 198.7 | 250.1 | 331.5 | 349.5 | 336.6 | 334.9 | 596.2 | 422.3 |
| 67.5° | 128.5 | 133.6 | 147.3 | 161.0 | 179.9 | 165.3 | 119.9 | 125.9 | 102.8 | 101.9 | 83.1 |
| 70° | 94.2 | 100.2 | 113.9 | 128.5 | 107.9 | 44.5 | 69.4 | 102.8 | 78.0 | 65.1 | 63.4 |
| 72.5° | 71.1 | 75.4 | 88.2 | 83.9 | 31.7 | 17.1 | 46.3 | 74.5 | 60.0 | 48.0 | 47.1 |
| 75° | 53.1 | 55.7 | 44.5 | 13.7 | 3.4 | 4.3 | 17.1 | 30.8 | 33.4 | 27.4 | 27.4 |
| 77.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 1.7 | 2.6 | 3.4 | 4.3 | 5.1 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P633597
 CATALOG NUMBER: GWS-SA2F-722-U-T2R-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 956.8 | 956.8 | 956.8 | 956.8 | 956.8 | 956.8 | 956.8 | 956.8 | 956.8 | 956.8 | 956.8 |
| 2.5° | 976.5 | 940.5 | 889.1 | 846.3 | 813.8 | 782.1 | 758.1 | 734.1 | 733.2 | 721.3 | 718.7 |
| 5° | 1017.6 | 952.5 | 858.3 | 790.6 | 749.5 | 724.7 | 707.5 | 699.0 | 694.7 | 690.4 | 688.7 |
| 7.5° | 1076.7 | 983.4 | 853.2 | 781.2 | 747.0 | 730.7 | 718.7 | 713.5 | 711.0 | 707.5 | 706.7 |
| 10° | 1149.6 | 1027.9 | 872.0 | 799.2 | 769.2 | 753.8 | 741.0 | 733.2 | 729.0 | 723.0 | 721.3 |
| 12.5° | 1236.9 | 1082.7 | 902.0 | 829.2 | 797.5 | 776.9 | 759.8 | 748.7 | 742.7 | 735.0 | 733.2 |
| 15° | 1331.1 | 1141.8 | 935.4 | 856.6 | 818.9 | 792.4 | 770.9 | 753.8 | 742.7 | 733.2 | 730.7 |
| 17.5° | 1428.8 | 1201.8 | 965.4 | 875.4 | 829.2 | 797.5 | 766.7 | 743.5 | 729.8 | 717.8 | 714.4 |
| 20° | 1538.4 | 1263.5 | 985.1 | 878.9 | 825.8 | 783.8 | 747.8 | 718.7 | 705.0 | 688.7 | 685.3 |
| 22.5° | 1653.2 | 1320.9 | 993.7 | 871.2 | 806.9 | 758.1 | 719.5 | 689.6 | 669.9 | 652.7 | 647.6 |
| 25° | 1764.6 | 1372.3 | 989.4 | 849.7 | 778.6 | 722.1 | 682.7 | 651.9 | 630.5 | 613.3 | 609.0 |
| 27.5° | 1882.8 | 1415.1 | 973.9 | 818.0 | 740.1 | 682.7 | 645.0 | 618.5 | 598.8 | 579.9 | 575.6 |
| 30° | 2015.6 | 1454.5 | 949.1 | 779.5 | 694.7 | 642.4 | 613.3 | 595.3 | 573.9 | 554.2 | 548.2 |
| 32.5° | 2175.8 | 1489.6 | 913.1 | 733.2 | 654.4 | 607.3 | 591.1 | 577.3 | 552.5 | 531.9 | 527.7 |
| 35° | 2359.1 | 1518.7 | 867.7 | 685.3 | 615.0 | 585.1 | 581.6 | 563.6 | 531.1 | 507.1 | 502.0 |
| 37.5° | 2571.5 | 1547.0 | 813.8 | 638.2 | 585.9 | 574.8 | 575.6 | 544.8 | 505.4 | 476.3 | 472.8 |
| 40° | 2800.2 | 1575.3 | 753.8 | 597.0 | 559.4 | 568.8 | 561.1 | 517.4 | 453.1 | 424.9 | 421.4 |
| 42.5° | 3038.3 | 1606.1 | 693.0 | 558.5 | 537.1 | 545.7 | 534.5 | 462.6 | 416.3 | 401.7 | 400.0 |
| 45° | 3253.3 | 1642.9 | 627.0 | 520.0 | 514.8 | 512.2 | 493.4 | 418.9 | 399.2 | 388.9 | 388.0 |
| 47.5° | 3408.4 | 1637.0 | 556.8 | 483.1 | 490.8 | 482.3 | 424.9 | 398.3 | 382.0 | 368.3 | 364.9 |
| 50° | 3380.1 | 1532.4 | 484.0 | 442.0 | 460.0 | 452.3 | 382.0 | 374.3 | 359.8 | 345.2 | 340.1 |
| 52.5° | 3308.2 | 1390.3 | 420.6 | 398.3 | 426.6 | 408.6 | 352.9 | 345.2 | 332.4 | 313.5 | 307.5 |
| 55° | 3346.7 | 1256.6 | 370.9 | 363.2 | 392.3 | 338.4 | 320.4 | 308.4 | 294.7 | 274.1 | 271.5 |
| 57.5° | 3222.5 | 1025.3 | 298.1 | 303.2 | 346.9 | 288.7 | 281.0 | 262.1 | 239.0 | 225.3 | 223.6 |
| 60° | 2230.6 | 550.8 | 186.7 | 192.7 | 251.0 | 242.4 | 251.8 | 234.7 | 206.4 | 193.6 | 191.0 |
| 62.5° | 1024.5 | 221.0 | 101.9 | 97.7 | 131.9 | 164.5 | 215.9 | 214.1 | 179.0 | 158.5 | 156.8 |
| 65° | 248.4 | 101.1 | 72.8 | 68.5 | 74.5 | 98.5 | 140.5 | 168.7 | 144.8 | 120.8 | 118.2 |
| 67.5° | 80.5 | 82.2 | 66.8 | 62.5 | 66.0 | 73.7 | 83.9 | 93.4 | 92.5 | 84.8 | 83.1 |
| 70° | 64.2 | 74.5 | 61.7 | 56.5 | 56.5 | 59.1 | 56.5 | 45.4 | 39.4 | 42.8 | 44.5 |
| 72.5° | 48.0 | 56.5 | 48.8 | 43.7 | 42.0 | 41.1 | 35.1 | 25.7 | 18.0 | 16.3 | 15.4 |
| 75° | 28.3 | 31.7 | 30.0 | 25.7 | 24.0 | 21.4 | 17.1 | 11.1 | 6.0 | 4.3 | 2.6 |
| 77.5° | 5.1 | 6.0 | 6.9 | 5.1 | 4.3 | 3.4 | 2.6 | 0.9 | 0.0 | 0.0 | 0.0 |
| 80° | 0.0 | 0.9 | 0.9 | 0.9 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-10-R4

Test Date: 10/25/2019

Luminaire Tested: SA1C-722-U-5WQ

Data in this report applies to families of products SA1C-722-U-5WQ.

Test Information

Test Method: LM-79-2008 Report
 Number: SP1-1908-441-10-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-722-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2237
 CIE u': 0.2876
 CIE v': 0.5346
 Duv: -0.0006
 CIE x: 0.5005
 CIE y: 0.4134
 CIE z: 0.0860
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 587
 Purity: 74.5
 Rf: 69.8
 Rg: 99.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 72.0 | | |
| R1: | 68.9 | R9: | -17.4 |
| R2: | 83.0 | R10: | 61.3 |
| R3: | 95.2 | R11: | 59.8 |
| R4: | 66.2 | R12: | 50.5 |
| R5: | 65.9 | R13: | 71.1 |
| R6: | 76.3 | R14: | 96.9 |
| R7: | 76.7 | | |
| R8: | 43.8 | | |



Test Conditions

Stabilization Time: 71M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.7/41%
 Sphere Temperature (°C): 25.6

REPORT NUMBER: SP1-1908-441-10-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-10-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2200K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-10-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 1768 | NR | 490 | 5206 | NR | 620 | 130919 | NR | 750 | 8553 | NR | 880 | 2713 | NR |
| 365 | 1569 | NR | 495 | 7286 | NR | 625 | 125335 | NR | 755 | 7696 | NR | 885 | 2316 | NR |
| 370 | 1594 | NR | 500 | 10654 | NR | 630 | 118388 | NR | 760 | 6978 | NR | 890 | 2539 | NR |
| 375 | 1744 | NR | 505 | 15189 | NR | 635 | 111855 | NR | 765 | 6377 | NR | 895 | 1933 | NR |
| 380 | 1659 | NR | 510 | 20541 | NR | 640 | 104062 | NR | 770 | 5600 | NR | 900 | 2216 | NR |
| 385 | 1504 | NR | 515 | 26492 | NR | 645 | 96365 | NR | 775 | 5000 | NR | 905 | 2067 | NR |
| 390 | 1541 | NR | 520 | 32294 | NR | 650 | 88651 | NR | 780 | 4709 | NR | 910 | 1959 | NR |
| 395 | 1355 | NR | 525 | 38123 | NR | 655 | 81152 | NR | 785 | 4305 | NR | 915 | 1874 | NR |
| 400 | 1243 | NR | 530 | 43232 | NR | 660 | 73523 | NR | 790 | 4040 | NR | 920 | 1484 | NR |
| 405 | 1417 | NR | 535 | 48012 | NR | 665 | 66123 | NR | 795 | 3642 | NR | 925 | 1914 | NR |
| 410 | 2147 | NR | 540 | 52623 | NR | 670 | 58677 | NR | 800 | 3594 | NR | 930 | 1948 | NR |
| 415 | 3837 | NR | 545 | 57516 | NR | 675 | 52349 | NR | 805 | 3190 | NR | 935 | 2079 | NR |
| 420 | 7159 | NR | 550 | 62613 | NR | 680 | 46159 | NR | 810 | 3241 | NR | 940 | 2263 | NR |
| 425 | 12599 | NR | 555 | 68554 | NR | 685 | 40525 | NR | 815 | 2732 | NR | 945 | 1688 | NR |
| 430 | 19019 | NR | 560 | 75325 | NR | 690 | 35615 | NR | 820 | 2612 | NR | 950 | 1560 | NR |
| 435 | 24875 | NR | 565 | 82533 | NR | 695 | 31158 | NR | 825 | 2966 | NR | 955 | 2826 | NR |
| 440 | 29103 | NR | 570 | 90909 | NR | 700 | 27409 | NR | 830 | 2574 | NR | 960 | 1477 | NR |
| 445 | 29901 | NR | 575 | 99621 | NR | 705 | 24204 | NR | 835 | 2633 | NR | 965 | 1568 | NR |
| 450 | 24862 | NR | 580 | 108484 | NR | 710 | 21558 | NR | 840 | 2526 | NR | 970 | 2030 | NR |
| 455 | 15942 | NR | 585 | 116679 | NR | 715 | 19222 | NR | 845 | 2631 | NR | 975 | 1986 | NR |
| 460 | 9916 | NR | 590 | 123752 | NR | 720 | 17310 | NR | 850 | 2079 | NR | 980 | 2540 | NR |
| 465 | 7051 | NR | 595 | 129324 | NR | 725 | 15280 | NR | 855 | 2309 | NR | 985 | 1139 | NR |
| 470 | 5227 | NR | 600 | 134082 | NR | 730 | 13282 | NR | 860 | 2528 | NR | 990 | 2018 | NR |
| 475 | 4257 | NR | 605 | 135698 | NR | 735 | 11753 | NR | 865 | 2121 | NR | 995 | 3445 | NR |
| 480 | 4052 | NR | 610 | 135144 | NR | 740 | 10654 | NR | 870 | 2751 | NR | 1000 | 3704 | NR |
| 485 | 4298 | NR | 615 | 134180 | NR | 745 | 9451 | NR | 875 | 2317 | NR | | | |

REPORT NUMBER: SP1-1908-441-10-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 4696.9

S/P: 0.85

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 1768 | NR | 490 | 5206 | NR | 620 | 130919 | NR | 750 | 8553 | NR | 880 | 2713 | NR |
| 365 | 1569 | NR | 495 | 7286 | NR | 625 | 125335 | NR | 755 | 7696 | NR | 885 | 2316 | NR |
| 370 | 1594 | NR | 500 | 10654 | NR | 630 | 118388 | NR | 760 | 6978 | NR | 890 | 2539 | NR |
| 375 | 1744 | NR | 505 | 15189 | NR | 635 | 111855 | NR | 765 | 6377 | NR | 895 | 1933 | NR |
| 380 | 1659 | NR | 510 | 20541 | NR | 640 | 104062 | NR | 770 | 5600 | NR | 900 | 2216 | NR |
| 385 | 1504 | NR | 515 | 26492 | NR | 645 | 96365 | NR | 775 | 5000 | NR | 905 | 2067 | NR |
| 390 | 1541 | NR | 520 | 32294 | NR | 650 | 88651 | NR | 780 | 4709 | NR | 910 | 1959 | NR |
| 395 | 1355 | NR | 525 | 38123 | NR | 655 | 81152 | NR | 785 | 4305 | NR | 915 | 1874 | NR |
| 400 | 1243 | NR | 530 | 43232 | NR | 660 | 73523 | NR | 790 | 4040 | NR | 920 | 1484 | NR |
| 405 | 1417 | NR | 535 | 48012 | NR | 665 | 66123 | NR | 795 | 3642 | NR | 925 | 1914 | NR |
| 410 | 2147 | NR | 540 | 52623 | NR | 670 | 58677 | NR | 800 | 3594 | NR | 930 | 1948 | NR |
| 415 | 3837 | NR | 545 | 57516 | NR | 675 | 52349 | NR | 805 | 3190 | NR | 935 | 2079 | NR |
| 420 | 7159 | NR | 550 | 62613 | NR | 680 | 46159 | NR | 810 | 3241 | NR | 940 | 2263 | NR |
| 425 | 12599 | NR | 555 | 68554 | NR | 685 | 40525 | NR | 815 | 2732 | NR | 945 | 1688 | NR |
| 430 | 19019 | NR | 560 | 75325 | NR | 690 | 35615 | NR | 820 | 2612 | NR | 950 | 1560 | NR |
| 435 | 24875 | NR | 565 | 82533 | NR | 695 | 31158 | NR | 825 | 2966 | NR | 955 | 2826 | NR |
| 440 | 29103 | NR | 570 | 90909 | NR | 700 | 27409 | NR | 830 | 2574 | NR | 960 | 1477 | NR |
| 445 | 29901 | NR | 575 | 99621 | NR | 705 | 24204 | NR | 835 | 2633 | NR | 965 | 1568 | NR |
| 450 | 24862 | NR | 580 | 108484 | NR | 710 | 21558 | NR | 840 | 2526 | NR | 970 | 2030 | NR |
| 455 | 15942 | NR | 585 | 116679 | NR | 715 | 19222 | NR | 845 | 2631 | NR | 975 | 1986 | NR |
| 460 | 9916 | NR | 590 | 123752 | NR | 720 | 17310 | NR | 850 | 2079 | NR | 980 | 2540 | NR |
| 465 | 7051 | NR | 595 | 129324 | NR | 725 | 15280 | NR | 855 | 2309 | NR | 985 | 1139 | NR |
| 470 | 5227 | NR | 600 | 134082 | NR | 730 | 13282 | NR | 860 | 2528 | NR | 990 | 2018 | NR |
| 475 | 4257 | NR | 605 | 135698 | NR | 735 | 11753 | NR | 865 | 2121 | NR | 995 | 3445 | NR |
| 480 | 4052 | NR | 610 | 135144 | NR | 740 | 10654 | NR | 870 | 2751 | NR | 1000 | 3704 | NR |
| 485 | 4298 | NR | 615 | 134180 | NR | 745 | 9451 | NR | 875 | 2317 | NR | | | |

REPORT NUMBER: SP1-1908-441-10-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 1470.8 M/P: 0.27

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 1768 | NR | 490 | 5206 | NR | 620 | 130919 | NR | 750 | 8553 | NR | 880 | 2713 | NR |
| 365 | 1569 | NR | 495 | 7286 | NR | 625 | 125335 | NR | 755 | 7696 | NR | 885 | 2316 | NR |
| 370 | 1594 | NR | 500 | 10654 | NR | 630 | 118388 | NR | 760 | 6978 | NR | 890 | 2539 | NR |
| 375 | 1744 | NR | 505 | 15189 | NR | 635 | 111855 | NR | 765 | 6377 | NR | 895 | 1933 | NR |
| 380 | 1659 | NR | 510 | 20541 | NR | 640 | 104062 | NR | 770 | 5600 | NR | 900 | 2216 | NR |
| 385 | 1504 | NR | 515 | 26492 | NR | 645 | 96365 | NR | 775 | 5000 | NR | 905 | 2067 | NR |
| 390 | 1541 | NR | 520 | 32294 | NR | 650 | 88651 | NR | 780 | 4709 | NR | 910 | 1959 | NR |
| 395 | 1355 | NR | 525 | 38123 | NR | 655 | 81152 | NR | 785 | 4305 | NR | 915 | 1874 | NR |
| 400 | 1243 | NR | 530 | 43232 | NR | 660 | 73523 | NR | 790 | 4040 | NR | 920 | 1484 | NR |
| 405 | 1417 | NR | 535 | 48012 | NR | 665 | 66123 | NR | 795 | 3642 | NR | 925 | 1914 | NR |
| 410 | 2147 | NR | 540 | 52623 | NR | 670 | 58677 | NR | 800 | 3594 | NR | 930 | 1948 | NR |
| 415 | 3837 | NR | 545 | 57516 | NR | 675 | 52349 | NR | 805 | 3190 | NR | 935 | 2079 | NR |
| 420 | 7159 | NR | 550 | 62613 | NR | 680 | 46159 | NR | 810 | 3241 | NR | 940 | 2263 | NR |
| 425 | 12599 | NR | 555 | 68554 | NR | 685 | 40525 | NR | 815 | 2732 | NR | 945 | 1688 | NR |
| 430 | 19019 | NR | 560 | 75325 | NR | 690 | 35615 | NR | 820 | 2612 | NR | 950 | 1560 | NR |
| 435 | 24875 | NR | 565 | 82533 | NR | 695 | 31158 | NR | 825 | 2966 | NR | 955 | 2826 | NR |
| 440 | 29103 | NR | 570 | 90909 | NR | 700 | 27409 | NR | 830 | 2574 | NR | 960 | 1477 | NR |
| 445 | 29901 | NR | 575 | 99621 | NR | 705 | 24204 | NR | 835 | 2633 | NR | 965 | 1568 | NR |
| 450 | 24862 | NR | 580 | 108484 | NR | 710 | 21558 | NR | 840 | 2526 | NR | 970 | 2030 | NR |
| 455 | 15942 | NR | 585 | 116679 | NR | 715 | 19222 | NR | 845 | 2631 | NR | 975 | 1986 | NR |
| 460 | 9916 | NR | 590 | 123752 | NR | 720 | 17310 | NR | 850 | 2079 | NR | 980 | 2540 | NR |
| 465 | 7051 | NR | 595 | 129324 | NR | 725 | 15280 | NR | 855 | 2309 | NR | 985 | 1139 | NR |
| 470 | 5227 | NR | 600 | 134082 | NR | 730 | 13282 | NR | 860 | 2528 | NR | 990 | 2018 | NR |
| 475 | 4257 | NR | 605 | 135698 | NR | 735 | 11753 | NR | 865 | 2121 | NR | 995 | 3445 | NR |
| 480 | 4052 | NR | 610 | 135144 | NR | 740 | 10654 | NR | 870 | 2751 | NR | 1000 | 3704 | NR |
| 485 | 4298 | NR | 615 | 134180 | NR | 745 | 9451 | NR | 875 | 2317 | NR | | | |

REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Summary

$R_f = 69.8$
 $R_g = 99.2$
 $CIE R_a = 72.0$
 $R_9 = -17.4$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 87 | CES26 = 56 | CES51 = 74 | CES76 = 56 |
| CES02 = 65 | CES27 = 76 | CES52 = 76 | CES77 = 81 |
| CES03 = 32 | CES28 = 83 | CES53 = 65 | CES78 = 63 |
| CES04 = 72 | CES29 = 46 | CES54 = 78 | CES79 = 84 |
| CES05 = 52 | CES30 = 48 | CES55 = 75 | CES80 = 84 |
| CES06 = 52 | CES31 = 51 | CES56 = 65 | CES81 = 63 |
| CES07 = 44 | CES32 = 51 | CES57 = 62 | CES82 = 92 |
| CES08 = 42 | CES33 = 53 | CES58 = 66 | CES83 = 83 |
| CES09 = 29 | CES34 = 70 | CES59 = 84 | CES84 = 92 |
| CES10 = 78 | CES35 = 85 | CES60 = 90 | CES85 = 81 |
| CES11 = 61 | CES36 = 78 | CES61 = 84 | CES86 = 56 |
| CES12 = 68 | CES37 = 80 | CES62 = 70 | CES87 = 78 |
| CES13 = 45 | CES38 = 53 | CES63 = 68 | CES88 = 72 |
| CES14 = 75 | CES39 = 90 | CES64 = 69 | CES89 = 62 |
| CES15 = 72 | CES40 = 84 | CES65 = 67 | CES90 = 67 |
| CES16 = 49 | CES41 = 75 | CES66 = 64 | CES91 = 90 |
| CES17 = 51 | CES42 = 79 | CES67 = 63 | CES92 = 67 |
| CES18 = 57 | CES43 = 64 | CES68 = 69 | CES93 = 79 |
| CES19 = 74 | CES44 = 98 | CES69 = 80 | CES94 = 52 |
| CES20 = 68 | CES45 = 73 | CES70 = 63 | CES95 = 76 |
| CES21 = 89 | CES46 = 67 | CES71 = 63 | CES96 = 78 |
| CES22 = 81 | CES47 = 60 | CES72 = 87 | CES97 = 77 |
| CES23 = 92 | CES48 = 48 | CES73 = 56 | CES98 = 71 |
| CES24 = 92 | CES49 = 64 | CES74 = 87 | CES99 = 65 |
| CES25 = 74 | CES50 = 74 | CES75 = 66 | |



REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Measure Comparisons



(END OF REPORT)