

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P635061

Luminaire Tested: GWS-SA3D-722-U-SL2-W-HSS

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P635061
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-30)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA3D-722-U-SL2-W-HSS
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II SPILL LIGHT ELIMINATOR OPTICS WITH HOUSE SIDE SHIELD
Light Source: (48) 2200K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10275.8 lumens
Efficiency: N/A
Efficacy: 85.1 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 120.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P635061
 CATALOG NUMBER: GWS-SA3D-722-U-SL2-W-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 6.2 fc
 Type II - Short - N/A

REPORT NUMBER: P635061
CATALOG NUMBER: GWS-SA3D-722-U-SL2-W-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 65-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P635061

CATALOG NUMBER: GWS-SA3D-722-U-SL2-W-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 1283.1 | 0.0 | 1283.1 |
| | % Fixture | 12.5 | 0.0 | 12.5 |
| Street Side | Lumens | 8992.7 | 0.0 | 8992.7 |
| | % Fixture | 87.5 | 0.0 | 87.5 |
| Total | Lumens | 10275.8 | 0.0 | 10275.8 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 207.0 | 2.0 |
| 10°-20° | 465.3 | 4.5 |
| 20°-30° | 664.9 | 6.5 |
| 30°-40° | 967.3 | 9.4 |
| 40°-50° | 1515.0 | 14.7 |
| 50°-60° | 2363.5 | 23.0 |
| 60°-70° | 2596.1 | 25.3 |
| 70°-80° | 1381.7 | 13.4 |
| 80°-90° | 115.0 | 1.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 10275.8 | 100.0 |
| 0°-180° | 10275.8 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P635061

CATALOG NUMBER: GWS-SA3D-722-U-SL2-W-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 924.8 | 9.0 | | | |
| FM (30°-60°) | 4373.2 | 42.6 | | | |
| FH (60°-80°) | 3585.9 | 34.9 | | | G2/5000 |
| FVH (80°-90°) | 108.9 | 1.1 | | | G2/225 |
| BL (0°-30°) | 412.4 | 4.0 | B1/500 | | |
| BM (30°-60°) | 472.6 | 4.6 | B1/1000 | | |
| BH (60°-80°) | 391.9 | 3.8 | B1/500 | | G1/500 |
| BVH (80°-90°) | 6.1 | 0.1 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2
 Type II Short





REPORT NUMBER: P635061

CATALOG NUMBER: GWS-SA3D-722-U-SL2-W-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 66° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|---------|---------|--------|--------|
| 0° | 2492.2 | 2492.2 | 2492.2 | 2492.2 | 2492.2 | 2492.2 | 2492.2 | 2492.2 | 2492.2 | 2492.2 | 2492.2 |
| 2.5° | 2405.8 | 2413.2 | 2403.0 | 2428.1 | 2432.7 | 2460.6 | 2476.4 | 2487.6 | 2486.6 | 2500.6 | 2500.6 |
| 5° | 2264.5 | 2272.0 | 2266.4 | 2293.3 | 2314.7 | 2358.4 | 2394.6 | 2436.5 | 2438.3 | 2481.1 | 2496.9 |
| 7.5° | 2144.7 | 2145.6 | 2145.6 | 2179.1 | 2206.9 | 2260.8 | 2314.7 | 2378.8 | 2386.3 | 2452.2 | 2494.1 |
| 10° | 2046.2 | 2049.0 | 2049.9 | 2088.0 | 2118.7 | 2183.7 | 2252.5 | 2329.6 | 2338.0 | 2427.2 | 2492.2 |
| 12.5° | 1978.3 | 1979.3 | 1983.0 | 2022.9 | 2056.4 | 2124.2 | 2193.9 | 2282.2 | 2293.3 | 2398.4 | 2483.8 |
| 15° | 1945.8 | 1944.0 | 1945.8 | 1979.3 | 2012.7 | 2077.8 | 2149.3 | 2244.1 | 2256.2 | 2374.2 | 2484.8 |
| 17.5° | 1944.0 | 1941.2 | 1939.3 | 1964.4 | 1985.8 | 2043.4 | 2115.9 | 2219.0 | 2232.0 | 2363.0 | 2495.0 |
| 20° | 1970.9 | 1969.0 | 1959.8 | 1970.9 | 1975.6 | 2022.9 | 2094.5 | 2199.5 | 2212.5 | 2361.2 | 2517.3 |
| 22.5° | 2041.5 | 2036.9 | 2022.9 | 2012.7 | 1987.6 | 2015.5 | 2079.6 | 2185.6 | 2200.4 | 2365.8 | 2546.1 |
| 25° | 2146.5 | 2144.7 | 2127.0 | 2101.9 | 2037.8 | 2026.7 | 2080.6 | 2185.6 | 2199.5 | 2371.4 | 2576.8 |
| 27.5° | 2304.5 | 2293.3 | 2271.0 | 2227.4 | 2135.4 | 2070.3 | 2099.1 | 2191.1 | 2205.1 | 2378.8 | 2601.9 |
| 30° | 2465.3 | 2464.3 | 2456.9 | 2412.3 | 2275.7 | 2154.0 | 2138.2 | 2206.0 | 2219.0 | 2385.3 | 2625.1 |
| 32.5° | 2631.6 | 2634.4 | 2653.0 | 2618.6 | 2469.0 | 2278.5 | 2208.8 | 2236.7 | 2246.0 | 2398.4 | 2645.5 |
| 35° | 2789.6 | 2795.1 | 2844.4 | 2856.5 | 2704.1 | 2467.1 | 2324.0 | 2298.0 | 2298.9 | 2427.2 | 2672.5 |
| 37.5° | 2941.0 | 2959.6 | 3038.6 | 3097.1 | 2996.8 | 2695.7 | 2490.3 | 2402.1 | 2394.6 | 2484.8 | 2713.4 |
| 40° | 3112.9 | 3148.2 | 3247.7 | 3347.1 | 3315.5 | 2997.7 | 2717.1 | 2561.9 | 2546.1 | 2590.7 | 2786.8 |
| 42.5° | 3303.4 | 3341.5 | 3473.5 | 3612.9 | 3627.7 | 3362.9 | 3000.5 | 2795.1 | 2768.2 | 2769.1 | 2924.3 |
| 45° | 3507.9 | 3559.0 | 3712.3 | 3913.0 | 4003.1 | 3769.9 | 3349.9 | 3110.1 | 3083.2 | 3043.2 | 3145.5 |
| 47.5° | 3776.4 | 3821.0 | 3968.8 | 4200.1 | 4373.0 | 4206.6 | 3808.0 | 3515.3 | 3466.0 | 3407.5 | 3489.3 |
| 50° | 4007.8 | 4046.8 | 4174.1 | 4464.0 | 4823.7 | 4769.8 | 4327.4 | 4021.7 | 3974.3 | 3874.9 | 3942.7 |
| 52.5° | 4058.9 | 4089.6 | 4206.6 | 4532.8 | 5168.4 | 5480.6 | 4964.0 | 4634.1 | 4600.6 | 4416.6 | 4442.7 |
| 55° | 3829.4 | 3875.8 | 3980.8 | 4343.2 | 5258.5 | 6175.7 | 5790.1 | 5324.5 | 5254.8 | 4961.2 | 5007.6 |
| 57.5° | 3249.5 | 3332.2 | 3430.7 | 3901.9 | 5014.1 | 6545.5 | 6944.2 | 6055.8 | 5992.6 | 5485.3 | 5486.2 |
| 60° | 2381.6 | 2448.5 | 2514.5 | 2945.7 | 4434.3 | 6520.4 | 7991.4 | 6877.3 | 6762.0 | 5913.6 | 5897.8 |
| 62.5° | 1732.1 | 1766.5 | 1765.5 | 1918.9 | 3045.1 | 6091.1 | 8541.5 | 8115.0 | 7846.5 | 6371.8 | 6281.6 |
| 65° | 1362.3 | 1361.3 | 1401.3 | 1451.5 | 1700.5 | 4701.9 | 8609.4 | 9922.4 | 9632.4 | 6986.0 | 6798.3 |
| 67.5° | 1060.3 | 1080.7 | 1120.7 | 1268.4 | 1277.7 | 2460.6 | 8012.8 | 11040.2 | 11034.7 | 7923.6 | 7403.2 |
| 70° | 817.7 | 845.6 | 902.3 | 1117.9 | 1180.1 | 1377.1 | 5995.4 | 10686.2 | 10776.3 | 8342.7 | 6974.8 |
| 72.5° | 525.0 | 523.2 | 606.8 | 903.2 | 1133.7 | 1147.6 | 3315.5 | 8488.6 | 8590.8 | 7556.5 | 5639.5 |
| 75° | 293.6 | 295.5 | 342.9 | 552.9 | 1056.5 | 1079.8 | 1642.0 | 6053.0 | 6133.9 | 5891.3 | 4333.0 |
| 77.5° | 115.2 | 118.9 | 160.8 | 290.9 | 696.9 | 964.5 | 975.7 | 4127.7 | 4139.7 | 3651.0 | 2657.6 |
| 80° | 46.5 | 49.2 | 81.8 | 180.3 | 424.7 | 649.5 | 696.9 | 2431.8 | 2382.6 | 1413.4 | 773.1 |
| 82.5° | 13.9 | 14.9 | 32.5 | 102.2 | 222.1 | 461.8 | 470.2 | 933.0 | 880.9 | 303.9 | 197.0 |
| 85° | 0.9 | 0.9 | 7.4 | 31.6 | 79.0 | 116.2 | 313.2 | 303.9 | 269.5 | 76.2 | 87.3 |
| 87.5° | 0.0 | 0.0 | 0.9 | 0.9 | 1.9 | 3.7 | 33.5 | 55.8 | 56.7 | 13.9 | 39.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P635061
 CATALOG NUMBER: GWS-SA3D-722-U-SL2-W-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2492.2 | 2492.2 | 2492.2 | 2492.2 | 2492.2 | 2492.2 | 2492.2 | 2492.2 | 2492.2 | 2492.2 | 2492.2 |
| 2.5° | 2500.6 | 2467.1 | 2464.3 | 2438.3 | 2412.3 | 2379.8 | 2341.7 | 2313.8 | 2294.3 | 2259.9 | 2253.4 |
| 5° | 2496.9 | 2452.2 | 2410.4 | 2336.1 | 2253.4 | 2164.2 | 2086.1 | 2013.6 | 1968.1 | 1937.5 | 1924.4 |
| 7.5° | 2489.4 | 2432.7 | 2336.1 | 2195.8 | 2057.3 | 1901.2 | 1779.5 | 1668.0 | 1591.8 | 1547.2 | 1527.7 |
| 10° | 2483.8 | 2407.6 | 2250.6 | 2037.8 | 1823.2 | 1607.6 | 1422.7 | 1257.3 | 1165.3 | 1092.8 | 1080.7 |
| 12.5° | 2472.7 | 2371.4 | 2141.0 | 1852.9 | 1576.0 | 1289.8 | 1053.8 | 851.2 | 710.9 | 647.7 | 625.4 |
| 15° | 2461.5 | 2333.3 | 2031.3 | 1657.8 | 1306.5 | 953.4 | 667.2 | 472.1 | 375.4 | 345.7 | 343.8 |
| 17.5° | 2459.7 | 2298.9 | 1912.4 | 1472.8 | 1024.0 | 624.4 | 380.1 | 305.7 | 285.3 | 277.8 | 277.8 |
| 20° | 2465.3 | 2270.1 | 1795.3 | 1260.0 | 746.2 | 380.1 | 283.4 | 264.8 | 252.8 | 246.2 | 246.2 |
| 22.5° | 2470.8 | 2240.4 | 1682.8 | 1045.4 | 495.3 | 277.8 | 250.0 | 234.2 | 220.2 | 212.8 | 209.1 |
| 25° | 2474.5 | 2207.9 | 1558.3 | 829.8 | 323.4 | 241.6 | 219.3 | 198.9 | 182.1 | 172.8 | 172.8 |
| 27.5° | 2473.6 | 2168.8 | 1432.9 | 618.9 | 250.9 | 214.7 | 187.7 | 166.3 | 149.6 | 139.4 | 140.3 |
| 30° | 2466.2 | 2126.1 | 1302.8 | 432.1 | 219.3 | 187.7 | 160.8 | 138.5 | 121.7 | 113.4 | 112.4 |
| 32.5° | 2460.6 | 2080.6 | 1152.2 | 303.9 | 197.0 | 164.5 | 136.6 | 115.2 | 101.3 | 94.8 | 93.9 |
| 35° | 2454.1 | 2036.0 | 1009.1 | 231.4 | 177.5 | 142.2 | 115.2 | 97.6 | 86.4 | 80.8 | 80.8 |
| 37.5° | 2456.0 | 1989.5 | 854.0 | 198.9 | 158.0 | 123.6 | 98.5 | 83.6 | 74.3 | 68.8 | 67.8 |
| 40° | 2484.8 | 1961.6 | 701.6 | 180.3 | 140.3 | 106.9 | 85.5 | 72.5 | 63.2 | 57.6 | 56.7 |
| 42.5° | 2556.3 | 1962.5 | 555.7 | 166.3 | 124.5 | 91.1 | 74.3 | 62.3 | 53.9 | 47.4 | 46.5 |
| 45° | 2699.4 | 2001.6 | 426.5 | 151.5 | 107.8 | 79.0 | 64.1 | 53.0 | 44.6 | 39.0 | 38.1 |
| 47.5° | 2933.6 | 2117.7 | 323.4 | 138.5 | 93.9 | 68.8 | 54.8 | 44.6 | 37.2 | 32.5 | 31.6 |
| 50° | 3306.2 | 2327.7 | 254.6 | 122.7 | 79.0 | 59.5 | 46.5 | 37.2 | 30.7 | 26.0 | 25.1 |
| 52.5° | 3754.1 | 2642.7 | 218.4 | 108.7 | 67.8 | 52.0 | 40.0 | 30.7 | 25.1 | 21.4 | 20.4 |
| 55° | 4268.9 | 3019.1 | 201.6 | 94.8 | 57.6 | 44.6 | 32.5 | 25.1 | 20.4 | 17.7 | 15.8 |
| 57.5° | 4741.0 | 3358.3 | 200.7 | 80.8 | 49.2 | 38.1 | 26.9 | 21.4 | 17.7 | 13.9 | 13.0 |
| 60° | 5200.9 | 3641.7 | 188.6 | 66.9 | 42.7 | 31.6 | 23.2 | 17.7 | 14.9 | 12.1 | 11.2 |
| 62.5° | 5618.1 | 3872.1 | 158.0 | 53.9 | 36.2 | 26.0 | 19.5 | 15.8 | 13.0 | 10.2 | 10.2 |
| 65° | 6142.2 | 4165.8 | 120.8 | 43.7 | 29.7 | 21.4 | 16.7 | 13.9 | 12.1 | 9.3 | 9.3 |
| 67.5° | 6684.0 | 4320.9 | 86.4 | 36.2 | 24.2 | 18.6 | 14.9 | 13.0 | 10.2 | 8.4 | 8.4 |
| 70° | 6054.0 | 3651.0 | 62.3 | 29.7 | 20.4 | 15.8 | 13.0 | 12.1 | 10.2 | 8.4 | 7.4 |
| 72.5° | 4727.9 | 2632.5 | 46.5 | 23.2 | 17.7 | 14.9 | 12.1 | 11.2 | 9.3 | 7.4 | 7.4 |
| 75° | 3506.0 | 1535.1 | 35.3 | 18.6 | 13.9 | 12.1 | 12.1 | 11.2 | 9.3 | 7.4 | 6.5 |
| 77.5° | 1905.9 | 535.2 | 26.9 | 14.9 | 11.2 | 9.3 | 10.2 | 10.2 | 8.4 | 6.5 | 5.6 |
| 80° | 504.6 | 146.8 | 18.6 | 11.2 | 9.3 | 7.4 | 7.4 | 9.3 | 7.4 | 5.6 | 5.6 |
| 82.5° | 146.8 | 42.7 | 13.0 | 9.3 | 7.4 | 6.5 | 6.5 | 6.5 | 5.6 | 4.6 | 3.7 |
| 85° | 71.6 | 15.8 | 9.3 | 7.4 | 6.5 | 5.6 | 4.6 | 4.6 | 3.7 | 2.8 | 2.8 |
| 87.5° | 31.6 | 6.5 | 7.4 | 6.5 | 6.5 | 4.6 | 3.7 | 2.8 | 2.8 | 1.9 | 0.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-10-R4

Test Date: 10/25/2019

Luminaire Tested: SA1C-722-U-5WQ

Data in this report applies to families of products SA1C-722-U-5WQ.

Test Information

Test Method: LM-79-2008 Report
 Number: SP1-1908-441-10-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-722-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2237
 CIE u': 0.2876
 CIE v': 0.5346
 Duv: -0.0006
 CIE x: 0.5005
 CIE y: 0.4134
 CIE z: 0.0860
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 587
 Purity: 74.5
 Rf: 69.8
 Rg: 99.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 72.0 | | |
| R1: | 68.9 | R9: | -17.4 |
| R2: | 83.0 | R10: | 61.3 |
| R3: | 95.2 | R11: | 59.8 |
| R4: | 66.2 | R12: | 50.5 |
| R5: | 65.9 | R13: | 71.1 |
| R6: | 76.3 | R14: | 96.9 |
| R7: | 76.7 | | |
| R8: | 43.8 | | |



Test Conditions

Stabilization Time: 71M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.7/41%
 Sphere Temperature (°C): 25.6

REPORT NUMBER: SP1-1908-441-10-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-10-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2200K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-10-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 1768 | NR | 490 | 5206 | NR | 620 | 130919 | NR | 750 | 8553 | NR | 880 | 2713 | NR |
| 365 | 1569 | NR | 495 | 7286 | NR | 625 | 125335 | NR | 755 | 7696 | NR | 885 | 2316 | NR |
| 370 | 1594 | NR | 500 | 10654 | NR | 630 | 118388 | NR | 760 | 6978 | NR | 890 | 2539 | NR |
| 375 | 1744 | NR | 505 | 15189 | NR | 635 | 111855 | NR | 765 | 6377 | NR | 895 | 1933 | NR |
| 380 | 1659 | NR | 510 | 20541 | NR | 640 | 104062 | NR | 770 | 5600 | NR | 900 | 2216 | NR |
| 385 | 1504 | NR | 515 | 26492 | NR | 645 | 96365 | NR | 775 | 5000 | NR | 905 | 2067 | NR |
| 390 | 1541 | NR | 520 | 32294 | NR | 650 | 88651 | NR | 780 | 4709 | NR | 910 | 1959 | NR |
| 395 | 1355 | NR | 525 | 38123 | NR | 655 | 81152 | NR | 785 | 4305 | NR | 915 | 1874 | NR |
| 400 | 1243 | NR | 530 | 43232 | NR | 660 | 73523 | NR | 790 | 4040 | NR | 920 | 1484 | NR |
| 405 | 1417 | NR | 535 | 48012 | NR | 665 | 66123 | NR | 795 | 3642 | NR | 925 | 1914 | NR |
| 410 | 2147 | NR | 540 | 52623 | NR | 670 | 58677 | NR | 800 | 3594 | NR | 930 | 1948 | NR |
| 415 | 3837 | NR | 545 | 57516 | NR | 675 | 52349 | NR | 805 | 3190 | NR | 935 | 2079 | NR |
| 420 | 7159 | NR | 550 | 62613 | NR | 680 | 46159 | NR | 810 | 3241 | NR | 940 | 2263 | NR |
| 425 | 12599 | NR | 555 | 68554 | NR | 685 | 40525 | NR | 815 | 2732 | NR | 945 | 1688 | NR |
| 430 | 19019 | NR | 560 | 75325 | NR | 690 | 35615 | NR | 820 | 2612 | NR | 950 | 1560 | NR |
| 435 | 24875 | NR | 565 | 82533 | NR | 695 | 31158 | NR | 825 | 2966 | NR | 955 | 2826 | NR |
| 440 | 29103 | NR | 570 | 90909 | NR | 700 | 27409 | NR | 830 | 2574 | NR | 960 | 1477 | NR |
| 445 | 29901 | NR | 575 | 99621 | NR | 705 | 24204 | NR | 835 | 2633 | NR | 965 | 1568 | NR |
| 450 | 24862 | NR | 580 | 108484 | NR | 710 | 21558 | NR | 840 | 2526 | NR | 970 | 2030 | NR |
| 455 | 15942 | NR | 585 | 116679 | NR | 715 | 19222 | NR | 845 | 2631 | NR | 975 | 1986 | NR |
| 460 | 9916 | NR | 590 | 123752 | NR | 720 | 17310 | NR | 850 | 2079 | NR | 980 | 2540 | NR |
| 465 | 7051 | NR | 595 | 129324 | NR | 725 | 15280 | NR | 855 | 2309 | NR | 985 | 1139 | NR |
| 470 | 5227 | NR | 600 | 134082 | NR | 730 | 13282 | NR | 860 | 2528 | NR | 990 | 2018 | NR |
| 475 | 4257 | NR | 605 | 135698 | NR | 735 | 11753 | NR | 865 | 2121 | NR | 995 | 3445 | NR |
| 480 | 4052 | NR | 610 | 135144 | NR | 740 | 10654 | NR | 870 | 2751 | NR | 1000 | 3704 | NR |
| 485 | 4298 | NR | 615 | 134180 | NR | 745 | 9451 | NR | 875 | 2317 | NR | | | |

REPORT NUMBER: SP1-1908-441-10-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 4696.9

S/P: 0.85

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 1768 | NR | 490 | 5206 | NR | 620 | 130919 | NR | 750 | 8553 | NR | 880 | 2713 | NR |
| 365 | 1569 | NR | 495 | 7286 | NR | 625 | 125335 | NR | 755 | 7696 | NR | 885 | 2316 | NR |
| 370 | 1594 | NR | 500 | 10654 | NR | 630 | 118388 | NR | 760 | 6978 | NR | 890 | 2539 | NR |
| 375 | 1744 | NR | 505 | 15189 | NR | 635 | 111855 | NR | 765 | 6377 | NR | 895 | 1933 | NR |
| 380 | 1659 | NR | 510 | 20541 | NR | 640 | 104062 | NR | 770 | 5600 | NR | 900 | 2216 | NR |
| 385 | 1504 | NR | 515 | 26492 | NR | 645 | 96365 | NR | 775 | 5000 | NR | 905 | 2067 | NR |
| 390 | 1541 | NR | 520 | 32294 | NR | 650 | 88651 | NR | 780 | 4709 | NR | 910 | 1959 | NR |
| 395 | 1355 | NR | 525 | 38123 | NR | 655 | 81152 | NR | 785 | 4305 | NR | 915 | 1874 | NR |
| 400 | 1243 | NR | 530 | 43232 | NR | 660 | 73523 | NR | 790 | 4040 | NR | 920 | 1484 | NR |
| 405 | 1417 | NR | 535 | 48012 | NR | 665 | 66123 | NR | 795 | 3642 | NR | 925 | 1914 | NR |
| 410 | 2147 | NR | 540 | 52623 | NR | 670 | 58677 | NR | 800 | 3594 | NR | 930 | 1948 | NR |
| 415 | 3837 | NR | 545 | 57516 | NR | 675 | 52349 | NR | 805 | 3190 | NR | 935 | 2079 | NR |
| 420 | 7159 | NR | 550 | 62613 | NR | 680 | 46159 | NR | 810 | 3241 | NR | 940 | 2263 | NR |
| 425 | 12599 | NR | 555 | 68554 | NR | 685 | 40525 | NR | 815 | 2732 | NR | 945 | 1688 | NR |
| 430 | 19019 | NR | 560 | 75325 | NR | 690 | 35615 | NR | 820 | 2612 | NR | 950 | 1560 | NR |
| 435 | 24875 | NR | 565 | 82533 | NR | 695 | 31158 | NR | 825 | 2966 | NR | 955 | 2826 | NR |
| 440 | 29103 | NR | 570 | 90909 | NR | 700 | 27409 | NR | 830 | 2574 | NR | 960 | 1477 | NR |
| 445 | 29901 | NR | 575 | 99621 | NR | 705 | 24204 | NR | 835 | 2633 | NR | 965 | 1568 | NR |
| 450 | 24862 | NR | 580 | 108484 | NR | 710 | 21558 | NR | 840 | 2526 | NR | 970 | 2030 | NR |
| 455 | 15942 | NR | 585 | 116679 | NR | 715 | 19222 | NR | 845 | 2631 | NR | 975 | 1986 | NR |
| 460 | 9916 | NR | 590 | 123752 | NR | 720 | 17310 | NR | 850 | 2079 | NR | 980 | 2540 | NR |
| 465 | 7051 | NR | 595 | 129324 | NR | 725 | 15280 | NR | 855 | 2309 | NR | 985 | 1139 | NR |
| 470 | 5227 | NR | 600 | 134082 | NR | 730 | 13282 | NR | 860 | 2528 | NR | 990 | 2018 | NR |
| 475 | 4257 | NR | 605 | 135698 | NR | 735 | 11753 | NR | 865 | 2121 | NR | 995 | 3445 | NR |
| 480 | 4052 | NR | 610 | 135144 | NR | 740 | 10654 | NR | 870 | 2751 | NR | 1000 | 3704 | NR |
| 485 | 4298 | NR | 615 | 134180 | NR | 745 | 9451 | NR | 875 | 2317 | NR | | | |

REPORT NUMBER: SP1-1908-441-10-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 1470.8 M/P: 0.27

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 1768 | NR | 490 | 5206 | NR | 620 | 130919 | NR | 750 | 8553 | NR | 880 | 2713 | NR |
| 365 | 1569 | NR | 495 | 7286 | NR | 625 | 125335 | NR | 755 | 7696 | NR | 885 | 2316 | NR |
| 370 | 1594 | NR | 500 | 10654 | NR | 630 | 118388 | NR | 760 | 6978 | NR | 890 | 2539 | NR |
| 375 | 1744 | NR | 505 | 15189 | NR | 635 | 111855 | NR | 765 | 6377 | NR | 895 | 1933 | NR |
| 380 | 1659 | NR | 510 | 20541 | NR | 640 | 104062 | NR | 770 | 5600 | NR | 900 | 2216 | NR |
| 385 | 1504 | NR | 515 | 26492 | NR | 645 | 96365 | NR | 775 | 5000 | NR | 905 | 2067 | NR |
| 390 | 1541 | NR | 520 | 32294 | NR | 650 | 88651 | NR | 780 | 4709 | NR | 910 | 1959 | NR |
| 395 | 1355 | NR | 525 | 38123 | NR | 655 | 81152 | NR | 785 | 4305 | NR | 915 | 1874 | NR |
| 400 | 1243 | NR | 530 | 43232 | NR | 660 | 73523 | NR | 790 | 4040 | NR | 920 | 1484 | NR |
| 405 | 1417 | NR | 535 | 48012 | NR | 665 | 66123 | NR | 795 | 3642 | NR | 925 | 1914 | NR |
| 410 | 2147 | NR | 540 | 52623 | NR | 670 | 58677 | NR | 800 | 3594 | NR | 930 | 1948 | NR |
| 415 | 3837 | NR | 545 | 57516 | NR | 675 | 52349 | NR | 805 | 3190 | NR | 935 | 2079 | NR |
| 420 | 7159 | NR | 550 | 62613 | NR | 680 | 46159 | NR | 810 | 3241 | NR | 940 | 2263 | NR |
| 425 | 12599 | NR | 555 | 68554 | NR | 685 | 40525 | NR | 815 | 2732 | NR | 945 | 1688 | NR |
| 430 | 19019 | NR | 560 | 75325 | NR | 690 | 35615 | NR | 820 | 2612 | NR | 950 | 1560 | NR |
| 435 | 24875 | NR | 565 | 82533 | NR | 695 | 31158 | NR | 825 | 2966 | NR | 955 | 2826 | NR |
| 440 | 29103 | NR | 570 | 90909 | NR | 700 | 27409 | NR | 830 | 2574 | NR | 960 | 1477 | NR |
| 445 | 29901 | NR | 575 | 99621 | NR | 705 | 24204 | NR | 835 | 2633 | NR | 965 | 1568 | NR |
| 450 | 24862 | NR | 580 | 108484 | NR | 710 | 21558 | NR | 840 | 2526 | NR | 970 | 2030 | NR |
| 455 | 15942 | NR | 585 | 116679 | NR | 715 | 19222 | NR | 845 | 2631 | NR | 975 | 1986 | NR |
| 460 | 9916 | NR | 590 | 123752 | NR | 720 | 17310 | NR | 850 | 2079 | NR | 980 | 2540 | NR |
| 465 | 7051 | NR | 595 | 129324 | NR | 725 | 15280 | NR | 855 | 2309 | NR | 985 | 1139 | NR |
| 470 | 5227 | NR | 600 | 134082 | NR | 730 | 13282 | NR | 860 | 2528 | NR | 990 | 2018 | NR |
| 475 | 4257 | NR | 605 | 135698 | NR | 735 | 11753 | NR | 865 | 2121 | NR | 995 | 3445 | NR |
| 480 | 4052 | NR | 610 | 135144 | NR | 740 | 10654 | NR | 870 | 2751 | NR | 1000 | 3704 | NR |
| 485 | 4298 | NR | 615 | 134180 | NR | 745 | 9451 | NR | 875 | 2317 | NR | | | |

REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Summary

$R_f = 69.8$
 $R_g = 99.2$
 $CIE R_a = 72.0$
 $R_g = -17.4$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 87 | CES26 = 56 | CES51 = 74 | CES76 = 56 |
| CES02 = 65 | CES27 = 76 | CES52 = 76 | CES77 = 81 |
| CES03 = 32 | CES28 = 83 | CES53 = 65 | CES78 = 63 |
| CES04 = 72 | CES29 = 46 | CES54 = 78 | CES79 = 84 |
| CES05 = 52 | CES30 = 48 | CES55 = 75 | CES80 = 84 |
| CES06 = 52 | CES31 = 51 | CES56 = 65 | CES81 = 63 |
| CES07 = 44 | CES32 = 51 | CES57 = 62 | CES82 = 92 |
| CES08 = 42 | CES33 = 53 | CES58 = 66 | CES83 = 83 |
| CES09 = 29 | CES34 = 70 | CES59 = 84 | CES84 = 92 |
| CES10 = 78 | CES35 = 85 | CES60 = 90 | CES85 = 81 |
| CES11 = 61 | CES36 = 78 | CES61 = 84 | CES86 = 56 |
| CES12 = 68 | CES37 = 80 | CES62 = 70 | CES87 = 78 |
| CES13 = 45 | CES38 = 53 | CES63 = 68 | CES88 = 72 |
| CES14 = 75 | CES39 = 90 | CES64 = 69 | CES89 = 62 |
| CES15 = 72 | CES40 = 84 | CES65 = 67 | CES90 = 67 |
| CES16 = 49 | CES41 = 75 | CES66 = 64 | CES91 = 90 |
| CES17 = 51 | CES42 = 79 | CES67 = 63 | CES92 = 67 |
| CES18 = 57 | CES43 = 64 | CES68 = 69 | CES93 = 79 |
| CES19 = 74 | CES44 = 98 | CES69 = 80 | CES94 = 52 |
| CES20 = 68 | CES45 = 73 | CES70 = 63 | CES95 = 76 |
| CES21 = 89 | CES46 = 67 | CES71 = 63 | CES96 = 78 |
| CES22 = 81 | CES47 = 60 | CES72 = 87 | CES97 = 77 |
| CES23 = 92 | CES48 = 48 | CES73 = 56 | CES98 = 71 |
| CES24 = 92 | CES49 = 64 | CES74 = 87 | CES99 = 65 |
| CES25 = 74 | CES50 = 74 | CES75 = 66 | |



REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Measure Comparisons



(END OF REPORT)