

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P636124

Luminaire Tested: GWS-SA3F-727-U-T2-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P636124
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA3F-727-U-T2-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II OPTICS W/ FACTORY INSALLED GLARE SHIELD, WH
Light Source: (48) 2700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 17047.9 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G2


Input Watts (W): 183.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P636124
 CATALOG NUMBER: GWS-SA3F-727-U-T2-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 7.2 fc
 Type II - Short - N/A

REPORT NUMBER: P636124
CATALOG NUMBER: GWS-SA3F-727-U-T2-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P636124

CATALOG NUMBER: GWS-SA3F-727-U-T2-W-GRSWH


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 4611.8 | 0.0 | 4611.8 |
| | % Fixture | 27.1 | 0.0 | 27.1 |
| Street Side | Lumens | 12436.1 | 0.0 | 12436.1 |
| | % Fixture | 72.9 | 0.0 | 72.9 |
| Total | Lumens | 17047.9 | 0.0 | 17047.9 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 319.5 | 1.9 |
| 10°-20° | 1017.2 | 6.0 |
| 20°-30° | 1803.9 | 10.6 |
| 30°-40° | 2761.5 | 16.2 |
| 40°-50° | 3845.2 | 22.6 |
| 50°-60° | 4405.9 | 25.8 |
| 60°-70° | 2263.8 | 13.3 |
| 70°-80° | 569.9 | 3.3 |
| 80°-90° | 60.9 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 17047.9 | 100.0 |
| 0°-180° | 17047.9 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P636124
 CATALOG NUMBER: GWS-SA3F-727-U-T2-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1915.4 | 11.2 | | | |
| FM (30°-60°) | 8587.2 | 50.4 | | | |
| FH (60°-80°) | 1910.9 | 11.2 | | | G2/5000 |
| FVH (80°-90°) | 22.5 | 0.1 | | | G1/100 |
| BL (0°-30°) | 1225.2 | 7.2 | B3/2500 | | |
| BM (30°-60°) | 2425.4 | 14.2 | B2/2500 | | |
| BH (60°-80°) | 922.9 | 5.4 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 38.4 | 0.2 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G2
 Type II Short





REPORT NUMBER: P636124

CATALOG NUMBER: GWS-SA3F-727-U-T2-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 74° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|---------|---------|--------|
| 0° | 3192.7 | 3192.7 | 3192.7 | 3192.7 | 3192.7 | 3192.7 | 3192.7 | 3192.7 | 3192.7 | 3192.7 | 3192.7 |
| 2.5° | 3430.1 | 3438.9 | 3430.1 | 3444.8 | 3415.5 | 3402.3 | 3370.0 | 3321.7 | 3283.5 | 3277.7 | 3235.2 |
| 5° | 3696.9 | 3716.0 | 3704.3 | 3698.4 | 3658.8 | 3629.5 | 3581.1 | 3484.4 | 3405.2 | 3393.5 | 3309.9 |
| 7.5° | 3868.4 | 3881.6 | 3881.6 | 3886.0 | 3871.4 | 3837.6 | 3786.3 | 3672.0 | 3560.6 | 3543.0 | 3416.9 |
| 10° | 3925.6 | 3935.9 | 3954.9 | 3991.6 | 4020.9 | 4031.1 | 3997.4 | 3887.5 | 3751.2 | 3733.6 | 3557.7 |
| 12.5° | 3938.8 | 3950.5 | 3979.8 | 4047.3 | 4127.9 | 4201.2 | 4207.0 | 4126.4 | 3974.0 | 3954.9 | 3720.4 |
| 15° | 3963.7 | 3975.4 | 4015.0 | 4098.6 | 4217.3 | 4358.0 | 4444.5 | 4388.8 | 4220.2 | 4199.7 | 3905.1 |
| 17.5° | 3960.8 | 3974.0 | 4032.6 | 4144.0 | 4303.8 | 4507.5 | 4674.7 | 4698.1 | 4523.7 | 4488.5 | 4114.7 |
| 20° | 3953.4 | 3965.2 | 4028.2 | 4164.5 | 4362.4 | 4642.4 | 4944.4 | 5066.0 | 4878.4 | 4846.2 | 4359.5 |
| 22.5° | 4012.1 | 4025.3 | 4073.6 | 4186.5 | 4393.2 | 4746.5 | 5193.6 | 5486.7 | 5299.1 | 5253.7 | 4640.9 |
| 25° | 4144.0 | 4163.1 | 4192.4 | 4270.1 | 4448.9 | 4838.8 | 5448.6 | 5963.2 | 5771.1 | 5716.9 | 4947.3 |
| 27.5° | 4347.8 | 4371.2 | 4412.3 | 4448.9 | 4573.5 | 4956.1 | 5702.2 | 6496.7 | 6304.7 | 6247.5 | 5271.3 |
| 30° | 4597.0 | 4627.7 | 4680.5 | 4705.4 | 4790.5 | 5129.1 | 5977.8 | 7046.4 | 6935.0 | 6855.9 | 5636.3 |
| 32.5° | 4941.4 | 4984.0 | 5033.8 | 5041.1 | 5092.4 | 5391.5 | 6250.5 | 7591.7 | 7590.3 | 7534.6 | 6051.1 |
| 35° | 5390.0 | 5435.4 | 5445.7 | 5456.0 | 5480.9 | 5752.1 | 6580.3 | 8088.7 | 8280.7 | 8216.2 | 6502.6 |
| 37.5° | 5879.6 | 5945.6 | 5961.7 | 5916.2 | 5951.4 | 6186.0 | 6951.2 | 8487.4 | 8881.7 | 8812.8 | 6939.4 |
| 40° | 6402.9 | 6429.3 | 6473.3 | 6401.4 | 6445.4 | 6682.9 | 7314.7 | 8742.4 | 9330.3 | 9257.0 | 7283.9 |
| 42.5° | 6778.2 | 6826.6 | 6892.5 | 6866.1 | 6891.0 | 7108.0 | 7569.7 | 8865.6 | 9649.8 | 9576.5 | 7531.6 |
| 45° | 7185.7 | 7200.3 | 7242.9 | 7237.0 | 7251.7 | 7453.9 | 7753.0 | 8919.8 | 9935.7 | 9869.7 | 7742.7 |
| 47.5° | 7540.4 | 7562.4 | 7590.3 | 7558.0 | 7525.8 | 7657.7 | 7902.5 | 8966.7 | 10265.5 | 10186.3 | 7964.1 |
| 50° | 7882.0 | 7901.0 | 7934.7 | 7840.9 | 7720.7 | 7754.4 | 7975.8 | 9031.2 | 10574.8 | 10519.1 | 8138.5 |
| 52.5° | 7945.0 | 7965.5 | 8123.8 | 8142.9 | 7989.0 | 7870.2 | 8104.8 | 9173.4 | 10756.5 | 10721.4 | 8201.5 |
| 55° | 7152.0 | 7188.6 | 7503.8 | 7865.9 | 8245.5 | 8207.4 | 8311.5 | 9248.2 | 10828.4 | 10837.2 | 8314.4 |
| 57.5° | 5551.2 | 5604.0 | 6064.3 | 6561.2 | 7360.1 | 8021.2 | 8337.9 | 9229.1 | 10803.5 | 10851.8 | 8430.2 |
| 60° | 3641.2 | 3672.0 | 4217.3 | 4774.3 | 5602.6 | 6517.3 | 7462.7 | 8886.1 | 10582.1 | 10651.0 | 8400.9 |
| 62.5° | 2198.8 | 2234.0 | 2672.3 | 3094.4 | 3582.6 | 4193.9 | 5061.6 | 7141.7 | 8870.0 | 9023.9 | 6728.3 |
| 65° | 1534.8 | 1581.7 | 1965.7 | 2313.1 | 2481.7 | 2355.7 | 2563.8 | 3988.6 | 5526.3 | 5590.8 | 4111.8 |
| 67.5° | 1112.6 | 1144.8 | 1460.0 | 1873.4 | 2059.5 | 1663.8 | 1268.0 | 1766.4 | 2407.0 | 2430.4 | 1696.0 |
| 70° | 728.5 | 765.2 | 1051.0 | 1426.3 | 1681.4 | 1348.6 | 948.4 | 955.7 | 1012.9 | 1024.6 | 985.1 |
| 72.5° | 400.2 | 422.2 | 649.4 | 947.0 | 993.9 | 806.2 | 740.3 | 794.5 | 834.1 | 834.1 | 844.3 |
| 75° | 206.7 | 225.7 | 265.3 | 312.2 | 376.7 | 441.2 | 533.6 | 614.2 | 656.7 | 659.6 | 655.2 |
| 77.5° | 105.5 | 112.9 | 142.2 | 153.9 | 168.6 | 196.4 | 255.1 | 326.9 | 365.0 | 379.7 | 376.7 |
| 80° | 49.8 | 52.8 | 60.1 | 70.4 | 86.5 | 109.9 | 137.8 | 164.2 | 187.6 | 190.6 | 206.7 |
| 82.5° | 26.4 | 29.3 | 32.2 | 38.1 | 46.9 | 58.6 | 80.6 | 96.7 | 111.4 | 114.3 | 127.5 |
| 85° | 10.3 | 11.7 | 13.2 | 14.7 | 20.5 | 24.9 | 33.7 | 45.4 | 55.7 | 55.7 | 66.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 1.5 | 2.9 | 5.9 | 7.3 | 10.3 | 10.3 | 17.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P636124

CATALOG NUMBER: GWS-SA3F-727-U-T2-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3192.7 | 3192.7 | 3192.7 | 3192.7 | 3192.7 | 3192.7 | 3192.7 | 3192.7 | 3192.7 | 3192.7 | 3192.7 |
| 2.5° | 3224.9 | 3182.4 | 3163.3 | 3132.6 | 3107.6 | 3079.8 | 3057.8 | 3041.7 | 3031.4 | 3025.6 | 3019.7 |
| 5° | 3277.7 | 3213.2 | 3161.9 | 3100.3 | 3057.8 | 3016.8 | 2983.0 | 2959.6 | 2947.9 | 2939.1 | 2933.2 |
| 7.5° | 3359.8 | 3273.3 | 3176.5 | 3081.3 | 3006.5 | 2940.5 | 2898.0 | 2873.1 | 2857.0 | 2851.1 | 2846.7 |
| 10° | 3472.6 | 3352.4 | 3192.7 | 3041.7 | 2930.3 | 2858.4 | 2829.1 | 2817.4 | 2818.9 | 2815.9 | 2814.5 |
| 12.5° | 3600.2 | 3436.0 | 3188.3 | 2971.3 | 2848.2 | 2805.7 | 2807.1 | 2826.2 | 2848.2 | 2854.0 | 2855.5 |
| 15° | 3738.0 | 3518.1 | 3145.8 | 2880.4 | 2783.7 | 2788.1 | 2826.2 | 2871.6 | 2912.7 | 2928.8 | 2931.7 |
| 17.5° | 3887.5 | 3587.0 | 3068.1 | 2780.8 | 2730.9 | 2777.8 | 2848.2 | 2922.9 | 2983.0 | 3009.4 | 3016.8 |
| 20° | 4054.6 | 3645.6 | 2958.1 | 2682.5 | 2681.1 | 2758.8 | 2861.4 | 2959.6 | 3035.8 | 3071.0 | 3076.9 |
| 22.5° | 4232.0 | 3682.3 | 2823.3 | 2591.7 | 2629.8 | 2733.8 | 2851.1 | 2953.7 | 3034.3 | 3069.5 | 3076.9 |
| 25° | 4410.8 | 3694.0 | 2675.2 | 2508.1 | 2577.0 | 2694.3 | 2801.3 | 2883.4 | 2959.6 | 2990.4 | 2996.2 |
| 27.5° | 4577.9 | 3660.3 | 2534.5 | 2436.3 | 2528.6 | 2635.6 | 2707.5 | 2751.4 | 2804.2 | 2827.7 | 2832.1 |
| 30° | 4747.9 | 3592.8 | 2415.8 | 2379.1 | 2474.4 | 2555.0 | 2587.3 | 2590.2 | 2610.7 | 2610.7 | 2613.6 |
| 32.5° | 4919.5 | 3493.2 | 2311.7 | 2323.4 | 2407.0 | 2459.7 | 2464.1 | 2430.4 | 2405.5 | 2364.4 | 2363.0 |
| 35° | 5117.3 | 3392.0 | 2226.7 | 2260.4 | 2327.8 | 2360.0 | 2346.9 | 2282.4 | 2222.3 | 2154.8 | 2151.9 |
| 37.5° | 5300.6 | 3287.9 | 2154.8 | 2195.9 | 2238.4 | 2261.8 | 2231.1 | 2153.4 | 2103.5 | 2034.6 | 2024.4 |
| 40° | 5451.6 | 3194.1 | 2085.9 | 2128.4 | 2149.0 | 2169.5 | 2119.6 | 2056.6 | 2063.9 | 2025.8 | 2024.4 |
| 42.5° | 5539.5 | 3103.2 | 2021.4 | 2053.7 | 2066.9 | 2081.5 | 2037.6 | 1990.6 | 2030.2 | 2000.9 | 2002.4 |
| 45° | 5604.0 | 3024.1 | 1962.8 | 1974.5 | 2006.8 | 2028.8 | 1987.7 | 1934.9 | 1943.7 | 1830.9 | 1804.5 |
| 47.5° | 5677.3 | 2980.1 | 1907.1 | 1895.4 | 1952.5 | 1990.6 | 1927.6 | 1851.4 | 1798.6 | 1687.2 | 1677.0 |
| 50° | 5755.0 | 2964.0 | 1848.5 | 1816.2 | 1885.1 | 1921.8 | 1848.5 | 1753.2 | 1684.3 | 1624.2 | 1618.3 |
| 52.5° | 5781.4 | 2962.5 | 1775.2 | 1720.9 | 1789.8 | 1841.1 | 1779.6 | 1682.8 | 1600.7 | 1542.1 | 1539.2 |
| 55° | 5885.5 | 3005.0 | 1681.4 | 1590.5 | 1655.0 | 1760.5 | 1715.1 | 1575.8 | 1509.8 | 1483.5 | 1480.5 |
| 57.5° | 6007.1 | 3012.4 | 1533.3 | 1448.3 | 1537.7 | 1662.3 | 1605.1 | 1484.9 | 1413.1 | 1380.8 | 1377.9 |
| 60° | 5957.3 | 2832.1 | 1375.0 | 1339.8 | 1438.0 | 1569.9 | 1517.2 | 1413.1 | 1329.5 | 1298.8 | 1295.8 |
| 62.5° | 4539.8 | 1999.4 | 1259.2 | 1246.0 | 1331.0 | 1436.6 | 1426.3 | 1317.8 | 1238.7 | 1216.7 | 1213.7 |
| 65° | 2730.9 | 1404.3 | 1147.8 | 1146.3 | 1206.4 | 1307.6 | 1320.7 | 1232.8 | 1149.2 | 1118.5 | 1118.5 |
| 67.5° | 1350.1 | 1074.5 | 1021.7 | 1014.4 | 1052.5 | 1124.3 | 1180.0 | 1108.2 | 1037.8 | 1008.5 | 1004.1 |
| 70° | 954.3 | 947.0 | 929.4 | 908.8 | 916.2 | 945.5 | 968.9 | 908.8 | 834.1 | 804.8 | 798.9 |
| 72.5° | 825.3 | 826.8 | 815.0 | 798.9 | 793.0 | 772.5 | 752.0 | 708.0 | 662.6 | 631.8 | 634.7 |
| 75° | 640.6 | 643.5 | 650.8 | 645.0 | 628.9 | 606.9 | 584.9 | 529.2 | 492.5 | 463.2 | 457.4 |
| 77.5° | 373.8 | 388.5 | 411.9 | 406.0 | 409.0 | 378.2 | 369.4 | 315.2 | 281.4 | 260.9 | 256.5 |
| 80° | 211.1 | 219.9 | 230.1 | 237.5 | 228.7 | 215.5 | 196.4 | 167.1 | 156.8 | 142.2 | 139.3 |
| 82.5° | 127.5 | 136.3 | 140.7 | 146.6 | 143.7 | 126.1 | 111.4 | 92.3 | 83.6 | 76.2 | 74.8 |
| 85° | 64.5 | 70.4 | 74.8 | 77.7 | 68.9 | 57.2 | 51.3 | 41.0 | 35.2 | 30.8 | 30.8 |
| 87.5° | 16.1 | 17.6 | 20.5 | 17.6 | 16.1 | 7.3 | 5.9 | 1.5 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions
 Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 CIE $R_a = 71.5$
 $R_9 = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)