

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P638610

Luminaire Tested: GWS-SA4F-727-U-T3R-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P638610
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA4F-727-U-T3R-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III ROADWAY OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (64) 2700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 17846.5 lumens
Efficiency: N/A
Efficacy: 79.2 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G1


Input Watts (W): 225.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P638610
 CATALOG NUMBER: GWS-SA4F-727-U-T3R-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 7.2 fc
 Type II - Short - N/A

REPORT NUMBER: P638610
CATALOG NUMBER: GWS-SA4F-727-U-T3R-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 38-Deg Lateral - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P638610
 CATALOG NUMBER: GWS-SA4F-727-U-T3R-W-GRSBK


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 3477.0 | 0.0 | 3477.0 |
| | % Fixture | 19.5 | 0.0 | 19.5 |
| Street Side | Lumens | 14369.5 | 0.0 | 14369.5 |
| | % Fixture | 80.5 | 0.0 | 80.5 |
| Total | Lumens | 17846.5 | 0.0 | 17846.5 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 395.7 | 2.2 |
| 10°-20° | 1065.3 | 6.0 |
| 20°-30° | 1828.1 | 10.2 |
| 30°-40° | 3032.1 | 17.0 |
| 40°-50° | 4457.3 | 25.0 |
| 50°-60° | 5208.5 | 29.2 |
| 60°-70° | 1765.5 | 9.9 |
| 70°-80° | 90.3 | 0.5 |
| 80°-90° | 3.5 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 17846.5 | 100.0 |
| 0°-180° | 17846.5 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P638610
 CATALOG NUMBER: GWS-SA4F-727-U-T3R-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1964.5 | 11.0 | | | |
| FM (30°-60°) | 10778.8 | 60.4 | | | |
| FH (60°-80°) | 1624.3 | 9.1 | | | G1/1800 |
| FVH (80°-90°) | 1.9 | 0.0 | | | G0/10 |
| BL (0°-30°) | 1324.7 | 7.4 | B3/2500 | | |
| BM (30°-60°) | 1919.2 | 10.8 | B2/2500 | | |
| BH (60°-80°) | 231.5 | 1.3 | B1/500 | | G1/500 |
| BVH (80°-90°) | 1.7 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G1
 Type II Short





REPORT NUMBER: P638610

CATALOG NUMBER: GWS-SA4F-727-U-T3R-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 38° | 45° | 55° | 65° | 75° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 4279.7 | 4279.7 | 4279.7 | 4279.7 | 4279.7 | 4279.7 | 4279.7 | 4279.7 | 4279.7 | 4279.7 | 4279.7 |
| 2.5° | 3986.0 | 3977.8 | 3994.1 | 4026.8 | 4057.4 | 4067.6 | 4098.2 | 4141.0 | 4167.5 | 4230.8 | 4281.8 |
| 5° | 3806.5 | 3802.4 | 3818.7 | 3847.3 | 3888.1 | 3902.3 | 3949.3 | 4020.7 | 4092.1 | 4202.2 | 4310.3 |
| 7.5° | 3643.3 | 3641.2 | 3665.7 | 3729.0 | 3788.1 | 3806.5 | 3863.6 | 3951.3 | 4047.2 | 4216.5 | 4375.6 |
| 10° | 3429.1 | 3431.1 | 3478.0 | 3567.8 | 3675.9 | 3712.6 | 3804.4 | 3930.9 | 4055.3 | 4273.6 | 4493.9 |
| 12.5° | 3359.7 | 3363.8 | 3388.3 | 3457.6 | 3576.0 | 3622.9 | 3751.4 | 3943.1 | 4102.3 | 4355.2 | 4646.9 |
| 15° | 3529.0 | 3529.0 | 3508.6 | 3516.8 | 3569.8 | 3612.7 | 3747.3 | 3983.9 | 4181.8 | 4453.1 | 4797.9 |
| 17.5° | 3857.5 | 3845.2 | 3794.2 | 3724.9 | 3706.5 | 3720.8 | 3828.9 | 4071.7 | 4294.0 | 4567.4 | 4969.2 |
| 20° | 4302.2 | 4306.2 | 4206.3 | 4061.5 | 3945.2 | 3943.1 | 4008.4 | 4226.7 | 4455.2 | 4704.0 | 5154.8 |
| 22.5° | 4840.7 | 4824.4 | 4691.8 | 4493.9 | 4292.0 | 4275.6 | 4302.2 | 4463.3 | 4687.7 | 4920.3 | 5383.3 |
| 25° | 5464.9 | 5456.8 | 5269.1 | 5003.9 | 4736.7 | 4697.9 | 4697.9 | 4857.0 | 5020.2 | 5228.3 | 5656.7 |
| 27.5° | 6117.7 | 6117.7 | 5936.1 | 5630.1 | 5275.2 | 5205.8 | 5195.6 | 5383.3 | 5491.4 | 5532.2 | 5887.2 |
| 30° | 6788.8 | 6780.7 | 6601.1 | 6287.0 | 5907.6 | 5836.2 | 5807.6 | 5946.3 | 6023.8 | 5901.5 | 6174.8 |
| 32.5° | 7470.1 | 7484.4 | 7302.9 | 7011.2 | 6672.5 | 6625.6 | 6537.9 | 6537.9 | 6601.1 | 6429.8 | 6627.7 |
| 35° | 8202.5 | 8198.4 | 8055.6 | 7857.7 | 7568.1 | 7515.0 | 7370.2 | 7143.8 | 7239.6 | 7164.2 | 7253.9 |
| 37.5° | 8849.1 | 8879.7 | 8810.4 | 8663.5 | 8428.9 | 8375.9 | 8137.2 | 7727.2 | 7800.6 | 7918.9 | 7998.5 |
| 40° | 9506.0 | 9530.5 | 9599.8 | 9552.9 | 9257.1 | 9159.2 | 8734.9 | 8061.7 | 8143.3 | 8549.3 | 8777.7 |
| 42.5° | 10150.6 | 10162.8 | 10303.6 | 10381.1 | 9985.4 | 9814.0 | 9187.7 | 8265.7 | 8351.4 | 9042.9 | 9442.7 |
| 45° | 10560.6 | 10587.1 | 10819.7 | 11056.3 | 10627.9 | 10393.3 | 9581.4 | 8526.8 | 8563.5 | 9385.6 | 9934.4 |
| 47.5° | 10544.3 | 10605.5 | 11042.0 | 11472.4 | 11180.7 | 10927.8 | 10054.7 | 8945.0 | 8883.8 | 9707.9 | 10258.7 |
| 50° | 10215.9 | 10289.3 | 10915.5 | 11598.9 | 11578.5 | 11343.9 | 10581.0 | 9550.9 | 9359.1 | 9993.5 | 10299.5 |
| 52.5° | 9534.5 | 9746.7 | 10693.2 | 11615.2 | 11898.8 | 11780.5 | 11231.7 | 10366.8 | 10001.7 | 10403.5 | 10364.8 |
| 55° | 8061.7 | 8322.8 | 10018.0 | 11476.5 | 12188.5 | 12202.7 | 11915.1 | 11217.5 | 10699.3 | 11109.3 | 10766.6 |
| 57.5° | 6119.7 | 6327.8 | 7710.9 | 10215.9 | 11709.1 | 11943.7 | 12180.3 | 11666.2 | 11129.7 | 11590.8 | 10860.5 |
| 60° | 3688.2 | 3928.9 | 4828.5 | 7496.7 | 9457.0 | 9856.8 | 10785.0 | 10685.0 | 10038.4 | 10236.3 | 8906.2 |
| 62.5° | 1495.3 | 1621.7 | 2229.6 | 4130.8 | 5952.5 | 6325.8 | 7215.2 | 7366.1 | 7207.0 | 7005.0 | 5401.7 |
| 65° | 546.7 | 597.7 | 893.5 | 1707.4 | 2737.6 | 2874.2 | 3343.4 | 3610.6 | 3830.9 | 3261.8 | 2009.3 |
| 67.5° | 338.6 | 371.3 | 581.4 | 877.2 | 995.5 | 926.1 | 942.4 | 1124.0 | 1073.0 | 663.0 | 359.0 |
| 70° | 250.9 | 277.4 | 454.9 | 607.9 | 401.9 | 310.1 | 210.1 | 224.4 | 202.0 | 177.5 | 175.4 |
| 72.5° | 173.4 | 197.9 | 340.7 | 359.0 | 155.0 | 110.2 | 77.5 | 108.1 | 122.4 | 120.4 | 124.4 |
| 75° | 114.2 | 132.6 | 214.2 | 140.8 | 38.8 | 30.6 | 26.5 | 57.1 | 73.4 | 73.4 | 75.5 |
| 77.5° | 67.3 | 77.5 | 75.5 | 28.6 | 8.2 | 8.2 | 6.1 | 10.2 | 16.3 | 18.4 | 22.4 |
| 80° | 8.2 | 6.1 | 4.1 | 4.1 | 4.1 | 4.1 | 4.1 | 4.1 | 6.1 | 6.1 | 6.1 |
| 82.5° | 2.0 | 2.0 | 2.0 | 4.1 | 4.1 | 4.1 | 4.1 | 4.1 | 4.1 | 6.1 | 6.1 |
| 85° | 0.0 | 0.0 | 2.0 | 2.0 | 4.1 | 4.1 | 4.1 | 4.1 | 4.1 | 6.1 | 6.1 |
| 87.5° | 0.0 | 0.0 | 2.0 | 2.0 | 4.1 | 4.1 | 4.1 | 4.1 | 4.1 | 6.1 | 6.1 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P638610

CATALOG NUMBER: GWS-SA4F-727-U-T3R-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 4279.7 | 4279.7 | 4279.7 | 4279.7 | 4279.7 | 4279.7 | 4279.7 | 4279.7 | 4279.7 | 4279.7 | 4279.7 |
| 2.5° | 4320.5 | 4306.2 | 4365.4 | 4408.2 | 4442.9 | 4459.2 | 4436.8 | 4434.8 | 4434.8 | 4389.9 | 4377.6 |
| 5° | 4371.5 | 4377.6 | 4461.3 | 4498.0 | 4504.1 | 4483.7 | 4432.7 | 4398.0 | 4377.6 | 4330.7 | 4304.2 |
| 7.5° | 4469.4 | 4489.8 | 4569.4 | 4563.3 | 4508.2 | 4414.4 | 4279.7 | 4175.7 | 4108.4 | 4034.9 | 3990.1 |
| 10° | 4610.2 | 4649.0 | 4697.9 | 4612.2 | 4436.8 | 4198.1 | 3920.7 | 3722.8 | 3604.5 | 3520.9 | 3469.9 |
| 12.5° | 4781.5 | 4820.3 | 4804.0 | 4602.0 | 4236.9 | 3810.5 | 3453.6 | 3168.0 | 3031.3 | 2955.8 | 2902.8 |
| 15° | 4954.9 | 4979.4 | 4873.3 | 4479.6 | 3884.0 | 3310.8 | 2913.0 | 2629.4 | 2462.2 | 2401.0 | 2356.1 |
| 17.5° | 5132.4 | 5126.3 | 4885.6 | 4238.9 | 3412.8 | 2747.8 | 2356.1 | 2162.3 | 2115.4 | 2105.2 | 2101.1 |
| 20° | 5318.0 | 5263.0 | 4836.6 | 3894.2 | 2845.7 | 2190.9 | 1968.5 | 1980.8 | 2066.4 | 2107.2 | 2115.4 |
| 22.5° | 5530.2 | 5391.5 | 4714.2 | 3427.0 | 2266.3 | 1825.7 | 1848.2 | 1968.5 | 2084.8 | 2139.9 | 2148.0 |
| 25° | 5756.6 | 5509.8 | 4510.2 | 2827.3 | 1787.0 | 1678.8 | 1811.4 | 1950.2 | 2074.6 | 2141.9 | 2150.1 |
| 27.5° | 5905.5 | 5538.4 | 4175.7 | 2223.5 | 1534.0 | 1621.7 | 1762.5 | 1895.1 | 2023.6 | 2097.0 | 2107.2 |
| 30° | 6066.7 | 5526.1 | 3720.8 | 1713.5 | 1448.3 | 1572.8 | 1695.2 | 1815.5 | 1933.8 | 2015.4 | 2023.6 |
| 32.5° | 6303.3 | 5518.0 | 3165.9 | 1391.2 | 1413.7 | 1534.0 | 1623.8 | 1723.7 | 1805.3 | 1852.2 | 1846.1 |
| 35° | 6613.4 | 5507.8 | 2519.3 | 1254.5 | 1393.3 | 1503.4 | 1574.8 | 1621.7 | 1532.0 | 1503.4 | 1509.5 |
| 37.5° | 7011.2 | 5532.2 | 1974.6 | 1197.4 | 1387.1 | 1495.3 | 1556.4 | 1421.8 | 1283.1 | 1230.1 | 1221.9 |
| 40° | 7451.8 | 5595.5 | 1505.5 | 1175.0 | 1407.5 | 1515.7 | 1487.1 | 1264.7 | 1093.4 | 989.4 | 966.9 |
| 42.5° | 7894.4 | 5664.8 | 1191.3 | 1166.8 | 1442.2 | 1572.8 | 1372.9 | 1150.5 | 893.5 | 834.3 | 826.2 |
| 45° | 8222.9 | 5652.6 | 1030.2 | 1152.5 | 1472.8 | 1605.4 | 1342.3 | 987.3 | 797.6 | 771.1 | 773.1 |
| 47.5° | 8388.1 | 5518.0 | 942.4 | 1119.9 | 1485.1 | 1572.8 | 1266.8 | 920.0 | 732.3 | 760.9 | 785.4 |
| 50° | 8300.4 | 5169.1 | 860.8 | 1056.7 | 1458.5 | 1529.9 | 1146.4 | 869.0 | 699.7 | 818.0 | 873.1 |
| 52.5° | 8194.3 | 4740.7 | 771.1 | 958.8 | 1395.3 | 1470.8 | 1099.5 | 854.7 | 679.3 | 789.4 | 830.2 |
| 55° | 8335.1 | 4469.4 | 624.2 | 807.8 | 1270.9 | 1332.1 | 1062.8 | 852.7 | 632.4 | 614.0 | 607.9 |
| 57.5° | 8137.2 | 3928.9 | 446.7 | 581.4 | 975.1 | 1054.6 | 1036.3 | 838.4 | 561.0 | 558.9 | 567.1 |
| 60° | 6289.0 | 2396.9 | 306.0 | 369.2 | 597.7 | 673.2 | 940.4 | 801.7 | 483.5 | 444.7 | 446.7 |
| 62.5° | 3573.9 | 1020.0 | 210.1 | 228.5 | 306.0 | 363.1 | 718.0 | 728.2 | 446.7 | 424.3 | 446.7 |
| 65° | 1244.3 | 365.1 | 163.2 | 153.0 | 169.3 | 193.8 | 412.1 | 563.0 | 405.9 | 367.2 | 371.3 |
| 67.5° | 257.0 | 181.6 | 144.8 | 126.5 | 126.5 | 126.5 | 210.1 | 350.9 | 334.5 | 291.7 | 295.8 |
| 70° | 163.2 | 155.0 | 126.5 | 108.1 | 104.0 | 95.9 | 120.4 | 193.8 | 230.5 | 212.2 | 214.2 |
| 72.5° | 120.4 | 118.3 | 100.0 | 87.7 | 77.5 | 69.4 | 75.5 | 95.9 | 118.3 | 122.4 | 124.4 |
| 75° | 73.4 | 75.5 | 65.3 | 55.1 | 49.0 | 42.8 | 44.9 | 44.9 | 44.9 | 40.8 | 44.9 |
| 77.5° | 22.4 | 24.5 | 20.4 | 16.3 | 14.3 | 14.3 | 14.3 | 12.2 | 10.2 | 6.1 | 6.1 |
| 80° | 6.1 | 6.1 | 6.1 | 6.1 | 6.1 | 4.1 | 4.1 | 2.0 | 2.0 | 0.0 | 0.0 |
| 82.5° | 6.1 | 6.1 | 6.1 | 6.1 | 4.1 | 4.1 | 2.0 | 2.0 | 0.0 | 0.0 | 0.0 |
| 85° | 6.1 | 6.1 | 6.1 | 6.1 | 4.1 | 4.1 | 2.0 | 2.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 6.1 | 6.1 | 6.1 | 6.1 | 4.1 | 4.1 | 2.0 | 2.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 CIE $R_a = 71.5$
 $R_9 = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)