

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P641048

Luminaire Tested: GWS-SA5F-727-U-AFL-W-GRSWH

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641048  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-47)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA5F-727-U-AFL-W-GRSWH  
Description: GALLEON WALL SLIM LUMINAIRE. (5) LIGHTSQUARES WITH 16 LEDS EACH AND AUTOMOTIVE FRONTLINE OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH  
Light Source: (80) 2700K CCT, 70 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 31666.5 lumens  
Efficiency: N/A  
Efficacy: 102.1 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
IES Classification: Type II - Short  
BUG Rating: B3 - U0 - G2  
  
Input Watts (W): 310.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P641048  
 CATALOG NUMBER: GWS-SA5F-727-U-AFL-W-GRSWH

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 12.8 fc  
 Type II - Short - N/A

REPORT NUMBER: P641048  
CATALOG NUMBER: GWS-SA5F-727-U-AFL-W-GRSWH

### Luminous Intensity Polar Plot



— Vertical Plane Through 51-Deg Lateral    - - - Horizontal Cone Through 52.5-Deg Vertical

REPORT NUMBER: P641048

CATALOG NUMBER: GWS-SA5F-727-U-AFL-W-GRSWH

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 6170.0   | 0.0    | 6170.0  |
|                    | % Fixture | 19.5     | 0.0    | 19.5    |
| <b>Street Side</b> | Lumens    | 25496.5  | 0.0    | 25496.5 |
|                    | % Fixture | 80.5     | 0.0    | 80.5    |
| <b>Total</b>       | Lumens    | 31666.5  | 0.0    | 31666.5 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 879.8   | 2.8       |
| 10°-20°   | 2286.1  | 7.2       |
| 20°-30°   | 3717.1  | 11.7      |
| 30°-40°   | 5890.7  | 18.6      |
| 40°-50°   | 8884.5  | 28.1      |
| 50°-60°   | 7685.8  | 24.3      |
| 60°-70°   | 1742.4  | 5.5       |
| 70°-80°   | 513.8   | 1.6       |
| 80°-90°   | 66.2    | 0.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 31666.5 | 100.0     |
| 0°-180°   | 31666.5 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P641048


CATALOG NUMBER: GWS-SA5F-727-U-AFL-W-GRSWH

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|---------|-----------|-------------------------|------|---------|
|                |         |           | B                       | U    | G       |
| FL (0°-30°)    | 4726.3  | 14.9      |                         |      |         |
| FM (30°-60°)   | 19374.0 | 61.2      |                         |      |         |
| FH (60°-80°)   | 1371.3  | 4.3       |                         |      | G1/1800 |
| FVH (80°-90°)  | 24.9    | 0.1       |                         |      | G1/100  |
| BL (0°-30°)    | 2156.8  | 6.8       | B3/2500                 |      |         |
| BM (30°-60°)   | 3087.0  | 9.7       | B3/5000                 |      |         |
| BH (60°-80°)   | 884.9   | 2.8       | B2/1000                 |      | G2/1000 |
| BVH (80°-90°)  | 41.2    | 0.1       |                         |      | G1/100  |
| UL (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0     | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G2**

Type II Short





REPORT NUMBER: P641048

CATALOG NUMBER: GWS-SA5F-727-U-AFL-W-GRSWH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 15°     | 25°     | 35°     | 45°     | 51°     | 55°     | 65°     | 75°     | 85°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 9428.7  | 9428.7  | 9428.7  | 9428.7  | 9428.7  | 9428.7  | 9428.7  | 9428.7  | 9428.7  | 9428.7  | 9428.7  |
| 2.5°  | 10507.2 | 10567.2 | 10474.7 | 10439.6 | 10382.1 | 10282.0 | 10166.9 | 10134.3 | 9886.6  | 9724.0  | 9541.3  |
| 5°    | 11563.2 | 11595.7 | 11520.6 | 11445.6 | 11302.9 | 11125.3 | 10902.6 | 10855.0 | 10404.6 | 10031.8 | 9643.9  |
| 7.5°  | 11798.4 | 11785.9 | 11850.9 | 11893.5 | 11876.0 | 11805.9 | 11608.2 | 11515.6 | 10977.6 | 10387.1 | 9814.1  |
| 10°   | 10867.5 | 10797.5 | 11037.7 | 11322.9 | 11665.8 | 12061.1 | 12038.6 | 12031.1 | 11563.2 | 10865.0 | 10031.8 |
| 12.5° | 9633.9  | 9598.9  | 9794.0  | 10151.9 | 10800.0 | 11675.8 | 12003.6 | 12258.8 | 12091.2 | 11320.4 | 10274.5 |
| 15°   | 8928.2  | 8915.7  | 9048.3  | 9306.1  | 9821.6  | 10927.6 | 11628.2 | 12133.7 | 12544.1 | 11808.4 | 10532.2 |
| 17.5° | 8800.6  | 8808.1  | 8853.2  | 9000.8  | 9371.1  | 10282.0 | 11092.7 | 11798.4 | 12896.9 | 12343.9 | 10855.0 |
| 20°   | 9173.5  | 9223.5  | 9145.9  | 9168.5  | 9368.6  | 10049.3 | 10727.4 | 11460.6 | 13122.1 | 12881.9 | 11202.8 |
| 22.5° | 10001.7 | 9984.2  | 9814.1  | 9714.0  | 9716.5  | 10191.9 | 10687.4 | 11302.9 | 13269.7 | 13404.9 | 11518.1 |
| 25°   | 10940.1 | 10920.1 | 10717.4 | 10494.7 | 10354.6 | 10579.8 | 10975.1 | 11470.6 | 13402.4 | 13882.8 | 11770.9 |
| 27.5° | 12048.6 | 11986.1 | 11760.8 | 11475.6 | 11165.3 | 11262.9 | 11530.6 | 11923.5 | 13607.6 | 14353.2 | 11938.5 |
| 30°   | 13122.1 | 13194.7 | 12871.9 | 12534.1 | 12206.3 | 12146.2 | 12301.3 | 12656.7 | 14025.4 | 14903.7 | 12138.7 |
| 32.5° | 14545.9 | 14520.9 | 14163.1 | 13722.7 | 13254.7 | 13209.7 | 13332.3 | 13657.6 | 14776.1 | 15664.4 | 12444.0 |
| 35°   | 16270.0 | 16275.0 | 15767.0 | 15171.5 | 14505.9 | 14385.8 | 14591.0 | 14906.2 | 15894.7 | 16695.4 | 12926.9 |
| 37.5° | 18061.7 | 18054.2 | 17611.2 | 16935.6 | 16027.3 | 15857.1 | 16092.3 | 16327.6 | 17293.5 | 18099.2 | 13677.6 |
| 40°   | 19317.8 | 19367.9 | 19160.2 | 18804.8 | 17944.1 | 17528.7 | 17736.4 | 17899.0 | 18814.9 | 19750.7 | 14666.0 |
| 42.5° | 20031.0 | 20106.0 | 20151.1 | 20363.8 | 19910.9 | 19468.0 | 19392.9 | 19478.0 | 20173.6 | 21284.6 | 15594.4 |
| 45°   | 20183.6 | 20283.7 | 20611.5 | 21399.7 | 21574.9 | 21449.8 | 21204.6 | 20999.4 | 21187.0 | 22373.1 | 16202.4 |
| 47.5° | 19510.5 | 19685.7 | 20386.3 | 21765.1 | 22788.5 | 23181.4 | 22908.6 | 22595.8 | 21772.6 | 22653.4 | 16139.9 |
| 50°   | 16843.0 | 17048.2 | 18627.2 | 21019.4 | 22961.2 | 24392.5 | 24417.5 | 23954.6 | 21702.5 | 21845.1 | 15354.2 |
| 52.5° | 13334.8 | 13474.9 | 14378.3 | 17818.9 | 21267.1 | 24342.5 | 25343.4 | 24847.9 | 21364.7 | 20834.2 | 14370.8 |
| 55°   | 7969.9  | 8195.1  | 9038.3  | 11755.8 | 16567.8 | 21574.9 | 23706.9 | 23947.1 | 21199.6 | 19985.9 | 13700.1 |
| 57.5° | 2690.0  | 2800.1  | 3605.8  | 5192.3  | 9764.0  | 15797.1 | 18316.9 | 19292.8 | 19245.3 | 18689.7 | 12391.4 |
| 60°   | 1281.2  | 1306.2  | 1468.9  | 1969.3  | 3908.6  | 8255.1  | 10842.5 | 11968.5 | 12994.5 | 13097.1 | 7709.6  |
| 62.5° | 975.9   | 990.9   | 1073.5  | 1181.1  | 1571.4  | 3478.2  | 4969.6  | 5830.4  | 6228.2  | 5344.9  | 2807.6  |
| 65°   | 815.8   | 828.3   | 890.8   | 958.4   | 1068.5  | 1506.4  | 1906.8  | 2199.5  | 1981.8  | 1543.9  | 1338.7  |
| 67.5° | 680.6   | 690.6   | 738.2   | 810.7   | 885.8   | 1008.4  | 1058.5  | 1088.5  | 1141.1  | 1281.2  | 1231.1  |
| 70°   | 533.0   | 543.0   | 593.0   | 655.6   | 728.2   | 758.2   | 805.7   | 835.8   | 940.9   | 1121.0  | 1116.0  |
| 72.5° | 410.4   | 422.9   | 450.4   | 490.5   | 550.5   | 580.5   | 633.1   | 668.1   | 728.2   | 873.3   | 933.4   |
| 75°   | 300.3   | 307.8   | 332.8   | 345.3   | 352.8   | 345.3   | 397.9   | 437.9   | 518.0   | 573.0   | 588.0   |
| 77.5° | 122.6   | 137.6   | 132.6   | 132.6   | 157.6   | 190.2   | 217.7   | 242.7   | 297.8   | 330.3   | 332.8   |
| 80°   | 50.0    | 55.1    | 65.1    | 72.6    | 87.6    | 112.6   | 130.1   | 140.1   | 165.2   | 185.2   | 200.2   |
| 82.5° | 30.0    | 32.5    | 37.5    | 40.0    | 50.0    | 65.1    | 75.1    | 82.6    | 102.6   | 122.6   | 130.1   |
| 85°   | 15.0    | 15.0    | 17.5    | 20.0    | 25.0    | 30.0    | 35.0    | 40.0    | 52.5    | 65.1    | 72.6    |
| 87.5° | 2.5     | 2.5     | 2.5     | 5.0     | 7.5     | 10.0    | 12.5    | 15.0    | 17.5    | 20.0    | 25.0    |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P641048

CATALOG NUMBER: GWS-SA5F-727-U-AFL-W-GRSWH

**CANDELA DISTRIBUTION (continued):**

|       | 90°     | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 9428.7  | 9428.7 | 9428.7 | 9428.7 | 9428.7 | 9428.7 | 9428.7 | 9428.7 | 9428.7 | 9428.7 | 9428.7 |
| 2.5°  | 9433.7  | 9298.6 | 9140.9 | 9015.8 | 8870.7 | 8763.1 | 8610.4 | 8515.4 | 8425.3 | 8350.2 | 8295.2 |
| 5°    | 9443.7  | 9216.0 | 8888.2 | 8597.9 | 8297.7 | 8012.4 | 7719.6 | 7481.9 | 7269.2 | 7091.5 | 7076.5 |
| 7.5°  | 9501.3  | 9173.5 | 8660.5 | 8152.5 | 7567.0 | 7001.5 | 6435.9 | 5975.5 | 5625.2 | 5442.5 | 5405.0 |
| 10°   | 9598.9  | 9168.5 | 8427.8 | 7617.0 | 6618.6 | 5707.8 | 5037.1 | 4686.8 | 4484.1 | 4411.6 | 4386.5 |
| 12.5° | 9701.4  | 9155.9 | 8130.0 | 6861.3 | 5475.1 | 4676.8 | 4309.0 | 4266.4 | 4304.0 | 4309.0 | 4306.5 |
| 15°   | 9826.6  | 9148.4 | 7754.7 | 5975.5 | 4639.3 | 4198.9 | 4223.9 | 4314.0 | 4401.6 | 4421.6 | 4421.6 |
| 17.5° | 9979.2  | 9130.9 | 7244.2 | 5109.7 | 4116.3 | 4106.3 | 4238.9 | 4359.0 | 4441.6 | 4456.6 | 4456.6 |
| 20°   | 10139.4 | 9085.9 | 6616.1 | 4404.1 | 3903.6 | 4048.7 | 4191.4 | 4284.0 | 4341.5 | 4361.5 | 4364.0 |
| 22.5° | 10249.5 | 8965.8 | 5892.9 | 3881.1 | 3771.0 | 3938.6 | 4041.2 | 4136.3 | 4136.3 | 4086.3 | 4071.3 |
| 25°   | 10272.0 | 8708.0 | 5109.7 | 3523.2 | 3613.3 | 3768.5 | 3873.6 | 3818.5 | 3715.9 | 3675.9 | 3673.4 |
| 27.5° | 10189.4 | 8332.7 | 4336.5 | 3268.0 | 3423.2 | 3578.3 | 3560.8 | 3480.7 | 3435.7 | 3395.6 | 3410.6 |
| 30°   | 10089.3 | 7882.3 | 3665.9 | 3057.8 | 3203.0 | 3355.6 | 3295.5 | 3268.0 | 3235.5 | 3190.4 | 3200.5 |
| 32.5° | 10021.7 | 7379.3 | 3150.4 | 2895.2 | 3055.3 | 3080.3 | 3122.9 | 3120.4 | 3090.4 | 3005.3 | 3000.3 |
| 35°   | 10041.8 | 6871.3 | 2805.1 | 2762.5 | 2932.7 | 2922.7 | 3002.8 | 2987.8 | 2780.1 | 2662.5 | 2654.9 |
| 37.5° | 10201.9 | 6383.4 | 2602.4 | 2657.5 | 2737.5 | 2800.1 | 2870.1 | 2690.0 | 2617.4 | 2542.3 | 2547.3 |
| 40°   | 10507.2 | 5930.5 | 2492.3 | 2599.9 | 2619.9 | 2712.5 | 2549.9 | 2547.3 | 2514.8 | 2447.3 | 2444.8 |
| 42.5° | 10852.5 | 5547.6 | 2417.2 | 2572.4 | 2544.8 | 2562.4 | 2389.7 | 2409.7 | 2407.2 | 2364.7 | 2352.2 |
| 45°   | 11062.7 | 5194.8 | 2357.2 | 2469.8 | 2477.3 | 2302.1 | 2249.6 | 2272.1 | 2284.6 | 2262.1 | 2259.6 |
| 47.5° | 10845.0 | 4789.4 | 2294.6 | 2312.1 | 2377.2 | 2184.5 | 2119.5 | 2122.0 | 2144.5 | 2147.0 | 2137.0 |
| 50°   | 10234.4 | 4336.5 | 2219.5 | 2177.0 | 2134.5 | 2061.9 | 2001.8 | 1989.3 | 2011.9 | 2034.4 | 2041.9 |
| 52.5° | 9446.2  | 3903.6 | 2094.4 | 2029.4 | 1929.3 | 1929.3 | 1901.8 | 1861.7 | 1891.7 | 1921.8 | 1931.8 |
| 55°   | 8868.2  | 3583.3 | 1916.8 | 1844.2 | 1734.1 | 1771.6 | 1766.6 | 1731.6 | 1771.6 | 1794.2 | 1801.7 |
| 57.5° | 7684.6  | 2880.2 | 1686.6 | 1664.0 | 1571.4 | 1616.5 | 1626.5 | 1581.5 | 1561.4 | 1566.4 | 1574.0 |
| 60°   | 4561.7  | 1859.2 | 1521.4 | 1518.9 | 1436.3 | 1488.9 | 1518.9 | 1473.9 | 1413.8 | 1421.3 | 1431.3 |
| 62.5° | 2046.9  | 1421.3 | 1313.7 | 1303.7 | 1301.2 | 1368.8 | 1401.3 | 1358.8 | 1273.7 | 1281.2 | 1291.2 |
| 65°   | 1288.7  | 1228.6 | 1141.1 | 1141.1 | 1181.1 | 1238.6 | 1263.7 | 1228.6 | 1131.0 | 1118.5 | 1128.5 |
| 67.5° | 1196.1  | 1143.6 | 1053.5 | 1036.0 | 1056.0 | 1103.5 | 1106.0 | 1038.5 | 980.9  | 970.9  | 970.9  |
| 70°   | 1073.5  | 1033.5 | 945.9  | 910.8  | 903.3  | 900.8  | 893.3  | 875.8  | 838.3  | 828.3  | 833.3  |
| 72.5° | 888.3   | 860.8  | 805.7  | 768.2  | 748.2  | 745.7  | 715.7  | 700.6  | 668.1  | 663.1  | 660.6  |
| 75°   | 588.0   | 595.5  | 595.5  | 590.5  | 573.0  | 565.5  | 533.0  | 518.0  | 480.4  | 465.4  | 462.9  |
| 77.5° | 347.8   | 355.3  | 365.3  | 367.8  | 365.3  | 365.3  | 335.3  | 317.8  | 280.3  | 260.2  | 255.2  |
| 80°   | 212.7   | 217.7  | 222.7  | 230.2  | 220.2  | 212.7  | 185.2  | 167.7  | 150.1  | 137.6  | 135.1  |
| 82.5° | 137.6   | 142.6  | 145.1  | 150.1  | 145.1  | 135.1  | 112.6  | 102.6  | 90.1   | 80.1   | 77.6   |
| 85°   | 77.6    | 80.1   | 85.1   | 85.1   | 77.6   | 70.1   | 57.6   | 50.0   | 42.5   | 37.5   | 37.5   |
| 87.5° | 27.5    | 27.5   | 27.5   | 30.0   | 25.0   | 22.5   | 15.0   | 10.0   | 7.5    | 7.5    | 7.5    |
| 90°   | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

**Test Information**

Test Method: LM-79-2008  
 Report Number: SP1-1908-441-1-R4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/28/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGRAW-EDISON  
 Catalog Number: **SA1C-727-U-5WQ**  
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

\*\*\*THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.\*\*\*TESTED IN  
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

**Spectral Parameters**

CCT (K): 2741  
 CIE u': 0.2605  
 CIE v': 0.5272  
 Duv: 0.0005  
 CIE x: 0.4573  
 CIE y: 0.4113  
 CIE z: 0.1313  
 Peak Wavelength (nm): 602  
 Dominant Wavelength (nm): 583  
 Purity: 61.2

|           |      |      |       |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 |      |       |
| R1:       | 69.2 | R9:  | -16.1 |
| R2:       | 79.4 | R10: | 51.4  |
| R3:       | 87.8 | R11: | 63.1  |
| R4:       | 69.4 | R12: | 42.0  |
| R5:       | 66.4 | R13: | 70.2  |
| R6:       | 69.8 | R14: | 92.4  |
| R7:       | 79.8 |      |       |
| R8:       | 50.1 |      |       |

Rf: 69.9  
 Rg: 98.3



**Test Conditions**

Stabilization Time: 56M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.3./42%  
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/28/2019        | 12/28/2019           |
| Power Meter                    | IN0071                | 12/5/2018        | 12/5/2019            |
| AC Power Source                | IN0063                | 12/5/2018        | 12/5/2019            |
| DC Power Source                | IN0208                | 12/5/2018        | 12/5/2019            |
| Sphere Thermometer             | IN0085                | 12/5/2018        | 12/5/2019            |
| Room Thermometer               | IN0046                | 12/5/2018        | 12/5/2019            |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

**Photopic Flux vs. Wavelength**



**Photopic Lumens: 6211.7**

| $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360            | 2044                              | 0.0                         | 490            | 7179                              | 1.0                         | 620            | 118034                            | 30.7                        | 750            | 8362                              | 0.0                         | 880            | 3128                              | 0.0                         |
| 365            | 2016                              | 0.0                         | 495            | 10476                             | 1.9                         | 625            | 111884                            | 24.7                        | 755            | 7635                              | 0.0                         | 885            | 3110                              | 0.0                         |
| 370            | 2020                              | 0.0                         | 500            | 15549                             | 3.4                         | 630            | 106119                            | 19.2                        | 760            | 6582                              | 0.0                         | 890            | 2632                              | 0.0                         |
| 375            | 2137                              | 0.0                         | 505            | 22477                             | 6.3                         | 635            | 99706                             | 15.0                        | 765            | 5777                              | 0.0                         | 895            | 2709                              | 0.0                         |
| 380            | 2046                              | 0.0                         | 510            | 30417                             | 10.4                        | 640            | 92142                             | 11.0                        | 770            | 5474                              | 0.0                         | 900            | 2016                              | 0.0                         |
| 385            | 1925                              | 0.0                         | 515            | 39274                             | 16.3                        | 645            | 84987                             | 8.2                         | 775            | 4977                              | 0.0                         | 905            | 1748                              | 0.0                         |
| 390            | 1893                              | 0.0                         | 520            | 47282                             | 22.9                        | 650            | 78016                             | 5.7                         | 780            | 4723                              | 0.0                         | 910            | 2046                              | 0.0                         |
| 395            | 1695                              | 0.0                         | 525            | 55413                             | 29.7                        | 655            | 71541                             | 4.1                         | 785            | 4219                              | 0.0                         | 915            | 1844                              | 0.0                         |
| 400            | 1633                              | 0.0                         | 530            | 62377                             | 36.7                        | 660            | 64863                             | 2.7                         | 790            | 3969                              | 0.0                         | 920            | 2734                              | 0.0                         |
| 405            | 2065                              | 0.0                         | 535            | 68520                             | 42.5                        | 665            | 58485                             | 1.9                         | 795            | 4122                              | 0.0                         | 925            | 2307                              | 0.0                         |
| 410            | 3449                              | 0.0                         | 540            | 73435                             | 47.8                        | 670            | 51641                             | 1.1                         | 800            | 2864                              | 0.0                         | 930            | 2039                              | 0.0                         |
| 415            | 7117                              | 0.0                         | 545            | 78677                             | 52.4                        | 675            | 46030                             | 0.8                         | 805            | 3151                              | 0.0                         | 935            | 1784                              | 0.0                         |
| 420            | 13992                             | 0.0                         | 550            | 83331                             | 56.6                        | 680            | 40590                             | 0.5                         | 810            | 3022                              | 0.0                         | 940            | 2464                              | 0.0                         |
| 425            | 25176                             | 0.1                         | 555            | 89120                             | 60.9                        | 685            | 35691                             | 0.3                         | 815            | 3471                              | 0.0                         | 945            | 2794                              | 0.0                         |
| 430            | 38151                             | 0.3                         | 560            | 94613                             | 64.3                        | 690            | 31631                             | 0.2                         | 820            | 2749                              | 0.0                         | 950            | 3090                              | 0.0                         |
| 435            | 49673                             | 0.6                         | 565            | 99818                             | 66.4                        | 695            | 27437                             | 0.1                         | 825            | 2729                              | 0.0                         | 955            | 1866                              | 0.0                         |
| 440            | 57273                             | 0.9                         | 570            | 106526                            | 69.3                        | 700            | 24589                             | 0.1                         | 830            | 2282                              | 0.0                         | 960            | 3110                              | 0.0                         |
| 445            | 54802                             | 1.1                         | 575            | 111610                            | 69.4                        | 705            | 21832                             | 0.0                         | 835            | 3140                              | 0.0                         | 965            | 3880                              | 0.0                         |
| 450            | 39184                             | 1.0                         | 580            | 117163                            | 69.6                        | 710            | 19500                             | 0.0                         | 840            | 2365                              | 0.0                         | 970            | 3243                              | 0.0                         |
| 455            | 22506                             | 0.8                         | 585            | 122201                            | 67.9                        | 715            | 17870                             | 0.0                         | 845            | 3024                              | 0.0                         | 975            | 2014                              | 0.0                         |
| 460            | 13692                             | 0.6                         | 590            | 125662                            | 65.0                        | 720            | 15924                             | 0.0                         | 850            | 2510                              | 0.0                         | 980            | 1688                              | 0.0                         |
| 465            | 9446                              | 0.5                         | 595            | 127415                            | 60.4                        | 725            | 14268                             | 0.0                         | 855            | 2739                              | 0.0                         | 985            | 2827                              | 0.0                         |
| 470            | 6698                              | 0.4                         | 600            | 129155                            | 55.7                        | 730            | 12438                             | 0.0                         | 860            | 3515                              | 0.0                         | 990            | 4172                              | 0.0                         |
| 475            | 5328                              | 0.4                         | 605            | 128057                            | 49.6                        | 735            | 11255                             | 0.0                         | 865            | 3600                              | 0.0                         | 995            | 3177                              | 0.0                         |
| 480            | 5081                              | 0.5                         | 610            | 126031                            | 43.3                        | 740            | 9951                              | 0.0                         | 870            | 3609                              | 0.0                         | 1000           | 3241                              | 0.0                         |
| 485            | 5579                              | 0.7                         | 615            | 123059                            | 37.1                        | 745            | 8870                              | 0.0                         | 875            | 3208                              | 0.0                         |                |                                   |                             |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2044          | 0.0           | 490    | 7179          | 6.0           | 620    | 118034        | 0.1           | 750    | 8362          | 0.0           | 880    | 3128          | 0.0           |
| 365    | 2016          | 0.0           | 495    | 10476         | 8.6           | 625    | 111884        | 0.1           | 755    | 7635          | 0.0           | 885    | 3110          | 0.0           |
| 370    | 2020          | 0.0           | 500    | 15549         | 12.5          | 630    | 106119        | 0.0           | 760    | 6582          | 0.0           | 890    | 2632          | 0.0           |
| 375    | 2137          | 0.0           | 505    | 22477         | 17.3          | 635    | 99706         | 0.0           | 765    | 5777          | 0.0           | 895    | 2709          | 0.0           |
| 380    | 2046          | 0.0           | 510    | 30417         | 21.8          | 640    | 92142         | 0.0           | 770    | 5474          | 0.0           | 900    | 2016          | 0.0           |
| 385    | 1925          | 0.0           | 515    | 39274         | 25.7          | 645    | 84987         | 0.0           | 775    | 4977          | 0.0           | 905    | 1748          | 0.0           |
| 390    | 1893          | 0.0           | 520    | 47282         | 27.5          | 650    | 78016         | 0.0           | 780    | 4723          | 0.0           | 910    | 2046          | 0.0           |
| 395    | 1695          | 0.0           | 525    | 55413         | 28.1          | 655    | 71541         | 0.0           | 785    | 4219          | 0.0           | 915    | 1844          | 0.0           |
| 400    | 1633          | 0.0           | 530    | 62377         | 27.0          | 660    | 64863         | 0.0           | 790    | 3969          | 0.0           | 920    | 2734          | 0.0           |
| 405    | 2065          | 0.0           | 535    | 68520         | 24.7          | 665    | 58485         | 0.0           | 795    | 4122          | 0.0           | 925    | 2307          | 0.0           |
| 410    | 3449          | 0.1           | 540    | 73435         | 21.5          | 670    | 51641         | 0.0           | 800    | 2864          | 0.0           | 930    | 2039          | 0.0           |
| 415    | 7117          | 0.5           | 545    | 78677         | 18.3          | 675    | 46030         | 0.0           | 805    | 3151          | 0.0           | 935    | 1784          | 0.0           |
| 420    | 13992         | 1.6           | 550    | 83331         | 15.0          | 680    | 40590         | 0.0           | 810    | 3022          | 0.0           | 940    | 2464          | 0.0           |
| 425    | 25176         | 3.9           | 555    | 89120         | 12.0          | 685    | 35691         | 0.0           | 815    | 3471          | 0.0           | 945    | 2794          | 0.0           |
| 430    | 38151         | 8.1           | 560    | 94613         | 9.3           | 690    | 31631         | 0.0           | 820    | 2749          | 0.0           | 950    | 3090          | 0.0           |
| 435    | 49673         | 13.3          | 565    | 99818         | 7.0           | 695    | 27437         | 0.0           | 825    | 2729          | 0.0           | 955    | 1866          | 0.0           |
| 440    | 57273         | 19.1          | 570    | 106526        | 5.2           | 700    | 24589         | 0.0           | 830    | 2282          | 0.0           | 960    | 3110          | 0.0           |
| 445    | 54802         | 21.6          | 575    | 111610        | 3.7           | 705    | 21832         | 0.0           | 835    | 3140          | 0.0           | 965    | 3880          | 0.0           |
| 450    | 39184         | 18.1          | 580    | 117163        | 2.6           | 710    | 19500         | 0.0           | 840    | 2365          | 0.0           | 970    | 3243          | 0.0           |
| 455    | 22506         | 11.8          | 585    | 122201        | 1.8           | 715    | 17870         | 0.0           | 845    | 3024          | 0.0           | 975    | 2014          | 0.0           |
| 460    | 13692         | 8.1           | 590    | 125662        | 1.2           | 720    | 15924         | 0.0           | 850    | 2510          | 0.0           | 980    | 1688          | 0.0           |
| 465    | 9446          | 6.2           | 595    | 127415        | 0.8           | 725    | 14268         | 0.0           | 855    | 2739          | 0.0           | 985    | 2827          | 0.0           |
| 470    | 6698          | 4.8           | 600    | 129155        | 0.5           | 730    | 12438         | 0.0           | 860    | 3515          | 0.0           | 990    | 4172          | 0.0           |
| 475    | 5328          | 4.1           | 605    | 128057        | 0.4           | 735    | 11255         | 0.0           | 865    | 3600          | 0.0           | 995    | 3177          | 0.0           |
| 480    | 5081          | 4.1           | 610    | 126031        | 0.2           | 740    | 9951          | 0.0           | 870    | 3609          | 0.0           | 1000   | 3241          | 0.0           |
| 485    | 5579          | 4.6           | 615    | 123059        | 0.1           | 745    | 8870          | 0.0           | 875    | 3208          | 0.0           |        |               |               |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2044          | 0.0           | 490    | 7179          | 11.1          | 620    | 118034        | 1.5           | 750    | 8362          | 0.0           | 880    | 3128          | 0.0           |
| 365    | 2016          | 0.0           | 495    | 10476         | 16.9          | 625    | 111884        | 0.9           | 755    | 7635          | 0.0           | 885    | 3110          | 0.0           |
| 370    | 2020          | 0.0           | 500    | 15549         | 26.0          | 630    | 106119        | 0.6           | 760    | 6582          | 0.0           | 890    | 2632          | 0.0           |
| 375    | 2137          | 0.0           | 505    | 22477         | 38.2          | 635    | 99706         | 0.4           | 765    | 5777          | 0.0           | 895    | 2709          | 0.0           |
| 380    | 2046          | 0.0           | 510    | 30417         | 51.6          | 640    | 92142         | 0.2           | 770    | 5474          | 0.0           | 900    | 2016          | 0.0           |
| 385    | 1925          | 0.0           | 515    | 39274         | 65.1          | 645    | 84987         | 0.1           | 775    | 4977          | 0.0           | 905    | 1748          | 0.0           |
| 390    | 1893          | 0.0           | 520    | 47282         | 75.2          | 650    | 78016         | 0.1           | 780    | 4723          | 0.0           | 910    | 2046          | 0.0           |
| 395    | 1695          | 0.0           | 525    | 55413         | 82.9          | 655    | 71541         | 0.1           | 785    | 4219          | 0.0           | 915    | 1844          | 0.0           |
| 400    | 1633          | 0.0           | 530    | 62377         | 86.0          | 660    | 64863         | 0.0           | 790    | 3969          | 0.0           | 920    | 2734          | 0.0           |
| 405    | 2065          | 0.1           | 535    | 68520         | 85.4          | 665    | 58485         | 0.0           | 795    | 4122          | 0.0           | 925    | 2307          | 0.0           |
| 410    | 3449          | 0.2           | 540    | 73435         | 81.1          | 670    | 51641         | 0.0           | 800    | 2864          | 0.0           | 930    | 2039          | 0.0           |
| 415    | 7117          | 0.7           | 545    | 78677         | 75.4          | 675    | 46030         | 0.0           | 805    | 3151          | 0.0           | 935    | 1784          | 0.0           |
| 420    | 13992         | 2.3           | 550    | 83331         | 68.1          | 680    | 40590         | 0.0           | 810    | 3022          | 0.0           | 940    | 2464          | 0.0           |
| 425    | 25176         | 6.2           | 555    | 89120         | 60.9          | 685    | 35691         | 0.0           | 815    | 3471          | 0.0           | 945    | 2794          | 0.0           |
| 430    | 38151         | 13.0          | 560    | 94613         | 52.9          | 690    | 31631         | 0.0           | 820    | 2749          | 0.0           | 950    | 3090          | 0.0           |
| 435    | 49673         | 22.2          | 565    | 99818         | 44.8          | 695    | 27437         | 0.0           | 825    | 2729          | 0.0           | 955    | 1866          | 0.0           |
| 440    | 57273         | 32.0          | 570    | 106526        | 37.6          | 700    | 24589         | 0.0           | 830    | 2282          | 0.0           | 960    | 3110          | 0.0           |
| 445    | 54802         | 36.7          | 575    | 111610        | 30.4          | 705    | 21832         | 0.0           | 835    | 3140          | 0.0           | 965    | 3880          | 0.0           |
| 450    | 39184         | 30.4          | 580    | 117163        | 24.1          | 710    | 19500         | 0.0           | 840    | 2365          | 0.0           | 970    | 3243          | 0.0           |
| 455    | 22506         | 19.7          | 585    | 122201        | 18.7          | 715    | 17870         | 0.0           | 845    | 3024          | 0.0           | 975    | 2014          | 0.0           |
| 460    | 13692         | 13.2          | 590    | 125662        | 14.0          | 720    | 15924         | 0.0           | 850    | 2510          | 0.0           | 980    | 1688          | 0.0           |
| 465    | 9446          | 10.0          | 595    | 127415        | 10.2          | 725    | 14268         | 0.0           | 855    | 2739          | 0.0           | 985    | 2827          | 0.0           |
| 470    | 6698          | 7.7           | 600    | 129155        | 7.3           | 730    | 12438         | 0.0           | 860    | 3515          | 0.0           | 990    | 4172          | 0.0           |
| 475    | 5328          | 6.7           | 605    | 128057        | 5.0           | 735    | 11255         | 0.0           | 865    | 3600          | 0.0           | 995    | 3177          | 0.0           |
| 480    | 5081          | 6.9           | 610    | 126031        | 3.4           | 740    | 9951          | 0.0           | 870    | 3609          | 0.0           | 1000   | 3241          | 0.0           |
| 485    | 5579          | 8.1           | 615    | 123059        | 2.3           | 745    | 8870          | 0.0           | 875    | 3208          | 0.0           |        |               |               |

REPORT NUMBER: SP1-1908-441-1-R4


TM-30-18

**Summary**

$R_f = 69.9$   
 $R_g = 98.3$   
 $CIE R_a = 71.5$   
 $R_9 = -16.1$



**Color Vector Graphics**





REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 |            |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)