

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P641063

Luminaire Tested: GWS-SA5F-727-U-SL4-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P641063
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-35)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA5F-727-U-SL4-W
Description: GALLEON WALL SLIM LUMINAIRE. (5) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV SPILL LIGHT ELIMINATOR OPTICS
Light Source: (80) 2700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 33523.2 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B3 - U0 - G5


Input Watts (W): 310.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P641063
 CATALOG NUMBER: GWS-SA5F-727-U-SL4-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 6.3 fc
 Type IV - Short - N/A

REPORT NUMBER: P641063
CATALOG NUMBER: GWS-SA5F-727-U-SL4-W

Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P641063

CATALOG NUMBER: GWS-SA5F-727-U-SL4-W


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 5163.4 | 0.0 | 5163.4 |
| | % Fixture | 15.4 | 0.0 | 15.4 |
| Street Side | Lumens | 28359.8 | 0.0 | 28359.8 |
| | % Fixture | 84.6 | 0.0 | 84.6 |
| Total | Lumens | 33523.2 | 0.0 | 33523.2 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 502.9 | 1.5 |
| 10°-20° | 1310.8 | 3.9 |
| 20°-30° | 2058.3 | 6.1 |
| 30°-40° | 3094.6 | 9.2 |
| 40°-50° | 4776.7 | 14.2 |
| 50°-60° | 7093.7 | 21.2 |
| 60°-70° | 8941.5 | 26.7 |
| 70°-80° | 5170.8 | 15.4 |
| 80°-90° | 573.8 | 1.7 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 33523.2 | 100.0 |
| 0°-180° | 33523.2 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P641063


CATALOG NUMBER: GWS-SA5F-727-U-SL4-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 2541.3 | 7.6 | | | |
| FM (30°-60°) | 12419.9 | 37.0 | | | |
| FH (60°-80°) | 12920.6 | 38.5 | | | G5 |
| FVH (80°-90°) | 477.9 | 1.4 | | | G3/500 |
| BL (0°-30°) | 1330.7 | 4.0 | B3/2500 | | |
| BM (30°-60°) | 2545.1 | 7.6 | B3/5000 | | |
| BH (60°-80°) | 1191.7 | 3.6 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 95.9 | 0.3 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G5

Type IV Short





REPORT NUMBER: P641063
 CATALOG NUMBER: GWS-SA5F-727-U-SL4-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 40° | 45° | 55° | 65° | 75° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 5692.6 | 5692.6 | 5692.6 | 5692.6 | 5692.6 | 5692.6 | 5692.6 | 5692.6 | 5692.6 | 5692.6 | 5692.6 |
| 2.5° | 5727.7 | 5737.7 | 5745.2 | 5755.2 | 5750.2 | 5735.2 | 5747.7 | 5747.7 | 5720.1 | 5690.1 | 5662.6 |
| 5° | 5735.2 | 5747.7 | 5745.2 | 5742.7 | 5722.7 | 5697.6 | 5697.6 | 5682.6 | 5635.1 | 5587.5 | 5542.5 |
| 7.5° | 5720.1 | 5717.6 | 5715.1 | 5707.6 | 5685.1 | 5657.6 | 5652.6 | 5622.6 | 5560.0 | 5494.9 | 5429.9 |
| 10° | 5652.6 | 5650.1 | 5657.6 | 5675.1 | 5670.1 | 5645.1 | 5645.1 | 5617.6 | 5545.0 | 5464.9 | 5379.8 |
| 12.5° | 5597.5 | 5597.5 | 5627.6 | 5675.1 | 5692.6 | 5682.6 | 5685.1 | 5665.1 | 5582.5 | 5487.4 | 5387.3 |
| 15° | 5605.0 | 5607.5 | 5672.6 | 5750.2 | 5782.7 | 5775.2 | 5777.7 | 5755.2 | 5662.6 | 5567.5 | 5432.4 |
| 17.5° | 5655.1 | 5667.6 | 5780.2 | 5887.8 | 5930.3 | 5920.3 | 5902.8 | 5865.3 | 5760.2 | 5652.6 | 5487.4 |
| 20° | 5760.2 | 5780.2 | 5925.3 | 6060.5 | 6110.5 | 6088.0 | 6058.0 | 5982.9 | 5867.8 | 5750.2 | 5547.5 |
| 22.5° | 5967.9 | 5980.4 | 6140.5 | 6273.1 | 6313.2 | 6285.7 | 6225.6 | 6118.0 | 5985.4 | 5862.8 | 5620.1 |
| 25° | 6260.6 | 6275.6 | 6428.3 | 6550.9 | 6540.9 | 6508.4 | 6425.8 | 6293.2 | 6135.5 | 6005.4 | 5725.2 |
| 27.5° | 6608.4 | 6633.5 | 6783.6 | 6881.2 | 6816.1 | 6768.6 | 6676.0 | 6515.9 | 6338.2 | 6220.6 | 5885.3 |
| 30° | 6988.8 | 6998.8 | 7126.4 | 7224.0 | 7123.9 | 7058.9 | 6946.3 | 6773.6 | 6613.5 | 6525.9 | 6125.5 |
| 32.5° | 7356.6 | 7366.6 | 7476.7 | 7531.8 | 7426.7 | 7379.1 | 7281.6 | 7098.9 | 6986.3 | 6938.7 | 6483.3 |
| 35° | 7744.5 | 7742.0 | 7832.0 | 7879.6 | 7772.0 | 7752.0 | 7651.9 | 7511.8 | 7491.7 | 7554.3 | 7006.3 |
| 37.5° | 8132.3 | 8109.8 | 8157.3 | 8219.9 | 8159.8 | 8179.9 | 8114.8 | 8067.3 | 8144.8 | 8307.5 | 7701.9 |
| 40° | 8442.6 | 8442.6 | 8492.6 | 8570.2 | 8590.2 | 8677.8 | 8640.3 | 8702.8 | 8953.1 | 9340.9 | 8562.7 |
| 42.5° | 8717.8 | 8720.3 | 8825.4 | 8945.6 | 9090.7 | 9225.8 | 9255.8 | 9418.5 | 9936.4 | 10544.5 | 9643.7 |
| 45° | 9005.6 | 9008.1 | 9150.7 | 9325.9 | 9633.7 | 9891.4 | 9951.5 | 10316.8 | 11057.5 | 11798.1 | 10817.2 |
| 47.5° | 9338.4 | 9310.9 | 9508.6 | 9801.3 | 10239.2 | 10609.5 | 10764.7 | 11282.7 | 12218.5 | 13129.3 | 11923.2 |
| 50° | 9713.7 | 9656.2 | 9876.4 | 10381.8 | 10922.3 | 11430.3 | 11690.5 | 12283.6 | 13464.6 | 14357.9 | 12964.2 |
| 52.5° | 10136.6 | 10104.1 | 10334.3 | 10949.9 | 11775.6 | 12361.1 | 12713.9 | 13492.1 | 14675.7 | 15581.5 | 13789.9 |
| 55° | 10662.1 | 10584.5 | 10917.3 | 11700.5 | 12776.5 | 13522.2 | 13940.0 | 14688.2 | 15999.4 | 16692.5 | 14420.5 |
| 57.5° | 11237.6 | 11152.5 | 11597.9 | 12638.9 | 14077.7 | 14895.9 | 15418.9 | 16034.4 | 17245.5 | 17543.3 | 14790.8 |
| 60° | 11858.2 | 11830.6 | 12358.6 | 13739.9 | 15629.1 | 16579.9 | 16957.8 | 17515.8 | 18329.0 | 18036.2 | 14698.2 |
| 62.5° | 12426.2 | 12416.2 | 13184.4 | 14933.4 | 17273.0 | 18319.0 | 18619.3 | 18766.9 | 19109.7 | 18003.7 | 13962.6 |
| 65° | 13024.2 | 13109.3 | 14147.7 | 16317.2 | 19157.2 | 20183.2 | 20308.3 | 19932.9 | 19372.4 | 17150.4 | 12456.2 |
| 67.5° | 13099.3 | 13264.4 | 14753.3 | 17613.4 | 20943.9 | 21912.2 | 21812.1 | 20375.8 | 18596.7 | 14775.8 | 9763.8 |
| 70° | 11715.5 | 12003.3 | 13787.4 | 17811.0 | 22202.5 | 22915.6 | 22192.5 | 19422.5 | 15781.7 | 10704.6 | 6140.5 |
| 72.5° | 9788.8 | 10036.5 | 11613.0 | 15188.7 | 20578.5 | 21486.8 | 20508.5 | 16439.8 | 11152.5 | 6140.5 | 3127.8 |
| 75° | 7619.4 | 7907.1 | 9360.9 | 12073.4 | 15406.4 | 15769.2 | 15278.8 | 11465.3 | 6130.5 | 2532.3 | 1421.3 |
| 77.5° | 4649.2 | 4856.9 | 5987.9 | 8179.9 | 10779.7 | 10236.7 | 8675.3 | 6428.3 | 2689.9 | 1213.6 | 878.3 |
| 80° | 2056.9 | 2184.5 | 2950.2 | 4394.0 | 6228.1 | 5887.8 | 4641.7 | 2745.0 | 1471.3 | 770.7 | 613.1 |
| 82.5° | 1103.5 | 1186.1 | 1453.8 | 1739.1 | 2735.0 | 2860.1 | 2319.6 | 1581.4 | 790.7 | 440.4 | 350.3 |
| 85° | 485.4 | 533.0 | 660.6 | 630.6 | 898.3 | 883.3 | 890.8 | 1086.0 | 377.8 | 202.7 | 227.7 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 2.5 | 2.5 | 27.5 | 145.1 | 37.5 | 60.1 | 52.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P641063
 CATALOG NUMBER: GWS-SA5F-727-U-SL4-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 5692.6 | 5692.6 | 5692.6 | 5692.6 | 5692.6 | 5692.6 | 5692.6 | 5692.6 | 5692.6 | 5692.6 | 5692.6 |
| 2.5° | 5632.6 | 5587.5 | 5575.0 | 5560.0 | 5532.5 | 5484.9 | 5449.9 | 5409.9 | 5392.4 | 5372.3 | 5374.8 |
| 5° | 5492.4 | 5437.4 | 5384.8 | 5317.3 | 5232.2 | 5137.1 | 5072.1 | 4997.0 | 4957.0 | 4919.4 | 4929.4 |
| 7.5° | 5372.3 | 5287.3 | 5179.7 | 5037.0 | 4884.4 | 4714.2 | 4576.6 | 4469.0 | 4396.5 | 4346.4 | 4371.4 |
| 10° | 5297.3 | 5197.2 | 5009.5 | 4776.8 | 4519.1 | 4258.8 | 4061.2 | 3876.0 | 3760.9 | 3670.8 | 3665.8 |
| 12.5° | 5282.3 | 5152.1 | 4879.4 | 4541.6 | 4168.8 | 3820.9 | 3530.7 | 3280.5 | 3127.8 | 3015.2 | 3057.8 |
| 15° | 5297.3 | 5132.1 | 4766.8 | 4323.9 | 3853.5 | 3383.0 | 3022.7 | 2735.0 | 2552.3 | 2449.7 | 2442.2 |
| 17.5° | 5314.8 | 5112.1 | 4639.2 | 4088.7 | 3523.2 | 2985.2 | 2567.3 | 2262.0 | 2074.4 | 1971.8 | 1974.3 |
| 20° | 5329.8 | 5082.1 | 4489.0 | 3830.9 | 3187.9 | 2614.9 | 2182.0 | 1891.7 | 1724.1 | 1649.0 | 1661.5 |
| 22.5° | 5354.8 | 5052.0 | 4328.9 | 3555.7 | 2845.1 | 2257.0 | 1876.7 | 1641.5 | 1541.4 | 1491.3 | 1493.8 |
| 25° | 5402.4 | 5034.5 | 4163.7 | 3255.4 | 2507.3 | 1971.8 | 1666.5 | 1508.9 | 1446.3 | 1416.3 | 1413.8 |
| 27.5° | 5500.0 | 5049.5 | 3991.1 | 2965.2 | 2202.0 | 1754.1 | 1531.4 | 1428.8 | 1386.2 | 1366.2 | 1363.7 |
| 30° | 5662.6 | 5109.6 | 3841.0 | 2669.9 | 1939.2 | 1583.9 | 1438.8 | 1376.2 | 1351.2 | 1333.7 | 1331.2 |
| 32.5° | 5910.3 | 5222.2 | 3678.3 | 2394.7 | 1726.6 | 1458.8 | 1366.2 | 1333.7 | 1316.2 | 1306.2 | 1306.2 |
| 35° | 6285.7 | 5427.4 | 3518.2 | 2154.4 | 1561.4 | 1361.2 | 1308.7 | 1296.2 | 1281.2 | 1276.1 | 1281.2 |
| 37.5° | 6826.1 | 5755.2 | 3373.0 | 1944.2 | 1443.8 | 1286.2 | 1246.1 | 1251.1 | 1238.6 | 1246.1 | 1253.6 |
| 40° | 7511.8 | 6193.1 | 3250.4 | 1771.6 | 1356.2 | 1231.1 | 1191.1 | 1208.6 | 1201.1 | 1208.6 | 1221.1 |
| 42.5° | 8380.0 | 6736.1 | 3157.8 | 1636.5 | 1293.7 | 1186.1 | 1148.5 | 1166.0 | 1161.0 | 1171.1 | 1183.6 |
| 45° | 9348.4 | 7451.7 | 3115.3 | 1541.4 | 1248.6 | 1153.5 | 1113.5 | 1126.0 | 1121.0 | 1128.5 | 1141.0 |
| 47.5° | 10276.7 | 8102.3 | 3152.8 | 1486.3 | 1211.1 | 1126.0 | 1083.5 | 1088.5 | 1086.0 | 1083.5 | 1091.0 |
| 50° | 11077.5 | 8620.3 | 3260.4 | 1468.8 | 1186.1 | 1098.5 | 1058.5 | 1061.0 | 1053.4 | 1038.4 | 1043.4 |
| 52.5° | 11730.6 | 9035.6 | 3325.5 | 1468.8 | 1173.6 | 1068.5 | 1030.9 | 1033.4 | 1018.4 | 998.4 | 1000.9 |
| 55° | 12160.9 | 9203.3 | 3272.9 | 1466.3 | 1168.6 | 1043.4 | 1003.4 | 1005.9 | 990.9 | 965.9 | 968.4 |
| 57.5° | 12283.6 | 9040.6 | 3052.7 | 1438.8 | 1163.5 | 1023.4 | 975.9 | 980.9 | 970.9 | 943.3 | 943.3 |
| 60° | 11940.7 | 8445.1 | 2649.9 | 1376.2 | 1151.0 | 1010.9 | 955.9 | 963.4 | 958.4 | 930.8 | 930.8 |
| 62.5° | 11042.4 | 7386.6 | 2169.5 | 1281.2 | 1116.0 | 995.9 | 938.3 | 953.4 | 965.9 | 950.9 | 948.4 |
| 65° | 9360.9 | 5917.8 | 1764.1 | 1176.1 | 1071.0 | 970.9 | 913.3 | 950.9 | 978.4 | 998.4 | 998.4 |
| 67.5° | 7023.8 | 4236.3 | 1438.8 | 1066.0 | 1003.4 | 920.8 | 880.8 | 915.8 | 935.8 | 948.4 | 955.9 |
| 70° | 4281.4 | 2492.2 | 1133.5 | 938.3 | 905.8 | 845.8 | 815.7 | 780.7 | 753.2 | 748.2 | 750.7 |
| 72.5° | 2094.4 | 1426.3 | 920.8 | 798.2 | 773.2 | 718.1 | 650.6 | 635.6 | 623.1 | 615.6 | 613.1 |
| 75° | 1153.5 | 993.4 | 760.7 | 663.1 | 618.1 | 550.5 | 535.5 | 510.5 | 505.5 | 495.4 | 497.9 |
| 77.5° | 815.7 | 783.2 | 628.1 | 538.0 | 470.4 | 435.4 | 442.9 | 425.4 | 425.4 | 417.9 | 415.4 |
| 80° | 613.1 | 615.6 | 482.9 | 392.9 | 347.8 | 335.3 | 342.8 | 342.8 | 337.8 | 335.3 | 332.8 |
| 82.5° | 387.8 | 437.9 | 325.3 | 252.7 | 247.7 | 250.2 | 247.7 | 245.2 | 250.2 | 242.7 | 240.2 |
| 85° | 267.7 | 315.3 | 197.7 | 150.1 | 150.1 | 147.6 | 152.6 | 150.1 | 155.1 | 147.6 | 147.6 |
| 87.5° | 60.1 | 140.1 | 72.6 | 45.0 | 47.5 | 45.0 | 47.5 | 50.0 | 55.0 | 57.6 | 57.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: MCGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: MCGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 $CIE R_a = 71.5$
 $R_9 = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18


Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)