

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P641086

Luminaire Tested: GWS-SA5F-727-U-T3R-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P641086
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA5F-727-U-T3R-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (5) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III ROADWAY OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (80) 2700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 30603 lumens
Efficiency: N/A
Efficacy: 98.6 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B4 - U0 - G3


Input Watts (W): 310.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P641086
 CATALOG NUMBER: GWS-SA5F-727-U-T3R-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 8.5 fc
 Type II - Short - N/A

REPORT NUMBER: P641086
CATALOG NUMBER: GWS-SA5F-727-U-T3R-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 79-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P641086

CATALOG NUMBER: GWS-SA5F-727-U-T3R-W-GRSWH

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 9096.9 | 0.0 | 9096.9 |
| | % Fixture | 29.7 | 0.0 | 29.7 |
| Street Side | Lumens | 21506.1 | 0.0 | 21506.1 |
| | % Fixture | 70.3 | 0.0 | 70.3 |
| Total | Lumens | 30603.0 | 0.0 | 30603.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 702.4 | 2.3 |
| 10°-20° | 1951.8 | 6.4 |
| 20°-30° | 3308.5 | 10.8 |
| 30°-40° | 5064.0 | 16.5 |
| 40°-50° | 6752.4 | 22.1 |
| 50°-60° | 7798.5 | 25.5 |
| 60°-70° | 4052.4 | 13.2 |
| 70°-80° | 861.4 | 2.8 |
| 80°-90° | 111.6 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 30603.0 | 100.0 |
| 0°-180° | 30603.0 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P641086


CATALOG NUMBER: GWS-SA5F-727-U-T3R-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 3379.3 | 11.0 | | | |
| FM (30°-60°) | 14788.2 | 48.3 | | | |
| FH (60°-80°) | 3299.8 | 10.8 | | | G2/5000 |
| FVH (80°-90°) | 38.9 | 0.1 | | | G1/100 |
| BL (0°-30°) | 2583.4 | 8.4 | B4/5000 | | |
| BM (30°-60°) | 4826.7 | 15.8 | B3/5000 | | |
| BH (60°-80°) | 1614.0 | 5.3 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 72.7 | 0.2 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B4-U0-G3

Type II Short





REPORT NUMBER: P641086

CATALOG NUMBER: GWS-SA5F-727-U-T3R-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 79° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 7584.1 | 7584.1 | 7584.1 | 7584.1 | 7584.1 | 7584.1 | 7584.1 | 7584.1 | 7584.1 | 7584.1 | 7584.1 |
| 2.5° | 7238.8 | 7223.8 | 7228.8 | 7248.8 | 7323.9 | 7379.0 | 7436.5 | 7489.0 | 7539.1 | 7554.1 | 7566.6 |
| 5° | 6981.1 | 6953.6 | 6961.1 | 6993.6 | 7081.2 | 7173.8 | 7276.4 | 7401.5 | 7521.6 | 7561.6 | 7614.2 |
| 7.5° | 6798.4 | 6793.4 | 6806.0 | 6856.0 | 6948.6 | 7036.2 | 7168.8 | 7346.4 | 7554.1 | 7621.7 | 7714.2 |
| 10° | 6555.7 | 6545.7 | 6595.8 | 6698.4 | 6851.0 | 6991.1 | 7148.8 | 7358.9 | 7649.2 | 7749.3 | 7891.9 |
| 12.5° | 6363.1 | 6358.1 | 6410.6 | 6553.2 | 6748.4 | 6971.1 | 7188.8 | 7424.0 | 7776.8 | 7914.4 | 8089.6 |
| 15° | 6475.7 | 6453.1 | 6455.6 | 6555.7 | 6730.9 | 6993.6 | 7288.9 | 7541.6 | 7904.4 | 8079.6 | 8304.8 |
| 17.5° | 6803.4 | 6763.4 | 6733.4 | 6750.9 | 6851.0 | 7123.7 | 7441.5 | 7699.2 | 8052.0 | 8257.2 | 8532.5 |
| 20° | 7256.3 | 7233.8 | 7151.3 | 7096.2 | 7118.7 | 7358.9 | 7681.7 | 7921.9 | 8244.7 | 8474.9 | 8770.2 |
| 22.5° | 7864.4 | 7809.3 | 7696.7 | 7609.2 | 7541.6 | 7729.3 | 8027.0 | 8234.7 | 8512.4 | 8752.7 | 9060.4 |
| 25° | 8617.5 | 8537.5 | 8359.8 | 8222.2 | 8077.1 | 8269.7 | 8535.0 | 8692.6 | 8880.3 | 9103.0 | 9395.7 |
| 27.5° | 9385.7 | 9318.1 | 9120.5 | 8935.3 | 8755.2 | 8875.3 | 9190.5 | 9280.6 | 9260.6 | 9423.2 | 9673.5 |
| 30° | 10203.9 | 10118.8 | 9931.2 | 9731.0 | 9498.3 | 9575.9 | 9858.6 | 9903.7 | 9691.0 | 9826.1 | 9996.2 |
| 32.5° | 11067.2 | 10984.6 | 10822.0 | 10589.3 | 10326.5 | 10356.6 | 10434.1 | 10476.7 | 10274.0 | 10351.6 | 10481.7 |
| 35° | 11945.4 | 11867.9 | 11702.7 | 11472.5 | 11279.9 | 11097.2 | 10902.0 | 11072.2 | 10954.6 | 11104.7 | 11094.7 |
| 37.5° | 12748.6 | 12671.1 | 12568.5 | 12390.8 | 12060.5 | 11700.2 | 11249.8 | 11460.0 | 11642.7 | 11832.8 | 11800.3 |
| 40° | 13291.6 | 13239.1 | 13264.1 | 13236.6 | 12811.2 | 12098.1 | 11420.0 | 11650.2 | 12148.1 | 12473.4 | 12455.9 |
| 42.5° | 13759.5 | 13707.0 | 13852.1 | 13957.2 | 13456.8 | 12465.9 | 11502.6 | 11722.7 | 12470.9 | 12978.8 | 12953.8 |
| 45° | 13967.2 | 13952.2 | 14192.4 | 14525.2 | 14047.3 | 12856.2 | 11715.2 | 11872.9 | 12716.1 | 13366.7 | 13271.6 |
| 47.5° | 13719.5 | 13772.0 | 14245.0 | 14807.9 | 14537.7 | 13319.1 | 12150.6 | 12190.7 | 13036.4 | 13787.1 | 13519.3 |
| 50° | 13226.6 | 13341.7 | 13979.7 | 14815.5 | 14895.5 | 13842.1 | 12753.7 | 12653.6 | 13466.8 | 14234.9 | 13649.4 |
| 52.5° | 12508.4 | 12628.5 | 13669.5 | 14757.9 | 15100.7 | 14447.6 | 13556.9 | 13414.2 | 14009.7 | 14682.8 | 13672.0 |
| 55° | 10859.5 | 11022.1 | 12958.8 | 14627.8 | 15300.9 | 14998.1 | 14462.6 | 14172.4 | 14710.4 | 15298.4 | 13894.6 |
| 57.5° | 9420.7 | 9505.8 | 11227.3 | 14049.8 | 15340.9 | 15403.5 | 15108.2 | 14762.9 | 15406.0 | 15964.0 | 14144.9 |
| 60° | 6913.5 | 6933.6 | 8482.4 | 11625.2 | 14112.3 | 15168.3 | 15055.7 | 14542.7 | 15075.7 | 15431.0 | 12998.9 |
| 62.5° | 3905.9 | 3908.4 | 5144.5 | 7759.3 | 10541.7 | 12363.3 | 12433.4 | 11980.5 | 11532.6 | 11637.7 | 9047.9 |
| 65° | 1466.3 | 1603.9 | 2349.6 | 3813.3 | 6077.8 | 7298.9 | 7589.1 | 7694.2 | 6948.6 | 6485.7 | 4851.7 |
| 67.5° | 980.9 | 1013.4 | 1371.2 | 1961.7 | 2704.9 | 3122.7 | 3493.1 | 3503.1 | 2562.2 | 2284.5 | 1911.7 |
| 70° | 748.2 | 780.7 | 1078.4 | 1403.7 | 1371.2 | 1266.1 | 1368.7 | 1331.2 | 1376.2 | 1413.7 | 1453.8 |
| 72.5° | 558.0 | 590.5 | 835.7 | 990.9 | 823.2 | 810.7 | 918.3 | 1020.9 | 1116.0 | 1156.0 | 1218.6 |
| 75° | 370.3 | 395.3 | 563.0 | 530.5 | 455.4 | 538.0 | 670.6 | 773.2 | 828.2 | 875.8 | 923.3 |
| 77.5° | 235.2 | 252.7 | 300.3 | 242.7 | 252.7 | 315.3 | 390.3 | 482.9 | 535.5 | 583.0 | 608.0 |
| 80° | 107.6 | 105.1 | 102.6 | 115.1 | 142.6 | 185.2 | 235.2 | 290.3 | 330.3 | 350.3 | 365.3 |
| 82.5° | 42.5 | 47.5 | 52.5 | 62.6 | 77.6 | 100.1 | 132.6 | 170.1 | 202.7 | 207.7 | 220.2 |
| 85° | 17.5 | 20.0 | 22.5 | 27.5 | 35.0 | 45.0 | 55.0 | 77.6 | 97.6 | 105.1 | 112.6 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 2.5 | 5.0 | 7.5 | 12.5 | 22.5 | 25.0 | 27.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P641086

CATALOG NUMBER: GWS-SA5F-727-U-T3R-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 7584.1 | 7584.1 | 7584.1 | 7584.1 | 7584.1 | 7584.1 | 7584.1 | 7584.1 | 7584.1 | 7584.1 | 7584.1 |
| 2.5° | 7634.2 | 7601.6 | 7656.7 | 7694.2 | 7729.3 | 7691.7 | 7679.2 | 7646.7 | 7641.7 | 7641.7 | 7659.2 |
| 5° | 7704.2 | 7681.7 | 7739.3 | 7761.8 | 7759.3 | 7676.7 | 7626.7 | 7561.6 | 7529.1 | 7529.1 | 7534.1 |
| 7.5° | 7829.3 | 7816.8 | 7849.4 | 7814.3 | 7734.3 | 7566.6 | 7401.5 | 7263.9 | 7171.3 | 7123.7 | 7138.7 |
| 10° | 8037.0 | 8022.0 | 7994.5 | 7864.4 | 7634.2 | 7286.4 | 6948.6 | 6698.4 | 6548.2 | 6463.2 | 6468.2 |
| 12.5° | 8239.7 | 8214.7 | 8117.1 | 7829.3 | 7356.4 | 6803.4 | 6360.6 | 6080.3 | 5915.2 | 5815.1 | 5792.6 |
| 15° | 8462.4 | 8397.3 | 8187.2 | 7649.2 | 6903.5 | 6212.9 | 5750.0 | 5447.3 | 5269.6 | 5209.6 | 5207.1 |
| 17.5° | 8675.1 | 8560.0 | 8179.7 | 7328.9 | 6360.6 | 5594.9 | 5129.5 | 4941.8 | 4911.8 | 4939.3 | 4946.8 |
| 20° | 8890.3 | 8705.1 | 8097.1 | 6886.0 | 5715.0 | 4979.4 | 4739.1 | 4816.7 | 4929.3 | 5004.4 | 5021.9 |
| 22.5° | 9113.0 | 8825.2 | 7909.4 | 6315.5 | 5034.4 | 4564.0 | 4664.1 | 4834.2 | 4974.3 | 5074.4 | 5084.4 |
| 25° | 9363.2 | 8937.8 | 7629.2 | 5617.4 | 4488.9 | 4448.9 | 4646.6 | 4826.7 | 4976.9 | 5092.0 | 5112.0 |
| 27.5° | 9505.8 | 8940.3 | 7236.3 | 4899.3 | 4238.7 | 4403.9 | 4604.0 | 4774.2 | 4924.3 | 5049.4 | 5071.9 |
| 30° | 9645.9 | 8872.8 | 6613.3 | 4316.3 | 4166.1 | 4351.3 | 4531.5 | 4689.1 | 4831.7 | 4954.3 | 4981.9 |
| 32.5° | 9843.6 | 8810.2 | 5895.2 | 3981.0 | 4123.6 | 4301.3 | 4448.9 | 4589.0 | 4699.1 | 4754.2 | 4769.2 |
| 35° | 10088.8 | 8730.1 | 5132.0 | 3835.9 | 4096.1 | 4261.2 | 4391.3 | 4466.4 | 4323.8 | 4293.8 | 4326.3 |
| 37.5° | 10431.6 | 8655.1 | 4371.3 | 3773.3 | 4078.6 | 4246.2 | 4361.3 | 4168.6 | 3993.5 | 3923.4 | 3948.5 |
| 40° | 10801.9 | 8612.5 | 3855.9 | 3723.3 | 4086.1 | 4261.2 | 4236.2 | 3951.0 | 3698.2 | 3550.6 | 3545.6 |
| 42.5° | 11117.2 | 8547.5 | 3525.6 | 3690.7 | 4106.1 | 4318.8 | 4066.1 | 3758.3 | 3383.0 | 3295.4 | 3297.9 |
| 45° | 11329.9 | 8382.3 | 3350.4 | 3655.7 | 4123.6 | 4331.3 | 3986.0 | 3493.1 | 3225.3 | 3170.3 | 3167.8 |
| 47.5° | 11417.5 | 8082.1 | 3237.8 | 3600.6 | 4121.1 | 4228.7 | 3823.3 | 3383.0 | 3115.2 | 3100.2 | 3110.2 |
| 50° | 11359.9 | 7589.1 | 3122.7 | 3493.1 | 4061.1 | 4121.1 | 3635.7 | 3285.4 | 3040.2 | 3122.7 | 3182.8 |
| 52.5° | 11147.2 | 6951.1 | 2985.1 | 3345.4 | 3953.5 | 3998.5 | 3540.6 | 3225.3 | 2985.1 | 3095.2 | 3142.7 |
| 55° | 11092.2 | 6433.1 | 2810.0 | 3152.8 | 3793.3 | 3780.8 | 3440.5 | 3195.3 | 2947.6 | 2905.0 | 2912.5 |
| 57.5° | 11019.6 | 5927.7 | 2519.7 | 2807.5 | 3388.0 | 3408.0 | 3345.4 | 3160.3 | 2850.0 | 2837.5 | 2850.0 |
| 60° | 9573.4 | 4544.0 | 2247.0 | 2422.1 | 2782.4 | 2890.0 | 3237.8 | 3095.2 | 2692.4 | 2639.8 | 2637.3 |
| 62.5° | 6253.0 | 2752.4 | 1999.2 | 2111.8 | 2267.0 | 2392.1 | 2952.6 | 2907.5 | 2519.7 | 2487.2 | 2509.7 |
| 65° | 3362.9 | 1961.7 | 1819.1 | 1886.6 | 1971.7 | 2066.8 | 2447.1 | 2589.8 | 2277.0 | 2161.9 | 2164.4 |
| 67.5° | 1719.0 | 1669.0 | 1684.0 | 1731.5 | 1796.6 | 1844.1 | 1974.2 | 2099.3 | 1941.7 | 1844.1 | 1841.6 |
| 70° | 1471.3 | 1511.3 | 1533.8 | 1561.4 | 1603.9 | 1596.4 | 1608.9 | 1631.4 | 1618.9 | 1571.4 | 1568.9 |
| 72.5° | 1253.6 | 1316.2 | 1321.2 | 1326.2 | 1341.2 | 1306.1 | 1283.6 | 1246.1 | 1248.6 | 1256.1 | 1258.6 |
| 75° | 953.3 | 1013.4 | 1028.4 | 1020.9 | 1035.9 | 990.9 | 960.8 | 923.3 | 878.3 | 870.8 | 875.8 |
| 77.5° | 620.5 | 668.1 | 690.6 | 685.6 | 693.1 | 658.1 | 643.1 | 603.0 | 550.5 | 530.5 | 530.5 |
| 80° | 375.3 | 402.9 | 420.4 | 425.4 | 432.9 | 407.9 | 382.8 | 347.8 | 325.3 | 302.8 | 302.8 |
| 82.5° | 227.7 | 245.2 | 257.7 | 257.7 | 265.2 | 237.7 | 217.7 | 192.7 | 182.7 | 162.6 | 162.6 |
| 85° | 115.1 | 127.6 | 132.6 | 130.1 | 125.1 | 102.6 | 95.1 | 82.6 | 77.6 | 67.6 | 67.6 |
| 87.5° | 27.5 | 35.0 | 35.0 | 25.0 | 25.0 | 12.5 | 7.5 | 2.5 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 CIE $R_a = 71.5$
 $R_g = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)