

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P641090

Luminaire Tested: GWS-SA5F-727-U-T4FT-W

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641090  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-54)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA5F-727-U-T4FT-W  
Description: GALLEON WALL SLIM LUMINAIRE. (5) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV FORWARD THROW OPTICS  
Light Source: (80) 2700K CCT, 70 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 33715.9 lumens  
Efficiency: N/A  
Efficacy: 108.7 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B3 - U0 - G5  
  
Input Watts (W): 310.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P641090  
 CATALOG NUMBER: GWS-SA5F-727-U-T4FT-W

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 5.8 fc  
 Type IV - Short - N/A

REPORT NUMBER: P641090  
CATALOG NUMBER: GWS-SA5F-727-U-T4FT-W

### Luminous Intensity Polar Plot



— Vertical Plane Through 36-Deg Lateral    - - - Horizontal Cone Through 72.5-Deg Vertical

REPORT NUMBER: P641090

CATALOG NUMBER: GWS-SA5F-727-U-T4FT-W

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 7773.0   | 0.0    | 7773.0  |
|                    | % Fixture | 23.1     | 0.0    | 23.1    |
| <b>Street Side</b> | Lumens    | 25942.9  | 0.0    | 25942.9 |
|                    | % Fixture | 76.9     | 0.0    | 76.9    |
| <b>Total</b>       | Lumens    | 33715.9  | 0.0    | 33715.9 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 461.2   | 1.4       |
| 10°-20°   | 1301.3  | 3.9       |
| 20°-30°   | 2155.2  | 6.4       |
| 30°-40°   | 3227.6  | 9.6       |
| 40°-50°   | 4708.7  | 14.0      |
| 50°-60°   | 6702.0  | 19.9      |
| 60°-70°   | 8467.4  | 25.1      |
| 70°-80°   | 6033.8  | 17.9      |
| 80°-90°   | 658.7   | 2.0       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 33715.9 | 100.0     |
| 0°-180°   | 33715.9 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P641090


CATALOG NUMBER: GWS-SA5F-727-U-T4FT-W

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|---------|-----------|-------------------------|------|---------|
|                |         |           | B                       | U    | G       |
| FL (0°-30°)    | 1882.3  | 5.6       |                         |      |         |
| FM (30°-60°)   | 10805.1 | 32.0      |                         |      |         |
| FH (60°-80°)   | 12782.8 | 37.9      |                         |      | G5      |
| FVH (80°-90°)  | 472.8   | 1.4       |                         |      | G3/500  |
| BL (0°-30°)    | 2035.5  | 6.0       | B3/2500                 |      |         |
| BM (30°-60°)   | 3833.2  | 11.4      | B3/5000                 |      |         |
| BH (60°-80°)   | 1718.4  | 5.1       | B3/2500                 |      | G3/2500 |
| BVH (80°-90°)  | 185.9   | 0.6       |                         |      | G2/225  |
| UL (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0     | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G5**

Type IV Short





REPORT NUMBER: P641090

CATALOG NUMBER: GWS-SA5F-727-U-T4FT-W

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 15°     | 25°     | 35°     | 36°     | 45°     | 55°     | 65°     | 75°     | 85°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 4934.5  | 4934.5  | 4934.5  | 4934.5  | 4934.5  | 4934.5  | 4934.5  | 4934.5  | 4934.5  | 4934.5  | 4934.5  |
| 2.5°  | 4501.6  | 4494.1  | 4479.1  | 4524.1  | 4569.1  | 4564.1  | 4626.7  | 4686.7  | 4751.8  | 4819.4  | 4909.5  |
| 5°    | 4141.3  | 4136.2  | 4123.7  | 4191.3  | 4258.9  | 4256.4  | 4359.0  | 4456.5  | 4589.2  | 4734.3  | 4914.5  |
| 7.5°  | 3780.9  | 3768.4  | 3785.9  | 3871.0  | 3966.1  | 3976.1  | 4116.2  | 4276.4  | 4469.1  | 4686.7  | 4942.0  |
| 10°   | 3463.1  | 3460.6  | 3468.1  | 3563.2  | 3705.9  | 3715.9  | 3896.0  | 4118.7  | 4374.0  | 4664.2  | 5004.5  |
| 12.5° | 3380.6  | 3375.6  | 3355.5  | 3403.1  | 3510.7  | 3525.7  | 3723.4  | 3996.1  | 4308.9  | 4676.7  | 5089.6  |
| 15°   | 3515.7  | 3503.2  | 3433.1  | 3410.6  | 3463.1  | 3475.7  | 3643.3  | 3923.6  | 4271.4  | 4699.3  | 5197.2  |
| 17.5° | 3748.4  | 3740.9  | 3608.3  | 3515.7  | 3550.7  | 3560.7  | 3685.8  | 3911.0  | 4261.4  | 4744.3  | 5329.8  |
| 20°   | 4088.7  | 4056.2  | 3848.5  | 3708.4  | 3708.4  | 3723.4  | 3798.4  | 3966.1  | 4273.9  | 4799.4  | 5480.0  |
| 22.5° | 4539.1  | 4474.1  | 4181.3  | 3991.1  | 3941.1  | 3961.1  | 3993.6  | 4103.7  | 4326.4  | 4891.9  | 5667.6  |
| 25°   | 5044.6  | 4984.5  | 4636.7  | 4369.0  | 4298.9  | 4306.4  | 4278.9  | 4298.9  | 4441.5  | 5019.6  | 5900.3  |
| 27.5° | 5582.6  | 5542.5  | 5172.2  | 4831.9  | 4721.8  | 4721.8  | 4624.2  | 4576.6  | 4601.7  | 5164.7  | 6160.6  |
| 30°   | 6063.0  | 6007.9  | 5695.2  | 5322.3  | 5177.2  | 5177.2  | 4992.0  | 4889.4  | 4829.4  | 5342.3  | 6508.4  |
| 32.5° | 6315.7  | 6283.2  | 6075.5  | 5790.2  | 5612.6  | 5585.1  | 5424.9  | 5304.8  | 5164.7  | 5605.1  | 6978.8  |
| 35°   | 6646.0  | 6638.5  | 6513.4  | 6290.7  | 6065.5  | 6025.5  | 5915.4  | 5820.3  | 5577.6  | 5932.9  | 7604.4  |
| 37.5° | 7061.4  | 7048.9  | 7028.9  | 6896.3  | 6626.0  | 6618.5  | 6520.9  | 6405.8  | 6090.5  | 6405.8  | 8362.6  |
| 40°   | 7526.8  | 7504.3  | 7479.3  | 7476.8  | 7314.1  | 7286.6  | 7279.1  | 7149.0  | 6708.6  | 6976.3  | 9153.3  |
| 42.5° | 8167.4  | 8089.8  | 7854.6  | 7959.7  | 8079.8  | 8054.8  | 8149.9  | 7954.7  | 7479.3  | 7654.4  | 9901.5  |
| 45°   | 8955.6  | 8765.4  | 8300.0  | 8330.1  | 8632.8  | 8682.9  | 9013.2  | 8965.6  | 8327.5  | 8437.6  | 10689.7 |
| 47.5° | 9428.5  | 9263.4  | 8830.5  | 8805.5  | 9183.3  | 9245.9  | 9964.0  | 10054.1 | 9240.9  | 9381.0  | 11663.1 |
| 50°   | 9816.4  | 9701.3  | 9346.0  | 9381.0  | 9781.4  | 9843.9  | 10907.4 | 11100.1 | 10101.7 | 10346.9 | 12794.1 |
| 52.5° | 10284.3 | 10119.2 | 9843.9  | 10009.1 | 10499.5 | 10574.6 | 11955.8 | 12163.5 | 10877.4 | 11407.8 | 13965.2 |
| 55°   | 10547.1 | 10479.5 | 10484.5 | 10737.2 | 11352.8 | 11455.4 | 13054.3 | 13019.3 | 11588.0 | 12316.2 | 14846.0 |
| 57.5° | 11152.6 | 11127.6 | 11357.8 | 11452.9 | 12348.7 | 12481.3 | 14152.8 | 13852.6 | 12233.6 | 13019.3 | 15268.8 |
| 60°   | 12221.1 | 12158.5 | 12358.7 | 12503.8 | 13579.8 | 13767.5 | 15378.9 | 14668.3 | 12671.5 | 13542.3 | 15126.2 |
| 62.5° | 13722.4 | 13644.9 | 13652.4 | 13882.6 | 15228.8 | 15426.5 | 16742.7 | 15348.9 | 12806.6 | 13622.3 | 14222.9 |
| 65°   | 15589.1 | 15476.5 | 15348.9 | 15661.7 | 17418.3 | 17583.4 | 18226.5 | 15844.4 | 12483.8 | 12851.6 | 12336.2 |
| 67.5° | 17558.4 | 17465.8 | 17315.7 | 17971.3 | 20253.4 | 20353.4 | 19890.5 | 15801.8 | 11460.4 | 10789.8 | 8652.8  |
| 70°   | 17673.5 | 17696.0 | 18406.7 | 20778.8 | 23954.2 | 23979.2 | 21464.5 | 14946.0 | 9280.9  | 6993.8  | 4311.4  |
| 72.5° | 16487.4 | 16449.9 | 17375.8 | 21291.8 | 26931.9 | 27017.0 | 22207.6 | 12108.5 | 5735.2  | 3488.2  | 2021.8  |
| 75°   | 13392.1 | 13457.2 | 14430.6 | 18629.4 | 23083.4 | 23158.5 | 18103.9 | 7139.0  | 2725.0  | 1706.5  | 1293.7  |
| 77.5° | 5765.2  | 6128.1  | 8047.3  | 13124.4 | 16532.5 | 16299.8 | 9331.0  | 2892.6  | 1453.8  | 1216.1  | 990.9   |
| 80°   | 1664.0  | 1806.6  | 2867.6  | 6240.7  | 9906.5  | 9731.3  | 3693.3  | 1083.5  | 1013.4  | 913.3   | 710.6   |
| 82.5° | 538.0   | 595.5   | 1051.0  | 2484.8  | 4439.0  | 4434.0  | 1401.3  | 640.6   | 663.1   | 620.6   | 457.9   |
| 85°   | 150.1   | 172.7   | 322.8   | 753.2   | 1373.7  | 1346.2  | 405.4   | 302.8   | 352.8   | 357.8   | 227.7   |
| 87.5° | 0.0     | 0.0     | 2.5     | 5.0     | 5.0     | 5.0     | 10.0    | 45.0    | 102.6   | 130.1   | 92.6    |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P641090  
 CATALOG NUMBER: GWS-SA5F-727-U-T4FT-W

**CANDELA DISTRIBUTION (continued):**

|       | 90°     | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 4934.5  | 4934.5 | 4934.5 | 4934.5 | 4934.5 | 4934.5 | 4934.5 | 4934.5 | 4934.5 | 4934.5 | 4934.5 |
| 2.5°  | 4964.5  | 4957.0 | 5059.6 | 5139.7 | 5214.7 | 5264.8 | 5279.8 | 5289.8 | 5309.8 | 5319.8 | 5309.8 |
| 5°    | 4999.5  | 5037.1 | 5207.2 | 5332.3 | 5432.4 | 5492.5 | 5495.0 | 5490.0 | 5505.0 | 5492.5 | 5485.0 |
| 7.5°  | 5074.6  | 5147.2 | 5362.4 | 5495.0 | 5560.0 | 5562.5 | 5502.5 | 5432.4 | 5397.4 | 5367.4 | 5357.4 |
| 10°   | 5174.7  | 5282.3 | 5517.5 | 5605.1 | 5585.1 | 5492.5 | 5359.9 | 5249.8 | 5187.2 | 5142.2 | 5132.2 |
| 12.5° | 5312.3  | 5432.4 | 5655.1 | 5652.6 | 5527.5 | 5362.4 | 5207.2 | 5074.6 | 4984.5 | 4932.0 | 4914.5 |
| 15°   | 5442.4  | 5595.1 | 5755.2 | 5637.6 | 5439.9 | 5239.7 | 5039.6 | 4861.9 | 4741.8 | 4659.2 | 4644.2 |
| 17.5° | 5602.6  | 5765.2 | 5827.8 | 5590.1 | 5329.8 | 5072.1 | 4804.4 | 4571.6 | 4409.0 | 4311.4 | 4303.9 |
| 20°   | 5787.7  | 5932.9 | 5862.8 | 5507.5 | 5187.2 | 4849.4 | 4486.6 | 4226.3 | 4051.2 | 3956.1 | 3963.6 |
| 22.5° | 6002.9  | 6108.0 | 5872.8 | 5394.9 | 4989.5 | 4534.1 | 4128.7 | 3878.5 | 3760.9 | 3710.9 | 3713.4 |
| 25°   | 6233.2  | 6300.7 | 5855.3 | 5242.3 | 4686.7 | 4148.8 | 3760.9 | 3645.8 | 3635.8 | 3623.3 | 3628.3 |
| 27.5° | 6505.9  | 6490.9 | 5802.8 | 5027.1 | 4278.9 | 3700.9 | 3503.2 | 3533.2 | 3573.2 | 3568.2 | 3573.2 |
| 30°   | 6871.2  | 6728.6 | 5735.2 | 4729.3 | 3793.4 | 3325.5 | 3350.5 | 3435.6 | 3488.2 | 3493.2 | 3508.2 |
| 32.5° | 7289.1  | 6991.3 | 5627.6 | 4323.9 | 3330.5 | 3115.3 | 3207.9 | 3310.5 | 3373.1 | 3385.6 | 3405.6 |
| 35°   | 7787.1  | 7291.6 | 5437.4 | 3818.5 | 2997.7 | 2990.2 | 3075.3 | 3145.4 | 3212.9 | 3217.9 | 3217.9 |
| 37.5° | 8360.1  | 7591.9 | 5134.7 | 3260.5 | 2792.5 | 2882.6 | 2962.7 | 2977.7 | 2995.2 | 2980.2 | 2987.7 |
| 40°   | 8885.6  | 7882.1 | 4704.3 | 2752.5 | 2624.9 | 2787.5 | 2855.1 | 2805.0 | 2750.0 | 2712.5 | 2720.0 |
| 42.5° | 9326.0  | 8079.8 | 4133.7 | 2397.2 | 2454.7 | 2702.4 | 2755.0 | 2652.4 | 2544.8 | 2474.7 | 2484.8 |
| 45°   | 9821.4  | 8262.5 | 3463.1 | 2157.0 | 2309.6 | 2642.4 | 2677.4 | 2544.8 | 2407.2 | 2302.1 | 2287.1 |
| 47.5° | 10504.5 | 8635.3 | 2867.6 | 1989.3 | 2207.0 | 2609.9 | 2667.4 | 2487.3 | 2307.1 | 2149.4 | 2131.9 |
| 50°   | 11347.8 | 9163.3 | 2369.6 | 1879.2 | 2159.5 | 2592.3 | 2664.9 | 2424.7 | 2209.5 | 2024.3 | 2011.8 |
| 52.5° | 12268.6 | 9678.8 | 2001.8 | 1794.1 | 2111.9 | 2539.8 | 2652.4 | 2354.6 | 2106.9 | 1906.7 | 1891.7 |
| 55°   | 12881.7 | 9881.5 | 1754.1 | 1714.1 | 2034.3 | 2457.2 | 2602.4 | 2287.1 | 1951.8 | 1769.1 | 1746.6 |
| 57.5° | 13061.8 | 9621.2 | 1581.4 | 1641.5 | 1934.3 | 2342.1 | 2507.3 | 2144.4 | 1856.7 | 1711.6 | 1694.0 |
| 60°   | 12751.6 | 8965.6 | 1473.8 | 1581.4 | 1824.2 | 2194.5 | 2342.1 | 2061.9 | 1781.6 | 1651.5 | 1639.0 |
| 62.5° | 11875.8 | 7954.7 | 1391.3 | 1518.9 | 1711.6 | 2039.3 | 2237.0 | 1961.8 | 1699.0 | 1596.4 | 1578.9 |
| 65°   | 10114.2 | 6523.4 | 1323.7 | 1453.8 | 1604.0 | 1891.7 | 2121.9 | 1861.7 | 1609.0 | 1531.4 | 1511.4 |
| 67.5° | 7073.9  | 4581.7 | 1251.1 | 1376.2 | 1496.4 | 1749.1 | 2001.8 | 1769.1 | 1516.4 | 1458.8 | 1438.8 |
| 70°   | 3458.1  | 2429.7 | 1163.6 | 1286.2 | 1381.3 | 1604.0 | 1881.7 | 1656.5 | 1393.8 | 1361.2 | 1333.7 |
| 72.5° | 1646.5  | 1358.7 | 1061.0 | 1163.6 | 1223.6 | 1411.3 | 1681.5 | 1493.9 | 1248.6 | 1178.6 | 1131.0 |
| 75°   | 1103.5  | 965.9  | 925.8  | 1018.4 | 1033.4 | 1183.6 | 1441.3 | 1288.7 | 1101.0 | 1020.9 | 980.9  |
| 77.5° | 835.8   | 738.2  | 778.2  | 860.8  | 830.8  | 973.4  | 1186.1 | 1148.5 | 993.4  | 920.8  | 900.8  |
| 80°   | 588.0   | 538.0  | 618.1  | 668.1  | 645.6  | 828.3  | 1068.5 | 983.4  | 818.2  | 738.2  | 723.2  |
| 82.5° | 370.3   | 360.3  | 455.4  | 462.9  | 470.4  | 655.6  | 878.3  | 773.2  | 635.6  | 523.0  | 485.4  |
| 85°   | 185.2   | 205.2  | 272.7  | 272.7  | 270.2  | 337.8  | 500.5  | 435.4  | 342.8  | 272.7  | 265.2  |
| 87.5° | 62.6    | 87.6   | 117.6  | 95.1   | 72.6   | 57.6   | 65.1   | 80.1   | 85.1   | 82.6   | 82.6   |
| 90°   | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

**Test Information**

Test Method: LM-79-2008  
 Report Number: SP1-1908-441-1-R4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/28/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGRAW-EDISON  
 Catalog Number: **SA1C-727-U-5WQ**  
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

\*\*\*THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.\*\*\*TESTED IN  
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

**Spectral Parameters**

CCT (K): 2741  
 CIE u': 0.2605  
 CIE v': 0.5272  
 Duv: 0.0005  
 CIE x: 0.4573  
 CIE y: 0.4113  
 CIE z: 0.1313  
 Peak Wavelength (nm): 602  
 Dominant Wavelength (nm): 583  
 Purity: 61.2  
 Rf: 69.9  
 Rg: 98.3

|           |      |      |       |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 |      |       |
| R1:       | 69.2 | R9:  | -16.1 |
| R2:       | 79.4 | R10: | 51.4  |
| R3:       | 87.8 | R11: | 63.1  |
| R4:       | 69.4 | R12: | 42.0  |
| R5:       | 66.4 | R13: | 70.2  |
| R6:       | 69.8 | R14: | 92.4  |
| R7:       | 79.8 |      |       |
| R8:       | 50.1 |      |       |



**Test Conditions**

Stabilization Time: 56M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.3./42%  
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/28/2019        | 12/28/2019           |
| Power Meter                    | IN0071                | 12/5/2018        | 12/5/2019            |
| AC Power Source                | IN0063                | 12/5/2018        | 12/5/2019            |
| DC Power Source                | IN0208                | 12/5/2018        | 12/5/2019            |
| Sphere Thermometer             | IN0085                | 12/5/2018        | 12/5/2019            |
| Room Thermometer               | IN0046                | 12/5/2018        | 12/5/2019            |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

**Photopic Flux vs. Wavelength**



**Photopic Lumens: 6211.7**

| $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360            | 2044                              | 0.0                         | 490            | 7179                              | 1.0                         | 620            | 118034                            | 30.7                        | 750            | 8362                              | 0.0                         | 880            | 3128                              | 0.0                         |
| 365            | 2016                              | 0.0                         | 495            | 10476                             | 1.9                         | 625            | 111884                            | 24.7                        | 755            | 7635                              | 0.0                         | 885            | 3110                              | 0.0                         |
| 370            | 2020                              | 0.0                         | 500            | 15549                             | 3.4                         | 630            | 106119                            | 19.2                        | 760            | 6582                              | 0.0                         | 890            | 2632                              | 0.0                         |
| 375            | 2137                              | 0.0                         | 505            | 22477                             | 6.3                         | 635            | 99706                             | 15.0                        | 765            | 5777                              | 0.0                         | 895            | 2709                              | 0.0                         |
| 380            | 2046                              | 0.0                         | 510            | 30417                             | 10.4                        | 640            | 92142                             | 11.0                        | 770            | 5474                              | 0.0                         | 900            | 2016                              | 0.0                         |
| 385            | 1925                              | 0.0                         | 515            | 39274                             | 16.3                        | 645            | 84987                             | 8.2                         | 775            | 4977                              | 0.0                         | 905            | 1748                              | 0.0                         |
| 390            | 1893                              | 0.0                         | 520            | 47282                             | 22.9                        | 650            | 78016                             | 5.7                         | 780            | 4723                              | 0.0                         | 910            | 2046                              | 0.0                         |
| 395            | 1695                              | 0.0                         | 525            | 55413                             | 29.7                        | 655            | 71541                             | 4.1                         | 785            | 4219                              | 0.0                         | 915            | 1844                              | 0.0                         |
| 400            | 1633                              | 0.0                         | 530            | 62377                             | 36.7                        | 660            | 64863                             | 2.7                         | 790            | 3969                              | 0.0                         | 920            | 2734                              | 0.0                         |
| 405            | 2065                              | 0.0                         | 535            | 68520                             | 42.5                        | 665            | 58485                             | 1.9                         | 795            | 4122                              | 0.0                         | 925            | 2307                              | 0.0                         |
| 410            | 3449                              | 0.0                         | 540            | 73435                             | 47.8                        | 670            | 51641                             | 1.1                         | 800            | 2864                              | 0.0                         | 930            | 2039                              | 0.0                         |
| 415            | 7117                              | 0.0                         | 545            | 78677                             | 52.4                        | 675            | 46030                             | 0.8                         | 805            | 3151                              | 0.0                         | 935            | 1784                              | 0.0                         |
| 420            | 13992                             | 0.0                         | 550            | 83331                             | 56.6                        | 680            | 40590                             | 0.5                         | 810            | 3022                              | 0.0                         | 940            | 2464                              | 0.0                         |
| 425            | 25176                             | 0.1                         | 555            | 89120                             | 60.9                        | 685            | 35691                             | 0.3                         | 815            | 3471                              | 0.0                         | 945            | 2794                              | 0.0                         |
| 430            | 38151                             | 0.3                         | 560            | 94613                             | 64.3                        | 690            | 31631                             | 0.2                         | 820            | 2749                              | 0.0                         | 950            | 3090                              | 0.0                         |
| 435            | 49673                             | 0.6                         | 565            | 99818                             | 66.4                        | 695            | 27437                             | 0.1                         | 825            | 2729                              | 0.0                         | 955            | 1866                              | 0.0                         |
| 440            | 57273                             | 0.9                         | 570            | 106526                            | 69.3                        | 700            | 24589                             | 0.1                         | 830            | 2282                              | 0.0                         | 960            | 3110                              | 0.0                         |
| 445            | 54802                             | 1.1                         | 575            | 111610                            | 69.4                        | 705            | 21832                             | 0.0                         | 835            | 3140                              | 0.0                         | 965            | 3880                              | 0.0                         |
| 450            | 39184                             | 1.0                         | 580            | 117163                            | 69.6                        | 710            | 19500                             | 0.0                         | 840            | 2365                              | 0.0                         | 970            | 3243                              | 0.0                         |
| 455            | 22506                             | 0.8                         | 585            | 122201                            | 67.9                        | 715            | 17870                             | 0.0                         | 845            | 3024                              | 0.0                         | 975            | 2014                              | 0.0                         |
| 460            | 13692                             | 0.6                         | 590            | 125662                            | 65.0                        | 720            | 15924                             | 0.0                         | 850            | 2510                              | 0.0                         | 980            | 1688                              | 0.0                         |
| 465            | 9446                              | 0.5                         | 595            | 127415                            | 60.4                        | 725            | 14268                             | 0.0                         | 855            | 2739                              | 0.0                         | 985            | 2827                              | 0.0                         |
| 470            | 6698                              | 0.4                         | 600            | 129155                            | 55.7                        | 730            | 12438                             | 0.0                         | 860            | 3515                              | 0.0                         | 990            | 4172                              | 0.0                         |
| 475            | 5328                              | 0.4                         | 605            | 128057                            | 49.6                        | 735            | 11255                             | 0.0                         | 865            | 3600                              | 0.0                         | 995            | 3177                              | 0.0                         |
| 480            | 5081                              | 0.5                         | 610            | 126031                            | 43.3                        | 740            | 9951                              | 0.0                         | 870            | 3609                              | 0.0                         | 1000           | 3241                              | 0.0                         |
| 485            | 5579                              | 0.7                         | 615            | 123059                            | 37.1                        | 745            | 8870                              | 0.0                         | 875            | 3208                              | 0.0                         |                |                                   |                             |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2044          | 0.0           | 490    | 7179          | 6.0           | 620    | 118034        | 0.1           | 750    | 8362          | 0.0           | 880    | 3128          | 0.0           |
| 365    | 2016          | 0.0           | 495    | 10476         | 8.6           | 625    | 111884        | 0.1           | 755    | 7635          | 0.0           | 885    | 3110          | 0.0           |
| 370    | 2020          | 0.0           | 500    | 15549         | 12.5          | 630    | 106119        | 0.0           | 760    | 6582          | 0.0           | 890    | 2632          | 0.0           |
| 375    | 2137          | 0.0           | 505    | 22477         | 17.3          | 635    | 99706         | 0.0           | 765    | 5777          | 0.0           | 895    | 2709          | 0.0           |
| 380    | 2046          | 0.0           | 510    | 30417         | 21.8          | 640    | 92142         | 0.0           | 770    | 5474          | 0.0           | 900    | 2016          | 0.0           |
| 385    | 1925          | 0.0           | 515    | 39274         | 25.7          | 645    | 84987         | 0.0           | 775    | 4977          | 0.0           | 905    | 1748          | 0.0           |
| 390    | 1893          | 0.0           | 520    | 47282         | 27.5          | 650    | 78016         | 0.0           | 780    | 4723          | 0.0           | 910    | 2046          | 0.0           |
| 395    | 1695          | 0.0           | 525    | 55413         | 28.1          | 655    | 71541         | 0.0           | 785    | 4219          | 0.0           | 915    | 1844          | 0.0           |
| 400    | 1633          | 0.0           | 530    | 62377         | 27.0          | 660    | 64863         | 0.0           | 790    | 3969          | 0.0           | 920    | 2734          | 0.0           |
| 405    | 2065          | 0.0           | 535    | 68520         | 24.7          | 665    | 58485         | 0.0           | 795    | 4122          | 0.0           | 925    | 2307          | 0.0           |
| 410    | 3449          | 0.1           | 540    | 73435         | 21.5          | 670    | 51641         | 0.0           | 800    | 2864          | 0.0           | 930    | 2039          | 0.0           |
| 415    | 7117          | 0.5           | 545    | 78677         | 18.3          | 675    | 46030         | 0.0           | 805    | 3151          | 0.0           | 935    | 1784          | 0.0           |
| 420    | 13992         | 1.6           | 550    | 83331         | 15.0          | 680    | 40590         | 0.0           | 810    | 3022          | 0.0           | 940    | 2464          | 0.0           |
| 425    | 25176         | 3.9           | 555    | 89120         | 12.0          | 685    | 35691         | 0.0           | 815    | 3471          | 0.0           | 945    | 2794          | 0.0           |
| 430    | 38151         | 8.1           | 560    | 94613         | 9.3           | 690    | 31631         | 0.0           | 820    | 2749          | 0.0           | 950    | 3090          | 0.0           |
| 435    | 49673         | 13.3          | 565    | 99818         | 7.0           | 695    | 27437         | 0.0           | 825    | 2729          | 0.0           | 955    | 1866          | 0.0           |
| 440    | 57273         | 19.1          | 570    | 106526        | 5.2           | 700    | 24589         | 0.0           | 830    | 2282          | 0.0           | 960    | 3110          | 0.0           |
| 445    | 54802         | 21.6          | 575    | 111610        | 3.7           | 705    | 21832         | 0.0           | 835    | 3140          | 0.0           | 965    | 3880          | 0.0           |
| 450    | 39184         | 18.1          | 580    | 117163        | 2.6           | 710    | 19500         | 0.0           | 840    | 2365          | 0.0           | 970    | 3243          | 0.0           |
| 455    | 22506         | 11.8          | 585    | 122201        | 1.8           | 715    | 17870         | 0.0           | 845    | 3024          | 0.0           | 975    | 2014          | 0.0           |
| 460    | 13692         | 8.1           | 590    | 125662        | 1.2           | 720    | 15924         | 0.0           | 850    | 2510          | 0.0           | 980    | 1688          | 0.0           |
| 465    | 9446          | 6.2           | 595    | 127415        | 0.8           | 725    | 14268         | 0.0           | 855    | 2739          | 0.0           | 985    | 2827          | 0.0           |
| 470    | 6698          | 4.8           | 600    | 129155        | 0.5           | 730    | 12438         | 0.0           | 860    | 3515          | 0.0           | 990    | 4172          | 0.0           |
| 475    | 5328          | 4.1           | 605    | 128057        | 0.4           | 735    | 11255         | 0.0           | 865    | 3600          | 0.0           | 995    | 3177          | 0.0           |
| 480    | 5081          | 4.1           | 610    | 126031        | 0.2           | 740    | 9951          | 0.0           | 870    | 3609          | 0.0           | 1000   | 3241          | 0.0           |
| 485    | 5579          | 4.6           | 615    | 123059        | 0.1           | 745    | 8870          | 0.0           | 875    | 3208          | 0.0           |        |               |               |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2044          | 0.0           | 490    | 7179          | 11.1          | 620    | 118034        | 1.5           | 750    | 8362          | 0.0           | 880    | 3128          | 0.0           |
| 365    | 2016          | 0.0           | 495    | 10476         | 16.9          | 625    | 111884        | 0.9           | 755    | 7635          | 0.0           | 885    | 3110          | 0.0           |
| 370    | 2020          | 0.0           | 500    | 15549         | 26.0          | 630    | 106119        | 0.6           | 760    | 6582          | 0.0           | 890    | 2632          | 0.0           |
| 375    | 2137          | 0.0           | 505    | 22477         | 38.2          | 635    | 99706         | 0.4           | 765    | 5777          | 0.0           | 895    | 2709          | 0.0           |
| 380    | 2046          | 0.0           | 510    | 30417         | 51.6          | 640    | 92142         | 0.2           | 770    | 5474          | 0.0           | 900    | 2016          | 0.0           |
| 385    | 1925          | 0.0           | 515    | 39274         | 65.1          | 645    | 84987         | 0.1           | 775    | 4977          | 0.0           | 905    | 1748          | 0.0           |
| 390    | 1893          | 0.0           | 520    | 47282         | 75.2          | 650    | 78016         | 0.1           | 780    | 4723          | 0.0           | 910    | 2046          | 0.0           |
| 395    | 1695          | 0.0           | 525    | 55413         | 82.9          | 655    | 71541         | 0.1           | 785    | 4219          | 0.0           | 915    | 1844          | 0.0           |
| 400    | 1633          | 0.0           | 530    | 62377         | 86.0          | 660    | 64863         | 0.0           | 790    | 3969          | 0.0           | 920    | 2734          | 0.0           |
| 405    | 2065          | 0.1           | 535    | 68520         | 85.4          | 665    | 58485         | 0.0           | 795    | 4122          | 0.0           | 925    | 2307          | 0.0           |
| 410    | 3449          | 0.2           | 540    | 73435         | 81.1          | 670    | 51641         | 0.0           | 800    | 2864          | 0.0           | 930    | 2039          | 0.0           |
| 415    | 7117          | 0.7           | 545    | 78677         | 75.4          | 675    | 46030         | 0.0           | 805    | 3151          | 0.0           | 935    | 1784          | 0.0           |
| 420    | 13992         | 2.3           | 550    | 83331         | 68.1          | 680    | 40590         | 0.0           | 810    | 3022          | 0.0           | 940    | 2464          | 0.0           |
| 425    | 25176         | 6.2           | 555    | 89120         | 60.9          | 685    | 35691         | 0.0           | 815    | 3471          | 0.0           | 945    | 2794          | 0.0           |
| 430    | 38151         | 13.0          | 560    | 94613         | 52.9          | 690    | 31631         | 0.0           | 820    | 2749          | 0.0           | 950    | 3090          | 0.0           |
| 435    | 49673         | 22.2          | 565    | 99818         | 44.8          | 695    | 27437         | 0.0           | 825    | 2729          | 0.0           | 955    | 1866          | 0.0           |
| 440    | 57273         | 32.0          | 570    | 106526        | 37.6          | 700    | 24589         | 0.0           | 830    | 2282          | 0.0           | 960    | 3110          | 0.0           |
| 445    | 54802         | 36.7          | 575    | 111610        | 30.4          | 705    | 21832         | 0.0           | 835    | 3140          | 0.0           | 965    | 3880          | 0.0           |
| 450    | 39184         | 30.4          | 580    | 117163        | 24.1          | 710    | 19500         | 0.0           | 840    | 2365          | 0.0           | 970    | 3243          | 0.0           |
| 455    | 22506         | 19.7          | 585    | 122201        | 18.7          | 715    | 17870         | 0.0           | 845    | 3024          | 0.0           | 975    | 2014          | 0.0           |
| 460    | 13692         | 13.2          | 590    | 125662        | 14.0          | 720    | 15924         | 0.0           | 850    | 2510          | 0.0           | 980    | 1688          | 0.0           |
| 465    | 9446          | 10.0          | 595    | 127415        | 10.2          | 725    | 14268         | 0.0           | 855    | 2739          | 0.0           | 985    | 2827          | 0.0           |
| 470    | 6698          | 7.7           | 600    | 129155        | 7.3           | 730    | 12438         | 0.0           | 860    | 3515          | 0.0           | 990    | 4172          | 0.0           |
| 475    | 5328          | 6.7           | 605    | 128057        | 5.0           | 735    | 11255         | 0.0           | 865    | 3600          | 0.0           | 995    | 3177          | 0.0           |
| 480    | 5081          | 6.9           | 610    | 126031        | 3.4           | 740    | 9951          | 0.0           | 870    | 3609          | 0.0           | 1000   | 3241          | 0.0           |
| 485    | 5579          | 8.1           | 615    | 123059        | 2.3           | 745    | 8870          | 0.0           | 875    | 3208          | 0.0           |        |               |               |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

**Summary**

$R_f = 69.9$   
 $R_g = 98.3$   
 CIE  $R_a = 71.5$   
 $R_9 = -16.1$



**Color Vector Graphics**





REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 |            |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)