

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P823346

Luminaire Tested: **TTN-D1-830-U-CQ**

Issue Date: 4/16/2024

Test Information

Test Method: LM-79-08
Report Number: P823346
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-254-9)
Test Lab: INNOVATION CENTER
Issue Date: 4/16/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TTN-D1-830-U-CQ
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE
3000K, 80 CRI LEDS AND CONCENTRATED DISTRIBUTION
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3029 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Luminous Opening: Circular (Dia: 0.71' x H: 0')
IES Classification: Type V - Short
BUG Rating: B1 - U0 - G1


Input Watts (W): 26.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P823346
 CATALOG NUMBER: TTN-D1-830-U-CQ

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.2 fc
 Type V - Short - N/A

REPORT NUMBER: P823346
CATALOG NUMBER: TTN-D1-830-U-CQ

Luminous Intensity Polar Plot



REPORT NUMBER: P823346
 CATALOG NUMBER: TTN-D1-830-U-CQ


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1514.5	0.0	1514.5
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	1514.5	0.0	1514.5
	% Fixture	50.0	0.0	50.0
Total	Lumens	3029.0	0.0	3029.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.2	2.4
10°-20°	209.7	6.9
20°-30°	337.7	11.1
30°-40°	454.2	15.0
40°-50°	560.4	18.5
50°-60°	601.2	19.8
60°-70°	487.5	16.1
70°-80°	258.4	8.5
80°-90°	47.8	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3029.0	100.0
0°-180°	3029.0	100.0

Coefficient of Utilization




REPORT NUMBER: P823346
 CATALOG NUMBER: TTN-D1-830-U-CQ

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	309.8	10.2			
FM (30°-60°)	807.9	26.7			
FH (60°-80°)	373.0	12.3			G0/660
FVH (80°-90°)	23.9	0.8			G1/100
BL (0°-30°)	309.8	10.2	B1/500		
BM (30°-60°)	807.9	26.7	B1/1000		
BH (60°-80°)	373.0	12.3	B1/500		G0/660
BVH (80°-90°)	23.9	0.8			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1
 Type V Short





REPORT NUMBER: P823346
 CATALOG NUMBER: TTN-D1-830-U-CQ

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	765.9	765.9	765.9	765.9	765.9	765.9	765.9	765.9	765.9	765.9	765.9
2.5°	761.0	761.0	761.0	761.0	761.0	761.0	761.0	761.0	761.0	761.0	763.4
5°	761.0	761.0	761.0	761.0	758.5	761.0	761.0	761.0	761.0	761.0	761.0
7.5°	756.0	756.0	756.0	756.0	756.0	756.0	756.0	756.0	756.0	756.0	756.0
10°	748.6	748.6	748.6	748.6	748.6	748.6	748.6	748.6	748.6	748.6	748.6
12.5°	743.6	743.6	743.6	743.6	743.6	743.6	743.6	743.6	743.6	743.6	743.6
15°	741.1	741.1	741.1	741.1	741.1	741.1	741.1	741.1	741.1	738.7	738.7
17.5°	736.2	736.2	736.2	736.2	738.7	738.7	738.7	736.2	736.2	736.2	736.2
20°	731.2	731.2	731.2	733.7	733.7	733.7	733.7	733.7	731.2	731.2	731.2
22.5°	728.7	728.7	728.7	728.7	731.2	731.2	731.2	731.2	728.7	728.7	728.7
25°	726.3	726.3	728.7	728.7	731.2	731.2	731.2	728.7	728.7	726.3	726.3
27.5°	726.3	726.3	728.7	728.7	731.2	731.2	731.2	731.2	728.7	726.3	726.3
30°	723.8	726.3	726.3	728.7	731.2	731.2	731.2	728.7	726.3	723.8	723.8
32.5°	721.3	721.3	723.8	726.3	728.7	728.7	728.7	726.3	723.8	721.3	718.8
35°	718.8	718.8	718.8	723.8	726.3	726.3	726.3	723.8	718.8	716.4	716.4
37.5°	713.9	716.4	718.8	721.3	726.3	726.3	726.3	721.3	716.4	713.9	711.4
40°	713.9	713.9	718.8	721.3	728.7	728.7	726.3	721.3	716.4	711.4	708.9
42.5°	711.4	713.9	718.8	726.3	733.7	733.7	731.2	723.8	716.4	711.4	708.9
45°	711.4	711.4	718.8	728.7	738.7	741.1	736.2	728.7	718.8	708.9	708.9
47.5°	706.4	706.4	716.4	728.7	741.1	743.6	741.1	728.7	716.4	708.9	706.4
50°	694.0	694.0	706.4	721.3	736.2	741.1	736.2	726.3	708.9	699.0	696.5
52.5°	674.2	674.2	686.6	706.4	721.3	728.7	723.8	711.4	694.0	679.2	676.7
55°	644.5	646.9	659.3	681.6	699.0	706.4	701.5	686.6	666.8	651.9	646.9
57.5°	609.8	609.8	627.1	649.4	666.8	674.2	669.3	654.4	632.1	617.2	612.2
60°	562.7	565.1	580.0	609.8	627.1	634.6	629.6	612.2	587.5	570.1	565.1
62.5°	515.6	518.1	532.9	557.7	577.5	582.5	577.5	560.2	537.9	520.5	515.6
65°	461.0	463.5	480.9	503.2	518.1	525.5	518.1	503.2	483.4	466.0	463.5
67.5°	404.0	406.5	423.9	443.7	458.6	463.5	456.1	443.7	423.9	409.0	404.0
70°	344.5	347.0	361.9	379.2	391.6	396.6	391.6	376.8	361.9	347.0	344.5
72.5°	282.6	285.1	299.9	314.8	324.7	329.7	322.2	312.3	297.4	285.1	282.6
75°	223.1	223.1	235.5	247.9	257.8	260.3	255.3	247.9	235.5	225.6	220.6
77.5°	166.1	166.1	178.5	185.9	190.9	195.8	190.9	183.4	176.0	166.1	166.1
80°	111.5	111.5	121.5	126.4	131.4	133.9	131.4	126.4	121.5	114.0	111.5
82.5°	66.9	66.9	71.9	76.8	76.8	79.3	79.3	76.8	71.9	66.9	66.9
85°	29.7	27.3	32.2	34.7	34.7	37.2	37.2	34.7	32.2	29.7	29.7
87.5°	2.5	5.0	5.0	7.4	7.4	7.4	7.4	7.4	5.0	5.0	5.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)