

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P628704

Luminaire Tested: GWS-SA1A-727-U-T2R-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P628704
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1A-727-U-T2R-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II ROADWAY OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (16) 2700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1594.2 lumens
Efficiency: N/A
Efficacy: 80.9 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B0 - U0 - G0


Input Watts (W): 19.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P628704
 CATALOG NUMBER: GWS-SA1A-727-U-T2R-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 5.8 fc
 Type II - Short - N/A

REPORT NUMBER: P628704
CATALOG NUMBER: GWS-SA1A-727-U-T2R-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 58-Deg Lateral - - - Horizontal Cone Through 50-Deg Vertical

REPORT NUMBER: P628704

CATALOG NUMBER: GWS-SA1A-727-U-T2R-W-GRSBK


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 223.3 | 0.0 | 223.3 |
| | % Fixture | 14.0 | 0.0 | 14.0 |
| Street Side | Lumens | 1370.9 | 0.0 | 1370.9 |
| | % Fixture | 86.0 | 0.0 | 86.0 |
| Total | Lumens | 1594.2 | 0.0 | 1594.2 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 23.6 | 1.5 |
| 10°-20° | 93.4 | 5.9 |
| 20°-30° | 189.0 | 11.9 |
| 30°-40° | 334.3 | 21.0 |
| 40°-50° | 487.4 | 30.6 |
| 50°-60° | 390.6 | 24.5 |
| 60°-70° | 70.4 | 4.4 |
| 70°-80° | 5.6 | 0.3 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 1594.2 | 100.0 |
| 0°-180° | 1594.2 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P628704

CATALOG NUMBER: GWS-SA1A-727-U-T2R-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 237.2 | 14.9 | | | |
| FM (30°-60°) | 1073.7 | 67.3 | | | |
| FH (60°-80°) | 60.1 | 3.8 | | | G0/660 |
| FVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| BL (0°-30°) | 68.7 | 4.3 | B0/110 | | |
| BM (30°-60°) | 138.7 | 8.7 | B0/220 | | |
| BH (60°-80°) | 15.9 | 1.0 | B0/110 | | G0/110 |
| BVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B0-U0-G0
 Type II Short





REPORT NUMBER: P628704

CATALOG NUMBER: GWS-SA1A-727-U-T2R-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 58° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|-------|
| 0° | 190.4 | 190.4 | 190.4 | 190.4 | 190.4 | 190.4 | 190.4 | 190.4 | 190.4 | 190.4 | 190.4 |
| 2.5° | 281.8 | 277.4 | 274.8 | 272.8 | 263.7 | 249.4 | 240.0 | 235.1 | 226.9 | 213.1 | 201.2 |
| 5° | 367.7 | 364.5 | 358.5 | 354.4 | 342.8 | 322.5 | 301.6 | 293.2 | 274.6 | 243.4 | 215.5 |
| 7.5° | 424.7 | 422.3 | 420.1 | 414.6 | 403.7 | 385.3 | 362.1 | 353.4 | 324.8 | 280.4 | 234.6 |
| 10° | 468.5 | 466.6 | 464.0 | 463.9 | 455.3 | 438.8 | 416.1 | 407.1 | 376.1 | 320.7 | 257.1 |
| 12.5° | 507.0 | 505.5 | 505.0 | 509.7 | 504.3 | 492.0 | 467.5 | 456.2 | 423.3 | 361.8 | 282.0 |
| 15° | 533.4 | 533.1 | 535.3 | 544.7 | 547.7 | 542.1 | 521.5 | 509.4 | 471.5 | 403.0 | 309.4 |
| 17.5° | 545.5 | 546.6 | 550.8 | 567.0 | 580.6 | 585.4 | 569.6 | 559.3 | 519.4 | 444.8 | 338.7 |
| 20° | 566.2 | 565.8 | 568.4 | 583.7 | 600.4 | 617.5 | 612.7 | 604.0 | 567.9 | 488.9 | 371.3 |
| 22.5° | 624.3 | 619.3 | 613.9 | 616.3 | 622.2 | 642.2 | 651.1 | 646.6 | 617.8 | 534.3 | 404.9 |
| 25° | 713.6 | 708.5 | 690.9 | 673.9 | 662.6 | 671.7 | 683.8 | 686.0 | 667.4 | 580.8 | 440.0 |
| 27.5° | 808.4 | 803.8 | 784.0 | 758.5 | 726.2 | 710.6 | 719.6 | 724.0 | 716.2 | 636.2 | 477.3 |
| 30° | 897.2 | 891.1 | 869.4 | 837.7 | 800.4 | 776.4 | 766.1 | 769.2 | 773.8 | 701.9 | 521.2 |
| 32.5° | 974.3 | 969.7 | 943.8 | 910.4 | 874.4 | 849.3 | 825.5 | 830.6 | 841.8 | 782.2 | 577.2 |
| 35° | 1039.6 | 1037.2 | 1009.7 | 976.5 | 938.5 | 925.7 | 905.2 | 906.3 | 917.5 | 879.2 | 645.6 |
| 37.5° | 1096.3 | 1092.3 | 1067.4 | 1036.5 | 1006.3 | 1004.3 | 998.7 | 999.2 | 1005.0 | 992.2 | 724.2 |
| 40° | 1132.1 | 1128.4 | 1110.7 | 1091.6 | 1070.1 | 1070.4 | 1099.6 | 1101.8 | 1095.2 | 1103.2 | 807.2 |
| 42.5° | 1145.6 | 1142.9 | 1133.3 | 1133.5 | 1131.3 | 1141.4 | 1196.1 | 1200.2 | 1176.3 | 1190.3 | 878.1 |
| 45° | 1122.3 | 1121.1 | 1121.7 | 1146.3 | 1172.9 | 1203.9 | 1275.0 | 1282.2 | 1248.4 | 1248.1 | 933.5 |
| 47.5° | 1046.9 | 1044.5 | 1064.5 | 1106.2 | 1167.8 | 1228.1 | 1322.7 | 1333.8 | 1298.9 | 1281.1 | 968.3 |
| 50° | 899.3 | 906.1 | 937.6 | 1000.4 | 1094.0 | 1194.9 | 1322.2 | 1341.5 | 1300.8 | 1278.2 | 962.5 |
| 52.5° | 651.4 | 650.0 | 719.1 | 805.3 | 919.2 | 1088.5 | 1252.0 | 1280.1 | 1255.2 | 1249.8 | 949.6 |
| 55° | 354.4 | 366.9 | 413.4 | 527.6 | 669.8 | 887.2 | 1091.6 | 1152.9 | 1181.8 | 1239.4 | 972.9 |
| 57.5° | 130.2 | 135.7 | 164.9 | 245.7 | 354.6 | 551.7 | 833.8 | 926.4 | 1015.4 | 1210.4 | 969.0 |
| 60° | 52.5 | 53.5 | 65.1 | 90.4 | 149.0 | 280.8 | 500.2 | 582.4 | 666.2 | 926.6 | 743.6 |
| 62.5° | 38.2 | 39.6 | 44.2 | 52.8 | 75.4 | 122.7 | 215.7 | 250.8 | 274.1 | 458.9 | 366.4 |
| 65° | 30.9 | 31.9 | 35.6 | 39.6 | 49.8 | 66.0 | 69.6 | 67.0 | 66.7 | 118.7 | 84.0 |
| 67.5° | 25.6 | 26.6 | 29.3 | 32.0 | 35.8 | 32.9 | 23.9 | 25.1 | 20.5 | 20.3 | 16.5 |
| 70° | 18.8 | 19.9 | 22.7 | 25.6 | 21.5 | 8.9 | 13.8 | 20.5 | 15.5 | 13.0 | 12.6 |
| 72.5° | 14.1 | 15.0 | 17.6 | 16.7 | 6.3 | 3.4 | 9.2 | 14.8 | 11.9 | 9.5 | 9.4 |
| 75° | 10.6 | 11.1 | 8.9 | 2.7 | 0.7 | 0.9 | 3.4 | 6.1 | 6.6 | 5.5 | 5.5 |
| 77.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.3 | 0.5 | 0.7 | 0.9 | 1.0 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P628704

CATALOG NUMBER: GWS-SA1A-727-U-T2R-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 190.4 | 190.4 | 190.4 | 190.4 | 190.4 | 190.4 | 190.4 | 190.4 | 190.4 | 190.4 | 190.4 |
| 2.5° | 194.3 | 187.2 | 177.0 | 168.4 | 162.0 | 155.6 | 150.9 | 146.1 | 145.9 | 143.5 | 143.0 |
| 5° | 202.5 | 189.6 | 170.8 | 157.4 | 149.2 | 144.2 | 140.8 | 139.1 | 138.3 | 137.4 | 137.1 |
| 7.5° | 214.3 | 195.7 | 169.8 | 155.5 | 148.7 | 145.4 | 143.0 | 142.0 | 141.5 | 140.8 | 140.6 |
| 10° | 228.8 | 204.6 | 173.5 | 159.1 | 153.1 | 150.0 | 147.5 | 145.9 | 145.1 | 143.9 | 143.5 |
| 12.5° | 246.2 | 215.5 | 179.5 | 165.0 | 158.7 | 154.6 | 151.2 | 149.0 | 147.8 | 146.3 | 145.9 |
| 15° | 264.9 | 227.2 | 186.2 | 170.5 | 163.0 | 157.7 | 153.4 | 150.0 | 147.8 | 145.9 | 145.4 |
| 17.5° | 284.4 | 239.2 | 192.1 | 174.2 | 165.0 | 158.7 | 152.6 | 148.0 | 145.2 | 142.9 | 142.2 |
| 20° | 306.2 | 251.5 | 196.1 | 174.9 | 164.3 | 156.0 | 148.8 | 143.0 | 140.3 | 137.1 | 136.4 |
| 22.5° | 329.0 | 262.9 | 197.8 | 173.4 | 160.6 | 150.9 | 143.2 | 137.2 | 133.3 | 129.9 | 128.9 |
| 25° | 351.2 | 273.1 | 196.9 | 169.1 | 155.0 | 143.7 | 135.9 | 129.7 | 125.5 | 122.1 | 121.2 |
| 27.5° | 374.7 | 281.6 | 193.8 | 162.8 | 147.3 | 135.9 | 128.4 | 123.1 | 119.2 | 115.4 | 114.6 |
| 30° | 401.1 | 289.5 | 188.9 | 155.1 | 138.3 | 127.9 | 122.1 | 118.5 | 114.2 | 110.3 | 109.1 |
| 32.5° | 433.0 | 296.5 | 181.7 | 145.9 | 130.2 | 120.9 | 117.6 | 114.9 | 110.0 | 105.9 | 105.0 |
| 35° | 469.5 | 302.3 | 172.7 | 136.4 | 122.4 | 116.4 | 115.8 | 112.2 | 105.7 | 100.9 | 99.9 |
| 37.5° | 511.8 | 307.9 | 162.0 | 127.0 | 116.6 | 114.4 | 114.6 | 108.4 | 100.6 | 94.8 | 94.1 |
| 40° | 557.3 | 313.5 | 150.0 | 118.8 | 111.3 | 113.2 | 111.7 | 103.0 | 90.2 | 84.6 | 83.9 |
| 42.5° | 604.7 | 319.6 | 137.9 | 111.2 | 106.9 | 108.6 | 106.4 | 92.1 | 82.9 | 80.0 | 79.6 |
| 45° | 647.5 | 327.0 | 124.8 | 103.5 | 102.5 | 101.9 | 98.2 | 83.4 | 79.4 | 77.4 | 77.2 |
| 47.5° | 678.3 | 325.8 | 110.8 | 96.1 | 97.7 | 96.0 | 84.6 | 79.3 | 76.0 | 73.3 | 72.6 |
| 50° | 672.7 | 305.0 | 96.3 | 88.0 | 91.5 | 90.0 | 76.0 | 74.5 | 71.6 | 68.7 | 67.7 |
| 52.5° | 658.4 | 276.7 | 83.7 | 79.3 | 84.9 | 81.3 | 70.2 | 68.7 | 66.1 | 62.4 | 61.2 |
| 55° | 666.1 | 250.1 | 73.8 | 72.3 | 78.1 | 67.3 | 63.8 | 61.4 | 58.6 | 54.6 | 54.0 |
| 57.5° | 641.3 | 204.1 | 59.3 | 60.3 | 69.0 | 57.5 | 55.9 | 52.2 | 47.6 | 44.8 | 44.5 |
| 60° | 443.9 | 109.6 | 37.2 | 38.4 | 50.0 | 48.2 | 50.1 | 46.7 | 41.1 | 38.5 | 38.0 |
| 62.5° | 203.9 | 44.0 | 20.3 | 19.4 | 26.3 | 32.7 | 43.0 | 42.6 | 35.6 | 31.5 | 31.2 |
| 65° | 49.4 | 20.1 | 14.5 | 13.6 | 14.8 | 19.6 | 28.0 | 33.6 | 28.8 | 24.0 | 23.5 |
| 67.5° | 16.0 | 16.4 | 13.3 | 12.4 | 13.1 | 14.7 | 16.7 | 18.6 | 18.4 | 16.9 | 16.5 |
| 70° | 12.8 | 14.8 | 12.3 | 11.3 | 11.3 | 11.8 | 11.3 | 9.0 | 7.8 | 8.5 | 8.9 |
| 72.5° | 9.5 | 11.3 | 9.7 | 8.7 | 8.4 | 8.2 | 7.0 | 5.1 | 3.6 | 3.2 | 3.1 |
| 75° | 5.6 | 6.3 | 6.0 | 5.1 | 4.8 | 4.3 | 3.4 | 2.2 | 1.2 | 0.9 | 0.5 |
| 77.5° | 1.0 | 1.2 | 1.4 | 1.0 | 0.9 | 0.7 | 0.5 | 0.2 | 0.0 | 0.0 | 0.0 |
| 80° | 0.0 | 0.2 | 0.2 | 0.2 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: MCGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: MCGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 CIE $R_a = 71.5$
 $R_9 = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)