

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P639067

Luminaire Tested: GWS-SA5B-727-U-AFL-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P639067
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-46)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA5B-727-U-AFL-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (5) LIGHTSQUARES WITH 16 LEDS EACH AND AUTOMOTIVE FRONTLINE OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (80) 2700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11183.6 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B2 - U0 - G0


Input Watts (W): 115.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P639067
 CATALOG NUMBER: GWS-SA5B-727-U-AFL-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 10.9 fc
 Type II - Short - N/A

REPORT NUMBER: P639067
CATALOG NUMBER: GWS-SA5B-727-U-AFL-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 50-Deg Lateral - - - Horizontal Cone Through 50-Deg Vertical

REPORT NUMBER: P639067
 CATALOG NUMBER: GWS-SA5B-727-U-AFL-W-GRSBK


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 1436.9 | 0.0 | 1436.9 |
| | % Fixture | 12.8 | 0.0 | 12.8 |
| Street Side | Lumens | 9746.7 | 0.0 | 9746.7 |
| | % Fixture | 87.2 | 0.0 | 87.2 |
| Total | Lumens | 11183.6 | 0.0 | 11183.6 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 314.3 | 2.8 |
| 10°-20° | 810.9 | 7.3 |
| 20°-30° | 1338.3 | 12.0 |
| 30°-40° | 2208.5 | 19.7 |
| 40°-50° | 3494.4 | 31.2 |
| 50°-60° | 2645.7 | 23.7 |
| 60°-70° | 331.1 | 3.0 |
| 70°-80° | 37.5 | 0.3 |
| 80°-90° | 2.9 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 11183.6 | 100.0 |
| 0°-180° | 11183.6 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P639067

CATALOG NUMBER: GWS-SA5B-727-U-AFL-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 1818.6 | 16.3 | | | |
| FM (30°-60°) | 7634.0 | 68.3 | | | |
| FH (60°-80°) | 292.8 | 2.6 | | | G0/660 |
| FVH (80°-90°) | 1.3 | 0.0 | | | G0/10 |
| BL (0°-30°) | 645.0 | 5.8 | B2/1000 | | |
| BM (30°-60°) | 714.6 | 6.4 | B1/1000 | | |
| BH (60°-80°) | 75.8 | 0.7 | B0/110 | | G0/110 |
| BVH (80°-90°) | 1.5 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G0
 Type II Short





REPORT NUMBER: P639067
 CATALOG NUMBER: GWS-SA5B-727-U-AFL-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 50° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|---------|---------|---------|--------|--------|--------|
| 0° | 3388.2 | 3388.2 | 3388.2 | 3388.2 | 3388.2 | 3388.2 | 3388.2 | 3388.2 | 3388.2 | 3388.2 | 3388.2 |
| 2.5° | 3860.8 | 3891.7 | 3883.2 | 3842.7 | 3799.1 | 3768.2 | 3720.3 | 3705.4 | 3596.8 | 3521.2 | 3441.4 |
| 5° | 4327.0 | 4336.6 | 4326.0 | 4277.0 | 4200.4 | 4126.9 | 4048.2 | 4002.4 | 3820.4 | 3656.4 | 3489.3 |
| 7.5° | 4438.8 | 4427.1 | 4447.3 | 4471.8 | 4461.2 | 4429.2 | 4346.2 | 4296.2 | 4079.0 | 3811.8 | 3558.5 |
| 10° | 4089.7 | 4063.1 | 4138.6 | 4265.3 | 4398.4 | 4548.5 | 4527.2 | 4531.4 | 4331.3 | 4007.7 | 3649.0 |
| 12.5° | 3626.6 | 3616.0 | 3672.4 | 3819.3 | 4080.1 | 4420.7 | 4502.7 | 4640.0 | 4562.3 | 4219.5 | 3752.2 |
| 15° | 3423.3 | 3428.6 | 3462.7 | 3555.3 | 3742.7 | 4166.3 | 4363.2 | 4611.3 | 4768.8 | 4425.0 | 3866.1 |
| 17.5° | 3454.2 | 3473.3 | 3472.3 | 3503.1 | 3617.0 | 3956.6 | 4186.5 | 4520.8 | 4928.5 | 4661.3 | 3997.1 |
| 20° | 3663.9 | 3683.0 | 3654.3 | 3630.9 | 3669.2 | 3903.4 | 4093.9 | 4429.2 | 5036.0 | 4899.7 | 4135.4 |
| 22.5° | 3977.9 | 4000.3 | 3932.1 | 3865.1 | 3840.6 | 3990.7 | 4129.1 | 4392.0 | 5117.9 | 5117.9 | 4258.9 |
| 25° | 4357.9 | 4388.8 | 4283.4 | 4164.2 | 4096.1 | 4174.8 | 4279.1 | 4476.1 | 5202.0 | 5313.8 | 4343.0 |
| 27.5° | 4782.6 | 4783.7 | 4693.2 | 4559.1 | 4431.4 | 4440.9 | 4503.7 | 4665.5 | 5294.6 | 5524.6 | 4409.0 |
| 30° | 5260.6 | 5263.8 | 5143.5 | 4982.8 | 4822.0 | 4778.4 | 4831.6 | 4954.0 | 5487.3 | 5789.6 | 4500.6 |
| 32.5° | 5878.0 | 5892.9 | 5720.4 | 5484.1 | 5275.5 | 5193.5 | 5224.4 | 5353.2 | 5793.9 | 6121.7 | 4637.9 |
| 35° | 6712.5 | 6728.5 | 6474.1 | 6162.2 | 5830.1 | 5706.6 | 5737.5 | 5867.3 | 6237.8 | 6593.3 | 4857.1 |
| 37.5° | 7536.4 | 7557.7 | 7300.1 | 7009.5 | 6553.9 | 6349.5 | 6381.5 | 6504.9 | 6904.1 | 7244.7 | 5208.4 |
| 40° | 8105.9 | 8134.6 | 8054.8 | 7858.9 | 7436.3 | 7168.1 | 7206.4 | 7251.1 | 7637.5 | 8023.9 | 5664.0 |
| 42.5° | 8406.1 | 8446.5 | 8480.6 | 8580.6 | 8358.2 | 8133.6 | 8068.6 | 8071.8 | 8383.7 | 8818.0 | 6137.7 |
| 45° | 8424.2 | 8463.5 | 8638.1 | 9024.5 | 9193.8 | 9146.9 | 9028.8 | 8948.9 | 8953.2 | 9347.1 | 6433.6 |
| 47.5° | 7838.7 | 7912.2 | 8238.9 | 8995.8 | 9632.3 | 10020.9 | 9961.2 | 9771.8 | 9192.7 | 9382.2 | 6401.7 |
| 50° | 6451.7 | 6524.1 | 7118.1 | 8207.0 | 9313.0 | 10370.0 | 10615.9 | 10361.5 | 9036.2 | 8944.7 | 6072.8 |
| 52.5° | 4685.8 | 4693.2 | 5078.6 | 6350.6 | 8018.6 | 9726.0 | 10305.1 | 10280.6 | 8797.8 | 8414.6 | 5623.6 |
| 55° | 2225.8 | 2199.2 | 2632.4 | 3584.0 | 5545.9 | 7866.4 | 8842.5 | 9119.3 | 8459.3 | 8031.4 | 5275.5 |
| 57.5° | 648.3 | 661.0 | 853.7 | 1398.7 | 2774.0 | 5027.5 | 6055.7 | 6570.9 | 6943.5 | 6602.9 | 4091.8 |
| 60° | 290.6 | 291.7 | 324.7 | 425.8 | 924.0 | 2338.6 | 3130.6 | 3768.2 | 4151.4 | 3847.0 | 2029.9 |
| 62.5° | 210.8 | 211.8 | 224.6 | 240.6 | 314.0 | 792.0 | 1174.1 | 1564.8 | 1593.5 | 1043.2 | 514.1 |
| 65° | 175.6 | 175.6 | 177.8 | 177.8 | 188.4 | 283.1 | 356.6 | 459.8 | 387.5 | 287.4 | 201.2 |
| 67.5° | 141.6 | 142.6 | 144.8 | 144.8 | 141.6 | 141.6 | 153.3 | 168.2 | 179.9 | 222.5 | 185.2 |
| 70° | 110.7 | 109.6 | 109.6 | 110.7 | 107.5 | 91.5 | 99.0 | 112.8 | 123.5 | 173.5 | 160.7 |
| 72.5° | 86.2 | 87.3 | 86.2 | 82.0 | 74.5 | 54.3 | 58.5 | 73.4 | 78.8 | 108.6 | 108.6 |
| 75° | 64.9 | 66.0 | 61.7 | 46.8 | 30.9 | 17.0 | 22.4 | 36.2 | 45.8 | 53.2 | 39.4 |
| 77.5° | 8.5 | 8.5 | 6.4 | 6.4 | 5.3 | 6.4 | 6.4 | 8.5 | 12.8 | 12.8 | 9.6 |
| 80° | 1.1 | 1.1 | 1.1 | 2.1 | 3.2 | 4.3 | 4.3 | 4.3 | 4.3 | 5.3 | 5.3 |
| 82.5° | 1.1 | 1.1 | 1.1 | 1.1 | 3.2 | 3.2 | 4.3 | 4.3 | 4.3 | 4.3 | 4.3 |
| 85° | 0.0 | 0.0 | 0.0 | 1.1 | 2.1 | 3.2 | 3.2 | 4.3 | 4.3 | 4.3 | 4.3 |
| 87.5° | 0.0 | 0.0 | 0.0 | 1.1 | 2.1 | 3.2 | 3.2 | 3.2 | 4.3 | 4.3 | 4.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P639067

CATALOG NUMBER: GWS-SA5B-727-U-AFL-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3388.2 | 3388.2 | 3388.2 | 3388.2 | 3388.2 | 3388.2 | 3388.2 | 3388.2 | 3388.2 | 3388.2 | 3388.2 |
| 2.5° | 3393.5 | 3331.8 | 3257.3 | 3206.2 | 3133.8 | 3085.9 | 3017.8 | 2972.0 | 2932.6 | 2901.7 | 2918.8 |
| 5° | 3394.6 | 3296.6 | 3144.4 | 3014.6 | 2873.0 | 2743.1 | 2603.7 | 2494.0 | 2395.0 | 2350.3 | 2374.8 |
| 7.5° | 3415.9 | 3275.4 | 3042.2 | 2811.2 | 2539.8 | 2271.6 | 2020.4 | 1816.0 | 1714.9 | 1666.9 | 1681.9 |
| 10° | 3457.4 | 3265.8 | 2928.3 | 2545.1 | 2104.4 | 1738.3 | 1494.5 | 1356.1 | 1299.7 | 1269.9 | 1275.2 |
| 12.5° | 3495.7 | 3259.4 | 2780.4 | 2194.9 | 1660.6 | 1348.7 | 1222.0 | 1202.8 | 1214.6 | 1215.6 | 1214.6 |
| 15° | 3547.9 | 3247.7 | 2597.3 | 1835.1 | 1328.5 | 1165.6 | 1168.8 | 1196.5 | 1224.1 | 1232.6 | 1230.5 |
| 17.5° | 3603.2 | 3229.6 | 2361.0 | 1490.2 | 1127.3 | 1112.4 | 1149.6 | 1186.9 | 1214.6 | 1218.8 | 1219.9 |
| 20° | 3660.7 | 3192.3 | 2091.7 | 1216.7 | 1033.6 | 1071.9 | 1113.4 | 1141.1 | 1161.3 | 1167.7 | 1169.8 |
| 22.5° | 3687.3 | 3113.6 | 1780.8 | 1020.8 | 970.8 | 1021.9 | 1052.8 | 1088.9 | 1095.3 | 1071.9 | 1076.2 |
| 25° | 3673.5 | 2980.5 | 1477.5 | 888.8 | 908.0 | 959.1 | 1004.9 | 986.8 | 960.1 | 943.1 | 948.4 |
| 27.5° | 3629.8 | 2803.8 | 1180.5 | 792.0 | 840.9 | 905.9 | 911.2 | 891.0 | 886.7 | 872.9 | 877.1 |
| 30° | 3583.0 | 2600.5 | 949.5 | 714.3 | 772.8 | 840.9 | 825.0 | 832.4 | 833.5 | 817.5 | 822.8 |
| 32.5° | 3554.2 | 2387.6 | 755.8 | 662.1 | 729.2 | 741.9 | 773.9 | 788.8 | 789.8 | 752.6 | 759.0 |
| 35° | 3563.8 | 2177.9 | 639.7 | 619.5 | 688.7 | 685.5 | 730.2 | 738.7 | 677.0 | 625.9 | 631.2 |
| 37.5° | 3641.5 | 1984.2 | 573.7 | 586.5 | 618.5 | 642.9 | 677.0 | 620.6 | 606.7 | 583.3 | 586.5 |
| 40° | 3786.3 | 1819.2 | 534.4 | 566.3 | 570.6 | 609.9 | 557.8 | 565.2 | 566.3 | 551.4 | 554.6 |
| 42.5° | 3955.5 | 1681.9 | 510.9 | 554.6 | 543.9 | 550.3 | 498.2 | 513.1 | 529.0 | 522.7 | 523.7 |
| 45° | 4040.7 | 1547.7 | 490.7 | 514.1 | 517.3 | 456.7 | 444.9 | 460.9 | 481.1 | 484.3 | 485.4 |
| 47.5° | 3965.1 | 1420.0 | 469.4 | 455.6 | 476.9 | 416.2 | 402.4 | 407.7 | 431.1 | 443.9 | 446.0 |
| 50° | 3734.1 | 1273.1 | 437.5 | 403.4 | 391.7 | 373.6 | 360.9 | 361.9 | 388.5 | 410.9 | 415.1 |
| 52.5° | 3409.5 | 1119.8 | 385.3 | 341.7 | 315.1 | 328.9 | 332.1 | 325.7 | 350.2 | 372.6 | 376.8 |
| 55° | 3094.4 | 928.2 | 305.5 | 277.8 | 253.3 | 283.1 | 291.7 | 283.1 | 290.6 | 305.5 | 306.6 |
| 57.5° | 2179.0 | 524.8 | 234.2 | 229.9 | 209.7 | 242.7 | 256.5 | 243.8 | 231.0 | 240.6 | 242.7 |
| 60° | 1010.2 | 274.6 | 179.9 | 179.9 | 174.6 | 208.6 | 232.1 | 214.0 | 189.5 | 193.7 | 196.9 |
| 62.5° | 316.1 | 173.5 | 132.0 | 124.5 | 142.6 | 177.8 | 196.9 | 178.8 | 150.1 | 150.1 | 154.3 |
| 65° | 178.8 | 149.0 | 104.3 | 95.8 | 116.0 | 142.6 | 154.3 | 135.2 | 109.6 | 107.5 | 107.5 |
| 67.5° | 166.1 | 141.6 | 92.6 | 77.7 | 82.0 | 91.5 | 95.8 | 83.0 | 75.6 | 74.5 | 75.6 |
| 70° | 137.3 | 118.2 | 74.5 | 53.2 | 50.0 | 49.0 | 51.1 | 47.9 | 45.8 | 46.8 | 50.0 |
| 72.5° | 85.2 | 71.3 | 46.8 | 31.9 | 27.7 | 26.6 | 26.6 | 26.6 | 25.5 | 25.5 | 25.5 |
| 75° | 30.9 | 26.6 | 21.3 | 16.0 | 13.8 | 12.8 | 12.8 | 13.8 | 12.8 | 11.7 | 10.6 |
| 77.5° | 9.6 | 8.5 | 8.5 | 8.5 | 7.5 | 6.4 | 5.3 | 5.3 | 4.3 | 3.2 | 3.2 |
| 80° | 5.3 | 5.3 | 5.3 | 5.3 | 4.3 | 4.3 | 3.2 | 2.1 | 1.1 | 1.1 | 0.0 |
| 82.5° | 5.3 | 5.3 | 5.3 | 4.3 | 4.3 | 4.3 | 3.2 | 2.1 | 1.1 | 0.0 | 0.0 |
| 85° | 4.3 | 4.3 | 4.3 | 4.3 | 4.3 | 4.3 | 3.2 | 2.1 | 1.1 | 0.0 | 0.0 |
| 87.5° | 4.3 | 4.3 | 4.3 | 4.3 | 4.3 | 4.3 | 3.2 | 2.1 | 1.1 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 $CIE R_a = 71.5$
 $R_g = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)