

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P833315

Luminaire Tested: **TTN-D1-830-U-DL-CG-UPL2**

Issue Date: 5/15/2024

Test Information

Test Method: LM-79-08
Report Number: P833315
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND
Test Lab: INNOVATION CENTER
Issue Date: 5/15/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TTN-D1-830-U-DL-CG-UPL2
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT
3000K, 80 CRI LEDS AND DRIVE LANE DISTRIBUTION WITH CLEAR GLASS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3365.8 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')
IES Classification: Type IV - Short
BUG Rating: B1 - U4 - G1


Input Watts (W): 30.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P833315
 CATALOG NUMBER: TTN-D1-830-U-DL-CG-UPL2

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.7 fc
 Type IV - Short - N/A

REPORT NUMBER: P833315
CATALOG NUMBER: TTN-D1-830-U-DL-CG-UPL2

Luminous Intensity Polar Plot



— Vertical Plane Through 33-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P833315
 CATALOG NUMBER: TTN-D1-830-U-DL-CG-UPL2


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	625.0	267.0	892.1
	% Fixture	18.6	7.9	26.5
Street Side	Lumens	2206.7	267.0	2473.7
	% Fixture	65.6	7.9	73.5
Total	Lumens	2831.7	534.0	3365.8
	% Fixture	84.1	15.9	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.4	0.8
10°-20°	82.3	2.4
20°-30°	173.6	5.2
30°-40°	315.3	9.4
40°-50°	498.2	14.8
50°-60°	661.6	19.7
60°-70°	636.8	18.9
70°-80°	373.8	11.1
80°-90°	64.9	1.9
90°-100°	11.9	0.4
100°-110°	121.1	3.6
110°-120°	177.1	5.3
120°-130°	102.8	3.1
130°-140°	54.4	1.6
140°-150°	32.3	1.0
150°-160°	19.9	0.6
160°-170°	10.9	0.3
170°-180°	3.5	0.1
0°-90°	2831.7	84.1
0°-180°	3365.8	100.0




REPORT NUMBER: P833315
 CATALOG NUMBER: TTN-D1-830-U-DL-CG-UPL2

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	189.4	5.6			
FM (30°-60°)	1145.3	34.0			
FH (60°-80°)	817.4	24.3			G1/1800
FVH (80°-90°)	54.6	1.6			G1/100
BL (0°-30°)	91.9	2.7	B0/110		
BM (30°-60°)	329.6	9.8	B1/1000		
BH (60°-80°)	193.2	5.7	B1/500		G1/500
BVH (80°-90°)	10.3	0.3			G1/100
UL (90°-100°)	11.9	0.4		U2/50	
UH (100°-180°)	522.1	15.5		U4/1000	

BUG Rating: B1-U4-G1

Type IV Short





REPORT NUMBER: P833315

CATALOG NUMBER: TTN-D1-830-U-DL-CG-UPL2

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	33°	35°	45°	55°	65°	75°	85°
0°	265.3	265.3	265.3	265.3	265.3	265.3	265.3	265.3	265.3	265.3	265.3
2.5°	282.7	285.2	282.7	282.7	280.2	280.2	277.7	275.3	272.8	270.3	265.3
5°	314.9	314.9	312.4	307.5	305.0	302.5	297.6	290.1	285.2	277.7	270.3
7.5°	329.8	329.8	327.3	322.4	317.4	314.9	307.5	297.6	290.1	280.2	270.3
10°	349.6	352.1	347.2	342.2	337.2	334.8	324.8	312.4	300.0	287.7	272.8
12.5°	372.0	374.4	372.0	364.5	357.1	354.6	344.7	329.8	314.9	297.6	280.2
15°	401.7	406.7	399.2	394.3	386.8	384.4	372.0	354.6	337.2	314.9	292.6
17.5°	436.4	438.9	434.0	426.5	421.6	419.1	406.7	386.8	362.0	337.2	310.0
20°	476.1	478.6	476.1	466.2	461.2	458.8	446.4	424.0	394.3	367.0	332.3
22.5°	523.2	528.2	520.7	513.3	508.3	508.3	493.5	468.7	434.0	399.2	359.6
25°	577.8	585.2	575.3	570.3	565.4	562.9	550.5	520.7	481.1	438.9	389.3
27.5°	644.7	649.7	642.3	639.8	629.9	629.9	610.0	575.3	533.1	483.6	426.5
30°	704.2	709.2	704.2	704.2	696.8	694.3	674.5	639.8	587.7	528.2	458.8
32.5°	761.3	766.2	763.8	766.2	763.8	761.3	736.5	699.3	647.2	570.3	491.0
35°	818.3	825.8	823.3	830.7	828.2	825.8	805.9	761.3	699.3	622.4	525.7
37.5°	877.8	885.3	885.3	892.7	895.2	895.2	872.9	825.8	756.3	669.5	565.4
40°	942.3	949.7	949.7	962.1	967.1	967.1	942.3	895.2	818.3	721.6	607.5
42.5°	1004.3	1011.7	1014.2	1026.6	1034.1	1036.5	1016.7	962.1	872.9	773.7	647.2
45°	1063.8	1071.3	1078.7	1103.5	1115.9	1113.4	1098.5	1041.5	942.3	828.2	689.4
47.5°	1120.8	1130.8	1143.2	1175.4	1192.8	1190.3	1180.4	1115.9	1006.8	880.3	726.6
50°	1165.5	1172.9	1197.7	1232.4	1254.8	1257.2	1242.4	1180.4	1061.3	920.0	753.8
52.5°	1200.2	1210.1	1239.9	1289.5	1306.8	1314.3	1296.9	1234.9	1115.9	954.7	776.2
55°	1225.0	1225.0	1269.6	1326.7	1351.5	1356.4	1356.4	1279.6	1148.1	977.0	788.6
57.5°	1212.6	1212.6	1262.2	1324.2	1363.9	1361.4	1356.4	1282.0	1153.1	972.1	781.1
60°	1177.9	1185.3	1232.4	1294.4	1334.1	1331.6	1316.7	1249.8	1128.3	952.2	766.2
62.5°	1130.8	1143.2	1192.8	1239.9	1284.5	1291.9	1272.1	1212.6	1086.1	922.5	739.0
65°	1041.5	1058.9	1120.8	1172.9	1207.6	1222.5	1197.7	1143.2	1029.1	865.4	681.9
67.5°	942.3	954.7	1006.8	1081.2	1101.0	1115.9	1103.5	1046.5	949.7	773.7	617.5
70°	828.2	848.1	882.8	957.2	979.5	994.4	994.4	937.3	845.6	679.5	540.6
72.5°	694.3	716.6	758.8	813.4	843.1	853.0	850.6	803.4	721.6	575.3	456.3
75°	548.0	565.4	615.0	654.7	686.9	694.3	691.9	652.2	577.8	463.7	362.0
77.5°	404.2	421.6	458.8	488.5	518.3	513.3	513.3	483.6	436.4	344.7	275.3
80°	265.3	280.2	312.4	322.4	354.6	352.1	352.1	329.8	297.6	230.6	183.5
82.5°	146.3	158.7	181.0	190.9	210.8	205.8	208.3	193.4	173.6	128.9	104.1
85°	52.1	62.0	74.4	81.8	91.8	91.8	91.8	79.4	74.4	49.6	42.2
87.5°	2.5	5.0	9.9	9.9	14.9	14.9	14.9	9.9	9.9	2.5	2.5
90°	4.6	4.6	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	4.6
92.5°	4.6	4.6	4.6	6.4	7.1	7.3	6.4	7.3	5.5	5.5	4.6
95°	5.5	5.5	6.4	8.2	9.7	10.1	11.0	11.0	6.4	6.4	5.5
97.5°	7.3	8.2	8.2	10.1	15.1	16.4	30.2	18.3	9.1	9.1	8.2
100°	11.9	12.8	12.8	22.8	43.3	48.4	64.9	46.6	23.8	17.4	12.8
102.5°	38.4	40.2	49.3	74.0	102.5	109.6	99.6	84.1	79.5	54.8	43.9
105°	97.8	96.8	104.2	123.3	147.5	153.5	150.8	138.9	126.1	108.7	100.5
107.5°	128.8	128.8	135.2	151.7	169.9	174.5	203.7	206.5	163.5	143.4	134.3
110°	145.3	145.3	150.8	164.5	188.6	194.6	235.7	233.9	201.9	177.3	165.4



REPORT NUMBER: P833315
 CATALOG NUMBER: TTN-D1-830-U-DL-CG-UPL2

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	33°	35°	45°	55°	65°	75°	85°
112.5°	148.9	149.8	157.1	178.2	204.5	211.1	229.3	221.1	208.3	197.4	188.2
115°	154.4	154.4	162.6	182.7	197.3	201.0	208.3	199.2	189.1	181.8	178.2
117.5°	152.6	155.3	157.1	168.1	177.6	180.0	185.5	180.9	167.2	161.7	159.9
120°	141.6	141.6	143.4	148.9	154.0	155.3	158.1	156.2	147.1	142.5	141.6
122.5°	126.1	127.0	126.1	128.8	132.5	133.4	136.1	134.3	127.0	125.2	125.2
125°	110.6	110.6	109.6	111.5	113.7	114.2	113.3	114.2	110.6	109.6	109.6
127.5°	99.6	98.7	96.8	97.8	98.5	98.7	98.7	99.6	95.9	96.8	97.8
130°	88.6	88.6	86.8	86.8	86.8	86.8	85.0	86.8	85.0	85.9	86.8
132.5°	78.6	78.6	75.8	74.9	74.9	74.9	74.9	75.8	74.9	76.7	78.6
135°	70.4	70.4	67.6	68.5	68.5	68.5	67.6	68.5	67.6	69.4	70.4
137.5°	64.0	64.0	62.1	62.1	62.1	62.1	61.2	62.1	62.1	63.0	64.9
140°	58.5	58.5	57.6	57.6	56.8	56.6	57.6	57.6	57.6	58.5	59.4
142.5°	55.7	54.8	53.9	53.0	53.7	53.9	53.9	53.9	53.0	53.9	55.7
145°	51.2	51.2	50.3	50.3	50.3	50.3	51.2	50.3	50.3	51.2	51.2
147.5°	48.4	48.4	47.5	48.4	48.4	48.4	48.4	48.4	47.5	48.4	48.4
150°	47.5	46.6	45.7	46.6	46.6	46.6	45.7	45.7	45.7	45.7	46.6
152.5°	44.8	44.8	43.9	44.8	44.1	43.9	43.9	43.9	43.9	43.9	44.8
155°	42.9	42.9	42.0	42.9	42.9	42.9	42.9	42.9	42.9	42.9	42.9
157.5°	41.1	42.0	41.1	41.1	41.1	41.1	41.1	41.1	41.1	41.1	42.0
160°	40.2	40.2	40.2	40.2	39.5	39.3	39.3	39.3	40.2	40.2	40.2
162.5°	39.3	39.3	39.3	39.3	38.6	38.4	38.4	38.4	38.4	39.3	39.3
165°	39.3	38.4	38.4	38.4	37.7	37.5	37.5	37.5	37.5	38.4	39.3
167.5°	37.5	37.5	37.5	37.5	37.5	37.5	36.5	36.5	37.5	37.5	37.5
170°	37.5	37.5	36.5	36.5	36.5	36.5	36.5	36.5	36.5	36.5	36.5
172.5°	37.5	37.5	37.5	37.5	36.7	36.5	36.5	36.5	36.5	36.5	37.5
175°	37.5	37.5	37.5	37.5	36.7	36.5	36.5	36.5	37.5	37.5	37.5
177.5°	37.5	37.5	37.5	37.5	36.7	36.5	37.5	37.5	37.5	37.5	37.5
180°	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5



REPORT NUMBER: P833315

CATALOG NUMBER: TTN-D1-830-U-DL-CG-UPL2

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	265.3	265.3	265.3	265.3	265.3	265.3	265.3	265.3	265.3	265.3	265.3
2.5°	262.9	260.4	257.9	252.9	250.5	248.0	245.5	243.0	243.0	243.0	243.0
5°	265.3	262.9	255.4	248.0	240.5	233.1	228.1	225.7	223.2	220.7	220.7
7.5°	265.3	260.4	250.5	240.5	233.1	223.2	215.7	208.3	203.3	200.9	200.9
10°	267.8	260.4	248.0	238.1	225.7	213.3	203.3	193.4	188.5	183.5	183.5
12.5°	272.8	265.3	248.0	235.6	220.7	205.8	193.4	183.5	176.1	171.1	171.1
15°	282.7	272.8	252.9	235.6	218.2	200.9	188.5	176.1	168.6	163.7	163.7
17.5°	297.6	285.2	260.4	235.6	215.7	198.4	183.5	171.1	161.2	156.2	156.2
20°	314.9	300.0	270.3	240.5	215.7	195.9	181.0	166.1	156.2	151.3	151.3
22.5°	339.7	317.4	282.7	248.0	220.7	198.4	178.5	163.7	153.7	148.8	148.8
25°	367.0	342.2	297.6	257.9	225.7	198.4	178.5	163.7	153.7	148.8	146.3
27.5°	396.8	369.5	314.9	267.8	230.6	203.3	181.0	163.7	153.7	148.8	148.8
30°	424.0	391.8	332.3	280.2	238.1	205.8	183.5	166.1	153.7	148.8	148.8
32.5°	453.8	416.6	349.6	292.6	245.5	210.8	186.0	168.6	156.2	151.3	148.8
35°	483.6	441.4	367.0	302.5	252.9	215.7	188.5	171.1	158.7	153.7	153.7
37.5°	515.8	468.7	384.4	314.9	260.4	220.7	193.4	173.6	161.2	156.2	156.2
40°	550.5	496.0	401.7	324.8	267.8	225.7	198.4	178.5	166.1	161.2	161.2
42.5°	585.2	525.7	421.6	337.2	275.3	230.6	200.9	183.5	171.1	166.1	166.1
45°	619.9	550.5	438.9	349.6	282.7	238.1	208.3	188.5	176.1	171.1	171.1
47.5°	652.2	577.8	453.8	357.1	290.1	243.0	210.8	193.4	181.0	178.5	176.1
50°	674.5	595.1	463.7	364.5	292.6	245.5	215.7	195.9	186.0	181.0	181.0
52.5°	691.9	612.5	471.2	369.5	295.1	248.0	218.2	200.9	190.9	186.0	183.5
55°	701.8	615.0	471.2	364.5	292.6	248.0	218.2	200.9	190.9	186.0	186.0
57.5°	691.9	602.6	461.2	354.6	285.2	240.5	210.8	195.9	186.0	183.5	181.0
60°	672.0	582.7	441.4	339.7	272.8	228.1	200.9	188.5	181.0	178.5	176.1
62.5°	644.7	557.9	421.6	319.9	255.4	213.3	193.4	178.5	173.6	171.1	168.6
65°	590.2	510.8	389.3	295.1	233.1	195.9	176.1	166.1	161.2	156.2	153.7
67.5°	530.7	458.8	344.7	265.3	205.8	176.1	158.7	148.8	141.3	141.3	138.9
70°	466.2	404.2	297.6	225.7	178.5	153.7	136.4	128.9	124.0	124.0	121.5
72.5°	389.3	339.7	248.0	183.5	146.3	126.5	114.1	106.6	104.1	104.1	101.7
75°	312.4	267.8	195.9	143.8	114.1	99.2	89.3	84.3	81.8	81.8	79.4
77.5°	230.6	195.9	141.3	104.1	81.8	71.9	64.5	62.0	59.5	59.5	57.0
80°	153.7	128.9	91.8	67.0	49.6	44.6	39.7	39.7	37.2	39.7	37.2
82.5°	84.3	69.4	49.6	34.7	24.8	22.3	19.8	19.8	22.3	22.3	19.8
85°	32.2	24.8	17.4	9.9	7.4	7.4	7.4	7.4	7.4	7.4	5.0
87.5°	2.5	2.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	4.6	4.6	5.5	5.5	5.5	5.5	5.5	5.5	5.5	4.6	4.6
92.5°	4.6	4.6	5.5	5.5	7.3	6.4	7.3	6.4	4.6	4.6	4.6
95°	5.5	5.5	6.4	6.4	11.0	11.0	10.1	8.2	6.4	5.5	5.5
97.5°	7.3	8.2	9.1	9.1	18.3	30.2	16.4	10.1	8.2	8.2	7.3
100°	12.8	12.8	17.4	23.8	46.6	64.9	48.4	22.8	12.8	12.8	11.9
102.5°	42.0	43.9	54.8	79.5	84.1	99.6	109.6	74.0	49.3	40.2	38.4
105°	100.5	100.5	108.7	126.1	138.9	150.8	153.5	123.3	104.2	96.8	97.8
107.5°	133.4	134.3	143.4	163.5	206.5	203.7	174.5	151.7	135.2	128.8	128.8
110°	163.5	165.4	177.3	201.9	233.9	235.7	194.6	164.5	150.8	145.3	145.3



REPORT NUMBER: P833315
 CATALOG NUMBER: TTN-D1-830-U-DL-CG-UPL2

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	186.4	188.2	197.4	208.3	221.1	229.3	211.1	178.2	157.1	149.8	148.9
115°	180.0	178.2	181.8	189.1	199.2	208.3	201.0	182.7	162.6	154.4	154.4
117.5°	157.1	159.9	161.7	167.2	180.9	185.5	180.0	168.1	157.1	155.3	152.6
120°	139.8	141.6	142.5	147.1	156.2	158.1	155.3	148.9	143.4	141.6	141.6
122.5°	123.3	125.2	125.2	127.0	134.3	136.1	133.4	128.8	126.1	127.0	126.1
125°	108.7	109.6	109.6	110.6	114.2	113.3	114.2	111.5	109.6	110.6	110.6
127.5°	96.8	97.8	96.8	95.9	99.6	98.7	98.7	97.8	96.8	98.7	99.6
130°	87.7	86.8	85.9	85.0	86.8	85.0	86.8	86.8	86.8	88.6	88.6
132.5°	78.6	78.6	76.7	74.9	75.8	74.9	74.9	74.9	75.8	78.6	78.6
135°	70.4	70.4	69.4	67.6	68.5	67.6	68.5	68.5	67.6	70.4	70.4
137.5°	65.8	64.9	63.0	62.1	62.1	61.2	62.1	62.1	62.1	64.0	64.0
140°	59.4	59.4	58.5	57.6	57.6	57.6	56.6	57.6	57.6	58.5	58.5
142.5°	55.7	55.7	53.9	53.0	53.9	53.9	53.9	53.0	53.9	54.8	55.7
145°	52.1	51.2	51.2	50.3	50.3	51.2	50.3	50.3	50.3	51.2	51.2
147.5°	49.3	48.4	48.4	47.5	48.4	48.4	48.4	48.4	47.5	48.4	48.4
150°	46.6	46.6	45.7	45.7	45.7	45.7	46.6	46.6	45.7	46.6	47.5
152.5°	45.7	44.8	43.9	43.9	43.9	43.9	43.9	44.8	43.9	44.8	44.8
155°	42.9	42.9	42.9	42.9	42.9	42.9	42.9	42.9	42.0	42.9	42.9
157.5°	42.0	42.0	41.1	41.1	41.1	41.1	41.1	41.1	41.1	42.0	41.1
160°	41.1	40.2	40.2	40.2	39.3	39.3	39.3	40.2	40.2	40.2	40.2
162.5°	40.2	39.3	39.3	38.4	38.4	38.4	38.4	39.3	39.3	39.3	39.3
165°	38.4	39.3	38.4	37.5	37.5	37.5	37.5	38.4	38.4	38.4	39.3
167.5°	38.4	37.5	37.5	37.5	36.5	36.5	37.5	37.5	37.5	37.5	37.5
170°	37.5	36.5	36.5	36.5	36.5	36.5	36.5	36.5	36.5	37.5	37.5
172.5°	37.5	37.5	36.5	36.5	36.5	36.5	36.5	37.5	37.5	37.5	37.5
175°	36.5	37.5	37.5	37.5	36.5	36.5	36.5	37.5	37.5	37.5	37.5
177.5°	37.5	37.5	37.5	37.5	37.5	37.5	36.5	37.5	37.5	37.5	37.5
180°	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5

(END OF REPORT)