

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P637118

Luminaire Tested: GWS-SA4C-727-U-T2R-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P637118
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA4C-727-U-T2R-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II ROADWAY OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (64) 2700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14287.5 lumens
Efficiency: N/A
Efficacy: 111.2 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B2 - U0 - G2


Input Watts (W): 128.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P637118
 CATALOG NUMBER: GWS-SA4C-727-U-T2R-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 10.7 fc
 Type II - Short - N/A

REPORT NUMBER: P637118
CATALOG NUMBER: GWS-SA4C-727-U-T2R-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 59-Deg Lateral - - - Horizontal Cone Through 50-Deg Vertical

REPORT NUMBER: P637118

CATALOG NUMBER: GWS-SA4C-727-U-T2R-W-GRSWH

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 3286.4 | 0.0 | 3286.4 |
| | % Fixture | 23.0 | 0.0 | 23.0 |
| Street Side | Lumens | 11001.1 | 0.0 | 11001.1 |
| | % Fixture | 77.0 | 0.0 | 77.0 |
| Total | Lumens | 14287.5 | 0.0 | 14287.5 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 242.8 | 1.7 |
| 10°-20° | 881.5 | 6.2 |
| 20°-30° | 1669.3 | 11.7 |
| 30°-40° | 2768.2 | 19.4 |
| 40°-50° | 3781.5 | 26.5 |
| 50°-60° | 3432.6 | 24.0 |
| 60°-70° | 1143.1 | 8.0 |
| 70°-80° | 333.4 | 2.3 |
| 80°-90° | 35.0 | 0.2 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 14287.5 | 100.0 |
| 0°-180° | 14287.5 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P637118


CATALOG NUMBER: GWS-SA4C-727-U-T2R-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1959.2 | 13.7 | | | |
| FM (30°-60°) | 8138.3 | 57.0 | | | |
| FH (60°-80°) | 889.9 | 6.2 | | | G1/1800 |
| FVH (80°-90°) | 13.7 | 0.1 | | | G1/100 |
| BL (0°-30°) | 834.5 | 5.8 | B2/1000 | | |
| BM (30°-60°) | 1844.0 | 12.9 | B2/2500 | | |
| BH (60°-80°) | 586.6 | 4.1 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 21.3 | 0.1 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G2

Type II Short





REPORT NUMBER: P637118

CATALOG NUMBER: GWS-SA4C-727-U-T2R-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 59° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2164.7 | 2164.7 | 2164.7 | 2164.7 | 2164.7 | 2164.7 | 2164.7 | 2164.7 | 2164.7 | 2164.7 | 2164.7 |
| 2.5° | 2804.7 | 2825.7 | 2793.1 | 2795.4 | 2714.0 | 2676.7 | 2572.0 | 2510.3 | 2469.6 | 2355.5 | 2251.9 |
| 5° | 3370.3 | 3345.9 | 3320.3 | 3305.2 | 3234.2 | 3134.1 | 3003.8 | 2900.2 | 2804.7 | 2581.3 | 2366.0 |
| 7.5° | 3717.2 | 3704.4 | 3686.9 | 3677.6 | 3607.8 | 3503.0 | 3372.7 | 3284.2 | 3145.7 | 2843.1 | 2504.5 |
| 10° | 4011.6 | 3996.5 | 3986.0 | 3993.0 | 3936.0 | 3868.5 | 3726.5 | 3625.2 | 3469.3 | 3120.1 | 2672.1 |
| 12.5° | 4239.7 | 4247.8 | 4251.3 | 4288.6 | 4264.1 | 4223.4 | 4076.8 | 3969.7 | 3796.3 | 3412.2 | 2868.8 |
| 15° | 4420.1 | 4417.8 | 4458.5 | 4529.5 | 4569.1 | 4543.5 | 4425.9 | 4336.3 | 4124.5 | 3699.7 | 3080.6 |
| 17.5° | 4462.0 | 4464.3 | 4528.3 | 4652.8 | 4782.0 | 4844.9 | 4778.5 | 4671.5 | 4462.0 | 3983.7 | 3300.5 |
| 20° | 4495.7 | 4500.4 | 4566.7 | 4708.7 | 4897.2 | 5073.0 | 5083.5 | 5006.6 | 4826.3 | 4290.9 | 3524.0 |
| 22.5° | 4708.7 | 4719.2 | 4736.6 | 4826.3 | 4996.2 | 5218.5 | 5340.7 | 5324.4 | 5173.1 | 4613.3 | 3764.9 |
| 25° | 5268.5 | 5237.1 | 5152.1 | 5126.5 | 5191.7 | 5372.1 | 5580.4 | 5611.8 | 5537.3 | 4968.2 | 4024.4 |
| 27.5° | 5959.8 | 5926.0 | 5800.4 | 5667.7 | 5526.9 | 5589.7 | 5812.0 | 5906.3 | 5907.4 | 5359.3 | 4285.1 |
| 30° | 6587.1 | 6560.3 | 6457.9 | 6268.2 | 6025.0 | 5934.2 | 6098.3 | 6225.1 | 6300.8 | 5810.8 | 4581.9 |
| 32.5° | 7123.6 | 7099.1 | 6960.7 | 6805.9 | 6568.5 | 6385.7 | 6445.1 | 6567.3 | 6744.2 | 6395.0 | 4950.8 |
| 35° | 7575.1 | 7550.7 | 7418.0 | 7262.1 | 7042.1 | 6932.7 | 6911.8 | 6995.6 | 7224.8 | 7004.9 | 5374.4 |
| 37.5° | 7941.7 | 7917.3 | 7778.8 | 7632.2 | 7464.6 | 7471.6 | 7503.0 | 7543.7 | 7675.2 | 7657.8 | 5827.1 |
| 40° | 8179.1 | 8153.5 | 8054.6 | 7949.9 | 7844.0 | 7927.8 | 8083.7 | 8034.8 | 8104.7 | 8185.0 | 6243.8 |
| 42.5° | 8285.1 | 8252.5 | 8195.4 | 8172.2 | 8139.6 | 8269.9 | 8570.2 | 8521.3 | 8437.5 | 8536.4 | 6553.3 |
| 45° | 8179.1 | 8151.2 | 8150.1 | 8221.0 | 8296.7 | 8464.3 | 8906.5 | 8866.9 | 8655.1 | 8706.3 | 6738.4 |
| 47.5° | 7854.4 | 7830.0 | 7896.3 | 8082.6 | 8268.8 | 8513.2 | 9056.6 | 9063.6 | 8809.9 | 8777.3 | 6858.2 |
| 50° | 7152.7 | 7136.4 | 7328.4 | 7681.0 | 8002.2 | 8360.7 | 9008.9 | 9089.2 | 8847.2 | 8755.2 | 6843.1 |
| 52.5° | 5725.9 | 5801.5 | 6219.3 | 6808.2 | 7432.0 | 8093.0 | 8832.0 | 8936.8 | 8667.9 | 8609.7 | 6761.6 |
| 55° | 3919.7 | 3954.6 | 4372.4 | 5232.4 | 6221.6 | 7513.5 | 8425.9 | 8587.6 | 8456.1 | 8585.3 | 6846.6 |
| 57.5° | 2029.7 | 2057.6 | 2386.9 | 3150.4 | 4219.9 | 5937.7 | 7298.2 | 7828.8 | 8029.0 | 8708.7 | 7110.8 |
| 60° | 833.3 | 856.6 | 992.7 | 1361.6 | 2128.6 | 3457.6 | 5252.2 | 6038.9 | 6509.1 | 7953.4 | 6314.7 |
| 62.5° | 605.2 | 616.8 | 682.0 | 812.3 | 1114.9 | 1694.5 | 2972.3 | 3262.1 | 3592.6 | 4984.5 | 4009.3 |
| 65° | 509.7 | 522.5 | 574.9 | 654.1 | 813.5 | 1039.3 | 1269.7 | 1276.7 | 1407.0 | 2030.8 | 1486.2 |
| 67.5° | 427.1 | 438.8 | 485.3 | 552.8 | 657.5 | 737.8 | 682.0 | 683.1 | 680.8 | 736.7 | 712.2 |
| 70° | 332.8 | 342.2 | 388.7 | 460.9 | 515.6 | 473.7 | 533.0 | 590.0 | 565.6 | 587.7 | 621.5 |
| 72.5° | 243.2 | 253.7 | 294.4 | 349.1 | 335.2 | 337.5 | 431.8 | 490.0 | 476.0 | 500.4 | 531.9 |
| 75° | 175.7 | 182.7 | 203.7 | 174.6 | 183.9 | 222.3 | 303.8 | 335.2 | 349.1 | 370.1 | 398.0 |
| 77.5° | 57.0 | 57.0 | 64.0 | 80.3 | 100.1 | 123.4 | 154.8 | 167.6 | 188.5 | 211.8 | 231.6 |
| 80° | 29.1 | 30.3 | 36.1 | 44.2 | 55.9 | 71.0 | 90.8 | 96.6 | 107.1 | 119.9 | 128.0 |
| 82.5° | 14.0 | 15.1 | 17.5 | 22.1 | 29.1 | 37.2 | 50.0 | 55.9 | 62.8 | 71.0 | 76.8 |
| 85° | 3.5 | 3.5 | 4.7 | 7.0 | 9.3 | 14.0 | 18.6 | 22.1 | 27.9 | 33.8 | 37.2 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 1.2 | 3.5 | 4.7 | 5.8 | 7.0 | 9.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P637118

CATALOG NUMBER: GWS-SA4C-727-U-T2R-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2164.7 | 2164.7 | 2164.7 | 2164.7 | 2164.7 | 2164.7 | 2164.7 | 2164.7 | 2164.7 | 2164.7 | 2164.7 |
| 2.5° | 2205.4 | 2140.2 | 2056.4 | 1985.4 | 1920.3 | 1870.2 | 1827.2 | 1806.2 | 1786.4 | 1772.5 | 1777.1 |
| 5° | 2265.9 | 2154.2 | 1998.2 | 1890.0 | 1823.7 | 1789.9 | 1766.6 | 1755.0 | 1752.7 | 1743.4 | 1739.9 |
| 7.5° | 2354.4 | 2194.9 | 1986.6 | 1877.2 | 1833.0 | 1815.5 | 1802.7 | 1795.7 | 1799.2 | 1789.9 | 1786.4 |
| 10° | 2463.8 | 2262.4 | 2015.7 | 1919.1 | 1880.7 | 1867.9 | 1853.9 | 1844.6 | 1840.0 | 1826.0 | 1823.7 |
| 12.5° | 2599.9 | 2346.2 | 2068.1 | 1972.6 | 1934.2 | 1912.1 | 1893.5 | 1877.2 | 1866.7 | 1849.3 | 1844.6 |
| 15° | 2746.6 | 2439.3 | 2129.7 | 2025.0 | 1979.6 | 1947.0 | 1916.8 | 1892.3 | 1873.7 | 1850.4 | 1846.9 |
| 17.5° | 2906.0 | 2537.1 | 2181.0 | 2061.1 | 2002.9 | 1959.8 | 1915.6 | 1879.5 | 1853.9 | 1823.7 | 1820.2 |
| 20° | 3072.4 | 2636.0 | 2219.4 | 2078.5 | 2004.1 | 1945.9 | 1886.5 | 1838.8 | 1806.2 | 1776.0 | 1773.6 |
| 22.5° | 3244.7 | 2726.8 | 2242.6 | 2073.9 | 1985.4 | 1913.3 | 1842.3 | 1788.8 | 1750.3 | 1714.3 | 1711.9 |
| 25° | 3418.1 | 2814.1 | 2248.5 | 2055.3 | 1948.2 | 1864.4 | 1793.4 | 1730.6 | 1687.5 | 1646.8 | 1642.1 |
| 27.5° | 3593.8 | 2887.4 | 2234.5 | 2018.0 | 1898.1 | 1807.4 | 1736.4 | 1674.7 | 1630.5 | 1589.7 | 1582.8 |
| 30° | 3781.2 | 2950.2 | 2204.2 | 1969.1 | 1840.0 | 1746.9 | 1677.0 | 1630.5 | 1588.6 | 1547.8 | 1540.9 |
| 32.5° | 3981.3 | 3004.9 | 2161.2 | 1909.8 | 1772.5 | 1686.3 | 1635.1 | 1593.2 | 1551.3 | 1515.3 | 1508.3 |
| 35° | 4219.9 | 3041.0 | 2097.2 | 1833.0 | 1709.6 | 1642.1 | 1607.2 | 1558.3 | 1507.1 | 1467.5 | 1464.1 |
| 37.5° | 4466.6 | 3068.9 | 2020.3 | 1759.7 | 1654.9 | 1616.5 | 1587.4 | 1521.1 | 1457.1 | 1409.4 | 1403.5 |
| 40° | 4705.2 | 3092.2 | 1924.9 | 1691.0 | 1604.9 | 1597.9 | 1558.3 | 1475.7 | 1365.1 | 1311.6 | 1306.9 |
| 42.5° | 4927.5 | 3099.2 | 1824.8 | 1617.7 | 1559.5 | 1556.0 | 1511.8 | 1383.8 | 1298.8 | 1265.0 | 1260.4 |
| 45° | 5080.0 | 3093.4 | 1721.3 | 1549.0 | 1514.1 | 1495.5 | 1448.9 | 1317.4 | 1265.0 | 1234.8 | 1229.0 |
| 47.5° | 5192.8 | 3063.1 | 1604.9 | 1476.9 | 1462.9 | 1437.3 | 1337.2 | 1275.5 | 1226.6 | 1196.4 | 1190.6 |
| 50° | 5173.1 | 2937.4 | 1487.3 | 1407.0 | 1401.2 | 1379.1 | 1255.7 | 1223.1 | 1180.1 | 1147.5 | 1142.8 |
| 52.5° | 5070.7 | 2698.8 | 1367.5 | 1330.2 | 1341.9 | 1298.8 | 1197.5 | 1160.3 | 1123.1 | 1085.8 | 1077.7 |
| 55° | 5096.3 | 2526.6 | 1276.7 | 1255.7 | 1276.7 | 1178.9 | 1132.4 | 1092.8 | 1057.9 | 1021.8 | 1014.8 |
| 57.5° | 5208.0 | 2356.7 | 1180.1 | 1175.4 | 1197.5 | 1087.0 | 1048.6 | 998.5 | 948.5 | 919.4 | 919.4 |
| 60° | 4373.5 | 1717.8 | 1010.2 | 1021.8 | 1071.9 | 1012.5 | 978.8 | 927.5 | 872.8 | 847.2 | 847.2 |
| 62.5° | 2586.0 | 1077.7 | 837.9 | 825.1 | 856.6 | 893.8 | 912.4 | 870.5 | 805.3 | 771.6 | 772.8 |
| 65° | 1139.4 | 784.4 | 739.0 | 728.5 | 719.2 | 744.8 | 796.0 | 799.5 | 730.9 | 691.3 | 692.5 |
| 67.5° | 701.8 | 709.9 | 691.3 | 683.1 | 675.0 | 670.3 | 665.7 | 668.0 | 649.4 | 613.3 | 612.2 |
| 70° | 633.1 | 655.2 | 642.4 | 635.4 | 625.0 | 616.8 | 588.9 | 543.5 | 512.1 | 502.8 | 513.2 |
| 72.5° | 544.7 | 574.9 | 567.9 | 564.4 | 551.6 | 531.9 | 494.6 | 450.4 | 413.1 | 389.9 | 394.5 |
| 75° | 410.8 | 435.3 | 438.8 | 439.9 | 425.9 | 407.3 | 368.9 | 331.7 | 299.1 | 274.7 | 280.5 |
| 77.5° | 236.3 | 250.2 | 253.7 | 257.2 | 246.7 | 239.7 | 214.1 | 187.4 | 169.9 | 144.3 | 151.3 |
| 80° | 131.5 | 137.3 | 137.3 | 138.5 | 132.7 | 124.5 | 107.1 | 91.9 | 83.8 | 72.2 | 73.3 |
| 82.5° | 79.1 | 81.5 | 82.6 | 83.8 | 80.3 | 72.2 | 59.4 | 48.9 | 44.2 | 38.4 | 37.2 |
| 85° | 38.4 | 40.7 | 40.7 | 41.9 | 36.1 | 31.4 | 24.4 | 18.6 | 16.3 | 11.6 | 12.8 |
| 87.5° | 9.3 | 10.5 | 10.5 | 9.3 | 8.1 | 5.8 | 3.5 | 1.2 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 $CIE R_a = 71.5$
 $R_9 = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)