

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P638136

Luminaire Tested: GWS-SA4E-730-U-RW-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P638136
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-50)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA4E-730-U-RW-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND RECTANGULAR WIDE OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (64) 3000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 18061.4 lumens
Efficiency: N/A
Efficacy: 89.1 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type V - Short
BUG Rating: B4 - U0 - G0


Input Watts (W): 202.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P638136
 CATALOG NUMBER: GWS-SA4E-730-U-RW-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 4.9 fc
 Type V - Short - N/A

REPORT NUMBER: P638136
CATALOG NUMBER: GWS-SA4E-730-U-RW-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 43-Deg Lateral - - - Horizontal Cone Through 50-Deg Vertical

REPORT NUMBER: P638136
 CATALOG NUMBER: GWS-SA4E-730-U-RW-W-GRSBK

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 9030.5 | 0.0 | 9030.5 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Street Side | Lumens | 9030.9 | 0.0 | 9030.9 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Total | Lumens | 18061.4 | 0.0 | 18061.4 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 253.0 | 1.4 |
| 10°-20° | 870.6 | 4.8 |
| 20°-30° | 1761.3 | 9.8 |
| 30°-40° | 3267.9 | 18.1 |
| 40°-50° | 5424.5 | 30.0 |
| 50°-60° | 5535.9 | 30.7 |
| 60°-70° | 907.8 | 5.0 |
| 70°-80° | 39.8 | 0.2 |
| 80°-90° | 0.6 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 18061.4 | 100.0 |
| 0°-180° | 18061.4 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P638136


CATALOG NUMBER: GWS-SA4E-730-U-RW-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 1455.1 | 8.1 | | | |
| FM (30°-60°) | 7131.5 | 39.5 | | | |
| FH (60°-80°) | 444.1 | 2.5 | | | G0/660 |
| FVH (80°-90°) | 0.2 | 0.0 | | | G0/10 |
| BL (0°-30°) | 1429.8 | 7.9 | B3/2500 | | |
| BM (30°-60°) | 7096.9 | 39.3 | B4/8500 | | |
| BH (60°-80°) | 503.5 | 2.8 | B2/1000 | | G0/660 |
| BVH (80°-90°) | 0.4 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B4-U0-G0

Type V Short





REPORT NUMBER: P638136

CATALOG NUMBER: GWS-SA4E-730-U-RW-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 43° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2568.9 | 2568.9 | 2568.9 | 2568.9 | 2568.9 | 2568.9 | 2568.9 | 2568.9 | 2568.9 | 2568.9 | 2568.9 |
| 2.5° | 2521.0 | 2527.0 | 2535.0 | 2543.0 | 2553.0 | 2563.0 | 2568.9 | 2586.9 | 2582.9 | 2598.9 | 2598.9 |
| 5° | 2493.0 | 2499.0 | 2509.0 | 2527.0 | 2549.0 | 2570.9 | 2586.9 | 2622.9 | 2642.9 | 2674.8 | 2686.8 |
| 7.5° | 2507.0 | 2515.0 | 2527.0 | 2555.0 | 2588.9 | 2622.9 | 2640.9 | 2698.8 | 2738.7 | 2798.7 | 2832.6 |
| 10° | 2553.0 | 2561.0 | 2580.9 | 2628.9 | 2672.8 | 2720.8 | 2742.7 | 2816.7 | 2880.6 | 2962.5 | 3010.4 |
| 12.5° | 2604.9 | 2614.9 | 2654.8 | 2726.8 | 2802.7 | 2866.6 | 2896.6 | 2978.5 | 3044.4 | 3136.3 | 3212.2 |
| 15° | 2658.8 | 2674.8 | 2736.7 | 2842.6 | 2950.5 | 3036.4 | 3068.4 | 3156.3 | 3222.2 | 3320.1 | 3406.0 |
| 17.5° | 2784.7 | 2802.7 | 2872.6 | 2986.5 | 3134.3 | 3234.2 | 3262.1 | 3354.0 | 3404.0 | 3469.9 | 3559.8 |
| 20° | 2942.5 | 2976.5 | 3062.4 | 3200.2 | 3362.0 | 3457.9 | 3477.9 | 3567.8 | 3563.8 | 3591.7 | 3669.6 |
| 22.5° | 3138.3 | 3162.2 | 3256.1 | 3419.9 | 3601.7 | 3707.6 | 3753.5 | 3791.5 | 3741.6 | 3717.6 | 3767.5 |
| 25° | 3342.0 | 3370.0 | 3471.9 | 3651.7 | 3855.4 | 3977.3 | 4015.2 | 4045.2 | 3965.3 | 3875.4 | 3881.4 |
| 27.5° | 3605.7 | 3625.7 | 3725.6 | 3917.3 | 4121.1 | 4258.9 | 4292.9 | 4344.8 | 4239.0 | 4095.1 | 4055.2 |
| 30° | 3919.3 | 3939.3 | 4045.2 | 4247.0 | 4448.7 | 4566.6 | 4618.5 | 4682.4 | 4566.6 | 4386.8 | 4340.8 |
| 32.5° | 4286.9 | 4306.9 | 4442.7 | 4650.5 | 4816.3 | 4944.1 | 4994.1 | 5062.0 | 4970.1 | 4768.3 | 4716.4 |
| 35° | 4726.4 | 4738.4 | 4898.2 | 5123.9 | 5299.7 | 5423.6 | 5457.5 | 5537.4 | 5435.5 | 5233.8 | 5205.8 |
| 37.5° | 5235.8 | 5249.8 | 5423.6 | 5685.2 | 5865.0 | 6002.9 | 6056.8 | 6078.8 | 5954.9 | 5729.2 | 5707.2 |
| 40° | 5795.1 | 5841.1 | 6010.9 | 6292.5 | 6494.3 | 6668.1 | 6716.0 | 6642.1 | 6468.3 | 6160.7 | 6120.7 |
| 42.5° | 6378.4 | 6418.4 | 6608.2 | 6913.8 | 7147.5 | 7325.3 | 7327.3 | 7167.5 | 6871.8 | 6446.3 | 6386.4 |
| 45° | 6863.8 | 6879.8 | 7125.5 | 7433.2 | 7720.8 | 7846.7 | 7858.7 | 7569.0 | 7123.5 | 6612.1 | 6484.3 |
| 47.5° | 7197.5 | 7223.4 | 7437.2 | 7732.8 | 8050.4 | 8164.3 | 8140.3 | 7778.8 | 7243.4 | 6720.0 | 6508.3 |
| 50° | 7201.4 | 7245.4 | 7477.1 | 7762.8 | 8070.4 | 8208.2 | 8174.3 | 7838.7 | 7311.3 | 6724.0 | 6450.3 |
| 52.5° | 6564.2 | 6636.1 | 7013.7 | 7427.2 | 7898.6 | 8134.3 | 8142.3 | 7916.6 | 7285.3 | 6660.1 | 6398.4 |
| 55° | 4952.1 | 5030.0 | 5505.5 | 6210.6 | 7121.5 | 7778.8 | 7892.6 | 7824.7 | 7255.4 | 6688.1 | 6490.3 |
| 57.5° | 2620.9 | 2561.0 | 2824.6 | 3523.8 | 4668.5 | 5831.1 | 6164.7 | 6708.0 | 6921.8 | 6722.0 | 6660.1 |
| 60° | 571.3 | 609.3 | 811.0 | 1092.7 | 1821.8 | 2742.7 | 3068.4 | 3999.2 | 5105.9 | 5597.4 | 5952.9 |
| 62.5° | 245.7 | 241.7 | 251.7 | 285.7 | 417.5 | 695.2 | 849.0 | 1386.4 | 2187.4 | 3004.4 | 3557.8 |
| 65° | 201.8 | 203.8 | 211.7 | 211.7 | 197.8 | 199.8 | 209.8 | 317.6 | 511.4 | 717.1 | 962.9 |
| 67.5° | 151.8 | 153.8 | 167.8 | 171.8 | 161.8 | 143.8 | 141.8 | 119.9 | 125.9 | 157.8 | 163.8 |
| 70° | 95.9 | 95.9 | 103.9 | 107.9 | 107.9 | 99.9 | 97.9 | 85.9 | 83.9 | 95.9 | 107.9 |
| 72.5° | 51.9 | 51.9 | 55.9 | 57.9 | 55.9 | 53.9 | 53.9 | 51.9 | 49.9 | 57.9 | 73.9 |
| 75° | 22.0 | 22.0 | 24.0 | 24.0 | 22.0 | 22.0 | 22.0 | 22.0 | 22.0 | 26.0 | 40.0 |
| 77.5° | 4.0 | 6.0 | 8.0 | 6.0 | 4.0 | 4.0 | 4.0 | 6.0 | 6.0 | 8.0 | 12.0 |
| 80° | 2.0 | 2.0 | 4.0 | 2.0 | 0.0 | 0.0 | 0.0 | 0.0 | 2.0 | 2.0 | 2.0 |
| 82.5° | 2.0 | 2.0 | 2.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 2.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P638136
 CATALOG NUMBER: GWS-SA4E-730-U-RW-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2568.9 | 2568.9 | 2568.9 | 2568.9 | 2568.9 | 2568.9 | 2568.9 | 2568.9 | 2568.9 | 2568.9 | 2568.9 |
| 2.5° | 2612.9 | 2590.9 | 2598.9 | 2602.9 | 2596.9 | 2592.9 | 2570.9 | 2565.0 | 2555.0 | 2539.0 | 2535.0 |
| 5° | 2700.8 | 2682.8 | 2680.8 | 2668.8 | 2640.9 | 2606.9 | 2565.0 | 2547.0 | 2527.0 | 2507.0 | 2503.0 |
| 7.5° | 2848.6 | 2826.6 | 2812.7 | 2772.7 | 2708.8 | 2654.8 | 2584.9 | 2547.0 | 2521.0 | 2495.0 | 2489.0 |
| 10° | 3038.4 | 3012.4 | 2972.5 | 2898.6 | 2812.7 | 2734.8 | 2652.8 | 2602.9 | 2563.0 | 2527.0 | 2525.0 |
| 12.5° | 3240.2 | 3212.2 | 3140.3 | 3046.4 | 2942.5 | 2870.6 | 2766.7 | 2696.8 | 2636.9 | 2582.9 | 2576.9 |
| 15° | 3451.9 | 3417.9 | 3320.1 | 3208.2 | 3112.3 | 3038.4 | 2924.5 | 2812.7 | 2720.8 | 2642.9 | 2634.9 |
| 17.5° | 3613.7 | 3571.8 | 3455.9 | 3372.0 | 3294.1 | 3218.2 | 3090.3 | 2942.5 | 2820.6 | 2726.8 | 2704.8 |
| 20° | 3715.6 | 3675.6 | 3565.8 | 3519.8 | 3483.9 | 3429.9 | 3278.1 | 3124.3 | 2988.5 | 2872.6 | 2852.6 |
| 22.5° | 3813.5 | 3765.5 | 3669.6 | 3669.6 | 3697.6 | 3675.6 | 3511.8 | 3336.0 | 3176.2 | 3042.4 | 3012.4 |
| 25° | 3923.3 | 3885.4 | 3817.5 | 3873.4 | 3943.3 | 3941.3 | 3773.5 | 3553.8 | 3370.0 | 3220.2 | 3190.2 |
| 27.5° | 4083.1 | 4045.2 | 4021.2 | 4127.1 | 4215.0 | 4209.0 | 4025.2 | 3787.5 | 3593.7 | 3445.9 | 3417.9 |
| 30° | 4364.8 | 4328.9 | 4302.9 | 4430.7 | 4542.6 | 4500.7 | 4298.9 | 4069.2 | 3873.4 | 3705.6 | 3685.6 |
| 32.5° | 4740.4 | 4702.4 | 4668.5 | 4796.3 | 4896.2 | 4842.2 | 4650.5 | 4434.7 | 4209.0 | 4045.2 | 4005.2 |
| 35° | 5233.8 | 5153.9 | 5119.9 | 5271.7 | 5313.7 | 5253.8 | 5070.0 | 4880.2 | 4640.5 | 4452.7 | 4426.7 |
| 37.5° | 5743.2 | 5649.3 | 5625.3 | 5757.2 | 5825.1 | 5803.1 | 5587.4 | 5389.6 | 5129.9 | 4922.2 | 4892.2 |
| 40° | 6178.7 | 6092.8 | 6050.8 | 6256.6 | 6410.4 | 6424.4 | 6230.6 | 5988.9 | 5683.2 | 5467.5 | 5413.6 |
| 42.5° | 6434.4 | 6360.4 | 6350.5 | 6670.1 | 6921.8 | 7101.6 | 6869.8 | 6620.1 | 6298.5 | 6054.8 | 6010.9 |
| 45° | 6492.3 | 6444.3 | 6528.2 | 6947.7 | 7339.3 | 7666.9 | 7469.1 | 7205.4 | 6857.9 | 6600.2 | 6558.2 |
| 47.5° | 6486.3 | 6470.3 | 6620.1 | 7091.6 | 7587.0 | 7990.5 | 7892.6 | 7595.0 | 7259.4 | 6989.7 | 6949.7 |
| 50° | 6400.4 | 6402.4 | 6652.1 | 7163.5 | 7686.9 | 8078.4 | 7980.5 | 7704.8 | 7405.2 | 7139.5 | 7107.6 |
| 52.5° | 6366.4 | 6354.5 | 6592.2 | 7141.5 | 7788.7 | 8038.5 | 7818.7 | 7509.1 | 7175.5 | 6847.9 | 6799.9 |
| 55° | 6486.3 | 6456.3 | 6600.2 | 7123.5 | 7800.7 | 8016.5 | 7437.2 | 6766.0 | 6082.8 | 5695.2 | 5663.3 |
| 57.5° | 6666.1 | 6634.1 | 6702.0 | 6991.7 | 7175.5 | 6666.1 | 5473.5 | 4390.8 | 3687.6 | 3390.0 | 3260.1 |
| 60° | 5952.9 | 5931.0 | 5879.0 | 5529.4 | 4742.4 | 3577.8 | 2437.1 | 1554.2 | 1116.7 | 902.9 | 902.9 |
| 62.5° | 3693.6 | 3663.6 | 3382.0 | 2513.0 | 1825.8 | 1056.7 | 581.3 | 363.6 | 275.7 | 257.7 | 255.7 |
| 65° | 1036.8 | 1030.8 | 853.0 | 603.3 | 383.5 | 237.7 | 209.8 | 213.7 | 209.8 | 203.8 | 201.8 |
| 67.5° | 155.8 | 171.8 | 171.8 | 139.8 | 133.8 | 149.8 | 175.8 | 187.8 | 177.8 | 167.8 | 163.8 |
| 70° | 99.9 | 107.9 | 103.9 | 89.9 | 95.9 | 111.9 | 125.9 | 127.8 | 121.9 | 111.9 | 109.9 |
| 72.5° | 69.9 | 77.9 | 63.9 | 57.9 | 59.9 | 65.9 | 71.9 | 71.9 | 69.9 | 65.9 | 61.9 |
| 75° | 42.0 | 42.0 | 30.0 | 28.0 | 28.0 | 30.0 | 30.0 | 34.0 | 34.0 | 32.0 | 30.0 |
| 77.5° | 14.0 | 16.0 | 10.0 | 8.0 | 8.0 | 8.0 | 10.0 | 12.0 | 12.0 | 10.0 | 8.0 |
| 80° | 2.0 | 4.0 | 2.0 | 2.0 | 2.0 | 2.0 | 2.0 | 2.0 | 4.0 | 4.0 | 2.0 |
| 82.5° | 2.0 | 2.0 | 2.0 | 0.0 | 0.0 | 0.0 | 0.0 | 2.0 | 2.0 | 2.0 | 2.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 2.0 | 2.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-2-R4

Test Date: 10/03/2019

Luminaire Tested: SA1C-730-U-5WQ

Data in this report applies to families of products SA1C-730-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-2-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-730-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-2-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. (1) 70 CRI, 3000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 2993 | CRI (Ra): | 71.8 | R9: | -38.3 |
| CIE u': | 0.2508 | R1: | 67.5 | R10: | 62.5 |
| CIE v': | 0.5215 | R2: | 82.9 | R11: | 63.7 |
| Duv: | 0.0000 | R3: | 94.7 | R12: | 57.8 |
| CIE x: | 0.4374 | R4: | 67.7 | R13: | 70.4 |
| CIE y: | 0.4043 | R5: | 67.9 | R14: | 97.3 |
| CIE z: | 0.1583 | R6: | 77.6 | | |
| Peak Wavelength (nm): | 593 | R7: | 76.0 | | |
| Dominant Wavelength (nm): | 582 | R8: | 40.5 | | |
| Purity: | 53 | | | | |
| Rf: | 75.7 | | | | |
| Rg: | 93.9 | | | | |



Test Conditions

Stabilization Time: 53M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-2-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-2-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-2-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 8494.8

S/P: 1.23

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3101.5 M/P: 0.45

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Summary

$R_f = 75.7$
 $R_g = 93.9$
 CIE $R_a = 71.8$
 $R_9 = -38.3$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 67 | CES51 = 87 | CES76 = 63 |
| CES02 = 63 | CES27 = 88 | CES52 = 86 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 78 | CES78 = 67 |
| CES04 = 71 | CES29 = 66 | CES54 = 84 | CES79 = 87 |
| CES05 = 49 | CES30 = 73 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 70 | CES56 = 75 | CES81 = 71 |
| CES07 = 41 | CES32 = 65 | CES57 = 74 | CES82 = 94 |
| CES08 = 40 | CES33 = 73 | CES58 = 76 | CES83 = 90 |
| CES09 = 29 | CES34 = 79 | CES59 = 85 | CES84 = 89 |
| CES10 = 76 | CES35 = 89 | CES60 = 93 | CES85 = 77 |
| CES11 = 59 | CES36 = 97 | CES61 = 84 | CES86 = 61 |
| CES12 = 65 | CES37 = 87 | CES62 = 91 | CES87 = 78 |
| CES13 = 43 | CES38 = 81 | CES63 = 77 | CES88 = 77 |
| CES14 = 74 | CES39 = 95 | CES64 = 72 | CES89 = 67 |
| CES15 = 71 | CES40 = 92 | CES65 = 68 | CES90 = 76 |
| CES16 = 47 | CES41 = 88 | CES66 = 69 | CES91 = 89 |
| CES17 = 50 | CES42 = 89 | CES67 = 67 | CES92 = 58 |
| CES18 = 56 | CES43 = 79 | CES68 = 72 | CES93 = 74 |
| CES19 = 73 | CES44 = 99 | CES69 = 81 | CES94 = 49 |
| CES20 = 66 | CES45 = 85 | CES70 = 66 | CES95 = 68 |
| CES21 = 87 | CES46 = 80 | CES71 = 67 | CES96 = 76 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 69 | CES73 = 59 | CES98 = 75 |
| CES24 = 91 | CES49 = 80 | CES74 = 95 | CES99 = 62 |
| CES25 = 73 | CES50 = 87 | CES75 = 69 | |



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Measure Comparisons



(END OF REPORT)