

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P638166

Luminaire Tested: GWS-SA4E-730-U-T3-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P638166
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-24)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA4E-730-U-T3-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (64) 3000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 17208.4 lumens
Efficiency: N/A
Efficacy: 84.9 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G1


Input Watts (W): 202.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P638166
 CATALOG NUMBER: GWS-SA4E-730-U-T3-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 6.5 fc
 Type II - Short - N/A

REPORT NUMBER: P638166
CATALOG NUMBER: GWS-SA4E-730-U-T3-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 47-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P638166
 CATALOG NUMBER: GWS-SA4E-730-U-T3-W-GRSBK

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 3733.3 | 0.0 | 3733.3 |
| | % Fixture | 21.7 | 0.0 | 21.7 |
| Street Side | Lumens | 13475.1 | 0.0 | 13475.1 |
| | % Fixture | 78.3 | 0.0 | 78.3 |
| Total | Lumens | 17208.4 | 0.0 | 17208.4 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 286.6 | 1.7 |
| 10°-20° | 967.0 | 5.6 |
| 20°-30° | 1795.6 | 10.4 |
| 30°-40° | 2874.4 | 16.7 |
| 40°-50° | 4201.7 | 24.4 |
| 50°-60° | 5185.6 | 30.1 |
| 60°-70° | 1732.7 | 10.1 |
| 70°-80° | 161.5 | 0.9 |
| 80°-90° | 3.4 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 17208.4 | 100.0 |
| 0°-180° | 17208.4 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P638166


CATALOG NUMBER: GWS-SA4E-730-U-T3-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1778.4 | 10.3 | | | |
| FM (30°-60°) | 10084.0 | 58.6 | | | |
| FH (60°-80°) | 1610.4 | 9.4 | | | G1/1800 |
| FVH (80°-90°) | 2.3 | 0.0 | | | G0/10 |
| BL (0°-30°) | 1270.8 | 7.4 | B3/2500 | | |
| BM (30°-60°) | 2177.7 | 12.7 | B2/2500 | | |
| BH (60°-80°) | 283.8 | 1.6 | B1/500 | | G1/500 |
| BVH (80°-90°) | 1.1 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G1

Type II Short





REPORT NUMBER: P638166

CATALOG NUMBER: GWS-SA4E-730-U-T3-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 47° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 2880.7 | 2880.7 | 2880.7 | 2880.7 | 2880.7 | 2880.7 | 2880.7 | 2880.7 | 2880.7 | 2880.7 | 2880.7 |
| 2.5° | 2910.7 | 2908.7 | 2906.7 | 2918.7 | 2914.7 | 2912.7 | 2916.7 | 2916.7 | 2916.7 | 2904.7 | 2880.7 |
| 5° | 2980.6 | 2980.6 | 2978.6 | 2990.6 | 2980.6 | 2974.6 | 2976.6 | 2976.6 | 2968.6 | 2946.6 | 2916.7 |
| 7.5° | 3090.5 | 3086.5 | 3082.5 | 3094.5 | 3084.5 | 3082.5 | 3086.5 | 3074.5 | 3060.5 | 3024.5 | 2982.6 |
| 10° | 3248.3 | 3248.3 | 3242.3 | 3254.3 | 3246.3 | 3242.3 | 3242.3 | 3234.3 | 3208.3 | 3152.4 | 3090.5 |
| 12.5° | 3466.0 | 3456.0 | 3442.1 | 3432.1 | 3428.1 | 3426.1 | 3428.1 | 3416.1 | 3388.1 | 3316.2 | 3230.3 |
| 15° | 3703.8 | 3695.8 | 3673.8 | 3657.8 | 3635.8 | 3631.8 | 3643.8 | 3633.8 | 3605.9 | 3508.0 | 3386.1 |
| 17.5° | 4003.4 | 4013.4 | 3957.5 | 3923.5 | 3859.6 | 3855.6 | 3859.6 | 3875.6 | 3855.6 | 3729.7 | 3551.9 |
| 20° | 4259.1 | 4267.1 | 4225.2 | 4201.2 | 4143.3 | 4117.3 | 4125.3 | 4151.3 | 4129.3 | 3981.4 | 3733.7 |
| 22.5° | 4532.8 | 4542.8 | 4498.9 | 4448.9 | 4422.9 | 4422.9 | 4452.9 | 4488.9 | 4458.9 | 4265.1 | 3941.5 |
| 25° | 4860.4 | 4868.4 | 4832.5 | 4766.5 | 4720.6 | 4778.5 | 4822.5 | 4918.4 | 4868.4 | 4604.7 | 4187.2 |
| 27.5° | 5236.0 | 5238.0 | 5186.1 | 5118.1 | 5094.2 | 5202.0 | 5246.0 | 5393.8 | 5373.9 | 4986.3 | 4446.9 |
| 30° | 5637.6 | 5639.5 | 5627.6 | 5581.6 | 5559.6 | 5701.5 | 5761.4 | 5975.2 | 5961.2 | 5459.8 | 4800.5 |
| 32.5° | 6055.1 | 6055.1 | 6077.0 | 6073.1 | 6099.0 | 6330.8 | 6426.6 | 6670.4 | 6656.4 | 6039.1 | 5240.0 |
| 35° | 6474.6 | 6476.6 | 6514.5 | 6610.4 | 6718.3 | 7026.0 | 7151.8 | 7447.5 | 7415.5 | 6732.3 | 5801.4 |
| 37.5° | 6952.0 | 6932.1 | 6984.0 | 7127.8 | 7367.6 | 7723.2 | 7843.0 | 8124.7 | 8088.7 | 7441.5 | 6534.5 |
| 40° | 7527.4 | 7491.4 | 7491.4 | 7659.2 | 7930.9 | 8340.5 | 8442.3 | 8582.2 | 8460.3 | 8014.8 | 7253.7 |
| 42.5° | 8162.7 | 8128.7 | 8084.8 | 8232.6 | 8460.3 | 8780.0 | 8863.9 | 8825.9 | 8726.0 | 8556.2 | 8072.8 |
| 45° | 8805.9 | 8754.0 | 8784.0 | 8873.8 | 9005.7 | 9157.5 | 9189.5 | 9013.7 | 8967.7 | 9015.7 | 8750.0 |
| 47.5° | 9295.4 | 9259.4 | 9333.3 | 9459.2 | 9567.1 | 9589.0 | 9567.1 | 9323.3 | 9319.3 | 9489.1 | 9219.5 |
| 50° | 9459.2 | 9463.2 | 9666.9 | 9942.6 | 10116.4 | 10134.4 | 10104.4 | 9824.8 | 9786.8 | 9836.7 | 9473.2 |
| 52.5° | 9475.2 | 9491.1 | 9788.8 | 10314.2 | 10787.7 | 11003.4 | 10979.4 | 10677.8 | 10306.2 | 10252.3 | 9856.7 |
| 55° | 9089.6 | 9183.5 | 9599.0 | 10366.1 | 11373.0 | 12062.2 | 12142.1 | 11564.8 | 11013.4 | 10967.5 | 10681.8 |
| 57.5° | 7265.7 | 7457.5 | 7958.9 | 9051.6 | 10719.7 | 12172.1 | 12379.8 | 11964.3 | 11430.9 | 11235.1 | 10460.0 |
| 60° | 4343.0 | 4580.8 | 5062.2 | 6402.7 | 8158.7 | 10004.6 | 10362.1 | 10420.1 | 10174.4 | 9609.0 | 8024.8 |
| 62.5° | 1863.9 | 1843.9 | 2437.2 | 3464.0 | 4852.4 | 6358.7 | 6520.5 | 6772.3 | 6986.0 | 6394.7 | 4870.4 |
| 65° | 639.3 | 695.2 | 966.9 | 1562.2 | 2429.2 | 2952.6 | 3096.5 | 3322.2 | 3625.9 | 2992.6 | 1784.0 |
| 67.5° | 395.5 | 419.5 | 557.4 | 922.9 | 1310.5 | 1290.5 | 1226.6 | 1190.6 | 1158.7 | 793.1 | 489.4 |
| 70° | 287.7 | 307.6 | 391.6 | 635.3 | 881.0 | 619.3 | 537.4 | 435.5 | 483.4 | 445.5 | 347.6 |
| 72.5° | 193.8 | 209.8 | 269.7 | 385.6 | 451.5 | 301.7 | 279.7 | 317.6 | 383.6 | 365.6 | 283.7 |
| 75° | 115.9 | 125.9 | 153.8 | 187.8 | 183.8 | 155.8 | 157.8 | 223.7 | 293.7 | 273.7 | 201.8 |
| 77.5° | 79.9 | 83.9 | 101.9 | 121.9 | 89.9 | 47.9 | 43.9 | 61.9 | 99.9 | 99.9 | 67.9 |
| 80° | 20.0 | 26.0 | 26.0 | 16.0 | 14.0 | 12.0 | 12.0 | 18.0 | 28.0 | 20.0 | 10.0 |
| 82.5° | 2.0 | 2.0 | 2.0 | 2.0 | 2.0 | 2.0 | 2.0 | 4.0 | 4.0 | 4.0 | 4.0 |
| 85° | 0.0 | 0.0 | 2.0 | 2.0 | 2.0 | 2.0 | 2.0 | 2.0 | 4.0 | 4.0 | 4.0 |
| 87.5° | 0.0 | 0.0 | 2.0 | 2.0 | 2.0 | 2.0 | 2.0 | 2.0 | 2.0 | 4.0 | 4.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P638166

CATALOG NUMBER: GWS-SA4E-730-U-T3-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2880.7 | 2880.7 | 2880.7 | 2880.7 | 2880.7 | 2880.7 | 2880.7 | 2880.7 | 2880.7 | 2880.7 | 2880.7 |
| 2.5° | 2894.7 | 2870.7 | 2886.7 | 2882.7 | 2894.7 | 2898.7 | 2880.7 | 2876.7 | 2878.7 | 2854.7 | 2846.7 |
| 5° | 2922.7 | 2894.7 | 2902.7 | 2894.7 | 2908.7 | 2920.7 | 2914.7 | 2922.7 | 2932.6 | 2914.7 | 2906.7 |
| 7.5° | 2982.6 | 2954.6 | 2952.6 | 2940.6 | 2960.6 | 2968.6 | 2966.6 | 2988.6 | 3008.6 | 2996.6 | 2984.6 |
| 10° | 3086.5 | 3048.5 | 3044.5 | 3034.5 | 3040.5 | 3046.5 | 3024.5 | 3028.5 | 3046.5 | 3032.5 | 3026.5 |
| 12.5° | 3214.3 | 3168.4 | 3158.4 | 3134.4 | 3134.4 | 3104.4 | 3056.5 | 3046.5 | 3060.5 | 3050.5 | 3040.5 |
| 15° | 3352.2 | 3290.2 | 3274.3 | 3232.3 | 3192.3 | 3136.4 | 3086.5 | 3074.5 | 3084.5 | 3072.5 | 3064.5 |
| 17.5° | 3506.0 | 3436.1 | 3384.1 | 3310.2 | 3222.3 | 3156.4 | 3100.5 | 3074.5 | 3058.5 | 3034.5 | 3032.5 |
| 20° | 3657.8 | 3565.9 | 3478.0 | 3360.2 | 3244.3 | 3144.4 | 3052.5 | 2984.6 | 2926.7 | 2890.7 | 2876.7 |
| 22.5° | 3833.6 | 3697.8 | 3555.9 | 3390.1 | 3224.3 | 3072.5 | 2910.7 | 2794.8 | 2694.9 | 2661.0 | 2645.0 |
| 25° | 4021.4 | 3845.6 | 3633.8 | 3418.1 | 3156.4 | 2912.7 | 2692.9 | 2521.1 | 2389.3 | 2345.3 | 2327.3 |
| 27.5° | 4229.2 | 3987.4 | 3713.8 | 3412.1 | 3016.5 | 2684.9 | 2393.3 | 2179.5 | 2049.7 | 2009.7 | 2023.7 |
| 30° | 4492.9 | 4171.2 | 3813.6 | 3350.2 | 2806.8 | 2365.3 | 2023.7 | 1843.9 | 1746.0 | 1708.0 | 1710.0 |
| 32.5° | 4844.5 | 4434.9 | 3959.5 | 3218.3 | 2537.1 | 2001.7 | 1702.1 | 1570.2 | 1504.3 | 1454.3 | 1450.3 |
| 35° | 5347.9 | 4836.5 | 4095.3 | 3006.6 | 2209.5 | 1678.1 | 1460.3 | 1356.4 | 1264.6 | 1206.6 | 1216.6 |
| 37.5° | 5951.2 | 5341.9 | 4169.2 | 2720.9 | 1841.9 | 1426.4 | 1278.5 | 1172.7 | 1068.8 | 982.9 | 992.9 |
| 40° | 6666.4 | 6003.1 | 4163.2 | 2345.3 | 1506.3 | 1254.6 | 1126.7 | 1002.9 | 873.0 | 795.1 | 803.1 |
| 42.5° | 7463.5 | 6628.4 | 4033.4 | 1947.8 | 1248.6 | 1114.7 | 980.9 | 825.1 | 699.2 | 651.3 | 653.3 |
| 45° | 8154.7 | 7135.8 | 3805.6 | 1536.2 | 1050.8 | 978.9 | 829.1 | 669.2 | 613.3 | 579.3 | 577.3 |
| 47.5° | 8666.1 | 7507.4 | 3480.0 | 1208.6 | 891.0 | 855.0 | 681.2 | 599.3 | 555.4 | 527.4 | 523.4 |
| 50° | 8951.8 | 7637.3 | 3120.4 | 946.9 | 753.1 | 725.2 | 609.3 | 543.4 | 513.4 | 495.4 | 491.4 |
| 52.5° | 9335.3 | 7793.1 | 2862.7 | 747.1 | 631.3 | 593.3 | 561.4 | 505.4 | 485.4 | 471.5 | 465.5 |
| 55° | 9942.6 | 8094.7 | 2639.0 | 593.3 | 525.4 | 517.4 | 529.4 | 483.4 | 471.5 | 449.5 | 441.5 |
| 57.5° | 9371.3 | 7271.7 | 2049.7 | 459.5 | 443.5 | 473.5 | 511.4 | 461.5 | 431.5 | 411.5 | 403.5 |
| 60° | 6594.5 | 4834.5 | 1030.8 | 369.6 | 395.5 | 443.5 | 481.4 | 417.5 | 387.6 | 391.6 | 387.6 |
| 62.5° | 3635.8 | 2419.2 | 463.5 | 309.6 | 343.6 | 391.6 | 411.5 | 361.6 | 341.6 | 375.6 | 381.6 |
| 65° | 1188.6 | 823.1 | 267.7 | 239.7 | 271.7 | 319.6 | 355.6 | 343.6 | 339.6 | 379.6 | 391.6 |
| 67.5° | 365.6 | 271.7 | 181.8 | 171.8 | 187.8 | 235.7 | 299.7 | 371.6 | 399.5 | 411.5 | 417.5 |
| 70° | 273.7 | 213.8 | 155.8 | 145.8 | 153.8 | 179.8 | 253.7 | 309.6 | 291.7 | 293.7 | 289.7 |
| 72.5° | 219.7 | 169.8 | 133.8 | 127.9 | 127.9 | 123.9 | 133.8 | 167.8 | 189.8 | 199.8 | 199.8 |
| 75° | 153.8 | 119.9 | 101.9 | 93.9 | 73.9 | 59.9 | 53.9 | 53.9 | 47.9 | 45.9 | 43.9 |
| 77.5° | 51.9 | 43.9 | 40.0 | 32.0 | 22.0 | 18.0 | 16.0 | 14.0 | 10.0 | 6.0 | 4.0 |
| 80° | 8.0 | 6.0 | 4.0 | 4.0 | 4.0 | 2.0 | 2.0 | 2.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 4.0 | 4.0 | 4.0 | 4.0 | 4.0 | 2.0 | 2.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 4.0 | 4.0 | 4.0 | 4.0 | 4.0 | 2.0 | 2.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 4.0 | 4.0 | 4.0 | 4.0 | 2.0 | 2.0 | 2.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-2-R4

Test Date: 10/03/2019

Luminaire Tested: SA1C-730-U-5WQ

Data in this report applies to families of products SA1C-730-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-2-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: MCGRAW-EDISON
 Catalog Number: **SA1C-730-U-5WQ**
 Description: MCGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-2-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. (1) 70 CRI, 3000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 2993 | CRI (Ra): | 71.8 | R9: | -38.3 |
| CIE u': | 0.2508 | R1: | 67.5 | R10: | 62.5 |
| CIE v': | 0.5215 | R2: | 82.9 | R11: | 63.7 |
| Duv: | 0.0000 | R3: | 94.7 | R12: | 57.8 |
| CIE x: | 0.4374 | R4: | 67.7 | R13: | 70.4 |
| CIE y: | 0.4043 | R5: | 67.9 | R14: | 97.3 |
| CIE z: | 0.1583 | R6: | 77.6 | | |
| Peak Wavelength (nm): | 593 | R7: | 76.0 | | |
| Dominant Wavelength (nm): | 582 | R8: | 40.5 | | |
| Purity: | 53 | | | | |
| Rf: | 75.7 | | | | |
| Rg: | 93.9 | | | | |



Test Conditions

Stabilization Time: 53M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-2-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-2-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-2-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 8494.8

S/P: 1.23

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3101.5 M/P: 0.45

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Summary

$R_f = 75.7$
 $R_g = 93.9$
 CIE $R_a = 71.8$
 $R_9 = -38.3$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 67 | CES51 = 87 | CES76 = 63 |
| CES02 = 63 | CES27 = 88 | CES52 = 86 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 78 | CES78 = 67 |
| CES04 = 71 | CES29 = 66 | CES54 = 84 | CES79 = 87 |
| CES05 = 49 | CES30 = 73 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 70 | CES56 = 75 | CES81 = 71 |
| CES07 = 41 | CES32 = 65 | CES57 = 74 | CES82 = 94 |
| CES08 = 40 | CES33 = 73 | CES58 = 76 | CES83 = 90 |
| CES09 = 29 | CES34 = 79 | CES59 = 85 | CES84 = 89 |
| CES10 = 76 | CES35 = 89 | CES60 = 93 | CES85 = 77 |
| CES11 = 59 | CES36 = 97 | CES61 = 84 | CES86 = 61 |
| CES12 = 65 | CES37 = 87 | CES62 = 91 | CES87 = 78 |
| CES13 = 43 | CES38 = 81 | CES63 = 77 | CES88 = 77 |
| CES14 = 74 | CES39 = 95 | CES64 = 72 | CES89 = 67 |
| CES15 = 71 | CES40 = 92 | CES65 = 68 | CES90 = 76 |
| CES16 = 47 | CES41 = 88 | CES66 = 69 | CES91 = 89 |
| CES17 = 50 | CES42 = 89 | CES67 = 67 | CES92 = 58 |
| CES18 = 56 | CES43 = 79 | CES68 = 72 | CES93 = 74 |
| CES19 = 73 | CES44 = 99 | CES69 = 81 | CES94 = 49 |
| CES20 = 66 | CES45 = 85 | CES70 = 66 | CES95 = 68 |
| CES21 = 87 | CES46 = 80 | CES71 = 67 | CES96 = 76 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 69 | CES73 = 59 | CES98 = 75 |
| CES24 = 91 | CES49 = 80 | CES74 = 95 | CES99 = 62 |
| CES25 = 73 | CES50 = 87 | CES75 = 69 | |



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Measure Comparisons



(END OF REPORT)