

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P636185

Luminaire Tested: GWS-SA3F-730-U-T2R-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P636185
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA3F-730-U-T2R-W
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II ROADWAY OPTICS
Light Source: (48) 3000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 22703.2 lumens
Efficiency: N/A
Efficacy: 123.9 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G3


Input Watts (W): 183.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P636185
 CATALOG NUMBER: GWS-SA3F-730-U-T2R-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 8.9 fc
 Type II - Short - N/A

REPORT NUMBER: P636185
CATALOG NUMBER: GWS-SA3F-730-U-T2R-W

Luminous Intensity Polar Plot



— Vertical Plane Through 76-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P636185

CATALOG NUMBER: GWS-SA3F-730-U-T2R-W

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 3794.9 | 0.0 | 3794.9 |
| | % Fixture | 16.7 | 0.0 | 16.7 |
| Street Side | Lumens | 18908.3 | 0.0 | 18908.3 |
| | % Fixture | 83.3 | 0.0 | 83.3 |
| Total | Lumens | 22703.2 | 0.0 | 22703.2 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 255.4 | 1.1 |
| 10°-20° | 972.9 | 4.3 |
| 20°-30° | 1896.0 | 8.4 |
| 30°-40° | 3170.9 | 14.0 |
| 40°-50° | 4540.1 | 20.0 |
| 50°-60° | 5374.9 | 23.7 |
| 60°-70° | 4469.3 | 19.7 |
| 70°-80° | 1828.9 | 8.1 |
| 80°-90° | 194.7 | 0.9 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 22703.2 | 100.0 |
| 0°-180° | 22703.2 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P636185


CATALOG NUMBER: GWS-SA3F-730-U-T2R-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 2330.4 | 10.3 | | | |
| FM (30°-60°) | 11241.8 | 49.5 | | | |
| FH (60°-80°) | 5220.0 | 23.0 | | | G3/7500 |
| FVH (80°-90°) | 116.1 | 0.5 | | | G2/225 |
| BL (0°-30°) | 793.9 | 3.5 | B2/1000 | | |
| BM (30°-60°) | 1844.2 | 8.1 | B2/2500 | | |
| BH (60°-80°) | 1078.2 | 4.7 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 78.6 | 0.3 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G3

Type II Short





REPORT NUMBER: P636185
 CATALOG NUMBER: GWS-SA3F-730-U-T2R-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 76° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 2149.9 | 2149.9 | 2149.9 | 2149.9 | 2149.9 | 2149.9 | 2149.9 | 2149.9 | 2149.9 | 2149.9 | 2149.9 |
| 2.5° | 3013.4 | 3024.6 | 2987.8 | 2975.1 | 2888.9 | 2772.4 | 2675.0 | 2528.2 | 2392.5 | 2371.8 | 2250.5 |
| 5° | 3827.4 | 3779.5 | 3738.0 | 3710.9 | 3591.2 | 3458.7 | 3252.8 | 2976.7 | 2687.8 | 2652.7 | 2390.9 |
| 7.5° | 4311.0 | 4303.0 | 4251.9 | 4236.0 | 4143.4 | 4010.9 | 3798.7 | 3455.5 | 3035.7 | 2978.3 | 2580.8 |
| 10° | 4698.8 | 4694.0 | 4668.5 | 4682.9 | 4598.3 | 4469.0 | 4263.1 | 3908.8 | 3417.2 | 3359.7 | 2793.1 |
| 12.5° | 5037.2 | 5045.2 | 5040.4 | 5093.1 | 5050.0 | 4949.4 | 4735.5 | 4346.1 | 3798.7 | 3736.4 | 3051.7 |
| 15° | 5284.6 | 5291.0 | 5314.9 | 5429.8 | 5453.8 | 5433.0 | 5216.0 | 4775.4 | 4175.3 | 4085.9 | 3318.2 |
| 17.5° | 5354.8 | 5367.6 | 5425.0 | 5610.2 | 5739.5 | 5825.7 | 5664.5 | 5212.8 | 4545.6 | 4448.3 | 3589.6 |
| 20° | 5449.0 | 5463.4 | 5520.8 | 5713.9 | 5903.9 | 6100.2 | 6071.5 | 5656.5 | 4919.1 | 4839.3 | 3864.1 |
| 22.5° | 5884.7 | 5873.5 | 5848.0 | 5940.6 | 6076.2 | 6320.4 | 6392.3 | 6082.6 | 5305.3 | 5228.7 | 4167.3 |
| 25° | 6724.3 | 6703.5 | 6540.7 | 6456.1 | 6411.4 | 6559.9 | 6687.5 | 6470.5 | 5682.0 | 5567.1 | 4449.8 |
| 27.5° | 7650.0 | 7638.8 | 7431.3 | 7230.2 | 6955.7 | 6891.8 | 6966.9 | 6808.8 | 6047.5 | 5931.0 | 4695.6 |
| 30° | 8526.2 | 8492.7 | 8275.6 | 8023.5 | 7656.4 | 7381.8 | 7271.7 | 7140.8 | 6448.1 | 6326.8 | 4982.9 |
| 32.5° | 9309.9 | 9266.8 | 9011.4 | 8732.1 | 8347.5 | 8023.5 | 7694.7 | 7493.6 | 6901.4 | 6761.0 | 5276.6 |
| 35° | 9953.1 | 9910.0 | 9648.3 | 9351.4 | 8928.4 | 8689.0 | 8238.9 | 7876.6 | 7362.7 | 7220.6 | 5623.0 |
| 37.5° | 10451.1 | 10411.2 | 10138.2 | 9846.2 | 9477.5 | 9287.5 | 8896.5 | 8307.6 | 7894.2 | 7745.7 | 5990.1 |
| 40° | 10730.4 | 10701.7 | 10483.0 | 10251.6 | 9941.9 | 9777.5 | 9602.0 | 8851.8 | 8489.5 | 8341.1 | 6422.6 |
| 42.5° | 10815.0 | 10795.8 | 10642.6 | 10522.9 | 10313.8 | 10189.3 | 10289.9 | 9491.8 | 9124.7 | 8995.5 | 6909.4 |
| 45° | 10602.7 | 10602.7 | 10558.0 | 10618.7 | 10628.2 | 10626.6 | 10979.4 | 10214.9 | 9905.2 | 9763.2 | 7595.7 |
| 47.5° | 10060.0 | 10095.2 | 10160.6 | 10459.1 | 10773.5 | 11036.8 | 11785.4 | 11178.9 | 10909.2 | 10792.6 | 8567.7 |
| 50° | 9067.3 | 9163.0 | 9386.5 | 9969.1 | 10637.8 | 11308.2 | 12548.3 | 12604.2 | 12861.1 | 12655.3 | 9997.8 |
| 52.5° | 7613.3 | 7598.9 | 8168.7 | 8998.7 | 10018.5 | 11319.3 | 12968.1 | 13861.9 | 14553.0 | 14410.9 | 11060.8 |
| 55° | 6050.7 | 6026.8 | 6558.3 | 7702.6 | 9068.9 | 10891.6 | 13220.3 | 14438.1 | 15491.5 | 15363.8 | 12016.8 |
| 57.5° | 4633.4 | 4603.1 | 5075.5 | 6108.2 | 7728.2 | 9983.4 | 13172.4 | 15124.4 | 16782.7 | 16717.3 | 13316.0 |
| 60° | 3189.0 | 3152.2 | 3594.4 | 4497.7 | 6141.7 | 8594.8 | 12642.5 | 15477.1 | 18294.2 | 18316.5 | 14706.2 |
| 62.5° | 1915.3 | 1894.5 | 2215.3 | 2916.0 | 4417.9 | 6874.3 | 11402.3 | 15263.2 | 19497.6 | 19598.2 | 15600.0 |
| 65° | 1155.6 | 1141.2 | 1329.5 | 1739.7 | 2802.7 | 5016.5 | 9490.2 | 14169.9 | 19671.6 | 19903.0 | 15620.8 |
| 67.5° | 841.1 | 842.7 | 897.0 | 1059.8 | 1634.4 | 3240.0 | 7121.7 | 12210.0 | 18765.0 | 19004.4 | 14636.0 |
| 70° | 731.0 | 734.2 | 762.9 | 799.6 | 988.0 | 1854.6 | 4630.2 | 9638.7 | 16085.2 | 16270.4 | 12275.4 |
| 72.5° | 649.6 | 649.6 | 668.8 | 687.9 | 772.5 | 1130.0 | 2480.3 | 6737.0 | 12695.2 | 12744.6 | 9368.9 |
| 75° | 571.4 | 566.6 | 576.2 | 585.8 | 670.4 | 790.1 | 1206.6 | 4694.0 | 9376.9 | 9262.0 | 6055.5 |
| 77.5° | 454.9 | 450.1 | 451.7 | 461.3 | 537.9 | 565.0 | 611.3 | 2932.0 | 5284.6 | 4987.7 | 2675.0 |
| 80° | 324.0 | 320.8 | 338.4 | 362.3 | 397.4 | 346.3 | 383.1 | 1418.9 | 2095.6 | 1950.4 | 1037.4 |
| 82.5° | 193.1 | 199.5 | 226.6 | 245.8 | 274.5 | 217.1 | 247.4 | 474.0 | 742.2 | 723.0 | 421.4 |
| 85° | 27.1 | 28.7 | 81.4 | 94.2 | 118.1 | 84.6 | 130.9 | 213.9 | 296.9 | 317.6 | 148.4 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 11.2 | 38.3 | 84.6 | 86.2 | 36.7 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P636185
 CATALOG NUMBER: GWS-SA3F-730-U-T2R-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2149.9 | 2149.9 | 2149.9 | 2149.9 | 2149.9 | 2149.9 | 2149.9 | 2149.9 | 2149.9 | 2149.9 | 2149.9 |
| 2.5° | 2188.2 | 2113.2 | 2006.3 | 1916.9 | 1841.9 | 1781.2 | 1730.1 | 1691.8 | 1680.7 | 1664.7 | 1664.7 |
| 5° | 2268.0 | 2132.4 | 1940.8 | 1805.2 | 1727.0 | 1680.7 | 1648.7 | 1632.8 | 1624.8 | 1615.2 | 1610.4 |
| 7.5° | 2378.1 | 2188.2 | 1929.7 | 1792.4 | 1731.7 | 1703.0 | 1682.3 | 1672.7 | 1666.3 | 1656.7 | 1656.7 |
| 10° | 2529.8 | 2271.2 | 1964.8 | 1837.1 | 1789.2 | 1760.5 | 1736.5 | 1720.6 | 1706.2 | 1691.8 | 1688.6 |
| 12.5° | 2694.2 | 2379.7 | 2028.6 | 1897.7 | 1846.7 | 1811.5 | 1778.0 | 1754.1 | 1736.5 | 1719.0 | 1714.2 |
| 15° | 2876.1 | 2491.5 | 2097.2 | 1956.8 | 1892.9 | 1845.1 | 1805.2 | 1768.4 | 1744.5 | 1719.0 | 1715.8 |
| 17.5° | 3054.9 | 2604.8 | 2154.7 | 1996.7 | 1915.3 | 1856.2 | 1798.8 | 1750.9 | 1720.6 | 1691.8 | 1683.9 |
| 20° | 3268.8 | 2718.1 | 2194.6 | 2007.9 | 1910.5 | 1832.3 | 1763.7 | 1703.0 | 1669.5 | 1636.0 | 1631.2 |
| 22.5° | 3465.1 | 2823.5 | 2213.8 | 1991.9 | 1873.8 | 1781.2 | 1701.4 | 1636.0 | 1599.3 | 1565.7 | 1559.4 |
| 25° | 3655.0 | 2916.0 | 2205.8 | 1953.6 | 1817.9 | 1711.0 | 1628.0 | 1562.6 | 1527.4 | 1492.3 | 1482.8 |
| 27.5° | 3838.6 | 2978.3 | 2173.9 | 1894.5 | 1747.7 | 1632.8 | 1553.0 | 1493.9 | 1463.6 | 1433.3 | 1420.5 |
| 30° | 4018.9 | 3035.7 | 2124.4 | 1817.9 | 1658.3 | 1551.4 | 1485.9 | 1444.4 | 1414.1 | 1382.2 | 1372.6 |
| 32.5° | 4200.9 | 3077.2 | 2049.4 | 1728.5 | 1567.3 | 1479.6 | 1439.7 | 1409.3 | 1377.4 | 1345.5 | 1335.9 |
| 35° | 4384.4 | 3094.8 | 1958.4 | 1626.4 | 1490.7 | 1433.3 | 1418.9 | 1383.8 | 1340.7 | 1302.4 | 1289.6 |
| 37.5° | 4603.1 | 3110.7 | 1845.1 | 1525.8 | 1423.7 | 1410.9 | 1407.7 | 1355.1 | 1304.0 | 1251.3 | 1237.0 |
| 40° | 4866.4 | 3131.5 | 1728.5 | 1434.9 | 1369.4 | 1402.9 | 1390.2 | 1318.4 | 1216.2 | 1165.1 | 1149.2 |
| 42.5° | 5188.8 | 3169.8 | 1607.2 | 1351.9 | 1329.5 | 1372.6 | 1358.3 | 1229.0 | 1160.3 | 1131.6 | 1123.6 |
| 45° | 5662.9 | 3310.3 | 1485.9 | 1286.4 | 1299.2 | 1329.5 | 1307.2 | 1176.3 | 1149.2 | 1130.0 | 1120.4 |
| 47.5° | 6507.2 | 3525.7 | 1380.6 | 1237.0 | 1275.3 | 1291.2 | 1205.0 | 1161.9 | 1141.2 | 1115.7 | 1104.5 |
| 50° | 7385.0 | 3619.9 | 1296.0 | 1206.6 | 1248.1 | 1256.1 | 1149.2 | 1142.8 | 1128.4 | 1101.3 | 1090.1 |
| 52.5° | 7978.8 | 3607.1 | 1244.9 | 1195.5 | 1225.8 | 1195.5 | 1123.6 | 1122.0 | 1112.5 | 1080.5 | 1067.8 |
| 55° | 8649.1 | 3629.5 | 1222.6 | 1198.7 | 1216.2 | 1093.3 | 1091.7 | 1096.5 | 1091.7 | 1056.6 | 1050.2 |
| 57.5° | 9554.1 | 3698.1 | 1211.4 | 1209.8 | 1209.8 | 1043.8 | 1061.4 | 1067.8 | 1058.2 | 1042.2 | 1037.4 |
| 60° | 10423.9 | 3702.9 | 1190.7 | 1222.6 | 1205.0 | 1013.5 | 1026.3 | 1032.7 | 1021.5 | 1018.3 | 1016.7 |
| 62.5° | 10751.1 | 3473.1 | 1144.4 | 1213.0 | 1185.9 | 980.0 | 989.6 | 992.8 | 981.6 | 989.6 | 988.0 |
| 65° | 10264.3 | 2984.7 | 1067.8 | 1166.7 | 1126.8 | 949.7 | 943.3 | 951.3 | 932.1 | 952.9 | 954.5 |
| 67.5° | 9113.6 | 2371.8 | 951.3 | 1078.9 | 1043.8 | 916.1 | 903.4 | 903.4 | 871.5 | 903.4 | 901.8 |
| 70° | 7348.3 | 1675.9 | 780.5 | 938.5 | 952.9 | 876.2 | 869.9 | 833.1 | 782.1 | 830.0 | 825.2 |
| 72.5° | 5570.3 | 1203.4 | 614.5 | 742.2 | 820.4 | 820.4 | 822.0 | 759.7 | 700.7 | 723.0 | 703.9 |
| 75° | 3528.9 | 847.5 | 491.6 | 568.2 | 643.2 | 719.8 | 756.5 | 641.6 | 589.0 | 579.4 | 569.8 |
| 77.5° | 1589.7 | 557.0 | 383.1 | 435.7 | 456.5 | 568.2 | 691.1 | 552.2 | 480.4 | 459.7 | 453.3 |
| 80° | 665.6 | 346.3 | 272.9 | 308.0 | 280.9 | 477.2 | 609.7 | 429.3 | 352.7 | 324.0 | 303.3 |
| 82.5° | 292.1 | 205.9 | 174.0 | 166.0 | 175.6 | 354.3 | 454.9 | 285.7 | 220.3 | 298.5 | 301.7 |
| 85° | 122.9 | 108.5 | 89.4 | 81.4 | 71.8 | 135.7 | 213.9 | 111.7 | 137.3 | 78.2 | 63.8 |
| 87.5° | 28.7 | 31.9 | 23.9 | 16.0 | 9.6 | 1.6 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-2-R4

Test Date: 10/03/2019

Luminaire Tested: SA1C-730-U-5WQ

Data in this report applies to families of products SA1C-730-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-2-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-730-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-2-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. (1) 70 CRI, 3000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2993
 CIE u': 0.2508
 CIE v': 0.5215
 Duv: 0.0000
 CIE x: 0.4374
 CIE y: 0.4043
 CIE z: 0.1583
 Peak Wavelength (nm): 593
 Dominant Wavelength (nm): 582
 Purity: 53

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.8 | | |
| R1: | 67.5 | R9: | -38.3 |
| R2: | 82.9 | R10: | 62.5 |
| R3: | 94.7 | R11: | 63.7 |
| R4: | 67.7 | R12: | 57.8 |
| R5: | 67.9 | R13: | 70.4 |
| R6: | 77.6 | R14: | 97.3 |
| R7: | 76.0 | | |
| R8: | 40.5 | | |

Rf: 75.7
 Rg: 93.9



Test Conditions

Stabilization Time: 53M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-2-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-2-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-2-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 8494.8

S/P: 1.23

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3101.5 M/P: 0.45

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Summary

$R_f = 75.7$
 $R_g = 93.9$
 CIE $R_a = 71.8$
 $R_9 = -38.3$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 67 | CES51 = 87 | CES76 = 63 |
| CES02 = 63 | CES27 = 88 | CES52 = 86 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 78 | CES78 = 67 |
| CES04 = 71 | CES29 = 66 | CES54 = 84 | CES79 = 87 |
| CES05 = 49 | CES30 = 73 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 70 | CES56 = 75 | CES81 = 71 |
| CES07 = 41 | CES32 = 65 | CES57 = 74 | CES82 = 94 |
| CES08 = 40 | CES33 = 73 | CES58 = 76 | CES83 = 90 |
| CES09 = 29 | CES34 = 79 | CES59 = 85 | CES84 = 89 |
| CES10 = 76 | CES35 = 89 | CES60 = 93 | CES85 = 77 |
| CES11 = 59 | CES36 = 97 | CES61 = 84 | CES86 = 61 |
| CES12 = 65 | CES37 = 87 | CES62 = 91 | CES87 = 78 |
| CES13 = 43 | CES38 = 81 | CES63 = 77 | CES88 = 77 |
| CES14 = 74 | CES39 = 95 | CES64 = 72 | CES89 = 67 |
| CES15 = 71 | CES40 = 92 | CES65 = 68 | CES90 = 76 |
| CES16 = 47 | CES41 = 88 | CES66 = 69 | CES91 = 89 |
| CES17 = 50 | CES42 = 89 | CES67 = 67 | CES92 = 58 |
| CES18 = 56 | CES43 = 79 | CES68 = 72 | CES93 = 74 |
| CES19 = 73 | CES44 = 99 | CES69 = 81 | CES94 = 49 |
| CES20 = 66 | CES45 = 85 | CES70 = 66 | CES95 = 68 |
| CES21 = 87 | CES46 = 80 | CES71 = 67 | CES96 = 76 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 69 | CES73 = 59 | CES98 = 75 |
| CES24 = 91 | CES49 = 80 | CES74 = 95 | CES99 = 62 |
| CES25 = 73 | CES50 = 87 | CES75 = 69 | |



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Measure Comparisons



(END OF REPORT)