

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P638636

Luminaire Tested: GWS-SA4F-730-U-SL2-W-HSS

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P638636
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-30)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA4F-730-U-SL2-W-HSS
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II SPILL LIGHT ELIMINATOR OPTICS WITH HOUSE SIDE SHIELD
Light Source: (64) 3000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 24561 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B2 - U0 - G4


Input Watts (W): 225.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P638636
 CATALOG NUMBER: GWS-SA4F-730-U-SL2-W-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 9.5 fc
 Type II - Short - N/A

REPORT NUMBER: P638636
CATALOG NUMBER: GWS-SA4F-730-U-SL2-W-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 65-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P638636

CATALOG NUMBER: GWS-SA4F-730-U-SL2-W-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 3066.9 | 0.0 | 3066.9 |
| | % Fixture | 12.5 | 0.0 | 12.5 |
| Street Side | Lumens | 21494.1 | 0.0 | 21494.1 |
| | % Fixture | 87.5 | 0.0 | 87.5 |
| Total | Lumens | 24561.0 | 0.0 | 24561.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 494.7 | 2.0 |
| 10°-20° | 1112.2 | 4.5 |
| 20°-30° | 1589.2 | 6.5 |
| 30°-40° | 2312.1 | 9.4 |
| 40°-50° | 3621.1 | 14.7 |
| 50°-60° | 5649.1 | 23.0 |
| 60°-70° | 6205.2 | 25.3 |
| 70°-80° | 3302.4 | 13.4 |
| 80°-90° | 274.9 | 1.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 24561.0 | 100.0 |
| 0°-180° | 24561.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P638636

CATALOG NUMBER: GWS-SA4F-730-U-SL2-W-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|----------|
| | | | B | U | G |
| FL (0°-30°) | 2210.3 | 9.0 | | | |
| FM (30°-60°) | 10452.6 | 42.6 | | | |
| FH (60°-80°) | 8570.8 | 34.9 | | | G4/12000 |
| FVH (80°-90°) | 260.2 | 1.1 | | | G3/500 |
| BL (0°-30°) | 985.8 | 4.0 | B2/1000 | | |
| BM (30°-60°) | 1129.7 | 4.6 | B2/2500 | | |
| BH (60°-80°) | 936.8 | 3.8 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 14.7 | 0.1 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G4
 Type II Short





REPORT NUMBER: P638636

CATALOG NUMBER: GWS-SA4F-730-U-SL2-W-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 66° | 75° | 85° |
|-------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 5956.8 | 5956.8 | 5956.8 | 5956.8 | 5956.8 | 5956.8 | 5956.8 | 5956.8 | 5956.8 | 5956.8 | 5956.8 |
| 2.5° | 5750.3 | 5768.0 | 5743.6 | 5803.6 | 5814.7 | 5881.3 | 5919.1 | 5945.7 | 5943.5 | 5976.8 | 5976.8 |
| 5° | 5412.7 | 5430.4 | 5417.1 | 5481.5 | 5532.6 | 5637.0 | 5723.6 | 5823.6 | 5828.0 | 5930.2 | 5967.9 |
| 7.5° | 5126.1 | 5128.4 | 5128.4 | 5208.3 | 5275.0 | 5403.8 | 5532.6 | 5685.8 | 5703.6 | 5861.3 | 5961.3 |
| 10° | 4890.7 | 4897.4 | 4899.6 | 4990.7 | 5064.0 | 5219.4 | 5383.8 | 5568.1 | 5588.1 | 5801.3 | 5956.8 |
| 12.5° | 4728.6 | 4730.8 | 4739.7 | 4835.2 | 4915.2 | 5077.3 | 5243.9 | 5454.9 | 5481.5 | 5732.5 | 5936.8 |
| 15° | 4650.8 | 4646.4 | 4650.8 | 4730.8 | 4810.8 | 4966.2 | 5137.3 | 5363.8 | 5392.7 | 5674.7 | 5939.0 |
| 17.5° | 4646.4 | 4639.7 | 4635.3 | 4695.3 | 4746.4 | 4884.1 | 5057.3 | 5303.8 | 5334.9 | 5648.1 | 5963.5 |
| 20° | 4710.8 | 4706.4 | 4684.2 | 4710.8 | 4721.9 | 4835.2 | 5006.2 | 5257.2 | 5288.3 | 5643.7 | 6016.8 |
| 22.5° | 4879.6 | 4868.5 | 4835.2 | 4810.8 | 4750.8 | 4817.4 | 4970.7 | 5223.9 | 5259.4 | 5654.8 | 6085.6 |
| 25° | 5130.6 | 5126.1 | 5083.9 | 5024.0 | 4870.7 | 4844.1 | 4972.9 | 5223.9 | 5257.2 | 5668.1 | 6158.9 |
| 27.5° | 5508.2 | 5481.5 | 5428.2 | 5323.8 | 5103.9 | 4948.5 | 5017.3 | 5237.2 | 5270.5 | 5685.8 | 6218.9 |
| 30° | 5892.4 | 5890.2 | 5872.4 | 5765.8 | 5439.3 | 5148.4 | 5110.6 | 5272.7 | 5303.8 | 5701.4 | 6274.4 |
| 32.5° | 6290.0 | 6296.6 | 6341.1 | 6258.9 | 5901.3 | 5446.0 | 5279.4 | 5346.0 | 5368.2 | 5732.5 | 6323.3 |
| 35° | 6667.5 | 6680.9 | 6798.6 | 6827.5 | 6463.2 | 5896.8 | 5554.8 | 5492.6 | 5494.8 | 5801.3 | 6387.7 |
| 37.5° | 7029.6 | 7074.0 | 7262.8 | 7402.7 | 7162.8 | 6443.2 | 5952.4 | 5741.4 | 5723.6 | 5939.0 | 6485.4 |
| 40° | 7440.5 | 7524.9 | 7762.5 | 8000.2 | 7924.7 | 7165.1 | 6494.3 | 6123.4 | 6085.6 | 6192.2 | 6660.9 |
| 42.5° | 7895.8 | 7986.8 | 8302.2 | 8635.4 | 8670.9 | 8037.9 | 7171.7 | 6680.9 | 6616.5 | 6618.7 | 6989.6 |
| 45° | 8384.4 | 8506.6 | 8873.0 | 9352.8 | 9568.2 | 9010.7 | 8006.8 | 7433.8 | 7369.4 | 7273.9 | 7518.2 |
| 47.5° | 9026.3 | 9132.9 | 9486.0 | 10039.1 | 10452.2 | 10054.6 | 9101.8 | 8402.2 | 8284.5 | 8144.5 | 8340.0 |
| 50° | 9579.3 | 9672.6 | 9976.9 | 10669.9 | 11529.4 | 11400.6 | 10343.4 | 9612.6 | 9499.4 | 9261.7 | 9423.9 |
| 52.5° | 9701.5 | 9774.8 | 10054.6 | 10834.2 | 12353.4 | 13099.7 | 11864.8 | 11076.3 | 10996.3 | 10556.6 | 10618.8 |
| 55° | 9152.9 | 9263.9 | 9514.9 | 10381.1 | 12568.8 | 14761.0 | 13839.3 | 12726.5 | 12560.0 | 11858.1 | 11969.2 |
| 57.5° | 7767.0 | 7964.6 | 8200.1 | 9326.1 | 11984.7 | 15645.0 | 16597.8 | 14474.5 | 14323.5 | 13110.8 | 13113.0 |
| 60° | 5692.5 | 5852.4 | 6010.1 | 7040.7 | 10598.8 | 15585.0 | 19100.9 | 16437.9 | 16162.5 | 14134.7 | 14096.9 |
| 62.5° | 4140.0 | 4222.2 | 4220.0 | 4586.4 | 7278.3 | 14558.9 | 20415.8 | 19396.3 | 18754.4 | 15229.6 | 15014.2 |
| 65° | 3256.0 | 3253.8 | 3349.3 | 3469.3 | 4064.5 | 11238.4 | 20577.9 | 23716.2 | 23023.3 | 16697.7 | 16249.1 |
| 67.5° | 2534.2 | 2583.1 | 2678.6 | 3031.7 | 3053.9 | 5881.3 | 19152.0 | 26388.1 | 26374.8 | 18938.8 | 17695.0 |
| 70° | 1954.5 | 2021.1 | 2156.6 | 2671.9 | 2820.7 | 3291.6 | 14330.1 | 25541.9 | 25757.3 | 19940.5 | 16671.1 |
| 72.5° | 1254.9 | 1250.4 | 1450.3 | 2158.8 | 2709.7 | 2743.0 | 7924.7 | 20289.2 | 20533.5 | 18061.5 | 13479.5 |
| 75° | 701.8 | 706.3 | 819.6 | 1321.5 | 2525.3 | 2580.8 | 3924.6 | 14467.8 | 14661.1 | 14081.4 | 10356.7 |
| 77.5° | 275.4 | 284.3 | 384.2 | 695.2 | 1665.8 | 2305.4 | 2332.1 | 9865.8 | 9894.7 | 8726.4 | 6352.2 |
| 80° | 111.1 | 117.7 | 195.5 | 430.9 | 1015.0 | 1552.5 | 1665.8 | 5812.4 | 5694.7 | 3378.2 | 1847.9 |
| 82.5° | 33.3 | 35.5 | 77.7 | 244.3 | 530.8 | 1103.9 | 1123.8 | 2229.9 | 2105.5 | 726.3 | 470.9 |
| 85° | 2.2 | 2.2 | 17.8 | 75.5 | 188.8 | 277.6 | 748.5 | 726.3 | 644.1 | 182.1 | 208.8 |
| 87.5° | 0.0 | 0.0 | 2.2 | 2.2 | 4.4 | 8.9 | 80.0 | 133.3 | 135.5 | 33.3 | 93.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P638636

CATALOG NUMBER: GWS-SA4F-730-U-SL2-W-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 5956.8 | 5956.8 | 5956.8 | 5956.8 | 5956.8 | 5956.8 | 5956.8 | 5956.8 | 5956.8 | 5956.8 | 5956.8 |
| 2.5° | 5976.8 | 5896.8 | 5890.2 | 5828.0 | 5765.8 | 5688.1 | 5597.0 | 5530.4 | 5483.7 | 5401.6 | 5386.0 |
| 5° | 5967.9 | 5861.3 | 5761.4 | 5583.7 | 5386.0 | 5172.8 | 4986.2 | 4813.0 | 4704.2 | 4630.9 | 4599.8 |
| 7.5° | 5950.2 | 5814.7 | 5583.7 | 5248.3 | 4917.4 | 4544.2 | 4253.3 | 3986.8 | 3804.6 | 3698.0 | 3651.4 |
| 10° | 5936.8 | 5754.7 | 5379.3 | 4870.7 | 4357.7 | 3842.4 | 3400.4 | 3005.1 | 2785.2 | 2611.9 | 2583.1 |
| 12.5° | 5910.2 | 5668.1 | 5117.3 | 4428.7 | 3766.9 | 3082.8 | 2518.7 | 2034.5 | 1699.1 | 1548.1 | 1494.8 |
| 15° | 5883.5 | 5577.0 | 4855.2 | 3962.3 | 3122.8 | 2278.8 | 1594.7 | 1128.3 | 897.3 | 826.2 | 821.8 |
| 17.5° | 5879.1 | 5494.8 | 4570.9 | 3520.3 | 2447.6 | 1492.5 | 908.4 | 730.7 | 681.9 | 664.1 | 664.1 |
| 20° | 5892.4 | 5426.0 | 4291.0 | 3011.7 | 1783.5 | 908.4 | 677.4 | 633.0 | 604.1 | 588.6 | 588.6 |
| 22.5° | 5905.7 | 5354.9 | 4022.3 | 2498.7 | 1183.8 | 664.1 | 597.5 | 559.7 | 526.4 | 508.6 | 499.7 |
| 25° | 5914.6 | 5277.2 | 3724.7 | 1983.4 | 772.9 | 577.5 | 524.2 | 475.3 | 435.3 | 413.1 | 413.1 |
| 27.5° | 5912.4 | 5183.9 | 3424.8 | 1479.2 | 599.7 | 513.1 | 448.6 | 397.6 | 357.6 | 333.2 | 335.4 |
| 30° | 5894.6 | 5081.7 | 3113.9 | 1032.8 | 524.2 | 448.6 | 384.2 | 330.9 | 291.0 | 271.0 | 268.7 |
| 32.5° | 5881.3 | 4972.9 | 2754.1 | 726.3 | 470.9 | 393.1 | 326.5 | 275.4 | 242.1 | 226.5 | 224.3 |
| 35° | 5865.8 | 4866.3 | 2412.0 | 553.0 | 424.2 | 339.8 | 275.4 | 233.2 | 206.6 | 193.2 | 193.2 |
| 37.5° | 5870.2 | 4755.2 | 2041.1 | 475.3 | 377.6 | 295.4 | 235.4 | 199.9 | 177.7 | 164.4 | 162.1 |
| 40° | 5939.0 | 4688.6 | 1676.9 | 430.9 | 335.4 | 255.4 | 204.3 | 173.2 | 151.0 | 137.7 | 135.5 |
| 42.5° | 6110.1 | 4690.8 | 1328.2 | 397.6 | 297.6 | 217.7 | 177.7 | 148.8 | 128.8 | 113.3 | 111.1 |
| 45° | 6452.1 | 4784.1 | 1019.5 | 362.0 | 257.6 | 188.8 | 153.3 | 126.6 | 106.6 | 93.3 | 91.1 |
| 47.5° | 7011.8 | 5061.7 | 772.9 | 330.9 | 224.3 | 164.4 | 131.0 | 106.6 | 88.8 | 77.7 | 75.5 |
| 50° | 7902.4 | 5563.7 | 608.6 | 293.2 | 188.8 | 142.1 | 111.1 | 88.8 | 73.3 | 62.2 | 60.0 |
| 52.5° | 8973.0 | 6316.6 | 521.9 | 259.9 | 162.1 | 124.4 | 95.5 | 73.3 | 60.0 | 51.1 | 48.9 |
| 55° | 10203.4 | 7216.1 | 482.0 | 226.5 | 137.7 | 106.6 | 77.7 | 60.0 | 48.9 | 42.2 | 37.8 |
| 57.5° | 11331.7 | 8026.8 | 479.7 | 193.2 | 117.7 | 91.1 | 64.4 | 51.1 | 42.2 | 33.3 | 31.1 |
| 60° | 12431.1 | 8704.2 | 450.9 | 159.9 | 102.2 | 75.5 | 55.5 | 42.2 | 35.5 | 28.9 | 26.7 |
| 62.5° | 13428.4 | 9255.1 | 377.6 | 128.8 | 86.6 | 62.2 | 46.6 | 37.8 | 31.1 | 24.4 | 24.4 |
| 65° | 14681.0 | 9956.9 | 288.7 | 104.4 | 71.1 | 51.1 | 40.0 | 33.3 | 28.9 | 22.2 | 22.2 |
| 67.5° | 15975.9 | 10327.8 | 206.6 | 86.6 | 57.7 | 44.4 | 35.5 | 31.1 | 24.4 | 20.0 | 20.0 |
| 70° | 14470.0 | 8726.4 | 148.8 | 71.1 | 48.9 | 37.8 | 31.1 | 28.9 | 24.4 | 20.0 | 17.8 |
| 72.5° | 11300.6 | 6292.2 | 111.1 | 55.5 | 42.2 | 35.5 | 28.9 | 26.7 | 22.2 | 17.8 | 17.8 |
| 75° | 8380.0 | 3669.2 | 84.4 | 44.4 | 33.3 | 28.9 | 28.9 | 26.7 | 22.2 | 17.8 | 15.5 |
| 77.5° | 4555.3 | 1279.3 | 64.4 | 35.5 | 26.7 | 22.2 | 24.4 | 24.4 | 20.0 | 15.5 | 13.3 |
| 80° | 1206.0 | 350.9 | 44.4 | 26.7 | 22.2 | 17.8 | 17.8 | 22.2 | 17.8 | 13.3 | 13.3 |
| 82.5° | 350.9 | 102.2 | 31.1 | 22.2 | 17.8 | 15.5 | 15.5 | 15.5 | 13.3 | 11.1 | 8.9 |
| 85° | 171.0 | 37.8 | 22.2 | 17.8 | 15.5 | 13.3 | 11.1 | 11.1 | 8.9 | 6.7 | 6.7 |
| 87.5° | 75.5 | 15.5 | 17.8 | 15.5 | 15.5 | 11.1 | 8.9 | 6.7 | 6.7 | 4.4 | 2.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-2-R4

Test Date: 10/03/2019

Luminaire Tested: SA1C-730-U-5WQ

Data in this report applies to families of products SA1C-730-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-2-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-730-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-2-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. (1) 70 CRI, 3000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 2993 | CRI (Ra): | 71.8 | R9: | -38.3 |
| CIE u': | 0.2508 | R1: | 67.5 | R10: | 62.5 |
| CIE v': | 0.5215 | R2: | 82.9 | R11: | 63.7 |
| Duv: | 0.0000 | R3: | 94.7 | R12: | 57.8 |
| CIE x: | 0.4374 | R4: | 67.7 | R13: | 70.4 |
| CIE y: | 0.4043 | R5: | 67.9 | R14: | 97.3 |
| CIE z: | 0.1583 | R6: | 77.6 | | |
| Peak Wavelength (nm): | 593 | R7: | 76.0 | | |
| Dominant Wavelength (nm): | 582 | R8: | 40.5 | | |
| Purity: | 53 | | | | |
| Rf: | 75.7 | | | | |
| Rg: | 93.9 | | | | |



Test Conditions

Stabilization Time: 53M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-2-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-2-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-2-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 8494.8

S/P: 1.23

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3101.5 M/P: 0.45

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Summary

$R_f = 75.7$
 $R_g = 93.9$
 CIE $R_a = 71.8$
 $R_9 = -38.3$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 67 | CES51 = 87 | CES76 = 63 |
| CES02 = 63 | CES27 = 88 | CES52 = 86 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 78 | CES78 = 67 |
| CES04 = 71 | CES29 = 66 | CES54 = 84 | CES79 = 87 |
| CES05 = 49 | CES30 = 73 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 70 | CES56 = 75 | CES81 = 71 |
| CES07 = 41 | CES32 = 65 | CES57 = 74 | CES82 = 94 |
| CES08 = 40 | CES33 = 73 | CES58 = 76 | CES83 = 90 |
| CES09 = 29 | CES34 = 79 | CES59 = 85 | CES84 = 89 |
| CES10 = 76 | CES35 = 89 | CES60 = 93 | CES85 = 77 |
| CES11 = 59 | CES36 = 97 | CES61 = 84 | CES86 = 61 |
| CES12 = 65 | CES37 = 87 | CES62 = 91 | CES87 = 78 |
| CES13 = 43 | CES38 = 81 | CES63 = 77 | CES88 = 77 |
| CES14 = 74 | CES39 = 95 | CES64 = 72 | CES89 = 67 |
| CES15 = 71 | CES40 = 92 | CES65 = 68 | CES90 = 76 |
| CES16 = 47 | CES41 = 88 | CES66 = 69 | CES91 = 89 |
| CES17 = 50 | CES42 = 89 | CES67 = 67 | CES92 = 58 |
| CES18 = 56 | CES43 = 79 | CES68 = 72 | CES93 = 74 |
| CES19 = 73 | CES44 = 99 | CES69 = 81 | CES94 = 49 |
| CES20 = 66 | CES45 = 85 | CES70 = 66 | CES95 = 68 |
| CES21 = 87 | CES46 = 80 | CES71 = 67 | CES96 = 76 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 69 | CES73 = 59 | CES98 = 75 |
| CES24 = 91 | CES49 = 80 | CES74 = 95 | CES99 = 62 |
| CES25 = 73 | CES50 = 87 | CES75 = 69 | |



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Measure Comparisons



(END OF REPORT)