

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P833681

Luminaire Tested: **TTN-D2-830-U-MQ-CG-UPL2**

Issue Date: 5/15/2024

Test Information

Test Method: LM-79-08
Report Number: P833681
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND
Test Lab: INNOVATION CENTER
Issue Date: 5/15/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: TTN-D2-830-U-MQ-CG-UPL2
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT
3000K, 80 CRI LEDS AND MEDIUM DISTRIBUTION WITH CLEAR GLASS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5337.7 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')
IES Classification: Type V - Short
BUG Rating: B2 - U4 - G1


Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P833681
 CATALOG NUMBER: TTN-D2-830-U-MQ-CG-UPL2

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.8 fc
 Type V - Short - N/A

REPORT NUMBER: P833681
CATALOG NUMBER: TTN-D2-830-U-MQ-CG-UPL2

Luminous Intensity Polar Plot



REPORT NUMBER: P833681
 CATALOG NUMBER: TTN-D2-830-U-MQ-CG-UPL2


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2401.8	267.0	2668.8
	% Fixture	45.0	5.0	50.0
Street Side	Lumens	2401.8	267.0	2668.8
	% Fixture	45.0	5.0	50.0
Total	Lumens	4803.6	534.0	5337.7
	% Fixture	90.0	10.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.3	2.0
10°-20°	310.4	5.8
20°-30°	499.3	9.4
30°-40°	667.1	12.5
40°-50°	810.5	15.2
50°-60°	941.7	17.6
60°-70°	868.8	16.3
70°-80°	508.6	9.5
80°-90°	89.8	1.7
90°-100°	11.9	0.2
100°-110°	121.1	2.3
110°-120°	177.1	3.3
120°-130°	102.8	1.9
130°-140°	54.4	1.0
140°-150°	32.3	0.6
150°-160°	19.9	0.4
160°-170°	10.9	0.2
170°-180°	3.5	0.1
0°-90°	4803.6	90.0
0°-180°	5337.7	100.0

Coefficient of Utilization



REPORT NUMBER: P833681


CATALOG NUMBER: TTN-D2-830-U-MQ-CG-UPL2

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	458.5	8.6			
FM (30°-60°)	1209.6	22.7			
FH (60°-80°)	688.7	12.9			G1/1800
FVH (80°-90°)	44.9	0.8			G1/100
BL (0°-30°)	458.5	8.6	B1/500		
BM (30°-60°)	1209.6	22.7	B2/2500		
BH (60°-80°)	688.7	12.9	B2/1000		G1/1800
BVH (80°-90°)	44.9	0.8			G1/100
UL (90°-100°)	11.9	0.2		U2/50	
UH (100°-180°)	522.1	9.8		U4/1000	

BUG Rating: B2-U4-G1

Type V Short





REPORT NUMBER: P833681

CATALOG NUMBER: TTN-D2-830-U-MQ-CG-UPL2

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6
2.5°	1130.9	1134.8	1130.9	1130.9	1130.9	1130.9	1130.9	1130.9	1130.9	1130.9	1134.8
5°	1134.8	1134.8	1134.8	1134.8	1130.9	1130.9	1130.9	1130.9	1130.9	1134.8	1134.8
7.5°	1123.1	1123.1	1123.1	1123.1	1123.1	1119.2	1123.1	1123.1	1123.1	1123.1	1123.1
10°	1111.4	1111.4	1111.4	1111.4	1111.4	1111.4	1111.4	1111.4	1111.4	1111.4	1111.4
12.5°	1103.6	1103.6	1103.6	1103.6	1103.6	1103.6	1103.6	1103.6	1103.6	1099.7	1099.7
15°	1095.8	1095.8	1095.8	1095.8	1099.7	1099.7	1095.8	1095.8	1095.8	1095.8	1095.8
17.5°	1088.0	1088.0	1088.0	1088.0	1091.9	1091.9	1091.9	1088.0	1088.0	1088.0	1088.0
20°	1080.2	1080.2	1080.2	1080.2	1084.1	1084.1	1084.1	1084.1	1084.1	1080.2	1080.2
22.5°	1076.3	1076.3	1076.3	1076.3	1080.2	1080.2	1080.2	1080.2	1076.3	1076.3	1076.3
25°	1072.4	1076.3	1076.3	1076.3	1080.2	1084.1	1084.1	1080.2	1076.3	1072.4	1072.4
27.5°	1076.3	1076.3	1076.3	1080.2	1080.2	1084.1	1084.1	1080.2	1076.3	1076.3	1076.3
30°	1072.4	1072.4	1072.4	1076.3	1080.2	1084.1	1080.2	1080.2	1076.3	1072.4	1072.4
32.5°	1064.6	1064.6	1068.5	1072.4	1076.3	1076.3	1076.3	1072.4	1068.5	1064.6	1064.6
35°	1056.8	1056.8	1056.8	1060.7	1068.5	1068.5	1068.5	1064.6	1060.7	1056.8	1052.9
37.5°	1045.1	1049.0	1049.0	1056.8	1060.7	1064.6	1060.7	1056.8	1049.0	1045.1	1045.1
40°	1037.3	1037.3	1041.2	1049.0	1056.8	1056.8	1052.9	1049.0	1041.2	1037.3	1037.3
42.5°	1025.6	1025.6	1033.4	1041.2	1052.9	1052.9	1049.0	1041.2	1033.4	1025.6	1025.6
45°	1025.6	1025.6	1033.4	1049.0	1056.8	1064.6	1056.8	1049.0	1033.4	1025.6	1021.7
47.5°	1029.5	1029.5	1037.3	1056.8	1072.4	1080.2	1068.5	1052.9	1037.3	1029.5	1025.6
50°	1021.7	1025.6	1041.2	1060.7	1080.2	1084.1	1080.2	1056.8	1041.2	1021.7	1021.7
52.5°	1025.6	1025.6	1045.1	1076.3	1095.8	1103.6	1095.8	1076.3	1041.2	1021.7	1021.7
55°	1017.8	1013.9	1041.2	1076.3	1107.5	1123.1	1107.5	1076.3	1037.3	1013.9	1010.0
57.5°	982.7	982.7	1017.8	1052.9	1091.9	1099.7	1088.0	1052.9	1013.9	982.7	974.9
60°	935.9	939.8	974.9	1013.9	1049.0	1052.9	1045.1	1013.9	974.9	939.8	928.1
62.5°	885.2	893.0	928.1	967.1	1010.0	1017.8	1006.1	967.1	920.3	896.9	877.4
65°	811.1	822.8	861.8	904.7	951.5	947.6	947.6	900.8	865.7	826.7	807.2
67.5°	729.3	741.0	768.2	826.7	865.7	861.8	857.9	826.7	768.2	741.0	729.3
70°	639.6	647.4	674.7	733.2	768.2	772.1	760.4	729.3	674.7	655.2	635.7
72.5°	534.3	538.2	577.2	624.0	659.1	655.2	651.3	624.0	573.3	553.8	530.4
75°	421.2	425.1	460.2	503.1	530.4	526.5	522.6	503.1	460.2	436.8	417.3
77.5°	315.9	312.0	347.1	378.3	393.9	397.8	390.0	374.4	343.2	323.7	312.0
80°	206.7	202.8	234.0	257.4	269.1	269.1	265.2	253.5	230.1	214.5	206.7
82.5°	117.0	113.1	132.6	148.2	159.9	156.0	152.1	144.3	132.6	120.9	113.1
85°	42.9	42.9	54.6	62.4	70.2	70.2	66.3	62.4	50.7	46.8	42.9
87.5°	3.9	3.9	7.8	11.7	11.7	11.7	7.8	7.8	3.9	3.9	3.9
90°	4.6	4.6	5.5	5.5	5.5	5.5	5.5	5.5	5.5	4.6	4.6
92.5°	4.6	4.6	4.6	6.4	7.3	6.4	7.3	5.5	5.5	4.6	4.6
95°	5.5	5.5	6.4	8.2	10.1	11.0	11.0	6.4	6.4	5.5	5.5
97.5°	7.3	8.2	8.2	10.1	16.4	30.2	18.3	9.1	9.1	8.2	7.3
100°	11.9	12.8	12.8	22.8	48.4	64.9	46.6	23.8	17.4	12.8	12.8
102.5°	38.4	40.2	49.3	74.0	109.6	99.6	84.1	79.5	54.8	43.9	42.0
105°	97.8	96.8	104.2	123.3	153.5	150.8	138.9	126.1	108.7	100.5	100.5
107.5°	128.8	128.8	135.2	151.7	174.5	203.7	206.5	163.5	143.4	134.3	133.4
110°	145.3	145.3	150.8	164.5	194.6	235.7	233.9	201.9	177.3	165.4	163.5



REPORT NUMBER: P833681

CATALOG NUMBER: TTN-D2-830-U-MQ-CG-UPL2

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	148.9	149.8	157.1	178.2	211.1	229.3	221.1	208.3	197.4	188.2	186.4
115°	154.4	154.4	162.6	182.7	201.0	208.3	199.2	189.1	181.8	178.2	180.0
117.5°	152.6	155.3	157.1	168.1	180.0	185.5	180.9	167.2	161.7	159.9	157.1
120°	141.6	141.6	143.4	148.9	155.3	158.1	156.2	147.1	142.5	141.6	139.8
122.5°	126.1	127.0	126.1	128.8	133.4	136.1	134.3	127.0	125.2	125.2	123.3
125°	110.6	110.6	109.6	111.5	114.2	113.3	114.2	110.6	109.6	109.6	108.7
127.5°	99.6	98.7	96.8	97.8	98.7	98.7	99.6	95.9	96.8	97.8	96.8
130°	88.6	88.6	86.8	86.8	86.8	85.0	86.8	85.0	85.9	86.8	87.7
132.5°	78.6	78.6	75.8	74.9	74.9	74.9	75.8	74.9	76.7	78.6	78.6
135°	70.4	70.4	67.6	68.5	68.5	67.6	68.5	67.6	69.4	70.4	70.4
137.5°	64.0	64.0	62.1	62.1	62.1	61.2	62.1	62.1	63.0	64.9	65.8
140°	58.5	58.5	57.6	57.6	56.6	57.6	57.6	57.6	58.5	59.4	59.4
142.5°	55.7	54.8	53.9	53.0	53.9	53.9	53.9	53.0	53.9	55.7	55.7
145°	51.2	51.2	50.3	50.3	50.3	51.2	50.3	50.3	51.2	51.2	52.1
147.5°	48.4	48.4	47.5	48.4	48.4	48.4	48.4	47.5	48.4	48.4	49.3
150°	47.5	46.6	45.7	46.6	46.6	45.7	45.7	45.7	45.7	46.6	46.6
152.5°	44.8	44.8	43.9	44.8	43.9	43.9	43.9	43.9	43.9	44.8	45.7
155°	42.9	42.9	42.0	42.9	42.9	42.9	42.9	42.9	42.9	42.9	42.9
157.5°	41.1	42.0	41.1	41.1	41.1	41.1	41.1	41.1	41.1	42.0	42.0
160°	40.2	40.2	40.2	40.2	39.3	39.3	39.3	40.2	40.2	40.2	41.1
162.5°	39.3	39.3	39.3	39.3	38.4	38.4	38.4	38.4	39.3	39.3	40.2
165°	39.3	38.4	38.4	38.4	37.5	37.5	37.5	37.5	38.4	39.3	38.4
167.5°	37.5	37.5	37.5	37.5	37.5	36.5	36.5	37.5	37.5	37.5	38.4
170°	37.5	37.5	36.5	36.5	36.5	36.5	36.5	36.5	36.5	36.5	37.5
172.5°	37.5	37.5	37.5	37.5	36.5	36.5	36.5	36.5	36.5	37.5	37.5
175°	37.5	37.5	37.5	37.5	36.5	36.5	36.5	37.5	37.5	37.5	36.5
177.5°	37.5	37.5	37.5	37.5	36.5	37.5	37.5	37.5	37.5	37.5	37.5
180°	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5

(END OF REPORT)