

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P638650

Luminaire Tested: GWS-SA4F-730-U-SLR-W-HSS

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P638650
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA4F-730-U-SLR-W-HSS
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND
SPILL LIGHT ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD
Light Source: (64) 3000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 19228.1 lumens
Efficiency: N/A
Efficacy: 85.3 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B2 - U0 - G4


Input Watts (W): 225.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P638650
 CATALOG NUMBER: GWS-SA4F-730-U-SLR-W-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 6.2 fc
 Type IV - Short - N/A

REPORT NUMBER: P638650
CATALOG NUMBER: GWS-SA4F-730-U-SLR-W-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P638650
 CATALOG NUMBER: GWS-SA4F-730-U-SLR-W-HSS

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 2372.7 | 0.0 | 2372.7 |
| | % Fixture | 12.3 | 0.0 | 12.3 |
| Street Side | Lumens | 16855.4 | 0.0 | 16855.4 |
| | % Fixture | 87.7 | 0.0 | 87.7 |
| Total | Lumens | 19228.1 | 0.0 | 19228.1 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 88.7 | 0.5 |
| 10°-20° | 335.2 | 1.7 |
| 20°-30° | 728.7 | 3.8 |
| 30°-40° | 1196.1 | 6.2 |
| 40°-50° | 2198.9 | 11.4 |
| 50°-60° | 4722.1 | 24.6 |
| 60°-70° | 6342.6 | 33.0 |
| 70°-80° | 3302.6 | 17.2 |
| 80°-90° | 313.1 | 1.6 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 19228.1 | 100.0 |
| 0°-180° | 19228.1 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P638650


CATALOG NUMBER: GWS-SA4F-730-U-SLR-W-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|----------|
| | | | B | U | G |
| FL (0°-30°) | 812.3 | 4.2 | | | |
| FM (30°-60°) | 6748.8 | 35.1 | | | |
| FH (60°-80°) | 8995.1 | 46.8 | | | G4/12000 |
| FVH (80°-90°) | 299.2 | 1.6 | | | G3/500 |
| BL (0°-30°) | 340.3 | 1.8 | B1/500 | | |
| BM (30°-60°) | 1368.3 | 7.1 | B2/2500 | | |
| BH (60°-80°) | 650.1 | 3.4 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 14.0 | 0.1 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G4

Type IV Short





REPORT NUMBER: P638650

CATALOG NUMBER: GWS-SA4F-730-U-SLR-W-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 |
| 2.5° | 1019.4 | 1023.9 | 1028.3 | 1043.9 | 1055.0 | 1063.9 | 1066.1 | 1059.4 | 1043.9 | 1028.3 | 1006.1 |
| 5° | 988.4 | 992.8 | 1008.3 | 1050.5 | 1092.7 | 1126.1 | 1137.2 | 1130.5 | 1092.7 | 1043.9 | 992.8 |
| 7.5° | 986.1 | 995.0 | 1032.8 | 1121.6 | 1212.7 | 1281.5 | 1299.3 | 1283.7 | 1212.7 | 1115.0 | 1010.6 |
| 10° | 1066.1 | 1081.6 | 1137.2 | 1297.1 | 1463.7 | 1585.8 | 1634.7 | 1568.0 | 1454.8 | 1277.1 | 1106.1 |
| 12.5° | 1274.9 | 1301.5 | 1408.1 | 1641.3 | 1899.0 | 2061.1 | 2127.7 | 2045.6 | 1867.9 | 1610.2 | 1339.3 |
| 15° | 1603.6 | 1643.6 | 1803.5 | 2152.2 | 2456.4 | 2600.8 | 2623.0 | 2576.4 | 2369.8 | 2085.5 | 1721.3 |
| 17.5° | 2067.8 | 2125.5 | 2374.3 | 2729.6 | 2949.5 | 3000.6 | 2993.9 | 2945.1 | 2794.0 | 2598.6 | 2254.3 |
| 20° | 2623.0 | 2691.9 | 2936.2 | 3229.4 | 3251.6 | 3191.6 | 3158.3 | 3129.4 | 3078.3 | 3045.0 | 2776.3 |
| 22.5° | 3182.7 | 3267.1 | 3522.5 | 3595.8 | 3395.9 | 3222.7 | 3140.5 | 3162.7 | 3238.2 | 3402.6 | 3293.8 |
| 25° | 3740.2 | 3820.2 | 4060.0 | 3862.4 | 3462.6 | 3173.8 | 3069.4 | 3122.8 | 3302.7 | 3658.0 | 3797.9 |
| 27.5° | 4391.0 | 4450.9 | 4593.1 | 4044.5 | 3473.7 | 3133.9 | 3031.7 | 3113.9 | 3333.8 | 3817.9 | 4351.0 |
| 30° | 5068.4 | 5103.9 | 5035.1 | 4093.3 | 3435.9 | 3073.9 | 2993.9 | 3113.9 | 3387.1 | 3924.5 | 4766.3 |
| 32.5° | 5565.9 | 5572.5 | 5348.2 | 4097.8 | 3415.9 | 3025.0 | 2958.4 | 3100.5 | 3438.1 | 4013.4 | 5168.3 |
| 35° | 6078.9 | 6045.6 | 5648.1 | 4164.4 | 3469.2 | 3042.8 | 2985.1 | 3138.3 | 3518.1 | 4117.8 | 5521.5 |
| 37.5° | 6598.6 | 6538.7 | 5983.4 | 4273.2 | 3606.9 | 3236.0 | 3200.5 | 3331.5 | 3646.9 | 4262.1 | 5910.1 |
| 40° | 7131.7 | 7049.5 | 6332.1 | 4437.6 | 3913.4 | 3893.4 | 4015.6 | 4000.1 | 4000.1 | 4446.5 | 6309.9 |
| 42.5° | 7782.5 | 7686.9 | 6847.4 | 4901.8 | 4628.6 | 5075.0 | 5408.2 | 5201.6 | 4819.6 | 4870.7 | 6829.6 |
| 45° | 8642.0 | 8559.8 | 7740.3 | 5790.2 | 5750.2 | 6776.3 | 7225.0 | 6816.3 | 5865.7 | 5850.2 | 7698.1 |
| 47.5° | 10016.8 | 10001.3 | 9163.9 | 6820.8 | 7122.8 | 8941.8 | 9808.0 | 9021.8 | 7058.4 | 6887.4 | 9341.6 |
| 50° | 11949.1 | 11902.4 | 10938.5 | 8029.0 | 8755.3 | 11624.8 | 13170.6 | 11860.2 | 8499.8 | 8097.8 | 11542.6 |
| 52.5° | 14125.7 | 14174.5 | 13423.8 | 9348.3 | 10489.9 | 14609.9 | 16762.0 | 15111.8 | 10065.7 | 9637.0 | 14312.2 |
| 55° | 16175.7 | 16455.5 | 16257.9 | 10891.9 | 12184.5 | 17905.9 | 20706.6 | 18678.8 | 12004.6 | 11651.5 | 17417.2 |
| 57.5° | 17779.3 | 18567.7 | 19953.6 | 13135.1 | 14176.8 | 21761.5 | 25110.8 | 22545.6 | 14267.8 | 14923.0 | 21643.8 |
| 60° | 17868.1 | 18912.0 | 22130.2 | 17828.1 | 16739.8 | 25068.6 | 29508.5 | 26323.5 | 17825.9 | 20477.8 | 24955.4 |
| 62.5° | 16528.8 | 17648.2 | 20713.2 | 19960.3 | 19531.6 | 27882.7 | 31765.0 | 29077.6 | 21326.2 | 23731.6 | 23973.7 |
| 65° | 14996.3 | 16126.8 | 19131.9 | 17541.6 | 19207.4 | 27762.7 | 31192.0 | 29142.0 | 21643.8 | 21519.5 | 22216.9 |
| 67.5° | 12679.8 | 13694.8 | 16415.6 | 15527.1 | 17703.7 | 26423.5 | 28544.5 | 27305.2 | 19940.3 | 20126.9 | 20437.8 |
| 70° | 9255.0 | 10232.2 | 12757.5 | 12802.0 | 15460.5 | 24009.2 | 24526.7 | 24355.7 | 18363.4 | 18561.1 | 17672.7 |
| 72.5° | 6685.3 | 7509.3 | 9688.1 | 10498.8 | 12342.2 | 20133.5 | 19776.0 | 20435.6 | 15755.9 | 16531.0 | 14194.5 |
| 75° | 4806.3 | 5423.7 | 7107.3 | 9132.8 | 9783.6 | 14951.9 | 14156.8 | 15827.0 | 12642.0 | 14234.5 | 10672.0 |
| 77.5° | 1950.1 | 2167.7 | 2796.3 | 6152.2 | 6429.9 | 10059.0 | 8666.4 | 11496.0 | 9012.9 | 9352.7 | 5172.8 |
| 80° | 80.0 | 88.8 | 115.5 | 3176.1 | 4408.7 | 5659.2 | 4637.5 | 6145.6 | 5952.3 | 3766.8 | 1221.6 |
| 82.5° | 8.9 | 8.9 | 20.0 | 915.1 | 1930.1 | 3122.8 | 2185.5 | 3540.3 | 3013.9 | 1596.9 | 555.3 |
| 85° | 2.2 | 2.2 | 4.4 | 104.4 | 453.1 | 499.7 | 295.4 | 1086.1 | 1401.5 | 653.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 11.1 | 20.0 | 22.2 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P638650

CATALOG NUMBER: GWS-SA4F-730-U-SLR-W-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|---------|--------|--------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 |
| 2.5° | 1006.1 | 995.0 | 981.7 | 968.4 | 961.7 | 943.9 | 937.3 | 932.8 | 928.4 | 930.6 | 930.6 |
| 5° | 972.8 | 948.4 | 919.5 | 890.6 | 875.1 | 857.3 | 848.4 | 844.0 | 846.2 | 855.1 | 855.1 |
| 7.5° | 968.4 | 921.7 | 859.5 | 821.8 | 804.0 | 790.7 | 781.8 | 777.4 | 779.6 | 790.7 | 795.1 |
| 10° | 1041.7 | 959.5 | 848.4 | 784.0 | 764.0 | 750.7 | 741.8 | 735.2 | 730.7 | 739.6 | 741.8 |
| 12.5° | 1199.4 | 1086.1 | 901.7 | 779.6 | 744.0 | 726.3 | 719.6 | 706.3 | 699.6 | 704.1 | 706.3 |
| 15° | 1525.8 | 1330.4 | 1008.3 | 797.3 | 726.3 | 706.3 | 695.2 | 684.1 | 673.0 | 670.7 | 673.0 |
| 17.5° | 1952.3 | 1672.4 | 1170.5 | 839.5 | 712.9 | 688.5 | 673.0 | 657.4 | 641.9 | 639.7 | 637.4 |
| 20° | 2480.9 | 2092.2 | 1397.0 | 906.2 | 701.8 | 673.0 | 650.8 | 628.5 | 608.6 | 601.9 | 601.9 |
| 22.5° | 2962.8 | 2598.6 | 1688.0 | 988.4 | 686.3 | 650.8 | 624.1 | 597.5 | 575.2 | 564.1 | 561.9 |
| 25° | 3551.4 | 3136.1 | 2036.7 | 1083.9 | 664.1 | 621.9 | 593.0 | 566.4 | 544.1 | 530.8 | 526.4 |
| 27.5° | 4144.4 | 3702.4 | 2432.0 | 1208.2 | 637.4 | 593.0 | 566.4 | 541.9 | 517.5 | 502.0 | 497.5 |
| 30° | 4719.7 | 4313.2 | 2876.2 | 1363.7 | 617.4 | 564.1 | 541.9 | 517.5 | 495.3 | 470.9 | 464.2 |
| 32.5° | 5337.1 | 4937.3 | 3373.7 | 1536.9 | 601.9 | 544.1 | 519.7 | 497.5 | 468.6 | 446.4 | 435.3 |
| 35° | 5932.3 | 5581.4 | 3922.3 | 1705.7 | 586.3 | 526.4 | 499.7 | 477.5 | 446.4 | 422.0 | 406.4 |
| 37.5° | 6532.0 | 6236.6 | 4495.3 | 1807.9 | 564.1 | 502.0 | 477.5 | 459.8 | 424.2 | 395.3 | 377.6 |
| 40° | 7167.2 | 6914.0 | 5115.0 | 1765.7 | 544.1 | 475.3 | 462.0 | 442.0 | 402.0 | 368.7 | 346.5 |
| 42.5° | 7864.6 | 7560.4 | 5745.8 | 1603.6 | 526.4 | 453.1 | 439.8 | 419.8 | 382.0 | 342.0 | 313.2 |
| 45° | 8741.9 | 8268.9 | 6263.3 | 1359.3 | 535.3 | 430.9 | 404.2 | 399.8 | 364.2 | 313.2 | 277.6 |
| 47.5° | 10250.0 | 9357.2 | 6665.3 | 1201.6 | 595.2 | 406.4 | 375.4 | 386.5 | 348.7 | 284.3 | 244.3 |
| 50° | 12557.6 | 11160.6 | 7040.6 | 1190.5 | 686.3 | 395.3 | 348.7 | 377.6 | 333.2 | 255.4 | 215.4 |
| 52.5° | 14756.5 | 12993.0 | 7280.5 | 1288.2 | 766.3 | 424.2 | 322.0 | 366.5 | 322.0 | 235.4 | 195.4 |
| 55° | 16859.8 | 14050.2 | 6851.8 | 1359.3 | 841.8 | 510.8 | 302.1 | 348.7 | 308.7 | 224.3 | 188.8 |
| 57.5° | 19127.4 | 14521.0 | 5394.9 | 1503.6 | 895.1 | 584.1 | 306.5 | 322.0 | 291.0 | 217.7 | 186.6 |
| 60° | 19804.8 | 13919.1 | 3256.0 | 1692.4 | 866.2 | 606.3 | 339.8 | 286.5 | 266.5 | 204.3 | 179.9 |
| 62.5° | 18752.1 | 12491.0 | 1921.2 | 1541.4 | 841.8 | 573.0 | 388.7 | 264.3 | 242.1 | 186.6 | 166.6 |
| 65° | 17177.4 | 10552.1 | 1252.7 | 1301.5 | 892.8 | 510.8 | 413.1 | 253.2 | 219.9 | 168.8 | 146.6 |
| 67.5° | 15378.3 | 8499.8 | 877.3 | 768.5 | 824.0 | 459.8 | 348.7 | 251.0 | 197.7 | 142.1 | 119.9 |
| 70° | 12953.0 | 6365.4 | 617.4 | 508.6 | 686.3 | 408.7 | 271.0 | 244.3 | 173.2 | 115.5 | 93.3 |
| 72.5° | 10007.9 | 3984.5 | 459.8 | 328.7 | 488.6 | 333.2 | 215.4 | 206.6 | 139.9 | 95.5 | 71.1 |
| 75° | 7380.4 | 2272.1 | 324.3 | 237.6 | 322.0 | 253.2 | 159.9 | 146.6 | 119.9 | 91.1 | 64.4 |
| 77.5° | 3853.5 | 1137.2 | 202.1 | 182.1 | 184.3 | 157.7 | 115.5 | 106.6 | 111.1 | 91.1 | 60.0 |
| 80° | 739.6 | 226.5 | 122.2 | 133.3 | 99.9 | 99.9 | 84.4 | 88.8 | 97.7 | 73.3 | 51.1 |
| 82.5° | 308.7 | 48.9 | 66.6 | 75.5 | 62.2 | 68.9 | 68.9 | 71.1 | 68.9 | 53.3 | 37.8 |
| 85° | 0.0 | 0.0 | 28.9 | 31.1 | 42.2 | 42.2 | 35.5 | 35.5 | 35.5 | 31.1 | 22.2 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 2.2 | 6.7 | 13.3 | 15.5 | 17.8 | 13.3 | 8.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P638650
 CATALOG NUMBER: GWS-SA4F-730-U-SLR-W-HSS

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 |
| 2.5° | 928.4 | 923.9 | 930.6 | 935.0 | 939.5 | 939.5 | 935.0 | 930.6 | 923.9 | 930.6 | 923.9 |
| 5° | 857.3 | 864.0 | 875.1 | 879.5 | 884.0 | 875.1 | 870.6 | 857.3 | 846.2 | 848.4 | 844.0 |
| 7.5° | 801.8 | 808.5 | 821.8 | 830.7 | 830.7 | 826.2 | 812.9 | 799.6 | 781.8 | 781.8 | 779.6 |
| 10° | 750.7 | 759.6 | 775.1 | 786.2 | 790.7 | 786.2 | 772.9 | 755.1 | 739.6 | 739.6 | 732.9 |
| 12.5° | 708.5 | 719.6 | 737.4 | 752.9 | 757.4 | 752.9 | 739.6 | 721.8 | 704.1 | 704.1 | 699.6 |
| 15° | 673.0 | 686.3 | 706.3 | 724.1 | 730.7 | 724.1 | 708.5 | 686.3 | 668.5 | 670.7 | 664.1 |
| 17.5° | 639.7 | 650.8 | 677.4 | 697.4 | 704.1 | 697.4 | 677.4 | 648.5 | 630.8 | 635.2 | 630.8 |
| 20° | 601.9 | 615.2 | 641.9 | 664.1 | 670.7 | 664.1 | 641.9 | 610.8 | 593.0 | 593.0 | 595.2 |
| 22.5° | 561.9 | 575.2 | 601.9 | 617.4 | 626.3 | 619.7 | 597.5 | 568.6 | 550.8 | 550.8 | 553.0 |
| 25° | 526.4 | 533.0 | 553.0 | 568.6 | 570.8 | 564.1 | 546.4 | 524.2 | 510.8 | 517.5 | 519.7 |
| 27.5° | 493.1 | 493.1 | 502.0 | 510.8 | 508.6 | 502.0 | 495.3 | 477.5 | 475.3 | 482.0 | 488.6 |
| 30° | 457.5 | 446.4 | 442.0 | 435.3 | 433.1 | 430.9 | 437.5 | 437.5 | 442.0 | 450.9 | 457.5 |
| 32.5° | 426.4 | 404.2 | 384.2 | 364.2 | 353.1 | 362.0 | 379.8 | 395.3 | 410.9 | 424.2 | 430.9 |
| 35° | 390.9 | 355.4 | 322.0 | 295.4 | 277.6 | 291.0 | 319.8 | 348.7 | 375.4 | 393.1 | 404.2 |
| 37.5° | 355.4 | 304.3 | 264.3 | 231.0 | 217.7 | 228.8 | 259.9 | 299.8 | 339.8 | 362.0 | 377.6 |
| 40° | 317.6 | 253.2 | 206.6 | 179.9 | 166.6 | 177.7 | 208.8 | 248.8 | 302.1 | 330.9 | 350.9 |
| 42.5° | 279.8 | 208.8 | 166.6 | 139.9 | 133.3 | 139.9 | 164.4 | 204.3 | 262.1 | 297.6 | 324.3 |
| 45° | 242.1 | 173.2 | 133.3 | 113.3 | 106.6 | 113.3 | 133.3 | 166.6 | 224.3 | 264.3 | 295.4 |
| 47.5° | 208.8 | 146.6 | 111.1 | 93.3 | 88.8 | 95.5 | 111.1 | 139.9 | 188.8 | 228.8 | 264.3 |
| 50° | 182.1 | 128.8 | 95.5 | 80.0 | 75.5 | 82.2 | 95.5 | 117.7 | 159.9 | 195.4 | 233.2 |
| 52.5° | 164.4 | 119.9 | 84.4 | 68.9 | 66.6 | 71.1 | 82.2 | 99.9 | 135.5 | 166.6 | 202.1 |
| 55° | 159.9 | 119.9 | 77.7 | 62.2 | 60.0 | 64.4 | 73.3 | 86.6 | 117.7 | 144.4 | 175.5 |
| 57.5° | 164.4 | 128.8 | 73.3 | 53.3 | 51.1 | 55.5 | 64.4 | 75.5 | 102.2 | 124.4 | 153.3 |
| 60° | 164.4 | 131.0 | 64.4 | 42.2 | 40.0 | 44.4 | 53.3 | 66.6 | 91.1 | 108.8 | 133.3 |
| 62.5° | 148.8 | 119.9 | 53.3 | 33.3 | 28.9 | 33.3 | 44.4 | 55.5 | 80.0 | 97.7 | 117.7 |
| 65° | 128.8 | 102.2 | 44.4 | 24.4 | 20.0 | 24.4 | 35.5 | 46.6 | 68.9 | 84.4 | 106.6 |
| 67.5° | 104.4 | 77.7 | 33.3 | 17.8 | 13.3 | 17.8 | 26.7 | 37.8 | 57.7 | 73.3 | 95.5 |
| 70° | 77.7 | 55.5 | 26.7 | 15.5 | 13.3 | 15.5 | 24.4 | 35.5 | 51.1 | 66.6 | 88.8 |
| 72.5° | 57.7 | 37.8 | 22.2 | 15.5 | 11.1 | 15.5 | 22.2 | 33.3 | 48.9 | 64.4 | 84.4 |
| 75° | 48.9 | 31.1 | 20.0 | 13.3 | 11.1 | 13.3 | 20.0 | 31.1 | 44.4 | 60.0 | 80.0 |
| 77.5° | 46.6 | 28.9 | 17.8 | 11.1 | 8.9 | 11.1 | 17.8 | 26.7 | 40.0 | 55.5 | 77.7 |
| 80° | 40.0 | 24.4 | 15.5 | 8.9 | 6.7 | 8.9 | 15.5 | 22.2 | 31.1 | 42.2 | 60.0 |
| 82.5° | 31.1 | 20.0 | 11.1 | 4.4 | 2.2 | 4.4 | 11.1 | 13.3 | 20.0 | 24.4 | 35.5 |
| 85° | 20.0 | 11.1 | 4.4 | 0.0 | 0.0 | 0.0 | 4.4 | 8.9 | 8.9 | 11.1 | 17.8 |
| 87.5° | 8.9 | 2.2 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 2.2 | 4.4 | 6.7 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P638650
 CATALOG NUMBER: GWS-SA4F-730-U-SLR-W-HSS

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|-------|-------|-------|-------|-------|--------|--------|---------|---------|---------|
| 0° | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 | 999.5 |
| 2.5° | 937.3 | 939.5 | 943.9 | 950.6 | 966.1 | 979.5 | 992.8 | 1010.6 | 1019.4 | 1019.4 |
| 5° | 848.4 | 850.7 | 852.9 | 861.8 | 884.0 | 901.7 | 930.6 | 966.1 | 983.9 | 988.4 |
| 7.5° | 779.6 | 784.0 | 788.5 | 795.1 | 817.3 | 841.8 | 879.5 | 946.2 | 979.5 | 986.1 |
| 10° | 739.6 | 746.3 | 755.1 | 768.5 | 788.5 | 815.1 | 879.5 | 999.5 | 1055.0 | 1066.1 |
| 12.5° | 708.5 | 719.6 | 728.5 | 744.0 | 768.5 | 810.7 | 939.5 | 1150.5 | 1248.2 | 1274.9 |
| 15° | 677.4 | 690.7 | 704.1 | 719.6 | 746.3 | 826.2 | 1055.0 | 1421.5 | 1583.6 | 1603.6 |
| 17.5° | 646.3 | 661.9 | 679.6 | 697.4 | 730.7 | 864.0 | 1237.1 | 1796.8 | 2023.3 | 2067.8 |
| 20° | 610.8 | 630.8 | 655.2 | 677.4 | 715.2 | 923.9 | 1490.3 | 2243.2 | 2527.5 | 2623.0 |
| 22.5° | 573.0 | 597.5 | 626.3 | 655.2 | 697.4 | 997.2 | 1796.8 | 2723.0 | 3120.5 | 3182.7 |
| 25° | 541.9 | 566.4 | 593.0 | 621.9 | 668.5 | 1086.1 | 2167.7 | 3318.2 | 3680.2 | 3740.2 |
| 27.5° | 513.1 | 537.5 | 561.9 | 588.6 | 639.7 | 1201.6 | 2614.1 | 3951.2 | 4328.8 | 4391.0 |
| 30° | 482.0 | 510.8 | 535.3 | 561.9 | 613.0 | 1343.7 | 3129.4 | 4653.0 | 5010.6 | 5068.4 |
| 32.5° | 455.3 | 484.2 | 508.6 | 535.3 | 593.0 | 1499.2 | 3671.3 | 5274.9 | 5565.9 | 5565.9 |
| 35° | 433.1 | 464.2 | 482.0 | 517.5 | 577.5 | 1599.1 | 4184.4 | 5867.9 | 6087.8 | 6078.9 |
| 37.5° | 408.7 | 446.4 | 459.8 | 484.2 | 557.5 | 1610.2 | 4666.4 | 6494.3 | 6656.4 | 6598.6 |
| 40° | 384.2 | 424.2 | 444.2 | 457.5 | 535.3 | 1519.2 | 5195.0 | 7069.5 | 7207.2 | 7131.7 |
| 42.5° | 362.0 | 393.1 | 422.0 | 437.5 | 521.9 | 1359.3 | 5619.2 | 7684.7 | 7849.1 | 7782.5 |
| 45° | 339.8 | 366.5 | 384.2 | 413.1 | 530.8 | 1248.2 | 5983.4 | 8402.1 | 8690.8 | 8642.0 |
| 47.5° | 317.6 | 339.8 | 350.9 | 395.3 | 590.8 | 1197.1 | 6205.5 | 9512.6 | 10056.8 | 10016.8 |
| 50° | 293.2 | 319.8 | 319.8 | 390.9 | 679.6 | 1214.9 | 6398.8 | 11120.6 | 11962.4 | 11949.1 |
| 52.5° | 268.7 | 297.6 | 293.2 | 424.2 | 748.5 | 1297.1 | 6618.6 | 12539.9 | 14003.5 | 14125.7 |
| 55° | 244.3 | 271.0 | 275.4 | 490.8 | 788.5 | 1368.1 | 5768.0 | 13137.3 | 15747.0 | 16175.7 |
| 57.5° | 217.7 | 233.2 | 286.5 | 541.9 | 775.1 | 1574.7 | 3951.2 | 13246.2 | 16859.8 | 17779.3 |
| 60° | 188.8 | 202.1 | 324.3 | 530.8 | 732.9 | 1454.8 | 2487.5 | 12268.9 | 16702.1 | 17868.1 |
| 62.5° | 164.4 | 186.6 | 342.0 | 468.6 | 746.3 | 1261.5 | 1585.8 | 10456.6 | 15198.4 | 16528.8 |
| 65° | 144.4 | 179.9 | 310.9 | 424.2 | 755.1 | 855.1 | 1070.5 | 8506.5 | 13730.3 | 14996.3 |
| 67.5° | 128.8 | 199.9 | 255.4 | 377.6 | 648.5 | 601.9 | 735.2 | 6609.8 | 11544.9 | 12679.8 |
| 70° | 117.7 | 204.3 | 208.8 | 324.3 | 502.0 | 386.5 | 484.2 | 4448.7 | 7957.9 | 9255.0 |
| 72.5° | 106.6 | 151.0 | 157.7 | 259.9 | 324.3 | 235.4 | 313.2 | 2545.3 | 5801.3 | 6685.3 |
| 75° | 102.2 | 102.2 | 108.8 | 168.8 | 179.9 | 171.0 | 202.1 | 1519.2 | 4160.0 | 4806.3 |
| 77.5° | 95.5 | 77.7 | 68.9 | 108.8 | 97.7 | 122.2 | 119.9 | 675.2 | 1803.5 | 1950.1 |
| 80° | 75.5 | 55.5 | 46.6 | 68.9 | 66.6 | 82.2 | 71.1 | 55.5 | 82.2 | 80.0 |
| 82.5° | 46.6 | 35.5 | 33.3 | 42.2 | 37.8 | 42.2 | 33.3 | 8.9 | 8.9 | 8.9 |
| 85° | 22.2 | 20.0 | 17.8 | 17.8 | 20.0 | 17.8 | 13.3 | 4.4 | 2.2 | 2.2 |
| 87.5° | 11.1 | 11.1 | 8.9 | 6.7 | 8.9 | 8.9 | 6.7 | 2.2 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-2-R4

Test Date: 10/03/2019

Luminaire Tested: SA1C-730-U-5WQ

Data in this report applies to families of products SA1C-730-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-2-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-730-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-2-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. (1) 70 CRI, 3000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2993
 CIE u': 0.2508
 CIE v': 0.5215
 Duv: 0.0000
 CIE x: 0.4374
 CIE y: 0.4043
 CIE z: 0.1583
 Peak Wavelength (nm): 593
 Dominant Wavelength (nm): 582
 Purity: 53

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.8 | | |
| R1: | 67.5 | R9: | -38.3 |
| R2: | 82.9 | R10: | 62.5 |
| R3: | 94.7 | R11: | 63.7 |
| R4: | 67.7 | R12: | 57.8 |
| R5: | 67.9 | R13: | 70.4 |
| R6: | 77.6 | R14: | 97.3 |
| R7: | 76.0 | | |
| R8: | 40.5 | | |

Rf: 75.7
 Rg: 93.9



Test Conditions

Stabilization Time: 53M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-2-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-2-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-2-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 8494.8

S/P: 1.23

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3101.5 M/P: 0.45


| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4



TM-30-18

Summary

$R_f = 75.7$
 $R_g = 93.9$
 CIE $R_a = 71.8$
 $R_9 = -38.3$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 67 | CES51 = 87 | CES76 = 63 |
| CES02 = 63 | CES27 = 88 | CES52 = 86 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 78 | CES78 = 67 |
| CES04 = 71 | CES29 = 66 | CES54 = 84 | CES79 = 87 |
| CES05 = 49 | CES30 = 73 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 70 | CES56 = 75 | CES81 = 71 |
| CES07 = 41 | CES32 = 65 | CES57 = 74 | CES82 = 94 |
| CES08 = 40 | CES33 = 73 | CES58 = 76 | CES83 = 90 |
| CES09 = 29 | CES34 = 79 | CES59 = 85 | CES84 = 89 |
| CES10 = 76 | CES35 = 89 | CES60 = 93 | CES85 = 77 |
| CES11 = 59 | CES36 = 97 | CES61 = 84 | CES86 = 61 |
| CES12 = 65 | CES37 = 87 | CES62 = 91 | CES87 = 78 |
| CES13 = 43 | CES38 = 81 | CES63 = 77 | CES88 = 77 |
| CES14 = 74 | CES39 = 95 | CES64 = 72 | CES89 = 67 |
| CES15 = 71 | CES40 = 92 | CES65 = 68 | CES90 = 76 |
| CES16 = 47 | CES41 = 88 | CES66 = 69 | CES91 = 89 |
| CES17 = 50 | CES42 = 89 | CES67 = 67 | CES92 = 58 |
| CES18 = 56 | CES43 = 79 | CES68 = 72 | CES93 = 74 |
| CES19 = 73 | CES44 = 99 | CES69 = 81 | CES94 = 49 |
| CES20 = 66 | CES45 = 85 | CES70 = 66 | CES95 = 68 |
| CES21 = 87 | CES46 = 80 | CES71 = 67 | CES96 = 76 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 69 | CES73 = 59 | CES98 = 75 |
| CES24 = 91 | CES49 = 80 | CES74 = 95 | CES99 = 62 |
| CES25 = 73 | CES50 = 87 | CES75 = 69 | |



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Measure Comparisons



(END OF REPORT)