

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P636686

Luminaire Tested: GWS-SA4B-730-U-T3R-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P636686
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA4B-730-U-T3R-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III ROADWAY OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (64) 3000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11555.8 lumens
Efficiency: N/A
Efficacy: 122.4 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B2 - U0 - G2


Input Watts (W): 94.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P636686
 CATALOG NUMBER: GWS-SA4B-730-U-T3R-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 7.2 fc
 Type II - Short - N/A

REPORT NUMBER: P636686
CATALOG NUMBER: GWS-SA4B-730-U-T3R-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 79-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P636686

CATALOG NUMBER: GWS-SA4B-730-U-T3R-W-GRSWH


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 3435.0 | 0.0 | 3435.0 |
| | % Fixture | 29.7 | 0.0 | 29.7 |
| Street Side | Lumens | 8120.8 | 0.0 | 8120.8 |
| | % Fixture | 70.3 | 0.0 | 70.3 |
| Total | Lumens | 11555.8 | 0.0 | 11555.8 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 265.2 | 2.3 |
| 10°-20° | 737.0 | 6.4 |
| 20°-30° | 1249.3 | 10.8 |
| 30°-40° | 1912.2 | 16.5 |
| 40°-50° | 2549.7 | 22.1 |
| 50°-60° | 2944.7 | 25.5 |
| 60°-70° | 1530.2 | 13.2 |
| 70°-80° | 325.3 | 2.8 |
| 80°-90° | 42.1 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 11555.8 | 100.0 |
| 0°-180° | 11555.8 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P636686


CATALOG NUMBER: GWS-SA4B-730-U-T3R-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1276.0 | 11.0 | | | |
| FM (30°-60°) | 5584.1 | 48.3 | | | |
| FH (60°-80°) | 1246.0 | 10.8 | | | G1/1800 |
| FVH (80°-90°) | 14.7 | 0.1 | | | G1/100 |
| BL (0°-30°) | 975.5 | 8.4 | B2/1000 | | |
| BM (30°-60°) | 1822.6 | 15.8 | B2/2500 | | |
| BH (60°-80°) | 609.5 | 5.3 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 27.4 | 0.2 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G2

Type II Short





REPORT NUMBER: P636686
 CATALOG NUMBER: GWS-SA4B-730-U-T3R-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 79° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2863.8 | 2863.8 | 2863.8 | 2863.8 | 2863.8 | 2863.8 | 2863.8 | 2863.8 | 2863.8 | 2863.8 | 2863.8 |
| 2.5° | 2733.4 | 2727.7 | 2729.6 | 2737.2 | 2765.5 | 2786.3 | 2808.0 | 2827.9 | 2846.8 | 2852.5 | 2857.2 |
| 5° | 2636.1 | 2625.7 | 2628.5 | 2640.8 | 2673.9 | 2708.8 | 2747.6 | 2794.8 | 2840.2 | 2855.3 | 2875.1 |
| 7.5° | 2567.1 | 2565.2 | 2570.0 | 2588.8 | 2623.8 | 2656.9 | 2707.0 | 2774.0 | 2852.5 | 2878.0 | 2912.9 |
| 10° | 2475.5 | 2471.7 | 2490.6 | 2529.3 | 2587.0 | 2639.9 | 2699.4 | 2778.8 | 2888.4 | 2926.2 | 2980.0 |
| 12.5° | 2402.7 | 2400.8 | 2420.7 | 2474.5 | 2548.2 | 2632.3 | 2714.5 | 2803.3 | 2936.5 | 2988.5 | 3054.7 |
| 15° | 2445.2 | 2436.7 | 2437.7 | 2475.5 | 2541.6 | 2640.8 | 2752.3 | 2847.7 | 2984.7 | 3050.9 | 3135.9 |
| 17.5° | 2569.0 | 2553.9 | 2542.6 | 2549.2 | 2587.0 | 2689.9 | 2809.9 | 2907.3 | 3040.5 | 3118.0 | 3221.9 |
| 20° | 2740.0 | 2731.5 | 2700.3 | 2679.6 | 2688.1 | 2778.8 | 2900.6 | 2991.3 | 3113.2 | 3200.2 | 3311.6 |
| 22.5° | 2969.6 | 2948.8 | 2906.3 | 2873.2 | 2847.7 | 2918.6 | 3031.0 | 3109.5 | 3214.3 | 3305.0 | 3421.2 |
| 25° | 3254.0 | 3223.8 | 3156.7 | 3104.7 | 3049.9 | 3122.7 | 3222.8 | 3282.4 | 3353.2 | 3437.3 | 3547.9 |
| 27.5° | 3544.1 | 3518.6 | 3443.9 | 3374.0 | 3306.0 | 3351.3 | 3470.4 | 3504.4 | 3496.8 | 3558.2 | 3652.7 |
| 30° | 3853.0 | 3820.9 | 3750.0 | 3674.5 | 3586.6 | 3615.9 | 3722.6 | 3739.7 | 3659.3 | 3710.4 | 3774.6 |
| 32.5° | 4179.0 | 4147.8 | 4086.4 | 3998.5 | 3899.3 | 3910.7 | 3940.0 | 3956.0 | 3879.5 | 3908.8 | 3957.9 |
| 35° | 4510.6 | 4481.4 | 4419.0 | 4332.1 | 4259.3 | 4190.3 | 4116.6 | 4180.9 | 4136.5 | 4193.2 | 4189.4 |
| 37.5° | 4813.9 | 4784.6 | 4745.9 | 4678.8 | 4554.1 | 4418.0 | 4248.0 | 4327.3 | 4396.3 | 4468.1 | 4455.8 |
| 40° | 5019.0 | 4999.1 | 5008.6 | 4998.2 | 4837.6 | 4568.3 | 4312.2 | 4399.2 | 4587.2 | 4710.0 | 4703.4 |
| 42.5° | 5195.6 | 5175.8 | 5230.6 | 5270.3 | 5081.3 | 4707.2 | 4343.4 | 4426.6 | 4709.1 | 4900.9 | 4891.4 |
| 45° | 5274.1 | 5268.4 | 5359.1 | 5484.8 | 5304.3 | 4854.6 | 4423.7 | 4483.2 | 4801.7 | 5047.3 | 5011.4 |
| 47.5° | 5180.5 | 5200.4 | 5378.9 | 5591.5 | 5489.5 | 5029.4 | 4588.1 | 4603.2 | 4922.6 | 5206.0 | 5104.9 |
| 50° | 4994.4 | 5037.9 | 5278.8 | 5594.4 | 5624.6 | 5226.8 | 4815.8 | 4778.0 | 5085.1 | 5375.2 | 5154.1 |
| 52.5° | 4723.2 | 4768.6 | 5161.6 | 5572.6 | 5702.1 | 5455.5 | 5119.1 | 5065.3 | 5290.1 | 5544.3 | 5162.6 |
| 55° | 4100.6 | 4162.0 | 4893.3 | 5523.5 | 5777.7 | 5663.3 | 5461.1 | 5351.5 | 5554.7 | 5776.7 | 5246.7 |
| 57.5° | 3557.3 | 3589.4 | 4239.5 | 5305.2 | 5792.8 | 5816.4 | 5704.9 | 5574.5 | 5817.3 | 6028.0 | 5341.2 |
| 60° | 2610.6 | 2618.1 | 3203.0 | 4389.7 | 5328.9 | 5727.6 | 5685.1 | 5491.4 | 5692.6 | 5826.8 | 4908.4 |
| 62.5° | 1474.9 | 1475.8 | 1942.6 | 2929.9 | 3980.6 | 4668.4 | 4694.9 | 4523.9 | 4354.7 | 4394.4 | 3416.5 |
| 65° | 553.7 | 605.6 | 887.2 | 1439.9 | 2295.0 | 2756.1 | 2865.7 | 2905.4 | 2623.8 | 2449.0 | 1832.0 |
| 67.5° | 370.4 | 382.7 | 517.8 | 740.8 | 1021.4 | 1179.2 | 1319.0 | 1322.8 | 967.5 | 862.6 | 721.9 |
| 70° | 282.5 | 294.8 | 407.2 | 530.1 | 517.8 | 478.1 | 516.8 | 502.7 | 519.7 | 533.8 | 548.9 |
| 72.5° | 210.7 | 223.0 | 315.6 | 374.2 | 310.9 | 306.1 | 346.8 | 385.5 | 421.4 | 436.5 | 460.1 |
| 75° | 139.8 | 149.3 | 212.6 | 200.3 | 172.0 | 203.1 | 253.2 | 292.0 | 312.7 | 330.7 | 348.6 |
| 77.5° | 88.8 | 95.4 | 113.4 | 91.6 | 95.4 | 119.0 | 147.4 | 182.4 | 202.2 | 220.1 | 229.6 |
| 80° | 40.6 | 39.7 | 38.7 | 43.5 | 53.9 | 69.9 | 88.8 | 109.6 | 124.7 | 132.3 | 137.9 |
| 82.5° | 16.1 | 18.0 | 19.8 | 23.6 | 29.3 | 37.8 | 50.1 | 64.2 | 76.5 | 78.4 | 83.1 |
| 85° | 6.6 | 7.6 | 8.5 | 10.4 | 13.2 | 17.0 | 20.8 | 29.3 | 36.8 | 39.7 | 42.5 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.9 | 1.9 | 2.8 | 4.7 | 8.5 | 9.4 | 10.4 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P636686

CATALOG NUMBER: GWS-SA4B-730-U-T3R-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2863.8 | 2863.8 | 2863.8 | 2863.8 | 2863.8 | 2863.8 | 2863.8 | 2863.8 | 2863.8 | 2863.8 | 2863.8 |
| 2.5° | 2882.7 | 2870.4 | 2891.2 | 2905.4 | 2918.6 | 2904.4 | 2899.7 | 2887.4 | 2885.5 | 2885.5 | 2892.1 |
| 5° | 2909.1 | 2900.6 | 2922.4 | 2930.9 | 2929.9 | 2898.8 | 2879.9 | 2855.3 | 2843.0 | 2843.0 | 2844.9 |
| 7.5° | 2956.4 | 2951.7 | 2963.9 | 2950.7 | 2920.5 | 2857.2 | 2794.8 | 2742.9 | 2707.9 | 2689.9 | 2695.6 |
| 10° | 3034.8 | 3029.1 | 3018.7 | 2969.6 | 2882.7 | 2751.4 | 2623.8 | 2529.3 | 2472.6 | 2440.5 | 2442.4 |
| 12.5° | 3111.3 | 3101.9 | 3065.0 | 2956.4 | 2777.8 | 2569.0 | 2401.8 | 2295.9 | 2233.6 | 2195.8 | 2187.3 |
| 15° | 3195.4 | 3170.9 | 3091.5 | 2888.4 | 2606.8 | 2346.0 | 2171.2 | 2056.9 | 1989.8 | 1967.1 | 1966.2 |
| 17.5° | 3275.7 | 3232.3 | 3088.7 | 2767.4 | 2401.8 | 2112.7 | 1936.9 | 1866.0 | 1854.7 | 1865.1 | 1867.9 |
| 20° | 3357.0 | 3287.1 | 3057.5 | 2600.2 | 2158.0 | 1880.2 | 1789.5 | 1818.8 | 1861.3 | 1889.7 | 1896.3 |
| 22.5° | 3441.1 | 3332.4 | 2986.6 | 2384.8 | 1901.0 | 1723.4 | 1761.2 | 1825.4 | 1878.3 | 1916.1 | 1919.9 |
| 25° | 3535.6 | 3375.0 | 2880.8 | 2121.2 | 1695.0 | 1679.9 | 1754.6 | 1822.6 | 1879.3 | 1922.7 | 1930.3 |
| 27.5° | 3589.4 | 3375.9 | 2732.5 | 1850.0 | 1600.6 | 1662.9 | 1738.5 | 1802.7 | 1859.4 | 1906.7 | 1915.2 |
| 30° | 3642.3 | 3350.4 | 2497.2 | 1629.8 | 1573.2 | 1643.1 | 1711.1 | 1770.6 | 1824.5 | 1870.8 | 1881.2 |
| 32.5° | 3717.0 | 3326.8 | 2226.0 | 1503.2 | 1557.1 | 1624.2 | 1679.9 | 1732.8 | 1774.4 | 1795.2 | 1800.9 |
| 35° | 3809.6 | 3296.5 | 1937.9 | 1448.4 | 1546.7 | 1609.1 | 1658.2 | 1686.5 | 1632.7 | 1621.3 | 1633.6 |
| 37.5° | 3939.0 | 3268.2 | 1650.6 | 1424.8 | 1540.1 | 1603.4 | 1646.8 | 1574.1 | 1508.0 | 1481.5 | 1490.9 |
| 40° | 4078.9 | 3252.1 | 1456.0 | 1405.9 | 1542.9 | 1609.1 | 1599.6 | 1491.9 | 1396.5 | 1340.7 | 1338.8 |
| 42.5° | 4197.9 | 3227.6 | 1331.3 | 1393.6 | 1550.5 | 1630.8 | 1535.4 | 1419.1 | 1277.4 | 1244.3 | 1245.3 |
| 45° | 4278.2 | 3165.2 | 1265.1 | 1380.4 | 1557.1 | 1635.5 | 1505.1 | 1319.0 | 1217.9 | 1197.1 | 1196.2 |
| 47.5° | 4311.3 | 3051.8 | 1222.6 | 1359.6 | 1556.1 | 1596.8 | 1443.7 | 1277.4 | 1176.3 | 1170.7 | 1174.4 |
| 50° | 4289.6 | 2865.7 | 1179.2 | 1319.0 | 1533.5 | 1556.1 | 1372.8 | 1240.6 | 1148.0 | 1179.2 | 1201.8 |
| 52.5° | 4209.2 | 2624.8 | 1127.2 | 1263.2 | 1492.8 | 1509.8 | 1336.9 | 1217.9 | 1127.2 | 1168.8 | 1186.7 |
| 55° | 4188.5 | 2429.2 | 1061.0 | 1190.5 | 1432.4 | 1427.6 | 1299.1 | 1206.6 | 1113.0 | 1097.0 | 1099.8 |
| 57.5° | 4161.1 | 2238.3 | 951.4 | 1060.1 | 1279.3 | 1286.9 | 1263.2 | 1193.3 | 1076.2 | 1071.4 | 1076.2 |
| 60° | 3614.9 | 1715.8 | 848.5 | 914.6 | 1050.7 | 1091.3 | 1222.6 | 1168.8 | 1016.6 | 996.8 | 995.9 |
| 62.5° | 2361.1 | 1039.3 | 754.9 | 797.4 | 856.0 | 903.3 | 1114.9 | 1097.9 | 951.4 | 939.2 | 947.7 |
| 65° | 1269.9 | 740.8 | 686.9 | 712.4 | 744.5 | 780.4 | 924.0 | 977.9 | 859.8 | 816.3 | 817.3 |
| 67.5° | 649.1 | 630.2 | 635.9 | 653.8 | 678.4 | 696.3 | 745.5 | 792.7 | 733.2 | 696.3 | 695.4 |
| 70° | 555.6 | 570.7 | 579.2 | 589.6 | 605.6 | 602.8 | 607.5 | 616.0 | 611.3 | 593.4 | 592.4 |
| 72.5° | 473.4 | 497.0 | 498.9 | 500.8 | 506.4 | 493.2 | 484.7 | 470.5 | 471.5 | 474.3 | 475.3 |
| 75° | 360.0 | 382.7 | 388.3 | 385.5 | 391.2 | 374.2 | 362.8 | 348.6 | 331.6 | 328.8 | 330.7 |
| 77.5° | 234.3 | 252.3 | 260.8 | 258.9 | 261.7 | 248.5 | 242.8 | 227.7 | 207.9 | 200.3 | 200.3 |
| 80° | 141.7 | 152.1 | 158.7 | 160.6 | 163.5 | 154.0 | 144.6 | 131.3 | 122.8 | 114.3 | 114.3 |
| 82.5° | 86.0 | 92.6 | 97.3 | 97.3 | 100.2 | 89.8 | 82.2 | 72.8 | 69.0 | 61.4 | 61.4 |
| 85° | 43.5 | 48.2 | 50.1 | 49.1 | 47.2 | 38.7 | 35.9 | 31.2 | 29.3 | 25.5 | 25.5 |
| 87.5° | 10.4 | 13.2 | 13.2 | 9.4 | 9.4 | 4.7 | 2.8 | 0.9 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-2-R4

Test Date: 10/03/2019

Luminaire Tested: SA1C-730-U-5WQ

Data in this report applies to families of products SA1C-730-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-2-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-730-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-2-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. (1) 70 CRI, 3000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 2993 | CRI (Ra): | 71.8 | R9: | -38.3 |
| CIE u': | 0.2508 | R1: | 67.5 | R10: | 62.5 |
| CIE v': | 0.5215 | R2: | 82.9 | R11: | 63.7 |
| Duv: | 0.0000 | R3: | 94.7 | R12: | 57.8 |
| CIE x: | 0.4374 | R4: | 67.7 | R13: | 70.4 |
| CIE y: | 0.4043 | R5: | 67.9 | R14: | 97.3 |
| CIE z: | 0.1583 | R6: | 77.6 | | |
| Peak Wavelength (nm): | 593 | R7: | 76.0 | | |
| Dominant Wavelength (nm): | 582 | R8: | 40.5 | | |
| Purity: | 53 | | | | |
| Rf: | 75.7 | | | | |
| Rg: | 93.9 | | | | |



Test Conditions

Stabilization Time: 53M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-2-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-2-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-2-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 8494.8

S/P: 1.23

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3101.5 M/P: 0.45

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Summary

$R_f = 75.7$
 $R_g = 93.9$
 CIE $R_a = 71.8$
 $R_9 = -38.3$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 67 | CES51 = 87 | CES76 = 63 |
| CES02 = 63 | CES27 = 88 | CES52 = 86 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 78 | CES78 = 67 |
| CES04 = 71 | CES29 = 66 | CES54 = 84 | CES79 = 87 |
| CES05 = 49 | CES30 = 73 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 70 | CES56 = 75 | CES81 = 71 |
| CES07 = 41 | CES32 = 65 | CES57 = 74 | CES82 = 94 |
| CES08 = 40 | CES33 = 73 | CES58 = 76 | CES83 = 90 |
| CES09 = 29 | CES34 = 79 | CES59 = 85 | CES84 = 89 |
| CES10 = 76 | CES35 = 89 | CES60 = 93 | CES85 = 77 |
| CES11 = 59 | CES36 = 97 | CES61 = 84 | CES86 = 61 |
| CES12 = 65 | CES37 = 87 | CES62 = 91 | CES87 = 78 |
| CES13 = 43 | CES38 = 81 | CES63 = 77 | CES88 = 77 |
| CES14 = 74 | CES39 = 95 | CES64 = 72 | CES89 = 67 |
| CES15 = 71 | CES40 = 92 | CES65 = 68 | CES90 = 76 |
| CES16 = 47 | CES41 = 88 | CES66 = 69 | CES91 = 89 |
| CES17 = 50 | CES42 = 89 | CES67 = 67 | CES92 = 58 |
| CES18 = 56 | CES43 = 79 | CES68 = 72 | CES93 = 74 |
| CES19 = 73 | CES44 = 99 | CES69 = 81 | CES94 = 49 |
| CES20 = 66 | CES45 = 85 | CES70 = 66 | CES95 = 68 |
| CES21 = 87 | CES46 = 80 | CES71 = 67 | CES96 = 76 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 69 | CES73 = 59 | CES98 = 75 |
| CES24 = 91 | CES49 = 80 | CES74 = 95 | CES99 = 62 |
| CES25 = 73 | CES50 = 87 | CES75 = 69 | |



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Measure Comparisons



(END OF REPORT)