

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P833684

Luminaire Tested: **TTN-D2-830-U-MQ-UPL2**

Issue Date: 5/15/2024

Test Information

Test Method: LM-79-08
Report Number: P833684
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND
Test Lab: INNOVATION CENTER
Issue Date: 5/15/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TTN-D2-830-U-MQ-UPL2
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT
3000K, 80 CRI LEDS AND MEDIUM DISTRIBUTION
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5500.7 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')
IES Classification: Type V - Short
BUG Rating: B2 - U4 - G1


Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P833684
 CATALOG NUMBER: TTN-D2-830-U-MQ-UPL2

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.7 fc
 Type V - Short - N/A

REPORT NUMBER: P833684
CATALOG NUMBER: TTN-D2-830-U-MQ-UPL2

Luminous Intensity Polar Plot



REPORT NUMBER: P833684

CATALOG NUMBER: TTN-D2-830-U-MQ-UPL2


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2483.3	267.0	2750.3
	% Fixture	45.1	4.9	50.0
Street Side	Lumens	2483.3	267.0	2750.3
	% Fixture	45.1	4.9	50.0
Total	Lumens	4966.6	534.0	5500.7
	% Fixture	90.3	9.7	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.8	1.8
10°-20°	280.7	5.1
20°-30°	453.7	8.2
30°-40°	614.0	11.2
40°-50°	769.0	14.0
50°-60°	942.4	17.1
60°-70°	944.7	17.2
70°-80°	681.7	12.4
80°-90°	182.5	3.3
90°-100°	11.9	0.2
100°-110°	121.1	2.2
110°-120°	177.1	3.2
120°-130°	102.8	1.9
130°-140°	54.4	1.0
140°-150°	32.3	0.6
150°-160°	19.9	0.4
160°-170°	10.9	0.2
170°-180°	3.5	0.1
0°-90°	4966.6	90.3
0°-180°	5500.7	100.0

Coefficient of Utilization



REPORT NUMBER: P833684


CATALOG NUMBER: TTN-D2-830-U-MQ-UPL2

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	416.1	7.6			
FM (30°-60°)	1162.7	21.1			
FH (60°-80°)	813.2	14.8			G1/1800
FVH (80°-90°)	91.2	1.7			G1/100
BL (0°-30°)	416.1	7.6	B1/500		
BM (30°-60°)	1162.7	21.1	B2/2500		
BH (60°-80°)	813.2	14.8	B2/1000		G1/1800
BVH (80°-90°)	91.2	1.7			G1/100
UL (90°-100°)	11.9	0.2		U2/50	
UH (100°-180°)	522.1	9.5		U4/1000	

BUG Rating: B2-U4-G1

Type V Short





REPORT NUMBER: P833684

CATALOG NUMBER: TTN-D2-830-U-MQ-UPL2

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	1044.8	1044.8	1044.8	1044.8	1044.8	1044.8	1044.8	1044.8	1044.8	1044.8	1044.8
2.5°	1040.9	1040.9	1040.9	1037.0	1040.9	1040.9	1040.9	1040.9	1040.9	1040.9	1040.9
5°	1033.1	1033.1	1033.1	1033.1	1033.1	1033.1	1033.1	1033.1	1033.1	1033.1	1033.1
7.5°	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4
10°	1005.8	1005.8	1005.8	1005.8	1009.7	1009.7	1009.7	1009.7	1005.8	1005.8	1005.8
12.5°	994.1	994.1	994.1	998.0	998.0	998.0	998.0	998.0	998.0	998.0	994.1
15°	990.2	990.2	990.2	990.2	994.1	994.1	994.1	994.1	990.2	990.2	990.2
17.5°	982.4	982.4	982.4	986.3	986.3	986.3	986.3	986.3	982.4	982.4	982.4
20°	974.6	974.6	978.5	978.5	982.4	982.4	982.4	978.5	978.5	974.6	978.5
22.5°	974.6	974.6	974.6	978.5	978.5	978.5	978.5	974.6	974.6	974.6	974.6
25°	974.6	974.6	978.5	982.4	982.4	986.3	982.4	978.5	974.6	974.6	974.6
27.5°	978.5	978.5	982.4	986.3	986.3	990.2	986.3	982.4	978.5	978.5	978.5
30°	978.5	978.5	982.4	986.3	986.3	990.2	986.3	982.4	978.5	978.5	978.5
32.5°	970.7	974.6	978.5	982.4	986.3	986.3	986.3	982.4	978.5	974.6	974.6
35°	966.8	970.7	974.6	978.5	982.4	982.4	982.4	978.5	974.6	970.7	970.7
37.5°	962.9	962.9	970.7	974.6	978.5	986.3	982.4	974.6	970.7	966.8	966.8
40°	959.0	962.9	966.8	974.6	978.5	986.3	982.4	974.6	966.8	962.9	962.9
42.5°	959.0	959.0	966.8	974.6	982.4	990.2	986.3	978.5	966.8	962.9	959.0
45°	962.9	966.8	978.5	994.1	1001.9	1009.7	1005.8	994.1	974.6	966.8	962.9
47.5°	978.5	982.4	994.1	1009.7	1029.2	1040.9	1029.2	1009.7	994.1	982.4	978.5
50°	986.3	990.2	1009.7	1029.2	1056.5	1060.4	1056.5	1029.2	1009.7	990.2	990.2
52.5°	1001.9	1001.9	1025.3	1060.4	1083.8	1091.6	1083.8	1064.3	1025.3	1005.8	1001.9
55°	1005.8	1005.8	1033.1	1076.0	1111.1	1130.6	1111.1	1079.9	1037.0	1009.7	1009.7
57.5°	982.4	990.2	1025.3	1068.2	1111.1	1122.8	1111.1	1072.1	1029.2	994.1	990.2
60°	955.1	966.8	998.0	1048.7	1079.9	1091.6	1083.8	1048.7	1001.9	966.8	962.9
62.5°	927.9	943.4	978.5	1017.5	1064.3	1076.0	1064.3	1017.5	978.5	943.4	927.9
65°	869.4	885.0	935.6	982.4	1025.3	1033.1	1029.2	982.4	935.6	885.0	877.2
67.5°	810.9	822.6	857.7	931.8	966.8	978.5	970.7	927.9	861.6	822.6	818.7
70°	748.5	760.2	791.4	861.6	896.7	916.2	900.6	861.6	791.4	760.2	756.3
72.5°	666.7	682.2	717.3	779.7	814.8	834.3	818.7	779.7	717.3	678.3	670.5
75°	569.2	580.9	623.8	674.4	709.5	725.1	713.4	678.3	623.8	580.9	577.0
77.5°	463.9	475.6	514.6	565.3	584.8	600.4	588.7	561.4	514.6	475.6	471.7
80°	350.9	362.6	397.7	436.6	456.1	471.7	460.0	432.7	397.7	362.6	358.7
82.5°	230.0	241.7	272.9	304.1	323.6	339.2	327.5	300.2	276.8	241.7	237.8
85°	97.5	109.2	136.4	167.6	183.2	198.8	187.1	163.7	136.4	113.1	109.2
87.5°	7.8	11.7	11.7	15.6	11.7	19.5	11.7	11.7	11.7	11.7	11.7
90°	4.6	4.6	5.5	5.5	5.5	5.5	5.5	5.5	5.5	4.6	4.6
92.5°	4.6	4.6	4.6	6.4	7.3	6.4	7.3	5.5	5.5	4.6	4.6
95°	5.5	5.5	6.4	8.2	10.1	11.0	11.0	6.4	6.4	5.5	5.5
97.5°	7.3	8.2	8.2	10.1	16.4	30.2	18.3	9.1	9.1	8.2	7.3
100°	11.9	12.8	12.8	22.8	48.4	64.9	46.6	23.8	17.4	12.8	12.8
102.5°	38.4	40.2	49.3	74.0	109.6	99.6	84.1	79.5	54.8	43.9	42.0
105°	97.8	96.8	104.2	123.3	153.5	150.8	138.9	126.1	108.7	100.5	100.5
107.5°	128.8	128.8	135.2	151.7	174.5	203.7	206.5	163.5	143.4	134.3	133.4
110°	145.3	145.3	150.8	164.5	194.6	235.7	233.9	201.9	177.3	165.4	163.5



REPORT NUMBER: P833684
 CATALOG NUMBER: TTN-D2-830-U-MQ-UPL2

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	148.9	149.8	157.1	178.2	211.1	229.3	221.1	208.3	197.4	188.2	186.4
115°	154.4	154.4	162.6	182.7	201.0	208.3	199.2	189.1	181.8	178.2	180.0
117.5°	152.6	155.3	157.1	168.1	180.0	185.5	180.9	167.2	161.7	159.9	157.1
120°	141.6	141.6	143.4	148.9	155.3	158.1	156.2	147.1	142.5	141.6	139.8
122.5°	126.1	127.0	126.1	128.8	133.4	136.1	134.3	127.0	125.2	125.2	123.3
125°	110.6	110.6	109.6	111.5	114.2	113.3	114.2	110.6	109.6	109.6	108.7
127.5°	99.6	98.7	96.8	97.8	98.7	98.7	99.6	95.9	96.8	97.8	96.8
130°	88.6	88.6	86.8	86.8	86.8	85.0	86.8	85.0	85.9	86.8	87.7
132.5°	78.6	78.6	75.8	74.9	74.9	74.9	75.8	74.9	76.7	78.6	78.6
135°	70.4	70.4	67.6	68.5	68.5	67.6	68.5	67.6	69.4	70.4	70.4
137.5°	64.0	64.0	62.1	62.1	62.1	61.2	62.1	62.1	63.0	64.9	65.8
140°	58.5	58.5	57.6	57.6	56.6	57.6	57.6	57.6	58.5	59.4	59.4
142.5°	55.7	54.8	53.9	53.0	53.9	53.9	53.9	53.0	53.9	55.7	55.7
145°	51.2	51.2	50.3	50.3	50.3	51.2	50.3	50.3	51.2	51.2	52.1
147.5°	48.4	48.4	47.5	48.4	48.4	48.4	48.4	47.5	48.4	48.4	49.3
150°	47.5	46.6	45.7	46.6	46.6	45.7	45.7	45.7	45.7	46.6	46.6
152.5°	44.8	44.8	43.9	44.8	43.9	43.9	43.9	43.9	43.9	44.8	45.7
155°	42.9	42.9	42.0	42.9	42.9	42.9	42.9	42.9	42.9	42.9	42.9
157.5°	41.1	42.0	41.1	41.1	41.1	41.1	41.1	41.1	41.1	42.0	42.0
160°	40.2	40.2	40.2	40.2	39.3	39.3	39.3	40.2	40.2	40.2	41.1
162.5°	39.3	39.3	39.3	39.3	38.4	38.4	38.4	38.4	39.3	39.3	40.2
165°	39.3	38.4	38.4	38.4	37.5	37.5	37.5	37.5	38.4	39.3	38.4
167.5°	37.5	37.5	37.5	37.5	37.5	36.5	36.5	37.5	37.5	37.5	38.4
170°	37.5	37.5	36.5	36.5	36.5	36.5	36.5	36.5	36.5	36.5	37.5
172.5°	37.5	37.5	37.5	37.5	36.5	36.5	36.5	36.5	36.5	37.5	37.5
175°	37.5	37.5	37.5	37.5	36.5	36.5	36.5	37.5	37.5	37.5	36.5
177.5°	37.5	37.5	37.5	37.5	36.5	37.5	37.5	37.5	37.5	37.5	37.5
180°	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5

(END OF REPORT)