

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P639656

Luminaire Tested: GWS-SA5C-730-U-T3R-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P639656
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA5C-730-U-T3R-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (5) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III ROADWAY OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (80) 3000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 19011.1 lumens
Efficiency: N/A
Efficacy: 120.7 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G3

Input Watts (W): 157.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P639656

CATALOG NUMBER: GWS-SA5C-730-U-T3R-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 7.6 fc
 Type II - Short - N/A

REPORT NUMBER: P639656
CATALOG NUMBER: GWS-SA5C-730-U-T3R-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 79-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P639656

CATALOG NUMBER: GWS-SA5C-730-U-T3R-W-GRSWH

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 5651.1 | 0.0 | 5651.1 |
| | % Fixture | 29.7 | 0.0 | 29.7 |
| Street Side | Lumens | 13360.0 | 0.0 | 13360.0 |
| | % Fixture | 70.3 | 0.0 | 70.3 |
| Total | Lumens | 19011.1 | 0.0 | 19011.1 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 436.3 | 2.3 |
| 10°-20° | 1212.5 | 6.4 |
| 20°-30° | 2055.3 | 10.8 |
| 30°-40° | 3145.9 | 16.5 |
| 40°-50° | 4194.7 | 22.1 |
| 50°-60° | 4844.6 | 25.5 |
| 60°-70° | 2517.4 | 13.2 |
| 70°-80° | 535.1 | 2.8 |
| 80°-90° | 69.3 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 19011.1 | 100.0 |
| 0°-180° | 19011.1 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P639656


CATALOG NUMBER: GWS-SA5C-730-U-T3R-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 2099.3 | 11.0 | | | |
| FM (30°-60°) | 9186.7 | 48.3 | | | |
| FH (60°-80°) | 2049.9 | 10.8 | | | G2/5000 |
| FVH (80°-90°) | 24.2 | 0.1 | | | G1/100 |
| BL (0°-30°) | 1604.9 | 8.4 | B3/2500 | | |
| BM (30°-60°) | 2998.4 | 15.8 | B3/5000 | | |
| BH (60°-80°) | 1002.7 | 5.3 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 45.2 | 0.2 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G3

Type II Short





REPORT NUMBER: P639656

CATALOG NUMBER: GWS-SA5C-730-U-T3R-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 79° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 4711.4 | 4711.4 | 4711.4 | 4711.4 | 4711.4 | 4711.4 | 4711.4 | 4711.4 | 4711.4 | 4711.4 | 4711.4 |
| 2.5° | 4496.9 | 4487.6 | 4490.7 | 4503.1 | 4549.7 | 4583.9 | 4619.7 | 4652.3 | 4683.4 | 4692.7 | 4700.5 |
| 5° | 4336.8 | 4319.7 | 4324.3 | 4344.6 | 4399.0 | 4456.5 | 4520.2 | 4597.9 | 4672.5 | 4697.4 | 4730.0 |
| 7.5° | 4223.3 | 4220.2 | 4228.0 | 4259.1 | 4316.6 | 4371.0 | 4453.4 | 4563.7 | 4692.7 | 4734.7 | 4792.2 |
| 10° | 4072.5 | 4066.3 | 4097.4 | 4161.1 | 4256.0 | 4343.0 | 4440.9 | 4571.5 | 4751.8 | 4814.0 | 4902.6 |
| 12.5° | 3952.8 | 3949.7 | 3982.4 | 4071.0 | 4192.2 | 4330.6 | 4465.8 | 4611.9 | 4831.1 | 4916.6 | 5025.4 |
| 15° | 4022.8 | 4008.8 | 4010.4 | 4072.5 | 4181.3 | 4344.6 | 4528.0 | 4685.0 | 4910.4 | 5019.2 | 5159.1 |
| 17.5° | 4226.4 | 4201.5 | 4182.9 | 4193.8 | 4256.0 | 4425.4 | 4622.8 | 4782.9 | 5002.1 | 5129.5 | 5300.5 |
| 20° | 4507.8 | 4493.8 | 4442.5 | 4408.3 | 4422.3 | 4571.5 | 4772.0 | 4921.2 | 5121.8 | 5264.8 | 5448.2 |
| 22.5° | 4885.5 | 4851.3 | 4781.3 | 4726.9 | 4685.0 | 4801.5 | 4986.5 | 5115.5 | 5288.1 | 5437.3 | 5628.5 |
| 25° | 5353.4 | 5303.6 | 5193.3 | 5107.8 | 5017.6 | 5137.3 | 5302.1 | 5400.0 | 5516.6 | 5654.9 | 5836.8 |
| 27.5° | 5830.6 | 5788.6 | 5665.8 | 5550.8 | 5438.8 | 5513.5 | 5709.3 | 5765.3 | 5752.8 | 5853.9 | 6009.3 |
| 30° | 6338.8 | 6286.0 | 6169.4 | 6045.1 | 5900.5 | 5948.7 | 6124.3 | 6152.3 | 6020.2 | 6104.1 | 6209.8 |
| 32.5° | 6875.1 | 6823.8 | 6722.8 | 6578.2 | 6415.0 | 6433.7 | 6481.9 | 6508.3 | 6382.4 | 6430.6 | 6511.4 |
| 35° | 7420.7 | 7372.5 | 7269.9 | 7126.9 | 7007.2 | 6893.8 | 6772.5 | 6878.2 | 6805.2 | 6898.4 | 6892.2 |
| 37.5° | 7919.7 | 7871.5 | 7807.8 | 7697.4 | 7492.2 | 7268.4 | 6988.6 | 7119.2 | 7232.6 | 7350.8 | 7330.6 |
| 40° | 8257.0 | 8224.3 | 8239.9 | 8222.8 | 7958.5 | 7515.5 | 7094.3 | 7237.3 | 7546.6 | 7748.7 | 7737.8 |
| 42.5° | 8547.7 | 8515.0 | 8605.2 | 8670.5 | 8359.6 | 7744.0 | 7145.6 | 7282.4 | 7747.1 | 8062.7 | 8047.1 |
| 45° | 8676.7 | 8667.3 | 8816.6 | 9023.3 | 8726.4 | 7986.5 | 7277.7 | 7375.6 | 7899.5 | 8303.6 | 8244.5 |
| 47.5° | 8522.8 | 8555.4 | 8849.2 | 9198.9 | 9031.1 | 8274.1 | 7548.2 | 7573.0 | 8098.4 | 8564.8 | 8398.4 |
| 50° | 8216.6 | 8288.1 | 8684.4 | 9203.6 | 9253.4 | 8598.9 | 7922.8 | 7860.6 | 8365.8 | 8843.0 | 8479.3 |
| 52.5° | 7770.5 | 7845.1 | 8491.7 | 9167.9 | 9380.8 | 8975.1 | 8421.7 | 8333.1 | 8703.1 | 9121.2 | 8493.2 |
| 55° | 6746.1 | 6847.1 | 8050.2 | 9087.0 | 9505.2 | 9317.1 | 8984.4 | 8804.1 | 9138.3 | 9503.6 | 8631.6 |
| 57.5° | 5852.3 | 5905.2 | 6974.6 | 8728.0 | 9530.0 | 9568.9 | 9385.5 | 9171.0 | 9570.4 | 9917.1 | 8787.0 |
| 60° | 4294.8 | 4307.2 | 5269.4 | 7221.7 | 8766.8 | 9422.8 | 9352.8 | 9034.2 | 9365.3 | 9586.0 | 8075.1 |
| 62.5° | 2426.4 | 2428.0 | 3195.8 | 4820.2 | 6548.7 | 7680.3 | 7723.8 | 7442.5 | 7164.2 | 7229.5 | 5620.7 |
| 65° | 910.9 | 996.4 | 1459.6 | 2368.9 | 3775.6 | 4534.2 | 4714.5 | 4779.8 | 4316.6 | 4029.0 | 3014.0 |
| 67.5° | 609.3 | 629.5 | 851.8 | 1218.7 | 1680.3 | 1939.9 | 2169.9 | 2176.2 | 1591.7 | 1419.2 | 1187.6 |
| 70° | 464.8 | 485.0 | 669.9 | 872.0 | 851.8 | 786.5 | 850.3 | 826.9 | 854.9 | 878.2 | 903.1 |
| 72.5° | 346.6 | 366.8 | 519.2 | 615.5 | 511.4 | 503.6 | 570.5 | 634.2 | 693.3 | 718.1 | 757.0 |
| 75° | 230.1 | 245.6 | 349.7 | 329.5 | 282.9 | 334.2 | 416.6 | 480.3 | 514.5 | 544.0 | 573.6 |
| 77.5° | 146.1 | 157.0 | 186.5 | 150.8 | 157.0 | 195.9 | 242.5 | 300.0 | 332.6 | 362.2 | 377.7 |
| 80° | 66.8 | 65.3 | 63.7 | 71.5 | 88.6 | 115.0 | 146.1 | 180.3 | 205.2 | 217.6 | 226.9 |
| 82.5° | 26.4 | 29.5 | 32.6 | 38.9 | 48.2 | 62.2 | 82.4 | 105.7 | 125.9 | 129.0 | 136.8 |
| 85° | 10.9 | 12.4 | 14.0 | 17.1 | 21.8 | 28.0 | 34.2 | 48.2 | 60.6 | 65.3 | 69.9 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 1.6 | 3.1 | 4.7 | 7.8 | 14.0 | 15.5 | 17.1 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P639656

CATALOG NUMBER: GWS-SA5C-730-U-T3R-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 4711.4 | 4711.4 | 4711.4 | 4711.4 | 4711.4 | 4711.4 | 4711.4 | 4711.4 | 4711.4 | 4711.4 | 4711.4 |
| 2.5° | 4742.5 | 4722.3 | 4756.5 | 4779.8 | 4801.5 | 4778.2 | 4770.5 | 4750.3 | 4747.1 | 4747.1 | 4758.0 |
| 5° | 4786.0 | 4772.0 | 4807.8 | 4821.8 | 4820.2 | 4768.9 | 4737.8 | 4697.4 | 4677.2 | 4677.2 | 4680.3 |
| 7.5° | 4863.7 | 4855.9 | 4876.2 | 4854.4 | 4804.7 | 4700.5 | 4597.9 | 4512.4 | 4454.9 | 4425.4 | 4434.7 |
| 10° | 4992.7 | 4983.4 | 4966.3 | 4885.5 | 4742.5 | 4526.4 | 4316.6 | 4161.1 | 4067.9 | 4015.0 | 4018.1 |
| 12.5° | 5118.6 | 5103.1 | 5042.5 | 4863.7 | 4569.9 | 4226.4 | 3951.3 | 3777.2 | 3674.6 | 3612.4 | 3598.4 |
| 15° | 5257.0 | 5216.6 | 5086.0 | 4751.8 | 4288.6 | 3859.6 | 3572.0 | 3383.9 | 3273.6 | 3236.3 | 3234.7 |
| 17.5° | 5389.1 | 5317.6 | 5081.3 | 4552.8 | 3951.3 | 3475.6 | 3186.5 | 3069.9 | 3051.3 | 3068.4 | 3073.1 |
| 20° | 5522.8 | 5407.8 | 5030.0 | 4277.7 | 3550.3 | 3093.3 | 2944.0 | 2992.2 | 3062.2 | 3108.8 | 3119.7 |
| 22.5° | 5661.1 | 5482.4 | 4913.5 | 3923.3 | 3127.5 | 2835.2 | 2897.4 | 3003.1 | 3090.1 | 3152.3 | 3158.5 |
| 25° | 5816.6 | 5552.3 | 4739.4 | 3489.6 | 2788.6 | 2763.7 | 2886.5 | 2998.4 | 3091.7 | 3163.2 | 3175.6 |
| 27.5° | 5905.2 | 5553.9 | 4495.3 | 3043.5 | 2633.2 | 2735.7 | 2860.1 | 2965.8 | 3059.1 | 3136.8 | 3150.8 |
| 30° | 5992.2 | 5511.9 | 4108.3 | 2681.3 | 2588.1 | 2703.1 | 2815.0 | 2912.9 | 3001.5 | 3077.7 | 3094.8 |
| 32.5° | 6115.0 | 5473.0 | 3662.2 | 2473.1 | 2561.7 | 2672.0 | 2763.7 | 2850.8 | 2919.2 | 2953.4 | 2962.7 |
| 35° | 6267.3 | 5423.3 | 3188.1 | 2382.9 | 2544.6 | 2647.1 | 2728.0 | 2774.6 | 2686.0 | 2667.4 | 2687.6 |
| 37.5° | 6480.3 | 5376.7 | 2715.5 | 2344.0 | 2533.7 | 2637.8 | 2709.3 | 2589.6 | 2480.8 | 2437.3 | 2452.8 |
| 40° | 6710.4 | 5350.2 | 2395.3 | 2312.9 | 2538.3 | 2647.1 | 2631.6 | 2454.4 | 2297.4 | 2205.7 | 2202.6 |
| 42.5° | 6906.2 | 5309.8 | 2190.2 | 2292.7 | 2550.8 | 2682.9 | 2525.9 | 2334.7 | 2101.6 | 2047.1 | 2048.7 |
| 45° | 7038.3 | 5207.2 | 2081.3 | 2271.0 | 2561.7 | 2690.7 | 2476.2 | 2169.9 | 2003.6 | 1969.4 | 1967.9 |
| 47.5° | 7092.7 | 5020.7 | 2011.4 | 2236.8 | 2560.1 | 2626.9 | 2375.1 | 2101.6 | 1935.2 | 1925.9 | 1932.1 |
| 50° | 7057.0 | 4714.5 | 1939.9 | 2169.9 | 2522.8 | 2560.1 | 2258.5 | 2040.9 | 1888.6 | 1939.9 | 1977.2 |
| 52.5° | 6924.9 | 4318.1 | 1854.4 | 2078.2 | 2456.0 | 2483.9 | 2199.5 | 2003.6 | 1854.4 | 1922.8 | 1952.3 |
| 55° | 6890.7 | 3996.4 | 1745.6 | 1958.5 | 2356.5 | 2348.7 | 2137.3 | 1985.0 | 1831.1 | 1804.7 | 1809.3 |
| 57.5° | 6845.6 | 3682.4 | 1565.3 | 1744.0 | 2104.7 | 2117.1 | 2078.2 | 1963.2 | 1770.5 | 1762.7 | 1770.5 |
| 60° | 5947.1 | 2822.8 | 1395.9 | 1504.7 | 1728.5 | 1795.3 | 2011.4 | 1922.8 | 1672.5 | 1639.9 | 1638.3 |
| 62.5° | 3884.4 | 1709.8 | 1242.0 | 1311.9 | 1408.3 | 1486.0 | 1834.2 | 1806.2 | 1565.3 | 1545.1 | 1559.1 |
| 65° | 2089.1 | 1218.7 | 1130.0 | 1172.0 | 1224.9 | 1283.9 | 1520.2 | 1608.8 | 1414.5 | 1343.0 | 1344.6 |
| 67.5° | 1067.9 | 1036.8 | 1046.1 | 1075.6 | 1116.1 | 1145.6 | 1226.4 | 1304.1 | 1206.2 | 1145.6 | 1144.0 |
| 70° | 914.0 | 938.9 | 952.8 | 969.9 | 996.4 | 991.7 | 999.5 | 1013.5 | 1005.7 | 976.2 | 974.6 |
| 72.5° | 778.8 | 817.6 | 820.7 | 823.8 | 833.2 | 811.4 | 797.4 | 774.1 | 775.6 | 780.3 | 781.9 |
| 75° | 592.2 | 629.5 | 638.9 | 634.2 | 643.5 | 615.5 | 596.9 | 573.6 | 545.6 | 540.9 | 544.0 |
| 77.5° | 385.5 | 415.0 | 429.0 | 425.9 | 430.6 | 408.8 | 399.5 | 374.6 | 342.0 | 329.5 | 329.5 |
| 80° | 233.2 | 250.3 | 261.1 | 264.2 | 268.9 | 253.4 | 237.8 | 216.1 | 202.1 | 188.1 | 188.1 |
| 82.5° | 141.5 | 152.3 | 160.1 | 160.1 | 164.8 | 147.7 | 135.2 | 119.7 | 113.5 | 101.0 | 101.0 |
| 85° | 71.5 | 79.3 | 82.4 | 80.8 | 77.7 | 63.7 | 59.1 | 51.3 | 48.2 | 42.0 | 42.0 |
| 87.5° | 17.1 | 21.8 | 21.8 | 15.5 | 15.5 | 7.8 | 4.7 | 1.6 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-2-R4

Test Date: 10/03/2019

Luminaire Tested: SA1C-730-U-5WQ

Data in this report applies to families of products SA1C-730-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-2-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-730-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-2-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. (1) 70 CRI, 3000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2993
 CIE u': 0.2508
 CIE v': 0.5215
 Duv: 0.0000
 CIE x: 0.4374
 CIE y: 0.4043
 CIE z: 0.1583
 Peak Wavelength (nm): 593
 Dominant Wavelength (nm): 582
 Purity: 53

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.8 | | |
| R1: | 67.5 | R9: | -38.3 |
| R2: | 82.9 | R10: | 62.5 |
| R3: | 94.7 | R11: | 63.7 |
| R4: | 67.7 | R12: | 57.8 |
| R5: | 67.9 | R13: | 70.4 |
| R6: | 77.6 | R14: | 97.3 |
| R7: | 76.0 | | |
| R8: | 40.5 | | |

Rf: 75.7
 Rg: 93.9



Test Conditions

Stabilization Time: 53M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-2-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-2-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-2-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 8494.8

S/P: 1.23

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3101.5 M/P: 0.45

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Summary

$R_f = 75.7$
 $R_g = 93.9$
 CIE $R_a = 71.8$
 $R_9 = -38.3$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 67 | CES51 = 87 | CES76 = 63 |
| CES02 = 63 | CES27 = 88 | CES52 = 86 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 78 | CES78 = 67 |
| CES04 = 71 | CES29 = 66 | CES54 = 84 | CES79 = 87 |
| CES05 = 49 | CES30 = 73 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 70 | CES56 = 75 | CES81 = 71 |
| CES07 = 41 | CES32 = 65 | CES57 = 74 | CES82 = 94 |
| CES08 = 40 | CES33 = 73 | CES58 = 76 | CES83 = 90 |
| CES09 = 29 | CES34 = 79 | CES59 = 85 | CES84 = 89 |
| CES10 = 76 | CES35 = 89 | CES60 = 93 | CES85 = 77 |
| CES11 = 59 | CES36 = 97 | CES61 = 84 | CES86 = 61 |
| CES12 = 65 | CES37 = 87 | CES62 = 91 | CES87 = 78 |
| CES13 = 43 | CES38 = 81 | CES63 = 77 | CES88 = 77 |
| CES14 = 74 | CES39 = 95 | CES64 = 72 | CES89 = 67 |
| CES15 = 71 | CES40 = 92 | CES65 = 68 | CES90 = 76 |
| CES16 = 47 | CES41 = 88 | CES66 = 69 | CES91 = 89 |
| CES17 = 50 | CES42 = 89 | CES67 = 67 | CES92 = 58 |
| CES18 = 56 | CES43 = 79 | CES68 = 72 | CES93 = 74 |
| CES19 = 73 | CES44 = 99 | CES69 = 81 | CES94 = 49 |
| CES20 = 66 | CES45 = 85 | CES70 = 66 | CES95 = 68 |
| CES21 = 87 | CES46 = 80 | CES71 = 67 | CES96 = 76 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 69 | CES73 = 59 | CES98 = 75 |
| CES24 = 91 | CES49 = 80 | CES74 = 95 | CES99 = 62 |
| CES25 = 73 | CES50 = 87 | CES75 = 69 | |



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Measure Comparisons



(END OF REPORT)