

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P643637

Luminaire Tested: GWS-SA6F-735-U-RW-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P643637
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-51)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA6F-735-U-RW-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (6) LIGHTSQUARES WITH 16 LEDS EACH AND RECTANGULAR WIDE OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (96) 3500K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 43272.8 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')
IES Classification: Type V - Short
BUG Rating: B5 - U0 - G2

Input Watts (W): 372.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P643637

CATALOG NUMBER: GWS-SA6F-735-U-RW-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 8.8 fc
 Type V - Short - N/A

REPORT NUMBER: P643637
CATALOG NUMBER: GWS-SA6F-735-U-RW-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 49-Deg Lateral - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P643637

CATALOG NUMBER: GWS-SA6F-735-U-RW-W-GRSWH

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 21424.1 | 0.0 | 21424.1 |
| | % Fixture | 49.5 | 0.0 | 49.5 |
| Street Side | Lumens | 21848.7 | 0.0 | 21848.7 |
| | % Fixture | 50.5 | 0.0 | 50.5 |
| Total | Lumens | 43272.8 | 0.0 | 43272.8 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 699.3 | 1.6 |
| 10°-20° | 2306.5 | 5.3 |
| 20°-30° | 4393.3 | 10.2 |
| 30°-40° | 7447.5 | 17.2 |
| 40°-50° | 11208.0 | 25.9 |
| 50°-60° | 12268.2 | 28.4 |
| 60°-70° | 3879.3 | 9.0 |
| 70°-80° | 931.0 | 2.2 |
| 80°-90° | 139.7 | 0.3 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 43272.8 | 100.0 |
| 0°-180° | 43272.8 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P643637


CATALOG NUMBER: GWS-SA6F-735-U-RW-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 3741.3 | 8.6 | | | |
| FM (30°-60°) | 15709.2 | 36.3 | | | |
| FH (60°-80°) | 2333.4 | 5.4 | | | G2/5000 |
| FVH (80°-90°) | 64.7 | 0.1 | | | G1/100 |
| BL (0°-30°) | 3657.7 | 8.5 | B4/5000 | | |
| BM (30°-60°) | 15214.5 | 35.2 | B5 | | |
| BH (60°-80°) | 2476.9 | 5.7 | B3/2500 | | G2/5000 |
| BVH (80°-90°) | 75.0 | 0.2 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B5-U0-G2

Type V Short





REPORT NUMBER: P643637

CATALOG NUMBER: GWS-SA6F-735-U-RW-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 49° | 55° | 65° | 75° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 7168.4 | 7168.4 | 7168.4 | 7168.4 | 7168.4 | 7168.4 | 7168.4 | 7168.4 | 7168.4 | 7168.4 | 7168.4 |
| 2.5° | 7062.8 | 7069.9 | 7083.9 | 7108.6 | 7133.2 | 7168.4 | 7182.5 | 7200.1 | 7196.6 | 7217.7 | 7217.7 |
| 5° | 7027.6 | 7038.2 | 7059.3 | 7094.5 | 7136.7 | 7203.6 | 7221.2 | 7263.4 | 7305.6 | 7358.4 | 7376.0 |
| 7.5° | 7069.9 | 7083.9 | 7108.6 | 7164.9 | 7228.2 | 7316.2 | 7351.4 | 7421.8 | 7502.7 | 7597.7 | 7636.4 |
| 10° | 7150.8 | 7168.4 | 7210.6 | 7302.1 | 7404.2 | 7537.9 | 7569.6 | 7657.6 | 7787.8 | 7918.0 | 7995.4 |
| 12.5° | 7242.3 | 7270.5 | 7347.9 | 7492.2 | 7643.5 | 7819.4 | 7868.7 | 7977.8 | 8118.6 | 8287.5 | 8393.0 |
| 15° | 7347.9 | 7372.5 | 7492.2 | 7696.3 | 7932.0 | 8164.3 | 8220.6 | 8326.2 | 8484.5 | 8649.9 | 8797.7 |
| 17.5° | 7569.6 | 7611.8 | 7752.6 | 7988.4 | 8262.8 | 8537.3 | 8600.7 | 8720.3 | 8847.0 | 8977.2 | 9118.0 |
| 20° | 7872.2 | 7907.4 | 8086.9 | 8379.0 | 8702.7 | 8952.6 | 9015.9 | 9121.5 | 9181.3 | 9248.2 | 9367.8 |
| 22.5° | 8174.9 | 8224.1 | 8428.2 | 8773.1 | 9153.2 | 9424.1 | 9473.4 | 9571.9 | 9529.7 | 9508.6 | 9586.0 |
| 25° | 8551.4 | 8618.3 | 8818.9 | 9195.4 | 9582.5 | 9916.8 | 9955.5 | 10040.0 | 9969.6 | 9860.5 | 9857.0 |
| 27.5° | 9019.4 | 9079.3 | 9286.9 | 9674.0 | 10057.6 | 10406.0 | 10479.9 | 10592.5 | 10437.6 | 10303.9 | 10208.9 |
| 30° | 9575.5 | 9614.2 | 9842.9 | 10254.7 | 10648.8 | 10979.6 | 11074.6 | 11187.2 | 11071.1 | 10849.4 | 10754.4 |
| 32.5° | 10223.0 | 10275.8 | 10539.7 | 10972.5 | 11324.5 | 11655.3 | 11750.3 | 11891.0 | 11764.3 | 11514.5 | 11394.8 |
| 35° | 11000.7 | 11053.5 | 11331.5 | 11803.1 | 12162.0 | 12503.4 | 12570.2 | 12686.3 | 12528.0 | 12239.4 | 12144.4 |
| 37.5° | 11845.3 | 11912.1 | 12264.1 | 12711.0 | 13087.5 | 13485.2 | 13488.7 | 13523.9 | 13298.7 | 12939.7 | 12834.1 |
| 40° | 12795.4 | 12883.4 | 13235.3 | 13699.8 | 14153.8 | 14477.6 | 14474.0 | 14375.5 | 13995.5 | 13439.4 | 13277.6 |
| 42.5° | 13735.0 | 13805.4 | 14160.8 | 14639.4 | 15093.4 | 15399.6 | 15308.1 | 15068.8 | 14519.8 | 13763.2 | 13548.5 |
| 45° | 14414.2 | 14467.0 | 14840.0 | 15378.5 | 15839.5 | 16029.5 | 15864.1 | 15575.5 | 14833.0 | 13967.3 | 13650.6 |
| 47.5° | 14734.5 | 14804.8 | 15181.4 | 15716.3 | 16237.1 | 16346.2 | 16149.1 | 15878.2 | 15016.0 | 14157.3 | 13731.5 |
| 50° | 14562.0 | 14653.5 | 15079.3 | 15575.5 | 16163.2 | 16388.4 | 16247.7 | 15976.7 | 15209.5 | 14343.8 | 13875.8 |
| 52.5° | 14115.1 | 14203.1 | 14741.5 | 15343.3 | 16008.4 | 16455.3 | 16451.8 | 16230.1 | 15431.2 | 14396.6 | 13882.8 |
| 55° | 12587.8 | 12760.2 | 13597.8 | 14635.9 | 15818.3 | 16652.4 | 16736.8 | 16501.0 | 15466.4 | 14410.7 | 13956.7 |
| 57.5° | 8192.5 | 8495.1 | 9290.4 | 10641.8 | 13013.6 | 15146.2 | 15716.3 | 15772.6 | 15213.1 | 14350.9 | 13970.8 |
| 60° | 3420.6 | 3663.4 | 4293.3 | 5190.7 | 7150.8 | 9688.1 | 10793.1 | 11901.6 | 13238.8 | 13724.5 | 13840.6 |
| 62.5° | 2125.5 | 2146.6 | 2210.0 | 2414.1 | 3068.7 | 4307.4 | 5018.2 | 6056.4 | 8044.7 | 9737.3 | 10518.6 |
| 65° | 1917.9 | 1928.5 | 1942.5 | 1928.5 | 1960.1 | 2111.5 | 2301.5 | 2664.0 | 3473.3 | 4314.4 | 5313.8 |
| 67.5° | 1689.2 | 1703.2 | 1713.8 | 1703.2 | 1713.8 | 1720.8 | 1742.0 | 1773.6 | 1921.4 | 2041.1 | 2132.6 |
| 70° | 1365.4 | 1386.5 | 1404.1 | 1397.1 | 1439.3 | 1439.3 | 1460.4 | 1485.1 | 1559.0 | 1646.9 | 1710.3 |
| 72.5° | 1041.7 | 1024.1 | 1045.2 | 1052.2 | 1090.9 | 1112.0 | 1143.7 | 1171.9 | 1256.3 | 1309.1 | 1390.0 |
| 75° | 675.7 | 658.1 | 689.7 | 707.3 | 760.1 | 788.3 | 816.4 | 844.6 | 904.4 | 939.6 | 1017.0 |
| 77.5° | 366.0 | 362.5 | 394.1 | 418.8 | 475.1 | 510.3 | 531.4 | 552.5 | 601.8 | 612.3 | 661.6 |
| 80° | 211.1 | 211.1 | 232.3 | 249.9 | 285.0 | 323.8 | 344.9 | 362.5 | 397.7 | 408.2 | 429.3 |
| 82.5° | 116.1 | 116.1 | 126.7 | 137.2 | 165.4 | 186.5 | 204.1 | 218.2 | 249.9 | 260.4 | 271.0 |
| 85° | 56.3 | 52.8 | 59.8 | 66.9 | 77.4 | 88.0 | 98.5 | 105.6 | 130.2 | 137.2 | 151.3 |
| 87.5° | 7.0 | 7.0 | 7.0 | 10.6 | 14.1 | 21.1 | 24.6 | 24.6 | 38.7 | 45.7 | 52.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P643637

CATALOG NUMBER: GWS-SA6F-735-U-RW-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 7168.4 | 7168.4 | 7168.4 | 7168.4 | 7168.4 | 7168.4 | 7168.4 | 7168.4 | 7168.4 | 7168.4 | 7168.4 |
| 2.5° | 7238.8 | 7193.0 | 7221.2 | 7231.7 | 7231.7 | 7221.2 | 7175.4 | 7161.4 | 7140.2 | 7108.6 | 7108.6 |
| 5° | 7400.7 | 7365.5 | 7372.5 | 7354.9 | 7312.7 | 7259.9 | 7175.4 | 7133.2 | 7098.0 | 7059.3 | 7055.8 |
| 7.5° | 7678.7 | 7632.9 | 7625.9 | 7559.0 | 7446.4 | 7333.8 | 7207.1 | 7129.7 | 7076.9 | 7027.6 | 7024.1 |
| 10° | 8041.1 | 7998.9 | 7946.1 | 7812.4 | 7647.0 | 7481.6 | 7309.2 | 7203.6 | 7126.2 | 7055.8 | 7052.3 |
| 12.5° | 8445.8 | 8396.6 | 8298.0 | 8101.0 | 7893.3 | 7731.5 | 7534.4 | 7372.5 | 7256.4 | 7161.4 | 7143.8 |
| 15° | 8885.7 | 8815.3 | 8646.4 | 8414.2 | 8210.1 | 8037.6 | 7826.5 | 7594.2 | 7418.3 | 7266.9 | 7249.3 |
| 17.5° | 9223.6 | 9132.1 | 8949.1 | 8730.9 | 8562.0 | 8389.5 | 8115.0 | 7823.0 | 7569.6 | 7379.5 | 7351.4 |
| 20° | 9455.8 | 9381.9 | 9174.3 | 9012.4 | 8913.9 | 8762.6 | 8442.3 | 8111.5 | 7826.5 | 7587.2 | 7573.1 |
| 22.5° | 9670.5 | 9582.5 | 9378.4 | 9283.4 | 9283.4 | 9181.3 | 8875.2 | 8484.5 | 8150.2 | 7872.2 | 7837.0 |
| 25° | 9913.3 | 9818.3 | 9663.4 | 9652.9 | 9702.2 | 9656.4 | 9286.9 | 8868.1 | 8477.5 | 8164.3 | 8108.0 |
| 27.5° | 10251.1 | 10145.6 | 10054.1 | 10117.4 | 10187.8 | 10138.5 | 9726.8 | 9241.2 | 8829.4 | 8512.7 | 8463.4 |
| 30° | 10789.6 | 10659.3 | 10574.9 | 10652.3 | 10789.6 | 10645.3 | 10198.3 | 9684.6 | 9269.3 | 8920.9 | 8896.3 |
| 32.5° | 11416.0 | 11268.2 | 11180.2 | 11303.3 | 11426.5 | 11201.3 | 10757.9 | 10265.2 | 9828.8 | 9462.9 | 9420.6 |
| 35° | 12169.0 | 11982.5 | 11852.3 | 12017.7 | 12144.4 | 11922.7 | 11482.8 | 11014.8 | 10529.1 | 10149.1 | 10092.8 |
| 37.5° | 12837.7 | 12612.4 | 12524.5 | 12756.7 | 12925.6 | 12781.4 | 12302.8 | 11862.9 | 11331.5 | 10916.2 | 10891.6 |
| 40° | 13323.3 | 13101.6 | 13038.3 | 13421.8 | 13717.4 | 13682.3 | 13252.9 | 12749.7 | 12250.0 | 11771.4 | 11725.6 |
| 42.5° | 13534.4 | 13379.6 | 13393.7 | 13911.0 | 14368.5 | 14593.7 | 14210.1 | 13671.7 | 13189.6 | 12693.4 | 12661.7 |
| 45° | 13580.2 | 13485.2 | 13597.8 | 14245.3 | 14847.1 | 15308.1 | 14980.8 | 14530.4 | 13984.9 | 13506.3 | 13492.2 |
| 47.5° | 13629.5 | 13576.7 | 13749.1 | 14435.3 | 15149.7 | 15684.6 | 15501.6 | 15037.1 | 14484.6 | 14016.6 | 13981.4 |
| 50° | 13745.6 | 13724.5 | 13918.0 | 14569.1 | 15294.0 | 15786.7 | 15579.0 | 15118.0 | 14551.5 | 14090.5 | 14006.0 |
| 52.5° | 13780.8 | 13745.6 | 14023.6 | 14776.7 | 15533.3 | 15783.2 | 15336.2 | 14734.5 | 14164.4 | 13650.6 | 13562.6 |
| 55° | 13889.9 | 13826.5 | 14016.6 | 14854.1 | 15864.1 | 15987.3 | 15322.2 | 14421.3 | 13625.9 | 12925.6 | 12718.0 |
| 57.5° | 13918.0 | 13847.6 | 13970.8 | 14727.4 | 15505.1 | 15396.1 | 13467.6 | 11637.7 | 10138.5 | 9360.8 | 9448.8 |
| 60° | 13766.7 | 13787.8 | 13576.7 | 13492.2 | 12436.5 | 10979.6 | 8245.2 | 6591.3 | 5176.6 | 4578.3 | 4708.6 |
| 62.5° | 10479.9 | 10567.9 | 9846.4 | 8562.0 | 6584.2 | 5218.8 | 3452.2 | 2681.6 | 2269.8 | 2164.2 | 2181.8 |
| 65° | 5289.2 | 5408.9 | 4659.3 | 3853.4 | 2864.5 | 2315.6 | 2002.4 | 1939.0 | 1917.9 | 1893.3 | 1893.3 |
| 67.5° | 2093.9 | 2129.1 | 2100.9 | 1967.2 | 1829.9 | 1780.7 | 1766.6 | 1759.5 | 1734.9 | 1720.8 | 1724.4 |
| 70° | 1682.1 | 1710.3 | 1668.1 | 1583.6 | 1527.3 | 1523.8 | 1516.7 | 1502.7 | 1485.1 | 1485.1 | 1495.6 |
| 72.5° | 1372.4 | 1400.6 | 1340.8 | 1288.0 | 1245.8 | 1214.1 | 1196.5 | 1185.9 | 1161.3 | 1161.3 | 1171.9 |
| 75° | 1010.0 | 1027.6 | 978.3 | 971.3 | 925.5 | 893.9 | 865.7 | 851.6 | 819.9 | 805.9 | 816.4 |
| 77.5° | 672.1 | 668.6 | 644.0 | 644.0 | 626.4 | 587.7 | 556.0 | 524.3 | 482.1 | 454.0 | 461.0 |
| 80° | 436.4 | 436.4 | 425.8 | 425.8 | 408.2 | 376.5 | 337.8 | 306.2 | 281.5 | 260.4 | 260.4 |
| 82.5° | 278.0 | 274.5 | 271.0 | 267.5 | 260.4 | 228.7 | 200.6 | 179.5 | 161.9 | 147.8 | 151.3 |
| 85° | 154.8 | 154.8 | 147.8 | 147.8 | 133.7 | 116.1 | 102.1 | 88.0 | 77.4 | 73.9 | 73.9 |
| 87.5° | 52.8 | 52.8 | 49.3 | 49.3 | 42.2 | 31.7 | 24.6 | 21.1 | 17.6 | 14.1 | 17.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

All Brands

Data applicable to all product families using SA light engines

Report Number: SP1-2101-121-7

Luminaire Tested: IFLD-S-SA2A-735-U-T2

Test Date: 03/04/2021

Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/04/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-735-U-T2**
 Description: STREETWORKS INF FLOOD

PROGRAMMED @ 615mA.

Spectral Parameters

CCT (K): 3388
 CIE u': 0.2371
 CIE v': 0.5177
 Duv: 0.0032
 CIE x: 0.4153
 CIE y: 0.4030
 CIE z: 0.1817
 Peak Wavelength (nm): 590
 Dominant Wavelength (nm): 580
 Purity: 45.7

 Rf: 76.9
 Rg: 94.4

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 73.1 | | |
| R1: | 68.9 | R9: | -34.6 |
| R2: | 81.1 | R10: | 57.8 |
| R3: | 93.1 | R11: | 68.6 |
| R4: | 71.6 | R12: | 53.9 |
| R5: | 69.4 | R13: | 70.9 |
| R6: | 75.0 | R14: | 96.2 |
| R7: | 79.5 | | |
| R8: | 46.4 | | |

Test Conditions

Stabilization Time: 81M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0/30%
 Sphere Temperature (°C): 24.1



REPORT NUMBER: SP1-2101-121-7

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-121-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-7

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 4.9 | 620 | 136720 | 35.6 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 8.0 | 625 | 126308 | 27.9 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 12.1 | 630 | 114625 | 20.7 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 18.1 | 635 | 103216 | 15.5 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 25.4 | 640 | 92605 | 11.1 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 33.9 | 645 | 83234 | 8.0 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 43.0 | 650 | 73263 | 5.4 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 50.1 | 655 | 64627 | 3.7 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 57.9 | 660 | 56614 | 2.4 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.0 | 535 | 103269 | 64.0 | 665 | 49537 | 1.6 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.0 | 540 | 107316 | 69.9 | 670 | 42866 | 0.9 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.0 | 545 | 113101 | 75.3 | 675 | 36708 | 0.6 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 0.0 | 550 | 120690 | 82.0 | 680 | 31814 | 0.4 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 0.1 | 555 | 128583 | 87.8 | 685 | 27485 | 0.2 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 0.3 | 560 | 137796 | 93.6 | 690 | 23698 | 0.1 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 0.8 | 565 | 146577 | 97.5 | 695 | 20309 | 0.1 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 1.6 | 570 | 154581 | 100.5 | 700 | 17890 | 0.1 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 2.4 | 575 | 162633 | 101.2 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 2.5 | 580 | 168101 | 99.9 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 2.1 | 585 | 173145 | 96.2 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 1.8 | 590 | 174675 | 90.3 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 1.7 | 595 | 173724 | 82.3 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 1.5 | 600 | 171241 | 73.8 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 1.7 | 605 | 165134 | 64.0 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 2.2 | 610 | 156652 | 53.8 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 3.3 | 615 | 147879 | 44.6 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-7

Scotopic Flux vs. Wavelength



Scotopic Lumens: 12126

S/P: 1.36

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 53.2 | 620 | 136720 | 1.7 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 71.7 | 625 | 126308 | 1.1 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 91.4 | 630 | 114625 | 0.6 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 110.0 | 635 | 103216 | 0.4 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 125.1 | 640 | 92605 | 0.2 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 135.7 | 645 | 83234 | 0.1 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 140.8 | 650 | 73263 | 0.1 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 139.6 | 655 | 64627 | 0.1 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 135.7 | 660 | 56614 | 0.0 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.1 | 535 | 103269 | 128.7 | 665 | 49537 | 0.0 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.2 | 540 | 107316 | 118.6 | 670 | 42866 | 0.0 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.6 | 545 | 113101 | 108.4 | 675 | 36708 | 0.0 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 2.0 | 550 | 120690 | 98.7 | 680 | 31814 | 0.0 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 5.9 | 555 | 128583 | 87.9 | 685 | 27485 | 0.0 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 14.3 | 560 | 137796 | 77.0 | 690 | 23698 | 0.0 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 30.5 | 565 | 146577 | 65.8 | 695 | 20309 | 0.0 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 55.5 | 570 | 154581 | 54.6 | 700 | 17890 | 0.0 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 77.4 | 575 | 162633 | 44.3 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 73.6 | 580 | 168101 | 34.6 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 53.7 | 585 | 173145 | 26.5 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 41.9 | 590 | 174675 | 19.5 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 34.3 | 595 | 173724 | 13.9 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 27.9 | 600 | 171241 | 9.7 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 27.1 | 605 | 165134 | 6.5 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 31.3 | 610 | 156652 | 4.2 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 40.0 | 615 | 147879 | 2.7 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: 4490.7 M/P: 0.5

| λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 28.8 | 620 | 136720 | 0.1 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 36.6 | 625 | 126308 | 0.1 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 43.9 | 630 | 114625 | 0.0 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 49.6 | 635 | 103216 | 0.0 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 53.0 | 640 | 92605 | 0.0 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 53.5 | 645 | 83234 | 0.0 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 51.6 | 650 | 73263 | 0.0 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 47.3 | 655 | 64627 | 0.0 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 42.5 | 660 | 56614 | 0.0 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.0 | 535 | 103269 | 37.2 | 665 | 49537 | 0.0 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.1 | 540 | 107316 | 31.4 | 670 | 42866 | 0.0 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.4 | 545 | 113101 | 26.3 | 675 | 36708 | 0.0 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 1.4 | 550 | 120690 | 21.7 | 680 | 31814 | 0.0 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 3.7 | 555 | 128583 | 17.3 | 685 | 27485 | 0.0 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 8.9 | 560 | 137796 | 13.6 | 690 | 23698 | 0.0 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 18.2 | 565 | 146577 | 10.3 | 695 | 20309 | 0.0 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 33.2 | 570 | 154581 | 7.6 | 700 | 17890 | 0.0 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 45.6 | 575 | 162633 | 5.4 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 43.8 | 580 | 168101 | 3.8 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 32.2 | 585 | 173145 | 2.6 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 25.6 | 590 | 174675 | 1.7 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 21.2 | 595 | 173724 | 1.1 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 17.4 | 600 | 171241 | 0.7 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 16.6 | 605 | 165134 | 0.5 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 18.6 | 610 | 156652 | 0.3 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 22.7 | 615 | 147879 | 0.2 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

Summary

$R_f = 76.9$
 $R_g = 94.4$
 CIE $R_a = 73.1$
 $R_g = -34.6$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 68 | CES51 = 90 | CES76 = 63 |
| CES02 = 62 | CES27 = 88 | CES52 = 89 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 80 | CES78 = 65 |
| CES04 = 70 | CES29 = 67 | CES54 = 84 | CES79 = 87 |
| CES05 = 48 | CES30 = 74 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 71 | CES56 = 75 | CES81 = 75 |
| CES07 = 40 | CES32 = 67 | CES57 = 74 | CES82 = 94 |
| CES08 = 39 | CES33 = 74 | CES58 = 76 | CES83 = 91 |
| CES09 = 29 | CES34 = 78 | CES59 = 87 | CES84 = 89 |
| CES10 = 75 | CES35 = 89 | CES60 = 93 | CES85 = 80 |
| CES11 = 58 | CES36 = 98 | CES61 = 86 | CES86 = 66 |
| CES12 = 64 | CES37 = 86 | CES62 = 89 | CES87 = 79 |
| CES13 = 43 | CES38 = 82 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 95 | CES64 = 74 | CES89 = 70 |
| CES15 = 71 | CES40 = 91 | CES65 = 68 | CES90 = 77 |
| CES16 = 47 | CES41 = 89 | CES66 = 71 | CES91 = 88 |
| CES17 = 50 | CES42 = 88 | CES67 = 69 | CES92 = 60 |
| CES18 = 56 | CES43 = 82 | CES68 = 74 | CES93 = 77 |
| CES19 = 72 | CES44 = 99 | CES69 = 82 | CES94 = 52 |
| CES20 = 65 | CES45 = 87 | CES70 = 67 | CES95 = 69 |
| CES21 = 86 | CES46 = 82 | CES71 = 66 | CES96 = 78 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 85 |
| CES23 = 92 | CES48 = 72 | CES73 = 59 | CES98 = 76 |
| CES24 = 91 | CES49 = 82 | CES74 = 97 | CES99 = 63 |
| CES25 = 72 | CES50 = 88 | CES75 = 66 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)