

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P833698

Luminaire Tested: **TTN-D2-830-U-WQ-UPL1**

Issue Date: 5/15/2024

Test Information

Test Method: LM-79-08
Report Number: P833698
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND
Test Lab: INNOVATION CENTER
Issue Date: 5/15/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: TTN-D2-830-U-WQ-UPL1
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT
3000K, 80 CRI LEDS AND WIDE DISTRIBUTION
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5031.9 lumens
Efficiency: N/A
Efficacy: 111.6 lumens/watt
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')
IES Classification: Type V - Short
BUG Rating: B2 - U3 - G2


Input Watts (W): 45.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P833698
 CATALOG NUMBER: TTN-D2-830-U-WQ-UPL1

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.7 fc
 Type V - Short - N/A

REPORT NUMBER: P833698
CATALOG NUMBER: TTN-D2-830-U-WQ-UPL1

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P833698
 CATALOG NUMBER: TTN-D2-830-U-WQ-UPL1


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2368.2	147.7	2515.9
	% Fixture	47.1	2.9	50.0
Street Side	Lumens	2368.2	147.7	2515.9
	% Fixture	47.1	2.9	50.0
Total	Lumens	4736.4	295.5	5031.9
	% Fixture	94.1	5.9	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.7	0.7
10°-20°	120.4	2.4
20°-30°	252.6	5.0
30°-40°	458.4	9.1
40°-50°	747.2	14.8
50°-60°	1045.9	20.8
60°-70°	1091.8	21.7
70°-80°	780.1	15.5
80°-90°	202.2	4.0
90°-100°	6.6	0.1
100°-110°	67.0	1.3
110°-120°	98.0	1.9
120°-130°	56.9	1.1
130°-140°	30.1	0.6
140°-150°	17.9	0.4
150°-160°	11.0	0.2
160°-170°	6.0	0.1
170°-180°	2.0	0.0
0°-90°	4736.4	94.1
0°-180°	5031.9	100.0

Coefficient of Utilization




REPORT NUMBER: P833698
 CATALOG NUMBER: TTN-D2-830-U-WQ-UPL1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	205.4	4.1			
FM (30°-60°)	1125.7	22.4			
FH (60°-80°)	936.0	18.6			G1/1800
FVH (80°-90°)	101.1	2.0			G2/225
BL (0°-30°)	205.4	4.1	B1/500		
BM (30°-60°)	1125.7	22.4	B2/2500		
BH (60°-80°)	936.0	18.6	B2/1000		G1/1800
BVH (80°-90°)	101.1	2.0			G2/225
UL (90°-100°)	6.6	0.1		U1/10	
UH (100°-180°)	288.9	5.7		U3/500	

BUG Rating: B2-U3-G2

Type V Short





REPORT NUMBER: P833698
 CATALOG NUMBER: TTN-D2-830-U-WQ-UPL1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	401.4	401.4	401.4	401.4	401.4	401.4	401.4	401.4	401.4	401.4	401.4
2.5°	397.5	397.5	397.5	397.5	397.5	397.5	397.5	397.5	397.5	397.5	397.5
5°	397.5	397.5	397.5	397.5	397.5	397.5	397.5	397.5	397.5	397.5	397.5
7.5°	389.7	389.7	393.6	393.6	393.6	393.6	393.6	393.6	393.6	393.6	393.6
10°	389.7	389.7	393.6	393.6	397.5	397.5	397.5	393.6	393.6	389.7	389.7
12.5°	397.5	397.5	397.5	401.4	405.3	405.3	405.3	401.4	401.4	397.5	397.5
15°	409.2	413.1	413.1	417.0	420.9	420.9	420.9	417.0	417.0	413.1	413.1
17.5°	432.6	432.6	432.6	436.5	440.4	444.3	444.3	436.5	436.5	432.6	436.5
20°	456.0	459.9	459.9	463.8	467.7	471.6	467.7	463.8	459.9	459.9	459.9
22.5°	491.1	491.1	495.0	495.0	502.8	502.8	502.8	495.0	495.0	495.0	495.0
25°	530.1	530.1	534.0	537.9	545.6	545.6	541.8	534.0	534.0	534.0	537.9
27.5°	576.8	576.8	580.7	580.7	588.5	588.5	584.6	580.7	580.7	580.7	584.6
30°	619.7	619.7	627.5	631.4	635.3	635.3	635.3	627.5	627.5	623.6	623.6
32.5°	658.7	662.6	666.5	678.2	686.0	682.1	686.0	678.2	670.4	666.5	666.5
35°	701.5	705.4	713.2	724.9	736.6	736.6	736.6	724.9	717.1	709.3	713.2
37.5°	752.2	752.2	763.9	775.6	791.2	795.1	791.2	779.5	767.8	760.0	760.0
40°	806.8	806.8	818.5	830.2	849.7	853.5	849.7	834.1	818.5	814.6	814.6
42.5°	861.3	861.3	876.9	888.6	912.0	919.8	912.0	892.5	876.9	865.2	869.1
45°	919.8	923.7	943.2	966.6	993.9	1005.6	993.9	970.5	947.1	923.7	923.7
47.5°	986.1	986.1	1009.4	1036.7	1067.9	1079.6	1064.0	1040.6	1009.4	990.0	990.0
50°	1028.9	1032.8	1064.0	1099.1	1138.1	1145.9	1134.2	1099.1	1064.0	1036.7	1032.8
52.5°	1071.8	1075.7	1110.8	1161.5	1200.4	1212.1	1196.5	1161.5	1110.8	1075.7	1075.7
55°	1099.1	1106.9	1145.9	1200.4	1243.3	1262.8	1239.4	1200.4	1142.0	1103.0	1099.1
57.5°	1103.0	1110.8	1149.8	1216.0	1258.9	1282.3	1262.8	1212.1	1149.8	1106.9	1103.0
60°	1095.2	1099.1	1138.1	1208.2	1258.9	1274.5	1258.9	1204.3	1134.2	1099.1	1091.3
62.5°	1075.7	1083.5	1122.5	1180.9	1239.4	1251.1	1235.5	1177.0	1118.6	1075.7	1067.9
65°	1013.3	1021.1	1079.6	1138.1	1188.7	1200.4	1188.7	1138.1	1075.7	1013.3	1005.6
67.5°	943.2	947.1	1005.6	1075.7	1122.5	1142.0	1122.5	1079.6	1001.7	943.2	935.4
70°	869.1	873.0	919.8	993.9	1040.6	1064.0	1044.5	997.8	915.9	865.2	861.3
72.5°	783.4	783.4	830.2	888.6	935.4	958.8	943.2	884.7	822.4	771.7	763.9
75°	666.5	670.4	721.0	763.9	814.6	830.2	814.6	767.8	709.3	658.7	650.9
77.5°	545.6	549.5	592.4	627.5	674.3	686.0	674.3	635.3	580.7	537.9	534.0
80°	413.1	417.0	452.1	483.3	522.3	537.9	526.2	487.2	444.3	405.3	393.6
82.5°	268.9	272.8	307.9	331.3	366.4	378.1	370.3	335.2	300.1	261.1	257.2
85°	120.8	124.7	155.9	175.4	202.7	214.4	206.6	175.4	148.1	113.0	105.2
87.5°	11.7	11.7	11.7	11.7	11.7	15.6	15.6	11.7	11.7	11.7	11.7
90°	2.5	2.5	3.0	3.0	3.0	3.0	3.0	3.0	3.0	2.5	2.5
92.5°	2.5	2.5	2.5	3.5	4.0	3.5	4.0	3.0	3.0	2.5	2.5
95°	3.0	3.0	3.5	4.5	5.6	6.1	6.1	3.5	3.5	3.0	3.0
97.5°	4.0	4.5	4.5	5.6	9.1	16.7	10.1	5.1	5.1	4.5	4.0
100°	6.6	7.1	7.1	12.6	26.8	35.9	25.8	13.1	9.6	7.1	7.1
102.5°	21.2	22.2	27.3	40.9	60.7	55.1	46.5	44.0	30.3	24.3	23.3
105°	54.1	53.6	57.6	68.2	84.9	83.4	76.8	69.8	60.2	55.6	55.6
107.5°	71.3	71.3	74.8	83.9	96.6	112.7	114.2	90.5	79.4	74.3	73.8
110°	80.4	80.4	83.4	91.0	107.7	130.4	129.4	111.7	98.1	91.5	90.5



REPORT NUMBER: P833698
 CATALOG NUMBER: TTN-D2-830-U-WQ-UPL1

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	82.4	82.9	86.9	98.6	116.8	126.9	122.3	115.3	109.2	104.1	103.1
115°	85.4	85.4	90.0	101.1	111.2	115.3	110.2	104.6	100.6	98.6	99.6
117.5°	84.4	85.9	86.9	93.0	99.6	102.6	100.1	92.5	89.5	88.5	86.9
120°	78.4	78.4	79.4	82.4	85.9	87.5	86.4	81.4	78.9	78.4	77.3
122.5°	69.8	70.3	69.8	71.3	73.8	75.3	74.3	70.3	69.3	69.3	68.2
125°	61.2	61.2	60.7	61.7	63.2	62.7	63.2	61.2	60.7	60.7	60.2
127.5°	55.1	54.6	53.6	54.1	54.6	54.6	55.1	53.1	53.6	54.1	53.6
130°	49.0	49.0	48.0	48.0	48.0	47.0	48.0	47.0	47.5	48.0	48.5
132.5°	43.5	43.5	42.0	41.5	41.5	41.5	42.0	41.5	42.5	43.5	43.5
135°	38.9	38.9	37.4	37.9	37.9	37.4	37.9	37.4	38.4	38.9	38.9
137.5°	35.4	35.4	34.4	34.4	34.4	33.9	34.4	34.4	34.9	35.9	36.4
140°	32.4	32.4	31.8	31.8	31.3	31.8	31.8	31.8	32.4	32.9	32.9
142.5°	30.8	30.3	29.8	29.3	29.8	29.8	29.8	29.3	29.8	30.8	30.8
145°	28.3	28.3	27.8	27.8	27.8	28.3	27.8	27.8	28.3	28.3	28.8
147.5°	26.8	26.8	26.3	26.8	26.8	26.8	26.8	26.3	26.8	26.8	27.3
150°	26.3	25.8	25.3	25.8	25.8	25.3	25.3	25.3	25.3	25.8	25.8
152.5°	24.8	24.8	24.3	24.8	24.3	24.3	24.3	24.3	24.3	24.8	25.3
155°	23.8	23.8	23.3	23.8	23.8	23.8	23.8	23.8	23.8	23.8	23.8
157.5°	22.7	23.3	22.7	22.7	22.7	22.7	22.7	22.7	22.7	23.3	23.3
160°	22.2	22.2	22.2	22.2	21.7	21.7	21.7	22.2	22.2	22.2	22.7
162.5°	21.7	21.7	21.7	21.7	21.2	21.2	21.2	21.2	21.7	21.7	22.2
165°	21.7	21.2	21.2	21.2	20.7	20.7	20.7	20.7	21.2	21.7	21.2
167.5°	20.7	20.7	20.7	20.7	20.7	20.2	20.2	20.7	20.7	20.7	21.2
170°	20.7	20.7	20.2	20.2	20.2	20.2	20.2	20.2	20.2	20.2	20.7
172.5°	20.7	20.7	20.7	20.7	20.2	20.2	20.2	20.2	20.2	20.7	20.7
175°	20.7	20.7	20.7	20.7	20.2	20.2	20.2	20.7	20.7	20.7	20.2
177.5°	20.7	20.7	20.7	20.7	20.2	20.7	20.7	20.7	20.7	20.7	20.7
180°	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7

(END OF REPORT)