

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P834042

Luminaire Tested: **TTN-D3-830-U-MQ-CG-UPL3**

Issue Date: 5/15/2024

**Test Information**

Test Method: LM-79-08  
Report Number: P834042  
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND  
Test Lab: INNOVATION CENTER  
Issue Date: 5/15/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TTN-D3-830-U-MQ-CG-UPL3  
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT  
3000K, 80 CRI LEDS AND MEDIUM DISTRIBUTION WITH CLEAR GLASS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7133.7 lumens  
Efficiency: N/A  
Efficacy: 107.8 lumens/watt  
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')  
IES Classification: Type V - Short  
BUG Rating: B2 - U4 - G1  
  
Input Watts (W): 66.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P834042  
 CATALOG NUMBER: TTN-D3-830-U-MQ-CG-UPL3

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2.4 fc  
 Type V - Short - N/A

REPORT NUMBER: P834042  
CATALOG NUMBER: TTN-D3-830-U-MQ-CG-UPL3

### Luminous Intensity Polar Plot



REPORT NUMBER: P834042  
 CATALOG NUMBER: TTN-D3-830-U-MQ-CG-UPL3


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 3196.5   | 370.3  | 3566.8 |
|                    | % Fixture | 44.8     | 5.2    | 50.0   |
| <b>Street Side</b> | Lumens    | 3196.5   | 370.3  | 3566.8 |
|                    | % Fixture | 44.8     | 5.2    | 50.0   |
| <b>Total</b>       | Lumens    | 6393.0   | 740.7  | 7133.7 |
|                    | % Fixture | 89.6     | 10.4   | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 142.8  | 2.0       |
| 10°-20°   | 413.1  | 5.8       |
| 20°-30°   | 664.6  | 9.3       |
| 30°-40°   | 887.8  | 12.4      |
| 40°-50°   | 1078.6 | 15.1      |
| 50°-60°   | 1253.3 | 17.6      |
| 60°-70°   | 1156.3 | 16.2      |
| 70°-80°   | 676.9  | 9.5       |
| 80°-90°   | 119.6  | 1.7       |
| 90°-100°  | 16.5   | 0.2       |
| 100°-110° | 168.0  | 2.4       |
| 110°-120° | 245.6  | 3.4       |
| 120°-130° | 142.5  | 2.0       |
| 130°-140° | 75.5   | 1.1       |
| 140°-150° | 44.9   | 0.6       |
| 150°-160° | 27.6   | 0.4       |
| 160°-170° | 15.1   | 0.2       |
| 170°-180° | 4.9    | 0.1       |
| 0°-90°    | 6393.0 | 89.6      |
| 0°-180°   | 7133.7 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P834042  
 CATALOG NUMBER: TTN-D3-830-U-MQ-CG-UPL3

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |         |         |
|----------------|--------|-----------|-------------------------|---------|---------|
|                |        |           | B                       | U       | G       |
| FL (0°-30°)    | 610.3  | 8.6       |                         |         |         |
| FM (30°-60°)   | 1609.9 | 22.6      |                         |         |         |
| FH (60°-80°)   | 916.6  | 12.8      |                         |         | G1/1800 |
| FVH (80°-90°)  | 59.8   | 0.8       |                         |         | G1/100  |
| BL (0°-30°)    | 610.3  | 8.6       | B2/1000                 |         |         |
| BM (30°-60°)   | 1609.9 | 22.6      | B2/2500                 |         |         |
| BH (60°-80°)   | 916.6  | 12.8      | B2/1000                 |         | G1/1800 |
| BVH (80°-90°)  | 59.8   | 0.8       |                         |         | G1/100  |
| UL (90°-100°)  | 16.5   | 0.2       |                         | U2/50   |         |
| UH (100°-180°) | 724.2  | 10.2      |                         | U4/1000 |         |

**BUG Rating: B2-U4-G1**  
 Type V Short





REPORT NUMBER: P834042

CATALOG NUMBER: TTN-D3-830-U-MQ-CG-UPL3

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1520.6 | 1520.6 | 1520.6 | 1520.6 | 1520.6 | 1520.6 | 1520.6 | 1520.6 | 1520.6 | 1520.6 | 1520.6 |
| 2.5°   | 1505.1 | 1510.3 | 1505.1 | 1505.1 | 1505.1 | 1505.1 | 1505.1 | 1505.1 | 1505.1 | 1505.1 | 1510.3 |
| 5°     | 1510.3 | 1510.3 | 1510.3 | 1510.3 | 1505.1 | 1505.1 | 1505.1 | 1505.1 | 1505.1 | 1510.3 | 1510.3 |
| 7.5°   | 1494.7 | 1494.7 | 1494.7 | 1494.7 | 1494.7 | 1489.5 | 1494.7 | 1494.7 | 1494.7 | 1494.7 | 1494.7 |
| 10°    | 1479.1 | 1479.1 | 1479.1 | 1479.1 | 1479.1 | 1479.1 | 1479.1 | 1479.1 | 1479.1 | 1479.1 | 1479.1 |
| 12.5°  | 1468.7 | 1468.7 | 1468.7 | 1468.7 | 1468.7 | 1468.7 | 1468.7 | 1468.7 | 1468.7 | 1463.6 | 1463.6 |
| 15°    | 1458.4 | 1458.4 | 1458.4 | 1458.4 | 1463.6 | 1463.6 | 1458.4 | 1458.4 | 1458.4 | 1458.4 | 1458.4 |
| 17.5°  | 1448.0 | 1448.0 | 1448.0 | 1448.0 | 1453.2 | 1453.2 | 1453.2 | 1448.0 | 1448.0 | 1448.0 | 1448.0 |
| 20°    | 1437.6 | 1437.6 | 1437.6 | 1437.6 | 1442.8 | 1442.8 | 1442.8 | 1442.8 | 1442.8 | 1437.6 | 1437.6 |
| 22.5°  | 1432.4 | 1432.4 | 1432.4 | 1432.4 | 1437.6 | 1437.6 | 1437.6 | 1437.6 | 1432.4 | 1432.4 | 1432.4 |
| 25°    | 1427.2 | 1432.4 | 1432.4 | 1432.4 | 1437.6 | 1442.8 | 1442.8 | 1437.6 | 1432.4 | 1427.2 | 1427.2 |
| 27.5°  | 1432.4 | 1432.4 | 1432.4 | 1437.6 | 1437.6 | 1442.8 | 1442.8 | 1437.6 | 1432.4 | 1432.4 | 1432.4 |
| 30°    | 1427.2 | 1427.2 | 1427.2 | 1432.4 | 1437.6 | 1442.8 | 1437.6 | 1437.6 | 1432.4 | 1427.2 | 1427.2 |
| 32.5°  | 1416.8 | 1416.8 | 1422.0 | 1427.2 | 1432.4 | 1432.4 | 1432.4 | 1427.2 | 1422.0 | 1416.8 | 1416.8 |
| 35°    | 1406.5 | 1406.5 | 1406.5 | 1411.7 | 1422.0 | 1422.0 | 1422.0 | 1416.8 | 1411.7 | 1406.5 | 1401.3 |
| 37.5°  | 1390.9 | 1396.1 | 1396.1 | 1406.5 | 1411.7 | 1416.8 | 1411.7 | 1406.5 | 1396.1 | 1390.9 | 1390.9 |
| 40°    | 1380.5 | 1380.5 | 1385.7 | 1396.1 | 1406.5 | 1406.5 | 1401.3 | 1396.1 | 1385.7 | 1380.5 | 1380.5 |
| 42.5°  | 1364.9 | 1364.9 | 1375.3 | 1385.7 | 1401.3 | 1401.3 | 1396.1 | 1385.7 | 1375.3 | 1364.9 | 1364.9 |
| 45°    | 1364.9 | 1364.9 | 1375.3 | 1396.1 | 1406.5 | 1416.8 | 1406.5 | 1396.1 | 1375.3 | 1364.9 | 1359.8 |
| 47.5°  | 1370.1 | 1370.1 | 1380.5 | 1406.5 | 1427.2 | 1437.6 | 1422.0 | 1401.3 | 1380.5 | 1370.1 | 1364.9 |
| 50°    | 1359.8 | 1364.9 | 1385.7 | 1411.7 | 1437.6 | 1442.8 | 1437.6 | 1406.5 | 1385.7 | 1359.8 | 1359.8 |
| 52.5°  | 1364.9 | 1364.9 | 1390.9 | 1432.4 | 1458.4 | 1468.7 | 1458.4 | 1432.4 | 1385.7 | 1359.8 | 1359.8 |
| 55°    | 1354.6 | 1349.4 | 1385.7 | 1432.4 | 1473.9 | 1494.7 | 1473.9 | 1432.4 | 1380.5 | 1349.4 | 1344.2 |
| 57.5°  | 1307.9 | 1307.9 | 1354.6 | 1401.3 | 1453.2 | 1463.6 | 1448.0 | 1401.3 | 1349.4 | 1307.9 | 1297.5 |
| 60°    | 1245.6 | 1250.8 | 1297.5 | 1349.4 | 1396.1 | 1401.3 | 1390.9 | 1349.4 | 1297.5 | 1250.8 | 1235.2 |
| 62.5°  | 1178.1 | 1188.5 | 1235.2 | 1287.1 | 1344.2 | 1354.6 | 1339.0 | 1287.1 | 1224.8 | 1193.7 | 1167.7 |
| 65°    | 1079.5 | 1095.1 | 1147.0 | 1204.1 | 1266.3 | 1261.1 | 1261.1 | 1198.9 | 1152.2 | 1100.3 | 1074.3 |
| 67.5°  | 970.5  | 986.1  | 1022.4 | 1100.3 | 1152.2 | 1147.0 | 1141.8 | 1100.3 | 1022.4 | 986.1  | 970.5  |
| 70°    | 851.1  | 861.5  | 897.9  | 975.7  | 1022.4 | 1027.6 | 1012.0 | 970.5  | 897.9  | 871.9  | 846.0  |
| 72.5°  | 711.0  | 716.2  | 768.1  | 830.4  | 877.1  | 871.9  | 866.7  | 830.4  | 762.9  | 737.0  | 705.8  |
| 75°    | 560.5  | 565.7  | 612.4  | 669.5  | 705.8  | 700.6  | 695.4  | 669.5  | 612.4  | 581.3  | 555.3  |
| 77.5°  | 420.4  | 415.2  | 461.9  | 503.4  | 524.2  | 529.4  | 519.0  | 498.2  | 456.7  | 430.8  | 415.2  |
| 80°    | 275.1  | 269.9  | 311.4  | 342.5  | 358.1  | 358.1  | 352.9  | 337.3  | 306.2  | 285.4  | 275.1  |
| 82.5°  | 155.7  | 150.5  | 176.5  | 197.2  | 212.8  | 207.6  | 202.4  | 192.0  | 176.5  | 160.9  | 150.5  |
| 85°    | 57.1   | 57.1   | 72.7   | 83.0   | 93.4   | 93.4   | 88.2   | 83.0   | 67.5   | 62.3   | 57.1   |
| 87.5°  | 5.2    | 5.2    | 10.4   | 15.6   | 15.6   | 15.6   | 10.4   | 10.4   | 5.2    | 5.2    | 5.2    |
| 90°    | 6.3    | 6.3    | 7.6    | 7.6    | 7.6    | 7.6    | 7.6    | 7.6    | 7.6    | 6.3    | 6.3    |
| 92.5°  | 6.3    | 6.3    | 6.3    | 8.9    | 10.1   | 8.9    | 10.1   | 7.6    | 7.6    | 6.3    | 6.3    |
| 95°    | 7.6    | 7.6    | 8.9    | 11.4   | 13.9   | 15.2   | 15.2   | 8.9    | 8.9    | 7.6    | 7.6    |
| 97.5°  | 10.1   | 11.4   | 11.4   | 13.9   | 22.8   | 41.8   | 25.3   | 12.7   | 12.7   | 11.4   | 10.1   |
| 100°   | 16.5   | 17.7   | 17.7   | 31.7   | 67.2   | 90.0   | 64.6   | 32.9   | 24.1   | 17.7   | 17.7   |
| 102.5° | 53.2   | 55.8   | 68.4   | 102.6  | 152.1  | 138.1  | 116.6  | 110.2  | 76.0   | 60.8   | 58.3   |
| 105°   | 135.6  | 134.3  | 144.5  | 171.1  | 212.9  | 209.1  | 192.6  | 174.9  | 150.8  | 139.4  | 139.4  |
| 107.5° | 178.7  | 178.7  | 187.5  | 210.4  | 242.0  | 282.6  | 286.4  | 226.8  | 198.9  | 186.3  | 185.0  |
| 110°   | 201.5  | 201.5  | 209.1  | 228.1  | 269.9  | 326.9  | 324.4  | 280.0  | 245.8  | 229.4  | 226.8  |



REPORT NUMBER: P834042

CATALOG NUMBER: TTN-D3-830-U-MQ-CG-UPL3

**CANDELA DISTRIBUTION (continued):**

|        | 0°    | 5°    | 15°   | 25°   | 35°   | 45°   | 55°   | 65°   | 75°   | 85°   | 90°   |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 112.5° | 206.5 | 207.8 | 218.0 | 247.1 | 292.7 | 318.1 | 306.7 | 288.9 | 273.7 | 261.0 | 258.5 |
| 115°   | 214.2 | 214.2 | 225.6 | 253.4 | 278.8 | 288.9 | 276.2 | 262.3 | 252.2 | 247.1 | 249.6 |
| 117.5° | 211.6 | 215.4 | 218.0 | 233.2 | 249.6 | 257.2 | 250.9 | 231.9 | 224.3 | 221.8 | 218.0 |
| 120°   | 196.4 | 196.4 | 198.9 | 206.5 | 215.4 | 219.2 | 216.7 | 204.0 | 197.7 | 196.4 | 193.9 |
| 122.5° | 174.9 | 176.1 | 174.9 | 178.7 | 185.0 | 188.8 | 186.3 | 176.1 | 173.6 | 173.6 | 171.1 |
| 125°   | 153.3 | 153.3 | 152.1 | 154.6 | 158.4 | 157.1 | 158.4 | 153.3 | 152.1 | 152.1 | 150.8 |
| 127.5° | 138.1 | 136.9 | 134.3 | 135.6 | 136.9 | 136.9 | 138.1 | 133.1 | 134.3 | 135.6 | 134.3 |
| 130°   | 122.9 | 122.9 | 120.4 | 120.4 | 120.4 | 117.8 | 120.4 | 117.8 | 119.1 | 120.4 | 121.6 |
| 132.5° | 109.0 | 109.0 | 105.2 | 103.9 | 103.9 | 103.9 | 105.2 | 103.9 | 106.4 | 109.0 | 109.0 |
| 135°   | 97.6  | 97.6  | 93.8  | 95.0  | 95.0  | 93.8  | 95.0  | 93.8  | 96.3  | 97.6  | 97.6  |
| 137.5° | 88.7  | 88.7  | 86.2  | 86.2  | 86.2  | 84.9  | 86.2  | 86.2  | 87.4  | 90.0  | 91.2  |
| 140°   | 81.1  | 81.1  | 79.8  | 79.8  | 78.6  | 79.8  | 79.8  | 79.8  | 81.1  | 82.4  | 82.4  |
| 142.5° | 77.3  | 76.0  | 74.8  | 73.5  | 74.8  | 74.8  | 74.8  | 73.5  | 74.8  | 77.3  | 77.3  |
| 145°   | 71.0  | 71.0  | 69.7  | 69.7  | 69.7  | 71.0  | 69.7  | 69.7  | 71.0  | 71.0  | 72.2  |
| 147.5° | 67.2  | 67.2  | 65.9  | 67.2  | 67.2  | 67.2  | 67.2  | 65.9  | 67.2  | 67.2  | 68.4  |
| 150°   | 65.9  | 64.6  | 63.4  | 64.6  | 64.6  | 63.4  | 63.4  | 63.4  | 63.4  | 64.6  | 64.6  |
| 152.5° | 62.1  | 62.1  | 60.8  | 62.1  | 60.8  | 60.8  | 60.8  | 60.8  | 60.8  | 62.1  | 63.4  |
| 155°   | 59.6  | 59.6  | 58.3  | 59.6  | 59.6  | 59.6  | 59.6  | 59.6  | 59.6  | 59.6  | 59.6  |
| 157.5° | 57.0  | 58.3  | 57.0  | 57.0  | 57.0  | 57.0  | 57.0  | 57.0  | 57.0  | 58.3  | 58.3  |
| 160°   | 55.8  | 55.8  | 55.8  | 55.8  | 54.5  | 54.5  | 54.5  | 55.8  | 55.8  | 55.8  | 57.0  |
| 162.5° | 54.5  | 54.5  | 54.5  | 54.5  | 53.2  | 53.2  | 53.2  | 53.2  | 54.5  | 54.5  | 55.8  |
| 165°   | 54.5  | 53.2  | 53.2  | 53.2  | 52.0  | 52.0  | 52.0  | 52.0  | 53.2  | 54.5  | 53.2  |
| 167.5° | 52.0  | 52.0  | 52.0  | 52.0  | 52.0  | 50.7  | 50.7  | 52.0  | 52.0  | 52.0  | 53.2  |
| 170°   | 52.0  | 52.0  | 50.7  | 50.7  | 50.7  | 50.7  | 50.7  | 50.7  | 50.7  | 50.7  | 52.0  |
| 172.5° | 52.0  | 52.0  | 52.0  | 52.0  | 50.7  | 50.7  | 50.7  | 50.7  | 50.7  | 52.0  | 52.0  |
| 175°   | 52.0  | 52.0  | 52.0  | 52.0  | 50.7  | 50.7  | 50.7  | 52.0  | 52.0  | 52.0  | 50.7  |
| 177.5° | 52.0  | 52.0  | 52.0  | 52.0  | 50.7  | 52.0  | 52.0  | 52.0  | 52.0  | 52.0  | 52.0  |
| 180°   | 52.0  | 52.0  | 52.0  | 52.0  | 52.0  | 52.0  | 52.0  | 52.0  | 52.0  | 52.0  | 52.0  |



Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW EDISON

Report Number: SP1-2411-284-4

Test Date: 11/22/2024

Luminaire Tested: TTN-D0-830-U-WQ

Data in this report applies to TT and TTN families of products


**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2411-284-4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 11/22/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: MCGRAW EDISON  
 Catalog Number: **TTN-D0-830-U-WQ**  
 Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE. 3000K, 80 CRI LEDS AND WIDE DISTRIBUTION

**Spectral Parameters**

CCT (K): 2963  
 CIE u': 0.2515  
 CIE v': 0.5238  
 Duv: 0.0012  
 CIE x: 0.4414  
 CIE y: 0.4086  
 CIE z: 0.1501  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 582  
 Purity: 55.12798  
 R<sub>f</sub>: 86.1  
 R<sub>g</sub>: 94.9

|           |      |      |      |
|-----------|------|------|------|
| CRI (Ra): | 82.9 |      |      |
| R1:       | 81.4 | R9:  | 3.9  |
| R2:       | 91.9 | R10: | 82.5 |
| R3:       | 95.2 | R11: | 82.3 |
| R4:       | 81.6 | R12: | 76.5 |
| R5:       | 82.3 | R13: | 83.9 |
| R6:       | 91.4 | R14: | 97.8 |
| R7:       | 82.0 | R15: | 72.6 |
| R8:       | 57.2 |      |      |



**Test Conditions**


Stabilization Time: 37M  
 Operation Time: 1H 37M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2411-284-4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/22/2024       | 10/22/2025           |
| DC Power Source                | IN0208                | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | IN0085                | 10/22/2024       | 10/22/2025           |
| Room Thermometer               | IN0046                | 10/22/2024       | 10/22/2025           |

REPORT NUMBER: SP1-2411-284-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2411-284-4

**Photopic Flux vs. Wavelength**



**Photopic Lumens: NR**

| $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) |
|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|
| 360               | 0                           | NR                      | 490               | 267                         | NR                      | 620               | 915                         | NR                      | 750               | 23                          | NR                      | 880               | 0                           | NR                      |
| 365               | 0                           | NR                      | 495               | 315                         | NR                      | 625               | 866                         | NR                      | 755               | 20                          | NR                      | 885               | 0                           | NR                      |
| 370               | 0                           | NR                      | 500               | 360                         | NR                      | 630               | 811                         | NR                      | 760               | 17                          | NR                      | 890               | 0                           | NR                      |
| 375               | 0                           | NR                      | 505               | 396                         | NR                      | 635               | 750                         | NR                      | 765               | 14                          | NR                      | 895               | 0                           | NR                      |
| 380               | 0                           | NR                      | 510               | 418                         | NR                      | 640               | 686                         | NR                      | 770               | 12                          | NR                      | 900               | 0                           | NR                      |
| 385               | 0                           | NR                      | 515               | 435                         | NR                      | 645               | 619                         | NR                      | 775               | 10                          | NR                      | 905               | 0                           | NR                      |
| 390               | 0                           | NR                      | 520               | 448                         | NR                      | 650               | 554                         | NR                      | 780               | 9                           | NR                      | 910               | 0                           | NR                      |
| 395               | 0                           | NR                      | 525               | 462                         | NR                      | 655               | 491                         | NR                      | 785               | 7                           | NR                      | 915               | 0                           | NR                      |
| 400               | 1                           | NR                      | 530               | 476                         | NR                      | 660               | 431                         | NR                      | 790               | 6                           | NR                      | 920               | 0                           | NR                      |
| 405               | 2                           | NR                      | 535               | 495                         | NR                      | 665               | 376                         | NR                      | 795               | 5                           | NR                      | 925               | 0                           | NR                      |
| 410               | 5                           | NR                      | 540               | 520                         | NR                      | 670               | 325                         | NR                      | 800               | 4                           | NR                      | 930               | 0                           | NR                      |
| 415               | 10                          | NR                      | 545               | 547                         | NR                      | 675               | 280                         | NR                      | 805               | 4                           | NR                      | 935               | 0                           | NR                      |
| 420               | 21                          | NR                      | 550               | 576                         | NR                      | 680               | 241                         | NR                      | 810               | 3                           | NR                      | 940               | 0                           | NR                      |
| 425               | 42                          | NR                      | 555               | 612                         | NR                      | 685               | 207                         | NR                      | 815               | 3                           | NR                      | 945               | 0                           | NR                      |
| 430               | 77                          | NR                      | 560               | 651                         | NR                      | 690               | 176                         | NR                      | 820               | 2                           | NR                      | 950               | 0                           | NR                      |
| 435               | 135                         | NR                      | 565               | 693                         | NR                      | 695               | 149                         | NR                      | 825               | 2                           | NR                      | 955               | 0                           | NR                      |
| 440               | 215                         | NR                      | 570               | 741                         | NR                      | 700               | 127                         | NR                      | 830               | 2                           | NR                      | 960               | 0                           | NR                      |
| 445               | 321                         | NR                      | 575               | 793                         | NR                      | 705               | 107                         | NR                      | 835               | 2                           | NR                      | 965               | 0                           | NR                      |
| 450               | 479                         | NR                      | 580               | 847                         | NR                      | 710               | 89                          | NR                      | 840               | 1                           | NR                      | 970               | 0                           | NR                      |
| 455               | 432                         | NR                      | 585               | 897                         | NR                      | 715               | 75                          | NR                      | 845               | 1                           | NR                      | 975               | 0                           | NR                      |
| 460               | 265                         | NR                      | 590               | 940                         | NR                      | 720               | 62                          | NR                      | 850               | 1                           | NR                      | 980               | 0                           | NR                      |
| 465               | 231                         | NR                      | 595               | 971                         | NR                      | 725               | 51                          | NR                      | 855               | 1                           | NR                      | 985               | 0                           | NR                      |
| 470               | 204                         | NR                      | 600               | 993                         | NR                      | 730               | 43                          | NR                      | 860               | 1                           | NR                      | 990               | 0                           | NR                      |
| 475               | 168                         | NR                      | 605               | 996                         | NR                      | 735               | 36                          | NR                      | 865               | 1                           | NR                      | 995               | 0                           | NR                      |
| 480               | 183                         | NR                      | 610               | 986                         | NR                      | 740               | 31                          | NR                      | 870               | 1                           | NR                      | 1000              | 0                           | NR                      |
| 485               | 223                         | NR                      | 615               | 957                         | NR                      | 745               | 26                          | NR                      | 875               | 0                           | NR                      |                   |                             |                         |

REPORT NUMBER: SP1-2411-284-4

**Scotopic Flux vs. Wavelength**




**Scotopic Lumens: NR**

**S/P: 1.34**

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 267                      | NR            | 620    | 915                      | NR            | 750    | 23                       | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 315                      | NR            | 625    | 866                      | NR            | 755    | 20                       | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 360                      | NR            | 630    | 811                      | NR            | 760    | 17                       | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 396                      | NR            | 635    | 750                      | NR            | 765    | 14                       | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 418                      | NR            | 640    | 686                      | NR            | 770    | 12                       | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 435                      | NR            | 645    | 619                      | NR            | 775    | 10                       | NR            | 905    | 0                        | NR            |
| 390    | 0                        | NR            | 520    | 448                      | NR            | 650    | 554                      | NR            | 780    | 9                        | NR            | 910    | 0                        | NR            |
| 395    | 0                        | NR            | 525    | 462                      | NR            | 655    | 491                      | NR            | 785    | 7                        | NR            | 915    | 0                        | NR            |
| 400    | 1                        | NR            | 530    | 476                      | NR            | 660    | 431                      | NR            | 790    | 6                        | NR            | 920    | 0                        | NR            |
| 405    | 2                        | NR            | 535    | 495                      | NR            | 665    | 376                      | NR            | 795    | 5                        | NR            | 925    | 0                        | NR            |
| 410    | 5                        | NR            | 540    | 520                      | NR            | 670    | 325                      | NR            | 800    | 4                        | NR            | 930    | 0                        | NR            |
| 415    | 10                       | NR            | 545    | 547                      | NR            | 675    | 280                      | NR            | 805    | 4                        | NR            | 935    | 0                        | NR            |
| 420    | 21                       | NR            | 550    | 576                      | NR            | 680    | 241                      | NR            | 810    | 3                        | NR            | 940    | 0                        | NR            |
| 425    | 42                       | NR            | 555    | 612                      | NR            | 685    | 207                      | NR            | 815    | 3                        | NR            | 945    | 0                        | NR            |
| 430    | 77                       | NR            | 560    | 651                      | NR            | 690    | 176                      | NR            | 820    | 2                        | NR            | 950    | 0                        | NR            |
| 435    | 135                      | NR            | 565    | 693                      | NR            | 695    | 149                      | NR            | 825    | 2                        | NR            | 955    | 0                        | NR            |
| 440    | 215                      | NR            | 570    | 741                      | NR            | 700    | 127                      | NR            | 830    | 2                        | NR            | 960    | 0                        | NR            |
| 445    | 321                      | NR            | 575    | 793                      | NR            | 705    | 107                      | NR            | 835    | 2                        | NR            | 965    | 0                        | NR            |
| 450    | 479                      | NR            | 580    | 847                      | NR            | 710    | 89                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 432                      | NR            | 585    | 897                      | NR            | 715    | 75                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 265                      | NR            | 590    | 940                      | NR            | 720    | 62                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 231                      | NR            | 595    | 971                      | NR            | 725    | 51                       | NR            | 855    | 1                        | NR            | 985    | 0                        | NR            |
| 470    | 204                      | NR            | 600    | 993                      | NR            | 730    | 43                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 168                      | NR            | 605    | 996                      | NR            | 735    | 36                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 183                      | NR            | 610    | 986                      | NR            | 740    | 31                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 223                      | NR            | 615    | 957                      | NR            | 745    | 26                       | NR            | 875    | 0                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2411-284-4

Melanopic Flux vs. Wavelength




Melanopic Lumens: NR

M/P: 2.58



| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 267                      | NR            | 620    | 915                      | NR            | 750    | 23                       | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 315                      | NR            | 625    | 866                      | NR            | 755    | 20                       | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 360                      | NR            | 630    | 811                      | NR            | 760    | 17                       | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 396                      | NR            | 635    | 750                      | NR            | 765    | 14                       | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 418                      | NR            | 640    | 686                      | NR            | 770    | 12                       | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 435                      | NR            | 645    | 619                      | NR            | 775    | 10                       | NR            | 905    | 0                        | NR            |
| 390    | 0                        | NR            | 520    | 448                      | NR            | 650    | 554                      | NR            | 780    | 9                        | NR            | 910    | 0                        | NR            |
| 395    | 0                        | NR            | 525    | 462                      | NR            | 655    | 491                      | NR            | 785    | 7                        | NR            | 915    | 0                        | NR            |
| 400    | 1                        | NR            | 530    | 476                      | NR            | 660    | 431                      | NR            | 790    | 6                        | NR            | 920    | 0                        | NR            |
| 405    | 2                        | NR            | 535    | 495                      | NR            | 665    | 376                      | NR            | 795    | 5                        | NR            | 925    | 0                        | NR            |
| 410    | 5                        | NR            | 540    | 520                      | NR            | 670    | 325                      | NR            | 800    | 4                        | NR            | 930    | 0                        | NR            |
| 415    | 10                       | NR            | 545    | 547                      | NR            | 675    | 280                      | NR            | 805    | 4                        | NR            | 935    | 0                        | NR            |
| 420    | 21                       | NR            | 550    | 576                      | NR            | 680    | 241                      | NR            | 810    | 3                        | NR            | 940    | 0                        | NR            |
| 425    | 42                       | NR            | 555    | 612                      | NR            | 685    | 207                      | NR            | 815    | 3                        | NR            | 945    | 0                        | NR            |
| 430    | 77                       | NR            | 560    | 651                      | NR            | 690    | 176                      | NR            | 820    | 2                        | NR            | 950    | 0                        | NR            |
| 435    | 135                      | NR            | 565    | 693                      | NR            | 695    | 149                      | NR            | 825    | 2                        | NR            | 955    | 0                        | NR            |
| 440    | 215                      | NR            | 570    | 741                      | NR            | 700    | 127                      | NR            | 830    | 2                        | NR            | 960    | 0                        | NR            |
| 445    | 321                      | NR            | 575    | 793                      | NR            | 705    | 107                      | NR            | 835    | 2                        | NR            | 965    | 0                        | NR            |
| 450    | 479                      | NR            | 580    | 847                      | NR            | 710    | 89                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 432                      | NR            | 585    | 897                      | NR            | 715    | 75                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 265                      | NR            | 590    | 940                      | NR            | 720    | 62                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 231                      | NR            | 595    | 971                      | NR            | 725    | 51                       | NR            | 855    | 1                        | NR            | 985    | 0                        | NR            |
| 470    | 204                      | NR            | 600    | 993                      | NR            | 730    | 43                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 168                      | NR            | 605    | 996                      | NR            | 735    | 36                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 183                      | NR            | 610    | 986                      | NR            | 740    | 31                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 223                      | NR            | 615    | 957                      | NR            | 745    | 26                       | NR            | 875    | 0                        | NR            |        |                          |               |

**Summary**

$R_f = 86.1$   
 $R_g = 94.9$   
 CIE  $R_a = 82.9$   
 $R_9 = 3.9$




**Color Vector Graphics**







Individual Sample Fidelity Index ( $R_{f,i}$ )


|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 87 | CES51 = 95 | CES76 = 85 |
| CES02 = 63 | CES27 = 95 | CES52 = 95 | CES77 = 85 |
| CES03 = 31 | CES28 = 96 | CES53 = 91 | CES78 = 83 |
| CES04 = 70 | CES29 = 90 | CES54 = 92 | CES79 = 89 |
| CES05 = 50 | CES30 = 96 | CES55 = 91 | CES80 = 89 |
| CES06 = 51 | CES31 = 92 | CES56 = 88 | CES81 = 70 |
| CES07 = 42 | CES32 = 86 | CES57 = 87 | CES82 = 96 |
| CES08 = 41 | CES33 = 94 | CES58 = 88 | CES83 = 94 |
| CES09 = 29 | CES34 = 94 | CES59 = 92 | CES84 = 92 |
| CES10 = 76 | CES35 = 97 | CES60 = 93 | CES85 = 76 |
| CES11 = 59 | CES36 = 88 | CES61 = 90 | CES86 = 66 |
| CES12 = 65 | CES37 = 98 | CES62 = 92 | CES87 = 85 |
| CES13 = 44 | CES38 = 95 | CES63 = 90 | CES88 = 87 |
| CES14 = 74 | CES39 = 98 | CES64 = 85 | CES89 = 75 |
| CES15 = 72 | CES40 = 96 | CES65 = 81 | CES90 = 89 |
| CES16 = 48 | CES41 = 97 | CES66 = 84 | CES91 = 80 |
| CES17 = 50 | CES42 = 98 | CES67 = 83 | CES92 = 64 |
| CES18 = 57 | CES43 = 92 | CES68 = 85 | CES93 = 79 |
| CES19 = 72 | CES44 = 99 | CES69 = 89 | CES94 = 61 |
| CES20 = 67 | CES45 = 94 | CES70 = 83 | CES95 = 75 |
| CES21 = 87 | CES46 = 91 | CES71 = 81 | CES96 = 84 |
| CES22 = 79 | CES47 = 92 | CES72 = 93 | CES97 = 89 |
| CES23 = 92 | CES48 = 84 | CES73 = 78 | CES98 = 85 |
| CES24 = 91 | CES49 = 92 | CES74 = 91 | CES99 = 76 |
| CES25 = 72 | CES50 = 95 | CES75 = 84 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)