

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P636735

Luminaire Tested: GWS-SA4B-735-U-T2R-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P636735
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA4B-735-U-T2R-W
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II ROADWAY OPTICS
Light Source: (64) 3500K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14556.9 lumens
Efficiency: N/A
Efficacy: 154.2 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B2 - U0 - G2


Input Watts (W): 94.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P636735
 CATALOG NUMBER: GWS-SA4B-735-U-T2R-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 8.9 fc
 Type II - Short - N/A

REPORT NUMBER: P636735
CATALOG NUMBER: GWS-SA4B-735-U-T2R-W

Luminous Intensity Polar Plot



— Vertical Plane Through 76-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P636735

CATALOG NUMBER: GWS-SA4B-735-U-T2R-W


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 2433.2 | 0.0 | 2433.2 |
| | % Fixture | 16.7 | 0.0 | 16.7 |
| Street Side | Lumens | 12123.7 | 0.0 | 12123.7 |
| | % Fixture | 83.3 | 0.0 | 83.3 |
| Total | Lumens | 14556.9 | 0.0 | 14556.9 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 163.8 | 1.1 |
| 10°-20° | 623.8 | 4.3 |
| 20°-30° | 1215.7 | 8.4 |
| 30°-40° | 2033.1 | 14.0 |
| 40°-50° | 2911.1 | 20.0 |
| 50°-60° | 3446.3 | 23.7 |
| 60°-70° | 2865.6 | 19.7 |
| 70°-80° | 1172.7 | 8.1 |
| 80°-90° | 124.8 | 0.9 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 14556.9 | 100.0 |
| 0°-180° | 14556.9 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P636735

CATALOG NUMBER: GWS-SA4B-735-U-T2R-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1494.2 | 10.3 | | | |
| FM (30°-60°) | 7208.0 | 49.5 | | | |
| FH (60°-80°) | 3347.0 | 23.0 | | | G2/5000 |
| FVH (80°-90°) | 74.5 | 0.5 | | | G1/100 |
| BL (0°-30°) | 509.0 | 3.5 | B2/1000 | | |
| BM (30°-60°) | 1182.5 | 8.1 | B2/2500 | | |
| BH (60°-80°) | 691.3 | 4.7 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 50.4 | 0.3 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G2
 Type II Short





REPORT NUMBER: P636735
 CATALOG NUMBER: GWS-SA4B-735-U-T2R-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 76° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|---------|---------|---------|
| 0° | 1378.5 | 1378.5 | 1378.5 | 1378.5 | 1378.5 | 1378.5 | 1378.5 | 1378.5 | 1378.5 | 1378.5 | 1378.5 |
| 2.5° | 1932.1 | 1939.3 | 1915.8 | 1907.6 | 1852.3 | 1777.6 | 1715.2 | 1621.0 | 1534.0 | 1520.7 | 1443.0 |
| 5° | 2454.1 | 2423.3 | 2396.7 | 2379.3 | 2302.6 | 2217.7 | 2085.6 | 1908.6 | 1723.4 | 1700.8 | 1533.0 |
| 7.5° | 2764.1 | 2759.0 | 2726.3 | 2716.0 | 2656.7 | 2571.7 | 2435.6 | 2215.6 | 1946.5 | 1909.6 | 1654.8 |
| 10° | 3012.8 | 3009.7 | 2993.4 | 3002.6 | 2948.3 | 2865.4 | 2733.4 | 2506.2 | 2191.0 | 2154.2 | 1790.9 |
| 12.5° | 3229.8 | 3234.9 | 3231.8 | 3265.6 | 3238.0 | 3173.5 | 3036.4 | 2786.6 | 2435.6 | 2395.7 | 1956.7 |
| 15° | 3388.4 | 3392.5 | 3407.8 | 3481.5 | 3496.9 | 3483.6 | 3344.4 | 3061.9 | 2677.1 | 2619.8 | 2127.6 |
| 17.5° | 3433.4 | 3441.6 | 3478.4 | 3597.2 | 3680.1 | 3735.3 | 3632.0 | 3342.3 | 2914.6 | 2852.1 | 2301.6 |
| 20° | 3493.8 | 3503.0 | 3539.9 | 3663.7 | 3785.5 | 3911.3 | 3892.9 | 3626.8 | 3154.0 | 3102.9 | 2477.6 |
| 22.5° | 3773.2 | 3766.0 | 3749.6 | 3809.0 | 3896.0 | 4052.6 | 4098.6 | 3900.1 | 3401.7 | 3352.6 | 2672.0 |
| 25° | 4311.5 | 4298.2 | 4193.8 | 4139.5 | 4110.9 | 4206.1 | 4287.9 | 4148.8 | 3643.2 | 3569.5 | 2853.2 |
| 27.5° | 4905.0 | 4897.9 | 4764.8 | 4635.9 | 4459.9 | 4418.9 | 4467.0 | 4365.7 | 3877.6 | 3802.9 | 3010.8 |
| 30° | 5466.9 | 5445.4 | 5306.2 | 5144.5 | 4909.1 | 4733.1 | 4662.5 | 4578.6 | 4134.4 | 4056.7 | 3195.0 |
| 32.5° | 5969.3 | 5941.7 | 5778.0 | 5598.9 | 5352.2 | 5144.5 | 4933.7 | 4804.7 | 4425.1 | 4335.0 | 3383.3 |
| 35° | 6381.8 | 6354.1 | 6186.3 | 5995.9 | 5724.8 | 5571.2 | 5282.7 | 5050.4 | 4720.8 | 4629.7 | 3605.3 |
| 37.5° | 6701.1 | 6675.5 | 6500.5 | 6313.2 | 6076.8 | 5955.0 | 5704.3 | 5326.7 | 5061.6 | 4966.4 | 3840.7 |
| 40° | 6880.1 | 6861.7 | 6721.5 | 6573.1 | 6374.6 | 6269.2 | 6156.6 | 5675.6 | 5443.3 | 5348.2 | 4118.1 |
| 42.5° | 6934.4 | 6922.1 | 6823.9 | 6747.1 | 6613.0 | 6533.2 | 6597.7 | 6086.0 | 5850.6 | 5767.7 | 4430.2 |
| 45° | 6798.3 | 6798.3 | 6769.6 | 6808.5 | 6814.6 | 6813.6 | 7039.8 | 6549.6 | 6351.1 | 6260.0 | 4870.2 |
| 47.5° | 6450.3 | 6472.8 | 6514.8 | 6706.2 | 6907.8 | 7076.6 | 7556.6 | 7167.7 | 6994.8 | 6920.1 | 5493.5 |
| 50° | 5813.8 | 5875.2 | 6018.5 | 6392.0 | 6820.8 | 7250.6 | 8045.8 | 8081.6 | 8246.3 | 8114.3 | 6410.4 |
| 52.5° | 4881.5 | 4872.3 | 5237.6 | 5769.8 | 6423.7 | 7257.8 | 8314.9 | 8888.0 | 9331.1 | 9240.0 | 7092.0 |
| 55° | 3879.6 | 3864.3 | 4205.0 | 4938.8 | 5814.8 | 6983.5 | 8476.6 | 9257.4 | 9932.9 | 9851.0 | 7705.0 |
| 57.5° | 2970.9 | 2951.4 | 3254.3 | 3916.5 | 4955.2 | 6401.2 | 8445.9 | 9697.5 | 10760.8 | 10718.8 | 8538.0 |
| 60° | 2044.7 | 2021.2 | 2304.6 | 2883.9 | 3937.9 | 5510.9 | 8106.1 | 9923.7 | 11729.9 | 11744.2 | 9429.4 |
| 62.5° | 1228.0 | 1214.7 | 1420.4 | 1869.7 | 2832.7 | 4407.7 | 7311.0 | 9786.5 | 12501.5 | 12566.0 | 10002.5 |
| 65° | 740.9 | 731.7 | 852.5 | 1115.5 | 1797.0 | 3216.5 | 6085.0 | 9085.5 | 12613.1 | 12761.5 | 10015.8 |
| 67.5° | 539.3 | 540.3 | 575.1 | 679.5 | 1047.9 | 2077.4 | 4566.3 | 7828.8 | 12031.8 | 12185.3 | 9384.3 |
| 70° | 468.7 | 470.8 | 489.2 | 512.7 | 633.5 | 1189.2 | 2968.8 | 6180.2 | 10313.6 | 10432.3 | 7870.8 |
| 72.5° | 416.5 | 416.5 | 428.8 | 441.1 | 495.3 | 724.5 | 1590.3 | 4319.7 | 8139.9 | 8171.6 | 6007.2 |
| 75° | 366.4 | 363.3 | 369.4 | 375.6 | 429.8 | 506.6 | 773.7 | 3009.7 | 6012.3 | 5938.6 | 3882.7 |
| 77.5° | 291.7 | 288.6 | 289.6 | 295.8 | 344.9 | 362.3 | 392.0 | 1879.9 | 3388.4 | 3198.0 | 1715.2 |
| 80° | 207.7 | 205.7 | 217.0 | 232.3 | 254.8 | 222.1 | 245.6 | 909.8 | 1343.7 | 1250.6 | 665.2 |
| 82.5° | 123.8 | 127.9 | 145.3 | 157.6 | 176.0 | 139.2 | 158.6 | 303.9 | 475.9 | 463.6 | 270.2 |
| 85° | 17.4 | 18.4 | 52.2 | 60.4 | 75.7 | 54.2 | 83.9 | 137.1 | 190.3 | 203.7 | 95.2 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 7.2 | 24.6 | 54.2 | 55.3 | 23.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P636735

CATALOG NUMBER: GWS-SA4B-735-U-T2R-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1378.5 | 1378.5 | 1378.5 | 1378.5 | 1378.5 | 1378.5 | 1378.5 | 1378.5 | 1378.5 | 1378.5 | 1378.5 |
| 2.5° | 1403.0 | 1354.9 | 1286.4 | 1229.1 | 1181.0 | 1142.1 | 1109.3 | 1084.8 | 1077.6 | 1067.4 | 1067.4 |
| 5° | 1454.2 | 1367.2 | 1244.4 | 1157.4 | 1107.3 | 1077.6 | 1057.1 | 1046.9 | 1041.8 | 1035.7 | 1032.6 |
| 7.5° | 1524.8 | 1403.0 | 1237.3 | 1149.2 | 1110.4 | 1091.9 | 1078.6 | 1072.5 | 1068.4 | 1062.3 | 1062.3 |
| 10° | 1622.0 | 1456.3 | 1259.8 | 1177.9 | 1147.2 | 1128.8 | 1113.4 | 1103.2 | 1094.0 | 1084.8 | 1082.7 |
| 12.5° | 1727.5 | 1525.9 | 1300.7 | 1216.8 | 1184.0 | 1161.5 | 1140.0 | 1124.7 | 1113.4 | 1102.2 | 1099.1 |
| 15° | 1844.1 | 1597.5 | 1344.7 | 1254.7 | 1213.7 | 1183.0 | 1157.4 | 1133.9 | 1118.5 | 1102.2 | 1100.1 |
| 17.5° | 1958.7 | 1670.1 | 1381.6 | 1280.2 | 1228.0 | 1190.2 | 1153.3 | 1122.6 | 1103.2 | 1084.8 | 1079.7 |
| 20° | 2095.9 | 1742.8 | 1407.1 | 1287.4 | 1225.0 | 1174.8 | 1130.8 | 1091.9 | 1070.4 | 1049.0 | 1045.9 |
| 22.5° | 2221.7 | 1810.3 | 1419.4 | 1277.2 | 1201.4 | 1142.1 | 1090.9 | 1049.0 | 1025.4 | 1003.9 | 999.8 |
| 25° | 2343.5 | 1869.7 | 1414.3 | 1252.6 | 1165.6 | 1097.1 | 1043.8 | 1001.9 | 979.4 | 956.9 | 950.7 |
| 27.5° | 2461.2 | 1909.6 | 1393.8 | 1214.7 | 1120.6 | 1046.9 | 995.7 | 957.9 | 938.4 | 919.0 | 910.8 |
| 30° | 2576.9 | 1946.5 | 1362.1 | 1165.6 | 1063.3 | 994.7 | 952.8 | 926.2 | 906.7 | 886.2 | 880.1 |
| 32.5° | 2693.5 | 1973.1 | 1314.0 | 1108.3 | 1005.0 | 948.7 | 923.1 | 903.6 | 883.2 | 862.7 | 856.6 |
| 35° | 2811.2 | 1984.3 | 1255.7 | 1042.8 | 955.8 | 919.0 | 909.8 | 887.3 | 859.6 | 835.1 | 826.9 |
| 37.5° | 2951.4 | 1994.6 | 1183.0 | 978.3 | 912.8 | 904.7 | 902.6 | 868.8 | 836.1 | 802.3 | 793.1 |
| 40° | 3120.3 | 2007.9 | 1108.3 | 920.0 | 878.1 | 899.5 | 891.4 | 845.3 | 779.8 | 747.1 | 736.8 |
| 42.5° | 3327.0 | 2032.4 | 1030.5 | 866.8 | 852.5 | 880.1 | 870.9 | 788.0 | 744.0 | 725.6 | 720.5 |
| 45° | 3630.9 | 2122.5 | 952.8 | 824.8 | 833.0 | 852.5 | 838.1 | 754.2 | 736.8 | 724.5 | 718.4 |
| 47.5° | 4172.3 | 2260.6 | 885.2 | 793.1 | 817.7 | 827.9 | 772.6 | 745.0 | 731.7 | 715.3 | 708.2 |
| 50° | 4735.2 | 2321.0 | 831.0 | 773.7 | 800.3 | 805.4 | 736.8 | 732.7 | 723.5 | 706.1 | 699.0 |
| 52.5° | 5115.8 | 2312.8 | 798.2 | 766.5 | 786.0 | 766.5 | 720.5 | 719.4 | 713.3 | 692.8 | 684.6 |
| 55° | 5545.7 | 2327.2 | 783.9 | 768.6 | 779.8 | 701.0 | 700.0 | 703.1 | 700.0 | 677.5 | 673.4 |
| 57.5° | 6125.9 | 2371.2 | 776.7 | 775.7 | 775.7 | 669.3 | 680.5 | 684.6 | 678.5 | 668.3 | 665.2 |
| 60° | 6683.7 | 2374.2 | 763.4 | 783.9 | 772.6 | 649.8 | 658.0 | 662.1 | 655.0 | 652.9 | 651.9 |
| 62.5° | 6893.4 | 2226.9 | 733.8 | 777.8 | 760.4 | 628.4 | 634.5 | 636.5 | 629.4 | 634.5 | 633.5 |
| 65° | 6581.3 | 1913.7 | 684.6 | 748.1 | 722.5 | 608.9 | 604.8 | 609.9 | 597.7 | 611.0 | 612.0 |
| 67.5° | 5843.5 | 1520.7 | 609.9 | 691.8 | 669.3 | 587.4 | 579.2 | 579.2 | 558.8 | 579.2 | 578.2 |
| 70° | 4711.6 | 1074.5 | 500.4 | 601.7 | 611.0 | 561.8 | 557.7 | 534.2 | 501.5 | 532.2 | 529.1 |
| 72.5° | 3571.6 | 771.6 | 394.0 | 475.9 | 526.0 | 526.0 | 527.0 | 487.1 | 449.3 | 463.6 | 451.3 |
| 75° | 2262.7 | 543.4 | 315.2 | 364.3 | 412.4 | 461.5 | 485.1 | 411.4 | 377.6 | 371.5 | 365.3 |
| 77.5° | 1019.3 | 357.2 | 245.6 | 279.4 | 292.7 | 364.3 | 443.1 | 354.1 | 308.0 | 294.7 | 290.6 |
| 80° | 426.7 | 222.1 | 175.0 | 197.5 | 180.1 | 306.0 | 390.9 | 275.3 | 226.2 | 207.7 | 194.4 |
| 82.5° | 187.3 | 132.0 | 111.5 | 106.4 | 112.6 | 227.2 | 291.7 | 183.2 | 141.2 | 191.4 | 193.4 |
| 85° | 78.8 | 69.6 | 57.3 | 52.2 | 46.1 | 87.0 | 137.1 | 71.6 | 88.0 | 50.1 | 40.9 |
| 87.5° | 18.4 | 20.5 | 15.4 | 10.2 | 6.1 | 1.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

All Brands

Data applicable to all product families using SA light engines

Report Number: SP1-2101-121-7

Luminaire Tested: IFLD-S-SA2A-735-U-T2

Test Date: 03/04/2021

Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/04/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-735-U-T2**
 Description: STREETWORKS INF FLOOD

PROGRAMMED @ 615mA.

Spectral Parameters

CCT (K): 3388
 CIE u': 0.2371
 CIE v': 0.5177
 Duv: 0.0032
 CIE x: 0.4153
 CIE y: 0.4030
 CIE z: 0.1817
 Peak Wavelength (nm): 590
 Dominant Wavelength (nm): 580
 Purity: 45.7

 Rf: 76.9
 Rg: 94.4

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 73.1 | | |
| R1: | 68.9 | R9: | -34.6 |
| R2: | 81.1 | R10: | 57.8 |
| R3: | 93.1 | R11: | 68.6 |
| R4: | 71.6 | R12: | 53.9 |
| R5: | 69.4 | R13: | 70.9 |
| R6: | 75.0 | R14: | 96.2 |
| R7: | 79.5 | | |
| R8: | 46.4 | | |

Test Conditions

Stabilization Time: 81M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0/30%
 Sphere Temperature (°C): 24.1



REPORT NUMBER: SP1-2101-121-7

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-121-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-7

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 4.9 | 620 | 136720 | 35.6 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 8.0 | 625 | 126308 | 27.9 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 12.1 | 630 | 114625 | 20.7 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 18.1 | 635 | 103216 | 15.5 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 25.4 | 640 | 92605 | 11.1 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 33.9 | 645 | 83234 | 8.0 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 43.0 | 650 | 73263 | 5.4 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 50.1 | 655 | 64627 | 3.7 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 57.9 | 660 | 56614 | 2.4 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.0 | 535 | 103269 | 64.0 | 665 | 49537 | 1.6 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.0 | 540 | 107316 | 69.9 | 670 | 42866 | 0.9 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.0 | 545 | 113101 | 75.3 | 675 | 36708 | 0.6 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 0.0 | 550 | 120690 | 82.0 | 680 | 31814 | 0.4 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 0.1 | 555 | 128583 | 87.8 | 685 | 27485 | 0.2 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 0.3 | 560 | 137796 | 93.6 | 690 | 23698 | 0.1 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 0.8 | 565 | 146577 | 97.5 | 695 | 20309 | 0.1 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 1.6 | 570 | 154581 | 100.5 | 700 | 17890 | 0.1 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 2.4 | 575 | 162633 | 101.2 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 2.5 | 580 | 168101 | 99.9 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 2.1 | 585 | 173145 | 96.2 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 1.8 | 590 | 174675 | 90.3 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 1.7 | 595 | 173724 | 82.3 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 1.5 | 600 | 171241 | 73.8 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 1.7 | 605 | 165134 | 64.0 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 2.2 | 610 | 156652 | 53.8 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 3.3 | 615 | 147879 | 44.6 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-7

Scotopic Flux vs. Wavelength



Scotopic Lumens: 12126

S/P: 1.36

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 53.2 | 620 | 136720 | 1.7 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 71.7 | 625 | 126308 | 1.1 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 91.4 | 630 | 114625 | 0.6 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 110.0 | 635 | 103216 | 0.4 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 125.1 | 640 | 92605 | 0.2 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 135.7 | 645 | 83234 | 0.1 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 140.8 | 650 | 73263 | 0.1 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 139.6 | 655 | 64627 | 0.1 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 135.7 | 660 | 56614 | 0.0 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.1 | 535 | 103269 | 128.7 | 665 | 49537 | 0.0 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.2 | 540 | 107316 | 118.6 | 670 | 42866 | 0.0 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.6 | 545 | 113101 | 108.4 | 675 | 36708 | 0.0 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 2.0 | 550 | 120690 | 98.7 | 680 | 31814 | 0.0 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 5.9 | 555 | 128583 | 87.9 | 685 | 27485 | 0.0 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 14.3 | 560 | 137796 | 77.0 | 690 | 23698 | 0.0 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 30.5 | 565 | 146577 | 65.8 | 695 | 20309 | 0.0 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 55.5 | 570 | 154581 | 54.6 | 700 | 17890 | 0.0 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 77.4 | 575 | 162633 | 44.3 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 73.6 | 580 | 168101 | 34.6 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 53.7 | 585 | 173145 | 26.5 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 41.9 | 590 | 174675 | 19.5 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 34.3 | 595 | 173724 | 13.9 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 27.9 | 600 | 171241 | 9.7 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 27.1 | 605 | 165134 | 6.5 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 31.3 | 610 | 156652 | 4.2 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 40.0 | 615 | 147879 | 2.7 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: 4490.7 M/P: 0.5

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 28.8 | 620 | 136720 | 0.1 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 36.6 | 625 | 126308 | 0.1 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 43.9 | 630 | 114625 | 0.0 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 49.6 | 635 | 103216 | 0.0 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 53.0 | 640 | 92605 | 0.0 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 53.5 | 645 | 83234 | 0.0 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 51.6 | 650 | 73263 | 0.0 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 47.3 | 655 | 64627 | 0.0 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 42.5 | 660 | 56614 | 0.0 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.0 | 535 | 103269 | 37.2 | 665 | 49537 | 0.0 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.1 | 540 | 107316 | 31.4 | 670 | 42866 | 0.0 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.4 | 545 | 113101 | 26.3 | 675 | 36708 | 0.0 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 1.4 | 550 | 120690 | 21.7 | 680 | 31814 | 0.0 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 3.7 | 555 | 128583 | 17.3 | 685 | 27485 | 0.0 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 8.9 | 560 | 137796 | 13.6 | 690 | 23698 | 0.0 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 18.2 | 565 | 146577 | 10.3 | 695 | 20309 | 0.0 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 33.2 | 570 | 154581 | 7.6 | 700 | 17890 | 0.0 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 45.6 | 575 | 162633 | 5.4 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 43.8 | 580 | 168101 | 3.8 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 32.2 | 585 | 173145 | 2.6 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 25.6 | 590 | 174675 | 1.7 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 21.2 | 595 | 173724 | 1.1 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 17.4 | 600 | 171241 | 0.7 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 16.6 | 605 | 165134 | 0.5 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 18.6 | 610 | 156652 | 0.3 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 22.7 | 615 | 147879 | 0.2 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

Summary

$R_f = 76.9$
 $R_g = 94.4$
 CIE $R_a = 73.1$
 $R_g = -34.6$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 68 | CES51 = 90 | CES76 = 63 |
| CES02 = 62 | CES27 = 88 | CES52 = 89 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 80 | CES78 = 65 |
| CES04 = 70 | CES29 = 67 | CES54 = 84 | CES79 = 87 |
| CES05 = 48 | CES30 = 74 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 71 | CES56 = 75 | CES81 = 75 |
| CES07 = 40 | CES32 = 67 | CES57 = 74 | CES82 = 94 |
| CES08 = 39 | CES33 = 74 | CES58 = 76 | CES83 = 91 |
| CES09 = 29 | CES34 = 78 | CES59 = 87 | CES84 = 89 |
| CES10 = 75 | CES35 = 89 | CES60 = 93 | CES85 = 80 |
| CES11 = 58 | CES36 = 98 | CES61 = 86 | CES86 = 66 |
| CES12 = 64 | CES37 = 86 | CES62 = 89 | CES87 = 79 |
| CES13 = 43 | CES38 = 82 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 95 | CES64 = 74 | CES89 = 70 |
| CES15 = 71 | CES40 = 91 | CES65 = 68 | CES90 = 77 |
| CES16 = 47 | CES41 = 89 | CES66 = 71 | CES91 = 88 |
| CES17 = 50 | CES42 = 88 | CES67 = 69 | CES92 = 60 |
| CES18 = 56 | CES43 = 82 | CES68 = 74 | CES93 = 77 |
| CES19 = 72 | CES44 = 99 | CES69 = 82 | CES94 = 52 |
| CES20 = 65 | CES45 = 87 | CES70 = 67 | CES95 = 69 |
| CES21 = 86 | CES46 = 82 | CES71 = 66 | CES96 = 78 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 85 |
| CES23 = 92 | CES48 = 72 | CES73 = 59 | CES98 = 76 |
| CES24 = 91 | CES49 = 82 | CES74 = 97 | CES99 = 63 |
| CES25 = 72 | CES50 = 88 | CES75 = 66 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)