

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P641673

Luminaire Tested: GWS-SA6B-735-U-SLR-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P641673
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-42)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA6B-735-U-SLR-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (6) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR RIGHT OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (96) 3500K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11140.7 lumens
Efficiency: N/A
Efficacy: 80.2 lumens/watt
Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')
IES Classification: Type III - Short
BUG Rating: B2 - U0 - G1


Input Watts (W): 138.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P641673
 CATALOG NUMBER: GWS-SA6B-735-U-SLR-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 8.7 fc
 Type III - Short - N/A

REPORT NUMBER: P641673
CATALOG NUMBER: GWS-SA6B-735-U-SLR-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P641673
 CATALOG NUMBER: GWS-SA6B-735-U-SLR-W-GRSBK


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2494.7	0.0	2494.7
	% Fixture	22.4	0.0	22.4
Street Side	Lumens	8646.0	0.0	8646.0
	% Fixture	77.6	0.0	77.6
Total	Lumens	11140.7	0.0	11140.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	192.6	1.7
10°-20°	623.2	5.6
20°-30°	1012.3	9.1
30°-40°	1564.1	14.0
40°-50°	2508.1	22.5
50°-60°	3427.8	30.8
60°-70°	1660.2	14.9
70°-80°	152.0	1.4
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11140.7	100.0
0°-180°	11140.7	100.0

Coefficient of Utilization



REPORT NUMBER: P641673


CATALOG NUMBER: GWS-SA6B-735-U-SLR-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1089.9	9.8			
FM (30°-60°)	5930.4	53.2			
FH (60°-80°)	1625.2	14.6			G1/1800
FVH (80°-90°)	0.4	0.0			G0/10
BL (0°-30°)	738.2	6.6	B2/1000		
BM (30°-60°)	1569.6	14.1	B2/2500		
BH (60°-80°)	187.0	1.7	B1/500		G1/500
BVH (80°-90°)	0.0	0.0			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G1

Type III Short





REPORT NUMBER: P641673

CATALOG NUMBER: GWS-SA6B-735-U-SLR-W-GRSBK

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	1958.1	1958.1	1958.1	1958.1	1958.1	1958.1	1958.1	1958.1	1958.1	1958.1	1958.1
2.5°	2121.3	2134.7	2157.2	2205.1	2245.5	2272.5	2284.4	2281.5	2265.0	2253.0	2229.1
5°	2348.8	2348.8	2392.2	2501.5	2585.3	2637.7	2664.7	2648.2	2615.3	2562.9	2482.1
7.5°	2547.9	2555.4	2628.8	2784.5	2911.7	2986.5	3030.0	3021.0	2962.6	2862.3	2700.6
10°	2703.6	2712.6	2809.9	3000.0	3149.7	3226.1	3290.4	3296.4	3232.1	3098.8	2913.2
12.5°	2854.8	2863.8	2965.6	3148.2	3280.0	3311.4	3368.3	3390.7	3374.3	3280.0	3086.8
15°	3018.0	3038.9	3125.8	3262.0	3317.4	3280.0	3317.4	3357.8	3413.2	3404.2	3230.6
17.5°	3178.2	3193.1	3281.5	3329.4	3268.0	3170.7	3188.6	3236.5	3362.3	3485.1	3372.8
20°	3326.4	3347.3	3420.7	3357.8	3172.2	3021.0	3022.5	3085.4	3277.0	3534.5	3518.0
22.5°	3482.1	3513.5	3565.9	3389.2	3083.9	2902.7	2910.2	2967.1	3209.6	3580.9	3682.7
25°	3685.7	3715.6	3750.0	3467.1	3055.4	2844.3	2872.8	2925.2	3209.6	3660.2	3886.3
27.5°	3961.1	3982.1	3983.6	3612.3	3104.8	2853.3	2913.2	2973.1	3305.4	3818.9	4158.7
30°	4306.9	4339.9	4296.4	3838.4	3259.0	2973.1	3061.4	3136.2	3512.0	4086.9	4559.9
32.5°	4727.6	4774.0	4715.6	4173.7	3580.9	3386.3	3546.4	3589.8	3841.3	4474.6	5015.0
35°	5221.6	5260.5	5197.6	4637.8	4332.4	4368.3	4658.7	4603.3	4503.0	4952.1	5546.4
37.5°	5763.5	5799.4	5678.2	5341.4	5443.2	5598.8	6062.9	5872.8	5549.4	5567.4	6122.8
40°	6260.5	6299.4	6109.3	6106.3	6315.9	6600.3	7160.2	6898.3	6458.1	6372.8	6663.2
42.5°	6775.5	6802.4	6630.3	6513.5	6989.6	7574.9	8167.7	7814.4	7059.9	6967.1	7339.9
45°	7510.5	7567.4	7260.5	6714.1	7595.9	8696.2	9522.5	8832.4	7470.1	7395.3	8375.8
47.5°	8591.4	8633.3	8007.5	6839.9	8160.2	10092.9	11215.6	10152.8	7830.9	7660.2	9792.0
50°	9485.1	9513.5	8694.7	6977.6	8760.5	11598.9	13145.3	11718.6	8236.6	8098.9	11113.9
52.5°	10143.8	10251.6	9597.4	7260.5	9549.5	13369.9	15281.5	13573.4	8869.8	8946.2	12209.7
55°	10280.0	10426.7	10214.1	7434.2	10244.1	15173.8	17254.6	15233.6	9501.6	9588.4	12577.9
57.5°	9034.5	9151.3	9327.9	6733.6	10227.6	16000.1	18399.8	15784.5	9214.1	8598.9	11199.2
60°	6768.0	6848.9	7169.2	5146.7	9405.8	15269.6	17507.6	14847.4	8056.9	6561.4	8533.0
62.5°	4013.5	4049.4	4455.1	3333.9	7806.9	13149.8	14519.6	12811.5	6366.8	4413.2	5226.1
65°	1540.4	1525.5	1835.3	1645.2	5741.1	10474.6	10799.5	9766.5	4368.3	2022.5	1992.5
67.5°	238.0	227.5	306.9	486.5	4140.7	7259.0	7125.8	7039.0	2736.5	471.6	411.7
70°	53.9	53.9	65.9	143.7	2530.0	4265.0	4564.4	4351.8	1751.5	100.3	53.9
72.5°	25.4	25.4	31.4	61.4	916.2	1757.5	2047.9	2016.5	568.9	32.9	19.5
75°	9.0	10.5	10.5	13.5	55.4	91.3	209.6	149.7	35.9	0.0	0.0
77.5°	3.0	3.0	3.0	3.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	1.5	1.5	1.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	1.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P641673

CATALOG NUMBER: GWS-SA6B-735-U-SLR-W-GRSBK

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1958.1	1958.1	1958.1	1958.1	1958.1	1958.1	1958.1	1958.1	1958.1	1958.1	1958.1
2.5°	2176.7	2166.2	2127.3	2074.9	2024.0	1979.1	1932.6	1877.3	1836.8	1790.4	1775.5
5°	2419.2	2353.3	2247.0	2136.2	2034.4	1947.6	1863.8	1774.0	1708.1	1642.2	1619.8
7.5°	2624.3	2527.0	2354.8	2188.6	2049.4	1926.7	1805.4	1682.6	1586.8	1509.0	1485.0
10°	2808.4	2696.1	2465.6	2260.5	2085.3	1943.1	1796.4	1642.2	1518.0	1425.2	1402.7
12.5°	2967.1	2836.8	2559.9	2314.4	2100.3	1937.1	1794.9	1672.2	1559.9	1453.6	1425.2
15°	3100.3	2956.6	2639.2	2350.3	2077.9	1862.3	1738.0	1718.6	1709.6	1592.8	1537.4
17.5°	3230.6	3068.9	2703.6	2366.8	2015.0	1730.6	1640.7	1729.1	1823.4	1747.0	1676.7
20°	3366.8	3182.7	2769.5	2369.8	1910.2	1582.3	1567.4	1706.6	1826.4	1802.4	1736.5
22.5°	3527.0	3324.9	2851.8	2368.3	1778.5	1456.6	1513.5	1663.2	1760.5	1759.0	1706.6
25°	3759.0	3504.5	2962.6	2377.3	1634.7	1359.3	1453.6	1589.8	1669.2	1666.2	1622.8
27.5°	4007.5	3718.6	3106.3	2399.7	1512.0	1302.4	1383.2	1489.5	1558.4	1555.4	1518.0
30°	4356.3	3965.6	3244.0	2401.2	1423.7	1272.5	1305.4	1378.8	1444.6	1437.1	1408.7
32.5°	4780.0	4244.0	3359.3	2315.9	1368.3	1244.0	1224.6	1262.0	1312.9	1302.4	1294.9
35°	5292.0	4574.9	3458.1	2128.8	1282.9	1187.1	1134.7	1142.2	1178.2	1184.1	1181.1
37.5°	5875.8	4968.6	3580.9	1881.7	1167.7	1104.8	1034.4	1028.5	1049.4	1068.9	1083.8
40°	6452.1	5411.7	3747.0	1631.7	1062.9	1000.0	932.6	917.7	926.7	961.1	992.5
42.5°	7100.3	5925.2	3926.7	1417.7	991.0	884.7	820.4	791.9	817.4	872.8	910.2
45°	8034.5	6645.3	4101.8	1247.0	961.1	782.9	696.1	693.1	721.6	793.4	835.3
47.5°	9345.9	7576.4	4217.1	1113.8	959.6	703.6	600.3	618.3	651.2	721.6	769.5
50°	10624.3	8742.6	4089.8	1012.0	928.2	651.2	528.4	564.4	597.3	658.7	708.1
52.5°	11395.3	9369.8	3594.3	916.2	830.8	627.2	458.1	521.0	526.9	582.3	634.7
55°	11314.5	8964.1	2753.0	768.0	687.1	592.8	384.7	470.1	473.1	515.0	559.9
57.5°	9820.4	7696.2	1890.7	622.8	516.5	489.5	317.4	396.7	425.2	450.6	483.5
60°	7318.9	5615.3	842.8	506.0	327.8	330.8	271.0	299.4	342.8	372.8	401.2
62.5°	4312.9	3230.6	342.8	303.9	181.1	208.1	218.6	218.6	245.5	268.0	285.9
65°	1630.3	1130.2	139.2	152.7	94.3	97.3	128.7	158.7	179.6	199.1	223.1
67.5°	285.9	197.6	71.9	56.9	55.4	49.4	65.9	103.3	115.3	130.2	140.7
70°	47.9	40.4	29.9	28.4	25.4	26.9	43.4	73.4	80.8	85.3	89.8
72.5°	13.5	12.0	9.0	7.5	6.0	7.5	26.9	56.9	59.9	62.9	67.4
75°	0.0	0.0	0.0	0.0	0.0	0.0	10.5	40.4	43.4	44.9	49.4
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	9.0	12.0	15.0	12.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P641673

CATALOG NUMBER: GWS-SA6B-735-U-SLR-W-GRSBK

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	1958.1	1958.1	1958.1	1958.1	1958.1	1958.1	1958.1	1958.1	1958.1	1958.1	1958.1
2.5°	1766.5	1736.5	1720.1	1711.1	1711.1	1699.1	1685.6	1681.1	1700.6	1700.6	1733.5
5°	1591.3	1567.4	1540.4	1524.0	1498.5	1503.0	1488.0	1486.5	1506.0	1515.0	1549.4
7.5°	1470.1	1440.1	1423.7	1413.2	1399.7	1393.7	1380.2	1375.8	1386.2	1401.2	1434.1
10°	1389.2	1384.7	1383.2	1390.7	1390.7	1383.2	1371.3	1363.8	1366.8	1395.2	1432.6
12.5°	1410.2	1419.2	1422.2	1434.1	1440.1	1434.1	1425.2	1428.2	1447.6	1500.0	1555.4
15°	1501.5	1494.0	1491.0	1497.0	1501.5	1495.5	1492.5	1515.0	1582.3	1657.2	1720.1
17.5°	1598.8	1550.9	1530.0	1530.0	1532.9	1530.0	1532.9	1576.4	1685.6	1760.5	1806.9
20°	1648.2	1559.9	1527.0	1519.5	1525.5	1527.0	1537.4	1586.8	1706.6	1759.0	1769.5
22.5°	1633.2	1522.5	1485.0	1479.1	1485.0	1491.0	1501.5	1543.4	1655.7	1682.6	1678.2
25°	1558.4	1449.1	1419.2	1419.2	1432.6	1431.1	1435.6	1465.6	1558.4	1574.9	1567.4
27.5°	1464.1	1360.8	1335.3	1350.3	1362.3	1359.3	1360.8	1386.2	1455.1	1459.6	1452.1
30°	1368.3	1278.5	1254.5	1272.5	1288.9	1285.9	1287.4	1312.9	1356.3	1351.8	1341.3
32.5°	1271.0	1205.1	1187.1	1197.6	1223.1	1220.1	1226.1	1253.0	1269.5	1250.0	1238.0
35°	1181.1	1146.7	1133.2	1139.2	1158.7	1163.2	1173.7	1191.6	1191.6	1167.7	1146.7
37.5°	1097.3	1092.8	1083.8	1076.4	1094.3	1107.8	1122.8	1143.7	1113.8	1079.3	1059.9
40°	1019.5	1038.9	1027.0	1007.5	1018.0	1037.4	1067.4	1083.8	1047.9	1013.5	980.5
42.5°	947.6	980.5	976.1	952.1	961.1	979.0	1013.5	1027.0	985.0	946.1	914.7
45°	878.7	925.2	928.2	898.2	907.2	925.2	965.6	970.1	916.2	874.3	851.8
47.5°	818.9	869.8	871.3	848.8	851.8	877.3	914.7	916.2	854.8	815.9	787.4
50°	762.0	820.4	824.9	805.4	808.4	838.3	869.8	863.8	797.9	757.5	732.0
52.5°	693.1	772.5	782.9	774.0	785.9	809.9	829.3	808.4	732.0	691.6	669.2
55°	618.3	721.6	744.0	738.0	751.5	771.0	775.5	762.0	666.2	625.8	604.8
57.5°	531.4	594.3	633.2	621.3	631.7	651.2	664.7	654.2	582.3	550.9	532.9
60°	440.1	482.0	491.0	471.6	462.6	497.0	528.4	515.0	453.6	434.1	413.2
62.5°	321.9	369.8	375.8	350.3	339.8	377.2	404.2	390.7	323.4	302.4	285.9
65°	257.5	302.4	314.4	290.4	284.4	312.9	329.3	296.4	248.5	226.0	208.1
67.5°	169.2	205.1	236.5	235.0	223.1	232.0	220.1	193.1	158.7	146.7	134.7
70°	104.8	125.7	145.2	152.7	151.2	148.2	131.7	112.3	101.8	97.3	91.3
72.5°	80.8	101.8	116.8	121.3	122.8	118.3	104.8	86.8	76.3	70.4	65.9
75°	59.9	76.3	88.3	94.3	97.3	94.3	80.8	68.9	58.4	53.9	49.4
77.5°	21.0	25.4	31.4	34.4	32.9	31.4	28.4	28.4	22.5	21.0	18.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P641673

CATALOG NUMBER: GWS-SA6B-735-U-SLR-W-GRSBK

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	1958.1	1958.1	1958.1	1958.1	1958.1	1958.1	1958.1	1958.1	1958.1	1958.1
2.5°	1771.0	1797.9	1847.3	1892.2	1940.1	1989.5	2043.4	2098.8	2124.3	2121.3
5°	1601.8	1660.2	1741.0	1829.4	1928.2	2034.4	2152.7	2274.0	2326.4	2348.8
7.5°	1495.5	1577.9	1684.1	1796.4	1926.7	2077.9	2256.0	2446.1	2522.5	2547.9
10°	1509.0	1604.8	1693.1	1802.4	1941.6	2137.7	2359.3	2585.3	2675.2	2703.6
12.5°	1618.3	1639.2	1663.2	1753.0	1928.2	2182.7	2453.6	2723.1	2826.4	2854.8
15°	1717.1	1619.8	1574.9	1657.2	1880.3	2214.1	2549.4	2871.3	2985.1	3018.0
17.5°	1721.6	1574.9	1474.6	1538.9	1802.4	2227.6	2643.7	3022.5	3146.7	3178.2
20°	1666.2	1525.5	1396.7	1398.2	1696.1	2224.6	2721.6	3158.7	3297.9	3326.4
22.5°	1585.3	1467.1	1333.8	1287.4	1582.3	2218.6	2806.9	3303.9	3455.1	3482.1
25°	1495.5	1392.2	1274.0	1203.6	1468.6	2224.6	2926.7	3494.0	3660.2	3685.7
27.5°	1398.2	1309.9	1227.6	1170.7	1372.8	2247.0	3070.4	3736.6	3934.2	3961.1
30°	1296.4	1230.5	1197.6	1163.2	1312.9	2253.0	3226.1	4019.5	4269.5	4306.9
32.5°	1196.1	1160.2	1161.7	1167.7	1256.0	2211.1	3368.3	4333.9	4667.7	4727.6
35°	1103.3	1092.8	1122.8	1152.7	1173.7	2103.3	3492.5	4705.1	5160.2	5221.6
37.5°	1024.0	1032.9	1070.4	1100.3	1083.8	1950.6	3657.2	5169.2	5711.1	5763.5
40°	947.6	970.1	1013.5	1027.0	1015.0	1772.5	3854.8	5616.8	6188.7	6260.5
42.5°	877.3	893.7	955.1	958.1	995.5	1591.3	4044.9	6098.8	6738.1	6775.5
45°	820.4	817.4	880.2	899.7	1021.0	1390.7	4230.6	6741.1	7456.6	7510.5
47.5°	765.0	762.0	777.0	865.3	1031.4	1205.1	4414.7	7681.2	8498.6	8591.4
50°	712.6	717.1	670.7	848.8	974.6	1062.9	4498.5	8551.0	9446.2	9485.1
52.5°	666.2	649.7	568.9	794.9	853.3	928.2	4260.5	8946.2	10033.0	10143.8
55°	600.3	509.0	468.6	645.2	673.7	809.9	3489.5	8717.1	10083.9	10280.0
57.5°	513.5	399.7	398.2	476.1	476.1	751.5	2235.0	7447.7	8690.2	9034.5
60°	395.2	309.9	329.3	330.8	305.4	547.9	1254.5	5395.2	6425.2	6768.0
62.5°	281.4	236.5	248.5	197.6	175.2	274.0	601.8	3106.3	3965.6	4013.5
65°	188.6	160.2	130.2	109.3	107.8	116.8	248.5	1122.8	1365.3	1540.4
67.5°	124.3	97.3	68.9	68.9	77.8	77.8	94.3	185.6	260.5	238.0
70°	80.8	67.4	43.4	41.9	50.9	50.9	47.9	50.9	53.9	53.9
72.5°	59.9	50.9	25.4	22.5	28.4	29.9	26.9	25.4	25.4	25.4
75°	44.9	35.9	15.0	10.5	13.5	18.0	15.0	10.5	10.5	9.0
77.5°	18.0	13.5	6.0	4.5	7.5	10.5	9.0	4.5	3.0	3.0
80°	1.5	3.0	3.0	3.0	4.5	6.0	7.5	3.0	1.5	1.5
82.5°	0.0	1.5	1.5	1.5	3.0	4.5	6.0	3.0	1.5	1.5
85°	0.0	0.0	0.0	0.0	3.0	4.5	3.0	1.5	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	1.5	4.5	3.0	1.5	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)