

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P632264

Luminaire Tested: GWS-SA2C-735-U-SLL-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P632264
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-38)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA2C-735-U-SLL-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (2) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR LEFT OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (32) 3500K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4894.8 lumens
Efficiency: N/A
Efficacy: 77.4 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B1 - U0 - G1


Input Watts (W): 63.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P632264
 CATALOG NUMBER: GWS-SA2C-735-U-SLL-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 13.1 fc
 Type III - Short - N/A

REPORT NUMBER: P632264
CATALOG NUMBER: GWS-SA2C-735-U-SLL-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 315-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P632264

CATALOG NUMBER: GWS-SA2C-735-U-SLL-W-GRSBK


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1054.5 | 0.0 | 1054.5 |
| | % Fixture | 21.5 | 0.0 | 21.5 |
| Street Side | Lumens | 3840.3 | 0.0 | 3840.3 |
| | % Fixture | 78.5 | 0.0 | 78.5 |
| Total | Lumens | 4894.8 | 0.0 | 4894.8 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 82.2 | 1.7 |
| 10°-20° | 270.5 | 5.5 |
| 20°-30° | 439.0 | 9.0 |
| 30°-40° | 673.7 | 13.8 |
| 40°-50° | 1076.0 | 22.0 |
| 50°-60° | 1506.6 | 30.8 |
| 60°-70° | 772.5 | 15.8 |
| 70°-80° | 74.4 | 1.5 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 4894.8 | 100.0 |
| 0°-180° | 4894.8 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P632264


CATALOG NUMBER: GWS-SA2C-735-U-SLL-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 484.6 | 9.9 | | | |
| FM (30°-60°) | 2588.5 | 52.9 | | | |
| FH (60°-80°) | 767.2 | 15.7 | | | G1/1800 |
| FVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| BL (0°-30°) | 307.1 | 6.3 | B1/500 | | |
| BM (30°-60°) | 667.8 | 13.6 | B1/1000 | | |
| BH (60°-80°) | 79.6 | 1.6 | B0/110 | | G0/110 |
| BVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G1

Type III Short





REPORT NUMBER: P632264

CATALOG NUMBER: GWS-SA2C-735-U-SLL-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|-------|-------|-------|-------|-------|-------|
| 0° | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 |
| 2.5° | 924.0 | 922.0 | 915.5 | 893.2 | 879.5 | 857.9 | 842.2 | 821.9 | 799.6 | 785.9 | 772.2 |
| 5° | 1022.1 | 1016.9 | 999.2 | 948.2 | 908.9 | 866.4 | 832.4 | 795.1 | 755.1 | 729.0 | 704.8 |
| 7.5° | 1116.3 | 1108.5 | 1084.9 | 998.6 | 939.0 | 878.2 | 829.7 | 775.4 | 719.1 | 679.9 | 649.8 |
| 10° | 1208.6 | 1190.9 | 1153.6 | 1047.6 | 967.2 | 893.9 | 836.9 | 774.8 | 708.7 | 658.9 | 625.6 |
| 12.5° | 1284.5 | 1271.4 | 1220.4 | 1094.1 | 990.7 | 897.1 | 827.1 | 769.5 | 725.0 | 691.7 | 660.9 |
| 15° | 1350.0 | 1335.6 | 1287.1 | 1136.0 | 1011.0 | 884.0 | 785.9 | 735.5 | 742.7 | 755.8 | 729.6 |
| 17.5° | 1410.2 | 1395.1 | 1342.8 | 1170.7 | 1018.8 | 852.0 | 728.3 | 704.1 | 744.0 | 793.1 | 783.3 |
| 20° | 1472.3 | 1455.3 | 1391.2 | 1198.8 | 1016.2 | 801.6 | 670.1 | 677.3 | 733.5 | 789.8 | 795.1 |
| 22.5° | 1545.0 | 1527.3 | 1452.7 | 1234.8 | 1014.3 | 741.4 | 619.7 | 653.7 | 713.9 | 761.7 | 770.8 |
| 25° | 1641.1 | 1620.2 | 1538.4 | 1287.8 | 1019.5 | 686.4 | 583.7 | 630.8 | 680.5 | 723.7 | 729.0 |
| 27.5° | 1768.1 | 1741.3 | 1637.2 | 1353.2 | 1030.6 | 643.2 | 568.0 | 599.4 | 638.0 | 676.6 | 681.2 |
| 30° | 1933.7 | 1899.6 | 1750.4 | 1410.2 | 1025.4 | 613.1 | 557.5 | 568.0 | 590.9 | 622.3 | 623.0 |
| 32.5° | 2127.3 | 2080.9 | 1877.4 | 1459.2 | 980.2 | 590.9 | 543.1 | 535.9 | 541.2 | 565.4 | 570.0 |
| 35° | 2355.1 | 2294.9 | 2017.4 | 1505.7 | 897.8 | 547.7 | 516.9 | 492.7 | 490.8 | 502.6 | 513.7 |
| 37.5° | 2616.2 | 2544.2 | 2194.1 | 1565.2 | 800.3 | 502.6 | 478.3 | 454.1 | 443.7 | 449.5 | 466.6 |
| 40° | 2857.0 | 2777.1 | 2378.6 | 1637.2 | 700.8 | 462.0 | 433.2 | 408.3 | 395.9 | 397.9 | 418.8 |
| 42.5° | 3139.6 | 3057.2 | 2604.4 | 1731.5 | 618.4 | 434.5 | 386.1 | 360.6 | 344.2 | 353.4 | 377.6 |
| 45° | 3568.9 | 3475.3 | 2933.5 | 1813.2 | 552.9 | 428.0 | 344.9 | 308.9 | 301.0 | 316.7 | 345.5 |
| 47.5° | 4155.2 | 4040.7 | 3385.7 | 1863.0 | 497.3 | 433.8 | 316.1 | 267.0 | 268.9 | 286.6 | 315.4 |
| 50° | 4737.0 | 4613.3 | 3908.5 | 1797.5 | 451.5 | 422.1 | 301.7 | 234.3 | 246.7 | 262.4 | 288.6 |
| 52.5° | 5136.8 | 4975.8 | 4163.1 | 1608.4 | 409.6 | 377.6 | 300.4 | 203.5 | 227.1 | 232.3 | 254.5 |
| 55° | 5152.5 | 4954.2 | 4032.9 | 1268.2 | 352.7 | 318.7 | 286.6 | 178.0 | 205.5 | 207.4 | 226.4 |
| 57.5° | 4516.4 | 4337.1 | 3524.4 | 871.0 | 313.4 | 233.6 | 228.4 | 155.7 | 168.8 | 185.2 | 197.0 |
| 60° | 3436.1 | 3283.6 | 2635.8 | 399.2 | 238.2 | 148.5 | 156.4 | 134.1 | 126.3 | 150.5 | 162.3 |
| 62.5° | 2104.4 | 2006.9 | 1580.9 | 176.7 | 151.8 | 79.2 | 94.9 | 106.7 | 94.9 | 104.0 | 113.9 |
| 65° | 835.6 | 792.4 | 600.1 | 75.3 | 62.2 | 39.9 | 43.2 | 62.2 | 66.7 | 73.3 | 82.5 |
| 67.5° | 145.3 | 137.4 | 100.8 | 33.4 | 25.5 | 24.2 | 20.9 | 28.8 | 40.6 | 45.2 | 52.3 |
| 70° | 19.0 | 18.3 | 16.4 | 13.7 | 13.1 | 11.8 | 9.2 | 18.3 | 27.5 | 28.8 | 33.4 |
| 72.5° | 4.6 | 3.9 | 3.9 | 3.3 | 3.9 | 1.3 | 1.3 | 9.8 | 19.6 | 20.3 | 23.6 |
| 75° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 3.3 | 12.4 | 13.7 | 16.4 |
| 77.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.7 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P632264
 CATALOG NUMBER: GWS-SA2C-735-U-SLL-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 |
| 2.5° | 761.0 | 747.9 | 743.4 | 736.8 | 728.3 | 730.9 | 719.1 | 715.2 | 721.1 | 729.0 | 727.0 |
| 5° | 691.7 | 677.3 | 667.5 | 652.4 | 649.8 | 643.9 | 640.0 | 634.7 | 641.3 | 650.4 | 652.4 |
| 7.5° | 636.7 | 624.3 | 614.4 | 609.9 | 606.6 | 604.0 | 596.1 | 592.2 | 592.2 | 596.1 | 599.4 |
| 10° | 613.1 | 604.0 | 602.0 | 603.3 | 608.6 | 607.9 | 600.7 | 595.5 | 588.9 | 585.7 | 589.6 |
| 12.5° | 645.9 | 630.8 | 628.2 | 628.8 | 635.4 | 634.7 | 626.9 | 620.3 | 619.0 | 620.3 | 632.8 |
| 15° | 701.5 | 678.6 | 661.6 | 658.3 | 661.6 | 660.3 | 654.4 | 650.4 | 652.4 | 671.4 | 692.3 |
| 17.5° | 751.2 | 715.9 | 685.1 | 673.3 | 672.7 | 670.7 | 664.8 | 663.5 | 673.3 | 708.7 | 739.4 |
| 20° | 765.6 | 730.9 | 687.1 | 672.0 | 668.8 | 666.8 | 660.3 | 662.2 | 674.7 | 717.2 | 743.4 |
| 22.5° | 746.6 | 713.3 | 667.5 | 652.4 | 649.8 | 649.1 | 642.6 | 645.2 | 655.7 | 693.0 | 714.6 |
| 25° | 710.6 | 682.5 | 634.7 | 621.6 | 621.6 | 620.3 | 614.4 | 615.8 | 622.3 | 655.0 | 676.0 |
| 27.5° | 666.8 | 640.0 | 600.1 | 587.0 | 588.9 | 590.9 | 583.7 | 581.7 | 587.0 | 617.7 | 630.2 |
| 30° | 616.4 | 597.4 | 566.0 | 554.2 | 553.6 | 561.4 | 551.6 | 549.0 | 556.2 | 580.4 | 583.0 |
| 32.5° | 567.3 | 558.2 | 535.9 | 526.8 | 527.4 | 528.7 | 523.5 | 523.5 | 530.0 | 543.1 | 542.5 |
| 35° | 519.6 | 513.7 | 509.8 | 503.2 | 502.6 | 499.9 | 499.9 | 501.2 | 508.4 | 513.0 | 504.5 |
| 37.5° | 473.8 | 479.7 | 484.2 | 477.7 | 472.5 | 472.5 | 472.5 | 478.3 | 484.9 | 482.9 | 468.5 |
| 40° | 433.2 | 445.6 | 460.0 | 452.8 | 440.4 | 439.7 | 442.4 | 452.2 | 462.0 | 450.2 | 437.1 |
| 42.5° | 398.5 | 414.2 | 434.5 | 430.6 | 416.8 | 414.9 | 416.8 | 429.3 | 437.1 | 422.1 | 407.7 |
| 45° | 364.5 | 384.1 | 408.3 | 408.3 | 393.3 | 391.3 | 392.0 | 408.3 | 412.9 | 395.2 | 376.9 |
| 47.5° | 335.7 | 357.3 | 382.8 | 382.8 | 370.4 | 366.4 | 369.7 | 386.7 | 390.0 | 365.1 | 348.1 |
| 50° | 308.2 | 331.8 | 359.9 | 357.9 | 349.4 | 346.2 | 352.0 | 370.4 | 366.4 | 339.0 | 321.3 |
| 52.5° | 273.5 | 298.4 | 337.0 | 339.0 | 334.4 | 335.0 | 342.2 | 354.0 | 342.9 | 309.5 | 294.5 |
| 55° | 242.1 | 267.6 | 306.2 | 316.7 | 316.7 | 316.1 | 319.3 | 328.5 | 319.3 | 279.4 | 261.1 |
| 57.5° | 208.1 | 229.7 | 261.7 | 264.4 | 266.3 | 259.1 | 263.7 | 276.1 | 271.6 | 237.5 | 227.1 |
| 60° | 170.8 | 189.1 | 207.4 | 209.4 | 200.9 | 185.8 | 194.3 | 208.7 | 212.0 | 186.5 | 174.7 |
| 62.5° | 121.1 | 138.7 | 160.3 | 160.3 | 151.8 | 136.8 | 147.9 | 160.3 | 155.7 | 129.6 | 122.4 |
| 65° | 90.3 | 106.7 | 123.0 | 130.2 | 123.0 | 112.6 | 121.1 | 130.2 | 123.0 | 101.4 | 91.0 |
| 67.5° | 58.2 | 69.4 | 79.2 | 85.1 | 86.4 | 85.1 | 89.0 | 86.4 | 77.9 | 63.5 | 57.6 |
| 70° | 35.3 | 41.2 | 46.5 | 51.7 | 55.6 | 57.6 | 59.5 | 53.7 | 45.2 | 37.3 | 35.3 |
| 72.5° | 25.5 | 30.8 | 35.3 | 39.3 | 43.8 | 45.2 | 45.2 | 41.2 | 33.4 | 26.2 | 24.2 |
| 75° | 17.7 | 22.2 | 26.2 | 28.8 | 32.7 | 34.0 | 34.0 | 30.8 | 24.9 | 19.0 | 17.0 |
| 77.5° | 0.7 | 4.6 | 4.6 | 3.9 | 5.2 | 6.5 | 6.5 | 7.9 | 7.2 | 5.2 | 4.6 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P632264
 CATALOG NUMBER: GWS-SA2C-735-U-SLL-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|-------|-------|-------|-------|-------|-------|-------|--------|--------|--------|--------|
| 0° | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 |
| 2.5° | 730.9 | 754.5 | 761.0 | 785.2 | 806.8 | 828.4 | 854.6 | 870.3 | 893.9 | 910.2 | 919.4 |
| 5° | 658.9 | 678.6 | 702.1 | 738.1 | 775.4 | 816.6 | 866.4 | 909.6 | 963.9 | 1003.8 | 1016.9 |
| 7.5° | 606.6 | 632.1 | 659.6 | 704.8 | 755.8 | 810.8 | 880.8 | 951.4 | 1034.6 | 1088.9 | 1123.5 |
| 10° | 596.8 | 623.0 | 659.6 | 704.1 | 757.8 | 820.6 | 906.3 | 997.9 | 1102.0 | 1168.0 | 1207.3 |
| 12.5° | 643.9 | 672.0 | 687.7 | 708.0 | 748.6 | 818.6 | 928.5 | 1045.0 | 1167.4 | 1239.4 | 1281.2 |
| 15° | 713.3 | 738.1 | 712.6 | 687.1 | 713.3 | 797.7 | 941.0 | 1084.3 | 1225.0 | 1308.1 | 1351.3 |
| 17.5° | 761.0 | 763.0 | 707.4 | 653.1 | 660.3 | 759.7 | 945.6 | 1123.5 | 1286.5 | 1373.5 | 1418.7 |
| 20° | 756.4 | 740.7 | 684.5 | 624.3 | 602.0 | 710.6 | 940.3 | 1158.2 | 1348.6 | 1439.6 | 1484.1 |
| 22.5° | 721.1 | 702.8 | 655.0 | 596.1 | 552.9 | 652.4 | 931.2 | 1189.6 | 1405.6 | 1509.0 | 1550.8 |
| 25° | 678.6 | 658.9 | 619.7 | 568.0 | 521.5 | 596.1 | 924.0 | 1232.8 | 1477.6 | 1599.3 | 1632.0 |
| 27.5° | 628.8 | 611.8 | 578.5 | 541.2 | 508.4 | 553.6 | 922.0 | 1289.8 | 1564.6 | 1709.2 | 1732.1 |
| 30° | 580.4 | 564.7 | 538.5 | 516.9 | 503.2 | 528.7 | 915.5 | 1350.6 | 1668.6 | 1835.5 | 1860.4 |
| 32.5° | 534.0 | 518.3 | 501.9 | 498.6 | 499.3 | 519.6 | 893.2 | 1410.8 | 1792.3 | 2018.7 | 2037.0 |
| 35° | 494.0 | 475.7 | 469.2 | 477.0 | 491.4 | 503.9 | 830.4 | 1460.5 | 1925.1 | 2218.3 | 2233.4 |
| 37.5° | 456.1 | 437.8 | 437.1 | 456.1 | 471.8 | 479.7 | 756.4 | 1509.6 | 2104.4 | 2421.2 | 2440.1 |
| 40° | 421.4 | 403.1 | 409.6 | 432.5 | 445.0 | 448.9 | 666.8 | 1584.2 | 2294.2 | 2635.1 | 2624.7 |
| 42.5° | 392.0 | 373.0 | 376.9 | 406.4 | 417.5 | 428.0 | 584.3 | 1646.4 | 2476.8 | 2838.0 | 2834.7 |
| 45° | 363.2 | 348.8 | 346.2 | 378.2 | 388.0 | 429.9 | 524.1 | 1694.2 | 2711.7 | 3096.5 | 3101.7 |
| 47.5° | 335.0 | 323.9 | 324.6 | 338.3 | 362.5 | 439.7 | 473.1 | 1725.6 | 3052.6 | 3506.1 | 3415.1 |
| 50° | 309.5 | 301.0 | 308.2 | 292.5 | 346.2 | 427.3 | 429.3 | 1719.0 | 3433.5 | 3898.7 | 3716.1 |
| 52.5° | 281.4 | 279.4 | 282.7 | 244.7 | 320.0 | 376.9 | 388.0 | 1632.0 | 3612.1 | 4167.0 | 4063.0 |
| 55° | 252.6 | 251.9 | 225.8 | 195.7 | 267.6 | 301.0 | 332.4 | 1361.7 | 3606.2 | 4309.7 | 4435.9 |
| 57.5° | 218.6 | 213.3 | 171.4 | 159.7 | 208.1 | 209.4 | 303.0 | 891.9 | 3195.9 | 3968.1 | 4229.8 |
| 60° | 165.6 | 161.6 | 125.6 | 129.6 | 145.3 | 134.1 | 241.5 | 444.3 | 2388.4 | 3091.2 | 3386.3 |
| 62.5° | 114.5 | 109.3 | 93.6 | 100.1 | 93.6 | 76.6 | 147.9 | 219.9 | 1446.8 | 1952.0 | 2219.6 |
| 65° | 83.8 | 77.9 | 64.1 | 55.0 | 43.8 | 43.8 | 56.3 | 84.4 | 560.1 | 829.7 | 1000.5 |
| 67.5° | 51.7 | 49.1 | 38.0 | 27.5 | 26.8 | 28.8 | 29.4 | 41.9 | 90.3 | 144.0 | 176.0 |
| 70° | 33.4 | 30.8 | 25.5 | 17.7 | 16.4 | 17.0 | 17.7 | 19.6 | 22.9 | 24.9 | 30.1 |
| 72.5° | 22.9 | 21.6 | 18.3 | 9.8 | 7.9 | 8.5 | 9.2 | 9.2 | 11.1 | 10.5 | 12.4 |
| 75° | 16.4 | 15.1 | 13.1 | 4.6 | 2.6 | 3.3 | 3.9 | 3.3 | 3.9 | 2.6 | 3.3 |
| 77.5° | 4.6 | 4.6 | 3.3 | 0.7 | 0.0 | 0.7 | 1.3 | 1.3 | 0.7 | 0.0 | 0.0 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.7 | 0.7 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P632264

CATALOG NUMBER: GWS-SA2C-735-U-SLL-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 | 831.7 |
| 2.5° | 942.9 | 958.0 | 963.9 | 955.4 | 962.6 | 950.8 | 946.2 | 928.5 | 927.2 | 924.0 |
| 5° | 1069.9 | 1103.9 | 1124.2 | 1136.6 | 1122.2 | 1106.5 | 1083.0 | 1042.4 | 1030.0 | 1022.1 |
| 7.5° | 1194.9 | 1247.9 | 1282.6 | 1298.9 | 1295.0 | 1262.9 | 1220.4 | 1152.3 | 1128.1 | 1116.3 |
| 10° | 1303.5 | 1368.3 | 1410.2 | 1430.4 | 1421.9 | 1393.8 | 1332.9 | 1247.9 | 1215.8 | 1208.6 |
| 12.5° | 1379.4 | 1439.0 | 1467.7 | 1485.4 | 1486.1 | 1474.9 | 1417.4 | 1331.6 | 1293.7 | 1284.5 |
| 15° | 1427.2 | 1452.7 | 1453.3 | 1463.8 | 1482.1 | 1507.0 | 1480.2 | 1404.3 | 1363.7 | 1350.0 |
| 17.5° | 1457.3 | 1429.1 | 1400.3 | 1403.0 | 1433.1 | 1499.2 | 1526.6 | 1468.4 | 1425.2 | 1410.2 |
| 20° | 1478.9 | 1389.9 | 1336.2 | 1336.9 | 1367.6 | 1467.7 | 1558.7 | 1530.6 | 1486.1 | 1472.3 |
| 22.5° | 1492.6 | 1355.2 | 1278.6 | 1276.7 | 1309.4 | 1430.4 | 1588.1 | 1604.5 | 1560.7 | 1545.0 |
| 25° | 1520.7 | 1338.8 | 1243.9 | 1255.1 | 1283.9 | 1418.7 | 1628.1 | 1702.7 | 1662.1 | 1641.1 |
| 27.5° | 1571.1 | 1355.2 | 1240.7 | 1266.2 | 1298.9 | 1453.3 | 1697.4 | 1833.5 | 1791.7 | 1768.1 |
| 30° | 1658.2 | 1416.7 | 1291.1 | 1326.4 | 1365.7 | 1544.3 | 1813.9 | 2016.1 | 1955.9 | 1933.7 |
| 32.5° | 1798.2 | 1544.3 | 1446.8 | 1522.7 | 1560.7 | 1693.5 | 1988.6 | 2220.9 | 2171.8 | 2127.3 |
| 35° | 1991.2 | 1835.5 | 1824.4 | 2001.1 | 1991.9 | 1976.2 | 2203.2 | 2472.2 | 2398.3 | 2355.1 |
| 37.5° | 2256.9 | 2304.0 | 2386.5 | 2561.8 | 2556.0 | 2436.2 | 2485.3 | 2709.7 | 2671.8 | 2616.2 |
| 40° | 2588.7 | 2688.8 | 2828.8 | 3080.1 | 3001.6 | 2851.1 | 2831.4 | 2953.2 | 2922.4 | 2857.0 |
| 42.5° | 2784.3 | 2957.1 | 3224.1 | 3449.8 | 3387.0 | 3123.9 | 3101.7 | 3278.4 | 3211.0 | 3139.6 |
| 45° | 2875.3 | 3175.6 | 3699.1 | 4004.7 | 3814.3 | 3305.2 | 3296.7 | 3702.4 | 3664.4 | 3568.9 |
| 47.5° | 2917.2 | 3396.2 | 4255.3 | 4718.0 | 4362.0 | 3464.2 | 3433.5 | 4317.5 | 4267.8 | 4155.2 |
| 50° | 2963.6 | 3700.4 | 4925.4 | 5544.4 | 5023.6 | 3644.2 | 3666.4 | 4890.7 | 4869.8 | 4737.0 |
| 52.5° | 3065.7 | 4022.4 | 5750.6 | 6489.3 | 5825.8 | 3926.2 | 4066.2 | 5431.2 | 5289.9 | 5136.8 |
| 55° | 3218.8 | 4373.1 | 6609.1 | 7454.5 | 6644.4 | 4305.1 | 4498.8 | 5718.5 | 5322.0 | 5152.5 |
| 57.5° | 3049.3 | 4460.8 | 7117.5 | 8128.5 | 7007.6 | 4306.4 | 4133.0 | 5220.5 | 4680.7 | 4516.4 |
| 60° | 2419.8 | 4150.0 | 6921.9 | 7982.6 | 6698.1 | 3824.1 | 3164.5 | 4076.0 | 3546.0 | 3436.1 |
| 62.5° | 1635.9 | 3480.6 | 6093.5 | 6751.1 | 5732.9 | 3008.1 | 2056.7 | 2650.8 | 2195.4 | 2104.4 |
| 65° | 896.5 | 2596.5 | 4923.4 | 5107.3 | 4487.0 | 2101.2 | 1058.1 | 1150.4 | 876.2 | 835.6 |
| 67.5° | 247.4 | 1807.4 | 3622.6 | 3388.3 | 3148.2 | 1368.3 | 273.5 | 205.5 | 146.6 | 145.3 |
| 70° | 62.2 | 1195.5 | 2170.5 | 2237.3 | 1930.4 | 876.2 | 52.3 | 24.9 | 19.6 | 19.0 |
| 72.5° | 26.2 | 514.3 | 1030.0 | 1183.7 | 988.1 | 405.7 | 19.0 | 7.2 | 5.9 | 4.6 |
| 75° | 3.3 | 41.2 | 87.7 | 132.8 | 91.0 | 43.8 | 0.0 | 0.0 | 0.0 | 0.0 |
| 77.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

All Brands

Data applicable to all product families using SA light engines

Report Number: SP1-2101-121-7

Luminaire Tested: IFLD-S-SA2A-735-U-T2

Test Date: 03/04/2021


Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/04/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-735-U-T2**
 Description: STREETWORKS INF FLOOD

PROGRAMMED @ 615mA.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 3388 | CRI (Ra): | 73.1 | R9: | -34.6 |
| CIE u': | 0.2371 | R1: | 68.9 | R10: | 57.8 |
| CIE v': | 0.5177 | R2: | 81.1 | R11: | 68.6 |
| Duv: | 0.0032 | R3: | 93.1 | R12: | 53.9 |
| CIE x: | 0.4153 | R4: | 71.6 | R13: | 70.9 |
| CIE y: | 0.4030 | R5: | 69.4 | R14: | 96.2 |
| CIE z: | 0.1817 | R6: | 75.0 | | |
| Peak Wavelength (nm): | 590 | R7: | 79.5 | | |
| Dominant Wavelength (nm): | 580 | R8: | 46.4 | | |
| Purity: | 45.7 | | | | |
| Rf: | 76.9 | | | | |
| Rg: | 94.4 | | | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0/30%
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-7


| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-121-7

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-7

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 4.9 | 620 | 136720 | 35.6 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 8.0 | 625 | 126308 | 27.9 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 12.1 | 630 | 114625 | 20.7 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 18.1 | 635 | 103216 | 15.5 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 25.4 | 640 | 92605 | 11.1 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 33.9 | 645 | 83234 | 8.0 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 43.0 | 650 | 73263 | 5.4 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 50.1 | 655 | 64627 | 3.7 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 57.9 | 660 | 56614 | 2.4 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.0 | 535 | 103269 | 64.0 | 665 | 49537 | 1.6 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.0 | 540 | 107316 | 69.9 | 670 | 42866 | 0.9 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.0 | 545 | 113101 | 75.3 | 675 | 36708 | 0.6 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 0.0 | 550 | 120690 | 82.0 | 680 | 31814 | 0.4 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 0.1 | 555 | 128583 | 87.8 | 685 | 27485 | 0.2 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 0.3 | 560 | 137796 | 93.6 | 690 | 23698 | 0.1 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 0.8 | 565 | 146577 | 97.5 | 695 | 20309 | 0.1 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 1.6 | 570 | 154581 | 100.5 | 700 | 17890 | 0.1 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 2.4 | 575 | 162633 | 101.2 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 2.5 | 580 | 168101 | 99.9 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 2.1 | 585 | 173145 | 96.2 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 1.8 | 590 | 174675 | 90.3 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 1.7 | 595 | 173724 | 82.3 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 1.5 | 600 | 171241 | 73.8 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 1.7 | 605 | 165134 | 64.0 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 2.2 | 610 | 156652 | 53.8 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 3.3 | 615 | 147879 | 44.6 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-7

Scotopic Flux vs. Wavelength



Scotopic Lumens: 12126

S/P: 1.36

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 53.2 | 620 | 136720 | 1.7 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 71.7 | 625 | 126308 | 1.1 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 91.4 | 630 | 114625 | 0.6 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 110.0 | 635 | 103216 | 0.4 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 125.1 | 640 | 92605 | 0.2 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 135.7 | 645 | 83234 | 0.1 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 140.8 | 650 | 73263 | 0.1 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 139.6 | 655 | 64627 | 0.1 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 135.7 | 660 | 56614 | 0.0 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.1 | 535 | 103269 | 128.7 | 665 | 49537 | 0.0 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.2 | 540 | 107316 | 118.6 | 670 | 42866 | 0.0 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.6 | 545 | 113101 | 108.4 | 675 | 36708 | 0.0 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 2.0 | 550 | 120690 | 98.7 | 680 | 31814 | 0.0 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 5.9 | 555 | 128583 | 87.9 | 685 | 27485 | 0.0 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 14.3 | 560 | 137796 | 77.0 | 690 | 23698 | 0.0 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 30.5 | 565 | 146577 | 65.8 | 695 | 20309 | 0.0 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 55.5 | 570 | 154581 | 54.6 | 700 | 17890 | 0.0 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 77.4 | 575 | 162633 | 44.3 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 73.6 | 580 | 168101 | 34.6 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 53.7 | 585 | 173145 | 26.5 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 41.9 | 590 | 174675 | 19.5 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 34.3 | 595 | 173724 | 13.9 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 27.9 | 600 | 171241 | 9.7 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 27.1 | 605 | 165134 | 6.5 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 31.3 | 610 | 156652 | 4.2 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 40.0 | 615 | 147879 | 2.7 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: 4490.7 M/P: 0.5

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 28.8 | 620 | 136720 | 0.1 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 36.6 | 625 | 126308 | 0.1 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 43.9 | 630 | 114625 | 0.0 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 49.6 | 635 | 103216 | 0.0 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 53.0 | 640 | 92605 | 0.0 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 53.5 | 645 | 83234 | 0.0 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 51.6 | 650 | 73263 | 0.0 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 47.3 | 655 | 64627 | 0.0 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 42.5 | 660 | 56614 | 0.0 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.0 | 535 | 103269 | 37.2 | 665 | 49537 | 0.0 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.1 | 540 | 107316 | 31.4 | 670 | 42866 | 0.0 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.4 | 545 | 113101 | 26.3 | 675 | 36708 | 0.0 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 1.4 | 550 | 120690 | 21.7 | 680 | 31814 | 0.0 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 3.7 | 555 | 128583 | 17.3 | 685 | 27485 | 0.0 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 8.9 | 560 | 137796 | 13.6 | 690 | 23698 | 0.0 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 18.2 | 565 | 146577 | 10.3 | 695 | 20309 | 0.0 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 33.2 | 570 | 154581 | 7.6 | 700 | 17890 | 0.0 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 45.6 | 575 | 162633 | 5.4 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 43.8 | 580 | 168101 | 3.8 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 32.2 | 585 | 173145 | 2.6 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 25.6 | 590 | 174675 | 1.7 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 21.2 | 595 | 173724 | 1.1 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 17.4 | 600 | 171241 | 0.7 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 16.6 | 605 | 165134 | 0.5 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 18.6 | 610 | 156652 | 0.3 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 22.7 | 615 | 147879 | 0.2 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

Summary

$R_f = 76.9$
 $R_g = 94.4$
 $CIE R_a = 73.1$
 $R_g = -34.6$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 68 | CES51 = 90 | CES76 = 63 |
| CES02 = 62 | CES27 = 88 | CES52 = 89 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 80 | CES78 = 65 |
| CES04 = 70 | CES29 = 67 | CES54 = 84 | CES79 = 87 |
| CES05 = 48 | CES30 = 74 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 71 | CES56 = 75 | CES81 = 75 |
| CES07 = 40 | CES32 = 67 | CES57 = 74 | CES82 = 94 |
| CES08 = 39 | CES33 = 74 | CES58 = 76 | CES83 = 91 |
| CES09 = 29 | CES34 = 78 | CES59 = 87 | CES84 = 89 |
| CES10 = 75 | CES35 = 89 | CES60 = 93 | CES85 = 80 |
| CES11 = 58 | CES36 = 98 | CES61 = 86 | CES86 = 66 |
| CES12 = 64 | CES37 = 86 | CES62 = 89 | CES87 = 79 |
| CES13 = 43 | CES38 = 82 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 95 | CES64 = 74 | CES89 = 70 |
| CES15 = 71 | CES40 = 91 | CES65 = 68 | CES90 = 77 |
| CES16 = 47 | CES41 = 89 | CES66 = 71 | CES91 = 88 |
| CES17 = 50 | CES42 = 88 | CES67 = 69 | CES92 = 60 |
| CES18 = 56 | CES43 = 82 | CES68 = 74 | CES93 = 77 |
| CES19 = 72 | CES44 = 99 | CES69 = 82 | CES94 = 52 |
| CES20 = 65 | CES45 = 87 | CES70 = 67 | CES95 = 69 |
| CES21 = 86 | CES46 = 82 | CES71 = 66 | CES96 = 78 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 85 |
| CES23 = 92 | CES48 = 72 | CES73 = 59 | CES98 = 76 |
| CES24 = 91 | CES49 = 82 | CES74 = 97 | CES99 = 63 |
| CES25 = 72 | CES50 = 88 | CES75 = 66 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)