

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P832822

Luminaire Tested: **TTN-D0-735-U-WQ-CG-UPL1**

Issue Date: 5/15/2024

Test Information

Test Method: LM-79-08
Report Number: P832822
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND
Test Lab: INNOVATION CENTER
Issue Date: 5/15/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: TTN-D0-735-U-WQ-CG-UPL1
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT
3500K, 70 CRI LEDS AND WIDE DISTRIBUTION WITH CLEAR GLASS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1394.9 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')
IES Classification: Type V - Short
BUG Rating: B1 - U3 - G1


Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P832822
 CATALOG NUMBER: TTN-D0-735-U-WQ-CG-UPL1

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.2 fc
 Type V - Short - N/A

REPORT NUMBER: P832822
CATALOG NUMBER: TTN-D0-735-U-WQ-CG-UPL1

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P832822
 CATALOG NUMBER: TTN-D0-735-U-WQ-CG-UPL1


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	547.2	150.2	697.4
	% Fixture	39.2	10.8	50.0
Street Side	Lumens	547.2	150.2	697.4
	% Fixture	39.2	10.8	50.0
Total	Lumens	1094.4	300.5	1394.9
	% Fixture	78.5	21.5	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	9.9	0.7
10°-20°	31.9	2.3
20°-30°	67.0	4.8
30°-40°	120.9	8.7
40°-50°	192.1	13.8
50°-60°	256.3	18.4
60°-70°	247.7	17.8
70°-80°	143.5	10.3
80°-90°	25.1	1.8
90°-100°	6.7	0.5
100°-110°	68.2	4.9
110°-120°	99.6	7.1
120°-130°	57.8	4.1
130°-140°	30.6	2.2
140°-150°	18.2	1.3
150°-160°	11.2	0.8
160°-170°	6.1	0.4
170°-180°	2.0	0.1
0°-90°	1094.4	78.5
0°-180°	1394.9	100.0

Coefficient of Utilization




REPORT NUMBER: P832822
 CATALOG NUMBER: TTN-D0-735-U-WQ-CG-UPL1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	54.4	3.9			
FM (30°-60°)	284.7	20.4			
FH (60°-80°)	195.6	14.0			G0/660
FVH (80°-90°)	12.6	0.9			G1/100
BL (0°-30°)	54.4	3.9	B0/110		
BM (30°-60°)	284.7	20.4	B1/1000		
BH (60°-80°)	195.6	14.0	B1/500		G0/660
BVH (80°-90°)	12.6	0.9			G1/100
UL (90°-100°)	6.7	0.5		U1/10	
UH (100°-180°)	293.8	21.1		U3/500	

BUG Rating: B1-U3-G1
 Type V Short





REPORT NUMBER: P832822

CATALOG NUMBER: TTN-D0-735-U-WQ-CG-UPL1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	103.3	103.3	103.3	103.3	103.3	103.3	103.3	103.3	103.3	103.3	103.3
2.5°	102.4	102.4	102.4	102.4	102.4	102.4	102.4	102.4	102.4	102.4	102.4
5°	103.3	103.3	103.3	103.3	103.3	103.3	103.3	103.3	103.3	103.3	103.3
7.5°	102.4	102.4	103.3	103.3	103.3	103.3	103.3	103.3	103.3	102.4	102.4
10°	103.3	103.3	103.3	104.3	104.3	104.3	104.3	104.3	103.3	103.3	103.3
12.5°	105.2	105.2	106.2	106.2	106.2	106.2	106.2	106.2	106.2	105.2	105.2
15°	110.0	110.0	110.0	110.9	110.9	110.9	110.9	110.9	110.0	110.0	110.0
17.5°	114.7	114.7	115.7	115.7	116.6	116.6	116.6	115.7	115.7	115.7	115.7
20°	121.4	121.4	122.3	122.3	123.3	124.2	124.2	123.3	122.3	122.3	122.3
22.5°	129.9	130.8	130.8	130.8	131.8	133.7	132.7	131.8	130.8	130.8	130.8
25°	140.3	141.3	142.2	142.2	143.2	145.1	145.1	142.2	142.2	142.2	142.2
27.5°	152.7	153.6	154.5	154.5	155.5	157.4	156.4	154.5	154.5	153.6	153.6
30°	164.0	165.0	165.9	166.9	167.8	168.8	168.8	166.9	165.9	165.0	164.0
32.5°	175.4	175.4	177.3	179.2	181.1	181.1	182.0	179.2	177.3	175.4	174.5
35°	186.8	187.7	188.7	191.5	194.4	195.3	194.4	191.5	188.7	186.8	186.8
37.5°	199.1	200.1	201.0	204.8	207.6	209.5	207.6	204.8	201.0	199.1	198.2
40°	212.4	213.3	214.3	219.0	221.9	223.8	220.9	218.1	214.3	212.4	211.4
42.5°	224.7	226.6	228.5	234.2	238.9	240.8	238.0	233.2	229.4	224.7	223.8
45°	239.9	241.8	244.6	250.3	255.0	257.9	254.1	249.4	243.7	239.9	238.9
47.5°	252.2	254.1	256.9	264.5	271.2	273.1	269.3	263.6	256.0	251.3	250.3
50°	261.7	263.6	269.3	277.8	285.4	287.3	283.5	275.9	267.4	260.7	259.8
52.5°	269.3	271.2	277.8	289.2	297.7	300.6	295.8	287.3	275.9	268.3	267.4
55°	273.1	274.0	282.5	294.9	303.4	307.2	302.5	293.0	280.6	272.1	271.2
57.5°	270.2	271.2	280.6	293.9	303.4	308.1	303.4	292.0	278.8	270.2	269.3
60°	264.5	264.5	273.1	288.2	299.6	302.5	297.7	286.3	272.1	263.6	262.6
62.5°	254.1	253.2	263.6	276.9	288.2	291.1	287.3	275.9	261.7	253.2	252.2
65°	234.2	232.3	247.5	259.8	270.2	273.1	270.2	259.8	246.5	233.2	231.3
67.5°	210.5	207.6	221.9	236.1	245.6	249.4	245.6	237.0	221.9	208.6	207.6
70°	185.8	183.0	194.4	206.7	217.1	219.0	215.2	206.7	192.5	183.9	183.9
72.5°	156.4	153.6	164.0	173.5	183.9	185.8	182.0	174.5	164.0	155.5	154.5
75°	124.2	121.4	130.8	138.4	148.9	149.8	147.9	139.4	130.8	122.3	122.3
77.5°	92.0	89.1	96.7	103.3	111.9	111.9	110.9	104.3	96.7	91.0	91.0
80°	60.7	58.8	65.4	68.3	75.9	75.9	74.9	70.2	64.5	60.7	59.7
82.5°	34.1	32.2	37.9	38.9	44.6	44.6	43.6	39.8	36.0	33.2	33.2
85°	13.3	11.4	15.2	16.1	19.0	19.0	18.0	17.1	14.2	12.3	12.3
87.5°	0.9	0.9	1.9	1.9	2.8	2.8	2.8	1.9	1.9	0.9	0.9
90°	2.6	2.6	3.1	3.1	3.1	3.1	3.1	3.1	3.1	2.6	2.6
92.5°	2.6	2.6	2.6	3.6	4.1	3.6	4.1	3.1	3.1	2.6	2.6
95°	3.1	3.1	3.6	4.6	5.7	6.2	6.2	3.6	3.6	3.1	3.1
97.5°	4.1	4.6	4.6	5.7	9.3	17.0	10.3	5.1	5.1	4.6	4.1
100°	6.7	7.2	7.2	12.9	27.2	36.5	26.2	13.4	9.8	7.2	7.2
102.5°	21.6	22.6	27.8	41.6	61.7	56.0	47.3	44.7	30.8	24.7	23.6
105°	55.0	54.5	58.6	69.4	86.4	84.8	78.1	70.9	61.2	56.5	56.5
107.5°	72.5	72.5	76.1	85.3	98.2	114.6	116.2	92.0	80.7	75.6	75.0
110°	81.7	81.7	84.8	92.5	109.5	132.6	131.6	113.6	99.7	93.0	92.0



REPORT NUMBER: P832822
 CATALOG NUMBER: TTN-D0-735-U-WQ-CG-UPL1

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	83.8	84.3	88.4	100.2	118.7	129.0	124.4	117.2	111.0	105.9	104.9
115°	86.9	86.9	91.5	102.8	113.1	117.2	112.1	106.4	102.3	100.2	101.3
117.5°	85.8	87.4	88.4	94.6	101.3	104.4	101.8	94.1	91.0	90.0	88.4
120°	79.7	79.7	80.7	83.8	87.4	88.9	87.9	82.8	80.2	79.7	78.6
122.5°	70.9	71.5	70.9	72.5	75.0	76.6	75.6	71.5	70.4	70.4	69.4
125°	62.2	62.2	61.7	62.7	64.3	63.7	64.3	62.2	61.7	61.7	61.2
127.5°	56.0	55.5	54.5	55.0	55.5	55.5	56.0	54.0	54.5	55.0	54.5
130°	49.9	49.9	48.8	48.8	48.8	47.8	48.8	47.8	48.3	48.8	49.3
132.5°	44.2	44.2	42.7	42.2	42.2	42.2	42.7	42.2	43.2	44.2	44.2
135°	39.6	39.6	38.0	38.6	38.6	38.0	38.6	38.0	39.1	39.6	39.6
137.5°	36.0	36.0	35.0	35.0	35.0	34.4	35.0	35.0	35.5	36.5	37.0
140°	32.9	32.9	32.4	32.4	31.9	32.4	32.4	32.4	32.9	33.4	33.4
142.5°	31.4	30.8	30.3	29.8	30.3	30.3	30.3	29.8	30.3	31.4	31.4
145°	28.8	28.8	28.3	28.3	28.3	28.8	28.3	28.3	28.8	28.8	29.3
147.5°	27.2	27.2	26.7	27.2	27.2	27.2	27.2	26.7	27.2	27.2	27.8
150°	26.7	26.2	25.7	26.2	26.2	25.7	25.7	25.7	25.7	26.2	26.2
152.5°	25.2	25.2	24.7	25.2	24.7	24.7	24.7	24.7	24.7	25.2	25.7
155°	24.2	24.2	23.6	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2
157.5°	23.1	23.6	23.1	23.1	23.1	23.1	23.1	23.1	23.1	23.6	23.6
160°	22.6	22.6	22.6	22.6	22.1	22.1	22.1	22.6	22.6	22.6	23.1
162.5°	22.1	22.1	22.1	22.1	21.6	21.6	21.6	21.6	22.1	22.1	22.6
165°	22.1	21.6	21.6	21.6	21.1	21.1	21.1	21.1	21.6	22.1	21.6
167.5°	21.1	21.1	21.1	21.1	21.1	20.6	20.6	21.1	21.1	21.1	21.6
170°	21.1	21.1	20.6	20.6	20.6	20.6	20.6	20.6	20.6	20.6	21.1
172.5°	21.1	21.1	21.1	21.1	20.6	20.6	20.6	20.6	20.6	21.1	21.1
175°	21.1	21.1	21.1	21.1	20.6	20.6	20.6	21.1	21.1	21.1	20.6
177.5°	21.1	21.1	21.1	21.1	20.6	21.1	21.1	21.1	21.1	21.1	21.1
180°	21.1	21.1	21.1	21.1	21.1	21.1	21.1	21.1	21.1	21.1	21.1

(END OF REPORT)