

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P640171

Luminaire Tested: GWS-SA5D-735-U-RW-W-GRSBK

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P640171  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-50)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA5D-735-U-RW-W-GRSBK  
Description: GALLEON WALL SLIM LUMINAIRE. (5) LIGHTSQUARES WITH 16 LEDS EACH AND RECTANGULAR WIDE OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK  
Light Source: (80) 3500K CCT, 70 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 19203.4 lumens  
Efficiency: N/A  
Efficacy: 93.9 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B4 - U0 - G0  
  
Input Watts (W): 204.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P640171  
 CATALOG NUMBER: GWS-SA5D-735-U-RW-W-GRSBK

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 5.2 fc  
 Type V - Short - N/A

REPORT NUMBER: P640171  
CATALOG NUMBER: GWS-SA5D-735-U-RW-W-GRSBK

### Luminous Intensity Polar Plot



— Vertical Plane Through 43-Deg Lateral    - - - Horizontal Cone Through 50-Deg Vertical

REPORT NUMBER: P640171  
 CATALOG NUMBER: GWS-SA5D-735-U-RW-W-GRSBK


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 9601.5   | 0.0    | 9601.5  |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Street Side</b> | Lumens    | 9601.9   | 0.0    | 9601.9  |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Total</b>       | Lumens    | 19203.4  | 0.0    | 19203.4 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 269.0   | 1.4       |
| 10°-20°   | 925.6   | 4.8       |
| 20°-30°   | 1872.7  | 9.8       |
| 30°-40°   | 3474.5  | 18.1      |
| 40°-50°   | 5767.5  | 30.0      |
| 50°-60°   | 5886.0  | 30.7      |
| 60°-70°   | 965.2   | 5.0       |
| 70°-80°   | 42.3    | 0.2       |
| 80°-90°   | 0.6     | 0.0       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 19203.4 | 100.0     |
| 0°-180°   | 19203.4 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P640171


CATALOG NUMBER: GWS-SA5D-735-U-RW-W-GRSBK

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |        |
|----------------|--------|-----------|-------------------------|------|--------|
|                |        |           | B                       | U    | G      |
| FL (0°-30°)    | 1547.1 | 8.1       |                         |      |        |
| FM (30°-60°)   | 7582.4 | 39.5      |                         |      |        |
| FH (60°-80°)   | 472.2  | 2.5       |                         |      | G0/660 |
| FVH (80°-90°)  | 0.2    | 0.0       |                         |      | G0/10  |
| BL (0°-30°)    | 1520.2 | 7.9       | B3/2500                 |      |        |
| BM (30°-60°)   | 7545.6 | 39.3      | B4/8500                 |      |        |
| BH (60°-80°)   | 535.3  | 2.8       | B2/1000                 |      | G0/660 |
| BVH (80°-90°)  | 0.4    | 0.0       |                         |      | G0/10  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |        |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |        |

**BUG Rating: B4-U0-G0**

Type V Short





REPORT NUMBER: P640171

CATALOG NUMBER: GWS-SA5D-735-U-RW-W-GRSBK

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 43°    | 45°    | 55°    | 65°    | 75°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 2731.4 | 2731.4 | 2731.4 | 2731.4 | 2731.4 | 2731.4 | 2731.4 | 2731.4 | 2731.4 | 2731.4 | 2731.4 |
| 2.5°  | 2680.4 | 2686.8 | 2695.3 | 2703.8 | 2714.4 | 2725.0 | 2731.4 | 2750.5 | 2746.2 | 2763.2 | 2763.2 |
| 5°    | 2650.7 | 2657.0 | 2667.7 | 2686.8 | 2710.1 | 2733.5 | 2750.5 | 2788.7 | 2810.0 | 2843.9 | 2856.7 |
| 7.5°  | 2665.5 | 2674.0 | 2686.8 | 2716.5 | 2752.6 | 2788.7 | 2807.8 | 2869.4 | 2911.9 | 2975.6 | 3011.7 |
| 10°   | 2714.4 | 2722.9 | 2744.1 | 2795.1 | 2841.8 | 2892.8 | 2916.2 | 2994.7 | 3062.7 | 3149.8 | 3200.8 |
| 12.5° | 2769.6 | 2780.2 | 2822.7 | 2899.2 | 2979.9 | 3047.8 | 3079.7 | 3166.8 | 3236.9 | 3334.6 | 3415.3 |
| 15°   | 2827.0 | 2843.9 | 2909.8 | 3022.4 | 3137.1 | 3228.4 | 3262.4 | 3355.8 | 3425.9 | 3530.0 | 3621.3 |
| 17.5° | 2960.8 | 2979.9 | 3054.2 | 3175.3 | 3332.5 | 3438.7 | 3468.4 | 3566.1 | 3619.2 | 3689.3 | 3784.9 |
| 20°   | 3128.6 | 3164.7 | 3256.0 | 3402.5 | 3574.6 | 3676.5 | 3697.8 | 3793.3 | 3789.1 | 3818.8 | 3901.7 |
| 22.5° | 3336.7 | 3362.2 | 3462.0 | 3636.2 | 3829.5 | 3942.0 | 3990.9 | 4031.2 | 3978.1 | 3952.6 | 4005.7 |
| 25°   | 3553.3 | 3583.1 | 3691.4 | 3882.6 | 4099.2 | 4228.8 | 4269.1 | 4301.0 | 4216.0 | 4120.4 | 4126.8 |
| 27.5° | 3833.7 | 3854.9 | 3961.1 | 4165.0 | 4381.7 | 4528.2 | 4564.3 | 4619.6 | 4507.0 | 4354.1 | 4311.6 |
| 30°   | 4167.2 | 4188.4 | 4301.0 | 4515.5 | 4730.0 | 4855.3 | 4910.5 | 4978.5 | 4855.3 | 4664.2 | 4615.3 |
| 32.5° | 4558.0 | 4579.2 | 4723.6 | 4944.5 | 5120.8 | 5256.7 | 5309.8 | 5382.1 | 5284.3 | 5069.8 | 5014.6 |
| 35°   | 5025.2 | 5038.0 | 5207.9 | 5447.9 | 5634.8 | 5766.5 | 5802.6 | 5887.5 | 5779.2 | 5564.7 | 5535.0 |
| 37.5° | 5566.8 | 5581.7 | 5766.5 | 6044.7 | 6235.9 | 6382.4 | 6439.8 | 6463.1 | 6331.4 | 6091.4 | 6068.1 |
| 40°   | 6161.5 | 6210.4 | 6390.9 | 6690.4 | 6904.9 | 7089.7 | 7140.7 | 7062.1 | 6877.3 | 6550.2 | 6507.7 |
| 42.5° | 6781.7 | 6824.2 | 7026.0 | 7350.9 | 7599.4 | 7788.5 | 7790.6 | 7620.7 | 7306.3 | 6853.9 | 6790.2 |
| 45°   | 7297.8 | 7314.8 | 7576.1 | 7903.2 | 8209.0 | 8342.8 | 8355.6 | 8047.6 | 7574.0 | 7030.2 | 6894.3 |
| 47.5° | 7652.5 | 7680.1 | 7907.4 | 8221.8 | 8559.5 | 8680.5 | 8655.0 | 8270.6 | 7701.4 | 7144.9 | 6919.8 |
| 50°   | 7656.8 | 7703.5 | 7949.9 | 8253.6 | 8580.7 | 8727.2 | 8691.1 | 8334.3 | 7773.6 | 7149.2 | 6858.2 |
| 52.5° | 6979.2 | 7055.7 | 7457.1 | 7896.8 | 8398.0 | 8648.7 | 8657.2 | 8417.2 | 7746.0 | 7081.2 | 6803.0 |
| 55°   | 5265.2 | 5348.1 | 5853.6 | 6603.3 | 7571.8 | 8270.6 | 8391.7 | 8319.5 | 7714.1 | 7110.9 | 6900.7 |
| 57.5° | 2786.6 | 2722.9 | 3003.2 | 3746.6 | 4963.6 | 6199.8 | 6554.5 | 7132.2 | 7359.4 | 7147.0 | 7081.2 |
| 60°   | 607.4  | 647.8  | 862.3  | 1161.8 | 1937.0 | 2916.2 | 3262.4 | 4252.1 | 5428.8 | 5951.3 | 6329.3 |
| 62.5° | 261.2  | 257.0  | 267.6  | 303.7  | 443.9  | 739.1  | 902.7  | 1474.0 | 2325.7 | 3194.4 | 3782.7 |
| 65°   | 214.5  | 216.6  | 225.1  | 225.1  | 210.3  | 212.4  | 223.0  | 337.7  | 543.7  | 762.5  | 1023.7 |
| 67.5° | 161.4  | 163.5  | 178.4  | 182.7  | 172.0  | 152.9  | 150.8  | 127.4  | 133.8  | 167.8  | 174.2  |
| 70°   | 101.9  | 101.9  | 110.4  | 114.7  | 114.7  | 106.2  | 104.1  | 91.3   | 89.2   | 101.9  | 114.7  |
| 72.5° | 55.2   | 55.2   | 59.5   | 61.6   | 59.5   | 57.3   | 57.3   | 55.2   | 53.1   | 61.6   | 78.6   |
| 75°   | 23.4   | 23.4   | 25.5   | 25.5   | 23.4   | 23.4   | 23.4   | 23.4   | 23.4   | 27.6   | 42.5   |
| 77.5° | 4.2    | 6.4    | 8.5    | 6.4    | 4.2    | 4.2    | 4.2    | 6.4    | 6.4    | 8.5    | 12.7   |
| 80°   | 2.1    | 2.1    | 4.2    | 2.1    | 0.0    | 0.0    | 0.0    | 0.0    | 2.1    | 2.1    | 2.1    |
| 82.5° | 2.1    | 2.1    | 2.1    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 2.1    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P640171

CATALOG NUMBER: GWS-SA5D-735-U-RW-W-GRSBK

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 2731.4 | 2731.4 | 2731.4 | 2731.4 | 2731.4 | 2731.4 | 2731.4 | 2731.4 | 2731.4 | 2731.4 | 2731.4 |
| 2.5°  | 2778.1 | 2754.7 | 2763.2 | 2767.5 | 2761.1 | 2756.9 | 2733.5 | 2727.1 | 2716.5 | 2699.5 | 2695.3 |
| 5°    | 2871.6 | 2852.4 | 2850.3 | 2837.6 | 2807.8 | 2771.7 | 2727.1 | 2708.0 | 2686.8 | 2665.5 | 2661.3 |
| 7.5°  | 3028.7 | 3005.4 | 2990.5 | 2948.0 | 2880.1 | 2822.7 | 2748.4 | 2708.0 | 2680.4 | 2652.8 | 2646.4 |
| 10°   | 3230.5 | 3202.9 | 3160.4 | 3081.8 | 2990.5 | 2907.7 | 2820.6 | 2767.5 | 2725.0 | 2686.8 | 2684.7 |
| 12.5° | 3445.0 | 3415.3 | 3338.8 | 3239.0 | 3128.6 | 3052.1 | 2941.6 | 2867.3 | 2803.6 | 2746.2 | 2739.9 |
| 15°   | 3670.2 | 3634.1 | 3530.0 | 3411.0 | 3309.1 | 3230.5 | 3109.4 | 2990.5 | 2892.8 | 2810.0 | 2801.5 |
| 17.5° | 3842.2 | 3797.6 | 3674.4 | 3585.2 | 3502.4 | 3421.7 | 3285.7 | 3128.6 | 2999.0 | 2899.2 | 2875.8 |
| 20°   | 3950.5 | 3908.0 | 3791.2 | 3742.4 | 3704.1 | 3646.8 | 3485.4 | 3321.8 | 3177.4 | 3054.2 | 3033.0 |
| 22.5° | 4054.6 | 4003.6 | 3901.7 | 3901.7 | 3931.4 | 3908.0 | 3733.9 | 3547.0 | 3377.1 | 3234.8 | 3202.9 |
| 25°   | 4171.4 | 4131.1 | 4058.8 | 4118.3 | 4192.6 | 4190.5 | 4012.1 | 3778.5 | 3583.1 | 3423.8 | 3391.9 |
| 27.5° | 4341.3 | 4301.0 | 4275.5 | 4388.0 | 4481.5 | 4475.1 | 4279.7 | 4027.0 | 3821.0 | 3663.8 | 3634.1 |
| 30°   | 4640.8 | 4602.6 | 4575.0 | 4710.9 | 4829.8 | 4785.2 | 4570.7 | 4326.5 | 4118.3 | 3939.9 | 3918.7 |
| 32.5° | 5040.1 | 4999.7 | 4963.6 | 5099.6 | 5205.8 | 5148.4 | 4944.5 | 4715.1 | 4475.1 | 4301.0 | 4258.5 |
| 35°   | 5564.7 | 5479.8 | 5443.6 | 5605.1 | 5649.7 | 5585.9 | 5390.5 | 5188.8 | 4933.9 | 4734.3 | 4706.6 |
| 37.5° | 6106.3 | 6006.5 | 5981.0 | 6121.2 | 6193.4 | 6170.0 | 5940.6 | 5730.4 | 5454.3 | 5233.4 | 5201.5 |
| 40°   | 6569.3 | 6478.0 | 6433.4 | 6652.2 | 6815.7 | 6830.6 | 6624.6 | 6367.6 | 6042.6 | 5813.2 | 5755.9 |
| 42.5° | 6841.2 | 6762.6 | 6752.0 | 7091.8 | 7359.4 | 7550.6 | 7304.2 | 7038.7 | 6696.8 | 6437.6 | 6390.9 |
| 45°   | 6902.8 | 6851.8 | 6941.0 | 7387.0 | 7803.3 | 8151.7 | 7941.4 | 7661.0 | 7291.5 | 7017.5 | 6972.9 |
| 47.5° | 6896.4 | 6879.4 | 7038.7 | 7540.0 | 8066.7 | 8495.7 | 8391.7 | 8075.2 | 7718.4 | 7431.6 | 7389.2 |
| 50°   | 6805.1 | 6807.2 | 7072.7 | 7616.4 | 8172.9 | 8589.2 | 8485.1 | 8192.0 | 7873.4 | 7590.9 | 7557.0 |
| 52.5° | 6769.0 | 6756.2 | 7009.0 | 7593.1 | 8281.2 | 8546.7 | 8313.1 | 7983.9 | 7629.2 | 7280.8 | 7229.9 |
| 55°   | 6896.4 | 6864.6 | 7017.5 | 7574.0 | 8294.0 | 8523.3 | 7907.4 | 7193.8 | 6467.4 | 6055.3 | 6021.4 |
| 57.5° | 7087.6 | 7053.6 | 7125.8 | 7433.8 | 7629.2 | 7087.6 | 5819.6 | 4668.4 | 3920.8 | 3604.3 | 3466.3 |
| 60°   | 6329.3 | 6306.0 | 6250.7 | 5879.1 | 5042.2 | 3804.0 | 2591.2 | 1652.4 | 1187.3 | 960.0  | 960.0  |
| 62.5° | 3927.2 | 3895.3 | 3595.8 | 2671.9 | 1941.3 | 1123.6 | 618.1  | 386.6  | 293.1  | 274.0  | 271.9  |
| 65°   | 1102.3 | 1096.0 | 906.9  | 641.4  | 407.8  | 252.7  | 223.0  | 227.3  | 223.0  | 216.6  | 214.5  |
| 67.5° | 165.7  | 182.7  | 182.7  | 148.7  | 142.3  | 159.3  | 186.9  | 199.6  | 189.0  | 178.4  | 174.2  |
| 70°   | 106.2  | 114.7  | 110.4  | 95.6   | 101.9  | 118.9  | 133.8  | 135.9  | 129.6  | 118.9  | 116.8  |
| 72.5° | 74.3   | 82.8   | 68.0   | 61.6   | 63.7   | 70.1   | 76.5   | 76.5   | 74.3   | 70.1   | 65.8   |
| 75°   | 44.6   | 44.6   | 31.9   | 29.7   | 29.7   | 31.9   | 31.9   | 36.1   | 36.1   | 34.0   | 31.9   |
| 77.5° | 14.9   | 17.0   | 10.6   | 8.5    | 8.5    | 8.5    | 10.6   | 12.7   | 12.7   | 10.6   | 8.5    |
| 80°   | 2.1    | 4.2    | 2.1    | 2.1    | 2.1    | 2.1    | 2.1    | 2.1    | 4.2    | 4.2    | 2.1    |
| 82.5° | 2.1    | 2.1    | 2.1    | 0.0    | 0.0    | 0.0    | 0.0    | 2.1    | 2.1    | 2.1    | 2.1    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 2.1    | 2.1    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

All Brands

Data applicable to all product families using SA light engines

Report Number: SP1-2101-121-7

Luminaire Tested: IFLD-S-SA2A-735-U-T2

Test Date: 03/04/2021

**Test Information**

Test Method: LM-79-08  
 Report Number: SP1-2101-121-7  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry: 4π  
 Issue Date: 03/04/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **IFLD-S-SA2A-735-U-T2**  
 Description: STREETWORKS INF FLOOD

PROGRAMMED @ 615mA.

**Spectral Parameters**

|                           |        |           |      |      |       |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K):                  | 3388   | CRI (Ra): | 73.1 | R9:  | -34.6 |
| CIE u':                   | 0.2371 | R1:       | 68.9 | R10: | 57.8  |
| CIE v':                   | 0.5177 | R2:       | 81.1 | R11: | 68.6  |
| Duv:                      | 0.0032 | R3:       | 93.1 | R12: | 53.9  |
| CIE x:                    | 0.4153 | R4:       | 71.6 | R13: | 70.9  |
| CIE y:                    | 0.4030 | R5:       | 69.4 | R14: | 96.2  |
| CIE z:                    | 0.1817 | R6:       | 75.0 |      |       |
| Peak Wavelength (nm):     | 590    | R7:       | 79.5 |      |       |
| Dominant Wavelength (nm): | 580    | R8:       | 46.4 |      |       |
| Purity:                   | 45.7   |           |      |      |       |
| Rf:                       | 76.9   |           |      |      |       |
| Rg:                       | 94.4   |           |      |      |       |



**Test Conditions**

Stabilization Time: 81M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.0/30%  
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-7

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2101-121-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-7

**Photopic Flux vs. Wavelength**



#####

| λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2672          | 0.0           | 490    | 34553         | 4.9           | 620    | 136720        | 35.6          | 750    | 5870          | 0.0           | 880    | 4216          | 0.0           |
| 365    | 2252          | 0.0           | 495    | 44336         | 8.0           | 625    | 126308        | 27.9          | 755    | 5421          | 0.0           | 885    | 4132          | 0.0           |
| 370    | 2217          | 0.0           | 500    | 54643         | 12.1          | 630    | 114625        | 20.7          | 760    | 5097          | 0.0           | 890    | 3992          | 0.0           |
| 375    | 2697          | 0.0           | 505    | 64676         | 18.1          | 635    | 103216        | 15.5          | 765    | 4626          | 0.0           | 895    | 3214          | 0.0           |
| 380    | 3039          | 0.0           | 510    | 73825         | 25.4          | 640    | 92605         | 11.1          | 770    | 3782          | 0.0           | 900    | 2580          | 0.0           |
| 385    | 2655          | 0.0           | 515    | 81872         | 33.9          | 645    | 83234         | 8.0           | 775    | 3506          | 0.0           | 905    | 1776          | 0.0           |
| 390    | 2357          | 0.0           | 520    | 88574         | 43.0          | 650    | 73263         | 5.4           | 780    | 3507          | 0.0           | 910    | 3995          | 0.0           |
| 395    | 2186          | 0.0           | 525    | 93289         | 50.1          | 655    | 64627         | 3.7           | 785    | 3267          | 0.0           | 915    | 4288          | 0.0           |
| 400    | 2015          | 0.0           | 530    | 98393         | 57.9          | 660    | 56614         | 2.4           | 790    | 2849          | 0.0           | 920    | 2446          | 0.0           |
| 405    | 2234          | 0.0           | 535    | 103269        | 64.0          | 665    | 49537         | 1.6           | 795    | 3037          | 0.0           | 925    | 3009          | 0.0           |
| 410    | 3412          | 0.0           | 540    | 107316        | 69.9          | 670    | 42866         | 0.9           | 800    | 2716          | 0.0           | 930    | 3026          | 0.0           |
| 415    | 6135          | 0.0           | 545    | 113101        | 75.3          | 675    | 36708         | 0.6           | 805    | 2648          | 0.0           | 935    | 4734          | 0.0           |
| 420    | 12146         | 0.0           | 550    | 120690        | 82.0          | 680    | 31814         | 0.4           | 810    | 3187          | 0.0           | 940    | 3719          | 0.0           |
| 425    | 23983         | 0.1           | 555    | 128583        | 87.8          | 685    | 27485         | 0.2           | 815    | 2931          | 0.0           | 945    | 1480          | 0.0           |
| 430    | 42142         | 0.3           | 560    | 137796        | 93.6          | 690    | 23698         | 0.1           | 820    | 2717          | 0.0           | 950    | 3450          | 0.0           |
| 435    | 68228         | 0.8           | 565    | 146577        | 97.5          | 695    | 20309         | 0.1           | 825    | 2236          | 0.0           | 955    | 5051          | 0.0           |
| 440    | 99323         | 1.6           | 570    | 154581        | 100.5         | 700    | 17890         | 0.1           | 830    | 2628          | 0.0           | 960    | 3176          | 0.0           |
| 445    | 115584        | 2.4           | 575    | 162633        | 101.2         | 705    | 15500         | 0.0           | 835    | 3140          | 0.0           | 965    | 5178          | 0.0           |
| 450    | 94997         | 2.5           | 580    | 168101        | 99.9          | 710    | 13699         | 0.0           | 840    | 3675          | 0.0           | 970    | 6385          | 0.0           |
| 455    | 61433         | 2.1           | 585    | 173145        | 96.2          | 715    | 12398         | 0.0           | 845    | 3283          | 0.0           | 975    | 3810          | 0.0           |
| 460    | 43373         | 1.8           | 590    | 174675        | 90.3          | 720    | 11147         | 0.0           | 850    | 3055          | 0.0           | 980    | 4322          | 0.0           |
| 465    | 32472         | 1.7           | 595    | 173724        | 82.3          | 725    | 9761          | 0.0           | 855    | 2932          | 0.0           | 985    | 4200          | 0.0           |
| 470    | 24257         | 1.5           | 600    | 171241        | 73.8          | 730    | 8651          | 0.0           | 860    | 3382          | 0.0           | 990    | 4661          | 0.0           |
| 475    | 21690         | 1.7           | 605    | 165134        | 64.0          | 735    | 7730          | 0.0           | 865    | 2605          | 0.0           | 995    | 6746          | 0.0           |
| 480    | 23173         | 2.2           | 610    | 156652        | 53.8          | 740    | 6847          | 0.0           | 870    | 3325          | 0.0           | 1000   | 4150          | 0.0           |
| 485    | 27564         | 3.3           | 615    | 147879        | 44.6          | 745    | 6124          | 0.0           | 875    | 3325          | 0.0           |        |               |               |

REPORT NUMBER: SP1-2101-121-7

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: 12126**

**S/P: 1.36**

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 2672                                 | 0.0                            | 490               | 34553                                | 53.2                           | 620               | 136720                               | 1.7                            | 750               | 5870                                 | 0.0                            | 880               | 4216                                 | 0.0                            |
| 365               | 2252                                 | 0.0                            | 495               | 44336                                | 71.7                           | 625               | 126308                               | 1.1                            | 755               | 5421                                 | 0.0                            | 885               | 4132                                 | 0.0                            |
| 370               | 2217                                 | 0.0                            | 500               | 54643                                | 91.4                           | 630               | 114625                               | 0.6                            | 760               | 5097                                 | 0.0                            | 890               | 3992                                 | 0.0                            |
| 375               | 2697                                 | 0.0                            | 505               | 64676                                | 110.0                          | 635               | 103216                               | 0.4                            | 765               | 4626                                 | 0.0                            | 895               | 3214                                 | 0.0                            |
| 380               | 3039                                 | 0.0                            | 510               | 73825                                | 125.1                          | 640               | 92605                                | 0.2                            | 770               | 3782                                 | 0.0                            | 900               | 2580                                 | 0.0                            |
| 385               | 2655                                 | 0.0                            | 515               | 81872                                | 135.7                          | 645               | 83234                                | 0.1                            | 775               | 3506                                 | 0.0                            | 905               | 1776                                 | 0.0                            |
| 390               | 2357                                 | 0.0                            | 520               | 88574                                | 140.8                          | 650               | 73263                                | 0.1                            | 780               | 3507                                 | 0.0                            | 910               | 3995                                 | 0.0                            |
| 395               | 2186                                 | 0.0                            | 525               | 93289                                | 139.6                          | 655               | 64627                                | 0.1                            | 785               | 3267                                 | 0.0                            | 915               | 4288                                 | 0.0                            |
| 400               | 2015                                 | 0.0                            | 530               | 98393                                | 135.7                          | 660               | 56614                                | 0.0                            | 790               | 2849                                 | 0.0                            | 920               | 2446                                 | 0.0                            |
| 405               | 2234                                 | 0.1                            | 535               | 103269                               | 128.7                          | 665               | 49537                                | 0.0                            | 795               | 3037                                 | 0.0                            | 925               | 3009                                 | 0.0                            |
| 410               | 3412                                 | 0.2                            | 540               | 107316                               | 118.6                          | 670               | 42866                                | 0.0                            | 800               | 2716                                 | 0.0                            | 930               | 3026                                 | 0.0                            |
| 415               | 6135                                 | 0.6                            | 545               | 113101                               | 108.4                          | 675               | 36708                                | 0.0                            | 805               | 2648                                 | 0.0                            | 935               | 4734                                 | 0.0                            |
| 420               | 12146                                | 2.0                            | 550               | 120690                               | 98.7                           | 680               | 31814                                | 0.0                            | 810               | 3187                                 | 0.0                            | 940               | 3719                                 | 0.0                            |
| 425               | 23983                                | 5.9                            | 555               | 128583                               | 87.9                           | 685               | 27485                                | 0.0                            | 815               | 2931                                 | 0.0                            | 945               | 1480                                 | 0.0                            |
| 430               | 42142                                | 14.3                           | 560               | 137796                               | 77.0                           | 690               | 23698                                | 0.0                            | 820               | 2717                                 | 0.0                            | 950               | 3450                                 | 0.0                            |
| 435               | 68228                                | 30.5                           | 565               | 146577                               | 65.8                           | 695               | 20309                                | 0.0                            | 825               | 2236                                 | 0.0                            | 955               | 5051                                 | 0.0                            |
| 440               | 99323                                | 55.5                           | 570               | 154581                               | 54.6                           | 700               | 17890                                | 0.0                            | 830               | 2628                                 | 0.0                            | 960               | 3176                                 | 0.0                            |
| 445               | 115584                               | 77.4                           | 575               | 162633                               | 44.3                           | 705               | 15500                                | 0.0                            | 835               | 3140                                 | 0.0                            | 965               | 5178                                 | 0.0                            |
| 450               | 94997                                | 73.6                           | 580               | 168101                               | 34.6                           | 710               | 13699                                | 0.0                            | 840               | 3675                                 | 0.0                            | 970               | 6385                                 | 0.0                            |
| 455               | 61433                                | 53.7                           | 585               | 173145                               | 26.5                           | 715               | 12398                                | 0.0                            | 845               | 3283                                 | 0.0                            | 975               | 3810                                 | 0.0                            |
| 460               | 43373                                | 41.9                           | 590               | 174675                               | 19.5                           | 720               | 11147                                | 0.0                            | 850               | 3055                                 | 0.0                            | 980               | 4322                                 | 0.0                            |
| 465               | 32472                                | 34.3                           | 595               | 173724                               | 13.9                           | 725               | 9761                                 | 0.0                            | 855               | 2932                                 | 0.0                            | 985               | 4200                                 | 0.0                            |
| 470               | 24257                                | 27.9                           | 600               | 171241                               | 9.7                            | 730               | 8651                                 | 0.0                            | 860               | 3382                                 | 0.0                            | 990               | 4661                                 | 0.0                            |
| 475               | 21690                                | 27.1                           | 605               | 165134                               | 6.5                            | 735               | 7730                                 | 0.0                            | 865               | 2605                                 | 0.0                            | 995               | 6746                                 | 0.0                            |
| 480               | 23173                                | 31.3                           | 610               | 156652                               | 4.2                            | 740               | 6847                                 | 0.0                            | 870               | 3325                                 | 0.0                            | 1000              | 4150                                 | 0.0                            |
| 485               | 27564                                | 40.0                           | 615               | 147879                               | 2.7                            | 745               | 6124                                 | 0.0                            | 875               | 3325                                 | 0.0                            |                   |                                      |                                |

REPORT NUMBER: SP1-2101-121-7

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 4490.7 M/P: 0.5**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2672          | 0.0           | 490    | 34553         | 28.8          | 620    | 136720        | 0.1           | 750    | 5870          | 0.0           | 880    | 4216          | 0.0           |
| 365    | 2252          | 0.0           | 495    | 44336         | 36.6          | 625    | 126308        | 0.1           | 755    | 5421          | 0.0           | 885    | 4132          | 0.0           |
| 370    | 2217          | 0.0           | 500    | 54643         | 43.9          | 630    | 114625        | 0.0           | 760    | 5097          | 0.0           | 890    | 3992          | 0.0           |
| 375    | 2697          | 0.0           | 505    | 64676         | 49.6          | 635    | 103216        | 0.0           | 765    | 4626          | 0.0           | 895    | 3214          | 0.0           |
| 380    | 3039          | 0.0           | 510    | 73825         | 53.0          | 640    | 92605         | 0.0           | 770    | 3782          | 0.0           | 900    | 2580          | 0.0           |
| 385    | 2655          | 0.0           | 515    | 81872         | 53.5          | 645    | 83234         | 0.0           | 775    | 3506          | 0.0           | 905    | 1776          | 0.0           |
| 390    | 2357          | 0.0           | 520    | 88574         | 51.6          | 650    | 73263         | 0.0           | 780    | 3507          | 0.0           | 910    | 3995          | 0.0           |
| 395    | 2186          | 0.0           | 525    | 93289         | 47.3          | 655    | 64627         | 0.0           | 785    | 3267          | 0.0           | 915    | 4288          | 0.0           |
| 400    | 2015          | 0.0           | 530    | 98393         | 42.5          | 660    | 56614         | 0.0           | 790    | 2849          | 0.0           | 920    | 2446          | 0.0           |
| 405    | 2234          | 0.0           | 535    | 103269        | 37.2          | 665    | 49537         | 0.0           | 795    | 3037          | 0.0           | 925    | 3009          | 0.0           |
| 410    | 3412          | 0.1           | 540    | 107316        | 31.4          | 670    | 42866         | 0.0           | 800    | 2716          | 0.0           | 930    | 3026          | 0.0           |
| 415    | 6135          | 0.4           | 545    | 113101        | 26.3          | 675    | 36708         | 0.0           | 805    | 2648          | 0.0           | 935    | 4734          | 0.0           |
| 420    | 12146         | 1.4           | 550    | 120690        | 21.7          | 680    | 31814         | 0.0           | 810    | 3187          | 0.0           | 940    | 3719          | 0.0           |
| 425    | 23983         | 3.7           | 555    | 128583        | 17.3          | 685    | 27485         | 0.0           | 815    | 2931          | 0.0           | 945    | 1480          | 0.0           |
| 430    | 42142         | 8.9           | 560    | 137796        | 13.6          | 690    | 23698         | 0.0           | 820    | 2717          | 0.0           | 950    | 3450          | 0.0           |
| 435    | 68228         | 18.2          | 565    | 146577        | 10.3          | 695    | 20309         | 0.0           | 825    | 2236          | 0.0           | 955    | 5051          | 0.0           |
| 440    | 99323         | 33.2          | 570    | 154581        | 7.6           | 700    | 17890         | 0.0           | 830    | 2628          | 0.0           | 960    | 3176          | 0.0           |
| 445    | 115584        | 45.6          | 575    | 162633        | 5.4           | 705    | 15500         | 0.0           | 835    | 3140          | 0.0           | 965    | 5178          | 0.0           |
| 450    | 94997         | 43.8          | 580    | 168101        | 3.8           | 710    | 13699         | 0.0           | 840    | 3675          | 0.0           | 970    | 6385          | 0.0           |
| 455    | 61433         | 32.2          | 585    | 173145        | 2.6           | 715    | 12398         | 0.0           | 845    | 3283          | 0.0           | 975    | 3810          | 0.0           |
| 460    | 43373         | 25.6          | 590    | 174675        | 1.7           | 720    | 11147         | 0.0           | 850    | 3055          | 0.0           | 980    | 4322          | 0.0           |
| 465    | 32472         | 21.2          | 595    | 173724        | 1.1           | 725    | 9761          | 0.0           | 855    | 2932          | 0.0           | 985    | 4200          | 0.0           |
| 470    | 24257         | 17.4          | 600    | 171241        | 0.7           | 730    | 8651          | 0.0           | 860    | 3382          | 0.0           | 990    | 4661          | 0.0           |
| 475    | 21690         | 16.6          | 605    | 165134        | 0.5           | 735    | 7730          | 0.0           | 865    | 2605          | 0.0           | 995    | 6746          | 0.0           |
| 480    | 23173         | 18.6          | 610    | 156652        | 0.3           | 740    | 6847          | 0.0           | 870    | 3325          | 0.0           | 1000   | 4150          | 0.0           |
| 485    | 27564         | 22.7          | 615    | 147879        | 0.2           | 745    | 6124          | 0.0           | 875    | 3325          | 0.0           |        |               |               |

**Summary**

$R_f = 76.9$   
 $R_g = 94.4$   
 CIE  $R_a = 73.1$   
 $R_g = -34.6$



**Color Vector Graphics**





**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 68 | CES51 = 90 | CES76 = 63 |
| CES02 = 62 | CES27 = 88 | CES52 = 89 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 80 | CES78 = 65 |
| CES04 = 70 | CES29 = 67 | CES54 = 84 | CES79 = 87 |
| CES05 = 48 | CES30 = 74 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 71 | CES56 = 75 | CES81 = 75 |
| CES07 = 40 | CES32 = 67 | CES57 = 74 | CES82 = 94 |
| CES08 = 39 | CES33 = 74 | CES58 = 76 | CES83 = 91 |
| CES09 = 29 | CES34 = 78 | CES59 = 87 | CES84 = 89 |
| CES10 = 75 | CES35 = 89 | CES60 = 93 | CES85 = 80 |
| CES11 = 58 | CES36 = 98 | CES61 = 86 | CES86 = 66 |
| CES12 = 64 | CES37 = 86 | CES62 = 89 | CES87 = 79 |
| CES13 = 43 | CES38 = 82 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 95 | CES64 = 74 | CES89 = 70 |
| CES15 = 71 | CES40 = 91 | CES65 = 68 | CES90 = 77 |
| CES16 = 47 | CES41 = 89 | CES66 = 71 | CES91 = 88 |
| CES17 = 50 | CES42 = 88 | CES67 = 69 | CES92 = 60 |
| CES18 = 56 | CES43 = 82 | CES68 = 74 | CES93 = 77 |
| CES19 = 72 | CES44 = 99 | CES69 = 82 | CES94 = 52 |
| CES20 = 65 | CES45 = 87 | CES70 = 67 | CES95 = 69 |
| CES21 = 86 | CES46 = 82 | CES71 = 66 | CES96 = 78 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 85 |
| CES23 = 92 | CES48 = 72 | CES73 = 59 | CES98 = 76 |
| CES24 = 91 | CES49 = 82 | CES74 = 97 | CES99 = 63 |
| CES25 = 72 | CES50 = 88 | CES75 = 66 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)