

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P632309

Luminaire Tested: GWS-SA2C-740-U-SL2-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P632309
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA2C-740-U-SL2-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (2) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II SPILL LIGHT ELIMINATOR OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (32) 4000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5434.6 lumens
Efficiency: N/A
Efficacy: 86.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B1 - U0 - G0


Input Watts (W): 63.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P632309
 CATALOG NUMBER: GWS-SA2C-740-U-SL2-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 19.1 fc
 Type II - Short - N/A

REPORT NUMBER: P632309
CATALOG NUMBER: GWS-SA2C-740-U-SL2-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 50-Deg Lateral - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P632309
 CATALOG NUMBER: GWS-SA2C-740-U-SL2-W-GRSBK


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1070.9 | 0.0 | 1070.9 |
| | % Fixture | 19.7 | 0.0 | 19.7 |
| Street Side | Lumens | 4363.7 | 0.0 | 4363.7 |
| | % Fixture | 80.3 | 0.0 | 80.3 |
| Total | Lumens | 5434.6 | 0.0 | 5434.6 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 167.5 | 3.1 |
| 10°-20° | 412.1 | 7.6 |
| 20°-30° | 581.2 | 10.7 |
| 30°-40° | 860.1 | 15.8 |
| 40°-50° | 1240.9 | 22.8 |
| 50°-60° | 1463.7 | 26.9 |
| 60°-70° | 652.9 | 12.0 |
| 70°-80° | 56.1 | 1.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 5434.6 | 100.0 |
| 0°-180° | 5434.6 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P632309

CATALOG NUMBER: GWS-SA2C-740-U-SL2-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 701.6 | 12.9 | | | |
| FM (30°-60°) | 3049.7 | 56.1 | | | |
| FH (60°-80°) | 612.4 | 11.3 | | | G0/660 |
| FVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| BL (0°-30°) | 459.1 | 8.4 | B1/500 | | |
| BM (30°-60°) | 515.0 | 9.5 | B1/1000 | | |
| BH (60°-80°) | 96.7 | 1.8 | B0/110 | | G0/110 |
| BVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G0
 Type II Short





REPORT NUMBER: P632309

CATALOG NUMBER: GWS-SA2C-740-U-SL2-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 50° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1906.8 | 1906.8 | 1906.8 | 1906.8 | 1906.8 | 1906.8 | 1906.8 | 1906.8 | 1906.8 | 1906.8 | 1906.8 |
| 2.5° | 1771.4 | 1772.7 | 1773.4 | 1791.3 | 1798.0 | 1824.5 | 1838.4 | 1845.7 | 1865.0 | 1887.5 | 1906.1 |
| 5° | 1652.7 | 1650.7 | 1654.0 | 1676.5 | 1691.1 | 1730.3 | 1751.5 | 1766.1 | 1808.6 | 1861.6 | 1906.1 |
| 7.5° | 1549.2 | 1553.1 | 1557.1 | 1581.7 | 1603.6 | 1646.0 | 1676.5 | 1698.4 | 1757.5 | 1836.4 | 1911.4 |
| 10° | 1476.2 | 1476.2 | 1482.2 | 1510.0 | 1535.9 | 1588.3 | 1618.8 | 1646.7 | 1717.0 | 1813.9 | 1917.4 |
| 12.5° | 1422.4 | 1423.1 | 1430.4 | 1462.2 | 1492.1 | 1546.5 | 1578.4 | 1605.6 | 1683.2 | 1791.3 | 1918.7 |
| 15° | 1397.2 | 1395.2 | 1401.2 | 1435.0 | 1468.2 | 1519.3 | 1552.5 | 1579.0 | 1659.3 | 1778.7 | 1925.3 |
| 17.5° | 1390.6 | 1389.3 | 1393.9 | 1427.1 | 1460.9 | 1510.7 | 1543.2 | 1569.7 | 1656.0 | 1782.7 | 1945.2 |
| 20° | 1409.8 | 1407.2 | 1405.2 | 1433.7 | 1465.6 | 1514.7 | 1548.5 | 1578.4 | 1671.9 | 1804.6 | 1975.8 |
| 22.5° | 1455.6 | 1455.6 | 1451.0 | 1464.9 | 1486.1 | 1530.6 | 1565.7 | 1604.9 | 1713.7 | 1848.4 | 2020.9 |
| 25° | 1539.9 | 1533.2 | 1524.6 | 1530.6 | 1527.9 | 1555.8 | 1597.6 | 1652.0 | 1792.6 | 1920.7 | 2075.9 |
| 27.5° | 1636.1 | 1642.0 | 1627.4 | 1628.1 | 1604.9 | 1594.9 | 1643.4 | 1725.6 | 1910.1 | 2022.9 | 2157.5 |
| 30° | 1766.8 | 1762.1 | 1762.8 | 1760.8 | 1707.1 | 1660.0 | 1712.4 | 1821.8 | 2058.0 | 2178.8 | 2263.7 |
| 32.5° | 1868.9 | 1875.6 | 1897.5 | 1910.1 | 1839.8 | 1764.1 | 1819.8 | 1952.5 | 2226.5 | 2356.6 | 2393.7 |
| 35° | 1977.1 | 1989.0 | 2033.5 | 2074.6 | 2015.6 | 1928.7 | 1988.4 | 2125.7 | 2385.1 | 2532.4 | 2543.0 |
| 37.5° | 2091.2 | 2115.1 | 2168.2 | 2240.5 | 2231.2 | 2154.2 | 2208.6 | 2329.4 | 2509.8 | 2638.5 | 2666.4 |
| 40° | 2221.9 | 2245.1 | 2332.0 | 2436.2 | 2458.1 | 2440.8 | 2458.8 | 2529.1 | 2592.1 | 2643.2 | 2719.5 |
| 42.5° | 2365.2 | 2397.1 | 2507.2 | 2646.5 | 2728.8 | 2744.0 | 2702.2 | 2694.9 | 2627.9 | 2590.1 | 2708.2 |
| 45° | 2534.4 | 2571.5 | 2696.3 | 2876.7 | 3007.4 | 3028.0 | 2955.7 | 2862.1 | 2650.5 | 2551.0 | 2674.4 |
| 47.5° | 2724.1 | 2759.3 | 2883.4 | 3100.3 | 3294.7 | 3302.7 | 3176.6 | 3026.0 | 2717.5 | 2596.1 | 2700.2 |
| 50° | 2787.8 | 2809.7 | 2917.2 | 3172.0 | 3530.2 | 3591.3 | 3408.8 | 3210.4 | 2852.2 | 2728.8 | 2826.3 |
| 52.5° | 2568.9 | 2577.5 | 2671.1 | 2928.5 | 3482.5 | 3874.6 | 3747.8 | 3485.8 | 3091.7 | 2931.1 | 3020.7 |
| 55° | 2035.5 | 2021.5 | 2097.2 | 2333.4 | 3026.7 | 3816.8 | 4055.0 | 3918.3 | 3400.2 | 3168.6 | 3273.5 |
| 57.5° | 1423.8 | 1407.2 | 1389.9 | 1549.8 | 2258.4 | 3235.7 | 3736.6 | 3978.7 | 3694.1 | 3404.2 | 3546.1 |
| 60° | 1170.3 | 1154.4 | 1070.8 | 997.2 | 1365.4 | 2323.4 | 2870.1 | 3325.9 | 3670.2 | 3392.2 | 3537.5 |
| 62.5° | 1011.1 | 1001.8 | 968.0 | 867.8 | 803.4 | 1326.2 | 1797.3 | 2233.8 | 2816.4 | 2663.8 | 2671.7 |
| 65° | 794.2 | 791.5 | 814.7 | 825.3 | 710.6 | 733.8 | 916.9 | 1161.0 | 1522.6 | 1435.7 | 1361.4 |
| 67.5° | 542.7 | 536.7 | 580.5 | 713.9 | 683.4 | 579.2 | 536.7 | 541.4 | 658.8 | 402.7 | 319.8 |
| 70° | 345.0 | 331.1 | 331.7 | 442.5 | 556.0 | 457.1 | 414.0 | 364.2 | 327.7 | 59.7 | 67.7 |
| 72.5° | 220.9 | 212.3 | 182.4 | 199.7 | 257.4 | 222.9 | 224.9 | 193.7 | 129.4 | 31.8 | 37.2 |
| 75° | 92.9 | 85.6 | 65.7 | 52.4 | 51.7 | 32.5 | 28.5 | 26.5 | 17.9 | 17.9 | 19.2 |
| 77.5° | 0.7 | 0.0 | 0.0 | 0.7 | 1.3 | 0.7 | 0.7 | 1.3 | 2.7 | 4.0 | 4.6 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.7 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P632309

CATALOG NUMBER: GWS-SA2C-740-U-SL2-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1906.8 | 1906.8 | 1906.8 | 1906.8 | 1906.8 | 1906.8 | 1906.8 | 1906.8 | 1906.8 | 1906.8 | 1906.8 |
| 2.5° | 1917.4 | 1901.5 | 1919.4 | 1926.0 | 1925.3 | 1926.0 | 1906.8 | 1893.5 | 1892.8 | 1876.2 | 1868.3 |
| 5° | 1924.7 | 1912.1 | 1925.3 | 1916.7 | 1896.1 | 1870.3 | 1835.8 | 1805.9 | 1792.6 | 1773.4 | 1764.1 |
| 7.5° | 1938.6 | 1925.3 | 1923.3 | 1888.8 | 1837.8 | 1783.4 | 1722.3 | 1667.9 | 1638.7 | 1603.6 | 1605.6 |
| 10° | 1948.6 | 1933.3 | 1907.4 | 1837.1 | 1752.2 | 1665.3 | 1574.4 | 1493.4 | 1442.3 | 1395.2 | 1387.3 |
| 12.5° | 1952.5 | 1930.0 | 1869.6 | 1763.5 | 1644.0 | 1530.6 | 1397.2 | 1281.8 | 1202.2 | 1140.5 | 1131.8 |
| 15° | 1959.8 | 1923.3 | 1821.2 | 1674.6 | 1510.7 | 1350.1 | 1180.3 | 1022.4 | 916.9 | 845.9 | 851.9 |
| 17.5° | 1971.1 | 1916.0 | 1766.8 | 1575.0 | 1367.4 | 1140.5 | 910.9 | 729.8 | 632.9 | 591.8 | 592.5 |
| 20° | 1987.0 | 1907.4 | 1707.1 | 1465.6 | 1195.5 | 903.6 | 636.9 | 500.2 | 473.0 | 471.7 | 469.7 |
| 22.5° | 2008.3 | 1898.8 | 1643.4 | 1345.5 | 991.9 | 632.9 | 423.9 | 381.5 | 392.8 | 414.7 | 418.6 |
| 25° | 2033.5 | 1888.2 | 1572.4 | 1210.1 | 769.6 | 415.3 | 317.8 | 311.2 | 338.4 | 367.6 | 374.2 |
| 27.5° | 2072.6 | 1882.9 | 1491.4 | 1056.2 | 540.0 | 297.9 | 260.1 | 264.1 | 288.6 | 313.1 | 319.1 |
| 30° | 2139.0 | 1892.8 | 1403.2 | 883.7 | 347.0 | 237.5 | 225.6 | 231.5 | 244.8 | 257.4 | 262.7 |
| 32.5° | 2229.2 | 1922.0 | 1317.6 | 695.3 | 247.5 | 206.3 | 203.7 | 207.0 | 212.3 | 219.6 | 221.6 |
| 35° | 2334.7 | 1972.4 | 1229.4 | 497.6 | 204.3 | 188.4 | 185.8 | 185.8 | 188.4 | 189.7 | 190.4 |
| 37.5° | 2421.6 | 2025.5 | 1146.4 | 331.1 | 183.1 | 174.5 | 170.5 | 168.5 | 167.9 | 169.2 | 169.8 |
| 40° | 2459.4 | 2047.4 | 1056.2 | 240.8 | 167.9 | 161.9 | 155.9 | 149.9 | 149.9 | 154.6 | 155.2 |
| 42.5° | 2432.9 | 2022.9 | 952.1 | 199.0 | 157.2 | 148.6 | 139.3 | 134.0 | 136.7 | 141.3 | 142.6 |
| 45° | 2376.5 | 1962.5 | 837.3 | 175.8 | 146.6 | 135.3 | 124.7 | 121.4 | 124.1 | 130.0 | 131.4 |
| 47.5° | 2367.2 | 1922.7 | 699.9 | 160.6 | 135.3 | 124.1 | 112.8 | 109.5 | 112.8 | 117.4 | 118.8 |
| 50° | 2459.4 | 1957.2 | 547.3 | 147.3 | 124.7 | 112.1 | 102.8 | 99.5 | 101.5 | 104.2 | 105.5 |
| 52.5° | 2627.9 | 2085.2 | 441.9 | 134.7 | 112.1 | 100.2 | 94.2 | 90.2 | 90.2 | 92.9 | 93.5 |
| 55° | 2876.7 | 2308.8 | 381.5 | 120.1 | 97.5 | 90.9 | 85.6 | 81.6 | 81.6 | 82.9 | 83.6 |
| 57.5° | 3163.3 | 2579.5 | 395.4 | 100.8 | 85.6 | 82.3 | 77.6 | 74.3 | 75.6 | 75.6 | 75.6 |
| 60° | 3123.5 | 2559.6 | 423.3 | 84.9 | 75.6 | 74.3 | 70.3 | 69.0 | 72.3 | 69.7 | 68.3 |
| 62.5° | 2300.9 | 1768.1 | 221.6 | 69.7 | 65.0 | 63.7 | 61.0 | 63.7 | 68.3 | 61.0 | 58.4 |
| 65° | 1117.3 | 855.9 | 88.9 | 57.1 | 55.1 | 53.7 | 52.4 | 56.4 | 59.0 | 47.8 | 45.1 |
| 67.5° | 262.7 | 213.6 | 57.7 | 48.4 | 45.8 | 43.1 | 44.5 | 45.1 | 43.1 | 32.5 | 31.2 |
| 70° | 68.3 | 67.0 | 45.1 | 40.5 | 36.5 | 33.8 | 33.8 | 33.2 | 28.5 | 20.6 | 19.2 |
| 72.5° | 37.2 | 36.5 | 32.5 | 30.5 | 25.2 | 22.6 | 23.2 | 20.6 | 15.9 | 11.9 | 11.3 |
| 75° | 18.6 | 19.9 | 18.6 | 17.2 | 13.9 | 12.6 | 12.6 | 11.3 | 8.0 | 4.6 | 4.6 |
| 77.5° | 4.0 | 4.6 | 4.6 | 4.0 | 3.3 | 2.7 | 2.7 | 3.3 | 1.3 | 0.0 | 0.0 |
| 80° | 0.7 | 0.7 | 0.7 | 0.7 | 0.7 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW, INVUE, LUMARK AND STREETWORKS

DATA VALID FOR LUMINAIRES UTILIZING SA LIGHT ENGINES

Report Number: SP1-2101-121-2

Luminaire Tested: IFLD-S-SA2A-740-U-T3R-HSS

Test Date: 03/05/2021

Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/05/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

Spectral Parameters

| | | | | | |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K): | 3905 | CRI (Ra): | 71.2 | R9: | -29.7 |
| CIE u': | 0.2273 | R1: | 68.9 | R10: | 46.2 |
| CIE v': | 0.5024 | R2: | 77.0 | R11: | 68.8 |
| Duv: | -0.0008 | R3: | 84.0 | R12: | 45.6 |
| CIE x: | 0.3841 | R4: | 71.6 | R13: | 69.5 |
| CIE y: | 0.3774 | R5: | 68.9 | R14: | 90.7 |
| CIE z: | 0.2385 | R6: | 68.3 | | |
| Peak Wavelength (nm): | 443 | R7: | 78.7 | | |
| Dominant Wavelength (nm): | 579 | R8: | 52.2 | | |
| Purity: | 28.7 | | | | |
| Rf: | 71.7 | | | | |
| Rg: | 96.9 | | | | |



Test Conditions

Stabilization Time: 211M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.8/312%
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-2

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-121-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 3905K
 CIE x = 0.3841
 CIE y = 0.3774
 Duv = -0.0008

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 2.7 | 620 | 97577 | 25.4 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 4.8 | 625 | 90158 | 19.9 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 8.0 | 630 | 82240 | 14.9 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 13.3 | 635 | 74361 | 11.2 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 20.2 | 640 | 66994 | 8.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 28.5 | 645 | 60405 | 5.8 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 37.4 | 650 | 53806 | 3.9 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 44.9 | 655 | 47610 | 2.7 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 52.6 | 660 | 42018 | 1.8 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 58.4 | 665 | 36742 | 1.2 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.0 | 540 | 96845 | 63.1 | 670 | 32105 | 0.7 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.0 | 545 | 100829 | 67.1 | 675 | 27946 | 0.5 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 0.1 | 550 | 105648 | 71.8 | 680 | 24146 | 0.3 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 0.2 | 555 | 110017 | 75.1 | 685 | 21191 | 0.2 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 0.5 | 560 | 114586 | 77.9 | 690 | 18544 | 0.1 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 1.2 | 565 | 118987 | 79.1 | 695 | 16058 | 0.1 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 2.1 | 570 | 122326 | 79.5 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 2.9 | 575 | 125968 | 78.4 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 2.7 | 580 | 127613 | 75.8 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 2.0 | 585 | 129466 | 71.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 1.5 | 590 | 128813 | 66.6 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 1.3 | 595 | 126387 | 59.9 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 1.0 | 600 | 123477 | 53.2 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 1.1 | 605 | 118718 | 46.0 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 1.2 | 610 | 112091 | 38.5 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 1.7 | 615 | 105039 | 31.7 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: 10425.8 S/P: 1.47

| λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 29.3 | 620 | 97577 | 1.2 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 43.0 | 625 | 90158 | 0.8 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 60.8 | 630 | 82240 | 0.5 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 81.1 | 635 | 74361 | 0.3 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 99.6 | 640 | 66994 | 0.2 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 113.9 | 645 | 60405 | 0.1 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 122.6 | 650 | 53806 | 0.1 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 125.0 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 123.1 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.1 | 535 | 94097 | 117.3 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 107.0 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.9 | 545 | 100829 | 96.7 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 3.0 | 550 | 105648 | 86.4 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 9.3 | 555 | 110017 | 75.2 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 23.0 | 560 | 114586 | 64.0 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 45.7 | 565 | 118987 | 53.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 75.5 | 570 | 122326 | 43.2 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 93.8 | 575 | 125968 | 34.3 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 79.3 | 580 | 127613 | 26.3 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 51.3 | 585 | 129466 | 19.8 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 35.6 | 590 | 128813 | 14.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 26.0 | 595 | 126387 | 10.1 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 19.3 | 600 | 123477 | 7.0 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 16.8 | 605 | 118718 | 4.7 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 17.7 | 610 | 112091 | 3.0 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 21.4 | 615 | 105039 | 1.9 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3927.2 M/P: 0.55

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 15.8 | 620 | 97577 | 0.1 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 22.0 | 625 | 90158 | 0.0 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 29.2 | 630 | 82240 | 0.0 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 36.6 | 635 | 74361 | 0.0 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 42.2 | 640 | 66994 | 0.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 44.9 | 645 | 60405 | 0.0 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 44.9 | 650 | 53806 | 0.0 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 42.4 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 38.6 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 33.9 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 28.3 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.6 | 545 | 100829 | 23.4 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 2.1 | 550 | 105648 | 19.0 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 5.9 | 555 | 110017 | 14.8 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 14.3 | 560 | 114586 | 11.3 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 27.3 | 565 | 118987 | 8.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 45.1 | 570 | 122326 | 6.0 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 55.3 | 575 | 125968 | 4.2 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 47.2 | 580 | 127613 | 2.9 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 30.8 | 585 | 129466 | 1.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 21.7 | 590 | 128813 | 1.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 16.1 | 595 | 126387 | 0.8 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 12.0 | 600 | 123477 | 0.5 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 10.3 | 605 | 118718 | 0.3 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 10.5 | 610 | 112091 | 0.2 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 12.1 | 615 | 105039 | 0.1 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

Summary

$R_f = 71.7$
 $R_g = 96.9$
 CIE $R_a = 71.2$
 $R_g = -29.7$




Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)