

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P637269

Luminaire Tested: GWS-SA4C-740-U-SLL-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P637269
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-38)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA4C-740-U-SLL-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND
SPILL LIGHT ELIMINATOR LEFT OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (64) 4000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10408.9 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type III - Short
BUG Rating: B2 - U0 - G1


Input Watts (W): 128.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P637269
 CATALOG NUMBER: GWS-SA4C-740-U-SLL-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 6.9 fc
 Type III - Short - N/A

REPORT NUMBER: P637269
CATALOG NUMBER: GWS-SA4C-740-U-SLL-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 315-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P637269

CATALOG NUMBER: GWS-SA4C-740-U-SLL-W-GRSBK


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 2242.4 | 0.0 | 2242.4 |
| | % Fixture | 21.5 | 0.0 | 21.5 |
| Street Side | Lumens | 8166.5 | 0.0 | 8166.5 |
| | % Fixture | 78.5 | 0.0 | 78.5 |
| Total | Lumens | 10408.9 | 0.0 | 10408.9 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 174.8 | 1.7 |
| 10°-20° | 575.2 | 5.5 |
| 20°-30° | 933.5 | 9.0 |
| 30°-40° | 1432.7 | 13.8 |
| 40°-50° | 2288.1 | 22.0 |
| 50°-60° | 3203.8 | 30.8 |
| 60°-70° | 1642.7 | 15.8 |
| 70°-80° | 158.2 | 1.5 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 10408.9 | 100.0 |
| 0°-180° | 10408.9 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P637269


CATALOG NUMBER: GWS-SA4C-740-U-SLL-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1030.5 | 9.9 | | | |
| FM (30°-60°) | 5504.5 | 52.9 | | | |
| FH (60°-80°) | 1631.5 | 15.7 | | | G1/1800 |
| FVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| BL (0°-30°) | 653.0 | 6.3 | B2/1000 | | |
| BM (30°-60°) | 1420.1 | 13.6 | B2/2500 | | |
| BH (60°-80°) | 169.4 | 1.6 | B1/500 | | G1/500 |
| BVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G1

Type III Short





REPORT NUMBER: P637269

CATALOG NUMBER: GWS-SA4C-740-U-SLL-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 |
| 2.5° | 1964.8 | 1960.7 | 1946.7 | 1899.4 | 1870.2 | 1824.3 | 1790.9 | 1747.8 | 1700.4 | 1671.2 | 1642.0 |
| 5° | 2173.6 | 2162.4 | 2124.9 | 2016.3 | 1932.8 | 1842.4 | 1770.0 | 1690.7 | 1605.8 | 1550.2 | 1498.7 |
| 7.5° | 2373.9 | 2357.2 | 2307.1 | 2123.5 | 1996.8 | 1867.4 | 1764.5 | 1649.0 | 1529.3 | 1445.8 | 1381.8 |
| 10° | 2570.1 | 2532.6 | 2453.3 | 2227.8 | 2056.7 | 1900.8 | 1779.8 | 1647.6 | 1507.0 | 1401.3 | 1330.3 |
| 12.5° | 2731.6 | 2703.7 | 2595.2 | 2326.6 | 2106.8 | 1907.8 | 1758.9 | 1636.4 | 1541.8 | 1470.8 | 1405.4 |
| 15° | 2870.7 | 2840.1 | 2737.1 | 2415.7 | 2149.9 | 1879.9 | 1671.2 | 1564.1 | 1579.4 | 1607.2 | 1551.5 |
| 17.5° | 2998.7 | 2966.7 | 2855.4 | 2489.4 | 2166.6 | 1811.8 | 1548.8 | 1497.3 | 1582.2 | 1686.5 | 1665.7 |
| 20° | 3130.9 | 3094.7 | 2958.4 | 2549.3 | 2161.0 | 1704.6 | 1424.9 | 1440.2 | 1559.9 | 1679.6 | 1690.7 |
| 22.5° | 3285.4 | 3247.8 | 3089.2 | 2625.8 | 2156.9 | 1576.6 | 1317.8 | 1390.1 | 1518.2 | 1619.7 | 1639.2 |
| 25° | 3489.9 | 3445.4 | 3271.5 | 2738.5 | 2168.0 | 1459.7 | 1241.2 | 1341.4 | 1447.2 | 1539.0 | 1550.2 |
| 27.5° | 3759.9 | 3702.8 | 3481.6 | 2877.7 | 2191.6 | 1367.9 | 1207.8 | 1274.6 | 1356.7 | 1438.8 | 1448.6 |
| 30° | 4112.0 | 4039.6 | 3722.3 | 2998.7 | 2180.5 | 1303.9 | 1185.6 | 1207.8 | 1256.5 | 1323.3 | 1324.7 |
| 32.5° | 4523.8 | 4425.0 | 3992.3 | 3103.1 | 2084.5 | 1256.5 | 1155.0 | 1139.7 | 1150.8 | 1202.3 | 1212.0 |
| 35° | 5008.1 | 4880.1 | 4290.1 | 3201.9 | 1909.2 | 1164.7 | 1099.3 | 1047.8 | 1043.6 | 1068.7 | 1092.3 |
| 37.5° | 5563.3 | 5410.2 | 4665.8 | 3328.5 | 1701.8 | 1068.7 | 1017.2 | 965.7 | 943.5 | 956.0 | 992.2 |
| 40° | 6075.4 | 5905.6 | 5058.2 | 3481.6 | 1490.3 | 982.4 | 921.2 | 868.3 | 841.9 | 846.0 | 890.6 |
| 42.5° | 6676.5 | 6501.2 | 5538.3 | 3682.0 | 1315.0 | 924.0 | 821.0 | 766.7 | 731.9 | 751.4 | 802.9 |
| 45° | 7589.4 | 7390.4 | 6238.2 | 3855.9 | 1175.8 | 910.1 | 733.3 | 656.8 | 640.1 | 673.5 | 734.7 |
| 47.5° | 8836.2 | 8592.7 | 7199.7 | 3961.7 | 1057.6 | 922.6 | 672.1 | 567.7 | 571.9 | 609.5 | 670.7 |
| 50° | 10073.2 | 9810.2 | 8311.6 | 3822.5 | 960.2 | 897.5 | 641.5 | 498.2 | 524.6 | 558.0 | 613.7 |
| 52.5° | 10923.5 | 10581.1 | 8852.9 | 3420.4 | 871.1 | 802.9 | 638.7 | 432.8 | 482.9 | 494.0 | 541.3 |
| 55° | 10956.9 | 10535.2 | 8576.0 | 2696.8 | 750.0 | 677.7 | 609.5 | 378.5 | 436.9 | 441.1 | 481.5 |
| 57.5° | 9604.3 | 9223.0 | 7494.7 | 1852.1 | 666.5 | 496.8 | 485.6 | 331.2 | 359.0 | 393.8 | 418.8 |
| 60° | 7306.9 | 6982.7 | 5605.1 | 848.8 | 506.5 | 315.9 | 332.6 | 285.3 | 268.6 | 320.1 | 345.1 |
| 62.5° | 4475.1 | 4267.8 | 3361.9 | 375.7 | 322.8 | 168.4 | 201.8 | 226.8 | 201.8 | 221.3 | 242.1 |
| 65° | 1777.0 | 1685.1 | 1276.0 | 160.0 | 132.2 | 84.9 | 91.8 | 132.2 | 141.9 | 155.9 | 175.3 |
| 67.5° | 308.9 | 292.2 | 214.3 | 71.0 | 54.3 | 51.5 | 44.5 | 61.2 | 86.3 | 96.0 | 111.3 |
| 70° | 40.4 | 39.0 | 34.8 | 29.2 | 27.8 | 25.0 | 19.5 | 39.0 | 58.4 | 61.2 | 71.0 |
| 72.5° | 9.7 | 8.3 | 8.3 | 7.0 | 8.3 | 2.8 | 2.8 | 20.9 | 41.7 | 43.1 | 50.1 |
| 75° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 7.0 | 26.4 | 29.2 | 34.8 |
| 77.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 1.4 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P637269

CATALOG NUMBER: GWS-SA4C-740-U-SLL-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 |
| 2.5° | 1618.3 | 1590.5 | 1580.8 | 1566.9 | 1548.8 | 1554.3 | 1529.3 | 1520.9 | 1533.5 | 1550.2 | 1546.0 |
| 5° | 1470.8 | 1440.2 | 1419.4 | 1387.3 | 1381.8 | 1369.3 | 1360.9 | 1349.8 | 1363.7 | 1383.2 | 1387.3 |
| 7.5° | 1354.0 | 1327.5 | 1306.6 | 1296.9 | 1289.9 | 1284.4 | 1267.7 | 1259.3 | 1259.3 | 1267.7 | 1274.6 |
| 10° | 1303.9 | 1284.4 | 1280.2 | 1283.0 | 1294.1 | 1292.7 | 1277.4 | 1266.3 | 1252.4 | 1245.4 | 1253.8 |
| 12.5° | 1373.4 | 1341.4 | 1335.9 | 1337.3 | 1351.2 | 1349.8 | 1333.1 | 1319.2 | 1316.4 | 1319.2 | 1345.6 |
| 15° | 1491.7 | 1443.0 | 1406.8 | 1399.9 | 1406.8 | 1404.0 | 1391.5 | 1383.2 | 1387.3 | 1427.7 | 1472.2 |
| 17.5° | 1597.5 | 1522.3 | 1456.9 | 1431.9 | 1430.5 | 1426.3 | 1413.8 | 1411.0 | 1431.9 | 1507.0 | 1572.4 |
| 20° | 1628.1 | 1554.3 | 1461.1 | 1429.1 | 1422.1 | 1418.0 | 1404.0 | 1408.2 | 1434.7 | 1525.1 | 1580.8 |
| 22.5° | 1587.7 | 1516.8 | 1419.4 | 1387.3 | 1381.8 | 1380.4 | 1366.5 | 1372.0 | 1394.3 | 1473.6 | 1519.5 |
| 25° | 1511.2 | 1451.4 | 1349.8 | 1321.9 | 1321.9 | 1319.2 | 1306.6 | 1309.4 | 1323.3 | 1392.9 | 1437.4 |
| 27.5° | 1418.0 | 1360.9 | 1276.0 | 1248.2 | 1252.4 | 1256.5 | 1241.2 | 1237.1 | 1248.2 | 1313.6 | 1340.0 |
| 30° | 1310.8 | 1270.5 | 1203.7 | 1178.6 | 1177.2 | 1193.9 | 1173.1 | 1167.5 | 1182.8 | 1234.3 | 1239.8 |
| 32.5° | 1206.5 | 1187.0 | 1139.7 | 1120.2 | 1121.6 | 1124.4 | 1113.2 | 1113.2 | 1127.1 | 1155.0 | 1153.6 |
| 35° | 1104.9 | 1092.3 | 1084.0 | 1070.1 | 1068.7 | 1063.1 | 1063.1 | 1065.9 | 1081.2 | 1091.0 | 1072.9 |
| 37.5° | 1007.5 | 1020.0 | 1029.7 | 1015.8 | 1004.7 | 1004.7 | 1004.7 | 1017.2 | 1031.1 | 1026.9 | 996.3 |
| 40° | 921.2 | 947.6 | 978.2 | 962.9 | 936.5 | 935.1 | 940.7 | 961.5 | 982.4 | 957.4 | 929.5 |
| 42.5° | 847.4 | 880.8 | 924.0 | 915.6 | 886.4 | 882.2 | 886.4 | 912.8 | 929.5 | 897.5 | 866.9 |
| 45° | 775.1 | 816.8 | 868.3 | 868.3 | 836.3 | 832.1 | 833.5 | 868.3 | 878.1 | 840.5 | 801.5 |
| 47.5° | 713.9 | 759.8 | 814.0 | 814.0 | 787.6 | 779.3 | 786.2 | 822.4 | 829.3 | 776.5 | 740.3 |
| 50° | 655.4 | 705.5 | 765.3 | 761.2 | 743.1 | 736.1 | 748.6 | 787.6 | 779.3 | 720.8 | 683.2 |
| 52.5° | 581.7 | 634.5 | 716.6 | 720.8 | 711.1 | 712.5 | 727.8 | 752.8 | 729.2 | 658.2 | 626.2 |
| 55° | 514.9 | 569.1 | 651.2 | 673.5 | 673.5 | 672.1 | 679.1 | 698.5 | 679.1 | 594.2 | 555.2 |
| 57.5° | 442.5 | 488.4 | 556.6 | 562.2 | 566.4 | 551.0 | 560.8 | 587.2 | 577.5 | 505.1 | 482.9 |
| 60° | 363.2 | 402.2 | 441.1 | 445.3 | 427.2 | 395.2 | 413.3 | 443.9 | 450.9 | 396.6 | 371.5 |
| 62.5° | 257.4 | 295.0 | 340.9 | 340.9 | 322.8 | 290.8 | 314.5 | 340.9 | 331.2 | 275.5 | 260.2 |
| 65° | 192.0 | 226.8 | 261.6 | 276.9 | 261.6 | 239.3 | 257.4 | 276.9 | 261.6 | 215.7 | 193.4 |
| 67.5° | 123.8 | 147.5 | 168.4 | 180.9 | 183.7 | 180.9 | 189.2 | 183.7 | 165.6 | 135.0 | 122.5 |
| 70° | 75.1 | 87.7 | 98.8 | 109.9 | 118.3 | 122.5 | 126.6 | 114.1 | 96.0 | 79.3 | 75.1 |
| 72.5° | 54.3 | 65.4 | 75.1 | 83.5 | 93.2 | 96.0 | 96.0 | 87.7 | 71.0 | 55.7 | 51.5 |
| 75° | 37.6 | 47.3 | 55.7 | 61.2 | 69.6 | 72.4 | 72.4 | 65.4 | 52.9 | 40.4 | 36.2 |
| 77.5° | 1.4 | 9.7 | 9.7 | 8.3 | 11.1 | 13.9 | 13.9 | 16.7 | 15.3 | 11.1 | 9.7 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P637269

CATALOG NUMBER: GWS-SA4C-740-U-SLL-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 |
| 2.5° | 1554.3 | 1604.4 | 1618.3 | 1669.8 | 1715.7 | 1761.7 | 1817.3 | 1850.7 | 1900.8 | 1935.6 | 1955.1 |
| 5° | 1401.3 | 1443.0 | 1493.1 | 1569.6 | 1649.0 | 1736.6 | 1842.4 | 1934.2 | 2049.7 | 2134.6 | 2162.4 |
| 7.5° | 1289.9 | 1344.2 | 1402.7 | 1498.7 | 1607.2 | 1724.1 | 1873.0 | 2023.3 | 2200.0 | 2315.5 | 2389.2 |
| 10° | 1269.1 | 1324.7 | 1402.7 | 1497.3 | 1611.4 | 1745.0 | 1927.3 | 2122.1 | 2343.3 | 2483.9 | 2567.4 |
| 12.5° | 1369.3 | 1429.1 | 1462.5 | 1505.6 | 1591.9 | 1740.8 | 1974.6 | 2222.3 | 2482.5 | 2635.5 | 2724.6 |
| 15° | 1516.8 | 1569.6 | 1515.4 | 1461.1 | 1516.8 | 1696.3 | 2001.0 | 2305.8 | 2604.9 | 2781.7 | 2873.5 |
| 17.5° | 1618.3 | 1622.5 | 1504.2 | 1388.7 | 1404.0 | 1615.6 | 2010.8 | 2389.2 | 2735.7 | 2920.8 | 3016.8 |
| 20° | 1608.6 | 1575.2 | 1455.5 | 1327.5 | 1280.2 | 1511.2 | 1999.6 | 2463.0 | 2867.9 | 3061.4 | 3156.0 |
| 22.5° | 1533.5 | 1494.5 | 1392.9 | 1267.7 | 1175.8 | 1387.3 | 1980.1 | 2529.8 | 2989.0 | 3208.9 | 3297.9 |
| 25° | 1443.0 | 1401.3 | 1317.8 | 1207.8 | 1109.0 | 1267.7 | 1964.8 | 2621.6 | 3142.1 | 3400.9 | 3470.5 |
| 27.5° | 1337.3 | 1301.1 | 1230.1 | 1150.8 | 1081.2 | 1177.2 | 1960.7 | 2742.7 | 3327.1 | 3634.7 | 3683.4 |
| 30° | 1234.3 | 1200.9 | 1145.2 | 1099.3 | 1070.1 | 1124.4 | 1946.7 | 2872.1 | 3548.4 | 3903.2 | 3956.1 |
| 32.5° | 1135.5 | 1102.1 | 1067.3 | 1060.3 | 1061.7 | 1104.9 | 1899.4 | 3000.1 | 3811.4 | 4292.8 | 4331.8 |
| 35° | 1050.6 | 1011.6 | 997.7 | 1014.4 | 1045.0 | 1071.5 | 1765.8 | 3105.9 | 4093.9 | 4717.3 | 4749.3 |
| 37.5° | 969.9 | 930.9 | 929.5 | 969.9 | 1003.3 | 1020.0 | 1608.6 | 3210.2 | 4475.1 | 5148.6 | 5189.0 |
| 40° | 896.1 | 857.2 | 871.1 | 919.8 | 946.2 | 954.6 | 1418.0 | 3368.9 | 4878.7 | 5603.7 | 5581.4 |
| 42.5° | 833.5 | 793.2 | 801.5 | 864.1 | 887.8 | 910.1 | 1242.6 | 3501.1 | 5266.9 | 6035.0 | 6028.1 |
| 45° | 772.3 | 741.7 | 736.1 | 804.3 | 825.2 | 914.2 | 1114.6 | 3602.7 | 5766.5 | 6584.7 | 6595.8 |
| 47.5° | 712.5 | 688.8 | 690.2 | 719.4 | 770.9 | 935.1 | 1006.1 | 3669.4 | 6491.5 | 7455.8 | 7262.4 |
| 50° | 658.2 | 640.1 | 655.4 | 622.0 | 736.1 | 908.7 | 912.8 | 3655.5 | 7301.3 | 8290.7 | 7902.5 |
| 52.5° | 598.4 | 594.2 | 601.1 | 520.4 | 680.5 | 801.5 | 825.2 | 3470.5 | 7681.2 | 8861.2 | 8640.0 |
| 55° | 537.1 | 535.7 | 480.1 | 416.1 | 569.1 | 640.1 | 706.9 | 2895.8 | 7668.7 | 9164.6 | 9433.1 |
| 57.5° | 464.8 | 453.6 | 364.6 | 339.5 | 442.5 | 445.3 | 644.3 | 1896.6 | 6796.2 | 8438.2 | 8994.8 |
| 60° | 352.1 | 343.7 | 267.2 | 275.5 | 308.9 | 285.3 | 513.5 | 944.8 | 5079.1 | 6573.6 | 7201.1 |
| 62.5° | 243.5 | 232.4 | 199.0 | 212.9 | 199.0 | 162.8 | 314.5 | 467.6 | 3076.7 | 4150.9 | 4720.0 |
| 65° | 178.1 | 165.6 | 136.4 | 116.9 | 93.2 | 93.2 | 119.7 | 179.5 | 1191.1 | 1764.5 | 2127.6 |
| 67.5° | 109.9 | 104.4 | 80.7 | 58.4 | 57.1 | 61.2 | 62.6 | 89.1 | 192.0 | 306.1 | 374.3 |
| 70° | 71.0 | 65.4 | 54.3 | 37.6 | 34.8 | 36.2 | 37.6 | 41.7 | 48.7 | 52.9 | 64.0 |
| 72.5° | 48.7 | 45.9 | 39.0 | 20.9 | 16.7 | 18.1 | 19.5 | 19.5 | 23.7 | 22.3 | 26.4 |
| 75° | 34.8 | 32.0 | 27.8 | 9.7 | 5.6 | 7.0 | 8.3 | 7.0 | 8.3 | 5.6 | 7.0 |
| 77.5° | 9.7 | 9.7 | 7.0 | 1.4 | 0.0 | 1.4 | 2.8 | 2.8 | 1.4 | 0.0 | 0.0 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 1.4 | 1.4 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P637269

CATALOG NUMBER: GWS-SA4C-740-U-SLL-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|--------|--------|---------|---------|---------|--------|--------|---------|---------|---------|
| 0° | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 | 1768.6 |
| 2.5° | 2005.2 | 2037.2 | 2049.7 | 2031.6 | 2046.9 | 2021.9 | 2012.1 | 1974.6 | 1971.8 | 1964.8 |
| 5° | 2275.1 | 2347.5 | 2390.6 | 2417.1 | 2386.5 | 2353.1 | 2303.0 | 2216.7 | 2190.3 | 2173.6 |
| 7.5° | 2540.9 | 2653.6 | 2727.4 | 2762.2 | 2753.8 | 2685.6 | 2595.2 | 2450.5 | 2399.0 | 2373.9 |
| 10° | 2771.9 | 2909.7 | 2998.7 | 3041.9 | 3023.8 | 2963.9 | 2834.5 | 2653.6 | 2585.5 | 2570.1 |
| 12.5° | 2933.3 | 3060.0 | 3121.2 | 3158.8 | 3160.1 | 3136.5 | 3014.0 | 2831.8 | 2751.0 | 2731.6 |
| 15° | 3034.9 | 3089.2 | 3090.6 | 3112.8 | 3151.8 | 3204.7 | 3147.6 | 2986.2 | 2899.9 | 2870.7 |
| 17.5° | 3098.9 | 3039.1 | 2977.9 | 2983.4 | 3047.4 | 3188.0 | 3246.4 | 3122.6 | 3030.7 | 2998.7 |
| 20° | 3144.8 | 2955.6 | 2841.5 | 2842.9 | 2908.3 | 3121.2 | 3314.6 | 3254.8 | 3160.1 | 3130.9 |
| 22.5° | 3174.1 | 2881.8 | 2719.0 | 2714.9 | 2784.4 | 3041.9 | 3377.2 | 3412.0 | 3318.8 | 3285.4 |
| 25° | 3233.9 | 2847.1 | 2645.3 | 2668.9 | 2730.2 | 3016.8 | 3462.1 | 3620.7 | 3534.5 | 3489.9 |
| 27.5° | 3341.0 | 2881.8 | 2638.3 | 2692.6 | 2762.2 | 3090.6 | 3609.6 | 3899.0 | 3810.0 | 3759.9 |
| 30° | 3526.1 | 3012.6 | 2745.5 | 2820.6 | 2904.1 | 3284.0 | 3857.3 | 4287.3 | 4159.3 | 4112.0 |
| 32.5° | 3823.9 | 3284.0 | 3076.7 | 3238.1 | 3318.8 | 3601.3 | 4228.8 | 4722.8 | 4618.5 | 4523.8 |
| 35° | 4234.4 | 3903.2 | 3879.6 | 4255.3 | 4235.8 | 4202.4 | 4685.3 | 5257.2 | 5099.9 | 5008.1 |
| 37.5° | 4799.4 | 4899.6 | 5074.9 | 5447.8 | 5435.3 | 5180.6 | 5285.0 | 5762.3 | 5681.6 | 5563.3 |
| 40° | 5504.9 | 5717.8 | 6015.6 | 6549.9 | 6382.9 | 6062.9 | 6021.1 | 6279.9 | 6214.5 | 6075.4 |
| 42.5° | 5920.9 | 6288.3 | 6856.0 | 7336.1 | 7202.5 | 6643.1 | 6595.8 | 6971.5 | 6828.2 | 6676.5 |
| 45° | 6114.4 | 6753.1 | 7866.3 | 8516.1 | 8111.2 | 7028.6 | 7010.5 | 7873.2 | 7792.5 | 7589.4 |
| 47.5° | 6203.4 | 7222.0 | 9049.1 | 10032.9 | 9275.9 | 7366.7 | 7301.3 | 9181.3 | 9075.5 | 8836.2 |
| 50° | 6302.2 | 7869.1 | 10474.0 | 11790.4 | 10682.7 | 7749.4 | 7796.7 | 10400.2 | 10355.7 | 10073.2 |
| 52.5° | 6519.3 | 8553.7 | 12228.7 | 13799.7 | 12388.7 | 8349.1 | 8646.9 | 11549.6 | 11249.1 | 10923.5 |
| 55° | 6844.9 | 9299.6 | 14054.4 | 15852.2 | 14129.5 | 9154.8 | 9566.7 | 12160.5 | 11317.3 | 10956.9 |
| 57.5° | 6484.5 | 9486.0 | 15135.6 | 17285.5 | 14901.8 | 9157.6 | 8788.9 | 11101.6 | 9953.6 | 9604.3 |
| 60° | 5145.9 | 8825.0 | 14719.5 | 16975.2 | 14243.6 | 8132.1 | 6729.4 | 8667.8 | 7540.7 | 7306.9 |
| 62.5° | 3478.8 | 7401.5 | 12957.9 | 14356.3 | 12191.1 | 6396.8 | 4373.6 | 5637.1 | 4668.6 | 4475.1 |
| 65° | 1906.4 | 5521.6 | 10469.8 | 10860.8 | 9541.7 | 4468.2 | 2250.1 | 2446.3 | 1863.2 | 1777.0 |
| 67.5° | 526.0 | 3843.4 | 7703.5 | 7205.3 | 6694.6 | 2909.7 | 581.7 | 436.9 | 311.7 | 308.9 |
| 70° | 132.2 | 2542.3 | 4615.7 | 4757.6 | 4105.0 | 1863.2 | 111.3 | 52.9 | 41.7 | 40.4 |
| 72.5° | 55.7 | 1093.7 | 2190.3 | 2517.3 | 2101.2 | 862.7 | 40.4 | 15.3 | 12.5 | 9.7 |
| 75° | 7.0 | 87.7 | 186.5 | 282.5 | 193.4 | 93.2 | 0.0 | 0.0 | 0.0 | 0.0 |
| 77.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW, INVUE, LUMARK AND STREETWORKS

DATA VALID FOR LUMINAIRES UTILIZING SA LIGHT ENGINES

Report Number: SP1-2101-121-2

Luminaire Tested: IFLD-S-SA2A-740-U-T3R-HSS

Test Date: 03/05/2021

Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/05/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

Spectral Parameters

| | | | | | |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K): | 3905 | CRI (Ra): | 71.2 | R9: | -29.7 |
| CIE u': | 0.2273 | R1: | 68.9 | R10: | 46.2 |
| CIE v': | 0.5024 | R2: | 77.0 | R11: | 68.8 |
| Duv: | -0.0008 | R3: | 84.0 | R12: | 45.6 |
| CIE x: | 0.3841 | R4: | 71.6 | R13: | 69.5 |
| CIE y: | 0.3774 | R5: | 68.9 | R14: | 90.7 |
| CIE z: | 0.2385 | R6: | 68.3 | | |
| Peak Wavelength (nm): | 443 | R7: | 78.7 | | |
| Dominant Wavelength (nm): | 579 | R8: | 52.2 | | |
| Purity: | 28.7 | | | | |
| Rf: | 71.7 | | | | |
| Rg: | 96.9 | | | | |



Test Conditions


Stabilization Time: 211M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.8/312%
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-2


| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-121-2

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 2.7 | 620 | 97577 | 25.4 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 4.8 | 625 | 90158 | 19.9 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 8.0 | 630 | 82240 | 14.9 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 13.3 | 635 | 74361 | 11.2 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 20.2 | 640 | 66994 | 8.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 28.5 | 645 | 60405 | 5.8 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 37.4 | 650 | 53806 | 3.9 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 44.9 | 655 | 47610 | 2.7 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 52.6 | 660 | 42018 | 1.8 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 58.4 | 665 | 36742 | 1.2 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.0 | 540 | 96845 | 63.1 | 670 | 32105 | 0.7 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.0 | 545 | 100829 | 67.1 | 675 | 27946 | 0.5 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 0.1 | 550 | 105648 | 71.8 | 680 | 24146 | 0.3 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 0.2 | 555 | 110017 | 75.1 | 685 | 21191 | 0.2 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 0.5 | 560 | 114586 | 77.9 | 690 | 18544 | 0.1 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 1.2 | 565 | 118987 | 79.1 | 695 | 16058 | 0.1 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 2.1 | 570 | 122326 | 79.5 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 2.9 | 575 | 125968 | 78.4 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 2.7 | 580 | 127613 | 75.8 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 2.0 | 585 | 129466 | 71.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 1.5 | 590 | 128813 | 66.6 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 1.3 | 595 | 126387 | 59.9 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 1.0 | 600 | 123477 | 53.2 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 1.1 | 605 | 118718 | 46.0 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 1.2 | 610 | 112091 | 38.5 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 1.7 | 615 | 105039 | 31.7 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: 10425.8 S/P: 1.47

| λ (nm) | Power ($\mu\text{W/nm}$) | Lumens (Φ/nm) | λ (nm) | Power ($\mu\text{W/nm}$) | Lumens (Φ/nm) | λ (nm) | Power ($\mu\text{W/nm}$) | Lumens (Φ/nm) | λ (nm) | Power ($\mu\text{W/nm}$) | Lumens (Φ/nm) | λ (nm) | Power ($\mu\text{W/nm}$) | Lumens (Φ/nm) |
|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 29.3 | 620 | 97577 | 1.2 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 43.0 | 625 | 90158 | 0.8 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 60.8 | 630 | 82240 | 0.5 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 81.1 | 635 | 74361 | 0.3 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 99.6 | 640 | 66994 | 0.2 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 113.9 | 645 | 60405 | 0.1 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 122.6 | 650 | 53806 | 0.1 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 125.0 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 123.1 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.1 | 535 | 94097 | 117.3 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 107.0 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.9 | 545 | 100829 | 96.7 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 3.0 | 550 | 105648 | 86.4 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 9.3 | 555 | 110017 | 75.2 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 23.0 | 560 | 114586 | 64.0 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 45.7 | 565 | 118987 | 53.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 75.5 | 570 | 122326 | 43.2 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 93.8 | 575 | 125968 | 34.3 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 79.3 | 580 | 127613 | 26.3 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 51.3 | 585 | 129466 | 19.8 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 35.6 | 590 | 128813 | 14.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 26.0 | 595 | 126387 | 10.1 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 19.3 | 600 | 123477 | 7.0 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 16.8 | 605 | 118718 | 4.7 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 17.7 | 610 | 112091 | 3.0 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 21.4 | 615 | 105039 | 1.9 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Melanopic Flux vs. Wavelength




Melanopic Lumens: 3927.2 M/P: 0.55





| λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 15.8 | 620 | 97577 | 0.1 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 22.0 | 625 | 90158 | 0.0 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 29.2 | 630 | 82240 | 0.0 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 36.6 | 635 | 74361 | 0.0 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 42.2 | 640 | 66994 | 0.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 44.9 | 645 | 60405 | 0.0 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 44.9 | 650 | 53806 | 0.0 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 42.4 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 38.6 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 33.9 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 28.3 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.6 | 545 | 100829 | 23.4 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 2.1 | 550 | 105648 | 19.0 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 5.9 | 555 | 110017 | 14.8 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 14.3 | 560 | 114586 | 11.3 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 27.3 | 565 | 118987 | 8.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 45.1 | 570 | 122326 | 6.0 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 55.3 | 575 | 125968 | 4.2 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 47.2 | 580 | 127613 | 2.9 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 30.8 | 585 | 129466 | 1.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 21.7 | 590 | 128813 | 1.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 16.1 | 595 | 126387 | 0.8 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 12.0 | 600 | 123477 | 0.5 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 10.3 | 605 | 118718 | 0.3 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 10.5 | 610 | 112091 | 0.2 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 12.1 | 615 | 105039 | 0.1 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

Summary

$R_f = 71.7$
 $R_g = 96.9$
 CIE $R_a = 71.2$
 $R_g = -29.7$



Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)


| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)