

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P637274

Luminaire Tested: GWS-SA4C-740-U-SLR-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P637274
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-43)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA4C-740-U-SLR-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND
SPILL LIGHT ELIMINATOR RIGHT OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (64) 4000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15187.5 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type III - Short
BUG Rating: B3 - U0 - G3


Input Watts (W): 128.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P637274
 CATALOG NUMBER: GWS-SA4C-740-U-SLR-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 6.7 fc
 Type III - Short - N/A

REPORT NUMBER: P637274
CATALOG NUMBER: GWS-SA4C-740-U-SLR-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P637274

CATALOG NUMBER: GWS-SA4C-740-U-SLR-W-GRSWH


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 5323.8 | 0.0 | 5323.8 |
| | % Fixture | 35.1 | 0.0 | 35.1 |
| Street Side | Lumens | 9863.7 | 0.0 | 9863.7 |
| | % Fixture | 64.9 | 0.0 | 64.9 |
| Total | Lumens | 15187.5 | 0.0 | 15187.5 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 304.4 | 2.0 |
| 10°-20° | 961.9 | 6.3 |
| 20°-30° | 1562.5 | 10.3 |
| 30°-40° | 2203.6 | 14.5 |
| 40°-50° | 3045.3 | 20.1 |
| 50°-60° | 3920.3 | 25.8 |
| 60°-70° | 2483.9 | 16.4 |
| 70°-80° | 637.4 | 4.2 |
| 80°-90° | 68.2 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 15187.5 | 100.0 |
| 0°-180° | 15187.5 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P637274


CATALOG NUMBER: GWS-SA4C-740-U-SLR-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1542.1 | 10.2 | | | |
| FM (30°-60°) | 6207.8 | 40.9 | | | |
| FH (60°-80°) | 2095.4 | 13.8 | | | G2/5000 |
| FVH (80°-90°) | 18.5 | 0.1 | | | G1/100 |
| BL (0°-30°) | 1286.7 | 8.5 | B3/2500 | | |
| BM (30°-60°) | 2961.4 | 19.5 | B3/5000 | | |
| BH (60°-80°) | 1025.9 | 6.8 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 49.6 | 0.3 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G3

Type III Short





REPORT NUMBER: P637274

CATALOG NUMBER: GWS-SA4C-740-U-SLR-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|---------|---------|---------|--------|--------|---------|
| 0° | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 |
| 2.5° | 3263.3 | 3285.6 | 3299.5 | 3325.9 | 3373.2 | 3399.7 | 3428.9 | 3396.9 | 3405.2 | 3401.1 | 3349.6 |
| 5° | 3456.7 | 3483.2 | 3519.3 | 3597.3 | 3684.9 | 3733.7 | 3779.6 | 3772.6 | 3729.5 | 3657.1 | 3605.6 |
| 7.5° | 3637.6 | 3668.2 | 3730.9 | 3857.5 | 3986.9 | 4062.1 | 4117.7 | 4081.6 | 4045.4 | 3931.3 | 3801.8 |
| 10° | 3779.6 | 3797.7 | 3882.6 | 4052.3 | 4202.6 | 4287.5 | 4355.7 | 4347.3 | 4297.2 | 4169.2 | 3995.3 |
| 12.5° | 3913.2 | 3925.7 | 4017.5 | 4187.3 | 4322.3 | 4359.9 | 4415.5 | 4433.6 | 4416.9 | 4320.9 | 4149.7 |
| 15° | 4056.5 | 4080.2 | 4165.0 | 4294.5 | 4355.7 | 4316.7 | 4336.2 | 4386.3 | 4433.6 | 4433.6 | 4276.4 |
| 17.5° | 4190.1 | 4211.0 | 4297.2 | 4352.9 | 4294.5 | 4191.5 | 4197.1 | 4261.1 | 4373.8 | 4492.1 | 4391.9 |
| 20° | 4308.4 | 4327.9 | 4412.8 | 4359.9 | 4174.8 | 4024.5 | 4020.3 | 4098.2 | 4280.5 | 4529.6 | 4515.7 |
| 22.5° | 4437.8 | 4465.6 | 4536.6 | 4365.4 | 4063.5 | 3872.8 | 3871.4 | 3952.1 | 4198.4 | 4567.2 | 4657.7 |
| 25° | 4621.5 | 4664.6 | 4700.8 | 4414.1 | 4003.6 | 3774.0 | 3792.1 | 3868.6 | 4172.0 | 4628.4 | 4867.8 |
| 27.5° | 4894.2 | 4929.0 | 4926.2 | 4515.7 | 4000.8 | 3733.7 | 3771.2 | 3860.3 | 4219.3 | 4737.0 | 5089.1 |
| 30° | 5189.3 | 5207.4 | 5178.1 | 4657.7 | 4064.9 | 3758.7 | 3814.4 | 3920.1 | 4339.0 | 4916.5 | 5414.7 |
| 32.5° | 5516.3 | 5538.6 | 5482.9 | 4870.6 | 4213.8 | 3943.8 | 4066.2 | 4117.7 | 4507.4 | 5175.3 | 5759.8 |
| 35° | 5892.0 | 5935.2 | 5819.7 | 5151.7 | 4652.1 | 4618.7 | 4796.8 | 4730.0 | 4865.0 | 5481.5 | 6128.6 |
| 37.5° | 6287.2 | 6288.6 | 6123.0 | 5567.8 | 5512.1 | 5569.2 | 5925.4 | 5716.7 | 5623.4 | 5822.4 | 6504.3 |
| 40° | 6622.6 | 6614.3 | 6359.6 | 6128.6 | 6260.8 | 6487.6 | 6917.6 | 6597.6 | 6352.6 | 6280.3 | 6816.0 |
| 42.5° | 6958.0 | 6927.4 | 6669.9 | 6484.8 | 6777.1 | 7243.3 | 7728.9 | 7336.5 | 6820.2 | 6696.4 | 7123.6 |
| 45° | 7386.6 | 7376.8 | 7066.5 | 6626.8 | 7243.3 | 8089.3 | 8733.7 | 8097.7 | 7097.1 | 6938.5 | 7635.7 |
| 47.5° | 8078.2 | 8030.9 | 7453.4 | 6615.6 | 7680.2 | 9216.5 | 10030.6 | 9056.5 | 7290.6 | 6944.1 | 8462.3 |
| 50° | 8754.5 | 8696.1 | 7915.4 | 6614.3 | 8131.1 | 10385.5 | 11561.4 | 10221.3 | 7488.2 | 6977.5 | 9302.8 |
| 52.5° | 9437.8 | 9437.8 | 8673.8 | 6771.5 | 8604.2 | 11690.8 | 13330.1 | 11672.7 | 7824.9 | 7414.4 | 10336.8 |
| 55° | 9844.1 | 9952.7 | 9526.9 | 7037.3 | 9158.1 | 13227.1 | 15079.3 | 13239.6 | 8345.4 | 8203.5 | 11291.4 |
| 57.5° | 9327.9 | 9531.0 | 9469.8 | 6852.2 | 9485.1 | 14355.7 | 16562.8 | 14428.1 | 8602.8 | 8296.7 | 11148.1 |
| 60° | 7600.9 | 7883.4 | 8023.9 | 5917.1 | 9162.3 | 14486.5 | 16873.1 | 14506.0 | 8071.3 | 7065.1 | 9549.1 |
| 62.5° | 5052.9 | 5285.3 | 5499.6 | 4227.7 | 7932.1 | 13032.3 | 14923.5 | 13036.5 | 6740.9 | 5272.8 | 6615.6 |
| 65° | 2478.4 | 2651.0 | 2882.0 | 2499.3 | 6196.8 | 10889.2 | 11635.1 | 10534.4 | 4876.2 | 2951.6 | 3374.6 |
| 67.5° | 648.5 | 697.2 | 729.2 | 969.9 | 4439.2 | 7823.6 | 7588.4 | 7705.3 | 3132.5 | 964.4 | 882.3 |
| 70° | 336.8 | 339.5 | 338.2 | 400.8 | 3000.3 | 4972.2 | 5229.6 | 4838.6 | 2186.2 | 403.6 | 347.9 |
| 72.5° | 240.7 | 242.1 | 238.0 | 270.0 | 1448.7 | 2848.6 | 2951.6 | 2919.6 | 1145.3 | 239.4 | 238.0 |
| 75° | 157.3 | 158.6 | 155.9 | 158.6 | 218.5 | 324.2 | 299.2 | 314.5 | 190.6 | 151.7 | 151.7 |
| 77.5° | 93.2 | 94.6 | 93.2 | 96.0 | 93.2 | 93.2 | 86.3 | 86.3 | 82.1 | 82.1 | 83.5 |
| 80° | 62.6 | 62.6 | 61.2 | 64.0 | 58.4 | 58.4 | 55.7 | 54.3 | 50.1 | 48.7 | 48.7 |
| 82.5° | 37.6 | 39.0 | 37.6 | 37.6 | 34.8 | 34.8 | 32.0 | 30.6 | 26.4 | 26.4 | 25.0 |
| 85° | 19.5 | 19.5 | 18.1 | 18.1 | 15.3 | 13.9 | 11.1 | 11.1 | 8.3 | 7.0 | 7.0 |
| 87.5° | 2.8 | 2.8 | 1.4 | 1.4 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P637274

CATALOG NUMBER: GWS-SA4C-740-U-SLR-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 |
| 2.5° | 3335.7 | 3307.8 | 3266.1 | 3225.7 | 3188.1 | 3149.2 | 3104.7 | 3058.7 | 3019.8 | 2979.4 | 2958.5 |
| 5° | 3537.4 | 3480.4 | 3371.8 | 3275.8 | 3189.5 | 3118.6 | 3042.0 | 2976.6 | 2915.4 | 2865.3 | 2840.2 |
| 7.5° | 3719.7 | 3630.7 | 3466.5 | 3314.8 | 3197.9 | 3100.5 | 2994.7 | 2897.3 | 2815.2 | 2754.0 | 2730.3 |
| 10° | 3888.1 | 3782.4 | 3566.7 | 3374.6 | 3238.2 | 3129.7 | 3000.3 | 2868.1 | 2759.5 | 2678.8 | 2659.3 |
| 12.5° | 4024.5 | 3903.4 | 3646.0 | 3423.3 | 3261.9 | 3145.0 | 3030.9 | 2916.8 | 2809.6 | 2705.3 | 2688.6 |
| 15° | 4145.6 | 4002.2 | 3705.8 | 3453.9 | 3253.6 | 3104.7 | 3008.6 | 2994.7 | 2994.7 | 2876.4 | 2843.0 |
| 17.5° | 4249.9 | 4092.7 | 3754.5 | 3467.9 | 3200.7 | 2985.0 | 2926.5 | 3047.6 | 3184.0 | 3099.1 | 3023.9 |
| 20° | 4369.6 | 4179.0 | 3794.9 | 3467.9 | 3103.3 | 2833.3 | 2827.7 | 3033.7 | 3235.5 | 3236.9 | 3157.5 |
| 22.5° | 4490.7 | 4279.2 | 3842.2 | 3455.3 | 2969.7 | 2657.9 | 2760.9 | 2978.0 | 3157.5 | 3234.1 | 3179.8 |
| 25° | 4686.9 | 4418.3 | 3917.3 | 3445.6 | 2813.8 | 2538.3 | 2701.1 | 2904.3 | 3055.9 | 3136.7 | 3101.9 |
| 27.5° | 4936.0 | 4602.0 | 4031.5 | 3460.9 | 2659.3 | 2467.3 | 2637.1 | 2808.2 | 2946.0 | 3017.0 | 2991.9 |
| 30° | 5214.3 | 4813.5 | 4153.9 | 3487.3 | 2548.0 | 2431.1 | 2560.5 | 2698.3 | 2820.8 | 2891.7 | 2880.6 |
| 32.5° | 5569.2 | 5043.1 | 4259.7 | 3451.2 | 2485.4 | 2413.0 | 2479.8 | 2578.6 | 2696.9 | 2741.4 | 2751.2 |
| 35° | 5993.6 | 5296.4 | 4340.4 | 3309.2 | 2428.3 | 2393.5 | 2392.2 | 2453.4 | 2536.9 | 2607.9 | 2614.8 |
| 37.5° | 6384.6 | 5592.8 | 4429.4 | 3065.7 | 2325.4 | 2344.8 | 2289.2 | 2325.4 | 2407.5 | 2478.4 | 2506.3 |
| 40° | 6771.5 | 5893.4 | 4553.3 | 2755.4 | 2190.4 | 2236.3 | 2170.9 | 2195.9 | 2261.3 | 2354.6 | 2399.1 |
| 42.5° | 7147.2 | 6164.8 | 4684.1 | 2438.1 | 2055.4 | 2084.6 | 2035.9 | 2061.0 | 2129.1 | 2246.0 | 2296.1 |
| 45° | 7556.4 | 6532.2 | 4785.7 | 2138.9 | 1938.5 | 1926.0 | 1887.0 | 1923.2 | 2026.2 | 2154.2 | 2214.0 |
| 47.5° | 8330.1 | 7111.1 | 4852.5 | 1939.9 | 1875.9 | 1785.4 | 1740.9 | 1818.8 | 1935.7 | 2065.1 | 2137.5 |
| 50° | 9275.0 | 7948.8 | 4833.0 | 1813.2 | 1821.6 | 1640.7 | 1625.4 | 1728.4 | 1853.6 | 1988.6 | 2067.9 |
| 52.5° | 10023.7 | 8771.2 | 4611.7 | 1692.2 | 1715.8 | 1548.8 | 1504.3 | 1654.6 | 1774.3 | 1912.1 | 1994.2 |
| 55° | 10595.6 | 9048.2 | 3932.6 | 1548.8 | 1543.3 | 1482.0 | 1388.8 | 1578.1 | 1695.0 | 1823.0 | 1912.1 |
| 57.5° | 10129.4 | 8431.7 | 2915.4 | 1351.2 | 1317.8 | 1349.8 | 1259.4 | 1448.7 | 1597.6 | 1724.2 | 1803.5 |
| 60° | 8406.6 | 6722.8 | 1624.0 | 1196.8 | 1102.1 | 1180.1 | 1166.2 | 1312.3 | 1491.8 | 1625.4 | 1693.6 |
| 62.5° | 5706.9 | 4476.8 | 963.0 | 946.3 | 893.4 | 1004.7 | 1078.5 | 1174.5 | 1351.2 | 1459.8 | 1523.8 |
| 65° | 2844.4 | 2175.1 | 640.1 | 708.3 | 715.3 | 826.6 | 965.8 | 1071.5 | 1219.0 | 1330.4 | 1394.4 |
| 67.5° | 825.2 | 676.3 | 487.1 | 541.3 | 616.5 | 705.5 | 816.9 | 942.1 | 1085.4 | 1217.6 | 1292.8 |
| 70° | 356.2 | 360.4 | 386.9 | 450.9 | 524.6 | 616.5 | 727.8 | 850.3 | 971.3 | 1072.9 | 1130.0 |
| 72.5° | 251.9 | 261.6 | 290.8 | 356.2 | 425.8 | 513.5 | 624.8 | 743.1 | 830.8 | 933.8 | 993.6 |
| 75° | 161.4 | 168.4 | 192.0 | 242.1 | 293.6 | 378.5 | 484.3 | 592.8 | 683.3 | 757.0 | 814.1 |
| 77.5° | 89.1 | 90.5 | 109.9 | 139.2 | 173.9 | 228.2 | 306.2 | 391.0 | 457.8 | 499.6 | 551.1 |
| 80° | 51.5 | 51.5 | 61.2 | 79.3 | 100.2 | 133.6 | 176.7 | 218.5 | 258.8 | 285.3 | 310.3 |
| 82.5° | 27.8 | 27.8 | 32.0 | 43.1 | 54.3 | 73.8 | 98.8 | 119.7 | 144.7 | 158.6 | 175.3 |
| 85° | 8.3 | 8.3 | 11.1 | 15.3 | 19.5 | 27.8 | 39.0 | 50.1 | 61.2 | 71.0 | 80.7 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 1.4 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P637274

CATALOG NUMBER: GWS-SA4C-740-U-SLR-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 |
| 2.5° | 2954.4 | 2934.9 | 2923.7 | 2909.8 | 2914.0 | 2901.5 | 2894.5 | 2898.7 | 2873.6 | 2898.7 | 2923.7 |
| 5° | 2830.5 | 2802.7 | 2780.4 | 2762.3 | 2754.0 | 2737.3 | 2727.5 | 2727.5 | 2712.2 | 2737.3 | 2767.9 |
| 7.5° | 2722.0 | 2699.7 | 2688.6 | 2677.4 | 2664.9 | 2649.6 | 2632.9 | 2627.3 | 2617.6 | 2644.0 | 2670.5 |
| 10° | 2649.6 | 2652.4 | 2659.3 | 2674.6 | 2671.9 | 2662.1 | 2637.1 | 2623.2 | 2623.2 | 2653.8 | 2694.1 |
| 12.5° | 2683.0 | 2712.2 | 2728.9 | 2756.8 | 2762.3 | 2754.0 | 2728.9 | 2717.8 | 2745.6 | 2791.5 | 2858.3 |
| 15° | 2812.4 | 2831.9 | 2845.8 | 2868.1 | 2866.7 | 2859.7 | 2840.2 | 2848.6 | 2940.4 | 3029.5 | 3089.3 |
| 17.5° | 2953.0 | 2930.7 | 2927.9 | 2941.8 | 2946.0 | 2937.7 | 2926.5 | 2964.1 | 3115.8 | 3199.3 | 3229.9 |
| 20° | 3054.6 | 2978.0 | 2961.3 | 2966.9 | 2978.0 | 2973.8 | 2973.8 | 3035.1 | 3192.3 | 3231.3 | 3192.3 |
| 22.5° | 3085.2 | 2976.6 | 2951.6 | 2953.0 | 2968.3 | 2969.7 | 2976.6 | 3040.6 | 3132.5 | 3133.9 | 3074.0 |
| 25° | 3036.5 | 2932.1 | 2914.0 | 2916.8 | 2934.9 | 2933.5 | 2936.3 | 2972.4 | 3012.8 | 2996.1 | 2951.6 |
| 27.5° | 2944.6 | 2854.2 | 2848.6 | 2863.9 | 2887.6 | 2875.0 | 2866.7 | 2876.4 | 2895.9 | 2875.0 | 2836.1 |
| 30° | 2840.2 | 2763.7 | 2766.5 | 2795.7 | 2820.8 | 2799.9 | 2779.0 | 2784.6 | 2786.0 | 2763.7 | 2719.2 |
| 32.5° | 2730.3 | 2673.3 | 2683.0 | 2713.6 | 2742.8 | 2720.6 | 2698.3 | 2695.5 | 2669.1 | 2642.6 | 2599.5 |
| 35° | 2620.4 | 2598.1 | 2610.6 | 2635.7 | 2660.7 | 2642.6 | 2628.7 | 2620.4 | 2563.3 | 2524.4 | 2488.2 |
| 37.5° | 2520.2 | 2536.9 | 2559.1 | 2574.5 | 2582.8 | 2581.4 | 2573.1 | 2553.6 | 2478.4 | 2432.5 | 2385.2 |
| 40° | 2431.1 | 2482.6 | 2506.3 | 2513.2 | 2525.7 | 2523.0 | 2521.6 | 2493.7 | 2394.9 | 2346.2 | 2292.0 |
| 42.5° | 2350.4 | 2422.8 | 2463.1 | 2470.1 | 2477.0 | 2478.4 | 2474.3 | 2433.9 | 2321.2 | 2264.1 | 2212.6 |
| 45° | 2272.5 | 2367.1 | 2418.6 | 2411.6 | 2421.4 | 2421.4 | 2425.6 | 2372.7 | 2248.8 | 2190.4 | 2136.1 |
| 47.5° | 2204.3 | 2315.6 | 2362.9 | 2354.6 | 2360.1 | 2364.3 | 2368.5 | 2307.3 | 2169.5 | 2113.8 | 2058.2 |
| 50° | 2141.7 | 2260.0 | 2300.3 | 2303.1 | 2303.1 | 2312.8 | 2311.4 | 2251.6 | 2102.7 | 2042.9 | 1987.2 |
| 52.5° | 2074.9 | 2202.9 | 2246.0 | 2264.1 | 2269.7 | 2273.9 | 2254.4 | 2184.8 | 2034.5 | 1962.1 | 1910.7 |
| 55° | 1996.9 | 2144.4 | 2183.4 | 2207.1 | 2218.2 | 2215.4 | 2189.0 | 2118.0 | 1964.9 | 1892.6 | 1834.1 |
| 57.5° | 1878.7 | 2019.2 | 2074.9 | 2086.0 | 2104.1 | 2093.0 | 2062.3 | 2002.5 | 1853.6 | 1781.2 | 1721.4 |
| 60° | 1749.2 | 1850.8 | 1895.4 | 1905.1 | 1891.2 | 1895.4 | 1891.2 | 1834.1 | 1704.7 | 1647.6 | 1586.4 |
| 62.5° | 1579.5 | 1669.9 | 1717.2 | 1729.8 | 1706.1 | 1721.4 | 1715.8 | 1644.9 | 1515.4 | 1455.6 | 1401.3 |
| 65° | 1451.4 | 1550.2 | 1605.9 | 1612.9 | 1605.9 | 1612.9 | 1593.4 | 1507.1 | 1384.6 | 1323.4 | 1267.7 |
| 67.5° | 1351.2 | 1452.8 | 1511.3 | 1530.8 | 1523.8 | 1522.4 | 1491.8 | 1391.6 | 1265.0 | 1198.2 | 1127.2 |
| 70° | 1178.7 | 1267.7 | 1342.9 | 1390.2 | 1390.2 | 1363.8 | 1305.3 | 1212.1 | 1110.5 | 1053.4 | 997.8 |
| 72.5° | 1043.7 | 1156.4 | 1230.2 | 1278.9 | 1288.6 | 1273.3 | 1191.2 | 1092.4 | 975.5 | 918.5 | 860.0 |
| 75° | 860.0 | 969.9 | 1049.3 | 1113.3 | 1125.8 | 1109.1 | 1014.5 | 917.1 | 808.5 | 752.9 | 694.4 |
| 77.5° | 574.7 | 640.1 | 704.1 | 762.6 | 750.1 | 761.2 | 697.2 | 623.4 | 556.6 | 514.9 | 488.5 |
| 80° | 324.2 | 367.4 | 386.9 | 418.9 | 418.9 | 418.9 | 377.1 | 342.3 | 304.8 | 281.1 | 254.7 |
| 82.5° | 183.7 | 211.5 | 219.9 | 246.3 | 253.3 | 254.7 | 226.8 | 204.6 | 180.9 | 168.4 | 150.3 |
| 85° | 84.9 | 100.2 | 101.6 | 116.9 | 122.5 | 133.6 | 121.1 | 105.8 | 91.8 | 86.3 | 75.1 |
| 87.5° | 2.8 | 8.3 | 11.1 | 20.9 | 27.8 | 32.0 | 34.8 | 34.8 | 29.2 | 26.4 | 22.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P637274

CATALOG NUMBER: GWS-SA4C-740-U-SLR-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 | 3120.0 |
| 2.5° | 2954.4 | 2987.8 | 3026.7 | 3054.6 | 3104.7 | 3146.4 | 3189.5 | 3236.9 | 3271.6 | 3263.3 |
| 5° | 2805.5 | 2861.1 | 2932.1 | 2997.5 | 3090.7 | 3185.4 | 3289.7 | 3396.9 | 3459.5 | 3456.7 |
| 7.5° | 2722.0 | 2801.3 | 2887.6 | 2975.2 | 3085.2 | 3221.5 | 3381.6 | 3548.6 | 3633.5 | 3637.6 |
| 10° | 2766.5 | 2851.4 | 2909.8 | 2983.6 | 3099.1 | 3270.2 | 3462.3 | 3662.7 | 3760.1 | 3779.6 |
| 12.5° | 2907.0 | 2900.1 | 2895.9 | 2948.8 | 3088.0 | 3305.0 | 3540.2 | 3779.6 | 3889.5 | 3913.2 |
| 15° | 3040.6 | 2897.3 | 2811.0 | 2847.2 | 3037.9 | 3327.3 | 3616.8 | 3907.6 | 4031.5 | 4056.5 |
| 17.5° | 3065.7 | 2848.6 | 2688.6 | 2713.6 | 2958.5 | 3334.3 | 3690.5 | 4032.8 | 4166.4 | 4190.1 |
| 20° | 2996.1 | 2786.0 | 2599.5 | 2564.7 | 2858.3 | 3316.2 | 3736.4 | 4137.2 | 4283.3 | 4308.4 |
| 22.5° | 2908.4 | 2730.3 | 2532.7 | 2442.3 | 2735.9 | 3298.1 | 3787.9 | 4247.2 | 4415.5 | 4437.8 |
| 25° | 2816.6 | 2659.3 | 2470.1 | 2332.3 | 2596.7 | 3286.9 | 3874.2 | 4391.9 | 4595.0 | 4621.5 |
| 27.5° | 2719.2 | 2573.1 | 2415.8 | 2279.4 | 2468.7 | 3300.9 | 3996.7 | 4625.7 | 4856.7 | 4894.2 |
| 30° | 2614.8 | 2486.8 | 2381.0 | 2261.3 | 2381.0 | 3313.4 | 4131.6 | 4865.0 | 5136.4 | 5189.3 |
| 32.5° | 2506.3 | 2407.5 | 2344.8 | 2269.7 | 2326.7 | 3284.2 | 4249.9 | 5133.6 | 5470.4 | 5516.3 |
| 35° | 2397.7 | 2326.7 | 2298.9 | 2285.0 | 2254.4 | 3177.0 | 4346.0 | 5405.0 | 5851.7 | 5892.0 |
| 37.5° | 2296.1 | 2243.3 | 2234.9 | 2250.2 | 2143.1 | 3001.7 | 4457.3 | 5750.1 | 6226.0 | 6287.2 |
| 40° | 2201.5 | 2152.8 | 2151.4 | 2148.6 | 2020.6 | 2762.3 | 4607.6 | 6100.8 | 6594.8 | 6622.6 |
| 42.5° | 2113.8 | 2052.6 | 2063.7 | 2030.3 | 1920.4 | 2503.5 | 4749.5 | 6399.9 | 6938.5 | 6958.0 |
| 45° | 2035.9 | 1955.2 | 1967.7 | 1926.0 | 1873.1 | 2232.1 | 4874.8 | 6753.4 | 7374.1 | 7386.6 |
| 47.5° | 1960.8 | 1874.5 | 1839.7 | 1836.9 | 1864.7 | 1981.6 | 4997.2 | 7433.9 | 8055.9 | 8078.2 |
| 50° | 1891.2 | 1797.9 | 1699.1 | 1760.4 | 1813.2 | 1793.8 | 5150.3 | 8163.1 | 8760.1 | 8754.5 |
| 52.5° | 1824.4 | 1701.9 | 1561.4 | 1679.7 | 1679.7 | 1654.6 | 5107.2 | 8605.6 | 9341.8 | 9437.8 |
| 55° | 1747.8 | 1547.5 | 1418.0 | 1544.7 | 1483.4 | 1529.4 | 4343.2 | 8750.4 | 9707.8 | 9844.1 |
| 57.5° | 1596.2 | 1356.8 | 1244.1 | 1312.3 | 1220.4 | 1418.0 | 3120.0 | 8032.3 | 9085.7 | 9327.9 |
| 60° | 1450.0 | 1216.3 | 1142.5 | 1130.0 | 1010.3 | 1156.4 | 2022.0 | 6288.6 | 7478.4 | 7600.9 |
| 62.5° | 1278.9 | 1095.2 | 1032.6 | 936.5 | 812.7 | 841.9 | 1224.6 | 4138.6 | 5025.1 | 5052.9 |
| 65° | 1149.5 | 992.2 | 872.5 | 758.4 | 665.2 | 610.9 | 723.6 | 1995.5 | 2511.8 | 2478.4 |
| 67.5° | 986.6 | 850.3 | 736.2 | 654.0 | 577.5 | 509.3 | 481.5 | 592.8 | 670.7 | 648.5 |
| 70° | 878.1 | 747.3 | 637.4 | 559.4 | 488.5 | 420.3 | 371.6 | 349.3 | 342.3 | 336.8 |
| 72.5° | 757.0 | 642.9 | 528.8 | 453.7 | 386.9 | 324.2 | 279.7 | 253.3 | 246.3 | 240.7 |
| 75° | 604.0 | 496.8 | 392.4 | 321.5 | 263.0 | 218.5 | 189.3 | 167.0 | 162.8 | 157.3 |
| 77.5° | 399.4 | 318.7 | 233.8 | 190.6 | 155.9 | 132.2 | 112.7 | 98.8 | 96.0 | 93.2 |
| 80° | 219.9 | 183.7 | 143.3 | 115.5 | 93.2 | 80.7 | 73.8 | 65.4 | 64.0 | 62.6 |
| 82.5° | 130.8 | 109.9 | 82.1 | 65.4 | 54.3 | 48.7 | 44.5 | 40.4 | 39.0 | 37.6 |
| 85° | 65.4 | 51.5 | 36.2 | 30.6 | 27.8 | 25.0 | 25.0 | 20.9 | 19.5 | 19.5 |
| 87.5° | 16.7 | 13.9 | 8.3 | 7.0 | 7.0 | 7.0 | 5.6 | 4.2 | 4.2 | 2.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW, INVUE, LUMARK AND STREETWORKS

DATA VALID FOR LUMINIAIRES UTILIZING SA LIGHT ENGINES

Report Number: SP1-2101-121-2

Luminaire Tested: IFLD-S-SA2A-740-U-T3R-HSS

Test Date: 03/05/2021

Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/05/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

Spectral Parameters

| | | | | | |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K): | 3905 | CRI (Ra): | 71.2 | R9: | -29.7 |
| CIE u': | 0.2273 | R1: | 68.9 | R10: | 46.2 |
| CIE v': | 0.5024 | R2: | 77.0 | R11: | 68.8 |
| Duv: | -0.0008 | R3: | 84.0 | R12: | 45.6 |
| CIE x: | 0.3841 | R4: | 71.6 | R13: | 69.5 |
| CIE y: | 0.3774 | R5: | 68.9 | R14: | 90.7 |
| CIE z: | 0.2385 | R6: | 68.3 | | |
| Peak Wavelength (nm): | 443 | R7: | 78.7 | | |
| Dominant Wavelength (nm): | 579 | R8: | 52.2 | | |
| Purity: | 28.7 | | | | |
| Rf: | 71.7 | | | | |
| Rg: | 96.9 | | | | |



Test Conditions


Stabilization Time: 211M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.8/312%
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-2


| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-121-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 2.7 | 620 | 97577 | 25.4 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 4.8 | 625 | 90158 | 19.9 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 8.0 | 630 | 82240 | 14.9 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 13.3 | 635 | 74361 | 11.2 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 20.2 | 640 | 66994 | 8.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 28.5 | 645 | 60405 | 5.8 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 37.4 | 650 | 53806 | 3.9 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 44.9 | 655 | 47610 | 2.7 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 52.6 | 660 | 42018 | 1.8 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 58.4 | 665 | 36742 | 1.2 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.0 | 540 | 96845 | 63.1 | 670 | 32105 | 0.7 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.0 | 545 | 100829 | 67.1 | 675 | 27946 | 0.5 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 0.1 | 550 | 105648 | 71.8 | 680 | 24146 | 0.3 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 0.2 | 555 | 110017 | 75.1 | 685 | 21191 | 0.2 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 0.5 | 560 | 114586 | 77.9 | 690 | 18544 | 0.1 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 1.2 | 565 | 118987 | 79.1 | 695 | 16058 | 0.1 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 2.1 | 570 | 122326 | 79.5 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 2.9 | 575 | 125968 | 78.4 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 2.7 | 580 | 127613 | 75.8 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 2.0 | 585 | 129466 | 71.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 1.5 | 590 | 128813 | 66.6 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 1.3 | 595 | 126387 | 59.9 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 1.0 | 600 | 123477 | 53.2 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 1.1 | 605 | 118718 | 46.0 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 1.2 | 610 | 112091 | 38.5 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 1.7 | 615 | 105039 | 31.7 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: 10425.8 S/P: 1.47

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 29.3 | 620 | 97577 | 1.2 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 43.0 | 625 | 90158 | 0.8 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 60.8 | 630 | 82240 | 0.5 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 81.1 | 635 | 74361 | 0.3 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 99.6 | 640 | 66994 | 0.2 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 113.9 | 645 | 60405 | 0.1 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 122.6 | 650 | 53806 | 0.1 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 125.0 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 123.1 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.1 | 535 | 94097 | 117.3 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 107.0 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.9 | 545 | 100829 | 96.7 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 3.0 | 550 | 105648 | 86.4 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 9.3 | 555 | 110017 | 75.2 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 23.0 | 560 | 114586 | 64.0 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 45.7 | 565 | 118987 | 53.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 75.5 | 570 | 122326 | 43.2 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 93.8 | 575 | 125968 | 34.3 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 79.3 | 580 | 127613 | 26.3 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 51.3 | 585 | 129466 | 19.8 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 35.6 | 590 | 128813 | 14.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 26.0 | 595 | 126387 | 10.1 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 19.3 | 600 | 123477 | 7.0 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 16.8 | 605 | 118718 | 4.7 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 17.7 | 610 | 112091 | 3.0 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 21.4 | 615 | 105039 | 1.9 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Melanopic Flux vs. Wavelength




Melanopic Lumens: 3927.2 M/P: 0.55





| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 15.8 | 620 | 97577 | 0.1 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 22.0 | 625 | 90158 | 0.0 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 29.2 | 630 | 82240 | 0.0 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 36.6 | 635 | 74361 | 0.0 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 42.2 | 640 | 66994 | 0.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 44.9 | 645 | 60405 | 0.0 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 44.9 | 650 | 53806 | 0.0 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 42.4 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 38.6 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 33.9 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 28.3 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.6 | 545 | 100829 | 23.4 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 2.1 | 550 | 105648 | 19.0 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 5.9 | 555 | 110017 | 14.8 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 14.3 | 560 | 114586 | 11.3 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 27.3 | 565 | 118987 | 8.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 45.1 | 570 | 122326 | 6.0 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 55.3 | 575 | 125968 | 4.2 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 47.2 | 580 | 127613 | 2.9 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 30.8 | 585 | 129466 | 1.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 21.7 | 590 | 128813 | 1.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 16.1 | 595 | 126387 | 0.8 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 12.0 | 600 | 123477 | 0.5 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 10.3 | 605 | 118718 | 0.3 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 10.5 | 610 | 112091 | 0.2 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 12.1 | 615 | 105039 | 0.1 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

Summary

$R_f = 71.7$
 $R_g = 96.9$
 CIE $R_a = 71.2$
 $R_g = -29.7$



Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)


| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)