

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P639753

Luminaire Tested: GWS-SA5C-740-U-T2-W-GRSBK

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P639753  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-20)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA5C-740-U-T2-W-GRSBK  
Description: GALLEON WALL SLIM LUMINAIRE. (5) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK  
Light Source: (80) 4000K CCT, 70 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 14144.6 lumens  
Efficiency: N/A  
Efficacy: 89.8 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
IES Classification: Type II - Short  
BUG Rating: B2 - U0 - G1  
  
Input Watts (W): 157.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P639753  
 CATALOG NUMBER: GWS-SA5C-740-U-T2-W-GRSBK

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 11 fc  
 Type II - Short - N/A

REPORT NUMBER: P639753  
CATALOG NUMBER: GWS-SA5C-740-U-T2-W-GRSBK

### Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral    - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P639753  
 CATALOG NUMBER: GWS-SA5C-740-U-T2-W-GRSBK


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 2310.5   | 0.0    | 2310.5  |
|                    | % Fixture | 16.3     | 0.0    | 16.3    |
| <b>Street Side</b> | Lumens    | 11834.1  | 0.0    | 11834.1 |
|                    | % Fixture | 83.7     | 0.0    | 83.7    |
| <b>Total</b>       | Lumens    | 14144.6  | 0.0    | 14144.6 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 240.1   | 1.7       |
| 10°-20°   | 779.8   | 5.5       |
| 20°-30°   | 1428.0  | 10.1      |
| 30°-40°   | 2369.2  | 16.8      |
| 40°-50°   | 3618.4  | 25.6      |
| 50°-60°   | 4065.9  | 28.7      |
| 60°-70°   | 1499.7  | 10.6      |
| 70°-80°   | 143.3   | 1.0       |
| 80°-90°   | 0.1     | 0.0       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 14144.6 | 100.0     |
| 0°-180°   | 14144.6 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P639753

CATALOG NUMBER: GWS-SA5C-740-U-T2-W-GRSBK

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 1650.6 | 11.7      |                         |      |         |
| FM (30°-60°)   | 8780.3 | 62.1      |                         |      |         |
| FH (60°-80°)   | 1403.1 | 9.9       |                         |      | G1/1800 |
| FVH (80°-90°)  | 0.1    | 0.0       |                         |      | G0/10   |
| BL (0°-30°)    | 797.3  | 5.6       | B2/1000                 |      |         |
| BM (30°-60°)   | 1273.2 | 9.0       | B2/2500                 |      |         |
| BH (60°-80°)   | 239.9  | 1.7       | B1/500                  |      | G1/500  |
| BVH (80°-90°)  | 0.1    | 0.0       |                         |      | G0/10   |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G1**  
 Type II Short





REPORT NUMBER: P639753

CATALOG NUMBER: GWS-SA5C-740-U-T2-W-GRSBK

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°     | 76°     | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|---------|---------|--------|
| 0°    | 2359.1 | 2359.1 | 2359.1 | 2359.1 | 2359.1 | 2359.1 | 2359.1 | 2359.1 | 2359.1  | 2359.1  | 2359.1 |
| 2.5°  | 2635.7 | 2663.0 | 2654.4 | 2637.4 | 2627.1 | 2591.3 | 2569.1 | 2504.2 | 2458.1  | 2453.0  | 2410.3 |
| 5°    | 2968.5 | 2963.4 | 2956.6 | 2936.1 | 2919.0 | 2862.7 | 2796.1 | 2686.9 | 2589.6  | 2577.6  | 2487.1 |
| 7.5°  | 3151.2 | 3154.6 | 3158.0 | 3154.6 | 3142.7 | 3100.0 | 3026.6 | 2898.5 | 2750.0  | 2739.8  | 2596.4 |
| 10°   | 3226.3 | 3233.1 | 3250.2 | 3282.6 | 3311.6 | 3308.2 | 3265.6 | 3134.1 | 2951.5  | 2934.4  | 2741.5 |
| 12.5° | 3262.1 | 3270.7 | 3298.0 | 3359.4 | 3438.0 | 3499.4 | 3506.2 | 3388.5 | 3187.0  | 3159.7  | 2913.9 |
| 15°   | 3311.6 | 3320.2 | 3354.3 | 3434.6 | 3548.9 | 3670.1 | 3748.6 | 3673.5 | 3448.2  | 3419.2  | 3103.4 |
| 17.5° | 3333.8 | 3345.8 | 3395.3 | 3501.1 | 3649.6 | 3835.7 | 4013.2 | 4006.4 | 3757.2  | 3735.0  | 3323.6 |
| 20°   | 3376.5 | 3385.1 | 3429.4 | 3543.8 | 3723.0 | 3991.0 | 4289.8 | 4397.3 | 4134.4  | 4102.0  | 3589.9 |
| 22.5° | 3511.4 | 3514.8 | 3535.3 | 3607.0 | 3774.3 | 4103.7 | 4571.4 | 4853.1 | 4580.0  | 4537.3  | 3888.6 |
| 25°   | 3731.6 | 3729.9 | 3738.4 | 3750.4 | 3873.3 | 4218.1 | 4842.9 | 5366.9 | 5090.4  | 5044.3  | 4226.6 |
| 27.5° | 4011.5 | 4011.5 | 4032.0 | 3997.9 | 4047.4 | 4359.8 | 5110.9 | 5957.6 | 5684.4  | 5619.6  | 4597.0 |
| 30°   | 4341.0 | 4339.3 | 4387.1 | 4332.5 | 4347.8 | 4583.4 | 5399.4 | 6601.1 | 6401.4  | 6321.2  | 5023.8 |
| 32.5° | 4788.2 | 4778.0 | 4832.6 | 4757.5 | 4706.3 | 4921.4 | 5751.0 | 7273.7 | 7260.0  | 7137.1  | 5559.8 |
| 35°   | 5353.3 | 5336.2 | 5353.3 | 5279.9 | 5187.7 | 5394.2 | 6211.9 | 7944.5 | 8212.5  | 8082.8  | 6198.2 |
| 37.5° | 5914.9 | 5969.5 | 5988.3 | 5862.0 | 5786.8 | 5993.4 | 6766.7 | 8545.4 | 9122.4  | 8987.5  | 6862.3 |
| 40°   | 6577.2 | 6560.1 | 6625.0 | 6483.3 | 6435.5 | 6664.3 | 7309.5 | 8992.7 | 9842.8  | 9714.7  | 7452.9 |
| 42.5° | 7065.4 | 7096.1 | 7176.4 | 7097.9 | 7060.3 | 7275.4 | 7765.3 | 9253.8 | 10342.9 | 10216.6 | 7874.6 |
| 45°   | 7650.9 | 7673.1 | 7703.8 | 7639.0 | 7599.7 | 7811.4 | 8094.8 | 9368.2 | 10723.6 | 10587.0 | 8157.9 |
| 47.5° | 8284.2 | 8301.3 | 8301.3 | 8168.2 | 8041.8 | 8128.9 | 8315.0 | 9433.1 | 11073.5 | 10942.1 | 8367.9 |
| 50°   | 8738.3 | 8746.8 | 8822.0 | 8728.1 | 8453.2 | 8318.4 | 8415.7 | 9496.2 | 11305.7 | 11182.8 | 8436.2 |
| 52.5° | 8335.5 | 8325.2 | 8572.7 | 8767.3 | 8840.7 | 8572.7 | 8589.8 | 9588.4 | 11418.4 | 11312.5 | 8490.8 |
| 55°   | 7019.3 | 7002.3 | 7350.5 | 7823.3 | 8470.3 | 8813.4 | 8799.8 | 9643.0 | 11543.0 | 11478.1 | 8688.8 |
| 57.5° | 5088.7 | 5059.7 | 5544.4 | 6070.2 | 6918.6 | 7848.9 | 8395.2 | 9612.3 | 11597.6 | 11592.5 | 8919.3 |
| 60°   | 3059.0 | 3035.1 | 3492.6 | 4045.7 | 4701.2 | 5636.6 | 6543.1 | 8610.3 | 10867.0 | 10877.2 | 8320.1 |
| 62.5° | 1882.9 | 1905.1 | 2318.2 | 2599.8 | 2843.9 | 3125.6 | 3649.6 | 5792.0 | 8050.4  | 8117.0  | 5846.6 |
| 65°   | 1266.6 | 1283.7 | 1666.1 | 2021.1 | 2021.1 | 1652.4 | 1418.5 | 2768.8 | 4294.9  | 4182.2  | 2765.4 |
| 67.5° | 850.1  | 868.9  | 1171.0 | 1585.8 | 1645.6 | 1152.2 | 575.3  | 826.2  | 1196.6  | 1160.8  | 684.5  |
| 70°   | 500.2  | 520.6  | 780.1  | 1087.4 | 1198.3 | 802.3  | 384.1  | 349.9  | 339.7   | 329.5   | 266.3  |
| 72.5° | 223.6  | 232.2  | 397.7  | 553.1  | 505.3  | 338.0  | 271.4  | 280.0  | 264.6   | 259.5   | 216.8  |
| 75°   | 68.3   | 71.7   | 102.4  | 119.5  | 121.2  | 121.2  | 163.9  | 220.2  | 208.3   | 210.0   | 167.3  |
| 77.5° | 17.1   | 17.1   | 27.3   | 25.6   | 13.7   | 11.9   | 30.7   | 49.5   | 51.2    | 46.1    | 34.1   |
| 80°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 1.7    | 1.7    | 1.7    | 1.7     | 1.7     | 1.7    |
| 82.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0    |



REPORT NUMBER: P639753

CATALOG NUMBER: GWS-SA5C-740-U-T2-W-GRSBK

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 2359.1 | 2359.1 | 2359.1 | 2359.1 | 2359.1 | 2359.1 | 2359.1 | 2359.1 | 2359.1 | 2359.1 | 2359.1 |
| 2.5°  | 2391.6 | 2347.2 | 2318.2 | 2277.2 | 2248.2 | 2217.4 | 2190.1 | 2167.9 | 2156.0 | 2152.6 | 2154.3 |
| 5°    | 2446.2 | 2376.2 | 2307.9 | 2229.4 | 2174.8 | 2123.6 | 2082.6 | 2050.1 | 2034.8 | 2029.7 | 2029.7 |
| 7.5°  | 2529.8 | 2432.5 | 2311.3 | 2188.4 | 2096.2 | 2016.0 | 1968.2 | 1932.4 | 1918.7 | 1915.3 | 1905.1 |
| 10°   | 2639.1 | 2505.9 | 2306.2 | 2115.0 | 1985.3 | 1901.6 | 1867.5 | 1857.3 | 1862.4 | 1864.1 | 1862.4 |
| 12.5° | 2770.5 | 2582.7 | 2273.8 | 2007.5 | 1867.5 | 1816.3 | 1819.7 | 1847.0 | 1877.7 | 1893.1 | 1896.5 |
| 15°   | 2910.5 | 2652.7 | 2200.4 | 1879.4 | 1766.8 | 1765.1 | 1814.6 | 1877.7 | 1937.5 | 1963.1 | 1969.9 |
| 17.5° | 3067.5 | 2709.1 | 2087.7 | 1742.9 | 1679.7 | 1729.2 | 1818.0 | 1915.3 | 1995.5 | 2038.2 | 2046.7 |
| 20°   | 3240.0 | 2755.2 | 1944.3 | 1614.9 | 1602.9 | 1691.7 | 1814.6 | 1934.1 | 2033.1 | 2080.9 | 2089.4 |
| 22.5° | 3419.2 | 2787.6 | 1778.7 | 1497.1 | 1532.9 | 1649.0 | 1782.1 | 1898.2 | 1992.1 | 2046.7 | 2053.6 |
| 25°   | 3624.0 | 2791.0 | 1609.7 | 1398.1 | 1468.1 | 1591.0 | 1703.6 | 1799.2 | 1877.7 | 1925.5 | 1930.7 |
| 27.5° | 3803.3 | 2750.0 | 1459.5 | 1317.8 | 1408.3 | 1519.3 | 1594.4 | 1647.3 | 1701.9 | 1729.2 | 1730.9 |
| 30°   | 4009.8 | 2678.3 | 1317.8 | 1253.0 | 1346.9 | 1430.5 | 1468.1 | 1480.0 | 1485.1 | 1490.2 | 1483.4 |
| 32.5° | 4255.6 | 2591.3 | 1212.0 | 1189.8 | 1276.9 | 1333.2 | 1343.4 | 1319.5 | 1290.5 | 1249.5 | 1239.3 |
| 35°   | 4557.8 | 2512.8 | 1124.9 | 1128.4 | 1200.0 | 1234.2 | 1225.7 | 1174.4 | 1118.1 | 1068.6 | 1060.1 |
| 37.5° | 4885.5 | 2446.2 | 1058.4 | 1068.6 | 1116.4 | 1140.3 | 1114.7 | 1058.4 | 1032.8 | 990.1  | 991.8  |
| 40°   | 5175.7 | 2391.6 | 998.6  | 1008.9 | 1031.0 | 1053.2 | 1012.3 | 974.7  | 1022.5 | 1019.1 | 1022.5 |
| 42.5° | 5382.3 | 2345.5 | 947.4  | 942.3  | 957.6  | 973.0  | 942.3  | 923.5  | 1003.7 | 981.5  | 993.5  |
| 45°   | 5503.5 | 2302.8 | 904.7  | 874.0  | 897.9  | 925.2  | 904.7  | 880.8  | 908.1  | 805.7  | 797.2  |
| 47.5° | 5585.4 | 2278.9 | 867.2  | 807.4  | 850.1  | 897.9  | 855.2  | 797.2  | 757.9  | 669.2  | 662.3  |
| 50°   | 5594.0 | 2266.9 | 822.8  | 739.1  | 793.8  | 845.0  | 795.5  | 715.2  | 658.9  | 619.7  | 614.5  |
| 52.5° | 5638.3 | 2290.8 | 761.3  | 652.1  | 711.8  | 793.8  | 759.6  | 679.4  | 602.6  | 568.4  | 561.6  |
| 55°   | 5836.4 | 2391.6 | 658.9  | 532.6  | 619.7  | 754.5  | 730.6  | 606.0  | 532.6  | 512.1  | 507.0  |
| 57.5° | 6041.2 | 2412.0 | 518.9  | 421.6  | 539.4  | 698.2  | 667.5  | 558.2  | 486.5  | 462.6  | 457.5  |
| 60°   | 5524.0 | 1987.0 | 389.2  | 348.2  | 476.3  | 645.3  | 617.9  | 529.2  | 445.5  | 416.5  | 411.4  |
| 62.5° | 3629.2 | 1073.7 | 309.0  | 295.3  | 401.2  | 546.3  | 563.3  | 478.0  | 397.7  | 367.0  | 365.3  |
| 65°   | 1672.9 | 498.5  | 237.3  | 233.9  | 314.1  | 435.3  | 484.8  | 418.2  | 336.3  | 309.0  | 309.0  |
| 67.5° | 455.8  | 247.5  | 186.1  | 172.4  | 213.4  | 291.9  | 353.4  | 312.4  | 239.0  | 206.6  | 204.8  |
| 70°   | 227.0  | 199.7  | 167.3  | 148.5  | 153.6  | 180.9  | 208.3  | 174.1  | 121.2  | 99.0   | 97.3   |
| 72.5° | 186.1  | 163.9  | 141.7  | 126.3  | 116.1  | 111.0  | 107.5  | 87.1   | 56.3   | 42.7   | 41.0   |
| 75°   | 138.3  | 117.8  | 100.7  | 81.9   | 70.0   | 64.9   | 58.0   | 42.7   | 23.9   | 13.7   | 11.9   |
| 77.5° | 30.7   | 29.0   | 27.3   | 20.5   | 18.8   | 15.4   | 11.9   | 8.5    | 3.4    | 0.0    | 0.0    |
| 80°   | 1.7    | 1.7    | 1.7    | 1.7    | 1.7    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 82.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW, INVUE, LUMARK AND STREETWORKS

DATA VALID FOR LUMINAIRES UTILIZING SA LIGHT ENGINES

Report Number: SP1-2101-121-2

Luminaire Tested: IFLD-S-SA2A-740-U-T3R-HSS

Test Date: 03/05/2021

**Test Information**

Test Method: LM-79-08  
 Report Number: SP1-2101-121-2  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry: 4π  
 Issue Date: 03/05/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**  
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

**Spectral Parameters**

|                           |         |           |      |      |       |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K):                  | 3905    | CRI (Ra): | 71.2 | R9:  | -29.7 |
| CIE u':                   | 0.2273  | R1:       | 68.9 | R10: | 46.2  |
| CIE v':                   | 0.5024  | R2:       | 77.0 | R11: | 68.8  |
| Duv:                      | -0.0008 | R3:       | 84.0 | R12: | 45.6  |
| CIE x:                    | 0.3841  | R4:       | 71.6 | R13: | 69.5  |
| CIE y:                    | 0.3774  | R5:       | 68.9 | R14: | 90.7  |
| CIE z:                    | 0.2385  | R6:       | 68.3 |      |       |
| Peak Wavelength (nm):     | 443     | R7:       | 78.7 |      |       |
| Dominant Wavelength (nm): | 579     | R8:       | 52.2 |      |       |
| Purity:                   | 28.7    |           |      |      |       |
| Rf:                       | 71.7    |           |      |      |       |
| Rg:                       | 96.9    |           |      |      |       |



**Test Conditions**

Stabilization Time: 211M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 24.8/312%  
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-2

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2101-121-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

**Photopic Flux vs. Wavelength**



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2304          | 0.0           | 490    | 19043         | 2.7           | 620    | 97577         | 25.4          | 750    | 4830          | 0.0           | 880    | 3505          | 0.0           |
| 365    | 2150          | 0.0           | 495    | 26606         | 4.8           | 625    | 90158         | 19.9          | 755    | 4664          | 0.0           | 885    | 2991          | 0.0           |
| 370    | 2146          | 0.0           | 500    | 36376         | 8.0           | 630    | 82240         | 14.9          | 760    | 4006          | 0.0           | 890    | 2327          | 0.0           |
| 375    | 2332          | 0.0           | 505    | 47714         | 13.3          | 635    | 74361         | 11.2          | 765    | 3715          | 0.0           | 895    | 2775          | 0.0           |
| 380    | 2527          | 0.0           | 510    | 58741         | 20.2          | 640    | 66994         | 8.0           | 770    | 3696          | 0.0           | 900    | 2141          | 0.0           |
| 385    | 2304          | 0.0           | 515    | 68716         | 28.5          | 645    | 60405         | 5.8           | 775    | 3117          | 0.0           | 905    | 2421          | 0.0           |
| 390    | 2064          | 0.0           | 520    | 77136         | 37.4          | 650    | 53806         | 3.9           | 780    | 3062          | 0.0           | 910    | 2200          | 0.0           |
| 395    | 1856          | 0.0           | 525    | 83567         | 44.9          | 655    | 47610         | 2.7           | 785    | 2907          | 0.0           | 915    | 2716          | 0.0           |
| 400    | 1856          | 0.0           | 530    | 89283         | 52.6          | 660    | 42018         | 1.8           | 790    | 2655          | 0.0           | 920    | 2656          | 0.0           |
| 405    | 2374          | 0.0           | 535    | 94097         | 58.4          | 665    | 36742         | 1.2           | 795    | 2467          | 0.0           | 925    | 2671          | 0.0           |
| 410    | 4084          | 0.0           | 540    | 96845         | 63.1          | 670    | 32105         | 0.7           | 800    | 2609          | 0.0           | 930    | 3292          | 0.0           |
| 415    | 8543          | 0.0           | 545    | 100829        | 67.1          | 675    | 27946         | 0.5           | 805    | 2293          | 0.0           | 935    | 3188          | 0.0           |
| 420    | 18394         | 0.1           | 550    | 105648        | 71.8          | 680    | 24146         | 0.3           | 810    | 2188          | 0.0           | 940    | 1997          | 0.0           |
| 425    | 37987         | 0.2           | 555    | 110017        | 75.1          | 685    | 21191         | 0.2           | 815    | 2386          | 0.0           | 945    | 2623          | 0.0           |
| 430    | 67605         | 0.5           | 560    | 114586        | 77.9          | 690    | 18544         | 0.1           | 820    | 2712          | 0.0           | 950    | 2969          | 0.0           |
| 435    | 102160        | 1.2           | 565    | 118987        | 79.1          | 695    | 16058         | 0.1           | 825    | 2473          | 0.0           | 955    | 2277          | 0.0           |
| 440    | 135103        | 2.1           | 570    | 122326        | 79.5          | 700    | 14133         | 0.0           | 830    | 1969          | 0.0           | 960    | 4267          | 0.0           |
| 445    | 140126        | 2.9           | 575    | 125968        | 78.4          | 705    | 12309         | 0.0           | 835    | 1917          | 0.0           | 965    | 2034          | 0.0           |
| 450    | 102339        | 2.7           | 580    | 127613        | 75.8          | 710    | 11142         | 0.0           | 840    | 2248          | 0.0           | 970    | 3586          | 0.0           |
| 455    | 58751         | 2.0           | 585    | 129466        | 71.9          | 715    | 10143         | 0.0           | 845    | 2266          | 0.0           | 975    | 2505          | 0.0           |
| 460    | 36892         | 1.5           | 590    | 128813        | 66.6          | 720    | 9072          | 0.0           | 850    | 2558          | 0.0           | 980    | 2666          | 0.0           |
| 465    | 24637         | 1.3           | 595    | 126387        | 59.9          | 725    | 8130          | 0.0           | 855    | 2767          | 0.0           | 985    | 2934          | 0.0           |
| 470    | 16738         | 1.0           | 600    | 123477        | 53.2          | 730    | 7149          | 0.0           | 860    | 2826          | 0.0           | 990    | 4120          | 0.0           |
| 475    | 13456         | 1.1           | 605    | 118718        | 46.0          | 735    | 6311          | 0.0           | 865    | 2385          | 0.0           | 995    | 3858          | 0.0           |
| 480    | 13081         | 1.2           | 610    | 112091        | 38.5          | 740    | 5711          | 0.0           | 870    | 3194          | 0.0           | 1000   | 3405          | 0.0           |
| 485    | 14734         | 1.7           | 615    | 105039        | 31.7          | 745    | 5111          | 0.0           | 875    | 3189          | 0.0           |        |               |               |

REPORT NUMBER: SP1-2101-121-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: 10425.8 S/P: 1.47

| λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2304          | 0.0           | 490    | 19043         | 29.3          | 620    | 97577         | 1.2           | 750    | 4830          | 0.0           | 880    | 3505          | 0.0           |
| 365    | 2150          | 0.0           | 495    | 26606         | 43.0          | 625    | 90158         | 0.8           | 755    | 4664          | 0.0           | 885    | 2991          | 0.0           |
| 370    | 2146          | 0.0           | 500    | 36376         | 60.8          | 630    | 82240         | 0.5           | 760    | 4006          | 0.0           | 890    | 2327          | 0.0           |
| 375    | 2332          | 0.0           | 505    | 47714         | 81.1          | 635    | 74361         | 0.3           | 765    | 3715          | 0.0           | 895    | 2775          | 0.0           |
| 380    | 2527          | 0.0           | 510    | 58741         | 99.6          | 640    | 66994         | 0.2           | 770    | 3696          | 0.0           | 900    | 2141          | 0.0           |
| 385    | 2304          | 0.0           | 515    | 68716         | 113.9         | 645    | 60405         | 0.1           | 775    | 3117          | 0.0           | 905    | 2421          | 0.0           |
| 390    | 2064          | 0.0           | 520    | 77136         | 122.6         | 650    | 53806         | 0.1           | 780    | 3062          | 0.0           | 910    | 2200          | 0.0           |
| 395    | 1856          | 0.0           | 525    | 83567         | 125.0         | 655    | 47610         | 0.0           | 785    | 2907          | 0.0           | 915    | 2716          | 0.0           |
| 400    | 1856          | 0.0           | 530    | 89283         | 123.1         | 660    | 42018         | 0.0           | 790    | 2655          | 0.0           | 920    | 2656          | 0.0           |
| 405    | 2374          | 0.1           | 535    | 94097         | 117.3         | 665    | 36742         | 0.0           | 795    | 2467          | 0.0           | 925    | 2671          | 0.0           |
| 410    | 4084          | 0.2           | 540    | 96845         | 107.0         | 670    | 32105         | 0.0           | 800    | 2609          | 0.0           | 930    | 3292          | 0.0           |
| 415    | 8543          | 0.9           | 545    | 100829        | 96.7          | 675    | 27946         | 0.0           | 805    | 2293          | 0.0           | 935    | 3188          | 0.0           |
| 420    | 18394         | 3.0           | 550    | 105648        | 86.4          | 680    | 24146         | 0.0           | 810    | 2188          | 0.0           | 940    | 1997          | 0.0           |
| 425    | 37987         | 9.3           | 555    | 110017        | 75.2          | 685    | 21191         | 0.0           | 815    | 2386          | 0.0           | 945    | 2623          | 0.0           |
| 430    | 67605         | 23.0          | 560    | 114586        | 64.0          | 690    | 18544         | 0.0           | 820    | 2712          | 0.0           | 950    | 2969          | 0.0           |
| 435    | 102160        | 45.7          | 565    | 118987        | 53.4          | 695    | 16058         | 0.0           | 825    | 2473          | 0.0           | 955    | 2277          | 0.0           |
| 440    | 135103        | 75.5          | 570    | 122326        | 43.2          | 700    | 14133         | 0.0           | 830    | 1969          | 0.0           | 960    | 4267          | 0.0           |
| 445    | 140126        | 93.8          | 575    | 125968        | 34.3          | 705    | 12309         | 0.0           | 835    | 1917          | 0.0           | 965    | 2034          | 0.0           |
| 450    | 102339        | 79.3          | 580    | 127613        | 26.3          | 710    | 11142         | 0.0           | 840    | 2248          | 0.0           | 970    | 3586          | 0.0           |
| 455    | 58751         | 51.3          | 585    | 129466        | 19.8          | 715    | 10143         | 0.0           | 845    | 2266          | 0.0           | 975    | 2505          | 0.0           |
| 460    | 36892         | 35.6          | 590    | 128813        | 14.3          | 720    | 9072          | 0.0           | 850    | 2558          | 0.0           | 980    | 2666          | 0.0           |
| 465    | 24637         | 26.0          | 595    | 126387        | 10.1          | 725    | 8130          | 0.0           | 855    | 2767          | 0.0           | 985    | 2934          | 0.0           |
| 470    | 16738         | 19.3          | 600    | 123477        | 7.0           | 730    | 7149          | 0.0           | 860    | 2826          | 0.0           | 990    | 4120          | 0.0           |
| 475    | 13456         | 16.8          | 605    | 118718        | 4.7           | 735    | 6311          | 0.0           | 865    | 2385          | 0.0           | 995    | 3858          | 0.0           |
| 480    | 13081         | 17.7          | 610    | 112091        | 3.0           | 740    | 5711          | 0.0           | 870    | 3194          | 0.0           | 1000   | 3405          | 0.0           |
| 485    | 14734         | 21.4          | 615    | 105039        | 1.9           | 745    | 5111          | 0.0           | 875    | 3189          | 0.0           |        |               |               |

REPORT NUMBER: SP1-2101-121-2

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 3927.2 M/P: 0.55**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2304          | 0.0           | 490    | 19043         | 15.8          | 620    | 97577         | 0.1           | 750    | 4830          | 0.0           | 880    | 3505          | 0.0           |
| 365    | 2150          | 0.0           | 495    | 26606         | 22.0          | 625    | 90158         | 0.0           | 755    | 4664          | 0.0           | 885    | 2991          | 0.0           |
| 370    | 2146          | 0.0           | 500    | 36376         | 29.2          | 630    | 82240         | 0.0           | 760    | 4006          | 0.0           | 890    | 2327          | 0.0           |
| 375    | 2332          | 0.0           | 505    | 47714         | 36.6          | 635    | 74361         | 0.0           | 765    | 3715          | 0.0           | 895    | 2775          | 0.0           |
| 380    | 2527          | 0.0           | 510    | 58741         | 42.2          | 640    | 66994         | 0.0           | 770    | 3696          | 0.0           | 900    | 2141          | 0.0           |
| 385    | 2304          | 0.0           | 515    | 68716         | 44.9          | 645    | 60405         | 0.0           | 775    | 3117          | 0.0           | 905    | 2421          | 0.0           |
| 390    | 2064          | 0.0           | 520    | 77136         | 44.9          | 650    | 53806         | 0.0           | 780    | 3062          | 0.0           | 910    | 2200          | 0.0           |
| 395    | 1856          | 0.0           | 525    | 83567         | 42.4          | 655    | 47610         | 0.0           | 785    | 2907          | 0.0           | 915    | 2716          | 0.0           |
| 400    | 1856          | 0.0           | 530    | 89283         | 38.6          | 660    | 42018         | 0.0           | 790    | 2655          | 0.0           | 920    | 2656          | 0.0           |
| 405    | 2374          | 0.0           | 535    | 94097         | 33.9          | 665    | 36742         | 0.0           | 795    | 2467          | 0.0           | 925    | 2671          | 0.0           |
| 410    | 4084          | 0.2           | 540    | 96845         | 28.3          | 670    | 32105         | 0.0           | 800    | 2609          | 0.0           | 930    | 3292          | 0.0           |
| 415    | 8543          | 0.6           | 545    | 100829        | 23.4          | 675    | 27946         | 0.0           | 805    | 2293          | 0.0           | 935    | 3188          | 0.0           |
| 420    | 18394         | 2.1           | 550    | 105648        | 19.0          | 680    | 24146         | 0.0           | 810    | 2188          | 0.0           | 940    | 1997          | 0.0           |
| 425    | 37987         | 5.9           | 555    | 110017        | 14.8          | 685    | 21191         | 0.0           | 815    | 2386          | 0.0           | 945    | 2623          | 0.0           |
| 430    | 67605         | 14.3          | 560    | 114586        | 11.3          | 690    | 18544         | 0.0           | 820    | 2712          | 0.0           | 950    | 2969          | 0.0           |
| 435    | 102160        | 27.3          | 565    | 118987        | 8.4           | 695    | 16058         | 0.0           | 825    | 2473          | 0.0           | 955    | 2277          | 0.0           |
| 440    | 135103        | 45.1          | 570    | 122326        | 6.0           | 700    | 14133         | 0.0           | 830    | 1969          | 0.0           | 960    | 4267          | 0.0           |
| 445    | 140126        | 55.3          | 575    | 125968        | 4.2           | 705    | 12309         | 0.0           | 835    | 1917          | 0.0           | 965    | 2034          | 0.0           |
| 450    | 102339        | 47.2          | 580    | 127613        | 2.9           | 710    | 11142         | 0.0           | 840    | 2248          | 0.0           | 970    | 3586          | 0.0           |
| 455    | 58751         | 30.8          | 585    | 129466        | 1.9           | 715    | 10143         | 0.0           | 845    | 2266          | 0.0           | 975    | 2505          | 0.0           |
| 460    | 36892         | 21.7          | 590    | 128813        | 1.3           | 720    | 9072          | 0.0           | 850    | 2558          | 0.0           | 980    | 2666          | 0.0           |
| 465    | 24637         | 16.1          | 595    | 126387        | 0.8           | 725    | 8130          | 0.0           | 855    | 2767          | 0.0           | 985    | 2934          | 0.0           |
| 470    | 16738         | 12.0          | 600    | 123477        | 0.5           | 730    | 7149          | 0.0           | 860    | 2826          | 0.0           | 990    | 4120          | 0.0           |
| 475    | 13456         | 10.3          | 605    | 118718        | 0.3           | 735    | 6311          | 0.0           | 865    | 2385          | 0.0           | 995    | 3858          | 0.0           |
| 480    | 13081         | 10.5          | 610    | 112091        | 0.2           | 740    | 5711          | 0.0           | 870    | 3194          | 0.0           | 1000   | 3405          | 0.0           |
| 485    | 14734         | 12.1          | 615    | 105039        | 0.1           | 745    | 5111          | 0.0           | 875    | 3189          | 0.0           |        |               |               |

**Summary**

$R_f = 71.7$   
 $R_g = 96.9$   
 CIE  $R_a = 71.2$   
 $R_g = -29.7$



**Color Vector Graphics**





**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)