

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P642226

Luminaire Tested: GWS-SA6C-740-U-SLR-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P642226
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-41)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA6C-740-U-SLR-W
Description: GALLEON WALL SLIM LUMINAIRE. (6) LIGHTSQUARES WITH 16 LEDS EACH AND
SPILL LIGHT ELIMINATOR RIGHT OPTICS
Light Source: (96) 4000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 26885.4 lumens
Efficiency: N/A
Efficacy: 142.1 lumens/watt
Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')
IES Classification: Type III - Short
BUG Rating: B3 - U0 - G4


Input Watts (W): 189.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P642226
 CATALOG NUMBER: GWS-SA6C-740-U-SLR-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 8.1 fc
 Type III - Short - N/A

REPORT NUMBER: P642226
CATALOG NUMBER: GWS-SA6C-740-U-SLR-W

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P642226

CATALOG NUMBER: GWS-SA6C-740-U-SLR-W

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	6415.4	0.0	6415.4
	% Fixture	23.9	0.0	23.9
Street Side	Lumens	20470.0	0.0	20470.0
	% Fixture	76.1	0.0	76.1
Total	Lumens	26885.4	0.0	26885.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	348.5	1.3
10°-20°	1092.4	4.1
20°-30°	1696.8	6.3
30°-40°	2303.8	8.6
40°-50°	3651.4	13.6
50°-60°	6441.0	24.0
60°-70°	7166.6	26.7
70°-80°	3634.6	13.5
80°-90°	550.4	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	26885.4	100.0
0°-180°	26885.4	100.0

Coefficient of Utilization



REPORT NUMBER: P642226


CATALOG NUMBER: GWS-SA6C-740-U-SLR-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1755.4	6.5			
FM (30°-60°)	9128.8	34.0			
FH (60°-80°)	9168.2	34.1			G4/12000
FVH (80°-90°)	417.7	1.6			G3/500
BL (0°-30°)	1382.3	5.1	B3/2500		
BM (30°-60°)	3267.4	12.2	B3/5000		
BH (60°-80°)	1633.0	6.1	B3/2500		G3/2500
BVH (80°-90°)	132.6	0.5			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G4

Type III Short





REPORT NUMBER: P642226
 CATALOG NUMBER: GWS-SA6C-740-U-SLR-W

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	3568.2	3568.2	3568.2	3568.2	3568.2	3568.2	3568.2	3568.2	3568.2	3568.2	3568.2
2.5°	3834.9	3832.9	3871.5	3930.6	3985.5	4009.9	4050.7	4046.6	4014.0	3971.3	3957.0
5°	4136.1	4144.3	4211.5	4341.7	4486.3	4547.3	4573.8	4563.6	4504.6	4429.3	4297.0
7.5°	4408.9	4423.2	4527.0	4722.4	4901.5	4982.9	5048.1	5035.8	4950.4	4809.9	4614.5
10°	4608.4	4624.7	4748.8	4978.8	5178.3	5249.6	5333.0	5337.1	5261.8	5072.5	4873.0
12.5°	4807.9	4824.1	4940.2	5149.8	5280.1	5282.1	5331.0	5357.5	5361.5	5274.0	5074.5
15°	5015.5	5029.7	5135.6	5253.6	5247.5	5133.5	5133.5	5184.4	5296.4	5359.5	5221.1
17.5°	5192.6	5210.9	5292.3	5253.6	5072.5	4866.9	4842.5	4907.6	5103.0	5345.2	5331.0
20°	5339.1	5353.4	5398.2	5141.7	4811.9	4543.2	4496.4	4571.7	4836.4	5257.7	5414.4
22.5°	5479.6	5487.7	5463.3	4995.1	4531.0	4223.7	4166.7	4246.1	4531.0	5103.0	5485.7
25°	5646.5	5638.4	5522.3	4842.5	4274.6	3971.3	3912.2	4001.8	4299.0	4897.4	5563.0
27.5°	5839.9	5809.3	5573.2	4677.6	4077.1	3784.0	3743.3	3839.0	4115.8	4708.1	5624.1
30°	6004.7	5945.7	5581.4	4531.0	3975.3	3704.6	3680.2	3769.8	4026.2	4579.9	5701.5
32.5°	6187.9	6106.5	5628.2	4492.4	4032.3	3896.0	3928.5	3934.6	4050.7	4543.2	5817.5
35°	6450.5	6344.7	5756.4	4604.3	4618.6	4848.6	4966.6	4807.9	4419.1	4624.7	6037.3
37.5°	6847.4	6713.1	6017.0	5088.8	5829.7	6344.7	6629.6	6267.3	5538.6	4932.0	6369.1
40°	7329.9	7158.9	6350.8	5984.4	6961.4	7785.8	8292.7	7761.4	6690.7	5699.4	6835.2
42.5°	8003.6	7824.5	6998.1	6863.7	8009.7	9237.1	9898.7	9106.9	7706.4	6690.7	7582.3
45°	9178.1	9005.1	8184.8	7745.1	9237.1	11024.3	11952.5	10851.3	8738.4	7686.1	8978.6
47.5°	11347.9	11144.4	9947.5	8722.1	10637.6	13344.8	14643.4	13039.4	9811.1	8826.0	11323.5
50°	13953.4	13758.0	12160.1	9878.3	12184.5	15826.1	17631.6	15610.3	11046.7	10212.1	14126.4
52.5°	17088.1	17051.4	15317.2	11339.8	13794.6	18472.2	20947.4	18458.0	12400.3	12078.7	17301.8
55°	19913.4	20271.6	19327.1	13568.7	15874.9	21796.2	24356.9	21564.1	14236.3	15164.5	21020.7
57.5°	21435.9	22398.7	23850.0	18116.0	18899.7	25769.5	28564.3	25356.3	17391.4	20302.1	24468.8
60°	20430.4	21521.4	24151.3	21539.7	21900.0	28953.0	32036.8	28543.9	20489.4	23868.3	24273.4
62.5°	18757.2	19736.3	22075.1	19540.9	22364.1	29653.2	32118.2	29099.6	21720.9	22058.8	21926.5
65°	16772.6	17759.8	20237.0	17057.5	20888.4	27990.2	29748.9	27465.1	19508.3	19929.6	19978.5
67.5°	14136.6	15048.5	17570.5	15166.6	19040.1	25549.7	26111.5	25136.5	17965.4	18637.1	17934.8
70°	10562.2	11384.6	13611.4	12325.0	16050.0	22370.2	21916.3	22060.8	16233.2	16900.8	14981.3
72.5°	7217.9	7836.7	9746.0	9684.9	12290.4	17908.4	17275.3	18645.2	13558.5	14443.9	11421.2
75°	5048.1	5530.5	7044.9	7651.5	9290.0	13273.5	12302.6	13955.4	10588.7	11852.8	8333.4
77.5°	3098.0	3417.6	4449.6	5668.9	5976.2	9084.5	7641.3	10501.2	7435.7	8644.8	5559.0
80°	1549.0	1703.7	2161.7	3564.2	3963.1	5353.4	4219.6	6096.3	5031.8	5353.4	3075.6
82.5°	468.2	517.0	633.0	1353.6	2053.8	3081.8	2493.5	3541.8	2747.9	2509.8	1211.1
85°	124.2	140.4	175.1	401.0	720.6	1105.3	842.7	1715.9	1317.0	926.2	456.0
87.5°	10.2	10.2	8.1	8.1	4.1	0.0	0.0	122.1	246.3	140.4	79.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P642226
 CATALOG NUMBER: GWS-SA6C-740-U-SLR-W

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3568.2	3568.2	3568.2	3568.2	3568.2	3568.2	3568.2	3568.2	3568.2	3568.2	3568.2
2.5°	3885.8	3877.6	3794.2	3733.1	3661.9	3592.7	3521.4	3458.3	3387.1	3315.8	3295.5
5°	4199.2	4142.3	3965.2	3816.6	3670.0	3541.8	3429.8	3313.8	3220.2	3128.6	3094.0
7.5°	4476.1	4376.3	4119.9	3893.9	3690.4	3531.6	3366.7	3197.8	3065.5	2935.2	2902.6
10°	4726.4	4594.1	4270.5	3985.5	3759.6	3578.4	3385.0	3159.1	2967.8	2809.0	2766.3
12.5°	4911.7	4767.2	4400.8	4073.0	3816.6	3613.0	3421.7	3222.2	3020.7	2815.1	2768.3
15°	5058.2	4907.6	4508.6	4140.2	3818.6	3556.0	3370.8	3301.6	3238.5	3037.0	2951.5
17.5°	5176.3	5017.5	4602.3	4180.9	3763.7	3383.0	3222.2	3324.0	3484.8	3358.6	3197.8
20°	5284.2	5123.4	4673.5	4209.4	3641.5	3144.9	3055.3	3271.1	3513.3	3509.2	3364.7
22.5°	5402.2	5245.5	4777.3	4225.7	3470.5	2902.6	2955.6	3193.7	3391.2	3450.2	3360.6
25°	5552.9	5414.4	4921.9	4262.3	3277.2	2735.7	2882.3	3094.0	3258.8	3273.1	3220.2
27.5°	5727.9	5624.1	5137.6	4347.8	3089.9	2650.2	2796.8	2953.5	3104.1	3110.3	3047.2
30°	5919.3	5850.0	5337.1	4419.1	2949.4	2623.8	2686.9	2813.1	2908.7	2925.0	2870.1
32.5°	6163.5	6102.4	5514.2	4372.3	2866.0	2617.7	2585.1	2650.2	2729.6	2729.6	2686.9
35°	6499.4	6413.9	5701.5	4193.1	2764.2	2593.2	2477.2	2495.5	2530.1	2536.2	2511.8
37.5°	6975.7	6835.2	5890.8	3839.0	2597.3	2505.7	2353.0	2330.7	2342.9	2359.2	2353.0
40°	7566.0	7336.0	6167.6	3413.5	2397.8	2336.8	2224.8	2182.1	2171.9	2204.5	2216.7
42.5°	8308.9	7956.8	6464.8	3016.6	2216.7	2143.4	2074.2	2037.5	2021.3	2076.2	2108.8
45°	9495.6	8915.5	6749.7	2623.8	2114.9	1978.5	1931.7	1905.2	1913.4	1978.5	2019.2
47.5°	11545.4	10379.0	7020.5	2375.4	2106.7	1860.5	1803.5	1809.6	1832.0	1901.2	1950.0
50°	14138.6	12339.2	7201.6	2271.6	2131.2	1789.2	1713.9	1746.5	1781.1	1848.2	1905.2
52.5°	16778.7	14165.1	6985.9	2214.6	2129.1	1791.2	1630.4	1728.1	1744.4	1811.6	1872.7
55°	18594.3	14368.6	6035.3	2127.1	2096.6	1872.7	1565.3	1720.0	1730.2	1791.2	1846.2
57.5°	19286.4	13672.5	4602.3	2151.5	1998.9	1935.8	1536.8	1663.0	1736.3	1789.2	1846.2
60°	18449.8	12359.6	2796.8	2214.6	1842.1	1931.7	1555.1	1559.2	1685.4	1775.0	1832.0
62.5°	16872.3	10674.2	1964.3	2035.5	1728.1	1823.8	1597.9	1437.1	1595.8	1703.7	1754.6
65°	15064.8	8691.6	1498.1	1752.6	1673.2	1656.9	1612.1	1329.2	1473.7	1579.6	1624.3
67.5°	13181.9	6755.8	1217.2	1306.8	1512.4	1498.1	1473.7	1233.5	1329.2	1404.5	1455.4
70°	10810.6	4726.4	1027.9	981.1	1296.6	1343.4	1288.5	1113.4	1144.0	1221.3	1262.0
72.5°	7907.9	2945.4	844.7	810.1	1042.2	1174.5	1146.0	981.1	995.4	1068.6	1101.2
75°	5687.2	1685.4	677.8	667.6	795.9	1005.5	948.5	844.7	861.0	916.0	938.4
77.5°	3615.1	938.4	523.1	537.4	569.9	751.1	810.1	722.6	722.6	755.2	773.5
80°	1935.8	537.4	382.7	388.8	399.0	574.0	639.1	559.8	559.8	537.4	559.8
82.5°	789.8	309.4	262.6	244.3	266.7	392.9	447.8	356.2	372.5	335.9	344.0
85°	260.5	154.7	130.3	128.2	126.2	173.0	215.8	177.1	211.7	134.3	140.4
87.5°	34.6	28.5	16.3	12.2	14.2	6.1	12.2	14.2	14.2	10.2	10.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P642226
 CATALOG NUMBER: GWS-SA6C-740-U-SLR-W

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	3568.2	3568.2	3568.2	3568.2	3568.2	3568.2	3568.2	3568.2	3568.2	3568.2	3568.2
2.5°	3281.2	3265.0	3205.9	3220.2	3210.0	3193.7	3210.0	3179.5	3203.9	3212.0	3262.9
5°	3067.5	3028.8	2971.8	2943.3	2937.2	2921.0	2923.0	2908.7	2912.8	2947.4	3004.4
7.5°	2876.2	2839.5	2794.7	2774.4	2756.1	2737.8	2735.7	2733.7	2750.0	2780.5	2835.5
10°	2737.8	2717.4	2699.1	2707.2	2699.1	2690.9	2676.7	2676.7	2703.2	2758.1	2825.3
12.5°	2737.8	2733.7	2737.8	2762.2	2760.1	2762.2	2743.9	2754.0	2827.3	2921.0	3016.6
15°	2884.3	2851.7	2851.7	2864.0	2859.9	2859.9	2859.9	2902.6	3069.5	3214.1	3315.8
17.5°	3063.4	2967.8	2927.1	2921.0	2918.9	2918.9	2927.1	3018.7	3279.2	3431.9	3490.9
20°	3187.6	3006.4	2939.3	2912.8	2914.8	2918.9	2943.3	3069.5	3356.5	3433.9	3419.6
22.5°	3210.0	2975.9	2894.5	2855.8	2861.9	2866.0	2902.6	3037.0	3250.7	3262.9	3234.4
25°	3106.2	2890.4	2802.9	2772.4	2780.5	2778.5	2811.0	2908.7	3061.4	3057.3	3041.0
27.5°	2951.5	2754.0	2688.9	2668.5	2682.8	2666.5	2676.7	2752.0	2870.1	2866.0	2859.9
30°	2792.7	2621.7	2562.7	2552.5	2570.8	2546.4	2548.5	2611.6	2693.0	2688.9	2686.9
32.5°	2633.9	2489.4	2436.5	2436.5	2454.8	2428.4	2432.4	2487.4	2542.3	2526.1	2526.1
35°	2483.3	2381.5	2338.8	2330.7	2344.9	2326.6	2334.7	2385.6	2406.0	2383.6	2369.3
37.5°	2351.0	2306.2	2263.5	2235.0	2237.0	2239.1	2263.5	2302.2	2289.9	2257.4	2239.1
40°	2228.9	2228.9	2188.2	2135.2	2129.1	2143.4	2184.1	2226.8	2192.2	2155.6	2133.2
42.5°	2141.4	2159.7	2121.0	2068.1	2055.9	2080.3	2125.1	2155.6	2114.9	2074.2	2043.6
45°	2059.9	2104.7	2078.3	2019.2	2002.9	2031.4	2088.4	2100.6	2045.7	2007.0	1984.6
47.5°	2002.9	2064.0	2045.7	1988.7	1964.3	2005.0	2064.0	2062.0	1992.8	1952.1	1933.7
50°	1962.2	2039.6	2037.5	1988.7	1962.2	2013.1	2066.0	2039.6	1964.3	1921.5	1903.2
52.5°	1929.7	2037.5	2051.8	2023.3	2005.0	2049.8	2082.3	2031.4	1943.9	1899.1	1884.9
55°	1915.4	2045.7	2055.9	2029.4	2013.1	2053.8	2082.3	2047.7	1943.9	1903.2	1891.0
57.5°	1919.5	2035.5	2037.5	2000.9	1972.4	2023.3	2068.1	2057.9	1966.3	1919.5	1905.2
60°	1895.1	1980.5	1984.6	1927.6	1895.1	1956.1	2035.5	2029.4	1956.1	1907.3	1880.8
62.5°	1813.6	1888.9	1891.0	1838.1	1791.2	1878.8	1966.3	1964.3	1897.1	1848.2	1817.7
65°	1677.3	1756.6	1777.0	1726.1	1689.5	1783.1	1874.7	1870.6	1803.5	1758.7	1728.1
67.5°	1508.3	1593.8	1632.5	1597.9	1583.6	1669.1	1754.6	1752.6	1697.6	1654.9	1628.4
70°	1302.7	1374.0	1439.1	1439.1	1428.9	1526.6	1618.2	1610.1	1559.2	1526.6	1506.3
72.5°	1131.7	1186.7	1207.1	1227.4	1257.9	1359.7	1437.1	1443.2	1406.5	1390.3	1406.5
75°	962.8	997.4	1015.7	999.4	1052.4	1158.2	1260.0	1270.2	1231.5	1205.0	1211.1
77.5°	791.8	830.5	848.8	812.2	808.1	942.4	1066.6	1089.0	1056.4	1015.7	1027.9
80°	572.0	622.9	653.4	629.0	620.8	679.9	850.8	875.3	844.7	812.2	830.5
82.5°	350.1	378.6	386.7	411.2	462.1	486.5	547.6	629.0	606.6	578.1	629.0
85°	138.4	164.9	183.2	207.6	242.2	287.0	337.9	403.0	366.4	354.2	417.3
87.5°	8.1	2.0	0.0	4.1	34.6	67.2	144.5	199.5	166.9	179.1	215.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P642226
 CATALOG NUMBER: GWS-SA6C-740-U-SLR-W

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	3568.2	3568.2	3568.2	3568.2	3568.2	3568.2	3568.2	3568.2	3568.2	3568.2
2.5°	3303.6	3356.5	3427.8	3486.8	3562.1	3633.4	3706.7	3779.9	3818.6	3834.9
5°	3069.5	3167.2	3281.2	3407.4	3554.0	3708.7	3865.4	4026.2	4128.0	4136.1
7.5°	2929.1	3069.5	3226.3	3385.0	3566.2	3779.9	4028.3	4276.6	4380.4	4408.9
10°	2973.9	3130.6	3254.8	3403.4	3602.8	3869.5	4162.6	4453.7	4573.8	4608.4
12.5°	3153.0	3183.5	3222.2	3358.6	3602.8	3946.8	4301.0	4647.1	4775.3	4807.9
15°	3301.6	3155.0	3085.8	3230.3	3554.0	4014.0	4447.6	4830.3	4985.0	5015.5
17.5°	3313.8	3061.4	2910.8	3041.0	3468.5	4060.8	4588.0	5033.8	5164.1	5192.6
20°	3189.6	2961.7	2766.3	2845.6	3352.5	4081.2	4689.8	5182.4	5310.6	5339.1
22.5°	3049.2	2880.2	2668.5	2664.5	3212.0	4103.6	4811.9	5322.8	5461.3	5479.6
25°	2916.9	2768.3	2589.2	2532.2	3049.2	4146.3	4976.8	5534.5	5640.4	5646.5
27.5°	2762.2	2648.2	2526.1	2471.1	2906.7	4227.7	5221.1	5786.9	5850.0	5839.9
30°	2621.7	2536.2	2481.3	2465.0	2817.1	4288.8	5453.1	6035.3	6039.3	6004.7
32.5°	2473.1	2440.6	2440.6	2493.5	2743.9	4274.6	5642.4	6277.5	6238.8	6187.9
35°	2340.8	2346.9	2389.7	2513.8	2621.7	4132.1	5823.6	6580.8	6523.8	6450.5
37.5°	2214.6	2261.4	2322.5	2442.6	2460.9	3920.4	6035.3	7010.3	6939.0	6847.4
40°	2106.7	2178.0	2249.2	2308.3	2289.9	3619.1	6330.4	7515.1	7435.7	7329.9
42.5°	2021.3	2090.5	2169.8	2176.0	2182.1	3305.7	6643.9	8133.9	8119.6	8003.6
45°	1966.3	2011.1	2086.4	2076.2	2176.0	2959.6	6932.9	9078.4	9265.6	9178.1
47.5°	1929.7	1964.3	1972.4	2015.2	2228.9	2650.2	7305.4	10926.6	11447.7	11347.9
50°	1909.3	1943.9	1852.3	2019.2	2237.0	2450.7	7820.4	13247.1	14085.7	13953.4
52.5°	1907.3	1899.1	1760.7	2062.0	2192.2	2328.6	8089.1	14940.6	16801.1	17088.1
55°	1911.3	1809.6	1713.9	2074.2	2102.7	2283.8	7189.4	15754.8	19306.8	19913.4
57.5°	1874.7	1711.9	1740.4	2025.3	1933.7	2403.9	5314.7	15463.7	20308.2	21435.9
60°	1805.5	1618.2	1789.2	1893.0	1760.7	2198.3	3659.8	14165.1	19270.1	20430.4
62.5°	1705.8	1553.1	1783.1	1722.0	1697.6	1799.4	2515.9	12347.4	17623.4	18757.2
65°	1593.8	1500.2	1687.4	1557.2	1571.4	1384.1	1779.0	10295.6	15657.1	16772.6
67.5°	1473.7	1467.6	1547.0	1386.2	1327.1	1097.1	1296.6	8251.9	13131.0	14136.6
70°	1337.3	1382.1	1406.5	1231.5	1076.8	861.0	962.8	5770.7	9687.0	10562.2
72.5°	1200.9	1205.0	1239.6	1070.7	806.1	690.0	722.6	3495.0	6580.8	7217.9
75°	1062.5	1023.9	1056.4	871.2	600.5	565.9	557.7	2159.7	4545.3	5048.1
77.5°	913.9	871.2	828.5	655.4	482.4	437.6	427.5	1211.1	2788.6	3098.0
80°	743.0	686.0	618.8	480.4	352.1	313.5	311.4	590.3	1390.3	1549.0
82.5°	578.1	470.2	451.9	299.2	217.8	191.3	203.6	225.9	419.3	468.2
85°	405.1	342.0	240.2	120.1	97.7	79.4	77.3	67.2	112.0	124.2
87.5°	225.9	148.6	77.3	14.2	16.3	18.3	14.2	10.2	10.2	10.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)