

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P630363

Luminaire Tested: GWS-SA1D-740-U-T3R-W

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P630363  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-15)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA1D-740-U-T3R-W  
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III ROADWAY OPTICS  
Light Source: (16) 4000K CCT, 70 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6164.4 lumens  
Efficiency: N/A  
Efficacy: 139.2 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type III - Medium  
BUG Rating: B1 - U0 - G2  
  
Input Watts (W): 44.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P630363  
 CATALOG NUMBER: GWS-SA1D-740-U-T3R-W

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 10.3 fc  
 Type III - Medium - N/A

REPORT NUMBER: P630363  
CATALOG NUMBER: GWS-SA1D-740-U-T3R-W

### Luminous Intensity Polar Plot



— Vertical Plane Through 56-Deg Lateral    - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P630363

CATALOG NUMBER: GWS-SA1D-740-U-T3R-W

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 1185.1   | 0.0    | 1185.1 |
|                    | % Fixture | 19.2     | 0.0    | 19.2   |
| <b>Street Side</b> | Lumens    | 4979.3   | 0.0    | 4979.3 |
|                    | % Fixture | 80.8     | 0.0    | 80.8   |
| <b>Total</b>       | Lumens    | 6164.4   | 0.0    | 6164.4 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 92.1   | 1.5       |
| 10°-20°   | 249.5  | 4.0       |
| 20°-30°   | 412.5  | 6.7       |
| 30°-40°   | 616.7  | 10.0      |
| 40°-50°   | 917.7  | 14.9      |
| 50°-60°   | 1304.8 | 21.2      |
| 60°-70°   | 1616.0 | 26.2      |
| 70°-80°   | 892.3  | 14.5      |
| 80°-90°   | 62.8   | 1.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 6164.4 | 100.0     |
| 0°-180°   | 6164.4 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P630363


CATALOG NUMBER: GWS-SA1D-740-U-T3R-W

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 433.2  | 7.0       |                         |      |         |
| FM (30°-60°)   | 2309.1 | 37.5      |                         |      |         |
| FH (60°-80°)   | 2193.3 | 35.6      |                         |      | G2/5000 |
| FVH (80°-90°)  | 43.7   | 0.7       |                         |      | G1/100  |
| BL (0°-30°)    | 320.8  | 5.2       | B1/500                  |      |         |
| BM (30°-60°)   | 530.1  | 8.6       | B1/1000                 |      |         |
| BH (60°-80°)   | 315.0  | 5.1       | B1/500                  |      | G1/500  |
| BVH (80°-90°)  | 19.2   | 0.3       |                         |      | G1/100  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B1-U0-G2**

Type III Medium





REPORT NUMBER: P630363  
 CATALOG NUMBER: GWS-SA1D-740-U-T3R-W

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 56°    | 65°    | 75°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 995.0  | 995.0  | 995.0  | 995.0  | 995.0  | 995.0  | 995.0  | 995.0  | 995.0  | 995.0  | 995.0  |
| 2.5°  | 931.1  | 925.9  | 932.0  | 935.0  | 942.9  | 954.2  | 964.2  | 964.6  | 969.8  | 982.4  | 994.6  |
| 5°    | 889.0  | 886.4  | 888.1  | 897.2  | 905.5  | 919.8  | 935.0  | 936.3  | 951.1  | 975.9  | 1000.2 |
| 7.5°  | 856.4  | 852.9  | 859.4  | 871.1  | 881.6  | 897.7  | 917.7  | 919.4  | 940.3  | 977.6  | 1015.0 |
| 10°   | 809.4  | 806.8  | 819.0  | 834.6  | 857.2  | 883.7  | 910.3  | 912.4  | 939.8  | 988.9  | 1041.1 |
| 12.5° | 789.0  | 789.0  | 794.2  | 809.0  | 833.8  | 869.0  | 909.0  | 912.4  | 946.8  | 1006.3 | 1074.6 |
| 15°   | 820.7  | 822.9  | 818.5  | 817.7  | 827.7  | 861.1  | 910.7  | 915.9  | 959.8  | 1024.2 | 1107.6 |
| 17.5° | 884.6  | 886.8  | 875.5  | 857.7  | 847.7  | 868.5  | 917.2  | 922.9  | 973.7  | 1043.7 | 1143.3 |
| 20°   | 974.2  | 976.8  | 952.0  | 924.6  | 890.3  | 889.8  | 929.8  | 935.0  | 991.6  | 1065.0 | 1181.1 |
| 22.5° | 1078.9 | 1080.7 | 1049.4 | 1005.9 | 953.3  | 929.4  | 951.6  | 956.8  | 1014.6 | 1094.6 | 1221.9 |
| 25°   | 1200.2 | 1205.4 | 1167.6 | 1104.6 | 1033.3 | 983.7  | 987.6  | 993.7  | 1055.9 | 1134.1 | 1270.2 |
| 27.5° | 1329.7 | 1336.3 | 1292.8 | 1223.2 | 1125.0 | 1043.7 | 1034.2 | 1039.4 | 1099.8 | 1158.5 | 1295.8 |
| 30°   | 1462.3 | 1467.1 | 1423.6 | 1344.1 | 1223.7 | 1111.5 | 1073.3 | 1076.3 | 1118.9 | 1170.2 | 1321.9 |
| 32.5° | 1609.7 | 1605.8 | 1564.1 | 1472.3 | 1337.6 | 1192.8 | 1109.8 | 1108.9 | 1140.2 | 1193.7 | 1359.3 |
| 35°   | 1747.9 | 1753.6 | 1709.2 | 1608.0 | 1462.8 | 1293.2 | 1164.6 | 1161.1 | 1185.4 | 1231.9 | 1411.9 |
| 37.5° | 1915.3 | 1913.6 | 1860.5 | 1751.0 | 1588.4 | 1389.3 | 1241.5 | 1235.4 | 1244.1 | 1291.5 | 1485.4 |
| 40°   | 2034.8 | 2047.0 | 2012.7 | 1910.5 | 1735.3 | 1507.5 | 1331.5 | 1318.0 | 1320.2 | 1365.0 | 1583.6 |
| 42.5° | 2132.6 | 2143.9 | 2147.4 | 2082.2 | 1903.6 | 1653.6 | 1443.6 | 1430.2 | 1431.5 | 1494.9 | 1704.5 |
| 45°   | 2207.8 | 2223.1 | 2272.2 | 2253.1 | 2093.1 | 1822.3 | 1595.4 | 1581.4 | 1582.3 | 1652.7 | 1850.5 |
| 47.5° | 2238.7 | 2255.2 | 2354.8 | 2400.4 | 2294.3 | 2024.0 | 1784.0 | 1763.6 | 1766.6 | 1844.4 | 2017.4 |
| 50°   | 2228.7 | 2250.9 | 2385.6 | 2513.9 | 2463.0 | 2229.1 | 2009.6 | 1995.3 | 1983.5 | 2096.6 | 2198.7 |
| 52.5° | 2142.6 | 2167.0 | 2382.6 | 2586.0 | 2600.8 | 2423.0 | 2242.6 | 2234.4 | 2231.8 | 2364.3 | 2401.3 |
| 55°   | 1889.2 | 1930.1 | 2277.8 | 2605.2 | 2708.6 | 2605.6 | 2495.2 | 2481.3 | 2494.7 | 2651.2 | 2606.0 |
| 57.5° | 1748.8 | 1779.2 | 2072.7 | 2583.9 | 2796.9 | 2779.5 | 2747.3 | 2748.6 | 2763.8 | 2962.9 | 2854.2 |
| 60°   | 1668.8 | 1704.5 | 1958.8 | 2525.6 | 2881.6 | 2990.7 | 3011.2 | 3011.2 | 3038.6 | 3298.9 | 3106.4 |
| 62.5° | 1562.7 | 1598.8 | 1852.3 | 2413.5 | 2959.9 | 3239.4 | 3342.8 | 3341.5 | 3352.4 | 3659.3 | 3352.8 |
| 65°   | 1347.6 | 1381.0 | 1638.4 | 2236.5 | 2998.1 | 3513.2 | 3719.7 | 3715.8 | 3694.1 | 3980.1 | 3515.9 |
| 67.5° | 978.5  | 1010.2 | 1255.0 | 1900.1 | 2860.3 | 3734.1 | 4107.9 | 4109.7 | 3979.7 | 4182.3 | 3524.5 |
| 70°   | 645.1  | 666.8  | 806.8  | 1234.1 | 2326.1 | 3638.9 | 4270.5 | 4275.7 | 4023.6 | 4056.2 | 3136.8 |
| 72.5° | 402.5  | 417.7  | 503.8  | 735.9  | 1374.5 | 2880.3 | 3853.2 | 3867.5 | 3619.7 | 3564.5 | 2577.3 |
| 75°   | 267.3  | 277.8  | 335.2  | 429.0  | 636.0  | 1558.8 | 2929.0 | 2975.1 | 2901.2 | 2794.3 | 1795.7 |
| 77.5° | 160.8  | 169.5  | 213.4  | 272.6  | 281.7  | 609.0  | 1709.7 | 1828.8 | 1839.2 | 1458.9 | 752.0  |
| 80°   | 73.5   | 83.5   | 117.8  | 155.6  | 150.0  | 212.1  | 602.9  | 630.8  | 744.2  | 463.4  | 237.3  |
| 82.5° | 43.5   | 47.8   | 78.2   | 77.4   | 63.9   | 103.0  | 216.9  | 222.6  | 189.1  | 169.5  | 101.3  |
| 85°   | 17.4   | 20.4   | 33.0   | 29.1   | 23.5   | 33.5   | 81.7   | 85.6   | 82.2   | 73.9   | 37.4   |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.4    | 0.9    | 7.4    | 7.8    | 11.3   | 20.4   | 11.3   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P630363  
 CATALOG NUMBER: GWS-SA1D-740-U-T3R-W

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 995.0  | 995.0  | 995.0  | 995.0  | 995.0  | 995.0  | 995.0  | 995.0  | 995.0  | 995.0  | 995.0  |
| 2.5°  | 1002.4 | 999.8  | 1012.9 | 1022.8 | 1027.2 | 1031.5 | 1027.6 | 1026.3 | 1026.3 | 1017.6 | 1013.3 |
| 5°    | 1013.3 | 1014.6 | 1032.4 | 1040.7 | 1040.7 | 1037.2 | 1026.8 | 1019.4 | 1016.8 | 1005.5 | 1002.4 |
| 7.5°  | 1033.7 | 1039.4 | 1055.9 | 1055.5 | 1043.3 | 1024.2 | 998.1  | 978.1  | 959.8  | 952.0  | 947.2  |
| 10°   | 1067.2 | 1074.6 | 1085.9 | 1067.6 | 1033.7 | 983.3  | 928.1  | 884.6  | 858.5  | 837.7  | 837.7  |
| 12.5° | 1105.4 | 1112.4 | 1110.2 | 1068.1 | 998.1  | 903.7  | 824.2  | 774.2  | 737.7  | 718.6  | 718.6  |
| 15°   | 1143.7 | 1149.3 | 1125.9 | 1048.1 | 923.7  | 798.1  | 711.2  | 651.2  | 619.4  | 601.6  | 601.6  |
| 17.5° | 1182.4 | 1182.0 | 1132.4 | 1002.0 | 826.8  | 681.2  | 596.0  | 549.5  | 538.6  | 535.6  | 535.1  |
| 20°   | 1219.8 | 1209.8 | 1124.1 | 925.0  | 714.2  | 563.4  | 509.5  | 512.5  | 528.6  | 535.6  | 536.4  |
| 22.5° | 1261.9 | 1237.2 | 1099.8 | 826.8  | 586.4  | 481.6  | 485.1  | 510.3  | 533.8  | 544.2  | 545.5  |
| 25°   | 1305.0 | 1260.6 | 1058.9 | 711.6  | 479.5  | 451.7  | 478.6  | 506.9  | 533.4  | 546.9  | 548.2  |
| 27.5° | 1322.4 | 1260.6 | 989.4  | 578.2  | 422.5  | 439.0  | 468.6  | 496.0  | 523.8  | 539.5  | 542.5  |
| 30°   | 1336.7 | 1249.8 | 892.0  | 457.7  | 399.1  | 426.9  | 452.5  | 477.7  | 505.1  | 524.2  | 527.7  |
| 32.5° | 1356.7 | 1240.2 | 774.2  | 384.7  | 388.2  | 415.1  | 433.0  | 454.3  | 479.0  | 491.6  | 490.3  |
| 35°   | 1380.2 | 1225.4 | 632.1  | 349.9  | 379.1  | 405.1  | 417.7  | 430.4  | 419.1  | 418.6  | 419.9  |
| 37.5° | 1413.6 | 1212.4 | 508.2  | 334.3  | 373.0  | 398.2  | 408.6  | 381.7  | 366.0  | 359.5  | 356.9  |
| 40°   | 1461.9 | 1207.2 | 400.8  | 325.2  | 372.1  | 397.8  | 390.4  | 348.6  | 327.3  | 304.7  | 304.3  |
| 42.5° | 1522.8 | 1203.3 | 331.2  | 320.8  | 375.1  | 407.7  | 365.1  | 326.9  | 283.0  | 273.0  | 272.1  |
| 45°   | 1601.0 | 1197.2 | 296.5  | 319.9  | 382.5  | 415.6  | 362.5  | 296.9  | 266.9  | 262.6  | 262.6  |
| 47.5° | 1695.3 | 1187.6 | 280.8  | 319.9  | 390.8  | 412.1  | 354.7  | 290.4  | 259.5  | 264.3  | 267.3  |
| 50°   | 1803.6 | 1175.4 | 272.6  | 319.1  | 399.1  | 412.1  | 338.2  | 289.1  | 257.8  | 282.6  | 292.6  |
| 52.5° | 1919.2 | 1161.5 | 266.9  | 315.6  | 404.7  | 412.5  | 339.1  | 293.4  | 259.5  | 286.9  | 295.2  |
| 55°   | 2047.0 | 1159.3 | 259.1  | 308.2  | 406.4  | 401.2  | 341.2  | 303.0  | 262.1  | 260.0  | 260.4  |
| 57.5° | 2208.3 | 1185.4 | 253.4  | 297.3  | 399.5  | 378.2  | 345.6  | 309.9  | 259.1  | 259.5  | 262.6  |
| 60°   | 2376.9 | 1234.5 | 258.2  | 286.9  | 385.1  | 356.5  | 348.6  | 306.5  | 244.3  | 237.3  | 238.2  |
| 62.5° | 2520.4 | 1271.9 | 262.1  | 282.1  | 364.3  | 337.3  | 345.6  | 298.6  | 236.0  | 234.3  | 238.2  |
| 65°   | 2580.4 | 1241.1 | 252.6  | 272.1  | 333.8  | 313.9  | 339.1  | 288.6  | 229.1  | 222.6  | 223.0  |
| 67.5° | 2513.9 | 1096.3 | 233.9  | 250.0  | 299.5  | 283.9  | 328.6  | 275.6  | 219.5  | 211.7  | 210.0  |
| 70°   | 2147.4 | 805.5  | 201.7  | 214.7  | 257.8  | 248.6  | 312.5  | 258.6  | 204.3  | 198.7  | 194.7  |
| 72.5° | 1730.5 | 570.3  | 167.4  | 170.8  | 202.1  | 209.5  | 284.7  | 237.3  | 186.9  | 170.8  | 165.2  |
| 75°   | 1204.6 | 358.2  | 139.5  | 136.1  | 146.1  | 160.0  | 222.1  | 196.9  | 161.3  | 144.3  | 139.1  |
| 77.5° | 518.2  | 183.9  | 109.1  | 107.4  | 97.4   | 110.8  | 170.4  | 164.3  | 135.2  | 115.6  | 112.6  |
| 80°   | 173.4  | 106.5  | 78.7   | 75.6   | 64.8   | 77.8   | 120.0  | 131.3  | 106.1  | 85.6   | 80.4   |
| 82.5° | 86.9   | 61.7   | 50.0   | 45.2   | 43.5   | 49.1   | 70.9   | 81.7   | 73.5   | 59.1   | 50.0   |
| 85°   | 42.6   | 35.2   | 27.4   | 27.0   | 22.6   | 21.3   | 29.6   | 34.8   | 33.0   | 24.3   | 23.0   |
| 87.5° | 15.6   | 13.9   | 8.7    | 7.0    | 4.3    | 3.0    | 1.7    | 1.7    | 1.3    | 1.3    | 1.3    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW, INVUE, LUMARK AND STREETWORKS

DATA VALID FOR LUMINAIRES UTILIZING SA LIGHT ENGINES

Report Number: SP1-2101-121-2

Luminaire Tested: IFLD-S-SA2A-740-U-T3R-HSS

Test Date: 03/05/2021

**Test Information**

Test Method: LM-79-08  
 Report Number: SP1-2101-121-2  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry: 4π  
 Issue Date: 03/05/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**  
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

**Spectral Parameters**

|                           |         |           |      |      |       |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K):                  | 3905    | CRI (Ra): | 71.2 | R9:  | -29.7 |
| CIE u':                   | 0.2273  | R1:       | 68.9 | R10: | 46.2  |
| CIE v':                   | 0.5024  | R2:       | 77.0 | R11: | 68.8  |
| Duv:                      | -0.0008 | R3:       | 84.0 | R12: | 45.6  |
| CIE x:                    | 0.3841  | R4:       | 71.6 | R13: | 69.5  |
| CIE y:                    | 0.3774  | R5:       | 68.9 | R14: | 90.7  |
| CIE z:                    | 0.2385  | R6:       | 68.3 |      |       |
| Peak Wavelength (nm):     | 443     | R7:       | 78.7 |      |       |
| Dominant Wavelength (nm): | 579     | R8:       | 52.2 |      |       |
| Purity:                   | 28.7    |           |      |      |       |
| Rf:                       | 71.7    |           |      |      |       |
| Rg:                       | 96.9    |           |      |      |       |



**Test Conditions**

Stabilization Time: 211M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 24.8/312%  
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-2

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2101-121-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 3905K  
 CIE x = 0.3841  
 CIE y = 0.3774  
 Duv = -0.0008

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

**Photopic Flux vs. Wavelength**



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2304          | 0.0           | 490    | 19043         | 2.7           | 620    | 97577         | 25.4          | 750    | 4830          | 0.0           | 880    | 3505          | 0.0           |
| 365    | 2150          | 0.0           | 495    | 26606         | 4.8           | 625    | 90158         | 19.9          | 755    | 4664          | 0.0           | 885    | 2991          | 0.0           |
| 370    | 2146          | 0.0           | 500    | 36376         | 8.0           | 630    | 82240         | 14.9          | 760    | 4006          | 0.0           | 890    | 2327          | 0.0           |
| 375    | 2332          | 0.0           | 505    | 47714         | 13.3          | 635    | 74361         | 11.2          | 765    | 3715          | 0.0           | 895    | 2775          | 0.0           |
| 380    | 2527          | 0.0           | 510    | 58741         | 20.2          | 640    | 66994         | 8.0           | 770    | 3696          | 0.0           | 900    | 2141          | 0.0           |
| 385    | 2304          | 0.0           | 515    | 68716         | 28.5          | 645    | 60405         | 5.8           | 775    | 3117          | 0.0           | 905    | 2421          | 0.0           |
| 390    | 2064          | 0.0           | 520    | 77136         | 37.4          | 650    | 53806         | 3.9           | 780    | 3062          | 0.0           | 910    | 2200          | 0.0           |
| 395    | 1856          | 0.0           | 525    | 83567         | 44.9          | 655    | 47610         | 2.7           | 785    | 2907          | 0.0           | 915    | 2716          | 0.0           |
| 400    | 1856          | 0.0           | 530    | 89283         | 52.6          | 660    | 42018         | 1.8           | 790    | 2655          | 0.0           | 920    | 2656          | 0.0           |
| 405    | 2374          | 0.0           | 535    | 94097         | 58.4          | 665    | 36742         | 1.2           | 795    | 2467          | 0.0           | 925    | 2671          | 0.0           |
| 410    | 4084          | 0.0           | 540    | 96845         | 63.1          | 670    | 32105         | 0.7           | 800    | 2609          | 0.0           | 930    | 3292          | 0.0           |
| 415    | 8543          | 0.0           | 545    | 100829        | 67.1          | 675    | 27946         | 0.5           | 805    | 2293          | 0.0           | 935    | 3188          | 0.0           |
| 420    | 18394         | 0.1           | 550    | 105648        | 71.8          | 680    | 24146         | 0.3           | 810    | 2188          | 0.0           | 940    | 1997          | 0.0           |
| 425    | 37987         | 0.2           | 555    | 110017        | 75.1          | 685    | 21191         | 0.2           | 815    | 2386          | 0.0           | 945    | 2623          | 0.0           |
| 430    | 67605         | 0.5           | 560    | 114586        | 77.9          | 690    | 18544         | 0.1           | 820    | 2712          | 0.0           | 950    | 2969          | 0.0           |
| 435    | 102160        | 1.2           | 565    | 118987        | 79.1          | 695    | 16058         | 0.1           | 825    | 2473          | 0.0           | 955    | 2277          | 0.0           |
| 440    | 135103        | 2.1           | 570    | 122326        | 79.5          | 700    | 14133         | 0.0           | 830    | 1969          | 0.0           | 960    | 4267          | 0.0           |
| 445    | 140126        | 2.9           | 575    | 125968        | 78.4          | 705    | 12309         | 0.0           | 835    | 1917          | 0.0           | 965    | 2034          | 0.0           |
| 450    | 102339        | 2.7           | 580    | 127613        | 75.8          | 710    | 11142         | 0.0           | 840    | 2248          | 0.0           | 970    | 3586          | 0.0           |
| 455    | 58751         | 2.0           | 585    | 129466        | 71.9          | 715    | 10143         | 0.0           | 845    | 2266          | 0.0           | 975    | 2505          | 0.0           |
| 460    | 36892         | 1.5           | 590    | 128813        | 66.6          | 720    | 9072          | 0.0           | 850    | 2558          | 0.0           | 980    | 2666          | 0.0           |
| 465    | 24637         | 1.3           | 595    | 126387        | 59.9          | 725    | 8130          | 0.0           | 855    | 2767          | 0.0           | 985    | 2934          | 0.0           |
| 470    | 16738         | 1.0           | 600    | 123477        | 53.2          | 730    | 7149          | 0.0           | 860    | 2826          | 0.0           | 990    | 4120          | 0.0           |
| 475    | 13456         | 1.1           | 605    | 118718        | 46.0          | 735    | 6311          | 0.0           | 865    | 2385          | 0.0           | 995    | 3858          | 0.0           |
| 480    | 13081         | 1.2           | 610    | 112091        | 38.5          | 740    | 5711          | 0.0           | 870    | 3194          | 0.0           | 1000   | 3405          | 0.0           |
| 485    | 14734         | 1.7           | 615    | 105039        | 31.7          | 745    | 5111          | 0.0           | 875    | 3189          | 0.0           |        |               |               |

REPORT NUMBER: SP1-2101-121-2

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: 10425.8 S/P: 1.47**

| λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2304          | 0.0           | 490    | 19043         | 29.3          | 620    | 97577         | 1.2           | 750    | 4830          | 0.0           | 880    | 3505          | 0.0           |
| 365    | 2150          | 0.0           | 495    | 26606         | 43.0          | 625    | 90158         | 0.8           | 755    | 4664          | 0.0           | 885    | 2991          | 0.0           |
| 370    | 2146          | 0.0           | 500    | 36376         | 60.8          | 630    | 82240         | 0.5           | 760    | 4006          | 0.0           | 890    | 2327          | 0.0           |
| 375    | 2332          | 0.0           | 505    | 47714         | 81.1          | 635    | 74361         | 0.3           | 765    | 3715          | 0.0           | 895    | 2775          | 0.0           |
| 380    | 2527          | 0.0           | 510    | 58741         | 99.6          | 640    | 66994         | 0.2           | 770    | 3696          | 0.0           | 900    | 2141          | 0.0           |
| 385    | 2304          | 0.0           | 515    | 68716         | 113.9         | 645    | 60405         | 0.1           | 775    | 3117          | 0.0           | 905    | 2421          | 0.0           |
| 390    | 2064          | 0.0           | 520    | 77136         | 122.6         | 650    | 53806         | 0.1           | 780    | 3062          | 0.0           | 910    | 2200          | 0.0           |
| 395    | 1856          | 0.0           | 525    | 83567         | 125.0         | 655    | 47610         | 0.0           | 785    | 2907          | 0.0           | 915    | 2716          | 0.0           |
| 400    | 1856          | 0.0           | 530    | 89283         | 123.1         | 660    | 42018         | 0.0           | 790    | 2655          | 0.0           | 920    | 2656          | 0.0           |
| 405    | 2374          | 0.1           | 535    | 94097         | 117.3         | 665    | 36742         | 0.0           | 795    | 2467          | 0.0           | 925    | 2671          | 0.0           |
| 410    | 4084          | 0.2           | 540    | 96845         | 107.0         | 670    | 32105         | 0.0           | 800    | 2609          | 0.0           | 930    | 3292          | 0.0           |
| 415    | 8543          | 0.9           | 545    | 100829        | 96.7          | 675    | 27946         | 0.0           | 805    | 2293          | 0.0           | 935    | 3188          | 0.0           |
| 420    | 18394         | 3.0           | 550    | 105648        | 86.4          | 680    | 24146         | 0.0           | 810    | 2188          | 0.0           | 940    | 1997          | 0.0           |
| 425    | 37987         | 9.3           | 555    | 110017        | 75.2          | 685    | 21191         | 0.0           | 815    | 2386          | 0.0           | 945    | 2623          | 0.0           |
| 430    | 67605         | 23.0          | 560    | 114586        | 64.0          | 690    | 18544         | 0.0           | 820    | 2712          | 0.0           | 950    | 2969          | 0.0           |
| 435    | 102160        | 45.7          | 565    | 118987        | 53.4          | 695    | 16058         | 0.0           | 825    | 2473          | 0.0           | 955    | 2277          | 0.0           |
| 440    | 135103        | 75.5          | 570    | 122326        | 43.2          | 700    | 14133         | 0.0           | 830    | 1969          | 0.0           | 960    | 4267          | 0.0           |
| 445    | 140126        | 93.8          | 575    | 125968        | 34.3          | 705    | 12309         | 0.0           | 835    | 1917          | 0.0           | 965    | 2034          | 0.0           |
| 450    | 102339        | 79.3          | 580    | 127613        | 26.3          | 710    | 11142         | 0.0           | 840    | 2248          | 0.0           | 970    | 3586          | 0.0           |
| 455    | 58751         | 51.3          | 585    | 129466        | 19.8          | 715    | 10143         | 0.0           | 845    | 2266          | 0.0           | 975    | 2505          | 0.0           |
| 460    | 36892         | 35.6          | 590    | 128813        | 14.3          | 720    | 9072          | 0.0           | 850    | 2558          | 0.0           | 980    | 2666          | 0.0           |
| 465    | 24637         | 26.0          | 595    | 126387        | 10.1          | 725    | 8130          | 0.0           | 855    | 2767          | 0.0           | 985    | 2934          | 0.0           |
| 470    | 16738         | 19.3          | 600    | 123477        | 7.0           | 730    | 7149          | 0.0           | 860    | 2826          | 0.0           | 990    | 4120          | 0.0           |
| 475    | 13456         | 16.8          | 605    | 118718        | 4.7           | 735    | 6311          | 0.0           | 865    | 2385          | 0.0           | 995    | 3858          | 0.0           |
| 480    | 13081         | 17.7          | 610    | 112091        | 3.0           | 740    | 5711          | 0.0           | 870    | 3194          | 0.0           | 1000   | 3405          | 0.0           |
| 485    | 14734         | 21.4          | 615    | 105039        | 1.9           | 745    | 5111          | 0.0           | 875    | 3189          | 0.0           |        |               |               |

REPORT NUMBER: SP1-2101-121-2

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 3927.2 M/P: 0.55**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2304          | 0.0           | 490    | 19043         | 15.8          | 620    | 97577         | 0.1           | 750    | 4830          | 0.0           | 880    | 3505          | 0.0           |
| 365    | 2150          | 0.0           | 495    | 26606         | 22.0          | 625    | 90158         | 0.0           | 755    | 4664          | 0.0           | 885    | 2991          | 0.0           |
| 370    | 2146          | 0.0           | 500    | 36376         | 29.2          | 630    | 82240         | 0.0           | 760    | 4006          | 0.0           | 890    | 2327          | 0.0           |
| 375    | 2332          | 0.0           | 505    | 47714         | 36.6          | 635    | 74361         | 0.0           | 765    | 3715          | 0.0           | 895    | 2775          | 0.0           |
| 380    | 2527          | 0.0           | 510    | 58741         | 42.2          | 640    | 66994         | 0.0           | 770    | 3696          | 0.0           | 900    | 2141          | 0.0           |
| 385    | 2304          | 0.0           | 515    | 68716         | 44.9          | 645    | 60405         | 0.0           | 775    | 3117          | 0.0           | 905    | 2421          | 0.0           |
| 390    | 2064          | 0.0           | 520    | 77136         | 44.9          | 650    | 53806         | 0.0           | 780    | 3062          | 0.0           | 910    | 2200          | 0.0           |
| 395    | 1856          | 0.0           | 525    | 83567         | 42.4          | 655    | 47610         | 0.0           | 785    | 2907          | 0.0           | 915    | 2716          | 0.0           |
| 400    | 1856          | 0.0           | 530    | 89283         | 38.6          | 660    | 42018         | 0.0           | 790    | 2655          | 0.0           | 920    | 2656          | 0.0           |
| 405    | 2374          | 0.0           | 535    | 94097         | 33.9          | 665    | 36742         | 0.0           | 795    | 2467          | 0.0           | 925    | 2671          | 0.0           |
| 410    | 4084          | 0.2           | 540    | 96845         | 28.3          | 670    | 32105         | 0.0           | 800    | 2609          | 0.0           | 930    | 3292          | 0.0           |
| 415    | 8543          | 0.6           | 545    | 100829        | 23.4          | 675    | 27946         | 0.0           | 805    | 2293          | 0.0           | 935    | 3188          | 0.0           |
| 420    | 18394         | 2.1           | 550    | 105648        | 19.0          | 680    | 24146         | 0.0           | 810    | 2188          | 0.0           | 940    | 1997          | 0.0           |
| 425    | 37987         | 5.9           | 555    | 110017        | 14.8          | 685    | 21191         | 0.0           | 815    | 2386          | 0.0           | 945    | 2623          | 0.0           |
| 430    | 67605         | 14.3          | 560    | 114586        | 11.3          | 690    | 18544         | 0.0           | 820    | 2712          | 0.0           | 950    | 2969          | 0.0           |
| 435    | 102160        | 27.3          | 565    | 118987        | 8.4           | 695    | 16058         | 0.0           | 825    | 2473          | 0.0           | 955    | 2277          | 0.0           |
| 440    | 135103        | 45.1          | 570    | 122326        | 6.0           | 700    | 14133         | 0.0           | 830    | 1969          | 0.0           | 960    | 4267          | 0.0           |
| 445    | 140126        | 55.3          | 575    | 125968        | 4.2           | 705    | 12309         | 0.0           | 835    | 1917          | 0.0           | 965    | 2034          | 0.0           |
| 450    | 102339        | 47.2          | 580    | 127613        | 2.9           | 710    | 11142         | 0.0           | 840    | 2248          | 0.0           | 970    | 3586          | 0.0           |
| 455    | 58751         | 30.8          | 585    | 129466        | 1.9           | 715    | 10143         | 0.0           | 845    | 2266          | 0.0           | 975    | 2505          | 0.0           |
| 460    | 36892         | 21.7          | 590    | 128813        | 1.3           | 720    | 9072          | 0.0           | 850    | 2558          | 0.0           | 980    | 2666          | 0.0           |
| 465    | 24637         | 16.1          | 595    | 126387        | 0.8           | 725    | 8130          | 0.0           | 855    | 2767          | 0.0           | 985    | 2934          | 0.0           |
| 470    | 16738         | 12.0          | 600    | 123477        | 0.5           | 730    | 7149          | 0.0           | 860    | 2826          | 0.0           | 990    | 4120          | 0.0           |
| 475    | 13456         | 10.3          | 605    | 118718        | 0.3           | 735    | 6311          | 0.0           | 865    | 2385          | 0.0           | 995    | 3858          | 0.0           |
| 480    | 13081         | 10.5          | 610    | 112091        | 0.2           | 740    | 5711          | 0.0           | 870    | 3194          | 0.0           | 1000   | 3405          | 0.0           |
| 485    | 14734         | 12.1          | 615    | 105039        | 0.1           | 745    | 5111          | 0.0           | 875    | 3189          | 0.0           |        |               |               |

**Summary**

$R_f = 71.7$   
 $R_g = 96.9$   
 CIE  $R_a = 71.2$   
 $R_g = -29.7$



**Color Vector Graphics**





**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)