

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P833531

Luminaire Tested: **TTN-D2-735-U-MQ-CG-UPL2**

Issue Date: 5/15/2024

**Test Information**

Test Method: LM-79-08  
Report Number: P833531  
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND  
Test Lab: INNOVATION CENTER  
Issue Date: 5/15/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TTN-D2-735-U-MQ-CG-UPL2  
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT  
3500K, 70 CRI LEDS AND MEDIUM DISTRIBUTION WITH CLEAR GLASS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5624.8 lumens  
Efficiency: N/A  
Efficacy: 119.7 lumens/watt  
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')  
IES Classification: Type V - Short  
BUG Rating: B2 - U4 - G1  
  
Input Watts (W): 47  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P833531  
 CATALOG NUMBER: TTN-D2-735-U-MQ-CG-UPL2

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.9 fc  
 Type V - Short - N/A

REPORT NUMBER: P833531  
CATALOG NUMBER: TTN-D2-735-U-MQ-CG-UPL2

### Luminous Intensity Polar Plot



REPORT NUMBER: P833531  
 CATALOG NUMBER: TTN-D2-735-U-MQ-CG-UPL2


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	2540.9	271.5	2812.4
	% Fixture	45.2	4.8	50.0
<b>Street Side</b>	Lumens	2540.9	271.5	2812.4
	% Fixture	45.2	4.8	50.0
<b>Total</b>	Lumens	5081.8	543.0	5624.8
	% Fixture	90.3	9.7	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	113.5	2.0
10°-20°	328.4	5.8
20°-30°	528.3	9.4
30°-40°	705.7	12.5
40°-50°	857.4	15.2
50°-60°	996.2	17.7
60°-70°	919.1	16.3
70°-80°	538.1	9.6
80°-90°	95.0	1.7
90°-100°	12.1	0.2
100°-110°	123.2	2.2
110°-120°	180.1	3.2
120°-130°	104.5	1.9
130°-140°	55.4	1.0
140°-150°	32.9	0.6
150°-160°	20.2	0.4
160°-170°	11.0	0.2
170°-180°	3.6	0.1
0°-90°	5081.8	90.3
0°-180°	5624.8	100.0



REPORT NUMBER: P833531


CATALOG NUMBER: TTN-D2-735-U-MQ-CG-UPL2

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	485.1	8.6			
FM (30°-60°)	1279.7	22.8			
FH (60°-80°)	728.6	13.0			G1/1800
FVH (80°-90°)	47.5	0.8			G1/100
BL (0°-30°)	485.1	8.6	B1/500		
BM (30°-60°)	1279.7	22.8	B2/2500		
BH (60°-80°)	728.6	13.0	B2/1000		G1/1800
BVH (80°-90°)	47.5	0.8			G1/100
UL (90°-100°)	12.1	0.2		U2/50	
UH (100°-180°)	530.9	9.4		U4/1000	

**BUG Rating: B2-U4-G1**

Type V Short





REPORT NUMBER: P833531

CATALOG NUMBER: TTN-D2-735-U-MQ-CG-UPL2

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	1208.8	1208.8	1208.8	1208.8	1208.8	1208.8	1208.8	1208.8	1208.8	1208.8	1208.8
2.5°	1196.4	1200.5	1196.4	1196.4	1196.4	1196.4	1196.4	1196.4	1196.4	1196.4	1200.5
5°	1200.5	1200.5	1200.5	1200.5	1196.4	1196.4	1196.4	1196.4	1196.4	1200.5	1200.5
7.5°	1188.1	1188.1	1188.1	1188.1	1188.1	1184.0	1188.1	1188.1	1188.1	1188.1	1188.1
10°	1175.8	1175.8	1175.8	1175.8	1175.8	1175.8	1175.8	1175.8	1175.8	1175.8	1175.8
12.5°	1167.5	1167.5	1167.5	1167.5	1167.5	1167.5	1167.5	1167.5	1167.5	1163.4	1163.4
15°	1159.3	1159.3	1159.3	1159.3	1163.4	1163.4	1159.3	1159.3	1159.3	1159.3	1159.3
17.5°	1151.0	1151.0	1151.0	1151.0	1155.1	1155.1	1155.1	1151.0	1151.0	1151.0	1151.0
20°	1142.8	1142.8	1142.8	1142.8	1146.9	1146.9	1146.9	1146.9	1146.9	1142.8	1142.8
22.5°	1138.6	1138.6	1138.6	1138.6	1142.8	1142.8	1142.8	1142.8	1138.6	1138.6	1138.6
25°	1134.5	1138.6	1138.6	1138.6	1142.8	1146.9	1146.9	1142.8	1138.6	1134.5	1134.5
27.5°	1138.6	1138.6	1138.6	1142.8	1142.8	1146.9	1146.9	1142.8	1138.6	1138.6	1138.6
30°	1134.5	1134.5	1134.5	1138.6	1142.8	1146.9	1142.8	1142.8	1138.6	1134.5	1134.5
32.5°	1126.3	1126.3	1130.4	1134.5	1138.6	1138.6	1138.6	1134.5	1130.4	1126.3	1126.3
35°	1118.0	1118.0	1118.0	1122.1	1130.4	1130.4	1130.4	1126.3	1122.1	1118.0	1113.9
37.5°	1105.6	1109.7	1109.7	1118.0	1122.1	1126.3	1122.1	1118.0	1109.7	1105.6	1105.6
40°	1097.4	1097.4	1101.5	1109.7	1118.0	1118.0	1113.9	1109.7	1101.5	1097.4	1097.4
42.5°	1085.0	1085.0	1093.2	1101.5	1113.9	1113.9	1109.7	1101.5	1093.2	1085.0	1085.0
45°	1085.0	1085.0	1093.2	1109.7	1118.0	1126.3	1118.0	1109.7	1093.2	1085.0	1080.9
47.5°	1089.1	1089.1	1097.4	1118.0	1134.5	1142.8	1130.4	1113.9	1097.4	1089.1	1085.0
50°	1080.9	1085.0	1101.5	1122.1	1142.8	1146.9	1142.8	1118.0	1101.5	1080.9	1080.9
52.5°	1085.0	1085.0	1105.6	1138.6	1159.3	1167.5	1159.3	1138.6	1101.5	1080.9	1080.9
55°	1076.7	1072.6	1101.5	1138.6	1171.6	1188.1	1171.6	1138.6	1097.4	1072.6	1068.5
57.5°	1039.6	1039.6	1076.7	1113.9	1155.1	1163.4	1151.0	1113.9	1072.6	1039.6	1031.4
60°	990.1	994.2	1031.4	1072.6	1109.7	1113.9	1105.6	1072.6	1031.4	994.2	981.9
62.5°	936.5	944.7	981.9	1023.1	1068.5	1076.7	1064.4	1023.1	973.6	948.9	928.2
65°	858.1	870.5	911.7	957.1	1006.6	1002.5	1002.5	953.0	915.9	874.6	854.0
67.5°	771.5	783.8	812.7	874.6	915.9	911.7	907.6	874.6	812.7	783.8	771.5
70°	676.6	684.8	713.7	775.6	812.7	816.8	804.5	771.5	713.7	693.1	672.5
72.5°	565.2	569.3	610.6	660.1	697.2	693.1	689.0	660.1	606.4	585.8	561.1
75°	445.5	449.7	486.8	532.2	561.1	556.9	552.8	532.2	486.8	462.1	441.4
77.5°	334.2	330.0	367.2	400.2	416.7	420.8	412.5	396.0	363.0	342.4	330.0
80°	218.6	214.5	247.5	272.3	284.7	284.7	280.5	268.2	243.4	226.9	218.6
82.5°	123.8	119.6	140.3	156.8	169.1	165.0	160.9	152.6	140.3	127.9	119.6
85°	45.4	45.4	57.8	66.0	74.3	74.3	70.1	66.0	53.6	49.5	45.4
87.5°	4.1	4.1	8.3	12.4	12.4	12.4	8.3	8.3	4.1	4.1	4.1
90°	4.6	4.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	4.6	4.6
92.5°	4.6	4.6	4.6	6.5	7.4	6.5	7.4	5.6	5.6	4.6	4.6
95°	5.6	5.6	6.5	8.4	10.2	11.1	11.1	6.5	6.5	5.6	5.6
97.5°	7.4	8.4	8.4	10.2	16.7	30.7	18.6	9.3	9.3	8.4	7.4
100°	12.1	13.0	13.0	23.2	49.2	66.0	47.4	24.2	17.7	13.0	13.0
102.5°	39.0	40.9	50.2	75.3	111.5	101.3	85.5	80.8	55.7	44.6	42.7
105°	99.4	98.5	105.9	125.4	156.1	153.3	141.2	128.2	110.6	102.2	102.2
107.5°	131.0	131.0	137.5	154.2	177.4	207.2	210.0	166.3	145.9	136.6	135.6
110°	147.7	147.7	153.3	167.2	197.9	239.7	237.8	205.3	180.2	168.2	166.3



REPORT NUMBER: P833531  
 CATALOG NUMBER: TTN-D2-735-U-MQ-CG-UPL2

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	151.4	152.4	159.8	181.2	214.6	233.2	224.8	211.8	200.7	191.4	189.5
115°	157.0	157.0	165.4	185.8	204.4	211.8	202.5	192.3	184.9	181.2	183.0
117.5°	155.1	157.9	159.8	170.9	183.0	188.6	183.9	170.0	164.4	162.6	159.8
120°	144.0	144.0	145.9	151.4	157.9	160.7	158.9	149.6	144.9	144.0	142.1
122.5°	128.2	129.1	128.2	131.0	135.6	138.4	136.6	129.1	127.3	127.3	125.4
125°	112.4	112.4	111.5	113.3	116.1	115.2	116.1	112.4	111.5	111.5	110.6
127.5°	101.3	100.3	98.5	99.4	100.3	100.3	101.3	97.5	98.5	99.4	98.5
130°	90.1	90.1	88.3	88.3	88.3	86.4	88.3	86.4	87.3	88.3	89.2
132.5°	79.9	79.9	77.1	76.2	76.2	76.2	77.1	76.2	78.0	79.9	79.9
135°	71.5	71.5	68.7	69.7	69.7	68.7	69.7	68.7	70.6	71.5	71.5
137.5°	65.0	65.0	63.2	63.2	63.2	62.2	63.2	63.2	64.1	66.0	66.9
140°	59.5	59.5	58.5	58.5	57.6	58.5	58.5	58.5	59.5	60.4	60.4
142.5°	56.7	55.7	54.8	53.9	54.8	54.8	54.8	53.9	54.8	56.7	56.7
145°	52.0	52.0	51.1	51.1	51.1	52.0	51.1	51.1	52.0	52.0	53.0
147.5°	49.2	49.2	48.3	49.2	49.2	49.2	49.2	48.3	49.2	49.2	50.2
150°	48.3	47.4	46.5	47.4	47.4	46.5	46.5	46.5	46.5	47.4	47.4
152.5°	45.5	45.5	44.6	45.5	44.6	44.6	44.6	44.6	44.6	45.5	46.5
155°	43.7	43.7	42.7	43.7	43.7	43.7	43.7	43.7	43.7	43.7	43.7
157.5°	41.8	42.7	41.8	41.8	41.8	41.8	41.8	41.8	41.8	42.7	42.7
160°	40.9	40.9	40.9	40.9	39.9	39.9	39.9	40.9	40.9	40.9	41.8
162.5°	39.9	39.9	39.9	39.9	39.0	39.0	39.0	39.0	39.9	39.9	40.9
165°	39.9	39.0	39.0	39.0	38.1	38.1	38.1	38.1	39.0	39.9	39.0
167.5°	38.1	38.1	38.1	38.1	38.1	37.2	37.2	38.1	38.1	38.1	39.0
170°	38.1	38.1	37.2	37.2	37.2	37.2	37.2	37.2	37.2	37.2	38.1
172.5°	38.1	38.1	38.1	38.1	37.2	37.2	37.2	37.2	37.2	38.1	38.1
175°	38.1	38.1	38.1	38.1	37.2	37.2	37.2	38.1	38.1	38.1	37.2
177.5°	38.1	38.1	38.1	38.1	37.2	38.1	38.1	38.1	38.1	38.1	38.1
180°	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1

(END OF REPORT)