

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P633358

Luminaire Tested: GWS-SA2E-750-U-SL3-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P633358
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-32)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA2E-750-U-SL3-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (2) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III SPILL LIGHT ELIMINATOR OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (32) 5000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8729.8 lumens
Efficiency: N/A
Efficacy: 80.7 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B2 - U0 - G1


Input Watts (W): 108.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P633358
 CATALOG NUMBER: GWS-SA2E-750-U-SL3-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 38.3 fc
 Type II - Short - N/A

REPORT NUMBER: P633358
CATALOG NUMBER: GWS-SA2E-750-U-SL3-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 53-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P633358

CATALOG NUMBER: GWS-SA2E-750-U-SL3-W-GRSBK

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1442.0 | 0.0 | 1442.0 |
| | % Fixture | 16.5 | 0.0 | 16.5 |
| Street Side | Lumens | 7287.7 | 0.0 | 7287.7 |
| | % Fixture | 83.5 | 0.0 | 83.5 |
| Total | Lumens | 8729.8 | 0.0 | 8729.8 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 327.6 | 3.8 |
| 10°-20° | 719.3 | 8.2 |
| 20°-30° | 937.0 | 10.7 |
| 30°-40° | 1359.2 | 15.6 |
| 40°-50° | 1961.2 | 22.5 |
| 50°-60° | 2371.9 | 27.2 |
| 60°-70° | 966.7 | 11.1 |
| 70°-80° | 86.9 | 1.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 8729.8 | 100.0 |
| 0°-180° | 8729.8 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P633358

CATALOG NUMBER: GWS-SA2E-750-U-SL3-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1310.9 | 15.0 | | | |
| FM (30°-60°) | 5023.0 | 57.5 | | | |
| FH (60°-80°) | 953.9 | 10.9 | | | G1/1800 |
| FVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| BL (0°-30°) | 673.0 | 7.7 | B2/1000 | | |
| BM (30°-60°) | 669.3 | 7.7 | B1/1000 | | |
| BH (60°-80°) | 99.7 | 1.1 | B0/110 | | G0/110 |
| BVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G1
 Type II Short





REPORT NUMBER: P633358
 CATALOG NUMBER: GWS-SA2E-750-U-SL3-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 53° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3829.4 | 3829.4 | 3829.4 | 3829.4 | 3829.4 | 3829.4 | 3829.4 | 3829.4 | 3829.4 | 3829.4 | 3829.4 |
| 2.5° | 3775.9 | 3784.4 | 3799.4 | 3818.7 | 3831.5 | 3837.9 | 3837.9 | 3856.1 | 3844.4 | 3834.7 | 3824.0 |
| 5° | 3614.3 | 3622.9 | 3643.2 | 3674.2 | 3705.3 | 3727.7 | 3753.4 | 3772.7 | 3780.2 | 3780.2 | 3762.0 |
| 7.5° | 3386.4 | 3398.2 | 3411.0 | 3453.8 | 3521.2 | 3571.5 | 3615.4 | 3643.2 | 3683.9 | 3696.7 | 3671.0 |
| 10° | 3141.4 | 3153.2 | 3182.1 | 3240.9 | 3317.9 | 3392.8 | 3467.7 | 3503.1 | 3572.6 | 3609.0 | 3580.1 |
| 12.5° | 2933.8 | 2939.2 | 2977.7 | 3048.3 | 3146.8 | 3249.5 | 3340.4 | 3376.8 | 3475.2 | 3529.8 | 3495.6 |
| 15° | 2762.6 | 2765.8 | 2804.4 | 2882.5 | 2995.9 | 3122.1 | 3236.6 | 3274.1 | 3395.0 | 3477.4 | 3426.0 |
| 17.5° | 2633.2 | 2634.2 | 2667.4 | 2751.9 | 2870.7 | 3010.9 | 3146.8 | 3192.8 | 3349.0 | 3448.5 | 3371.4 |
| 20° | 2567.9 | 2564.7 | 2588.2 | 2662.1 | 2774.4 | 2914.6 | 3075.1 | 3131.8 | 3323.3 | 3444.2 | 3329.7 |
| 22.5° | 2569.0 | 2561.5 | 2571.1 | 2623.5 | 2718.8 | 2850.4 | 3030.1 | 3094.3 | 3325.4 | 3462.4 | 3294.4 |
| 25° | 2630.0 | 2619.3 | 2621.4 | 2649.2 | 2716.6 | 2836.5 | 3036.5 | 3105.0 | 3368.2 | 3523.4 | 3281.6 |
| 27.5° | 2732.7 | 2720.9 | 2720.9 | 2734.8 | 2771.2 | 2880.3 | 3116.8 | 3194.9 | 3482.7 | 3642.1 | 3308.3 |
| 30° | 2865.4 | 2853.6 | 2849.3 | 2863.2 | 2893.2 | 2993.7 | 3295.5 | 3376.8 | 3678.5 | 3836.9 | 3393.9 |
| 32.5° | 3017.3 | 3003.4 | 3010.9 | 3030.1 | 3059.0 | 3198.1 | 3525.5 | 3633.6 | 3923.5 | 4099.0 | 3548.0 |
| 35° | 3177.8 | 3166.0 | 3200.3 | 3242.0 | 3286.9 | 3481.7 | 3843.3 | 3937.5 | 4224.2 | 4425.4 | 3783.4 |
| 37.5° | 3330.8 | 3325.4 | 3397.1 | 3484.9 | 3577.9 | 3821.9 | 4166.4 | 4239.2 | 4482.1 | 4780.6 | 4071.2 |
| 40° | 3483.8 | 3482.7 | 3605.8 | 3759.8 | 3908.6 | 4161.1 | 4411.4 | 4471.4 | 4639.3 | 5056.6 | 4347.2 |
| 42.5° | 3655.0 | 3655.0 | 3825.1 | 4030.5 | 4228.5 | 4447.8 | 4591.2 | 4617.9 | 4710.0 | 5216.1 | 4554.8 |
| 45° | 3818.7 | 3828.3 | 4025.2 | 4263.8 | 4498.1 | 4671.4 | 4715.3 | 4717.5 | 4738.9 | 5310.2 | 4727.1 |
| 47.5° | 3948.2 | 3956.7 | 4192.1 | 4467.1 | 4719.6 | 4841.6 | 4848.0 | 4838.4 | 4814.8 | 5400.1 | 4859.8 |
| 50° | 4053.0 | 4065.8 | 4311.9 | 4603.0 | 4871.5 | 5005.3 | 5054.5 | 5044.9 | 4984.9 | 5496.4 | 4952.8 |
| 52.5° | 4104.4 | 4122.6 | 4353.7 | 4670.4 | 5040.6 | 5285.6 | 5422.6 | 5445.0 | 5239.6 | 5549.9 | 5041.7 |
| 55° | 3693.5 | 3720.3 | 3933.2 | 4366.5 | 5134.7 | 5718.9 | 5934.0 | 5929.7 | 5515.6 | 5709.3 | 5257.8 |
| 57.5° | 2789.4 | 2787.2 | 2963.8 | 3437.8 | 4385.8 | 5743.5 | 6248.6 | 6240.0 | 5773.5 | 5894.4 | 5479.3 |
| 60° | 1899.2 | 1886.3 | 1933.4 | 2162.4 | 3066.5 | 4678.9 | 5686.8 | 5802.4 | 5590.5 | 5445.0 | 4652.2 |
| 62.5° | 1563.2 | 1551.4 | 1536.5 | 1473.3 | 1761.2 | 2914.6 | 3928.9 | 4104.4 | 4076.5 | 3784.4 | 2917.8 |
| 65° | 1279.7 | 1289.3 | 1331.0 | 1304.3 | 1225.1 | 1494.7 | 2039.3 | 2143.1 | 1959.1 | 1648.8 | 1019.7 |
| 67.5° | 943.7 | 948.0 | 1002.6 | 1143.8 | 1101.0 | 995.1 | 959.8 | 976.9 | 572.4 | 263.2 | 170.1 |
| 70° | 557.4 | 560.7 | 610.9 | 800.3 | 893.4 | 764.0 | 648.4 | 638.8 | 226.8 | 70.6 | 77.0 |
| 72.5° | 315.6 | 309.2 | 318.8 | 380.9 | 486.8 | 405.5 | 333.8 | 303.9 | 68.5 | 39.6 | 39.6 |
| 75° | 149.8 | 145.5 | 125.2 | 117.7 | 107.0 | 68.5 | 42.8 | 36.4 | 17.1 | 16.0 | 16.0 |
| 77.5° | 1.1 | 3.2 | 2.1 | 3.2 | 3.2 | 2.1 | 1.1 | 1.1 | 3.2 | 3.2 | 4.3 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P633358

CATALOG NUMBER: GWS-SA2E-750-U-SL3-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3829.4 | 3829.4 | 3829.4 | 3829.4 | 3829.4 | 3829.4 | 3829.4 | 3829.4 | 3829.4 | 3829.4 | 3829.4 |
| 2.5° | 3804.8 | 3772.7 | 3765.2 | 3763.1 | 3733.1 | 3701.0 | 3667.8 | 3655.0 | 3635.7 | 3624.0 | 3633.6 |
| 5° | 3733.1 | 3687.1 | 3646.4 | 3609.0 | 3542.6 | 3469.9 | 3406.8 | 3366.1 | 3327.6 | 3301.9 | 3308.3 |
| 7.5° | 3631.4 | 3571.5 | 3478.4 | 3383.2 | 3261.2 | 3152.1 | 3030.1 | 2955.2 | 2885.7 | 2847.2 | 2865.4 |
| 10° | 3523.4 | 3444.2 | 3295.5 | 3133.9 | 2942.4 | 2771.2 | 2596.8 | 2454.5 | 2372.1 | 2294.0 | 2302.6 |
| 12.5° | 3417.5 | 3312.6 | 3090.0 | 2845.0 | 2603.2 | 2350.7 | 2087.5 | 1890.6 | 1755.8 | 1658.4 | 1643.5 |
| 15° | 3319.0 | 3184.2 | 2890.0 | 2566.8 | 2237.3 | 1901.3 | 1565.4 | 1284.0 | 1127.7 | 1031.4 | 1025.0 |
| 17.5° | 3231.3 | 3064.4 | 2682.4 | 2275.8 | 1862.8 | 1432.7 | 1046.4 | 835.6 | 745.8 | 704.0 | 699.8 |
| 20° | 3146.8 | 2943.5 | 2470.5 | 1980.5 | 1454.1 | 1005.8 | 722.2 | 624.9 | 596.0 | 578.8 | 581.0 |
| 22.5° | 3065.4 | 2811.9 | 2248.0 | 1653.1 | 1090.3 | 706.2 | 559.6 | 522.1 | 518.9 | 521.1 | 522.1 |
| 25° | 2997.0 | 2691.0 | 2019.0 | 1337.5 | 777.9 | 538.2 | 467.6 | 456.9 | 466.5 | 480.4 | 482.6 |
| 27.5° | 2961.7 | 2592.5 | 1795.4 | 1019.7 | 562.8 | 437.6 | 405.5 | 409.8 | 426.9 | 441.9 | 444.0 |
| 30° | 2971.3 | 2518.7 | 1564.3 | 739.3 | 433.3 | 369.1 | 358.4 | 367.0 | 384.1 | 398.0 | 400.2 |
| 32.5° | 3039.8 | 2481.2 | 1327.8 | 538.2 | 356.3 | 322.1 | 317.8 | 324.2 | 339.2 | 349.9 | 350.9 |
| 35° | 3175.6 | 2489.8 | 1103.1 | 411.9 | 306.0 | 286.7 | 285.7 | 290.0 | 297.4 | 304.9 | 306.0 |
| 37.5° | 3375.7 | 2559.3 | 881.6 | 342.4 | 277.1 | 263.2 | 258.9 | 258.9 | 264.3 | 267.5 | 269.6 |
| 40° | 3590.8 | 2664.2 | 706.2 | 302.8 | 256.8 | 241.8 | 233.3 | 230.0 | 234.3 | 238.6 | 239.7 |
| 42.5° | 3768.4 | 2769.1 | 573.5 | 275.0 | 240.7 | 220.4 | 209.7 | 207.6 | 212.9 | 220.4 | 222.6 |
| 45° | 3904.3 | 2850.4 | 478.3 | 252.5 | 222.6 | 200.1 | 188.3 | 188.3 | 197.9 | 210.8 | 212.9 |
| 47.5° | 4028.4 | 2915.6 | 407.7 | 232.2 | 205.4 | 181.9 | 170.1 | 172.3 | 188.3 | 205.4 | 208.6 |
| 50° | 4112.9 | 2968.1 | 355.2 | 214.0 | 191.5 | 166.9 | 156.2 | 160.5 | 179.8 | 200.1 | 203.3 |
| 52.5° | 4203.9 | 3032.3 | 321.0 | 197.9 | 178.7 | 155.1 | 145.5 | 148.7 | 170.1 | 192.6 | 196.9 |
| 55° | 4455.3 | 3247.3 | 319.9 | 176.5 | 156.2 | 139.1 | 134.8 | 135.9 | 157.3 | 183.0 | 188.3 |
| 57.5° | 4660.7 | 3436.7 | 341.3 | 148.7 | 130.5 | 122.0 | 119.8 | 120.9 | 140.2 | 169.1 | 175.5 |
| 60° | 3856.1 | 2670.6 | 282.5 | 123.0 | 109.1 | 107.0 | 103.8 | 105.9 | 124.1 | 149.8 | 155.1 |
| 62.5° | 2282.2 | 1526.8 | 134.8 | 94.2 | 93.1 | 90.9 | 87.7 | 92.0 | 109.1 | 131.6 | 134.8 |
| 65° | 780.0 | 452.6 | 85.6 | 77.0 | 79.2 | 76.0 | 72.8 | 77.0 | 92.0 | 104.9 | 105.9 |
| 67.5° | 149.8 | 119.8 | 68.5 | 64.2 | 65.3 | 58.8 | 57.8 | 62.1 | 70.6 | 72.8 | 71.7 |
| 70° | 78.1 | 69.5 | 52.4 | 52.4 | 50.3 | 41.7 | 41.7 | 46.0 | 46.0 | 42.8 | 41.7 |
| 72.5° | 40.7 | 38.5 | 34.2 | 38.5 | 32.1 | 25.7 | 25.7 | 27.8 | 25.7 | 21.4 | 21.4 |
| 75° | 16.0 | 16.0 | 15.0 | 19.3 | 13.9 | 11.8 | 10.7 | 12.8 | 9.6 | 7.5 | 7.5 |
| 77.5° | 4.3 | 4.3 | 4.3 | 5.3 | 3.2 | 3.2 | 2.1 | 2.1 | 1.1 | 0.0 | 0.0 |
| 80° | 0.0 | 1.1 | 0.0 | 1.1 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-4-R4

Test Date: 10/02/2019

Luminaire Tested: SA1C-750-U-5WQ

Data in this report applies to families of products SA1C-760-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-4-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: MCGRAW-EDISON
 Catalog Number: **SA1C-750-U-5WQ**
 Description: MCGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 4884 | CRI (Ra): | 73.5 | R9: | -28.4 |
| CIE u': | 0.2101 | R1: | 70.5 | R10: | 48.6 |
| CIE v': | 0.4904 | R2: | 77.7 | R11: | 73.2 |
| Duv: | 0.0037 | R3: | 84.6 | R12: | 50.7 |
| CIE x: | 0.3493 | R4: | 74.7 | R13: | 71.2 |
| CIE y: | 0.3624 | R5: | 71.9 | R14: | 91.4 |
| CIE z: | 0.2884 | R6: | 70.7 | | |
| Peak Wavelength (nm): | 444 | R7: | 81.2 | | |
| Dominant Wavelength (nm): | 571 | R8: | 56.9 | | |
| Purity: | 13.7 | | | | |
| Rf: | 74.9 | | | | |
| Rg: | 96.3 | | | | |



Test Conditions

Stabilization Time: 240M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-4-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-4-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-4-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 13493.5 S/P: 1.77

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 5378.9 M/P: 0.71

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Summary

$R_f = 74.9$
 $R_g = 96.3$
 CIE $R_a = 73.5$
 $R_g = -28.4$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 61 | CES51 = 90 | CES76 = 52 |
| CES02 = 60 | CES27 = 84 | CES52 = 91 | CES77 = 71 |
| CES03 = 30 | CES28 = 81 | CES53 = 79 | CES78 = 54 |
| CES04 = 69 | CES29 = 58 | CES54 = 83 | CES79 = 80 |
| CES05 = 46 | CES30 = 67 | CES55 = 83 | CES80 = 77 |
| CES06 = 50 | CES31 = 63 | CES56 = 73 | CES81 = 77 |
| CES07 = 39 | CES32 = 59 | CES57 = 72 | CES82 = 90 |
| CES08 = 38 | CES33 = 69 | CES58 = 73 | CES83 = 86 |
| CES09 = 29 | CES34 = 69 | CES59 = 88 | CES84 = 88 |
| CES10 = 73 | CES35 = 83 | CES60 = 93 | CES85 = 84 |
| CES11 = 56 | CES36 = 95 | CES61 = 88 | CES86 = 75 |
| CES12 = 61 | CES37 = 78 | CES62 = 85 | CES87 = 78 |
| CES13 = 41 | CES38 = 76 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 93 | CES64 = 74 | CES89 = 75 |
| CES15 = 70 | CES40 = 86 | CES65 = 67 | CES90 = 77 |
| CES16 = 46 | CES41 = 87 | CES66 = 69 | CES91 = 89 |
| CES17 = 49 | CES42 = 78 | CES67 = 67 | CES92 = 66 |
| CES18 = 55 | CES43 = 75 | CES68 = 73 | CES93 = 80 |
| CES19 = 71 | CES44 = 99 | CES69 = 81 | CES94 = 57 |
| CES20 = 64 | CES45 = 83 | CES70 = 63 | CES95 = 71 |
| CES21 = 85 | CES46 = 81 | CES71 = 60 | CES96 = 78 |
| CES22 = 77 | CES47 = 80 | CES72 = 86 | CES97 = 85 |
| CES23 = 91 | CES48 = 72 | CES73 = 53 | CES98 = 75 |
| CES24 = 90 | CES49 = 81 | CES74 = 96 | CES99 = 62 |
| CES25 = 71 | CES50 = 89 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Measure Comparisons



(END OF REPORT)