

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P832846

Luminaire Tested: **TTN-D0-740-U-RW-CG-UPL1**

Issue Date: 5/15/2024

**Test Information**

Test Method: LM-79-08  
Report Number: P832846  
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND  
Test Lab: INNOVATION CENTER  
Issue Date: 5/15/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: TTN-D0-740-U-RW-CG-UPL1  
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT  
4000K, 70 CRI LEDS AND RECTANGULAR DISTRIBUTION WITH CLEAR GLASS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1434.9 lumens  
Efficiency: N/A  
Efficacy: 107.9 lumens/watt  
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')  
IES Classification: Type II - Short  
BUG Rating: B1 - U3 - G1  
  
Input Watts (W): 13.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P832846  
 CATALOG NUMBER: TTN-D0-740-U-RW-CG-UPL1

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.2 fc  
 Type II - Short - N/A

REPORT NUMBER: P832846  
CATALOG NUMBER: TTN-D0-740-U-RW-CG-UPL1

### Luminous Intensity Polar Plot



— Vertical Plane Through 90-Deg Lateral    - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P832846  
 CATALOG NUMBER: TTN-D0-740-U-RW-CG-UPL1


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	555.7	161.7	717.4
	% Fixture	38.7	11.3	50.0
<b>Street Side</b>	Lumens	555.7	161.7	717.4
	% Fixture	38.7	11.3	50.0
<b>Total</b>	Lumens	1111.4	323.4	1434.9
	% Fixture	77.5	22.5	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	9.5	0.7
10°-20°	30.7	2.1
20°-30°	65.3	4.6
30°-40°	120.4	8.4
40°-50°	193.9	13.5
50°-60°	262.4	18.3
60°-70°	255.2	17.8
70°-80°	148.5	10.3
80°-90°	25.5	1.8
90°-100°	7.2	0.5
100°-110°	73.4	5.1
110°-120°	107.3	7.5
120°-130°	62.3	4.3
130°-140°	33.0	2.3
140°-150°	19.6	1.4
150°-160°	12.1	0.8
160°-170°	6.6	0.5
170°-180°	2.1	0.1
0°-90°	1111.4	77.5
0°-180°	1434.9	100.0




REPORT NUMBER: P832846  
 CATALOG NUMBER: TTN-D0-740-U-RW-CG-UPL1

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	52.8	3.7			
FM (30°-60°)	288.4	20.1			
FH (60°-80°)	201.8	14.1			G0/660
FVH (80°-90°)	12.8	0.9			G1/100
BL (0°-30°)	52.8	3.7	B0/110		
BM (30°-60°)	288.4	20.1	B1/1000		
BH (60°-80°)	201.8	14.1	B1/500		G1/500
BVH (80°-90°)	12.8	0.9			G1/100
UL (90°-100°)	7.2	0.5		U1/10	
UH (100°-180°)	316.2	22.0		U3/500	

**BUG Rating: B1-U3-G1**  
 Type II Short





REPORT NUMBER: P832846

CATALOG NUMBER: TTN-D0-740-U-RW-CG-UPL1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	100.0	100.0	100.0	100.0	100.0	100.0	100.0	100.0	100.0	100.0	100.0
2.5°	100.0	100.0	100.0	100.0	99.0	99.0	99.0	98.0	98.0	98.0	98.0
5°	100.0	100.0	100.0	101.0	101.0	101.0	100.0	100.0	100.0	100.0	100.0
7.5°	100.0	101.0	101.0	100.0	100.0	99.0	99.0	99.0	98.0	98.0	98.0
10°	100.0	100.0	100.0	100.0	99.0	99.0	100.0	100.0	101.0	101.0	101.0
12.5°	99.0	99.0	100.0	100.0	100.0	101.0	103.0	104.0	105.0	106.0	106.0
15°	100.0	100.0	101.0	102.0	103.0	105.0	108.0	111.0	113.0	114.0	113.0
17.5°	100.0	101.0	102.0	104.0	107.0	110.0	115.0	119.0	123.0	124.0	125.0
20°	102.0	102.0	103.0	107.0	112.0	117.0	124.0	130.9	135.9	137.9	137.9
22.5°	103.0	104.0	105.0	110.0	118.0	126.0	135.9	143.9	150.9	154.9	155.9
25°	106.0	106.0	108.0	115.0	125.0	136.9	149.9	161.9	170.9	175.9	176.9
27.5°	108.0	109.0	112.0	121.0	133.9	148.9	166.9	180.9	191.9	197.9	198.9
30°	110.0	111.0	117.0	127.0	142.9	160.9	181.9	199.9	213.9	220.9	221.9
32.5°	113.0	114.0	121.0	131.9	150.9	172.9	196.9	218.9	238.9	244.9	245.9
35°	116.0	117.0	125.0	137.9	159.9	184.9	212.9	238.9	262.9	270.9	272.9
37.5°	119.0	120.0	128.0	143.9	168.9	197.9	230.9	261.9	287.9	298.9	301.9
40°	122.0	123.0	131.9	149.9	177.9	211.9	249.9	283.9	313.9	326.9	328.9
42.5°	124.0	125.0	134.9	154.9	186.9	224.9	269.9	307.9	339.9	356.9	358.9
45°	127.0	128.0	138.9	161.9	194.9	239.9	288.9	334.9	371.9	390.8	392.8
47.5°	129.0	129.9	141.9	165.9	203.9	253.9	308.9	358.9	402.8	422.8	428.8
50°	129.9	130.9	143.9	169.9	209.9	263.9	324.9	382.9	429.8	454.8	457.8
52.5°	129.9	131.9	144.9	172.9	213.9	272.9	337.9	402.8	455.8	483.8	484.8
55°	129.0	129.9	143.9	171.9	215.9	276.9	346.9	414.8	473.8	500.8	509.8
57.5°	125.0	126.0	139.9	168.9	211.9	274.9	344.9	417.8	477.8	503.8	514.8
60°	119.0	121.0	133.9	161.9	205.9	267.9	338.9	411.8	471.8	503.8	504.8
62.5°	112.0	113.0	126.0	152.9	196.9	256.9	327.9	399.8	457.8	490.8	489.8
65°	102.0	103.0	114.0	141.9	180.9	235.9	305.9	380.9	430.8	465.8	462.8
67.5°	91.0	92.0	102.0	127.0	161.9	212.9	275.9	348.9	392.8	428.8	426.8
70°	79.0	79.0	88.0	109.0	141.9	186.9	242.9	306.9	350.9	380.9	381.9
72.5°	65.0	65.0	73.0	91.0	119.0	156.9	204.9	261.9	297.9	323.9	325.9
75°	51.0	50.0	57.0	72.0	94.0	125.0	161.9	210.9	238.9	263.9	262.9
77.5°	36.0	36.0	40.0	52.0	68.0	93.0	120.0	158.9	177.9	198.9	194.9
80°	23.0	23.0	25.0	34.0	45.0	62.0	79.0	108.0	121.0	136.9	131.9
82.5°	12.0	11.0	13.0	18.0	24.0	34.0	44.0	63.0	69.0	81.0	77.0
85°	4.0	4.0	4.0	6.0	9.0	13.0	17.0	27.0	28.0	36.0	33.0
87.5°	1.0	0.0	0.0	1.0	1.0	1.0	1.0	3.0	3.0	6.0	4.0
90°	2.8	2.8	3.3	3.3	3.3	3.3	3.3	3.3	3.3	2.8	2.8
92.5°	2.8	2.8	2.8	3.9	4.4	3.9	4.4	3.3	3.3	2.8	2.8
95°	3.3	3.3	3.9	5.0	6.1	6.6	6.6	3.9	3.9	3.3	3.3
97.5°	4.4	5.0	5.0	6.1	10.0	18.3	11.1	5.5	5.5	5.0	4.4
100°	7.2	7.7	7.7	13.8	29.3	39.3	28.2	14.4	10.5	7.7	7.7
102.5°	23.2	24.3	29.9	44.8	66.4	60.3	50.9	48.1	33.2	26.6	25.5
105°	59.2	58.7	63.1	74.7	93.0	91.3	84.1	76.4	65.8	60.9	60.9
107.5°	78.0	78.0	81.9	91.9	105.7	123.4	125.1	99.0	86.9	81.3	80.8
110°	88.0	88.0	91.3	99.6	117.9	142.8	141.6	122.3	107.3	100.2	99.0



REPORT NUMBER: P832846  
 CATALOG NUMBER: TTN-D0-740-U-RW-CG-UPL1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	90.2	90.7	95.2	107.9	127.8	138.9	133.9	126.2	119.5	114.0	112.9
115°	93.5	93.5	98.5	110.7	121.7	126.2	120.6	114.5	110.1	107.9	109.0
117.5°	92.4	94.1	95.2	101.8	109.0	112.3	109.6	101.3	97.9	96.8	95.2
120°	85.8	85.8	86.9	90.2	94.1	95.7	94.6	89.1	86.3	85.8	84.7
122.5°	76.4	76.9	76.4	78.0	80.8	82.4	81.3	76.9	75.8	75.8	74.7
125°	67.0	67.0	66.4	67.5	69.2	68.6	69.2	67.0	66.4	66.4	65.8
127.5°	60.3	59.8	58.7	59.2	59.8	59.8	60.3	58.1	58.7	59.2	58.7
130°	53.7	53.7	52.6	52.6	52.6	51.5	52.6	51.5	52.0	52.6	53.1
132.5°	47.6	47.6	45.9	45.4	45.4	45.4	45.9	45.4	46.5	47.6	47.6
135°	42.6	42.6	40.9	41.5	41.5	40.9	41.5	40.9	42.1	42.6	42.6
137.5°	38.7	38.7	37.6	37.6	37.6	37.1	37.6	37.6	38.2	39.3	39.8
140°	35.4	35.4	34.9	34.9	34.3	34.9	34.9	34.9	35.4	36.0	36.0
142.5°	33.8	33.2	32.6	32.1	32.6	32.6	32.6	32.1	32.6	33.8	33.8
145°	31.0	31.0	30.4	30.4	30.4	31.0	30.4	30.4	31.0	31.0	31.5
147.5°	29.3	29.3	28.8	29.3	29.3	29.3	29.3	28.8	29.3	29.3	29.9
150°	28.8	28.2	27.7	28.2	28.2	27.7	27.7	27.7	27.7	28.2	28.2
152.5°	27.1	27.1	26.6	27.1	26.6	26.6	26.6	26.6	26.6	27.1	27.7
155°	26.0	26.0	25.5	26.0	26.0	26.0	26.0	26.0	26.0	26.0	26.0
157.5°	24.9	25.5	24.9	24.9	24.9	24.9	24.9	24.9	24.9	25.5	25.5
160°	24.3	24.3	24.3	24.3	23.8	23.8	23.8	24.3	24.3	24.3	24.9
162.5°	23.8	23.8	23.8	23.8	23.2	23.2	23.2	23.2	23.8	23.8	24.3
165°	23.8	23.2	23.2	23.2	22.7	22.7	22.7	22.7	23.2	23.8	23.2
167.5°	22.7	22.7	22.7	22.7	22.7	22.1	22.1	22.7	22.7	22.7	23.2
170°	22.7	22.7	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.7
172.5°	22.7	22.7	22.7	22.7	22.1	22.1	22.1	22.1	22.1	22.7	22.7
175°	22.7	22.7	22.7	22.7	22.1	22.1	22.1	22.7	22.7	22.7	22.1
177.5°	22.7	22.7	22.7	22.7	22.1	22.7	22.7	22.7	22.7	22.7	22.7
180°	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7

(END OF REPORT)