

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P833196

Luminaire Tested: **TTN-D1-740-U-DL-CG-UPL3**

Issue Date: 5/15/2024

Test Information

Test Method: LM-79-08
Report Number: P833196
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND
Test Lab: INNOVATION CENTER
Issue Date: 5/15/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: TTN-D1-740-U-DL-CG-UPL3
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT
4000K, 70 CRI LEDS AND DRIVE LANE DISTRIBUTION WITH CLEAR GLASS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3971.6 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')
IES Classification: Type IV - Short
BUG Rating: B1 - U4 - G1


Input Watts (W): 33.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P833196
 CATALOG NUMBER: TTN-D1-740-U-DL-CG-UPL3

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.8 fc
 Type IV - Short - N/A

REPORT NUMBER: P833196
CATALOG NUMBER: TTN-D1-740-U-DL-CG-UPL3

Luminous Intensity Polar Plot



— Vertical Plane Through 33-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P833196
 CATALOG NUMBER: TTN-D1-740-U-DL-CG-UPL3


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	697.6	405.8	1103.4
	% Fixture	17.6	10.2	27.8
Street Side	Lumens	2462.5	405.8	2868.2
	% Fixture	62.0	10.2	72.2
Total	Lumens	3160.1	811.5	3971.6
	% Fixture	79.6	20.4	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.3	0.7
10°-20°	91.9	2.3
20°-30°	193.7	4.9
30°-40°	351.8	8.9
40°-50°	555.9	14.0
50°-60°	738.2	18.6
60°-70°	710.5	17.9
70°-80°	417.1	10.5
80°-90°	72.7	1.8
90°-100°	18.1	0.5
100°-110°	184.1	4.6
110°-120°	269.1	6.8
120°-130°	156.2	3.9
130°-140°	82.7	2.1
140°-150°	49.1	1.2
150°-160°	30.3	0.8
160°-170°	16.5	0.4
170°-180°	5.4	0.1
0°-90°	3160.1	79.6
0°-180°	3971.6	100.0

Coefficient of Utilization




REPORT NUMBER: P833196
 CATALOG NUMBER: TTN-D1-740-U-DL-CG-UPL3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	211.3	5.3			
FM (30°-60°)	1278.0	32.2			
FH (60°-80°)	912.1	23.0			G1/1800
FVH (80°-90°)	61.0	1.5			G1/100
BL (0°-30°)	102.6	2.6	B0/110		
BM (30°-60°)	367.8	9.3	B1/1000		
BH (60°-80°)	215.6	5.4	B1/500		G1/500
BVH (80°-90°)	11.7	0.3			G1/100
UL (90°-100°)	18.1	0.5		U2/50	
UH (100°-180°)	793.4	20.0		U4/1000	

BUG Rating: B1-U4-G1

Type IV Short





REPORT NUMBER: P833196

CATALOG NUMBER: TTN-D1-740-U-DL-CG-UPL3

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	33°	35°	45°	55°	65°	75°	85°
0°	296.1	296.1	296.1	296.1	296.1	296.1	296.1	296.1	296.1	296.1	296.1
2.5°	315.4	318.2	315.4	315.4	312.7	312.7	309.9	307.1	304.4	301.6	296.1
5°	351.4	351.4	348.6	343.1	340.3	337.6	332.0	323.7	318.2	309.9	301.6
7.5°	368.0	368.0	365.3	359.7	354.2	351.4	343.1	332.0	323.7	312.7	301.6
10°	390.2	392.9	387.4	381.9	376.3	373.6	362.5	348.6	334.8	321.0	304.4
12.5°	415.1	417.8	415.1	406.8	398.5	395.7	384.6	368.0	351.4	332.0	312.7
15°	448.3	453.8	445.5	440.0	431.7	428.9	415.1	395.7	376.3	351.4	326.5
17.5°	487.0	489.8	484.2	475.9	470.4	467.6	453.8	431.7	404.0	376.3	345.9
20°	531.3	534.0	531.3	520.2	514.7	511.9	498.1	473.2	440.0	409.5	370.8
22.5°	583.8	589.4	581.1	572.8	567.2	567.2	550.6	523.0	484.2	445.5	401.2
25°	644.7	653.0	642.0	636.4	630.9	628.1	614.3	581.1	536.8	489.8	434.4
27.5°	719.4	725.0	716.7	713.9	702.8	702.8	680.7	642.0	594.9	539.6	475.9
30°	785.8	791.4	785.8	785.8	777.5	774.8	752.6	713.9	655.8	589.4	511.9
32.5°	849.5	855.0	852.3	855.0	852.3	849.5	821.8	780.3	722.2	636.4	547.9
35°	913.1	921.4	918.7	927.0	924.2	921.4	899.3	849.5	780.3	694.5	586.6
37.5°	979.5	987.8	987.8	996.1	998.9	998.9	974.0	921.4	844.0	747.1	630.9
40°	1051.5	1059.8	1059.8	1073.6	1079.2	1079.2	1051.5	998.9	913.1	805.2	677.9
42.5°	1120.7	1129.0	1131.7	1145.6	1153.9	1156.6	1134.5	1073.6	974.0	863.3	722.2
45°	1187.1	1195.4	1203.7	1231.3	1245.2	1242.4	1225.8	1162.2	1051.5	924.2	769.2
47.5°	1250.7	1261.8	1275.6	1311.6	1331.0	1328.2	1317.1	1245.2	1123.4	982.3	810.7
50°	1300.5	1308.8	1336.5	1375.2	1400.1	1402.9	1386.3	1317.1	1184.3	1026.6	841.2
52.5°	1339.3	1350.3	1383.5	1438.9	1458.2	1466.5	1447.2	1378.0	1245.2	1065.3	866.1
55°	1366.9	1366.9	1416.7	1480.4	1508.0	1513.6	1513.6	1427.8	1281.1	1090.2	879.9
57.5°	1353.1	1353.1	1408.4	1477.6	1521.9	1519.1	1513.6	1430.6	1286.7	1084.7	871.6
60°	1314.4	1322.7	1375.2	1444.4	1488.7	1485.9	1469.3	1394.6	1259.0	1062.5	855.0
62.5°	1261.8	1275.6	1331.0	1383.5	1433.3	1441.6	1419.5	1353.1	1212.0	1029.3	824.6
65°	1162.2	1181.5	1250.7	1308.8	1347.6	1364.2	1336.5	1275.6	1148.3	965.7	760.9
67.5°	1051.5	1065.3	1123.4	1206.4	1228.6	1245.2	1231.3	1167.7	1059.8	863.3	689.0
70°	924.2	946.3	985.1	1068.1	1093.0	1109.6	1109.6	1045.9	943.6	758.2	603.2
72.5°	774.8	799.7	846.7	907.6	940.8	951.9	949.1	896.5	805.2	642.0	509.1
75°	611.5	630.9	686.2	730.5	766.5	774.8	772.0	727.7	644.7	517.4	404.0
77.5°	451.0	470.4	511.9	545.1	578.3	572.8	572.8	539.6	487.0	384.6	307.1
80°	296.1	312.7	348.6	359.7	395.7	392.9	392.9	368.0	332.0	257.3	204.8
82.5°	163.3	177.1	202.0	213.1	235.2	229.7	232.4	215.8	193.7	143.9	116.2
85°	58.1	69.2	83.0	91.3	102.4	102.4	102.4	88.5	83.0	55.3	47.0
87.5°	2.8	5.5	11.1	11.1	16.6	16.6	16.6	11.1	11.1	2.8	2.8
90°	6.9	6.9	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	6.9
92.5°	6.9	6.9	6.9	9.7	10.8	11.1	9.7	11.1	8.3	8.3	6.9
95°	8.3	8.3	9.7	12.5	14.7	15.3	16.7	16.7	9.7	9.7	8.3
97.5°	11.1	12.5	12.5	15.3	23.1	25.0	45.8	27.8	13.9	13.9	12.5
100°	18.0	19.4	19.4	34.7	65.8	73.6	98.6	70.8	36.1	26.4	19.4
102.5°	58.3	61.1	75.0	112.5	155.8	166.6	151.3	127.7	120.8	83.3	66.6
105°	148.6	147.2	158.3	187.4	224.1	233.3	229.1	211.0	191.6	165.2	152.7
107.5°	195.8	195.8	205.5	230.5	258.3	265.2	309.6	313.8	248.5	218.0	204.1
110°	220.8	220.8	229.1	249.9	286.5	295.7	358.2	355.4	306.8	269.4	251.3



REPORT NUMBER: P833196
 CATALOG NUMBER: TTN-D1-740-U-DL-CG-UPL3

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	33°	35°	45°	55°	65°	75°	85°
112.5°	226.3	227.7	238.8	270.7	310.7	320.7	348.5	336.0	316.6	299.9	286.0
115°	234.6	234.6	247.1	277.7	299.9	305.5	316.6	302.7	287.4	276.3	270.7
117.5°	231.9	236.0	238.8	255.5	269.9	273.5	281.8	274.9	254.1	245.8	243.0
120°	215.2	215.2	218.0	226.3	234.1	236.0	240.2	237.4	223.5	216.6	215.2
122.5°	191.6	193.0	191.6	195.8	201.3	202.7	206.9	204.1	193.0	190.2	190.2
125°	168.0	168.0	166.6	169.4	172.8	173.6	172.2	173.6	168.0	166.6	166.6
127.5°	151.3	149.9	147.2	148.6	149.6	149.9	149.9	151.3	145.8	147.2	148.6
130°	134.7	134.7	131.9	131.9	131.9	131.9	129.1	131.9	129.1	130.5	131.9
132.5°	119.4	119.4	115.2	113.9	113.9	113.9	113.9	115.2	113.9	116.6	119.4
135°	106.9	106.9	102.7	104.1	104.1	104.1	102.7	104.1	102.7	105.5	106.9
137.5°	97.2	97.2	94.4	94.4	94.4	94.4	93.0	94.4	94.4	95.8	98.6
140°	88.9	88.9	87.5	87.5	86.4	86.1	87.5	87.5	87.5	88.9	90.2
142.5°	84.7	83.3	81.9	80.5	81.6	81.9	81.9	81.9	80.5	81.9	84.7
145°	77.8	77.8	76.4	76.4	76.4	76.4	77.8	76.4	76.4	77.8	77.8
147.5°	73.6	73.6	72.2	73.6	73.6	73.6	73.6	73.6	72.2	73.6	73.6
150°	72.2	70.8	69.4	70.8	70.8	70.8	69.4	69.4	69.4	69.4	70.8
152.5°	68.0	68.0	66.6	68.0	66.9	66.6	66.6	66.6	66.6	66.6	68.0
155°	65.3	65.3	63.9	65.3	65.3	65.3	65.3	65.3	65.3	65.3	65.3
157.5°	62.5	63.9	62.5	62.5	62.5	62.5	62.5	62.5	62.5	62.5	63.9
160°	61.1	61.1	61.1	61.1	60.0	59.7	59.7	59.7	61.1	61.1	61.1
162.5°	59.7	59.7	59.7	59.7	58.6	58.3	58.3	58.3	58.3	59.7	59.7
165°	59.7	58.3	58.3	58.3	57.2	56.9	56.9	56.9	56.9	58.3	59.7
167.5°	56.9	56.9	56.9	56.9	56.9	56.9	55.5	55.5	56.9	56.9	56.9
170°	56.9	56.9	55.5	55.5	55.5	55.5	55.5	55.5	55.5	55.5	55.5
172.5°	56.9	56.9	56.9	56.9	55.8	55.5	55.5	55.5	55.5	55.5	56.9
175°	56.9	56.9	56.9	56.9	55.8	55.5	55.5	55.5	56.9	56.9	56.9
177.5°	56.9	56.9	56.9	56.9	55.8	55.5	56.9	56.9	56.9	56.9	56.9
180°	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9



REPORT NUMBER: P833196

CATALOG NUMBER: TTN-D1-740-U-DL-CG-UPL3

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	296.1	296.1	296.1	296.1	296.1	296.1	296.1	296.1	296.1	296.1	296.1
2.5°	293.3	290.5	287.8	282.2	279.5	276.7	273.9	271.2	271.2	271.2	271.2
5°	296.1	293.3	285.0	276.7	268.4	260.1	254.6	251.8	249.0	246.3	246.3
7.5°	296.1	290.5	279.5	268.4	260.1	249.0	240.7	232.4	226.9	224.1	224.1
10°	298.8	290.5	276.7	265.6	251.8	238.0	226.9	215.8	210.3	204.8	204.8
12.5°	304.4	296.1	276.7	262.9	246.3	229.7	215.8	204.8	196.5	190.9	190.9
15°	315.4	304.4	282.2	262.9	243.5	224.1	210.3	196.5	188.2	182.6	182.6
17.5°	332.0	318.2	290.5	262.9	240.7	221.4	204.8	190.9	179.9	174.3	174.3
20°	351.4	334.8	301.6	268.4	240.7	218.6	202.0	185.4	174.3	168.8	168.8
22.5°	379.1	354.2	315.4	276.7	246.3	221.4	199.2	182.6	171.6	166.0	166.0
25°	409.5	381.9	332.0	287.8	251.8	221.4	199.2	182.6	171.6	166.0	163.3
27.5°	442.7	412.3	351.4	298.8	257.3	226.9	202.0	182.6	171.6	166.0	166.0
30°	473.2	437.2	370.8	312.7	265.6	229.7	204.8	185.4	171.6	166.0	166.0
32.5°	506.4	464.9	390.2	326.5	273.9	235.2	207.5	188.2	174.3	168.8	166.0
35°	539.6	492.5	409.5	337.6	282.2	240.7	210.3	190.9	177.1	171.6	171.6
37.5°	575.5	523.0	428.9	351.4	290.5	246.3	215.8	193.7	179.9	174.3	174.3
40°	614.3	553.4	448.3	362.5	298.8	251.8	221.4	199.2	185.4	179.9	179.9
42.5°	653.0	586.6	470.4	376.3	307.1	257.3	224.1	204.8	190.9	185.4	185.4
45°	691.8	614.3	489.8	390.2	315.4	265.6	232.4	210.3	196.5	190.9	190.9
47.5°	727.7	644.7	506.4	398.5	323.7	271.2	235.2	215.8	202.0	199.2	196.5
50°	752.6	664.1	517.4	406.8	326.5	273.9	240.7	218.6	207.5	202.0	202.0
52.5°	772.0	683.5	525.7	412.3	329.3	276.7	243.5	224.1	213.1	207.5	204.8
55°	783.1	686.2	525.7	406.8	326.5	276.7	243.5	224.1	213.1	207.5	207.5
57.5°	772.0	672.4	514.7	395.7	318.2	268.4	235.2	218.6	207.5	204.8	202.0
60°	749.9	650.3	492.5	379.1	304.4	254.6	224.1	210.3	202.0	199.2	196.5
62.5°	719.4	622.6	470.4	357.0	285.0	238.0	215.8	199.2	193.7	190.9	188.2
65°	658.6	570.0	434.4	329.3	260.1	218.6	196.5	185.4	179.9	174.3	171.6
67.5°	592.1	511.9	384.6	296.1	229.7	196.5	177.1	166.0	157.7	157.7	155.0
70°	520.2	451.0	332.0	251.8	199.2	171.6	152.2	143.9	138.4	138.4	135.6
72.5°	434.4	379.1	276.7	204.8	163.3	141.1	127.3	119.0	116.2	116.2	113.4
75°	348.6	298.8	218.6	160.5	127.3	110.7	99.6	94.1	91.3	91.3	88.5
77.5°	257.3	218.6	157.7	116.2	91.3	80.2	71.9	69.2	66.4	66.4	63.6
80°	171.6	143.9	102.4	74.7	55.3	49.8	44.3	44.3	41.5	44.3	41.5
82.5°	94.1	77.5	55.3	38.7	27.7	24.9	22.1	22.1	24.9	24.9	22.1
85°	36.0	27.7	19.4	11.1	8.3	8.3	8.3	8.3	8.3	8.3	5.5
87.5°	2.8	2.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	6.9	6.9	8.3	8.3	8.3	8.3	8.3	8.3	8.3	6.9	6.9
92.5°	6.9	6.9	8.3	8.3	11.1	9.7	11.1	9.7	6.9	6.9	6.9
95°	8.3	8.3	9.7	9.7	16.7	16.7	15.3	12.5	9.7	8.3	8.3
97.5°	11.1	12.5	13.9	13.9	27.8	45.8	25.0	15.3	12.5	12.5	11.1
100°	19.4	19.4	26.4	36.1	70.8	98.6	73.6	34.7	19.4	19.4	18.0
102.5°	63.9	66.6	83.3	120.8	127.7	151.3	166.6	112.5	75.0	61.1	58.3
105°	152.7	152.7	165.2	191.6	211.0	229.1	233.3	187.4	158.3	147.2	148.6
107.5°	202.7	204.1	218.0	248.5	313.8	309.6	265.2	230.5	205.5	195.8	195.8
110°	248.5	251.3	269.4	306.8	355.4	358.2	295.7	249.9	229.1	220.8	220.8



REPORT NUMBER: P833196
 CATALOG NUMBER: TTN-D1-740-U-DL-CG-UPL3

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	283.2	286.0	299.9	316.6	336.0	348.5	320.7	270.7	238.8	227.7	226.3
115°	273.5	270.7	276.3	287.4	302.7	316.6	305.5	277.7	247.1	234.6	234.6
117.5°	238.8	243.0	245.8	254.1	274.9	281.8	273.5	255.5	238.8	236.0	231.9
120°	212.4	215.2	216.6	223.5	237.4	240.2	236.0	226.3	218.0	215.2	215.2
122.5°	187.4	190.2	190.2	193.0	204.1	206.9	202.7	195.8	191.6	193.0	191.6
125°	165.2	166.6	166.6	168.0	173.6	172.2	173.6	169.4	166.6	168.0	168.0
127.5°	147.2	148.6	147.2	145.8	151.3	149.9	149.9	148.6	147.2	149.9	151.3
130°	133.3	131.9	130.5	129.1	131.9	129.1	131.9	131.9	131.9	134.7	134.7
132.5°	119.4	119.4	116.6	113.9	115.2	113.9	113.9	113.9	115.2	119.4	119.4
135°	106.9	106.9	105.5	102.7	104.1	102.7	104.1	104.1	102.7	106.9	106.9
137.5°	100.0	98.6	95.8	94.4	94.4	93.0	94.4	94.4	94.4	97.2	97.2
140°	90.2	90.2	88.9	87.5	87.5	87.5	86.1	87.5	87.5	88.9	88.9
142.5°	84.7	84.7	81.9	80.5	81.9	81.9	81.9	80.5	81.9	83.3	84.7
145°	79.1	77.8	77.8	76.4	76.4	77.8	76.4	76.4	76.4	77.8	77.8
147.5°	75.0	73.6	73.6	72.2	73.6	73.6	73.6	73.6	72.2	73.6	73.6
150°	70.8	70.8	69.4	69.4	69.4	69.4	70.8	70.8	69.4	70.8	72.2
152.5°	69.4	68.0	66.6	66.6	66.6	66.6	66.6	68.0	66.6	68.0	68.0
155°	65.3	65.3	65.3	65.3	65.3	65.3	65.3	65.3	63.9	65.3	65.3
157.5°	63.9	63.9	62.5	62.5	62.5	62.5	62.5	62.5	62.5	63.9	62.5
160°	62.5	61.1	61.1	61.1	59.7	59.7	59.7	61.1	61.1	61.1	61.1
162.5°	61.1	59.7	59.7	58.3	58.3	58.3	58.3	59.7	59.7	59.7	59.7
165°	58.3	59.7	58.3	56.9	56.9	56.9	56.9	58.3	58.3	58.3	59.7
167.5°	58.3	56.9	56.9	56.9	55.5	55.5	56.9	56.9	56.9	56.9	56.9
170°	56.9	55.5	55.5	55.5	55.5	55.5	55.5	55.5	55.5	56.9	56.9
172.5°	56.9	56.9	55.5	55.5	55.5	55.5	55.5	56.9	56.9	56.9	56.9
175°	55.5	56.9	56.9	56.9	55.5	55.5	55.5	56.9	56.9	56.9	56.9
177.5°	56.9	56.9	56.9	56.9	56.9	56.9	55.5	56.9	56.9	56.9	56.9
180°	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9

(END OF REPORT)