

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P630965

Luminaire Tested: GWS-SA1E-760-U-T3R-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P630965
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1E-760-U-T3R-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III ROADWAY OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (16) 5700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4794.9 lumens
Efficiency: N/A
Efficacy: 82.1 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B1 - U0 - G0


Input Watts (W): 58.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P630965
 CATALOG NUMBER: GWS-SA1E-760-U-T3R-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 12 fc
 Type II - Short - N/A

REPORT NUMBER: P630965
CATALOG NUMBER: GWS-SA1E-760-U-T3R-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 38-Deg Lateral - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P630965
 CATALOG NUMBER: GWS-SA1E-760-U-T3R-W-GRSBK

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 934.2 | 0.0 | 934.2 |
| | % Fixture | 19.5 | 0.0 | 19.5 |
| Street Side | Lumens | 3860.7 | 0.0 | 3860.7 |
| | % Fixture | 80.5 | 0.0 | 80.5 |
| Total | Lumens | 4794.9 | 0.0 | 4794.9 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 106.3 | 2.2 |
| 10°-20° | 286.2 | 6.0 |
| 20°-30° | 491.2 | 10.2 |
| 30°-40° | 814.6 | 17.0 |
| 40°-50° | 1197.6 | 25.0 |
| 50°-60° | 1399.4 | 29.2 |
| 60°-70° | 474.4 | 9.9 |
| 70°-80° | 24.2 | 0.5 |
| 80°-90° | 0.9 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 4794.9 | 100.0 |
| 0°-180° | 4794.9 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P630965

CATALOG NUMBER: GWS-SA1E-760-U-T3R-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 527.8 | 11.0 | | | |
| FM (30°-60°) | 2896.0 | 60.4 | | | |
| FH (60°-80°) | 436.4 | 9.1 | | | G0/660 |
| FVH (80°-90°) | 0.5 | 0.0 | | | G0/10 |
| BL (0°-30°) | 355.9 | 7.4 | B1/500 | | |
| BM (30°-60°) | 515.6 | 10.8 | B1/1000 | | |
| BH (60°-80°) | 62.2 | 1.3 | B0/110 | | G0/110 |
| BVH (80°-90°) | 0.4 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G0
 Type II Short





REPORT NUMBER: P630965
 CATALOG NUMBER: GWS-SA1E-760-U-T3R-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 38° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1149.9 | 1149.9 | 1149.9 | 1149.9 | 1149.9 | 1149.9 | 1149.9 | 1149.9 | 1149.9 | 1149.9 | 1149.9 |
| 2.5° | 1070.9 | 1068.7 | 1073.1 | 1081.9 | 1090.1 | 1092.9 | 1101.1 | 1112.6 | 1119.7 | 1136.7 | 1150.4 |
| 5° | 1022.7 | 1021.6 | 1026.0 | 1033.7 | 1044.6 | 1048.5 | 1061.1 | 1080.2 | 1099.4 | 1129.0 | 1158.1 |
| 7.5° | 978.9 | 978.3 | 984.9 | 1001.9 | 1017.8 | 1022.7 | 1038.0 | 1061.6 | 1087.4 | 1132.9 | 1175.6 |
| 10° | 921.3 | 921.9 | 934.5 | 958.6 | 987.6 | 997.5 | 1022.2 | 1056.1 | 1089.6 | 1148.2 | 1207.4 |
| 12.5° | 902.7 | 903.8 | 910.3 | 929.0 | 960.8 | 973.4 | 1007.9 | 1059.4 | 1102.2 | 1170.1 | 1248.5 |
| 15° | 948.2 | 948.2 | 942.7 | 944.9 | 959.1 | 970.6 | 1006.8 | 1070.4 | 1123.5 | 1196.4 | 1289.1 |
| 17.5° | 1036.4 | 1033.1 | 1019.4 | 1000.8 | 995.8 | 999.7 | 1028.7 | 1094.0 | 1153.7 | 1227.1 | 1335.1 |
| 20° | 1155.9 | 1157.0 | 1130.1 | 1091.2 | 1060.0 | 1059.4 | 1077.0 | 1135.6 | 1197.0 | 1263.9 | 1385.0 |
| 22.5° | 1300.6 | 1296.2 | 1260.6 | 1207.4 | 1153.1 | 1148.8 | 1155.9 | 1199.2 | 1259.5 | 1321.9 | 1446.4 |
| 25° | 1468.3 | 1466.1 | 1415.7 | 1344.4 | 1272.6 | 1262.2 | 1262.2 | 1305.0 | 1348.8 | 1404.7 | 1519.8 |
| 27.5° | 1643.7 | 1643.7 | 1594.9 | 1512.7 | 1417.3 | 1398.7 | 1395.9 | 1446.4 | 1475.4 | 1486.4 | 1581.7 |
| 30° | 1824.0 | 1821.8 | 1773.6 | 1689.2 | 1587.2 | 1568.0 | 1560.4 | 1597.6 | 1618.5 | 1585.6 | 1659.0 |
| 32.5° | 2007.0 | 2010.9 | 1962.1 | 1883.7 | 1792.7 | 1780.1 | 1756.6 | 1756.6 | 1773.6 | 1727.5 | 1780.7 |
| 35° | 2203.8 | 2202.7 | 2164.3 | 2111.2 | 2033.3 | 2019.1 | 1980.2 | 1919.3 | 1945.1 | 1924.8 | 1948.9 |
| 37.5° | 2377.5 | 2385.8 | 2367.1 | 2327.7 | 2264.6 | 2250.4 | 2186.3 | 2076.1 | 2095.8 | 2127.6 | 2149.0 |
| 40° | 2554.0 | 2560.6 | 2579.2 | 2566.6 | 2487.1 | 2460.8 | 2346.8 | 2166.0 | 2187.9 | 2297.0 | 2358.4 |
| 42.5° | 2727.2 | 2730.5 | 2768.3 | 2789.1 | 2682.8 | 2636.8 | 2468.5 | 2220.8 | 2243.8 | 2429.6 | 2537.0 |
| 45° | 2837.4 | 2844.5 | 2907.0 | 2970.5 | 2855.5 | 2792.4 | 2574.3 | 2290.9 | 2300.8 | 2521.7 | 2669.1 |
| 47.5° | 2833.0 | 2849.4 | 2966.7 | 3082.4 | 3004.0 | 2936.0 | 2701.4 | 2403.3 | 2386.9 | 2608.3 | 2756.3 |
| 50° | 2744.7 | 2764.5 | 2932.7 | 3116.3 | 3110.9 | 3047.8 | 2842.8 | 2566.1 | 2514.6 | 2685.0 | 2767.2 |
| 52.5° | 2561.7 | 2618.7 | 2873.0 | 3120.7 | 3196.9 | 3165.1 | 3017.7 | 2785.3 | 2687.2 | 2795.2 | 2784.8 |
| 55° | 2166.0 | 2236.1 | 2691.6 | 3083.4 | 3274.7 | 3278.6 | 3201.3 | 3013.8 | 2874.6 | 2984.8 | 2892.7 |
| 57.5° | 1644.2 | 1700.1 | 2071.7 | 2744.7 | 3145.9 | 3209.0 | 3272.5 | 3134.4 | 2990.3 | 3114.1 | 2917.9 |
| 60° | 990.9 | 1055.6 | 1297.3 | 2014.2 | 2540.9 | 2648.3 | 2897.7 | 2870.8 | 2697.1 | 2750.2 | 2392.9 |
| 62.5° | 401.7 | 435.7 | 599.0 | 1109.8 | 1599.3 | 1699.6 | 1938.5 | 1979.1 | 1936.3 | 1882.1 | 1451.3 |
| 65° | 146.9 | 160.6 | 240.1 | 458.7 | 735.5 | 772.2 | 898.3 | 970.1 | 1029.3 | 876.4 | 539.9 |
| 67.5° | 91.0 | 99.7 | 156.2 | 235.7 | 267.5 | 248.8 | 253.2 | 302.0 | 288.3 | 178.1 | 96.5 |
| 70° | 67.4 | 74.5 | 122.2 | 163.3 | 108.0 | 83.3 | 56.5 | 60.3 | 54.3 | 47.7 | 47.1 |
| 72.5° | 46.6 | 53.2 | 91.5 | 96.5 | 41.7 | 29.6 | 20.8 | 29.0 | 32.9 | 32.3 | 33.4 |
| 75° | 30.7 | 35.6 | 57.5 | 37.8 | 10.4 | 8.2 | 7.1 | 15.3 | 19.7 | 19.7 | 20.3 |
| 77.5° | 18.1 | 20.8 | 20.3 | 7.7 | 2.2 | 2.2 | 1.6 | 2.7 | 4.4 | 4.9 | 6.0 |
| 80° | 2.2 | 1.6 | 1.1 | 1.1 | 1.1 | 1.1 | 1.1 | 1.1 | 1.6 | 1.6 | 1.6 |
| 82.5° | 0.5 | 0.5 | 0.5 | 1.1 | 1.1 | 1.1 | 1.1 | 1.1 | 1.1 | 1.6 | 1.6 |
| 85° | 0.0 | 0.0 | 0.5 | 0.5 | 1.1 | 1.1 | 1.1 | 1.1 | 1.1 | 1.6 | 1.6 |
| 87.5° | 0.0 | 0.0 | 0.5 | 0.5 | 1.1 | 1.1 | 1.1 | 1.1 | 1.1 | 1.6 | 1.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P630965

CATALOG NUMBER: GWS-SA1E-760-U-T3R-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1149.9 | 1149.9 | 1149.9 | 1149.9 | 1149.9 | 1149.9 | 1149.9 | 1149.9 | 1149.9 | 1149.9 | 1149.9 |
| 2.5° | 1160.8 | 1157.0 | 1172.9 | 1184.4 | 1193.7 | 1198.1 | 1192.1 | 1191.5 | 1191.5 | 1179.4 | 1176.2 |
| 5° | 1174.5 | 1176.2 | 1198.6 | 1208.5 | 1210.1 | 1204.7 | 1191.0 | 1181.6 | 1176.2 | 1163.6 | 1156.4 |
| 7.5° | 1200.8 | 1206.3 | 1227.7 | 1226.0 | 1211.2 | 1186.0 | 1149.9 | 1121.9 | 1103.8 | 1084.1 | 1072.0 |
| 10° | 1238.6 | 1249.1 | 1262.2 | 1239.2 | 1192.1 | 1127.9 | 1053.4 | 1000.2 | 968.4 | 946.0 | 932.3 |
| 12.5° | 1284.7 | 1295.1 | 1290.7 | 1236.4 | 1138.3 | 1023.8 | 927.9 | 851.2 | 814.4 | 794.2 | 779.9 |
| 15° | 1331.3 | 1337.8 | 1309.3 | 1203.6 | 1043.5 | 889.5 | 782.6 | 706.5 | 661.5 | 645.1 | 633.0 |
| 17.5° | 1378.9 | 1377.3 | 1312.6 | 1138.9 | 916.9 | 738.3 | 633.0 | 581.0 | 568.4 | 565.6 | 564.5 |
| 20° | 1428.8 | 1414.0 | 1299.5 | 1046.3 | 764.6 | 588.6 | 528.9 | 532.2 | 555.2 | 566.2 | 568.4 |
| 22.5° | 1485.8 | 1448.6 | 1266.6 | 920.8 | 608.9 | 490.5 | 496.6 | 528.9 | 560.1 | 574.9 | 577.1 |
| 25° | 1546.7 | 1480.3 | 1211.8 | 759.6 | 480.1 | 451.1 | 486.7 | 524.0 | 557.4 | 575.5 | 577.7 |
| 27.5° | 1586.7 | 1488.0 | 1121.9 | 597.4 | 412.1 | 435.7 | 473.5 | 509.2 | 543.7 | 563.4 | 566.2 |
| 30° | 1630.0 | 1484.7 | 999.7 | 460.4 | 389.1 | 422.6 | 455.4 | 487.8 | 519.6 | 541.5 | 543.7 |
| 32.5° | 1693.5 | 1482.5 | 850.6 | 373.8 | 379.8 | 412.1 | 436.3 | 463.1 | 485.0 | 497.6 | 496.0 |
| 35° | 1776.8 | 1479.8 | 676.9 | 337.1 | 374.3 | 403.9 | 423.1 | 435.7 | 411.6 | 403.9 | 405.6 |
| 37.5° | 1883.7 | 1486.4 | 530.5 | 321.7 | 372.7 | 401.7 | 418.2 | 382.0 | 344.7 | 330.5 | 328.3 |
| 40° | 2002.1 | 1503.4 | 404.5 | 315.7 | 378.2 | 407.2 | 399.5 | 339.8 | 293.8 | 265.8 | 259.8 |
| 42.5° | 2121.0 | 1522.0 | 320.1 | 313.5 | 387.5 | 422.6 | 368.9 | 309.1 | 240.1 | 224.2 | 222.0 |
| 45° | 2209.3 | 1518.7 | 276.8 | 309.7 | 395.7 | 431.3 | 360.6 | 265.3 | 214.3 | 207.2 | 207.7 |
| 47.5° | 2253.7 | 1482.5 | 253.2 | 300.9 | 399.0 | 422.6 | 340.4 | 247.2 | 196.8 | 204.4 | 211.0 |
| 50° | 2230.1 | 1388.8 | 231.3 | 283.9 | 391.9 | 411.1 | 308.0 | 233.5 | 188.0 | 219.8 | 234.6 |
| 52.5° | 2201.6 | 1273.7 | 207.2 | 257.6 | 374.9 | 395.2 | 295.4 | 229.6 | 182.5 | 212.1 | 223.1 |
| 55° | 2239.4 | 1200.8 | 167.7 | 217.0 | 341.4 | 357.9 | 285.5 | 229.1 | 169.9 | 165.0 | 163.3 |
| 57.5° | 2186.3 | 1055.6 | 120.0 | 156.2 | 262.0 | 283.4 | 278.4 | 225.3 | 150.7 | 150.2 | 152.4 |
| 60° | 1689.7 | 644.0 | 82.2 | 99.2 | 160.6 | 180.9 | 252.7 | 215.4 | 129.9 | 119.5 | 120.0 |
| 62.5° | 960.2 | 274.0 | 56.5 | 61.4 | 82.2 | 97.6 | 192.9 | 195.7 | 120.0 | 114.0 | 120.0 |
| 65° | 334.3 | 98.1 | 43.8 | 41.1 | 45.5 | 52.1 | 110.7 | 151.3 | 109.1 | 98.7 | 99.7 |
| 67.5° | 69.1 | 48.8 | 38.9 | 34.0 | 34.0 | 34.0 | 56.5 | 94.3 | 89.9 | 78.4 | 79.5 |
| 70° | 43.8 | 41.7 | 34.0 | 29.0 | 28.0 | 25.8 | 32.3 | 52.1 | 61.9 | 57.0 | 57.5 |
| 72.5° | 32.3 | 31.8 | 26.9 | 23.6 | 20.8 | 18.6 | 20.3 | 25.8 | 31.8 | 32.9 | 33.4 |
| 75° | 19.7 | 20.3 | 17.5 | 14.8 | 13.2 | 11.5 | 12.1 | 12.1 | 12.1 | 11.0 | 12.1 |
| 77.5° | 6.0 | 6.6 | 5.5 | 4.4 | 3.8 | 3.8 | 3.8 | 3.3 | 2.7 | 1.6 | 1.6 |
| 80° | 1.6 | 1.6 | 1.6 | 1.6 | 1.6 | 1.1 | 1.1 | 0.5 | 0.5 | 0.0 | 0.0 |
| 82.5° | 1.6 | 1.6 | 1.6 | 1.6 | 1.1 | 1.1 | 0.5 | 0.5 | 0.0 | 0.0 | 0.0 |
| 85° | 1.6 | 1.6 | 1.6 | 1.6 | 1.1 | 1.1 | 0.5 | 0.5 | 0.0 | 0.0 | 0.0 |
| 87.5° | 1.6 | 1.6 | 1.6 | 1.6 | 1.1 | 1.1 | 0.5 | 0.5 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-9-R4

Test Date: 10/23/2019

Luminaire Tested: SA1C-760-U-5WQ

Data in this report applies to families of products SA1C-760-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-9-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-760-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 5474 | CRI (Ra): | 71.7 | R9: | -27.1 |
| CIE u': | 0.2052 | R1: | 70.6 | R10: | 40.8 |
| CIE v': | 0.4804 | R2: | 74.6 | R11: | 74.6 |
| Duv: | 0.0025 | R3: | 78.3 | R12: | 50.4 |
| CIE x: | 0.3330 | R4: | 73.8 | R13: | 70.0 |
| CIE y: | 0.3466 | R5: | 72.4 | R14: | 87.8 |
| CIE z: | 0.3204 | R6: | 67.5 | | |
| Peak Wavelength (nm): | 442 | R7: | 77.5 | | |
| Dominant Wavelength (nm): | 554 | R8: | 58.9 | | |
| Purity: | 4.1 | | | | |
| Rf: | 72.1 | | | | |
| Rg: | 97.2 | | | | |



Test Conditions

Stabilization Time: 240M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.6/31%
 Sphere Temperature (°C): 25.9

REPORT NUMBER: SP1-1908-441-9-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-9-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-9-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) |
|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 13759.3 S/P: 1.85

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 5527.6 M/P: 0.74

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Summary

$R_f = 72.1$
 $R_g = 97.2$
 CIE $R_a = 71.7$
 $R_g = -27.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 54 | CES51 = 88 | CES76 = 43 |
| CES02 = 59 | CES27 = 79 | CES52 = 90 | CES77 = 64 |
| CES03 = 30 | CES28 = 77 | CES53 = 77 | CES78 = 46 |
| CES04 = 69 | CES29 = 50 | CES54 = 81 | CES79 = 74 |
| CES05 = 46 | CES30 = 59 | CES55 = 80 | CES80 = 70 |
| CES06 = 50 | CES31 = 55 | CES56 = 70 | CES81 = 71 |
| CES07 = 38 | CES32 = 52 | CES57 = 68 | CES82 = 88 |
| CES08 = 38 | CES33 = 63 | CES58 = 70 | CES83 = 82 |
| CES09 = 29 | CES34 = 63 | CES59 = 88 | CES84 = 87 |
| CES10 = 72 | CES35 = 79 | CES60 = 92 | CES85 = 84 |
| CES11 = 55 | CES36 = 90 | CES61 = 88 | CES86 = 76 |
| CES12 = 61 | CES37 = 72 | CES62 = 81 | CES87 = 75 |
| CES13 = 41 | CES38 = 68 | CES63 = 75 | CES88 = 77 |
| CES14 = 74 | CES39 = 91 | CES64 = 72 | CES89 = 76 |
| CES15 = 70 | CES40 = 83 | CES65 = 65 | CES90 = 76 |
| CES16 = 46 | CES41 = 84 | CES66 = 66 | CES91 = 92 |
| CES17 = 48 | CES42 = 70 | CES67 = 64 | CES92 = 70 |
| CES18 = 55 | CES43 = 69 | CES68 = 71 | CES93 = 83 |
| CES19 = 70 | CES44 = 98 | CES69 = 80 | CES94 = 60 |
| CES20 = 64 | CES45 = 79 | CES70 = 58 | CES95 = 73 |
| CES21 = 85 | CES46 = 78 | CES71 = 55 | CES96 = 79 |
| CES22 = 77 | CES47 = 76 | CES72 = 84 | CES97 = 84 |
| CES23 = 91 | CES48 = 68 | CES73 = 47 | CES98 = 73 |
| CES24 = 90 | CES49 = 78 | CES74 = 94 | CES99 = 62 |
| CES25 = 71 | CES50 = 87 | CES75 = 51 | |



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Measure Comparisons



(END OF REPORT)