

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P833198

Luminaire Tested: **TTN-D1-740-U-DL-UPL2**

Issue Date: 5/15/2024

Test Information

Test Method: LM-79-08
Report Number: P833198
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND
Test Lab: INNOVATION CENTER
Issue Date: 5/15/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: TTN-D1-740-U-DL-UPL2
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT
4000K, 70 CRI LEDS AND DRIVE LANE DISTRIBUTION
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3772.7 lumens
Efficiency: N/A
Efficacy: 122.1 lumens/watt
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')
IES Classification: Type IV - Short
BUG Rating: B1 - U4 - G2


Input Watts (W): 30.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P833198
 CATALOG NUMBER: TTN-D1-740-U-DL-UPL2

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.7 fc
 Type IV - Short - N/A

REPORT NUMBER: P833198
CATALOG NUMBER: TTN-D1-740-U-DL-UPL2

Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P833198
 CATALOG NUMBER: TTN-D1-740-U-DL-UPL2


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	679.1	292.5	971.5
	% Fixture	18.0	7.8	25.8
Street Side	Lumens	2508.7	292.4	2801.2
	% Fixture	66.5	7.8	74.2
Total	Lumens	3187.8	584.9	3772.7
	% Fixture	84.5	15.5	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.3	0.7
10°-20°	80.8	2.1
20°-30°	170.7	4.5
30°-40°	311.9	8.3
40°-50°	506.8	13.4
50°-60°	704.5	18.7
60°-70°	730.3	19.4
70°-80°	523.3	13.9
80°-90°	134.2	3.6
90°-100°	13.1	0.3
100°-110°	132.7	3.5
110°-120°	194.0	5.1
120°-130°	112.6	3.0
130°-140°	59.7	1.6
140°-150°	35.4	0.9
150°-160°	21.8	0.6
160°-170°	11.9	0.3
170°-180°	3.9	0.1
0°-90°	3187.8	84.5
0°-180°	3772.7	100.0

Coefficient of Utilization




REPORT NUMBER: P833198
 CATALOG NUMBER: TTN-D1-740-U-DL-UPL2

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	186.5	4.9			
FM (30°-60°)	1190.0	31.5			
FH (60°-80°)	1020.7	27.1			G1/1800
FVH (80°-90°)	111.5	3.0			G2/225
BL (0°-30°)	90.3	2.4	B0/110		
BM (30°-60°)	333.2	8.8	B1/1000		
BH (60°-80°)	233.0	6.2	B1/500		G1/500
BVH (80°-90°)	22.7	0.6			G1/100
UL (90°-100°)	13.1	0.3		U2/50	
UH (100°-180°)	571.8	15.2		U4/1000	

BUG Rating: B1-U4-G2
 Type IV Short





REPORT NUMBER: P833198

CATALOG NUMBER: TTN-D1-740-U-DL-UPL2

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	40°	45°	55°	65°	75°	85°
0°	268.4	268.4	268.4	268.4	268.4	268.4	268.4	268.4	268.4	268.4	268.4
2.5°	287.8	287.8	287.8	287.8	285.0	285.0	282.3	279.5	276.7	274.0	268.4
5°	312.7	312.7	309.9	307.2	301.6	298.9	296.1	290.6	285.0	279.5	271.2
7.5°	323.8	323.8	323.8	321.0	312.7	309.9	304.4	296.1	287.8	279.5	268.4
10°	343.1	343.1	340.4	337.6	329.3	326.5	321.0	309.9	296.1	282.3	268.4
12.5°	368.0	365.3	362.5	359.7	351.4	345.9	337.6	326.5	309.9	293.3	276.7
15°	398.5	392.9	392.9	387.4	379.1	370.8	365.3	348.7	332.1	309.9	287.8
17.5°	431.7	428.9	426.1	420.6	412.3	406.8	398.5	379.1	357.0	329.3	304.4
20°	473.2	467.7	470.4	462.1	453.8	451.0	437.2	415.1	387.4	357.0	326.5
22.5°	523.0	517.5	517.5	509.2	503.6	498.1	484.3	459.4	423.4	390.2	351.4
25°	578.3	572.8	572.8	567.3	561.7	556.2	539.6	511.9	470.4	428.9	384.6
27.5°	639.2	633.7	633.7	630.9	617.1	608.8	594.9	564.5	523.0	470.4	417.8
30°	702.9	697.3	702.9	697.3	689.0	672.4	655.8	622.6	575.6	517.5	453.8
32.5°	752.7	752.7	755.4	761.0	755.4	741.6	722.2	694.6	630.9	559.0	487.0
35°	810.8	810.8	816.3	824.6	821.9	808.0	788.6	758.2	691.8	606.0	523.0
37.5°	874.4	874.4	880.0	893.8	888.3	880.0	866.1	827.4	752.7	653.1	561.7
40°	943.6	940.8	946.4	965.7	968.5	957.4	940.8	902.1	816.3	713.9	603.2
42.5°	1012.8	1010.0	1021.1	1040.5	1043.2	1040.5	1023.9	979.6	882.7	774.8	644.8
45°	1082.0	1082.0	1098.6	1129.0	1142.8	1137.3	1123.5	1068.1	965.7	838.5	700.1
47.5°	1153.9	1153.9	1176.0	1214.8	1231.4	1228.6	1223.1	1156.7	1046.0	904.9	747.1
50°	1209.3	1209.3	1245.2	1289.5	1317.2	1328.2	1300.6	1239.7	1115.2	963.0	785.9
52.5°	1264.6	1264.6	1300.6	1369.8	1397.4	1414.0	1378.1	1314.4	1192.7	1015.6	821.9
55°	1292.3	1297.8	1347.6	1414.0	1458.3	1450.0	1463.8	1378.1	1242.5	1054.3	844.0
57.5°	1295.0	1303.3	1358.7	1427.9	1477.7	1474.9	1477.7	1400.2	1261.8	1062.6	846.8
60°	1281.2	1295.0	1344.8	1414.0	1461.1	1483.2	1455.5	1386.4	1250.8	1054.3	844.0
62.5°	1248.0	1275.7	1328.2	1380.8	1450.0	1458.3	1436.2	1378.1	1220.3	1046.0	830.2
65°	1173.3	1203.7	1278.4	1339.3	1394.7	1405.7	1380.8	1331.0	1189.9	1007.3	785.9
67.5°	1098.6	1117.9	1181.6	1275.7	1314.4	1325.5	1317.2	1259.1	1137.3	929.8	733.3
70°	1012.8	1037.7	1087.5	1184.3	1223.1	1220.3	1245.2	1178.8	1057.1	863.4	678.0
72.5°	896.6	932.5	982.3	1062.6	1109.6	1093.0	1131.8	1076.4	951.9	780.3	603.2
75°	761.0	791.4	855.1	918.7	971.3	951.9	982.3	943.6	830.2	680.7	517.5
77.5°	608.8	644.8	702.9	761.0	796.9	796.9	810.8	777.6	689.0	559.0	423.4
80°	451.0	484.3	536.8	578.3	611.5	614.3	628.1	611.5	531.3	434.4	323.8
82.5°	298.9	315.5	362.5	395.7	428.9	426.1	448.3	437.2	370.8	298.9	215.8
85°	127.3	138.4	177.1	204.8	235.2	224.1	254.6	251.8	199.2	143.9	96.9
87.5°	5.5	8.3	8.3	5.5	8.3	2.8	8.3	11.1	8.3	5.5	5.5
90°	5.0	5.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	5.0
92.5°	5.0	5.0	5.0	7.0	8.0	7.5	7.0	8.0	6.0	6.0	5.0
95°	6.0	6.0	7.0	9.0	11.0	11.5	12.0	12.0	7.0	7.0	6.0
97.5°	8.0	9.0	9.0	11.0	18.0	25.5	33.0	20.0	10.0	10.0	9.0
100°	13.0	14.0	14.0	25.0	53.0	62.0	71.1	51.0	26.0	19.0	14.0
102.5°	42.0	44.0	54.0	81.1	120.1	114.6	109.1	92.1	87.1	60.0	48.0
105°	107.1	106.1	114.1	135.1	168.1	166.6	165.1	152.1	138.1	119.1	110.1
107.5°	141.1	141.1	148.1	166.1	191.1	207.2	223.2	226.2	179.1	157.1	147.1
110°	159.1	159.1	165.1	180.1	213.2	235.7	258.2	256.2	221.2	194.1	181.1



REPORT NUMBER: P833198
 CATALOG NUMBER: TTN-D1-740-U-DL-UPL2

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	40°	45°	55°	65°	75°	85°
112.5°	163.1	164.1	172.1	195.1	231.2	241.2	251.2	242.2	228.2	216.2	206.2
115°	169.1	169.1	178.1	200.2	220.2	224.2	228.2	218.2	207.2	199.2	195.1
117.5°	167.1	170.1	172.1	184.1	197.1	200.1	203.2	198.1	183.1	177.1	175.1
120°	155.1	155.1	157.1	163.1	170.1	171.6	173.1	171.1	161.1	156.1	155.1
122.5°	138.1	139.1	138.1	141.1	146.1	147.6	149.1	147.1	139.1	137.1	137.1
125°	121.1	121.1	120.1	122.1	125.1	124.6	124.1	125.1	121.1	120.1	120.1
127.5°	109.1	108.1	106.1	107.1	108.1	108.1	108.1	109.1	105.1	106.1	107.1
130°	97.1	97.1	95.1	95.1	95.1	94.1	93.1	95.1	93.1	94.1	95.1
132.5°	86.1	86.1	83.1	82.1	82.1	82.1	82.1	83.1	82.1	84.1	86.1
135°	77.1	77.1	74.1	75.1	75.1	74.6	74.1	75.1	74.1	76.1	77.1
137.5°	70.1	70.1	68.1	68.1	68.1	67.6	67.1	68.1	68.1	69.1	71.1
140°	64.0	64.0	63.0	63.0	62.0	62.5	63.0	63.0	63.0	64.0	65.0
142.5°	61.0	60.0	59.0	58.0	59.0	59.0	59.0	59.0	58.0	59.0	61.0
145°	56.0	56.0	55.0	55.0	55.0	55.5	56.0	55.0	55.0	56.0	56.0
147.5°	53.0	53.0	52.0	53.0	53.0	53.0	53.0	53.0	52.0	53.0	53.0
150°	52.0	51.0	50.0	51.0	51.0	50.5	50.0	50.0	50.0	50.0	51.0
152.5°	49.0	49.0	48.0	49.0	48.0	48.0	48.0	48.0	48.0	48.0	49.0
155°	47.0	47.0	46.0	47.0	47.0	47.0	47.0	47.0	47.0	47.0	47.0
157.5°	45.0	46.0	45.0	45.0	45.0	45.0	45.0	45.0	45.0	45.0	46.0
160°	44.0	44.0	44.0	44.0	43.0	43.0	43.0	43.0	44.0	44.0	44.0
162.5°	43.0	43.0	43.0	43.0	42.0	42.0	42.0	42.0	42.0	43.0	43.0
165°	43.0	42.0	42.0	42.0	41.0	41.0	41.0	41.0	41.0	42.0	43.0
167.5°	41.0	41.0	41.0	41.0	41.0	40.5	40.0	40.0	41.0	41.0	41.0
170°	41.0	41.0	40.0	40.0	40.0	40.0	40.0	40.0	40.0	40.0	40.0
172.5°	41.0	41.0	41.0	41.0	40.0	40.0	40.0	40.0	40.0	40.0	41.0
175°	41.0	41.0	41.0	41.0	40.0	40.0	40.0	40.0	41.0	41.0	41.0
177.5°	41.0	41.0	41.0	41.0	40.0	40.5	41.0	41.0	41.0	41.0	41.0
180°	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0



REPORT NUMBER: P833198
 CATALOG NUMBER: TTN-D1-740-U-DL-UPL2

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	268.4	268.4	268.4	268.4	268.4	268.4	268.4	268.4	268.4	268.4	268.4
2.5°	268.4	265.6	260.1	257.3	254.6	249.0	249.0	246.3	246.3	246.3	243.5
5°	268.4	262.9	257.3	249.0	243.5	238.0	232.4	226.9	224.1	224.1	221.4
7.5°	262.9	257.3	249.0	240.7	232.4	221.4	215.8	204.8	202.0	199.2	199.2
10°	262.9	257.3	243.5	232.4	221.4	210.3	202.0	190.9	182.6	179.9	179.9
12.5°	265.6	257.3	243.5	229.7	215.8	202.0	190.9	179.9	171.6	166.0	166.0
15°	276.7	265.6	249.0	229.7	213.1	196.5	185.4	171.6	163.3	157.7	157.7
17.5°	290.6	279.5	254.6	232.4	213.1	193.7	179.9	166.0	157.7	152.2	149.4
20°	309.9	293.3	265.6	235.2	213.1	193.7	177.1	163.3	152.2	146.7	146.7
22.5°	332.1	312.7	276.7	240.7	215.8	193.7	177.1	160.5	149.4	143.9	143.9
25°	359.7	334.8	293.3	251.8	221.4	196.5	177.1	160.5	149.4	143.9	143.9
27.5°	390.2	362.5	309.9	262.9	226.9	199.2	177.1	160.5	149.4	143.9	143.9
30°	417.8	387.4	326.5	274.0	235.2	202.0	179.9	163.3	152.2	146.7	143.9
32.5°	448.3	409.5	343.1	285.0	240.7	207.5	182.6	166.0	152.2	146.7	146.7
35°	478.7	437.2	359.7	298.9	249.0	213.1	185.4	168.8	155.0	149.4	149.4
37.5°	511.9	467.7	379.1	309.9	257.3	218.6	190.9	171.6	157.7	152.2	152.2
40°	550.7	498.1	398.5	323.8	265.6	224.1	193.7	177.1	163.3	157.7	157.7
42.5°	586.6	525.8	417.8	334.8	274.0	229.7	199.2	179.9	168.8	163.3	163.3
45°	622.6	559.0	437.2	348.7	282.3	238.0	204.8	188.2	174.3	168.8	168.8
47.5°	664.1	589.4	459.4	359.7	290.6	243.5	210.3	193.7	179.9	177.1	174.3
50°	697.3	611.5	473.2	370.8	296.1	249.0	215.8	196.5	185.4	179.9	179.9
52.5°	727.8	633.7	484.3	376.3	298.9	251.8	221.4	202.0	190.9	185.4	185.4
55°	744.4	642.0	492.6	376.3	301.6	254.6	221.4	202.0	190.9	188.2	185.4
57.5°	744.4	642.0	487.0	370.8	296.1	249.0	218.6	199.2	190.9	185.4	185.4
60°	733.3	633.7	473.2	359.7	287.8	240.7	213.1	193.7	185.4	182.6	182.6
62.5°	716.7	619.8	462.1	345.9	276.7	229.7	204.8	185.4	179.9	179.9	177.1
65°	672.4	578.3	437.2	326.5	260.1	215.8	193.7	177.1	171.6	168.8	166.0
67.5°	625.4	539.6	398.5	304.4	238.0	202.0	179.9	166.0	157.7	157.7	155.0
70°	578.3	498.1	362.5	274.0	213.1	185.4	163.3	149.4	143.9	143.9	143.9
72.5°	514.7	445.5	321.0	240.7	188.2	163.3	146.7	132.8	130.1	130.1	127.3
75°	440.0	379.1	271.2	204.8	157.7	138.4	124.5	110.7	110.7	110.7	110.7
77.5°	359.7	307.2	215.8	163.3	124.5	110.7	102.4	91.3	91.3	91.3	91.3
80°	271.2	226.9	157.7	119.0	91.3	80.2	74.7	69.2	71.9	71.9	69.2
82.5°	177.1	149.4	99.6	74.7	58.1	52.6	52.6	47.0	49.8	49.8	49.8
85°	77.5	66.4	41.5	33.2	27.7	27.7	27.7	24.9	27.7	27.7	27.7
87.5°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	0.0	2.8	5.5	2.8
90°	5.0	5.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	5.0	5.0
92.5°	5.0	5.0	6.0	6.0	8.0	7.0	8.0	7.0	5.0	5.0	5.0
95°	6.0	6.0	7.0	7.0	12.0	12.0	11.0	9.0	7.0	6.0	6.0
97.5°	8.0	9.0	10.0	10.0	20.0	33.0	18.0	11.0	9.0	9.0	8.0
100°	14.0	14.0	19.0	26.0	51.0	71.1	53.0	25.0	14.0	14.0	13.0
102.5°	46.0	48.0	60.0	87.1	92.1	109.1	120.1	81.1	54.0	44.0	42.0
105°	110.1	110.1	119.1	138.1	152.1	165.1	168.1	135.1	114.1	106.1	107.1
107.5°	146.1	147.1	157.1	179.1	226.2	223.2	191.1	166.1	148.1	141.1	141.1
110°	179.1	181.1	194.1	221.2	256.2	258.2	213.2	180.1	165.1	159.1	159.1



REPORT NUMBER: P833198
 CATALOG NUMBER: TTN-D1-740-U-DL-UPL2

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	204.2	206.2	216.2	228.2	242.2	251.2	231.2	195.1	172.1	164.1	163.1
115°	197.1	195.1	199.2	207.2	218.2	228.2	220.2	200.2	178.1	169.1	169.1
117.5°	172.1	175.1	177.1	183.1	198.1	203.2	197.1	184.1	172.1	170.1	167.1
120°	153.1	155.1	156.1	161.1	171.1	173.1	170.1	163.1	157.1	155.1	155.1
122.5°	135.1	137.1	137.1	139.1	147.1	149.1	146.1	141.1	138.1	139.1	138.1
125°	119.1	120.1	120.1	121.1	125.1	124.1	125.1	122.1	120.1	121.1	121.1
127.5°	106.1	107.1	106.1	105.1	109.1	108.1	108.1	107.1	106.1	108.1	109.1
130°	96.1	95.1	94.1	93.1	95.1	93.1	95.1	95.1	95.1	97.1	97.1
132.5°	86.1	86.1	84.1	82.1	83.1	82.1	82.1	82.1	83.1	86.1	86.1
135°	77.1	77.1	76.1	74.1	75.1	74.1	75.1	75.1	74.1	77.1	77.1
137.5°	72.1	71.1	69.1	68.1	68.1	67.1	68.1	68.1	68.1	70.1	70.1
140°	65.0	65.0	64.0	63.0	63.0	63.0	62.0	63.0	63.0	64.0	64.0
142.5°	61.0	61.0	59.0	58.0	59.0	59.0	59.0	58.0	59.0	60.0	61.0
145°	57.0	56.0	56.0	55.0	55.0	56.0	55.0	55.0	55.0	56.0	56.0
147.5°	54.0	53.0	53.0	52.0	53.0	53.0	53.0	53.0	52.0	53.0	53.0
150°	51.0	51.0	50.0	50.0	50.0	50.0	51.0	51.0	50.0	51.0	52.0
152.5°	50.0	49.0	48.0	48.0	48.0	48.0	48.0	49.0	48.0	49.0	49.0
155°	47.0	47.0	47.0	47.0	47.0	47.0	47.0	47.0	46.0	47.0	47.0
157.5°	46.0	46.0	45.0	45.0	45.0	45.0	45.0	45.0	45.0	46.0	45.0
160°	45.0	44.0	44.0	44.0	43.0	43.0	43.0	44.0	44.0	44.0	44.0
162.5°	44.0	43.0	43.0	42.0	42.0	42.0	42.0	43.0	43.0	43.0	43.0
165°	42.0	43.0	42.0	41.0	41.0	41.0	41.0	42.0	42.0	42.0	43.0
167.5°	42.0	41.0	41.0	41.0	40.0	40.0	41.0	41.0	41.0	41.0	41.0
170°	41.0	40.0	40.0	40.0	40.0	40.0	40.0	40.0	40.0	41.0	41.0
172.5°	41.0	41.0	40.0	40.0	40.0	40.0	40.0	41.0	41.0	41.0	41.0
175°	40.0	41.0	41.0	41.0	40.0	40.0	40.0	41.0	41.0	41.0	41.0
177.5°	41.0	41.0	41.0	41.0	41.0	41.0	40.0	41.0	41.0	41.0	41.0
180°	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0

(END OF REPORT)