

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P635898

Luminaire Tested: GWS-SA3E-760-U-SLR-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P635898
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-42)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA3E-760-U-SLR-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND
SPILL LIGHT ELIMINATOR RIGHT OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (48) 5700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11836.8 lumens
Efficiency: N/A
Efficacy: 74.4 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B2 - U0 - G1


Input Watts (W): 159.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P635898
 CATALOG NUMBER: GWS-SA3E-760-U-SLR-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 9.3 fc
 Type III - Short - N/A

REPORT NUMBER: P635898
CATALOG NUMBER: GWS-SA3E-760-U-SLR-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P635898
 CATALOG NUMBER: GWS-SA3E-760-U-SLR-W-GRSBK

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2650.6	0.0	2650.6
	% Fixture	22.4	0.0	22.4
Street Side	Lumens	9186.2	0.0	9186.2
	% Fixture	77.6	0.0	77.6
Total	Lumens	11836.8	0.0	11836.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	204.7	1.7
10°-20°	662.1	5.6
20°-30°	1075.5	9.1
30°-40°	1661.8	14.0
40°-50°	2664.8	22.5
50°-60°	3642.0	30.8
60°-70°	1763.9	14.9
70°-80°	161.5	1.4
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11836.8	100.0
0°-180°	11836.8	100.0

Coefficient of Utilization



REPORT NUMBER: P635898


CATALOG NUMBER: GWS-SA3E-760-U-SLR-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1158.0	9.8			
FM (30°-60°)	6301.0	53.2			
FH (60°-80°)	1726.8	14.6			G1/1800
FVH (80°-90°)	0.5	0.0			G0/10
BL (0°-30°)	784.3	6.6	B2/1000		
BM (30°-60°)	1667.6	14.1	B2/2500		
BH (60°-80°)	198.7	1.7	B1/500		G1/500
BVH (80°-90°)	0.0	0.0			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G1

Type III Short





REPORT NUMBER: P635898

CATALOG NUMBER: GWS-SA3E-760-U-SLR-W-GRSBK

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	2080.4	2080.4	2080.4	2080.4	2080.4	2080.4	2080.4	2080.4	2080.4	2080.4	2080.4
2.5°	2253.8	2268.1	2292.0	2342.9	2385.8	2414.5	2427.2	2424.0	2406.5	2393.8	2368.3
5°	2495.6	2495.6	2541.7	2657.8	2746.9	2802.6	2831.2	2813.7	2778.7	2723.0	2637.1
7.5°	2707.1	2715.1	2793.0	2958.4	3093.6	3173.2	3219.3	3209.7	3147.7	3041.1	2869.4
10°	2872.5	2882.1	2985.5	3187.5	3346.5	3427.6	3496.0	3502.4	3434.0	3292.4	3095.2
12.5°	3033.2	3042.7	3150.9	3344.9	3484.9	3518.3	3578.7	3602.6	3585.1	3484.9	3279.7
15°	3206.6	3228.8	3321.1	3465.8	3524.7	3484.9	3524.7	3567.6	3626.5	3616.9	3432.4
17.5°	3376.7	3392.7	3486.5	3537.4	3472.2	3368.8	3387.9	3438.8	3572.4	3702.8	3583.5
20°	3534.2	3556.5	3634.4	3567.6	3370.4	3209.7	3211.3	3278.1	3481.7	3755.3	3737.8
22.5°	3699.6	3733.0	3788.7	3601.0	3276.5	3084.1	3092.0	3152.5	3410.1	3804.6	3912.8
25°	3915.9	3947.8	3984.3	3683.7	3246.3	3022.1	3052.3	3107.9	3410.1	3888.9	4129.1
27.5°	4208.6	4230.9	4232.5	3838.0	3298.8	3031.6	3095.2	3158.8	3511.9	4057.5	4418.6
30°	4576.0	4611.0	4564.9	4078.2	3462.6	3158.8	3252.7	3332.2	3731.4	4342.2	4844.8
32.5°	5023.0	5072.3	5010.2	4434.5	3804.6	3597.8	3768.0	3814.1	4081.4	4754.2	5328.4
35°	5547.9	5589.2	5522.4	4927.5	4603.1	4641.2	4949.8	4891.0	4784.4	5261.6	5893.0
37.5°	6123.6	6161.8	6033.0	5675.1	5783.3	5948.7	6441.7	6239.7	5896.2	5915.3	6505.4
40°	6651.7	6693.1	6491.1	6487.9	6710.5	7012.8	7607.6	7329.3	6861.7	6771.0	7079.6
42.5°	7198.8	7227.5	7044.6	6920.5	7426.3	8048.2	8678.1	8302.7	7501.1	7402.4	7798.5
45°	7979.8	8040.3	7714.2	7133.6	8070.5	9239.5	10117.5	9384.3	7936.9	7857.3	8899.1
47.5°	9128.2	9172.7	8507.9	7267.2	8670.1	10723.5	11916.4	10787.1	8320.2	8138.9	10403.8
50°	10077.8	10108.0	9237.9	7413.6	9307.9	12323.6	13966.7	12450.9	8751.2	8604.9	11808.3
52.5°	10777.6	10892.1	10197.0	7714.2	10146.1	14205.2	16236.4	14421.6	9424.0	9505.2	12972.6
55°	10922.3	11078.2	10852.4	7898.7	10884.2	16121.9	18332.7	16185.5	10095.2	10187.5	13363.8
57.5°	9599.0	9723.1	9910.7	7154.3	10866.7	16999.8	19549.5	16770.8	9789.9	9136.1	11898.9
60°	7190.9	7276.8	7617.2	5468.3	9993.5	16223.7	18601.5	15775.1	8560.4	6971.4	9066.2
62.5°	4264.3	4302.4	4733.5	3542.2	8294.7	13971.4	15426.8	13612.0	6764.6	4689.0	5552.6
65°	1636.7	1620.8	1950.0	1748.0	6099.8	11129.1	11474.3	10376.8	4641.2	2148.8	2117.0
67.5°	252.9	241.8	326.1	516.9	4399.5	7712.6	7571.0	7478.8	2907.5	501.0	437.4
70°	57.3	57.3	70.0	152.7	2688.0	4531.5	4849.6	4623.7	1860.9	106.6	57.3
72.5°	27.0	27.0	33.4	65.2	973.4	1867.3	2175.9	2142.5	604.4	35.0	20.7
75°	9.5	11.1	11.1	14.3	58.9	97.0	222.7	159.1	38.2	0.0	0.0
77.5°	3.2	3.2	3.2	3.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	1.6	1.6	1.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	1.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P635898

CATALOG NUMBER: GWS-SA3E-760-U-SLR-W-GRSBK

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2080.4	2080.4	2080.4	2080.4	2080.4	2080.4	2080.4	2080.4	2080.4	2080.4	2080.4
2.5°	2312.7	2301.5	2260.2	2204.5	2150.4	2102.7	2053.4	1994.6	1951.6	1902.3	1886.4
5°	2570.3	2500.4	2387.4	2269.7	2161.6	2069.3	1980.2	1884.8	1814.8	1744.8	1721.0
7.5°	2788.2	2684.9	2501.9	2325.4	2177.5	2047.0	1918.2	1787.8	1686.0	1603.3	1577.8
10°	2983.9	2864.6	2619.6	2401.7	2215.6	2064.5	1908.7	1744.8	1612.8	1514.2	1490.3
12.5°	3152.5	3014.1	2719.8	2459.0	2231.5	2058.2	1907.1	1776.6	1657.4	1544.4	1514.2
15°	3294.0	3141.3	2804.1	2497.2	2207.7	1978.6	1846.6	1826.0	1816.4	1692.3	1633.5
17.5°	3432.4	3260.6	2872.5	2514.7	2140.9	1838.7	1743.2	1837.1	1937.3	1856.2	1781.4
20°	3577.2	3381.5	2942.5	2517.8	2029.5	1681.2	1665.3	1813.2	1940.5	1915.0	1845.0
22.5°	3747.3	3532.6	3030.0	2516.3	1889.6	1547.6	1608.1	1767.1	1870.5	1868.9	1813.2
25°	3993.9	3723.5	3147.7	2525.8	1736.9	1444.2	1544.4	1689.2	1773.5	1770.3	1724.2
27.5°	4257.9	3950.9	3300.4	2549.7	1606.5	1383.8	1469.7	1582.6	1655.8	1652.6	1612.8
30°	4628.5	4213.4	3446.7	2551.2	1512.6	1352.0	1387.0	1464.9	1534.9	1526.9	1496.7
32.5°	5078.6	4509.2	3569.2	2460.6	1453.8	1321.8	1301.1	1340.8	1394.9	1383.8	1375.8
35°	5622.6	4860.7	3674.2	2261.8	1363.1	1261.3	1205.6	1213.6	1251.8	1258.1	1254.9
37.5°	6242.9	5279.0	3804.6	1999.3	1240.6	1173.8	1099.1	1092.7	1115.0	1135.7	1151.6
40°	6855.3	5749.9	3981.2	1733.7	1129.3	1062.5	990.9	975.0	984.6	1021.1	1054.5
42.5°	7544.0	6295.4	4172.0	1506.3	1052.9	940.0	871.6	841.4	868.4	927.3	967.1
45°	8536.5	7060.5	4358.1	1324.9	1021.1	831.9	739.6	736.4	766.6	843.0	887.5
47.5°	9929.8	8049.8	4480.6	1183.4	1019.5	747.6	637.8	656.9	691.9	766.6	817.5
50°	11288.2	9288.8	4345.4	1075.2	986.1	691.9	561.5	599.6	634.6	699.8	752.3
52.5°	12107.3	9955.3	3818.9	973.4	882.8	666.4	486.7	553.5	559.9	618.7	674.4
55°	12021.4	9524.2	2925.0	816.0	730.1	629.9	408.8	499.4	502.6	547.2	594.9
57.5°	10434.0	8177.0	2008.9	661.7	548.7	520.1	337.2	421.5	451.7	478.8	513.7
60°	7776.2	5966.2	895.5	537.6	348.3	351.5	287.9	318.1	364.2	396.0	426.3
62.5°	4582.4	3432.4	364.2	322.9	192.5	221.1	232.2	232.2	260.9	284.7	303.8
65°	1732.1	1200.9	147.9	162.2	100.2	103.4	136.8	168.6	190.9	211.5	237.0
67.5°	303.8	210.0	76.3	60.4	58.9	52.5	70.0	109.7	122.5	138.4	149.5
70°	50.9	42.9	31.8	30.2	27.0	28.6	46.1	77.9	85.9	90.7	95.4
72.5°	14.3	12.7	9.5	8.0	6.4	8.0	28.6	60.4	63.6	66.8	71.6
75°	0.0	0.0	0.0	0.0	0.0	0.0	11.1	42.9	46.1	47.7	52.5
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	9.5	12.7	15.9	12.7
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P635898

CATALOG NUMBER: GWS-SA3E-760-U-SLR-W-GRSBK

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	2080.4	2080.4	2080.4	2080.4	2080.4	2080.4	2080.4	2080.4	2080.4	2080.4	2080.4
2.5°	1876.9	1845.0	1827.5	1818.0	1818.0	1805.3	1791.0	1786.2	1806.9	1806.9	1841.9
5°	1690.8	1665.3	1636.7	1619.2	1592.1	1596.9	1581.0	1579.4	1600.1	1609.6	1646.2
7.5°	1561.9	1530.1	1512.6	1501.5	1487.2	1480.8	1466.5	1461.7	1472.9	1488.8	1523.8
10°	1476.0	1471.3	1469.7	1477.6	1477.6	1469.7	1456.9	1449.0	1452.2	1482.4	1522.2
12.5°	1498.3	1507.8	1511.0	1523.8	1530.1	1523.8	1514.2	1517.4	1538.1	1593.7	1652.6
15°	1595.3	1587.4	1584.2	1590.6	1595.3	1589.0	1585.8	1609.6	1681.2	1760.7	1827.5
17.5°	1698.7	1647.8	1625.5	1625.5	1628.7	1625.5	1628.7	1674.9	1791.0	1870.5	1919.8
20°	1751.2	1657.4	1622.4	1614.4	1620.8	1622.4	1633.5	1686.0	1813.2	1868.9	1880.0
22.5°	1735.3	1617.6	1577.8	1571.5	1577.8	1584.2	1595.3	1639.9	1759.2	1787.8	1783.0
25°	1655.8	1539.7	1507.8	1507.8	1522.2	1520.6	1525.3	1557.2	1655.8	1673.3	1665.3
27.5°	1555.6	1445.8	1418.8	1434.7	1447.4	1444.2	1445.8	1472.9	1546.0	1550.8	1542.8
30°	1453.8	1358.3	1332.9	1352.0	1369.5	1366.3	1367.9	1394.9	1441.0	1436.3	1425.1
32.5°	1350.4	1280.4	1261.3	1272.4	1299.5	1296.3	1302.7	1331.3	1348.8	1328.1	1315.4
35°	1254.9	1218.4	1204.0	1210.4	1231.1	1235.9	1247.0	1266.1	1266.1	1240.6	1218.4
37.5°	1165.9	1161.1	1151.6	1143.6	1162.7	1177.0	1192.9	1215.2	1183.4	1146.8	1126.1
40°	1083.2	1103.8	1091.1	1070.4	1081.6	1102.3	1134.1	1151.6	1113.4	1076.8	1041.8
42.5°	1006.8	1041.8	1037.0	1011.6	1021.1	1040.2	1076.8	1091.1	1046.6	1005.2	971.8
45°	933.7	983.0	986.1	954.3	963.9	983.0	1025.9	1030.7	973.4	928.9	905.0
47.5°	870.0	924.1	925.7	901.8	905.0	932.1	971.8	973.4	908.2	866.9	836.6
50°	809.6	871.6	876.4	855.7	858.9	890.7	924.1	917.7	847.8	804.8	777.8
52.5°	736.4	820.7	831.9	822.3	835.0	860.5	881.2	858.9	777.8	734.8	711.0
55°	656.9	766.6	790.5	784.1	798.5	819.1	823.9	809.6	707.8	664.9	642.6
57.5°	564.6	631.4	672.8	660.1	671.2	691.9	706.2	695.1	618.7	585.3	566.2
60°	467.6	512.2	521.7	501.0	491.5	528.1	561.5	547.2	481.9	461.3	439.0
62.5°	342.0	392.9	399.2	372.2	361.1	400.8	429.4	415.1	343.6	321.3	303.8
65°	273.6	321.3	334.0	308.6	302.2	332.4	349.9	314.9	264.0	240.2	221.1
67.5°	179.7	217.9	251.3	249.7	237.0	246.5	233.8	205.2	168.6	155.9	143.1
70°	111.3	133.6	154.3	162.2	160.6	157.5	140.0	119.3	108.2	103.4	97.0
72.5°	85.9	108.2	124.1	128.8	130.4	125.7	111.3	92.3	81.1	74.8	70.0
75°	63.6	81.1	93.8	100.2	103.4	100.2	85.9	73.2	62.0	57.3	52.5
77.5°	22.3	27.0	33.4	36.6	35.0	33.4	30.2	30.2	23.9	22.3	19.1
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P635898

CATALOG NUMBER: GWS-SA3E-760-U-SLR-W-GRSBK

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	2080.4	2080.4	2080.4	2080.4	2080.4	2080.4	2080.4	2080.4	2080.4	2080.4
2.5°	1881.6	1910.3	1962.7	2010.5	2061.4	2113.8	2171.1	2230.0	2257.0	2253.8
5°	1701.9	1763.9	1849.8	1943.7	2048.6	2161.6	2287.2	2416.1	2471.7	2495.6
7.5°	1589.0	1676.4	1789.4	1908.7	2047.0	2207.7	2397.0	2599.0	2680.1	2707.1
10°	1603.3	1705.1	1798.9	1915.0	2062.9	2271.3	2506.7	2746.9	2842.3	2872.5
12.5°	1719.4	1741.7	1767.1	1862.5	2048.6	2319.0	2606.9	2893.2	3003.0	3033.2
15°	1824.4	1721.0	1673.3	1760.7	1997.7	2352.4	2708.7	3050.7	3171.6	3206.6
17.5°	1829.1	1673.3	1566.7	1635.1	1915.0	2366.7	2808.9	3211.3	3343.3	3376.7
20°	1770.3	1620.8	1484.0	1485.6	1802.1	2363.6	2891.6	3356.1	3504.0	3534.2
22.5°	1684.4	1558.7	1417.2	1367.9	1681.2	2357.2	2982.3	3510.4	3671.0	3699.6
25°	1589.0	1479.2	1353.6	1278.8	1560.3	2363.6	3109.5	3712.4	3888.9	3915.9
27.5°	1485.6	1391.7	1304.3	1243.8	1458.5	2387.4	3262.2	3970.0	4180.0	4208.6
30°	1377.4	1307.4	1272.4	1235.9	1394.9	2393.8	3427.6	4270.6	4536.3	4576.0
32.5°	1270.9	1232.7	1234.3	1240.6	1334.5	2349.2	3578.7	4604.7	4959.3	5023.0
35°	1172.2	1161.1	1192.9	1224.7	1247.0	2234.7	3710.8	4999.1	5482.6	5547.9
37.5°	1087.9	1097.5	1137.2	1169.1	1151.6	2072.5	3885.7	5492.2	6068.0	6123.6
40°	1006.8	1030.7	1076.8	1091.1	1078.4	1883.2	4095.7	5967.8	6575.4	6651.7
42.5°	932.1	949.6	1014.8	1018.0	1057.7	1690.8	4297.7	6479.9	7159.1	7198.8
45°	871.6	868.4	935.2	955.9	1084.8	1477.6	4494.9	7162.3	7922.5	7979.8
47.5°	812.8	809.6	825.5	919.3	1095.9	1280.4	4690.5	8161.1	9029.6	9128.2
50°	757.1	761.9	712.6	901.8	1035.5	1129.3	4779.6	9085.2	10036.4	10077.8
52.5°	707.8	690.3	604.4	844.6	906.6	986.1	4526.7	9505.2	10659.9	10777.6
55°	637.8	540.8	497.8	685.5	715.7	860.5	3707.6	9261.8	10714.0	10922.3
57.5°	545.6	424.7	423.1	505.8	505.8	798.5	2374.7	7913.0	9233.2	9599.0
60°	419.9	329.2	349.9	351.5	324.5	582.1	1332.9	5732.4	6826.7	7190.9
62.5°	299.0	251.3	264.0	210.0	186.1	291.1	639.4	3300.4	4213.4	4264.3
65°	200.4	170.2	138.4	116.1	114.5	124.1	264.0	1192.9	1450.6	1636.7
67.5°	132.0	103.4	73.2	73.2	82.7	82.7	100.2	197.2	276.8	252.9
70°	85.9	71.6	46.1	44.5	54.1	54.1	50.9	54.1	57.3	57.3
72.5°	63.6	54.1	27.0	23.9	30.2	31.8	28.6	27.0	27.0	27.0
75°	47.7	38.2	15.9	11.1	14.3	19.1	15.9	11.1	11.1	9.5
77.5°	19.1	14.3	6.4	4.8	8.0	11.1	9.5	4.8	3.2	3.2
80°	1.6	3.2	3.2	3.2	4.8	6.4	8.0	3.2	1.6	1.6
82.5°	0.0	1.6	1.6	1.6	3.2	4.8	6.4	3.2	1.6	1.6
85°	0.0	0.0	0.0	0.0	3.2	4.8	3.2	1.6	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	1.6	4.8	3.2	1.6	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)