

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P636384

Luminaire Tested: GWS-SA3F-760-U-SL3-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P636384
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-33)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA3F-760-U-SL3-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III SPILL LIGHT ELIMINATOR OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (48) 5700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 20658.3 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G3


Input Watts (W): 183.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P636384
 CATALOG NUMBER: GWS-SA3F-760-U-SL3-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 12.7 fc
 Type II - Short - N/A

REPORT NUMBER: P636384
CATALOG NUMBER: GWS-SA3F-760-U-SL3-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 54-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P636384

CATALOG NUMBER: GWS-SA3F-760-U-SL3-W-GRSWH

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 6005.6 | 0.0 | 6005.6 |
| | % Fixture | 29.1 | 0.0 | 29.1 |
| Street Side | Lumens | 14652.7 | 0.0 | 14652.7 |
| | % Fixture | 70.9 | 0.0 | 70.9 |
| Total | Lumens | 20658.3 | 0.0 | 20658.3 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 697.1 | 3.4 |
| 10°-20° | 1663.5 | 8.1 |
| 20°-30° | 2302.0 | 11.1 |
| 30°-40° | 3198.6 | 15.5 |
| 40°-50° | 4224.4 | 20.4 |
| 50°-60° | 5020.1 | 24.3 |
| 60°-70° | 2781.2 | 13.5 |
| 70°-80° | 692.6 | 3.4 |
| 80°-90° | 78.8 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 20658.3 | 100.0 |
| 0°-180° | 20658.3 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P636384

CATALOG NUMBER: GWS-SA3F-760-U-SL3-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 2811.9 | 13.6 | | | |
| FM (30°-60°) | 9480.4 | 45.9 | | | |
| FH (60°-80°) | 2335.7 | 11.3 | | | G2/5000 |
| FVH (80°-90°) | 24.6 | 0.1 | | | G1/100 |
| BL (0°-30°) | 1850.7 | 9.0 | B3/2500 | | |
| BM (30°-60°) | 2962.7 | 14.3 | B3/5000 | | |
| BH (60°-80°) | 1138.1 | 5.5 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 54.1 | 0.3 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G3
 Type II Short





REPORT NUMBER: P636384

CATALOG NUMBER: GWS-SA3F-760-U-SL3-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 54° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|---------|---------|---------|---------|---------|---------|
| 0° | 7931.2 | 7931.2 | 7931.2 | 7931.2 | 7931.2 | 7931.2 | 7931.2 | 7931.2 | 7931.2 | 7931.2 | 7931.2 |
| 2.5° | 7782.6 | 7798.6 | 7809.2 | 7846.3 | 7878.1 | 7906.4 | 7936.5 | 7936.5 | 7934.7 | 7929.4 | 7918.8 |
| 5° | 7474.9 | 7492.6 | 7517.4 | 7568.7 | 7637.6 | 7687.2 | 7768.5 | 7775.6 | 7810.9 | 7825.1 | 7818.0 |
| 7.5° | 7117.7 | 7123.0 | 7154.9 | 7222.1 | 7331.7 | 7420.1 | 7536.8 | 7551.0 | 7635.9 | 7685.4 | 7676.5 |
| 10° | 6726.9 | 6709.2 | 6765.8 | 6864.9 | 7008.1 | 7156.6 | 7307.0 | 7319.3 | 7455.5 | 7549.2 | 7542.1 |
| 12.5° | 6369.7 | 6371.5 | 6428.1 | 6548.3 | 6726.9 | 6910.8 | 7112.4 | 7140.7 | 7308.7 | 7429.0 | 7416.6 |
| 15° | 6070.9 | 6077.9 | 6146.9 | 6283.1 | 6486.4 | 6705.7 | 6956.8 | 6983.3 | 7195.5 | 7354.7 | 7319.3 |
| 17.5° | 5832.1 | 5839.2 | 5899.3 | 6054.9 | 6272.4 | 6537.7 | 6843.6 | 6870.2 | 7133.7 | 7322.9 | 7250.4 |
| 20° | 5667.7 | 5664.1 | 5722.5 | 5871.0 | 6095.6 | 6383.9 | 6744.6 | 6783.5 | 7114.2 | 7335.2 | 7204.4 |
| 22.5° | 5600.5 | 5598.7 | 5641.1 | 5763.2 | 5973.6 | 6265.4 | 6684.5 | 6737.5 | 7135.4 | 7390.1 | 7176.1 |
| 25° | 5634.1 | 5627.0 | 5664.1 | 5754.3 | 5922.3 | 6219.4 | 6702.2 | 6758.8 | 7225.6 | 7503.2 | 7181.4 |
| 27.5° | 5738.4 | 5729.6 | 5761.4 | 5842.7 | 5970.1 | 6267.1 | 6826.0 | 6891.4 | 7416.6 | 7710.1 | 7252.1 |
| 30° | 5897.6 | 5892.2 | 5924.1 | 6001.9 | 6113.3 | 6426.3 | 7062.9 | 7137.2 | 7711.9 | 8032.0 | 7406.0 |
| 32.5° | 6083.2 | 6074.4 | 6131.0 | 6221.2 | 6350.3 | 6716.3 | 7381.2 | 7478.5 | 8062.1 | 8445.8 | 7664.2 |
| 35° | 6291.9 | 6284.8 | 6362.6 | 6493.5 | 6679.2 | 7119.5 | 7766.7 | 7872.8 | 8419.3 | 8914.4 | 8007.2 |
| 37.5° | 6495.3 | 6495.3 | 6645.6 | 6840.1 | 7073.5 | 7558.1 | 8129.2 | 8196.4 | 8666.8 | 9330.0 | 8375.1 |
| 40° | 6675.6 | 6686.3 | 6912.6 | 7204.4 | 7501.5 | 7954.2 | 8368.0 | 8424.6 | 8776.5 | 9616.5 | 8695.1 |
| 42.5° | 6875.5 | 6884.3 | 7147.8 | 7529.8 | 7883.4 | 8274.3 | 8513.0 | 8541.3 | 8797.7 | 9759.7 | 8921.5 |
| 45° | 7034.6 | 7047.0 | 7374.2 | 7782.6 | 8215.9 | 8514.8 | 8627.9 | 8652.7 | 8827.8 | 9837.5 | 9085.9 |
| 47.5° | 7117.7 | 7135.4 | 7510.3 | 7986.0 | 8440.5 | 8730.5 | 8817.1 | 8827.8 | 8951.5 | 9973.7 | 9284.0 |
| 50° | 7103.6 | 7139.0 | 7561.6 | 8086.8 | 8606.7 | 8948.0 | 9121.3 | 9139.0 | 9204.4 | 10173.5 | 9515.7 |
| 52.5° | 7229.1 | 7245.1 | 7671.2 | 8207.1 | 8843.7 | 9349.4 | 9650.1 | 9674.8 | 9644.8 | 10323.8 | 9653.6 |
| 55° | 7020.5 | 7096.5 | 7535.1 | 8189.4 | 9204.4 | 9970.1 | 10433.5 | 10421.1 | 10044.4 | 10491.8 | 9883.5 |
| 57.5° | 5678.3 | 5789.7 | 6191.1 | 6951.5 | 8610.2 | 10405.2 | 11018.8 | 10988.7 | 10353.9 | 10620.9 | 10132.8 |
| 60° | 3931.1 | 3948.8 | 4311.3 | 4850.7 | 6645.6 | 9192.0 | 10847.3 | 10912.7 | 10410.5 | 10458.2 | 9671.3 |
| 62.5° | 3144.2 | 3138.9 | 3172.5 | 3186.6 | 4226.4 | 6461.7 | 8562.5 | 8801.2 | 8649.2 | 8148.7 | 6854.2 |
| 65° | 2684.4 | 2703.9 | 2802.9 | 2751.6 | 2758.7 | 3639.3 | 5115.9 | 5149.5 | 5043.4 | 4863.0 | 3625.2 |
| 67.5° | 2100.8 | 2134.4 | 2309.5 | 2509.3 | 2445.7 | 2343.1 | 2654.3 | 2638.4 | 2079.6 | 1609.2 | 1329.8 |
| 70° | 1315.7 | 1336.9 | 1524.3 | 1970.0 | 2129.1 | 1924.0 | 1706.5 | 1699.4 | 1114.1 | 916.0 | 1004.4 |
| 72.5° | 767.5 | 771.0 | 824.1 | 1098.2 | 1412.9 | 1315.7 | 1255.6 | 1209.6 | 716.2 | 730.3 | 801.1 |
| 75° | 422.6 | 422.6 | 420.9 | 473.9 | 557.0 | 493.4 | 477.5 | 465.1 | 479.2 | 542.9 | 595.9 |
| 77.5° | 88.4 | 90.2 | 95.5 | 125.6 | 162.7 | 198.1 | 249.3 | 251.1 | 313.0 | 362.5 | 405.0 |
| 80° | 40.7 | 42.4 | 53.1 | 67.2 | 86.7 | 114.9 | 152.1 | 153.8 | 189.2 | 228.1 | 256.4 |
| 82.5° | 21.2 | 23.0 | 28.3 | 35.4 | 46.0 | 60.1 | 84.9 | 84.9 | 113.2 | 134.4 | 152.1 |
| 85° | 7.1 | 7.1 | 10.6 | 14.1 | 19.5 | 24.8 | 33.6 | 33.6 | 49.5 | 65.4 | 76.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 1.8 | 3.5 | 7.1 | 7.1 | 8.8 | 10.6 | 17.7 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P636384

CATALOG NUMBER: GWS-SA3F-760-U-SL3-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 7931.2 | 7931.2 | 7931.2 | 7931.2 | 7931.2 | 7931.2 | 7931.2 | 7931.2 | 7931.2 | 7931.2 | 7931.2 |
| 2.5° | 7895.8 | 7841.0 | 7842.8 | 7853.4 | 7819.8 | 7768.5 | 7734.9 | 7692.5 | 7665.9 | 7660.6 | 7680.1 |
| 5° | 7782.6 | 7719.0 | 7674.8 | 7628.8 | 7533.3 | 7420.1 | 7331.7 | 7259.2 | 7211.5 | 7193.8 | 7172.6 |
| 7.5° | 7627.0 | 7543.9 | 7432.5 | 7303.4 | 7130.1 | 6928.5 | 6787.0 | 6654.4 | 6562.5 | 6535.9 | 6523.6 |
| 10° | 7471.4 | 7351.2 | 7153.1 | 6912.6 | 6624.4 | 6352.0 | 6095.6 | 5899.3 | 5743.7 | 5655.3 | 5683.6 |
| 12.5° | 7310.5 | 7161.9 | 6852.5 | 6482.9 | 6081.5 | 5671.2 | 5335.2 | 5009.8 | 4758.7 | 4633.2 | 4596.0 |
| 15° | 7169.0 | 6967.4 | 6535.9 | 6035.5 | 5501.4 | 4985.1 | 4498.8 | 4010.7 | 3692.4 | 3519.1 | 3471.3 |
| 17.5° | 7048.8 | 6787.0 | 6201.7 | 5579.2 | 4940.9 | 4205.2 | 3607.5 | 3154.8 | 2937.3 | 2841.8 | 2834.7 |
| 20° | 6930.3 | 6610.2 | 5871.0 | 5087.6 | 4293.6 | 3469.6 | 2935.5 | 2723.3 | 2645.5 | 2611.9 | 2610.1 |
| 22.5° | 6824.2 | 6424.5 | 5522.7 | 4596.0 | 3649.9 | 2916.1 | 2622.5 | 2530.6 | 2509.3 | 2509.3 | 2505.8 |
| 25° | 6734.0 | 6238.8 | 5165.4 | 4074.4 | 3068.1 | 2596.0 | 2459.8 | 2420.9 | 2429.8 | 2445.7 | 2447.4 |
| 27.5° | 6696.9 | 6093.8 | 4820.6 | 3538.5 | 2666.7 | 2410.3 | 2348.4 | 2343.1 | 2367.9 | 2392.6 | 2396.2 |
| 30° | 6735.8 | 5994.8 | 4466.9 | 3025.7 | 2426.2 | 2297.1 | 2268.8 | 2279.4 | 2309.5 | 2334.3 | 2334.3 |
| 32.5° | 6856.0 | 5945.3 | 4106.2 | 2650.8 | 2286.5 | 2217.6 | 2208.7 | 2219.3 | 2242.3 | 2256.5 | 2258.2 |
| 35° | 7059.4 | 5964.8 | 3733.1 | 2397.9 | 2196.3 | 2159.2 | 2157.4 | 2164.5 | 2173.3 | 2182.2 | 2184.0 |
| 37.5° | 7315.8 | 6051.4 | 3333.4 | 2251.1 | 2138.0 | 2116.8 | 2113.2 | 2111.4 | 2113.2 | 2113.2 | 2115.0 |
| 40° | 7566.9 | 6182.3 | 2976.2 | 2164.5 | 2097.3 | 2079.6 | 2070.8 | 2058.4 | 2056.6 | 2053.1 | 2051.3 |
| 42.5° | 7752.6 | 6283.1 | 2691.5 | 2102.6 | 2060.2 | 2038.9 | 2028.3 | 2008.9 | 2007.1 | 2005.3 | 2003.6 |
| 45° | 7892.3 | 6367.9 | 2454.5 | 2042.5 | 2021.3 | 2001.8 | 1978.8 | 1961.1 | 1964.7 | 1968.2 | 1968.2 |
| 47.5° | 8049.7 | 6442.2 | 2281.2 | 1985.9 | 1973.5 | 1954.1 | 1925.8 | 1913.4 | 1925.8 | 1938.1 | 1938.1 |
| 50° | 8240.7 | 6546.5 | 2139.7 | 1929.3 | 1924.0 | 1901.0 | 1876.3 | 1870.9 | 1885.1 | 1902.8 | 1902.8 |
| 52.5° | 8380.4 | 6636.7 | 2038.9 | 1872.7 | 1872.7 | 1842.7 | 1821.4 | 1819.7 | 1835.6 | 1853.3 | 1855.0 |
| 55° | 8642.1 | 6847.2 | 2003.6 | 1807.3 | 1800.2 | 1777.2 | 1761.3 | 1748.9 | 1768.4 | 1784.3 | 1784.3 |
| 57.5° | 8937.4 | 7126.6 | 2012.4 | 1713.6 | 1704.7 | 1697.6 | 1685.3 | 1671.1 | 1676.4 | 1694.1 | 1695.9 |
| 60° | 8311.4 | 6585.5 | 1915.2 | 1619.8 | 1614.5 | 1611.0 | 1595.1 | 1570.3 | 1577.4 | 1591.5 | 1593.3 |
| 62.5° | 5805.6 | 4376.7 | 1549.1 | 1503.1 | 1520.8 | 1519.0 | 1497.8 | 1469.5 | 1471.3 | 1490.7 | 1490.7 |
| 65° | 3013.3 | 2367.9 | 1359.9 | 1397.0 | 1423.5 | 1412.9 | 1377.6 | 1352.8 | 1349.3 | 1374.0 | 1368.7 |
| 67.5° | 1299.8 | 1292.7 | 1237.9 | 1285.6 | 1313.9 | 1290.9 | 1253.8 | 1213.1 | 1216.6 | 1225.5 | 1218.4 |
| 70° | 1046.9 | 1078.7 | 1101.7 | 1153.0 | 1176.0 | 1133.5 | 1092.9 | 1069.9 | 1050.4 | 1048.7 | 1036.3 |
| 72.5° | 836.4 | 880.7 | 931.9 | 985.0 | 992.1 | 949.6 | 898.3 | 877.1 | 847.1 | 845.3 | 832.9 |
| 75° | 629.5 | 666.7 | 707.4 | 749.8 | 749.8 | 709.1 | 675.5 | 664.9 | 629.5 | 618.9 | 608.3 |
| 77.5° | 429.7 | 452.7 | 484.5 | 495.1 | 505.8 | 489.8 | 456.2 | 438.6 | 397.9 | 387.3 | 373.1 |
| 80° | 270.6 | 286.5 | 305.9 | 313.0 | 323.6 | 304.2 | 277.6 | 258.2 | 229.9 | 221.0 | 214.0 |
| 82.5° | 162.7 | 173.3 | 185.7 | 189.2 | 198.1 | 183.9 | 159.2 | 145.0 | 129.1 | 122.0 | 116.7 |
| 85° | 83.1 | 88.4 | 95.5 | 97.3 | 95.5 | 81.3 | 72.5 | 65.4 | 54.8 | 53.1 | 49.5 |
| 87.5° | 21.2 | 24.8 | 26.5 | 24.8 | 23.0 | 17.7 | 12.4 | 8.8 | 3.5 | 3.5 | 1.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-9-R4

Test Date: 10/23/2019

Luminaire Tested: SA1C-760-U-5WQ

Data in this report applies to families of products SA1C-760-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-9-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-760-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 5474 | CRI (Ra): | 71.7 | R9: | -27.1 |
| CIE u': | 0.2052 | R1: | 70.6 | R10: | 40.8 |
| CIE v': | 0.4804 | R2: | 74.6 | R11: | 74.6 |
| Duv: | 0.0025 | R3: | 78.3 | R12: | 50.4 |
| CIE x: | 0.3330 | R4: | 73.8 | R13: | 70.0 |
| CIE y: | 0.3466 | R5: | 72.4 | R14: | 87.8 |
| CIE z: | 0.3204 | R6: | 67.5 | | |
| Peak Wavelength (nm): | 442 | R7: | 77.5 | | |
| Dominant Wavelength (nm): | 554 | R8: | 58.9 | | |
| Purity: | 4.1 | | | | |
| Rf: | 72.1 | | | | |
| Rg: | 97.2 | | | | |



Test Conditions

Stabilization Time: 240M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.6/31%
 Sphere Temperature (°C): 25.9

REPORT NUMBER: SP1-1908-441-9-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-9-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-9-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 13759.3 S/P: 1.85

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 5527.6 M/P: 0.74

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Summary

$R_f = 72.1$
 $R_g = 97.2$
CIE $R_a = 71.7$
 $R_9 = -27.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 54 | CES51 = 88 | CES76 = 43 |
| CES02 = 59 | CES27 = 79 | CES52 = 90 | CES77 = 64 |
| CES03 = 30 | CES28 = 77 | CES53 = 77 | CES78 = 46 |
| CES04 = 69 | CES29 = 50 | CES54 = 81 | CES79 = 74 |
| CES05 = 46 | CES30 = 59 | CES55 = 80 | CES80 = 70 |
| CES06 = 50 | CES31 = 55 | CES56 = 70 | CES81 = 71 |
| CES07 = 38 | CES32 = 52 | CES57 = 68 | CES82 = 88 |
| CES08 = 38 | CES33 = 63 | CES58 = 70 | CES83 = 82 |
| CES09 = 29 | CES34 = 63 | CES59 = 88 | CES84 = 87 |
| CES10 = 72 | CES35 = 79 | CES60 = 92 | CES85 = 84 |
| CES11 = 55 | CES36 = 90 | CES61 = 88 | CES86 = 76 |
| CES12 = 61 | CES37 = 72 | CES62 = 81 | CES87 = 75 |
| CES13 = 41 | CES38 = 68 | CES63 = 75 | CES88 = 77 |
| CES14 = 74 | CES39 = 91 | CES64 = 72 | CES89 = 76 |
| CES15 = 70 | CES40 = 83 | CES65 = 65 | CES90 = 76 |
| CES16 = 46 | CES41 = 84 | CES66 = 66 | CES91 = 92 |
| CES17 = 48 | CES42 = 70 | CES67 = 64 | CES92 = 70 |
| CES18 = 55 | CES43 = 69 | CES68 = 71 | CES93 = 83 |
| CES19 = 70 | CES44 = 98 | CES69 = 80 | CES94 = 60 |
| CES20 = 64 | CES45 = 79 | CES70 = 58 | CES95 = 73 |
| CES21 = 85 | CES46 = 78 | CES71 = 55 | CES96 = 79 |
| CES22 = 77 | CES47 = 76 | CES72 = 84 | CES97 = 84 |
| CES23 = 91 | CES48 = 68 | CES73 = 47 | CES98 = 73 |
| CES24 = 90 | CES49 = 78 | CES74 = 94 | CES99 = 62 |
| CES25 = 71 | CES50 = 87 | CES75 = 51 | |



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Measure Comparisons



(END OF REPORT)