

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P641834

Luminaire Tested: GWS-SA6B-760-U-SLL-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P641834
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-38)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA6B-760-U-SLL-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (6) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR LEFT OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (96) 5700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11454.1 lumens
Efficiency: N/A
Efficacy: 82.5 lumens/watt
Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')
IES Classification: Type III - Short
BUG Rating: B2 - U0 - G1


Input Watts (W): 138.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P641834
 CATALOG NUMBER: GWS-SA6B-760-U-SLL-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 7.6 fc
 Type III - Short - N/A

REPORT NUMBER: P641834
CATALOG NUMBER: GWS-SA6B-760-U-SLL-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 315-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P641834

CATALOG NUMBER: GWS-SA6B-760-U-SLL-W-GRSBK


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2467.6	0.0	2467.6
	% Fixture	21.5	0.0	21.5
Street Side	Lumens	8986.5	0.0	8986.5
	% Fixture	78.5	0.0	78.5
Total	Lumens	11454.1	0.0	11454.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	192.4	1.7
10°-20°	633.0	5.5
20°-30°	1027.2	9.0
30°-40°	1576.6	13.8
40°-50°	2517.9	22.0
50°-60°	3525.5	30.8
60°-70°	1807.6	15.8
70°-80°	174.0	1.5
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11454.1	100.0
0°-180°	11454.1	100.0

Coefficient of Utilization



REPORT NUMBER: P641834


CATALOG NUMBER: GWS-SA6B-760-U-SLL-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1134.0	9.9			
FM (30°-60°)	6057.2	52.9			
FH (60°-80°)	1795.3	15.7			G1/1800
FVH (80°-90°)	0.0	0.0			G0/10
BL (0°-30°)	718.5	6.3	B2/1000		
BM (30°-60°)	1562.7	13.6	B2/2500		
BH (60°-80°)	186.4	1.6	B1/500		G1/500
BVH (80°-90°)	0.0	0.0			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G1

Type III Short





REPORT NUMBER: P641834

CATALOG NUMBER: GWS-SA6B-760-U-SLL-W-GRSBK

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	1946.2	1946.2	1946.2	1946.2	1946.2	1946.2	1946.2	1946.2	1946.2	1946.2	1946.2
2.5°	2162.1	2157.5	2142.2	2090.2	2058.0	2007.5	1970.7	1923.3	1871.2	1839.0	1806.9
5°	2391.8	2379.6	2338.2	2218.8	2126.9	2027.4	1947.8	1860.5	1767.1	1705.8	1649.2
7.5°	2612.3	2593.9	2538.8	2336.7	2197.3	2054.9	1941.6	1814.5	1682.8	1591.0	1520.5
10°	2828.2	2786.9	2699.6	2451.5	2263.2	2091.7	1958.5	1813.0	1658.3	1542.0	1463.9
12.5°	3005.8	2975.2	2855.8	2560.3	2318.3	2099.3	1935.5	1800.8	1696.6	1618.5	1546.6
15°	3159.0	3125.3	3012.0	2658.3	2365.8	2068.7	1839.0	1721.1	1738.0	1768.6	1707.3
17.5°	3299.8	3264.6	3142.1	2739.4	2384.2	1993.7	1704.3	1647.6	1741.0	1855.9	1832.9
20°	3445.3	3405.5	3255.4	2805.3	2378.0	1875.8	1568.0	1584.8	1716.5	1848.2	1860.5
22.5°	3615.3	3573.9	3399.4	2889.5	2373.4	1734.9	1450.1	1529.7	1670.6	1782.4	1803.8
25°	3840.4	3791.4	3600.0	3013.5	2385.7	1606.3	1365.9	1476.1	1592.5	1693.6	1705.8
27.5°	4137.4	4074.7	3831.2	3166.6	2411.7	1505.2	1329.1	1402.6	1493.0	1583.3	1594.0
30°	4524.8	4445.2	4096.1	3299.8	2399.5	1434.8	1304.6	1329.1	1382.7	1456.2	1457.8
32.5°	4978.1	4869.4	4393.2	3414.7	2293.8	1382.7	1270.9	1254.1	1266.3	1323.0	1333.7
35°	5511.0	5370.1	4720.8	3523.4	2100.9	1281.7	1209.7	1153.0	1148.4	1176.0	1202.0
37.5°	6121.9	5953.5	5134.3	3662.8	1872.7	1176.0	1119.3	1062.7	1038.2	1052.0	1091.8
40°	6685.4	6498.6	5566.1	3831.2	1640.0	1081.1	1013.7	955.5	926.4	931.0	980.0
42.5°	7346.9	7154.0	6094.4	4051.7	1447.0	1016.8	903.4	843.7	805.4	826.9	883.5
45°	8351.4	8132.5	6864.6	4243.1	1293.9	1001.4	807.0	722.8	704.4	741.1	808.5
47.5°	9723.5	9455.5	7922.7	4359.5	1163.8	1015.2	739.6	624.8	629.3	670.7	738.1
50°	11084.7	10795.3	9146.2	4206.3	1056.6	987.7	705.9	548.2	577.3	614.0	675.3
52.5°	12020.3	11643.6	9741.8	3763.8	958.6	883.5	702.8	476.2	531.3	543.6	595.7
55°	12057.1	11593.1	9437.1	2967.6	825.3	745.7	670.7	416.5	480.8	485.4	529.8
57.5°	10568.7	10149.1	8247.3	2038.1	733.5	546.7	534.4	364.4	395.1	433.3	460.9
60°	8040.6	7683.8	6167.9	934.1	557.4	347.6	366.0	313.9	295.5	352.2	379.8
62.5°	4924.5	4696.3	3699.5	413.4	355.3	185.3	222.0	249.6	222.0	243.5	266.4
65°	1955.4	1854.3	1404.2	176.1	145.5	93.4	101.1	145.5	156.2	171.5	192.9
67.5°	339.9	321.6	235.8	78.1	59.7	56.7	49.0	67.4	94.9	105.7	122.5
70°	44.4	42.9	38.3	32.2	30.6	27.6	21.4	42.9	64.3	67.4	78.1
72.5°	10.7	9.2	9.2	7.7	9.2	3.1	3.1	23.0	45.9	47.5	55.1
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	7.7	29.1	32.2	38.3
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.5
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P641834

CATALOG NUMBER: GWS-SA6B-760-U-SLL-W-GRSBK

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1946.2	1946.2	1946.2	1946.2	1946.2	1946.2	1946.2	1946.2	1946.2	1946.2	1946.2
2.5°	1780.8	1750.2	1739.5	1724.2	1704.3	1710.4	1682.8	1673.7	1687.4	1705.8	1701.2
5°	1618.5	1584.8	1561.9	1526.7	1520.5	1506.8	1497.6	1485.3	1500.6	1522.1	1526.7
7.5°	1489.9	1460.8	1437.8	1427.1	1419.5	1413.3	1395.0	1385.8	1385.8	1395.0	1402.6
10°	1434.8	1413.3	1408.8	1411.8	1424.1	1422.5	1405.7	1393.4	1378.1	1370.5	1379.7
12.5°	1511.3	1476.1	1470.0	1471.5	1486.8	1485.3	1466.9	1451.6	1448.6	1451.6	1480.7
15°	1641.5	1587.9	1548.1	1540.4	1548.1	1545.0	1531.3	1522.1	1526.7	1571.1	1620.1
17.5°	1757.9	1675.2	1603.2	1575.7	1574.1	1569.5	1555.8	1552.7	1575.7	1658.3	1730.3
20°	1791.6	1710.4	1607.8	1572.6	1564.9	1560.3	1545.0	1549.6	1578.7	1678.3	1739.5
22.5°	1747.2	1669.1	1561.9	1526.7	1520.5	1519.0	1503.7	1509.8	1534.3	1621.6	1672.1
25°	1662.9	1597.1	1485.3	1454.7	1454.7	1451.6	1437.8	1440.9	1456.2	1532.8	1581.8
27.5°	1560.3	1497.6	1404.2	1373.5	1378.1	1382.7	1365.9	1361.3	1373.5	1445.5	1474.6
30°	1442.4	1398.0	1324.5	1297.0	1295.4	1313.8	1290.8	1284.7	1301.6	1358.2	1364.3
32.5°	1327.6	1306.2	1254.1	1232.7	1234.2	1237.3	1225.0	1225.0	1240.3	1270.9	1269.4
35°	1215.8	1202.0	1192.8	1177.5	1176.0	1169.9	1169.9	1172.9	1189.8	1200.5	1180.6
37.5°	1108.6	1122.4	1133.1	1117.8	1105.6	1105.6	1105.6	1119.3	1134.7	1130.1	1096.4
40°	1013.7	1042.8	1076.5	1059.6	1030.5	1029.0	1035.1	1058.1	1081.1	1053.5	1022.9
42.5°	932.5	969.3	1016.8	1007.6	975.4	970.8	975.4	1004.5	1022.9	987.7	954.0
45°	852.9	898.8	955.5	955.5	920.3	915.7	917.2	955.5	966.2	924.9	882.0
47.5°	785.5	836.1	895.8	895.8	866.7	857.5	865.2	905.0	912.6	854.4	814.6
50°	721.2	776.3	842.2	837.6	817.7	810.0	823.8	866.7	857.5	793.2	751.8
52.5°	640.1	698.3	788.6	793.2	782.5	784.0	800.8	828.4	802.4	724.3	689.1
55°	566.6	626.3	716.6	741.1	741.1	739.6	747.3	768.7	747.3	653.8	611.0
57.5°	486.9	537.5	612.5	618.6	623.2	606.4	617.1	646.2	635.5	555.8	531.3
60°	399.7	442.5	485.4	490.0	470.1	434.9	454.8	488.5	496.1	436.4	408.8
62.5°	283.3	324.6	375.2	375.2	355.3	320.0	346.1	375.2	364.4	303.2	286.3
65°	211.3	249.6	287.9	304.7	287.9	263.4	283.3	304.7	287.9	237.3	212.8
67.5°	136.3	162.3	185.3	199.1	202.1	199.1	208.3	202.1	182.2	148.5	134.8
70°	82.7	96.5	108.7	121.0	130.2	134.8	139.3	125.6	105.7	87.3	82.7
72.5°	59.7	72.0	82.7	91.9	102.6	105.7	105.7	96.5	78.1	61.3	56.7
75°	41.3	52.1	61.3	67.4	76.6	79.6	79.6	72.0	58.2	44.4	39.8
77.5°	1.5	10.7	10.7	9.2	12.3	15.3	15.3	18.4	16.8	12.3	10.7
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P641834

CATALOG NUMBER: GWS-SA6B-760-U-SLL-W-GRSBK

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	1946.2	1946.2	1946.2	1946.2	1946.2	1946.2	1946.2	1946.2	1946.2	1946.2	1946.2
2.5°	1710.4	1765.5	1780.8	1837.5	1888.0	1938.6	1999.8	2036.6	2091.7	2130.0	2151.4
5°	1542.0	1587.9	1643.0	1727.3	1814.5	1911.0	2027.4	2128.4	2255.5	2348.9	2379.6
7.5°	1419.5	1479.2	1543.5	1649.2	1768.6	1897.2	2061.1	2226.4	2420.9	2548.0	2629.2
10°	1396.5	1457.8	1543.5	1647.6	1773.2	1920.2	2120.8	2335.2	2578.6	2733.3	2825.2
12.5°	1506.8	1572.6	1609.3	1656.8	1751.8	1915.6	2172.8	2445.4	2731.8	2900.2	2998.2
15°	1669.1	1727.3	1667.5	1607.8	1669.1	1866.6	2201.9	2537.3	2866.5	3061.0	3162.0
17.5°	1780.8	1785.4	1655.3	1528.2	1545.0	1777.8	2212.7	2629.2	3010.4	3214.1	3319.8
20°	1770.1	1733.4	1601.7	1460.8	1408.8	1662.9	2200.4	2710.3	3155.9	3368.8	3472.9
22.5°	1687.4	1644.6	1532.8	1395.0	1293.9	1526.7	2179.0	2783.8	3289.1	3531.1	3629.1
25°	1587.9	1542.0	1450.1	1329.1	1220.4	1395.0	2162.1	2884.9	3457.6	3742.4	3818.9
27.5°	1471.5	1431.7	1353.6	1266.3	1189.8	1295.4	2157.5	3018.1	3661.2	3999.6	4053.2
30°	1358.2	1321.5	1260.2	1209.7	1177.5	1237.3	2142.2	3160.5	3904.7	4295.2	4353.3
32.5°	1249.5	1212.8	1174.5	1166.8	1168.3	1215.8	2090.2	3301.4	4194.1	4723.9	4766.8
35°	1156.1	1113.2	1097.9	1116.3	1150.0	1179.1	1943.2	3417.8	4504.9	5190.9	5226.2
37.5°	1067.3	1024.4	1022.9	1067.3	1104.0	1122.4	1770.1	3532.6	4924.5	5665.6	5710.0
40°	986.1	943.3	958.6	1012.2	1041.3	1050.4	1560.3	3707.2	5368.6	6166.4	6141.9
42.5°	917.2	872.8	882.0	950.9	976.9	1001.4	1367.4	3852.6	5795.8	6641.0	6633.4
45°	849.8	816.2	810.0	885.1	908.0	1006.0	1226.5	3964.4	6345.5	7245.9	7258.1
47.5°	784.0	758.0	759.5	791.7	848.3	1029.0	1107.1	4037.9	7143.3	8204.4	7991.6
50°	724.3	704.4	721.2	684.5	810.0	999.9	1004.5	4022.6	8034.5	9123.2	8696.0
52.5°	658.4	653.8	661.5	572.7	748.8	882.0	908.0	3818.9	8452.5	9751.0	9507.5
55°	591.1	589.5	528.3	457.8	626.3	704.4	777.9	3186.5	8438.7	10084.8	10380.4
57.5°	511.4	499.2	401.2	373.6	486.9	490.0	709.0	2087.1	7478.6	9285.5	9898.0
60°	387.4	378.2	294.0	303.2	339.9	313.9	565.0	1039.7	5589.1	7233.6	7924.2
62.5°	268.0	255.7	219.0	234.3	219.0	179.2	346.1	514.5	3385.6	4567.7	5194.0
65°	196.0	182.2	150.1	128.6	102.6	102.6	131.7	197.5	1310.8	1941.6	2341.3
67.5°	121.0	114.8	88.8	64.3	62.8	67.4	68.9	98.0	211.3	336.9	411.9
70°	78.1	72.0	59.7	41.3	38.3	39.8	41.3	45.9	53.6	58.2	70.4
72.5°	53.6	50.5	42.9	23.0	18.4	19.9	21.4	21.4	26.0	24.5	29.1
75°	38.3	35.2	30.6	10.7	6.1	7.7	9.2	7.7	9.2	6.1	7.7
77.5°	10.7	10.7	7.7	1.5	0.0	1.5	3.1	3.1	1.5	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	1.5	1.5	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P641834

CATALOG NUMBER: GWS-SA6B-760-U-SLL-W-GRSBK

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	1946.2	1946.2	1946.2	1946.2	1946.2	1946.2	1946.2	1946.2	1946.2	1946.2
2.5°	2206.5	2241.8	2255.5	2235.6	2252.5	2224.9	2214.2	2172.8	2169.8	2162.1
5°	2503.6	2583.2	2630.7	2659.8	2626.1	2589.3	2534.2	2439.3	2410.2	2391.8
7.5°	2796.1	2920.1	3001.3	3039.5	3030.3	2955.3	2855.8	2696.5	2639.9	2612.3
10°	3050.3	3201.8	3299.8	3347.3	3327.4	3261.6	3119.2	2920.1	2845.1	2828.2
12.5°	3227.9	3367.2	3434.6	3475.9	3477.5	3451.4	3316.7	3116.1	3027.3	3005.8
15°	3339.7	3399.4	3400.9	3425.4	3468.3	3526.5	3463.7	3286.1	3191.1	3159.0
17.5°	3410.1	3344.3	3276.9	3283.0	3353.4	3508.1	3572.4	3436.1	3335.1	3299.8
20°	3460.6	3252.4	3126.8	3128.3	3200.3	3434.6	3647.4	3581.6	3477.5	3445.3
22.5°	3492.8	3171.2	2992.1	2987.5	3064.0	3347.3	3716.3	3754.6	3652.0	3615.3
25°	3558.6	3132.9	2910.9	2936.9	3004.3	3319.8	3809.8	3984.3	3889.4	3840.4
27.5°	3676.5	3171.2	2903.3	2963.0	3039.5	3400.9	3972.1	4290.6	4192.6	4137.4
30°	3880.2	3315.2	3021.2	3103.8	3195.7	3613.8	4244.6	4717.8	4576.9	4524.8
32.5°	4207.9	3613.8	3385.6	3563.2	3652.0	3962.9	4653.5	5197.1	5082.2	4978.1
35°	4659.6	4295.2	4269.1	4682.6	4661.1	4624.4	5155.7	5785.1	5612.0	5511.0
37.5°	5281.3	5391.5	5584.5	5994.9	5981.1	5700.9	5815.7	6340.9	6252.1	6121.9
40°	6057.6	6291.9	6619.6	7207.6	7023.9	6671.7	6625.7	6910.5	6838.6	6685.4
42.5°	6515.5	6919.7	7544.5	8072.8	7925.8	7310.2	7258.1	7671.6	7513.9	7346.9
45°	6728.3	7431.2	8656.2	9371.3	8925.7	7734.4	7714.4	8663.8	8575.0	8351.4
47.5°	6826.3	7947.2	9957.7	11040.3	10207.3	8106.4	8034.5	10103.2	9986.8	9723.5
50°	6935.0	8659.2	11525.7	12974.3	11755.4	8527.5	8579.6	11444.6	11395.6	11084.7
52.5°	7173.9	9412.6	13456.6	15185.4	13632.7	9187.5	9515.2	12709.4	12378.6	12020.3
55°	7532.2	10233.4	15465.6	17444.0	15548.3	10074.1	10527.4	13381.6	12453.7	12057.1
57.5°	7135.6	10438.5	16655.4	19021.2	16398.2	10077.2	9671.4	12216.3	10953.0	10568.7
60°	5662.6	9711.2	16197.6	18679.7	15673.9	8948.6	7405.1	9538.2	8297.9	8040.6
62.5°	3828.1	8144.7	14259.0	15797.9	13415.3	7039.2	4812.7	6203.1	5137.4	4924.5
65°	2097.8	6076.0	11521.1	11951.4	10499.8	4916.9	2476.0	2691.9	2050.3	1955.4
67.5°	578.8	4229.3	8477.0	7928.8	7366.9	3201.8	640.1	480.8	343.0	339.9
70°	145.5	2797.6	5079.2	5235.4	4517.2	2050.3	122.5	58.2	45.9	44.4
72.5°	61.3	1203.6	2410.2	2770.0	2312.2	949.4	44.4	16.8	13.8	10.7
75°	7.7	96.5	205.2	310.8	212.8	102.6	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)