

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P833211

Luminaire Tested: **TTN-D1-740-U-RW-UPL3**

Issue Date: 5/15/2024

**Test Information**

Test Method: LM-79-08  
Report Number: P833211  
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND  
Test Lab: INNOVATION CENTER  
Issue Date: 5/15/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: TTN-D1-740-U-RW-UPL3  
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT  
4000K, 70 CRI LEDS AND RECTANGULAR DISTRIBUTION  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4090.6 lumens  
Efficiency: N/A  
Efficacy: 122.5 lumens/watt  
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')  
IES Classification: Type II - Short  
BUG Rating: B2 - U4 - G2  
  
Input Watts (W): 33.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P833211  
 CATALOG NUMBER: TTN-D1-740-U-RW-UPL3

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.7 fc  
 Type II - Short - N/A

REPORT NUMBER: P833211  
CATALOG NUMBER: TTN-D1-740-U-RW-UPL3

### Luminous Intensity Polar Plot



— Vertical Plane Through 90-Deg Lateral    - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P833211

CATALOG NUMBER: TTN-D1-740-U-RW-UPL3


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1639.5	405.8	2045.3
	% Fixture	40.1	9.9	50.0
<b>Street Side</b>	Lumens	1639.5	405.8	2045.3
	% Fixture	40.1	9.9	50.0
<b>Total</b>	Lumens	3279.1	811.5	4090.6
	% Fixture	80.2	19.8	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	27.5	0.7
10°-20°	87.9	2.1
20°-30°	183.4	4.5
30°-40°	328.9	8.0
40°-50°	525.6	12.8
50°-60°	719.5	17.6
60°-70°	742.2	18.1
70°-80°	527.8	12.9
80°-90°	136.2	3.3
90°-100°	18.1	0.4
100°-110°	184.1	4.5
110°-120°	269.1	6.6
120°-130°	156.2	3.8
130°-140°	82.7	2.0
140°-150°	49.1	1.2
150°-160°	30.3	0.7
160°-170°	16.5	0.4
170°-180°	5.4	0.1
0°-90°	3279.1	80.2
0°-180°	4090.6	100.0

**Coefficient of Utilization**




REPORT NUMBER: P833211  
 CATALOG NUMBER: TTN-D1-740-U-RW-UPL3

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	149.4	3.7			
FM (30°-60°)	787.0	19.2			
FH (60°-80°)	635.0	15.5			G0/660
FVH (80°-90°)	68.1	1.7			G1/100
BL (0°-30°)	149.4	3.7	B1/500		
BM (30°-60°)	787.0	19.2	B1/1000		
BH (60°-80°)	635.0	15.5	B2/1000		G2/1000
BVH (80°-90°)	68.1	1.7			G1/100
UL (90°-100°)	18.1	0.4		U2/50	
UH (100°-180°)	793.4	19.4		U4/1000	

**BUG Rating: B2-U4-G2**

Type II Short





REPORT NUMBER: P833211  
 CATALOG NUMBER: TTN-D1-740-U-RW-UPL3

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	293.2	293.2	293.2	293.2	293.2	293.2	293.2	293.2	293.2	293.2	293.2
2.5°	293.2	293.2	290.5	290.5	290.5	287.7	287.7	287.7	287.7	284.9	287.7
5°	293.2	293.2	293.2	293.2	290.5	287.7	287.7	287.7	284.9	284.9	284.9
7.5°	290.5	290.5	290.5	290.5	287.7	284.9	284.9	284.9	282.2	282.2	282.2
10°	287.7	290.5	287.7	287.7	284.9	284.9	287.7	287.7	290.5	290.5	290.5
12.5°	284.9	284.9	284.9	287.7	287.7	290.5	296.0	301.5	304.3	307.1	307.1
15°	284.9	284.9	287.7	290.5	296.0	301.5	309.8	318.1	323.7	329.2	329.2
17.5°	284.9	284.9	287.7	296.0	304.3	315.4	329.2	340.3	351.3	359.6	362.4
20°	284.9	284.9	290.5	301.5	318.1	334.7	354.1	370.7	387.3	401.1	401.1
22.5°	287.7	290.5	296.0	309.8	334.7	359.6	384.5	409.4	428.8	445.4	445.4
25°	293.2	293.2	301.5	323.7	354.1	387.3	423.2	453.7	478.6	500.7	500.7
27.5°	296.0	298.8	309.8	337.5	376.2	417.7	467.5	503.5	536.7	556.0	558.8
30°	301.5	304.3	320.9	348.6	395.6	448.1	506.2	556.0	592.0	611.4	616.9
32.5°	304.3	307.1	329.2	362.4	414.9	475.8	542.2	605.8	655.6	677.7	686.0
35°	312.6	315.4	337.5	376.2	437.1	506.2	583.7	658.4	716.5	744.1	749.7
37.5°	320.9	323.7	345.8	390.1	459.2	539.4	628.0	713.7	780.1	813.3	824.4
40°	326.4	329.2	354.1	406.6	484.1	575.4	677.7	771.8	846.5	888.0	896.3
42.5°	334.7	337.5	365.2	420.5	506.2	611.4	730.3	835.4	915.7	962.7	973.7
45°	343.0	345.8	376.2	437.1	531.1	650.1	782.9	910.1	1001.4	1056.7	1067.8
47.5°	351.3	354.1	387.3	453.7	556.0	688.8	838.2	976.5	1087.2	1139.7	1161.9
50°	354.1	359.6	392.8	464.7	572.6	722.0	885.2	1042.9	1159.1	1228.2	1233.8
52.5°	356.9	362.4	398.4	473.0	586.5	746.9	924.0	1098.2	1233.8	1316.8	1311.2
55°	359.6	359.6	398.4	473.0	592.0	763.5	951.6	1134.2	1283.6	1350.0	1388.7
57.5°	348.6	351.3	392.8	467.5	589.2	760.7	951.6	1148.0	1302.9	1374.9	1402.5
60°	334.7	340.3	379.0	453.7	578.2	752.4	946.1	1142.5	1311.2	1388.7	1380.4
62.5°	315.4	326.4	359.6	434.3	561.6	733.1	937.8	1128.7	1291.9	1372.1	1363.8
65°	293.2	304.3	334.7	414.9	525.6	686.0	893.5	1101.0	1239.3	1330.6	1314.0
67.5°	271.1	279.4	309.8	381.8	484.1	636.3	835.4	1040.1	1164.6	1264.2	1255.9
70°	246.2	249.0	279.4	343.0	442.6	586.5	780.1	954.4	1098.2	1172.9	1189.5
72.5°	215.8	215.8	246.2	301.5	392.8	520.1	705.4	857.6	993.1	1056.7	1081.6
75°	177.0	179.8	204.7	254.5	329.2	445.4	600.3	755.2	868.6	935.0	943.3
77.5°	138.3	141.1	160.4	201.9	265.6	359.6	495.2	616.9	724.8	782.9	766.3
80°	99.6	102.4	116.2	146.6	196.4	268.3	381.8	489.6	567.1	614.1	592.0
82.5°	60.9	63.6	71.9	91.3	124.5	174.3	260.0	340.3	401.1	439.8	431.5
85°	30.4	30.4	36.0	41.5	52.6	77.5	124.5	171.5	218.5	246.2	237.9
87.5°	5.5	8.3	8.3	8.3	8.3	5.5	8.3	8.3	8.3	13.8	5.5
90°	6.9	6.9	8.3	8.3	8.3	8.3	8.3	8.3	8.3	6.9	6.9
92.5°	6.9	6.9	6.9	9.7	11.1	9.7	11.1	8.3	8.3	6.9	6.9
95°	8.3	8.3	9.7	12.5	15.3	16.7	16.7	9.7	9.7	8.3	8.3
97.5°	11.1	12.5	12.5	15.3	25.0	45.8	27.8	13.9	13.9	12.5	11.1
100°	18.0	19.4	19.4	34.7	73.6	98.6	70.8	36.1	26.4	19.4	19.4
102.5°	58.3	61.1	75.0	112.5	166.6	151.3	127.7	120.8	83.3	66.6	63.9
105°	148.6	147.2	158.3	187.4	233.3	229.1	211.0	191.6	165.2	152.7	152.7
107.5°	195.8	195.8	205.5	230.5	265.2	309.6	313.8	248.5	218.0	204.1	202.7
110°	220.8	220.8	229.1	249.9	295.7	358.2	355.4	306.8	269.4	251.3	248.5



REPORT NUMBER: P833211  
 CATALOG NUMBER: TTN-D1-740-U-RW-UPL3

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	226.3	227.7	238.8	270.7	320.7	348.5	336.0	316.6	299.9	286.0	283.2
115°	234.6	234.6	247.1	277.7	305.5	316.6	302.7	287.4	276.3	270.7	273.5
117.5°	231.9	236.0	238.8	255.5	273.5	281.8	274.9	254.1	245.8	243.0	238.8
120°	215.2	215.2	218.0	226.3	236.0	240.2	237.4	223.5	216.6	215.2	212.4
122.5°	191.6	193.0	191.6	195.8	202.7	206.9	204.1	193.0	190.2	190.2	187.4
125°	168.0	168.0	166.6	169.4	173.6	172.2	173.6	168.0	166.6	166.6	165.2
127.5°	151.3	149.9	147.2	148.6	149.9	149.9	151.3	145.8	147.2	148.6	147.2
130°	134.7	134.7	131.9	131.9	131.9	129.1	131.9	129.1	130.5	131.9	133.3
132.5°	119.4	119.4	115.2	113.9	113.9	113.9	115.2	113.9	116.6	119.4	119.4
135°	106.9	106.9	102.7	104.1	104.1	102.7	104.1	102.7	105.5	106.9	106.9
137.5°	97.2	97.2	94.4	94.4	94.4	93.0	94.4	94.4	95.8	98.6	100.0
140°	88.9	88.9	87.5	87.5	86.1	87.5	87.5	87.5	88.9	90.2	90.2
142.5°	84.7	83.3	81.9	80.5	81.9	81.9	81.9	80.5	81.9	84.7	84.7
145°	77.8	77.8	76.4	76.4	76.4	77.8	76.4	76.4	77.8	77.8	79.1
147.5°	73.6	73.6	72.2	73.6	73.6	73.6	73.6	72.2	73.6	73.6	75.0
150°	72.2	70.8	69.4	70.8	70.8	69.4	69.4	69.4	69.4	70.8	70.8
152.5°	68.0	68.0	66.6	68.0	66.6	66.6	66.6	66.6	66.6	68.0	69.4
155°	65.3	65.3	63.9	65.3	65.3	65.3	65.3	65.3	65.3	65.3	65.3
157.5°	62.5	63.9	62.5	62.5	62.5	62.5	62.5	62.5	62.5	63.9	63.9
160°	61.1	61.1	61.1	61.1	59.7	59.7	59.7	61.1	61.1	61.1	62.5
162.5°	59.7	59.7	59.7	59.7	58.3	58.3	58.3	58.3	59.7	59.7	61.1
165°	59.7	58.3	58.3	58.3	56.9	56.9	56.9	56.9	58.3	59.7	58.3
167.5°	56.9	56.9	56.9	56.9	56.9	55.5	55.5	56.9	56.9	56.9	58.3
170°	56.9	56.9	55.5	55.5	55.5	55.5	55.5	55.5	55.5	55.5	56.9
172.5°	56.9	56.9	56.9	56.9	55.5	55.5	55.5	55.5	55.5	56.9	56.9
175°	56.9	56.9	56.9	56.9	55.5	55.5	55.5	56.9	56.9	56.9	55.5
177.5°	56.9	56.9	56.9	56.9	55.5	56.9	56.9	56.9	56.9	56.9	56.9
180°	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9

(END OF REPORT)