

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P832569

Luminaire Tested: **TTN-D1-740-U-WQ-CG**

Issue Date: 5/14/2024

**Test Information**

Test Method: LM-79-08  
Report Number: P832569  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-254-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/14/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TTN-D1-740-U-WQ-CG  
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE  
4000K, 70 CRI LEDS AND WIDE DISTRIBUTION WITH CLEAR GLASS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3192 lumens  
Efficiency: N/A  
Efficacy: 120.9 lumens/watt  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B2 - U0 - G1  
  
Input Watts (W): 26.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P832569  
 CATALOG NUMBER: TTN-D1-740-U-WQ-CG

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.5 fc  
 Type V - Short - N/A

REPORT NUMBER: P832569  
CATALOG NUMBER: TTN-D1-740-U-WQ-CG

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral      - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P832569

CATALOG NUMBER: TTN-D1-740-U-WQ-CG


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1596.0	0.0	1596.0
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	1596.0	0.0	1596.0
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	3192.0	0.0	3192.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	28.8	0.9
10°-20°	93.0	2.9
20°-30°	195.6	6.1
30°-40°	352.6	11.0
40°-50°	560.6	17.6
50°-60°	747.9	23.4
60°-70°	722.6	22.6
70°-80°	418.7	13.1
80°-90°	72.2	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3192.0	100.0
0°-180°	3192.0	100.0

**Coefficient of Utilization**



REPORT NUMBER: P832569


CATALOG NUMBER: TTN-D1-740-U-WQ-CG

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	158.7	5.0			
FM (30°-60°)	830.6	26.0			
FH (60°-80°)	570.7	17.9			G0/660
FVH (80°-90°)	36.1	1.1			G1/100
BL (0°-30°)	158.7	5.0	B1/500		
BM (30°-60°)	830.6	26.0	B1/1000		
BH (60°-80°)	570.7	17.9	B2/1000		G0/660
BVH (80°-90°)	36.1	1.1			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G1**

Type V Short





REPORT NUMBER: P832569  
 CATALOG NUMBER: TTN-D1-740-U-WQ-CG

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	301.5	301.5	301.5	301.5	301.5	301.5	301.5	301.5	301.5	301.5	301.5
2.5°	298.8	298.8	298.8	298.8	298.8	298.8	298.8	298.8	298.8	298.8	298.8
5°	301.5	301.5	301.5	301.5	301.5	301.5	301.5	301.5	301.5	301.5	301.5
7.5°	298.8	298.8	301.5	301.5	301.5	301.5	301.5	301.5	301.5	298.8	298.8
10°	301.5	301.5	301.5	304.3	304.3	304.3	304.3	304.3	301.5	301.5	301.5
12.5°	307.1	307.1	309.8	309.8	309.8	309.8	309.8	309.8	309.8	307.1	307.1
15°	320.9	320.9	320.9	323.7	323.7	323.7	323.7	323.7	320.9	320.9	320.9
17.5°	334.7	334.7	337.5	337.5	340.3	340.3	340.3	337.5	337.5	337.5	337.5
20°	354.1	354.1	356.9	356.9	359.6	362.4	362.4	359.6	356.9	356.9	356.9
22.5°	379.0	381.8	381.8	381.8	384.5	390.1	387.3	384.5	381.8	381.8	381.8
25°	409.4	412.2	415.0	415.0	417.7	423.3	423.3	415.0	415.0	415.0	415.0
27.5°	445.4	448.2	450.9	450.9	453.7	459.2	456.5	450.9	450.9	448.2	448.2
30°	478.6	481.4	484.1	486.9	489.7	492.4	492.4	486.9	484.1	481.4	478.6
32.5°	511.8	511.8	517.3	522.9	528.4	528.4	531.2	522.9	517.3	511.8	509.0
35°	545.0	547.8	550.5	558.8	567.1	569.9	567.1	558.8	550.5	545.0	545.0
37.5°	580.9	583.7	586.5	597.5	605.8	611.4	605.8	597.5	586.5	580.9	578.2
40°	619.7	622.4	625.2	639.0	647.3	652.9	644.6	636.3	625.2	619.7	616.9
42.5°	655.6	661.2	666.7	683.3	697.1	702.7	694.4	680.5	669.5	655.6	652.9
45°	699.9	705.4	713.7	730.3	744.2	752.5	741.4	727.6	711.0	699.9	697.1
47.5°	735.9	741.4	749.7	771.8	791.2	796.7	785.7	769.1	746.9	733.1	730.3
50°	763.5	769.1	785.7	810.6	832.7	838.2	827.2	805.0	780.1	760.8	758.0
52.5°	785.7	791.2	810.6	843.8	868.7	877.0	863.1	838.2	805.0	782.9	780.1
55°	796.7	799.5	824.4	860.4	885.3	896.3	882.5	854.8	818.9	794.0	791.2
57.5°	788.4	791.2	818.9	857.6	885.3	899.1	885.3	852.1	813.3	788.4	785.7
60°	771.8	771.8	796.7	841.0	874.2	882.5	868.7	835.5	794.0	769.1	766.3
62.5°	741.4	738.6	769.1	807.8	841.0	849.3	838.2	805.0	763.5	738.6	735.9
65°	683.3	677.8	722.0	758.0	788.4	796.7	788.4	758.0	719.3	680.5	675.0
67.5°	614.1	605.8	647.3	688.8	716.5	727.6	716.5	691.6	647.3	608.6	605.8
70°	542.2	533.9	567.1	603.1	633.5	639.0	628.0	603.1	561.6	536.7	536.7
72.5°	456.5	448.2	478.6	506.3	536.7	542.2	531.2	509.0	478.6	453.7	450.9
75°	362.4	354.1	381.8	403.9	434.3	437.1	431.6	406.7	381.8	356.9	356.9
77.5°	268.3	260.0	282.2	301.5	326.4	326.4	323.7	304.3	282.2	265.6	265.6
80°	177.1	171.5	190.9	199.2	221.3	221.3	218.5	204.7	188.1	177.1	174.3
82.5°	99.6	94.1	110.7	113.4	130.0	130.0	127.3	116.2	105.1	96.8	96.8
85°	38.7	33.2	44.3	47.0	55.3	55.3	52.6	49.8	41.5	36.0	36.0
87.5°	2.8	2.8	5.5	5.5	8.3	8.3	8.3	5.5	5.5	2.8	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)