

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P631004

Luminaire Tested: GWS-SA1E-827-U-SLR-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P631004
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-43)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1E-827-U-SLR-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR RIGHT OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (16) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4358.2 lumens
Efficiency: N/A
Efficacy: 74.6 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B1 - U0 - G1


Input Watts (W): 58.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P631004
 CATALOG NUMBER: GWS-SA1E-827-U-SLR-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 11.9 fc
 Type III - Short - N/A

REPORT NUMBER: P631004
CATALOG NUMBER: GWS-SA1E-827-U-SLR-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P631004

CATALOG NUMBER: GWS-SA1E-827-U-SLR-W-GRSWH

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1527.7 | 0.0 | 1527.7 |
| | % Fixture | 35.1 | 0.0 | 35.1 |
| Street Side | Lumens | 2830.5 | 0.0 | 2830.5 |
| | % Fixture | 64.9 | 0.0 | 64.9 |
| Total | Lumens | 4358.2 | 0.0 | 4358.2 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 87.4 | 2.0 |
| 10°-20° | 276.0 | 6.3 |
| 20°-30° | 448.4 | 10.3 |
| 30°-40° | 632.3 | 14.5 |
| 40°-50° | 873.9 | 20.1 |
| 50°-60° | 1125.0 | 25.8 |
| 60°-70° | 712.8 | 16.4 |
| 70°-80° | 182.9 | 4.2 |
| 80°-90° | 19.6 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 4358.2 | 100.0 |
| 0°-180° | 4358.2 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P631004


CATALOG NUMBER: GWS-SA1E-827-U-SLR-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 442.5 | 10.2 | | | |
| FM (30°-60°) | 1781.4 | 40.9 | | | |
| FH (60°-80°) | 601.3 | 13.8 | | | G0/660 |
| FVH (80°-90°) | 5.3 | 0.1 | | | G0/10 |
| BL (0°-30°) | 369.2 | 8.5 | B1/500 | | |
| BM (30°-60°) | 849.8 | 19.5 | B1/1000 | | |
| BH (60°-80°) | 294.4 | 6.8 | B1/500 | | G1/500 |
| BVH (80°-90°) | 14.2 | 0.3 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G1

Type III Short





REPORT NUMBER: P631004

CATALOG NUMBER: GWS-SA1E-827-U-SLR-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 |
| 2.5° | 936.4 | 942.8 | 946.8 | 954.4 | 968.0 | 975.6 | 984.0 | 974.8 | 977.2 | 976.0 | 961.2 |
| 5° | 991.9 | 999.5 | 1009.9 | 1032.3 | 1057.4 | 1071.4 | 1084.6 | 1082.6 | 1070.2 | 1049.4 | 1034.7 |
| 7.5° | 1043.9 | 1052.6 | 1070.6 | 1106.9 | 1144.1 | 1165.6 | 1181.6 | 1171.2 | 1160.9 | 1128.1 | 1091.0 |
| 10° | 1084.6 | 1089.8 | 1114.1 | 1162.9 | 1206.0 | 1230.3 | 1249.9 | 1247.5 | 1233.1 | 1196.4 | 1146.5 |
| 12.5° | 1122.9 | 1126.5 | 1152.9 | 1201.6 | 1240.3 | 1251.1 | 1267.1 | 1272.3 | 1267.5 | 1239.9 | 1190.8 |
| 15° | 1164.1 | 1170.8 | 1195.2 | 1232.3 | 1249.9 | 1238.7 | 1244.3 | 1258.7 | 1272.3 | 1272.3 | 1227.1 |
| 17.5° | 1202.4 | 1208.4 | 1233.1 | 1249.1 | 1232.3 | 1202.8 | 1204.4 | 1222.8 | 1255.1 | 1289.0 | 1260.3 |
| 20° | 1236.3 | 1241.9 | 1266.3 | 1251.1 | 1198.0 | 1154.9 | 1153.7 | 1176.0 | 1228.3 | 1299.8 | 1295.8 |
| 22.5° | 1273.5 | 1281.5 | 1301.8 | 1252.7 | 1166.0 | 1111.3 | 1110.9 | 1134.1 | 1204.8 | 1310.6 | 1336.6 |
| 25° | 1326.2 | 1338.6 | 1348.9 | 1266.7 | 1148.9 | 1083.0 | 1088.2 | 1110.1 | 1197.2 | 1328.2 | 1396.9 |
| 27.5° | 1404.5 | 1414.4 | 1413.6 | 1295.8 | 1148.1 | 1071.4 | 1082.2 | 1107.7 | 1210.8 | 1359.3 | 1460.4 |
| 30° | 1489.1 | 1494.3 | 1485.9 | 1336.6 | 1166.4 | 1078.6 | 1094.6 | 1124.9 | 1245.1 | 1410.8 | 1553.8 |
| 32.5° | 1583.0 | 1589.3 | 1573.4 | 1397.7 | 1209.2 | 1131.7 | 1166.8 | 1181.6 | 1293.4 | 1485.1 | 1652.8 |
| 35° | 1690.8 | 1703.2 | 1670.0 | 1478.3 | 1335.0 | 1325.4 | 1376.5 | 1357.3 | 1396.1 | 1573.0 | 1758.7 |
| 37.5° | 1804.2 | 1804.6 | 1757.1 | 1597.7 | 1581.8 | 1598.1 | 1700.4 | 1640.5 | 1613.7 | 1670.8 | 1866.5 |
| 40° | 1900.4 | 1898.0 | 1824.9 | 1758.7 | 1796.6 | 1861.7 | 1985.1 | 1893.2 | 1822.9 | 1802.2 | 1955.9 |
| 42.5° | 1996.7 | 1987.9 | 1914.0 | 1860.9 | 1944.7 | 2078.5 | 2217.9 | 2105.3 | 1957.1 | 1921.6 | 2044.2 |
| 45° | 2119.7 | 2116.9 | 2027.8 | 1901.6 | 2078.5 | 2321.3 | 2506.2 | 2323.7 | 2036.6 | 1991.1 | 2191.1 |
| 47.5° | 2318.1 | 2304.5 | 2138.8 | 1898.4 | 2203.9 | 2644.8 | 2878.4 | 2598.9 | 2092.1 | 1992.7 | 2428.3 |
| 50° | 2512.2 | 2495.4 | 2271.4 | 1898.0 | 2333.3 | 2980.2 | 3317.6 | 2933.1 | 2148.8 | 2002.2 | 2669.5 |
| 52.5° | 2708.3 | 2708.3 | 2489.0 | 1943.1 | 2469.1 | 3354.8 | 3825.2 | 3349.6 | 2245.4 | 2127.6 | 2966.2 |
| 55° | 2824.9 | 2856.0 | 2733.8 | 2019.4 | 2628.0 | 3795.6 | 4327.2 | 3799.2 | 2394.8 | 2354.1 | 3240.2 |
| 57.5° | 2676.7 | 2735.0 | 2717.5 | 1966.3 | 2721.8 | 4119.5 | 4752.8 | 4140.3 | 2468.7 | 2380.8 | 3199.0 |
| 60° | 2181.2 | 2262.2 | 2302.5 | 1698.0 | 2629.2 | 4157.0 | 4841.9 | 4162.6 | 2316.1 | 2027.4 | 2740.2 |
| 62.5° | 1450.0 | 1516.7 | 1578.2 | 1213.2 | 2276.2 | 3739.7 | 4282.4 | 3740.9 | 1934.4 | 1513.1 | 1898.4 |
| 65° | 711.2 | 760.7 | 827.0 | 717.2 | 1778.2 | 3124.8 | 3338.8 | 3022.9 | 1399.3 | 847.0 | 968.4 |
| 67.5° | 186.1 | 200.1 | 209.2 | 278.3 | 1273.9 | 2245.0 | 2177.6 | 2211.1 | 898.9 | 276.7 | 253.2 |
| 70° | 96.6 | 97.4 | 97.0 | 115.0 | 861.0 | 1426.8 | 1500.7 | 1388.5 | 627.4 | 115.8 | 99.8 |
| 72.5° | 69.1 | 69.5 | 68.3 | 77.5 | 415.7 | 817.4 | 847.0 | 837.8 | 328.7 | 68.7 | 68.3 |
| 75° | 45.1 | 45.5 | 44.7 | 45.5 | 62.7 | 93.0 | 85.9 | 90.2 | 54.7 | 43.5 | 43.5 |
| 77.5° | 26.8 | 27.2 | 26.8 | 27.6 | 26.8 | 26.8 | 24.8 | 24.8 | 23.6 | 23.6 | 24.0 |
| 80° | 18.0 | 18.0 | 17.6 | 18.4 | 16.8 | 16.8 | 16.0 | 15.6 | 14.4 | 14.0 | 14.0 |
| 82.5° | 10.8 | 11.2 | 10.8 | 10.8 | 10.0 | 10.0 | 9.2 | 8.8 | 7.6 | 7.6 | 7.2 |
| 85° | 5.6 | 5.6 | 5.2 | 5.2 | 4.4 | 4.0 | 3.2 | 3.2 | 2.4 | 2.0 | 2.0 |
| 87.5° | 0.8 | 0.8 | 0.4 | 0.4 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P631004

CATALOG NUMBER: GWS-SA1E-827-U-SLR-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 |
| 2.5° | 957.2 | 949.2 | 937.2 | 925.7 | 914.9 | 903.7 | 890.9 | 877.7 | 866.6 | 855.0 | 849.0 |
| 5° | 1015.1 | 998.7 | 967.6 | 940.0 | 915.3 | 894.9 | 872.9 | 854.2 | 836.6 | 822.2 | 815.0 |
| 7.5° | 1067.4 | 1041.9 | 994.7 | 951.2 | 917.7 | 889.7 | 859.4 | 831.4 | 807.8 | 790.3 | 783.5 |
| 10° | 1115.7 | 1085.4 | 1023.5 | 968.4 | 929.2 | 898.1 | 861.0 | 823.0 | 791.9 | 768.7 | 763.1 |
| 12.5° | 1154.9 | 1120.1 | 1046.2 | 982.4 | 936.0 | 902.5 | 869.7 | 837.0 | 806.3 | 776.3 | 771.5 |
| 15° | 1189.6 | 1148.5 | 1063.4 | 991.1 | 933.6 | 890.9 | 863.4 | 859.4 | 859.4 | 825.4 | 815.8 |
| 17.5° | 1219.6 | 1174.4 | 1077.4 | 995.1 | 918.5 | 856.6 | 839.8 | 874.5 | 913.7 | 889.3 | 867.7 |
| 20° | 1253.9 | 1199.2 | 1089.0 | 995.1 | 890.5 | 813.0 | 811.4 | 870.5 | 928.4 | 928.8 | 906.1 |
| 22.5° | 1288.6 | 1227.9 | 1102.6 | 991.5 | 852.2 | 762.7 | 792.3 | 854.6 | 906.1 | 928.0 | 912.5 |
| 25° | 1344.9 | 1267.9 | 1124.1 | 988.7 | 807.4 | 728.4 | 775.1 | 833.4 | 876.9 | 900.1 | 890.1 |
| 27.5° | 1416.4 | 1320.6 | 1156.9 | 993.1 | 763.1 | 708.0 | 756.7 | 805.9 | 845.4 | 865.8 | 858.6 |
| 30° | 1496.3 | 1381.3 | 1192.0 | 1000.7 | 731.2 | 697.6 | 734.8 | 774.3 | 809.4 | 829.8 | 826.6 |
| 32.5° | 1598.1 | 1447.2 | 1222.4 | 990.3 | 713.2 | 692.4 | 711.6 | 740.0 | 773.9 | 786.7 | 789.5 |
| 35° | 1719.9 | 1519.9 | 1245.5 | 949.6 | 696.8 | 686.9 | 686.5 | 704.0 | 728.0 | 748.3 | 750.3 |
| 37.5° | 1832.1 | 1604.9 | 1271.1 | 879.7 | 667.3 | 672.9 | 656.9 | 667.3 | 690.8 | 711.2 | 719.2 |
| 40° | 1943.1 | 1691.2 | 1306.6 | 790.7 | 628.5 | 641.7 | 623.0 | 630.1 | 648.9 | 675.7 | 688.4 |
| 42.5° | 2051.0 | 1769.0 | 1344.2 | 699.6 | 589.8 | 598.2 | 584.2 | 591.4 | 611.0 | 644.5 | 658.9 |
| 45° | 2168.4 | 1874.5 | 1373.3 | 613.8 | 556.3 | 552.7 | 541.5 | 551.9 | 581.4 | 618.2 | 635.3 |
| 47.5° | 2390.4 | 2040.6 | 1392.5 | 556.7 | 538.3 | 512.3 | 499.6 | 521.9 | 555.5 | 592.6 | 613.4 |
| 50° | 2661.5 | 2281.0 | 1386.9 | 520.3 | 522.7 | 470.8 | 466.4 | 496.0 | 531.9 | 570.6 | 593.4 |
| 52.5° | 2876.4 | 2517.0 | 1323.4 | 485.6 | 492.4 | 444.5 | 431.7 | 474.8 | 509.1 | 548.7 | 572.2 |
| 55° | 3040.5 | 2596.5 | 1128.5 | 444.5 | 442.9 | 425.3 | 398.5 | 452.8 | 486.4 | 523.1 | 548.7 |
| 57.5° | 2906.7 | 2419.6 | 836.6 | 387.8 | 378.2 | 387.4 | 361.4 | 415.7 | 458.4 | 494.8 | 517.5 |
| 60° | 2412.4 | 1929.2 | 466.0 | 343.4 | 316.3 | 338.6 | 334.6 | 376.6 | 428.1 | 466.4 | 486.0 |
| 62.5° | 1637.7 | 1284.7 | 276.3 | 271.5 | 256.4 | 288.3 | 309.5 | 337.0 | 387.8 | 418.9 | 437.3 |
| 65° | 816.2 | 624.2 | 183.7 | 203.3 | 205.3 | 237.2 | 277.1 | 307.5 | 349.8 | 381.8 | 400.1 |
| 67.5° | 236.8 | 194.1 | 139.8 | 155.3 | 176.9 | 202.5 | 234.4 | 270.3 | 311.5 | 349.4 | 371.0 |
| 70° | 102.2 | 103.4 | 111.0 | 129.4 | 150.5 | 176.9 | 208.9 | 244.0 | 278.7 | 307.9 | 324.3 |
| 72.5° | 72.3 | 75.1 | 83.5 | 102.2 | 122.2 | 147.4 | 179.3 | 213.2 | 238.4 | 268.0 | 285.1 |
| 75° | 46.3 | 48.3 | 55.1 | 69.5 | 84.3 | 108.6 | 139.0 | 170.1 | 196.1 | 217.2 | 233.6 |
| 77.5° | 25.6 | 26.0 | 31.5 | 39.9 | 49.9 | 65.5 | 87.9 | 112.2 | 131.4 | 143.4 | 158.1 |
| 80° | 14.8 | 14.8 | 17.6 | 22.8 | 28.8 | 38.3 | 50.7 | 62.7 | 74.3 | 81.9 | 89.1 |
| 82.5° | 8.0 | 8.0 | 9.2 | 12.4 | 15.6 | 21.2 | 28.4 | 34.3 | 41.5 | 45.5 | 50.3 |
| 85° | 2.4 | 2.4 | 3.2 | 4.4 | 5.6 | 8.0 | 11.2 | 14.4 | 17.6 | 20.4 | 23.2 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.4 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P631004
 CATALOG NUMBER: GWS-SA1E-827-U-SLR-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 |
| 2.5° | 847.8 | 842.2 | 839.0 | 835.0 | 836.2 | 832.6 | 830.6 | 831.8 | 824.6 | 831.8 | 839.0 |
| 5° | 812.2 | 804.3 | 797.9 | 792.7 | 790.3 | 785.5 | 782.7 | 782.7 | 778.3 | 785.5 | 794.3 |
| 7.5° | 781.1 | 774.7 | 771.5 | 768.3 | 764.7 | 760.3 | 755.5 | 753.9 | 751.1 | 758.7 | 766.3 |
| 10° | 760.3 | 761.1 | 763.1 | 767.5 | 766.7 | 763.9 | 756.7 | 752.7 | 752.7 | 761.5 | 773.1 |
| 12.5° | 769.9 | 778.3 | 783.1 | 791.1 | 792.7 | 790.3 | 783.1 | 779.9 | 787.9 | 801.1 | 820.2 |
| 15° | 807.0 | 812.6 | 816.6 | 823.0 | 822.6 | 820.6 | 815.0 | 817.4 | 843.8 | 869.3 | 886.5 |
| 17.5° | 847.4 | 841.0 | 840.2 | 844.2 | 845.4 | 843.0 | 839.8 | 850.6 | 894.1 | 918.1 | 926.8 |
| 20° | 876.5 | 854.6 | 849.8 | 851.4 | 854.6 | 853.4 | 853.4 | 870.9 | 916.1 | 927.2 | 916.1 |
| 22.5° | 885.3 | 854.2 | 847.0 | 847.4 | 851.8 | 852.2 | 854.2 | 872.5 | 898.9 | 899.3 | 882.1 |
| 25° | 871.3 | 841.4 | 836.2 | 837.0 | 842.2 | 841.8 | 842.6 | 853.0 | 864.6 | 859.8 | 847.0 |
| 27.5° | 845.0 | 819.0 | 817.4 | 821.8 | 828.6 | 825.0 | 822.6 | 825.4 | 831.0 | 825.0 | 813.8 |
| 30° | 815.0 | 793.1 | 793.9 | 802.3 | 809.4 | 803.5 | 797.5 | 799.1 | 799.5 | 793.1 | 780.3 |
| 32.5° | 783.5 | 767.1 | 769.9 | 778.7 | 787.1 | 780.7 | 774.3 | 773.5 | 765.9 | 758.3 | 746.0 |
| 35° | 751.9 | 745.6 | 749.1 | 756.3 | 763.5 | 758.3 | 754.3 | 751.9 | 735.6 | 724.4 | 714.0 |
| 37.5° | 723.2 | 728.0 | 734.4 | 738.8 | 741.2 | 740.8 | 738.4 | 732.8 | 711.2 | 698.0 | 684.5 |
| 40° | 697.6 | 712.4 | 719.2 | 721.2 | 724.8 | 724.0 | 723.6 | 715.6 | 687.3 | 673.3 | 657.7 |
| 42.5° | 674.5 | 695.2 | 706.8 | 708.8 | 710.8 | 711.2 | 710.0 | 698.4 | 666.1 | 649.7 | 634.9 |
| 45° | 652.1 | 679.3 | 694.0 | 692.0 | 694.8 | 694.8 | 696.0 | 680.9 | 645.3 | 628.5 | 613.0 |
| 47.5° | 632.5 | 664.5 | 678.1 | 675.7 | 677.3 | 678.5 | 679.7 | 662.1 | 622.6 | 606.6 | 590.6 |
| 50° | 614.6 | 648.5 | 660.1 | 660.9 | 660.9 | 663.7 | 663.3 | 646.1 | 603.4 | 586.2 | 570.2 |
| 52.5° | 595.4 | 632.1 | 644.5 | 649.7 | 651.3 | 652.5 | 646.9 | 627.0 | 583.8 | 563.1 | 548.3 |
| 55° | 573.0 | 615.4 | 626.6 | 633.3 | 636.5 | 635.7 | 628.1 | 607.8 | 563.9 | 543.1 | 526.3 |
| 57.5° | 539.1 | 579.4 | 595.4 | 598.6 | 603.8 | 600.6 | 591.8 | 574.6 | 531.9 | 511.1 | 494.0 |
| 60° | 502.0 | 531.1 | 543.9 | 546.7 | 542.7 | 543.9 | 542.7 | 526.3 | 489.2 | 472.8 | 455.2 |
| 62.5° | 453.2 | 479.2 | 492.8 | 496.4 | 489.6 | 494.0 | 492.4 | 472.0 | 434.9 | 417.7 | 402.1 |
| 65° | 416.5 | 444.9 | 460.8 | 462.8 | 460.8 | 462.8 | 457.2 | 432.5 | 397.3 | 379.8 | 363.8 |
| 67.5° | 387.8 | 416.9 | 433.7 | 439.3 | 437.3 | 436.9 | 428.1 | 399.3 | 363.0 | 343.8 | 323.5 |
| 70° | 338.2 | 363.8 | 385.4 | 398.9 | 398.9 | 391.3 | 374.6 | 347.8 | 318.7 | 302.3 | 286.3 |
| 72.5° | 299.5 | 331.8 | 353.0 | 367.0 | 369.8 | 365.4 | 341.8 | 313.5 | 279.9 | 263.6 | 246.8 |
| 75° | 246.8 | 278.3 | 301.1 | 319.5 | 323.1 | 318.3 | 291.1 | 263.2 | 232.0 | 216.0 | 199.3 |
| 77.5° | 164.9 | 183.7 | 202.1 | 218.8 | 215.2 | 218.4 | 200.1 | 178.9 | 159.7 | 147.8 | 140.2 |
| 80° | 93.0 | 105.4 | 111.0 | 120.2 | 120.2 | 120.2 | 108.2 | 98.2 | 87.5 | 80.7 | 73.1 |
| 82.5° | 52.7 | 60.7 | 63.1 | 70.7 | 72.7 | 73.1 | 65.1 | 58.7 | 51.9 | 48.3 | 43.1 |
| 85° | 24.4 | 28.8 | 29.2 | 33.5 | 35.1 | 38.3 | 34.7 | 30.3 | 26.4 | 24.8 | 21.6 |
| 87.5° | 0.8 | 2.4 | 3.2 | 6.0 | 8.0 | 9.2 | 10.0 | 10.0 | 8.4 | 7.6 | 6.4 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P631004
 CATALOG NUMBER: GWS-SA1E-827-U-SLR-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|-------|-------|-------|-------|-------|-------|--------|--------|--------|--------|
| 0° | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 | 895.3 |
| 2.5° | 847.8 | 857.4 | 868.5 | 876.5 | 890.9 | 902.9 | 915.3 | 928.8 | 938.8 | 936.4 |
| 5° | 805.1 | 821.0 | 841.4 | 860.2 | 886.9 | 914.1 | 944.0 | 974.8 | 992.7 | 991.9 |
| 7.5° | 781.1 | 803.9 | 828.6 | 853.8 | 885.3 | 924.5 | 970.4 | 1018.3 | 1042.7 | 1043.9 |
| 10° | 793.9 | 818.2 | 835.0 | 856.2 | 889.3 | 938.4 | 993.5 | 1051.0 | 1079.0 | 1084.6 |
| 12.5° | 834.2 | 832.2 | 831.0 | 846.2 | 886.1 | 948.4 | 1015.9 | 1084.6 | 1116.1 | 1122.9 |
| 15° | 872.5 | 831.4 | 806.7 | 817.0 | 871.7 | 954.8 | 1037.9 | 1121.3 | 1156.9 | 1164.1 |
| 17.5° | 879.7 | 817.4 | 771.5 | 778.7 | 849.0 | 956.8 | 1059.0 | 1157.3 | 1195.6 | 1202.4 |
| 20° | 859.8 | 799.5 | 746.0 | 736.0 | 820.2 | 951.6 | 1072.2 | 1187.2 | 1229.1 | 1236.3 |
| 22.5° | 834.6 | 783.5 | 726.8 | 700.8 | 785.1 | 946.4 | 1087.0 | 1218.8 | 1267.1 | 1273.5 |
| 25° | 808.2 | 763.1 | 708.8 | 669.3 | 745.2 | 943.2 | 1111.7 | 1260.3 | 1318.6 | 1326.2 |
| 27.5° | 780.3 | 738.4 | 693.2 | 654.1 | 708.4 | 947.2 | 1146.9 | 1327.4 | 1393.7 | 1404.5 |
| 30° | 750.3 | 713.6 | 683.3 | 648.9 | 683.3 | 950.8 | 1185.6 | 1396.1 | 1473.9 | 1489.1 |
| 32.5° | 719.2 | 690.8 | 672.9 | 651.3 | 667.7 | 942.4 | 1219.6 | 1473.1 | 1569.8 | 1583.0 |
| 35° | 688.0 | 667.7 | 659.7 | 655.7 | 646.9 | 911.7 | 1247.1 | 1551.0 | 1679.2 | 1690.8 |
| 37.5° | 658.9 | 643.7 | 641.3 | 645.7 | 615.0 | 861.4 | 1279.1 | 1650.0 | 1786.6 | 1804.2 |
| 40° | 631.7 | 617.8 | 617.4 | 616.6 | 579.8 | 792.7 | 1322.2 | 1750.7 | 1892.4 | 1900.4 |
| 42.5° | 606.6 | 589.0 | 592.2 | 582.6 | 551.1 | 718.4 | 1362.9 | 1836.5 | 1991.1 | 1996.7 |
| 45° | 584.2 | 561.1 | 564.7 | 552.7 | 537.5 | 640.5 | 1398.9 | 1938.0 | 2116.1 | 2119.7 |
| 47.5° | 562.7 | 537.9 | 527.9 | 527.1 | 535.1 | 568.6 | 1434.0 | 2133.2 | 2311.7 | 2318.1 |
| 50° | 542.7 | 515.9 | 487.6 | 505.2 | 520.3 | 514.7 | 1477.9 | 2342.5 | 2513.8 | 2512.2 |
| 52.5° | 523.5 | 488.4 | 448.1 | 482.0 | 482.0 | 474.8 | 1465.5 | 2469.5 | 2680.7 | 2708.3 |
| 55° | 501.6 | 444.1 | 406.9 | 443.3 | 425.7 | 438.9 | 1246.3 | 2511.0 | 2785.7 | 2824.9 |
| 57.5° | 458.0 | 389.3 | 357.0 | 376.6 | 350.2 | 406.9 | 895.3 | 2304.9 | 2607.2 | 2676.7 |
| 60° | 416.1 | 349.0 | 327.9 | 324.3 | 289.9 | 331.8 | 580.2 | 1804.6 | 2146.0 | 2181.2 |
| 62.5° | 367.0 | 314.3 | 296.3 | 268.8 | 233.2 | 241.6 | 351.4 | 1187.6 | 1442.0 | 1450.0 |
| 65° | 329.8 | 284.7 | 250.4 | 217.6 | 190.9 | 175.3 | 207.7 | 572.6 | 720.8 | 711.2 |
| 67.5° | 283.1 | 244.0 | 211.2 | 187.7 | 165.7 | 146.2 | 138.2 | 170.1 | 192.5 | 186.1 |
| 70° | 252.0 | 214.4 | 182.9 | 160.5 | 140.2 | 120.6 | 106.6 | 100.2 | 98.2 | 96.6 |
| 72.5° | 217.2 | 184.5 | 151.7 | 130.2 | 111.0 | 93.0 | 80.3 | 72.7 | 70.7 | 69.1 |
| 75° | 173.3 | 142.6 | 112.6 | 92.2 | 75.5 | 62.7 | 54.3 | 47.9 | 46.7 | 45.1 |
| 77.5° | 114.6 | 91.4 | 67.1 | 54.7 | 44.7 | 37.9 | 32.3 | 28.4 | 27.6 | 26.8 |
| 80° | 63.1 | 52.7 | 41.1 | 33.1 | 26.8 | 23.2 | 21.2 | 18.8 | 18.4 | 18.0 |
| 82.5° | 37.5 | 31.5 | 23.6 | 18.8 | 15.6 | 14.0 | 12.8 | 11.6 | 11.2 | 10.8 |
| 85° | 18.8 | 14.8 | 10.4 | 8.8 | 8.0 | 7.2 | 7.2 | 6.0 | 5.6 | 5.6 |
| 87.5° | 4.8 | 4.0 | 2.4 | 2.0 | 2.0 | 2.0 | 1.6 | 1.2 | 1.2 | 0.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 2764K
 CIE x = 0.4581
 CIE y = 0.4156
 Duv = 0.0020

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_g = -1.5$



Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)