

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P631014

Luminaire Tested: GWS-SA1E-827-U-T2R-W-HSS

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P631014
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1E-827-U-T2R-W-HSS
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II ROADWAY OPTICS WITH HOUSE SIDE SHIELD
Light Source: (16) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4492.4 lumens
Efficiency: N/A
Efficacy: 76.9 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B0 - U0 - G1


Input Watts (W): 58.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P631014
 CATALOG NUMBER: GWS-SA1E-827-U-T2R-W-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 13.5 fc
 Type II - Short - N/A

REPORT NUMBER: P631014
CATALOG NUMBER: GWS-SA1E-827-U-T2R-W-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 76-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P631014
 CATALOG NUMBER: GWS-SA1E-827-U-T2R-W-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 248.4 | 0.0 | 248.4 |
| | % Fixture | 5.5 | 0.0 | 5.5 |
| Street Side | Lumens | 4244.0 | 0.0 | 4244.0 |
| | % Fixture | 94.5 | 0.0 | 94.5 |
| Total | Lumens | 4492.4 | 0.0 | 4492.4 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 48.4 | 1.1 |
| 10°-20° | 183.6 | 4.1 |
| 20°-30° | 374.6 | 8.3 |
| 30°-40° | 666.2 | 14.8 |
| 40°-50° | 984.8 | 21.9 |
| 50°-60° | 1127.5 | 25.1 |
| 60°-70° | 860.3 | 19.1 |
| 70°-80° | 241.0 | 5.4 |
| 80°-90° | 6.1 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 4492.4 | 100.0 |
| 0°-180° | 4492.4 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P631014

CATALOG NUMBER: GWS-SA1E-827-U-T2R-W-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 535.7 | 11.9 | | | |
| FM (30°-60°) | 2656.0 | 59.1 | | | |
| FH (60°-80°) | 1046.6 | 23.3 | | | G1/1800 |
| FVH (80°-90°) | 5.7 | 0.1 | | | G0/10 |
| BL (0°-30°) | 70.9 | 1.6 | B0/110 | | |
| BM (30°-60°) | 122.6 | 2.7 | B0/220 | | |
| BH (60°-80°) | 54.6 | 1.2 | B0/110 | | G0/110 |
| BVH (80°-90°) | 0.4 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B0-U0-G1
 Type II Short





REPORT NUMBER: P631014

CATALOG NUMBER: GWS-SA1E-827-U-T2R-W-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 76° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 397.7 | 397.7 | 397.7 | 397.7 | 397.7 | 397.7 | 397.7 | 397.7 | 397.7 | 397.7 | 397.7 |
| 2.5° | 613.0 | 622.2 | 615.0 | 603.0 | 579.8 | 557.5 | 528.7 | 489.2 | 457.6 | 453.6 | 424.1 |
| 5° | 827.8 | 827.0 | 811.5 | 795.9 | 771.5 | 733.2 | 675.3 | 601.8 | 531.1 | 525.1 | 458.8 |
| 7.5° | 955.6 | 956.8 | 948.0 | 936.0 | 912.1 | 872.6 | 812.3 | 723.6 | 620.2 | 608.2 | 506.4 |
| 10° | 1063.0 | 1062.6 | 1056.3 | 1050.7 | 1029.1 | 1002.7 | 938.0 | 840.6 | 716.0 | 697.2 | 559.5 |
| 12.5° | 1143.7 | 1146.5 | 1149.7 | 1155.3 | 1146.1 | 1120.1 | 1059.0 | 952.8 | 813.1 | 792.3 | 620.2 |
| 15° | 1207.6 | 1208.4 | 1220.4 | 1241.9 | 1249.5 | 1236.0 | 1180.4 | 1061.4 | 908.9 | 890.9 | 690.1 |
| 17.5° | 1226.8 | 1228.4 | 1248.7 | 1288.3 | 1328.2 | 1335.8 | 1293.9 | 1170.9 | 1003.1 | 984.0 | 757.9 |
| 20° | 1267.1 | 1270.7 | 1285.9 | 1320.6 | 1370.9 | 1411.7 | 1395.3 | 1281.5 | 1097.4 | 1072.2 | 827.4 |
| 22.5° | 1394.1 | 1396.1 | 1390.9 | 1395.3 | 1421.2 | 1468.4 | 1478.4 | 1388.5 | 1194.0 | 1167.3 | 902.5 |
| 25° | 1612.5 | 1613.3 | 1577.0 | 1542.6 | 1523.1 | 1531.9 | 1553.8 | 1487.1 | 1289.9 | 1263.5 | 972.4 |
| 27.5° | 1839.4 | 1842.1 | 1798.6 | 1740.3 | 1670.4 | 1630.5 | 1624.1 | 1577.4 | 1386.5 | 1357.4 | 1041.5 |
| 30° | 2053.0 | 2053.0 | 2007.1 | 1936.0 | 1842.5 | 1764.7 | 1718.8 | 1668.4 | 1489.9 | 1458.0 | 1112.2 |
| 32.5° | 2245.1 | 2243.5 | 2184.8 | 2107.7 | 2015.5 | 1930.0 | 1833.4 | 1763.5 | 1604.9 | 1569.4 | 1193.6 |
| 35° | 2403.6 | 2399.6 | 2332.9 | 2259.1 | 2160.4 | 2096.9 | 1989.1 | 1865.7 | 1729.5 | 1694.0 | 1277.5 |
| 37.5° | 2523.4 | 2519.0 | 2457.9 | 2379.7 | 2288.2 | 2247.1 | 2156.8 | 1988.3 | 1860.9 | 1828.6 | 1370.5 |
| 40° | 2588.5 | 2579.7 | 2537.4 | 2479.1 | 2402.4 | 2366.5 | 2328.9 | 2140.5 | 2015.5 | 1975.1 | 1480.3 |
| 42.5° | 2607.7 | 2597.3 | 2569.3 | 2542.2 | 2495.9 | 2467.5 | 2507.8 | 2312.2 | 2185.2 | 2150.4 | 1605.7 |
| 45° | 2551.0 | 2545.0 | 2542.6 | 2562.2 | 2570.5 | 2578.5 | 2678.0 | 2502.3 | 2372.5 | 2346.1 | 1763.5 |
| 47.5° | 2414.4 | 2412.8 | 2434.0 | 2515.4 | 2604.1 | 2688.3 | 2862.9 | 2736.7 | 2615.3 | 2586.9 | 1983.9 |
| 50° | 2162.0 | 2178.4 | 2237.5 | 2380.5 | 2557.8 | 2750.6 | 3035.8 | 3061.7 | 3008.2 | 2966.7 | 2271.4 |
| 52.5° | 1767.5 | 1799.0 | 1931.6 | 2148.8 | 2403.6 | 2733.1 | 3115.6 | 3322.1 | 3376.8 | 3333.7 | 2477.5 |
| 55° | 1386.9 | 1416.5 | 1534.7 | 1810.2 | 2150.0 | 2599.3 | 3119.2 | 3411.9 | 3531.4 | 3491.4 | 2616.9 |
| 57.5° | 1033.1 | 1060.2 | 1167.7 | 1431.2 | 1805.0 | 2336.1 | 3033.8 | 3461.9 | 3714.6 | 3689.1 | 2836.9 |
| 60° | 675.3 | 702.0 | 799.1 | 1029.5 | 1400.1 | 1952.8 | 2823.3 | 3451.5 | 3964.2 | 3961.8 | 3107.3 |
| 62.5° | 374.6 | 395.7 | 466.0 | 645.7 | 977.2 | 1512.3 | 2492.7 | 3347.3 | 4205.8 | 4221.0 | 3330.1 |
| 65° | 191.7 | 205.3 | 248.0 | 355.0 | 591.4 | 1072.2 | 2057.8 | 3108.5 | 4317.6 | 4356.0 | 3388.8 |
| 67.5° | 125.4 | 129.8 | 140.2 | 184.5 | 316.7 | 674.5 | 1548.6 | 2725.5 | 4160.3 | 4205.0 | 3191.9 |
| 70° | 101.8 | 105.4 | 111.4 | 123.0 | 163.3 | 358.2 | 1017.1 | 2176.8 | 3476.2 | 3506.6 | 2541.8 |
| 72.5° | 74.7 | 79.5 | 91.0 | 98.6 | 117.8 | 196.5 | 529.1 | 1428.8 | 2387.2 | 2440.8 | 1597.4 |
| 75° | 55.1 | 57.9 | 67.5 | 77.9 | 96.2 | 124.2 | 202.5 | 751.2 | 1232.8 | 1201.6 | 670.9 |
| 77.5° | 33.1 | 35.1 | 43.1 | 49.9 | 68.7 | 77.5 | 70.7 | 277.5 | 375.0 | 352.6 | 162.1 |
| 80° | 16.4 | 18.4 | 28.4 | 37.5 | 43.9 | 31.1 | 29.6 | 77.5 | 83.5 | 83.5 | 40.7 |
| 82.5° | 5.6 | 7.2 | 15.2 | 24.8 | 21.6 | 12.0 | 14.0 | 20.0 | 22.4 | 23.6 | 12.0 |
| 85° | 0.0 | 0.0 | 3.6 | 7.2 | 3.2 | 1.6 | 3.6 | 4.4 | 5.6 | 6.0 | 4.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.4 | 1.2 | 1.6 | 1.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P631014
 CATALOG NUMBER: GWS-SA1E-827-U-T2R-W-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 397.7 | 397.7 | 397.7 | 397.7 | 397.7 | 397.7 | 397.7 | 397.7 | 397.7 | 397.7 | 397.7 |
| 2.5° | 408.1 | 389.4 | 361.0 | 335.4 | 315.9 | 297.5 | 283.5 | 272.3 | 270.4 | 264.0 | 264.8 |
| 5° | 426.5 | 392.5 | 340.2 | 299.9 | 271.6 | 252.4 | 236.4 | 224.4 | 219.2 | 214.0 | 210.1 |
| 7.5° | 454.8 | 405.7 | 332.2 | 283.1 | 250.0 | 220.4 | 195.7 | 175.7 | 166.1 | 160.1 | 156.1 |
| 10° | 489.6 | 424.1 | 332.6 | 273.1 | 224.0 | 178.9 | 145.0 | 123.0 | 112.6 | 109.4 | 109.0 |
| 12.5° | 531.1 | 447.3 | 335.8 | 256.8 | 186.5 | 133.0 | 107.4 | 97.4 | 94.2 | 91.4 | 91.4 |
| 15° | 575.0 | 473.2 | 335.8 | 226.8 | 142.2 | 103.8 | 93.0 | 86.7 | 82.7 | 81.1 | 80.3 |
| 17.5° | 621.4 | 497.6 | 327.9 | 185.7 | 109.0 | 91.4 | 82.7 | 76.7 | 73.5 | 71.1 | 70.3 |
| 20° | 670.9 | 520.7 | 307.9 | 142.2 | 93.4 | 81.9 | 73.5 | 67.5 | 64.3 | 61.9 | 61.9 |
| 22.5° | 721.2 | 542.3 | 275.5 | 109.4 | 82.7 | 72.7 | 64.7 | 59.1 | 55.9 | 53.5 | 53.5 |
| 25° | 767.9 | 556.7 | 234.0 | 90.3 | 74.7 | 64.7 | 57.5 | 51.9 | 48.3 | 46.7 | 45.9 |
| 27.5° | 811.5 | 565.9 | 188.1 | 79.5 | 67.1 | 57.9 | 50.3 | 45.1 | 42.3 | 41.1 | 40.3 |
| 30° | 856.6 | 568.3 | 143.8 | 72.3 | 60.7 | 51.1 | 43.9 | 39.9 | 37.5 | 35.9 | 35.9 |
| 32.5° | 900.5 | 565.5 | 109.8 | 66.3 | 55.1 | 45.1 | 39.1 | 35.5 | 33.5 | 32.3 | 31.9 |
| 35° | 945.2 | 552.7 | 89.1 | 61.1 | 49.5 | 39.5 | 34.7 | 31.9 | 30.7 | 29.2 | 29.2 |
| 37.5° | 994.0 | 535.5 | 77.5 | 55.9 | 43.9 | 35.5 | 31.1 | 29.2 | 27.6 | 26.4 | 26.0 |
| 40° | 1054.7 | 515.5 | 71.1 | 51.5 | 38.7 | 31.9 | 28.0 | 26.0 | 24.8 | 23.6 | 23.2 |
| 42.5° | 1126.5 | 496.0 | 67.9 | 46.7 | 34.7 | 28.4 | 25.2 | 22.8 | 21.6 | 20.0 | 19.6 |
| 45° | 1228.4 | 491.6 | 64.3 | 41.5 | 31.1 | 25.6 | 22.0 | 19.6 | 18.0 | 16.8 | 16.4 |
| 47.5° | 1392.1 | 504.0 | 58.3 | 35.9 | 27.6 | 22.4 | 18.8 | 16.8 | 14.8 | 13.6 | 12.8 |
| 50° | 1554.6 | 500.8 | 52.3 | 31.1 | 24.4 | 19.2 | 16.0 | 14.0 | 12.0 | 10.8 | 10.4 |
| 52.5° | 1643.3 | 485.6 | 46.7 | 27.6 | 21.2 | 16.4 | 13.6 | 11.2 | 10.0 | 8.8 | 8.4 |
| 55° | 1723.5 | 479.6 | 41.1 | 24.0 | 18.0 | 14.4 | 11.2 | 9.2 | 8.4 | 7.2 | 6.8 |
| 57.5° | 1880.9 | 493.6 | 36.3 | 20.8 | 15.6 | 12.4 | 9.6 | 7.6 | 6.8 | 5.6 | 5.2 |
| 60° | 2045.4 | 495.2 | 31.1 | 18.0 | 13.6 | 10.4 | 7.6 | 6.0 | 5.2 | 4.0 | 3.6 |
| 62.5° | 2131.3 | 454.8 | 25.6 | 15.2 | 11.2 | 8.8 | 6.4 | 4.8 | 4.0 | 2.4 | 2.4 |
| 65° | 2059.4 | 367.8 | 21.6 | 12.4 | 8.8 | 6.8 | 4.8 | 3.6 | 2.4 | 1.2 | 0.4 |
| 67.5° | 1822.6 | 261.6 | 18.0 | 10.0 | 6.4 | 4.8 | 3.6 | 2.4 | 0.4 | 0.0 | 0.0 |
| 70° | 1334.6 | 149.4 | 14.0 | 7.2 | 4.8 | 3.2 | 2.4 | 1.2 | 0.0 | 0.0 | 0.0 |
| 72.5° | 820.2 | 79.9 | 10.4 | 4.8 | 3.6 | 2.4 | 2.0 | 0.8 | 0.0 | 0.0 | 0.0 |
| 75° | 311.1 | 38.3 | 6.4 | 3.2 | 2.8 | 2.0 | 1.2 | 0.4 | 0.0 | 0.0 | 0.0 |
| 77.5° | 84.3 | 18.8 | 3.6 | 2.4 | 2.0 | 1.2 | 0.8 | 0.0 | 0.0 | 0.0 | 0.0 |
| 80° | 22.0 | 8.8 | 2.4 | 1.6 | 1.2 | 0.8 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 7.6 | 4.0 | 1.2 | 1.2 | 0.8 | 0.4 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 3.2 | 1.6 | 0.8 | 0.8 | 0.4 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 1.2 | 0.4 | 0.4 | 0.4 | 0.4 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 2764K
 CIE x = 0.4581
 CIE y = 0.4156
 Duv = 0.0020

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_g = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)