

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P638405

Luminaire Tested: GWS-SA4E-827-U-5WQ-W-GRSWH

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P638405  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA4E-827-U-5WQ-W-GRSWH  
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE V WIDE OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH  
Light Source: (64) 2700K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 18999.3 lumens  
Efficiency: N/A  
Efficacy: 93.8 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B4 - U0 - G2  
  
Input Watts (W): 202.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P638405  
 CATALOG NUMBER: GWS-SA4E-827-U-5WQ-W-GRSWH

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 5.6 fc  
 Type V - Short - N/A

REPORT NUMBER: P638405  
CATALOG NUMBER: GWS-SA4E-827-U-5WQ-W-GRSWH

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P638405

CATALOG NUMBER: GWS-SA4E-827-U-5WQ-W-GRSWH

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 9499.6   | 0.0    | 9499.6  |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Street Side</b> | Lumens    | 9499.6   | 0.0    | 9499.6  |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Total</b>       | Lumens    | 18999.3  | 0.0    | 18999.3 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 329.3   | 1.7       |
| 10°-20°   | 990.4   | 5.2       |
| 20°-30°   | 1752.2  | 9.2       |
| 30°-40°   | 2821.1  | 14.8      |
| 40°-50°   | 3877.6  | 20.4      |
| 50°-60°   | 5167.2  | 27.2      |
| 60°-70°   | 3220.5  | 17.0      |
| 70°-80°   | 740.6   | 3.9       |
| 80°-90°   | 100.5   | 0.5       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 18999.3 | 100.0     |
| 0°-180°   | 18999.3 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P638405


CATALOG NUMBER: GWS-SA4E-827-U-5WQ-W-GRSWH

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 1536.0 | 8.1       |                         |      |         |
| FM (30°-60°)   | 5932.9 | 31.2      |                         |      |         |
| FH (60°-80°)   | 1980.5 | 10.4      |                         |      | G2/5000 |
| FVH (80°-90°)  | 50.2   | 0.3       |                         |      | G1/100  |
| BL (0°-30°)    | 1536.0 | 8.1       | B3/2500                 |      |         |
| BM (30°-60°)   | 5932.9 | 31.2      | B4/8500                 |      |         |
| BH (60°-80°)   | 1980.5 | 10.4      | B3/2500                 |      | G2/5000 |
| BVH (80°-90°)  | 50.2   | 0.3       |                         |      | G1/100  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B4-U0-G2**

Type V Short





REPORT NUMBER: P638405

CATALOG NUMBER: GWS-SA4E-827-U-5WQ-W-GRSWH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 3472.1 | 3472.1 | 3472.1 | 3472.1 | 3472.1 | 3472.1 | 3472.1 | 3472.1 | 3472.1 | 3472.1 | 3472.1 |
| 2.5°  | 3447.9 | 3451.1 | 3457.6 | 3462.4 | 3468.9 | 3475.3 | 3478.5 | 3472.1 | 3468.9 | 3456.0 | 3470.5 |
| 5°    | 3451.1 | 3454.4 | 3459.2 | 3459.2 | 3460.8 | 3465.6 | 3465.6 | 3457.6 | 3449.5 | 3435.0 | 3451.1 |
| 7.5°  | 3446.3 | 3449.5 | 3451.1 | 3449.5 | 3451.1 | 3452.7 | 3449.5 | 3439.8 | 3431.8 | 3418.9 | 3431.8 |
| 10°   | 3438.2 | 3441.5 | 3444.7 | 3441.5 | 3438.2 | 3443.1 | 3443.1 | 3436.6 | 3431.8 | 3418.9 | 3433.4 |
| 12.5° | 3456.0 | 3460.8 | 3462.4 | 3454.4 | 3451.1 | 3452.7 | 3452.7 | 3446.3 | 3446.3 | 3435.0 | 3451.1 |
| 15°   | 3497.9 | 3501.1 | 3496.3 | 3486.6 | 3488.2 | 3493.1 | 3481.8 | 3465.6 | 3462.4 | 3457.6 | 3470.5 |
| 17.5° | 3530.2 | 3533.4 | 3528.5 | 3522.1 | 3533.4 | 3544.7 | 3523.7 | 3493.1 | 3483.4 | 3480.2 | 3494.7 |
| 20°   | 3565.6 | 3570.5 | 3564.0 | 3572.1 | 3594.7 | 3607.6 | 3581.8 | 3539.8 | 3520.5 | 3515.6 | 3533.4 |
| 22.5° | 3623.7 | 3630.1 | 3630.1 | 3647.9 | 3681.7 | 3702.7 | 3670.5 | 3614.0 | 3585.0 | 3576.9 | 3594.7 |
| 25°   | 3715.6 | 3720.4 | 3725.3 | 3760.8 | 3815.6 | 3844.6 | 3793.0 | 3715.6 | 3675.3 | 3662.4 | 3672.1 |
| 27.5° | 3843.0 | 3851.1 | 3859.1 | 3910.7 | 3978.5 | 4020.4 | 3946.2 | 3849.5 | 3799.5 | 3773.7 | 3793.0 |
| 30°   | 3994.6 | 4005.9 | 4025.2 | 4083.3 | 4178.4 | 4225.2 | 4130.1 | 4012.3 | 3955.9 | 3928.5 | 3954.3 |
| 32.5° | 4201.0 | 4202.6 | 4217.2 | 4281.7 | 4407.4 | 4460.7 | 4341.3 | 4210.7 | 4152.6 | 4120.4 | 4134.9 |
| 35°   | 4446.2 | 4447.8 | 4425.2 | 4491.3 | 4626.8 | 4686.4 | 4546.1 | 4413.9 | 4365.5 | 4355.8 | 4392.9 |
| 37.5° | 4697.7 | 4683.2 | 4660.6 | 4689.7 | 4826.7 | 4865.4 | 4717.1 | 4604.2 | 4583.2 | 4601.0 | 4655.8 |
| 40°   | 4876.7 | 4852.5 | 4807.4 | 4828.4 | 4967.0 | 5012.2 | 4854.2 | 4747.7 | 4741.3 | 4784.8 | 4850.9 |
| 42.5° | 4992.8 | 4967.0 | 4913.8 | 4913.8 | 5009.0 | 5028.3 | 4905.8 | 4849.3 | 4863.8 | 4913.8 | 4976.7 |
| 45°   | 5049.3 | 5034.8 | 5004.1 | 4988.0 | 5041.2 | 5049.3 | 4955.8 | 4933.2 | 4960.6 | 4984.8 | 5033.2 |
| 47.5° | 5092.8 | 5092.8 | 5083.2 | 5067.0 | 5091.2 | 5096.1 | 5026.7 | 5020.3 | 5055.7 | 5055.7 | 5088.0 |
| 50°   | 5170.2 | 5178.3 | 5191.2 | 5188.0 | 5213.8 | 5229.9 | 5178.3 | 5168.6 | 5183.1 | 5136.4 | 5152.5 |
| 52.5° | 5373.4 | 5394.4 | 5431.5 | 5460.5 | 5526.6 | 5576.6 | 5484.7 | 5407.3 | 5331.5 | 5228.3 | 5231.5 |
| 55°   | 5737.9 | 5747.6 | 5820.2 | 5905.6 | 6016.9 | 6118.5 | 5929.8 | 5689.5 | 5525.0 | 5404.1 | 5405.7 |
| 57.5° | 6045.9 | 6060.4 | 6166.9 | 6345.9 | 6595.9 | 6753.9 | 6336.2 | 5934.7 | 5702.4 | 5554.1 | 5558.9 |
| 60°   | 5779.8 | 5760.5 | 5962.1 | 6268.5 | 6721.6 | 6923.2 | 6307.2 | 5758.9 | 5425.0 | 5241.2 | 5254.1 |
| 62.5° | 4472.0 | 4434.9 | 4659.0 | 4979.9 | 5523.4 | 5725.0 | 5157.3 | 4631.6 | 4315.5 | 4172.0 | 4151.0 |
| 65°   | 2722.2 | 2688.3 | 2849.6 | 3046.3 | 3414.0 | 3541.4 | 3281.8 | 3002.8 | 2727.0 | 2640.0 | 2615.8 |
| 67.5° | 1482.1 | 1477.2 | 1520.8 | 1617.5 | 1778.8 | 1838.5 | 1788.5 | 1656.2 | 1585.3 | 1524.0 | 1524.0 |
| 70°   | 1175.6 | 1166.0 | 1157.9 | 1159.5 | 1174.0 | 1182.1 | 1183.7 | 1177.3 | 1185.3 | 1186.9 | 1180.5 |
| 72.5° | 974.1  | 970.8  | 954.7  | 956.3  | 949.9  | 946.6  | 957.9  | 964.4  | 977.3  | 978.9  | 978.9  |
| 75°   | 706.4  | 698.3  | 706.4  | 708.0  | 701.5  | 701.5  | 709.6  | 708.0  | 714.4  | 717.6  | 699.9  |
| 77.5° | 401.6  | 401.6  | 412.8  | 425.7  | 435.4  | 435.4  | 443.5  | 443.5  | 451.5  | 449.9  | 446.7  |
| 80°   | 220.9  | 220.9  | 227.4  | 235.5  | 245.1  | 254.8  | 262.9  | 264.5  | 269.3  | 267.7  | 262.9  |
| 82.5° | 125.8  | 127.4  | 130.6  | 135.5  | 145.1  | 153.2  | 161.3  | 162.9  | 167.7  | 167.7  | 162.9  |
| 85°   | 59.7   | 58.1   | 59.7   | 62.9   | 67.7   | 74.2   | 82.2   | 87.1   | 90.3   | 90.3   | 87.1   |
| 87.5° | 11.3   | 12.9   | 11.3   | 12.9   | 14.5   | 19.4   | 22.6   | 25.8   | 30.6   | 32.3   | 29.0   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine



**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2407-157-9  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/03/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Invue  
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**  
 Description: Epic Modern Light Square 40W 5WQ Optic

**Spectral Parameters**

CCT (K): 2764  
 CIE u': 0.2591  
 CIE v': 0.5290  
 Duv: 0.0020  
 CIE x: 0.4581  
 CIE y: 0.4156  
 CIE z: 0.1263  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 583  
 Purity: 62.2537  
 Rf: 84.7  
 Rg: 94.6

|           |      |      |      |
|-----------|------|------|------|
| CRI (Ra): | 80.9 |      |      |
| R1:       | 78.8 | R9:  | -1.5 |
| R2:       | 89.9 | R10: | 77.9 |
| R3:       | 96.2 | R11: | 78.9 |
| R4:       | 79.1 | R12: | 71.6 |
| R5:       | 79.1 | R13: | 81.2 |
| R6:       | 88.8 | R14: | 98.5 |
| R7:       | 81.3 | R15: | 69.9 |
| R8:       | 54.3 |      |      |



**Test Conditions**

Stabilization Time: 81M  
 Operation Time: 2H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2764K  
 CIE x = 0.4581  
 CIE y = 0.4156  
 Duv = 0.0020

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

**Photopic Flux vs. Wavelength**



**Photopic Lumens: 4337.9**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 0             | 0.0           | 490    | 18018         | 2.6           | 620    | 87426         | 22.8          | 750    | 2680          | 0.0           | 880    | 58            | 0.0           |
| 365    | 0             | 0.0           | 495    | 22295         | 3.9           | 625    | 83013         | 18.2          | 755    | 2287          | 0.0           | 885    | 46            | 0.0           |
| 370    | 0             | 0.0           | 500    | 26478         | 5.8           | 630    | 78077         | 14.1          | 760    | 1944          | 0.0           | 890    | 45            | 0.0           |
| 375    | 0             | 0.0           | 505    | 30524         | 8.5           | 635    | 72080         | 10.7          | 765    | 1653          | 0.0           | 895    | 41            | 0.0           |
| 380    | 0             | 0.0           | 510    | 33611         | 11.5          | 640    | 66249         | 7.9           | 770    | 1413          | 0.0           | 900    | 38            | 0.0           |
| 385    | 0             | 0.0           | 515    | 36490         | 15.2          | 645    | 59973         | 5.7           | 775    | 1198          | 0.0           | 905    | 33            | 0.0           |
| 390    | 0             | 0.0           | 520    | 38610         | 18.7          | 650    | 53972         | 3.9           | 780    | 1025          | 0.0           | 910    | 30            | 0.0           |
| 395    | 0             | 0.0           | 525    | 40511         | 21.9          | 655    | 48369         | 2.7           | 785    | 874           | 0.0           | 915    | 23            | 0.0           |
| 400    | 48            | 0.0           | 530    | 42223         | 24.9          | 660    | 42641         | 1.8           | 790    | 747           | 0.0           | 920    | 24            | 0.0           |
| 405    | 201           | 0.0           | 535    | 44137         | 27.6          | 665    | 37602         | 1.1           | 795    | 639           | 0.0           | 925    | 22            | 0.0           |
| 410    | 457           | 0.0           | 540    | 46032         | 30.0          | 670    | 32798         | 0.7           | 800    | 547           | 0.0           | 930    | 22            | 0.0           |
| 415    | 925           | 0.0           | 545    | 48553         | 32.5          | 675    | 28558         | 0.5           | 805    | 473           | 0.0           | 935    | 17            | 0.0           |
| 420    | 1816          | 0.0           | 550    | 51408         | 34.9          | 680    | 24782         | 0.3           | 810    | 401           | 0.0           | 940    | 13            | 0.0           |
| 425    | 3217          | 0.0           | 555    | 54711         | 37.4          | 685    | 21386         | 0.2           | 815    | 351           | 0.0           | 945    | 6             | 0.0           |
| 430    | 5520          | 0.0           | 560    | 58847         | 40.0          | 690    | 18413         | 0.1           | 820    | 307           | 0.0           | 950    | 10            | 0.0           |
| 435    | 9225          | 0.1           | 565    | 63386         | 42.4          | 695    | 15721         | 0.1           | 825    | 261           | 0.0           | 955    | 11            | 0.0           |
| 440    | 15522         | 0.2           | 570    | 68196         | 44.3          | 700    | 13432         | 0.0           | 830    | 228           | 0.0           | 960    | 8             | 0.0           |
| 445    | 27642         | 0.6           | 575    | 73613         | 46.0          | 705    | 11513         | 0.0           | 835    | 193           | 0.0           | 965    | 12            | 0.0           |
| 450    | 36602         | 0.9           | 580    | 79207         | 47.1          | 710    | 9780          | 0.0           | 840    | 174           | 0.0           | 970    | 3             | 0.0           |
| 455    | 28292         | 0.9           | 585    | 84248         | 47.0          | 715    | 8356          | 0.0           | 845    | 151           | 0.0           | 975    | 8             | 0.0           |
| 460    | 21166         | 0.9           | 590    | 88397         | 45.7          | 720    | 7161          | 0.0           | 850    | 123           | 0.0           | 980    | 2             | 0.0           |
| 465    | 19092         | 1.0           | 595    | 91428         | 43.4          | 725    | 6067          | 0.0           | 855    | 106           | 0.0           | 985    | 13            | 0.0           |
| 470    | 14951         | 0.9           | 600    | 93452         | 40.3          | 730    | 5164          | 0.0           | 860    | 95            | 0.0           | 990    | 16            | 0.0           |
| 475    | 12606         | 1.0           | 605    | 93959         | 36.4          | 735    | 4393          | 0.0           | 865    | 82            | 0.0           | 995    | 20            | 0.0           |
| 480    | 13323         | 1.3           | 610    | 93079         | 32.0          | 740    | 3694          | 0.0           | 870    | 77            | 0.0           | 1000   | 0             | 0.0           |
| 485    | 15164         | 1.8           | 615    | 90707         | 27.3          | 745    | 3157          | 0.0           | 875    | 65            | 0.0           |        |               |               |

REPORT NUMBER: SP1-2407-157-9

**Scotopic Flux vs. Wavelength**




**Scotopic Lumens: 5286.7**

**S/P: 1.22**

| $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360            | 0                                 | 0.0                         | 490            | 18018                             | 75.9                        | 620            | 87426                             | 0.4                         | 750            | 2680                              | 0.0                         | 880            | 58                                | 0.0                         |
| 365            | 0                                 | 0.0                         | 495            | 22295                             | 93.2                        | 625            | 83013                             | 0.2                         | 755            | 2287                              | 0.0                         | 885            | 46                                | 0.0                         |
| 370            | 0                                 | 0.0                         | 500            | 26478                             | 107.8                       | 630            | 78077                             | 0.1                         | 760            | 1944                              | 0.0                         | 890            | 45                                | 0.0                         |
| 375            | 0                                 | 0.0                         | 505            | 30524                             | 118.7                       | 635            | 72080                             | 0.1                         | 765            | 1653                              | 0.0                         | 895            | 41                                | 0.0                         |
| 380            | 0                                 | 0.0                         | 510            | 33611                             | 122.2                       | 640            | 66249                             | 0.1                         | 770            | 1413                              | 0.0                         | 900            | 38                                | 0.0                         |
| 385            | 0                                 | 0.0                         | 515            | 36490                             | 120.8                       | 645            | 59973                             | 0.0                         | 775            | 1198                              | 0.0                         | 905            | 33                                | 0.0                         |
| 390            | 0                                 | 0.0                         | 520            | 38610                             | 113.9                       | 650            | 53972                             | 0.0                         | 780            | 1025                              | 0.0                         | 910            | 30                                | 0.0                         |
| 395            | 0                                 | 0.0                         | 525            | 40511                             | 104.1                       | 655            | 48369                             | 0.0                         | 785            | 874                               | 0.0                         | 915            | 23                                | 0.0                         |
| 400            | 48                                | 0.0                         | 530            | 42223                             | 92.4                        | 660            | 42641                             | 0.0                         | 790            | 747                               | 0.0                         | 920            | 24                                | 0.0                         |
| 405            | 201                               | 0.0                         | 535            | 44137                             | 80.5                        | 665            | 37602                             | 0.0                         | 795            | 639                               | 0.0                         | 925            | 22                                | 0.0                         |
| 410            | 457                               | 0.1                         | 540            | 46032                             | 68.2                        | 670            | 32798                             | 0.0                         | 800            | 547                               | 0.0                         | 930            | 22                                | 0.0                         |
| 415            | 925                               | 0.3                         | 545            | 48553                             | 57.1                        | 675            | 28558                             | 0.0                         | 805            | 473                               | 0.0                         | 935            | 17                                | 0.0                         |
| 420            | 1816                              | 1.1                         | 550            | 51408                             | 46.7                        | 680            | 24782                             | 0.0                         | 810            | 401                               | 0.0                         | 940            | 13                                | 0.0                         |
| 425            | 3217                              | 2.5                         | 555            | 54711                             | 37.4                        | 685            | 21386                             | 0.0                         | 815            | 351                               | 0.0                         | 945            | 6                                 | 0.0                         |
| 430            | 5520                              | 5.9                         | 560            | 58847                             | 29.4                        | 690            | 18413                             | 0.0                         | 820            | 307                               | 0.0                         | 950            | 10                                | 0.0                         |
| 435            | 9225                              | 12.5                        | 565            | 63386                             | 22.5                        | 695            | 15721                             | 0.0                         | 825            | 261                               | 0.0                         | 955            | 11                                | 0.0                         |
| 440            | 15522                             | 26.3                        | 570            | 68196                             | 16.9                        | 700            | 13432                             | 0.0                         | 830            | 228                               | 0.0                         | 960            | 8                                 | 0.0                         |
| 445            | 27642                             | 55.2                        | 575            | 73613                             | 12.4                        | 705            | 11513                             | 0.0                         | 835            | 193                               | 0.0                         | 965            | 12                                | 0.0                         |
| 450            | 36602                             | 85.4                        | 580            | 79207                             | 9.0                         | 710            | 9780                              | 0.0                         | 840            | 174                               | 0.0                         | 970            | 3                                 | 0.0                         |
| 455            | 28292                             | 75.1                        | 585            | 84248                             | 6.3                         | 715            | 8356                              | 0.0                         | 845            | 151                               | 0.0                         | 975            | 8                                 | 0.0                         |
| 460            | 21166                             | 63.2                        | 590            | 88397                             | 4.4                         | 720            | 7161                              | 0.0                         | 850            | 123                               | 0.0                         | 980            | 2                                 | 0.0                         |
| 465            | 19092                             | 63.2                        | 595            | 91428                             | 3.0                         | 725            | 6067                              | 0.0                         | 855            | 106                               | 0.0                         | 985            | 13                                | 0.0                         |
| 470            | 14951                             | 54.2                        | 600            | 93452                             | 2.0                         | 730            | 5164                              | 0.0                         | 860            | 95                                | 0.0                         | 990            | 16                                | 0.0                         |
| 475            | 12606                             | 48.8                        | 605            | 93959                             | 1.3                         | 735            | 4393                              | 0.0                         | 865            | 82                                | 0.0                         | 995            | 20                                | 0.0                         |
| 480            | 13323                             | 54.2                        | 610            | 93079                             | 0.9                         | 740            | 3694                              | 0.0                         | 870            | 77                                | 0.0                         | 1000           | 0                                 | 0.0                         |
| 485            | 15164                             | 63.3                        | 615            | 90707                             | 0.5                         | 745            | 3157                              | 0.0                         | 875            | 65                                | 0.0                         |                |                                   |                             |

REPORT NUMBER: SP1-2407-157-9

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 9797**

**M/P: 2.26**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 0             | 0.0           | 490    | 18018         | 27.7          | 620    | 87426         | 1.1           | 750    | 2680          | 0.0           | 880    | 58            | 0.0           |
| 365    | 0             | 0.0           | 495    | 22295         | 36.0          | 625    | 83013         | 0.7           | 755    | 2287          | 0.0           | 885    | 46            | 0.0           |
| 370    | 0             | 0.0           | 500    | 26478         | 44.2          | 630    | 78077         | 0.4           | 760    | 1944          | 0.0           | 890    | 45            | 0.0           |
| 375    | 0             | 0.0           | 505    | 30524         | 51.8          | 635    | 72080         | 0.3           | 765    | 1653          | 0.0           | 895    | 41            | 0.0           |
| 380    | 0             | 0.0           | 510    | 33611         | 57.0          | 640    | 66249         | 0.2           | 770    | 1413          | 0.0           | 900    | 38            | 0.0           |
| 385    | 0             | 0.0           | 515    | 36490         | 60.5          | 645    | 59973         | 0.1           | 775    | 1198          | 0.0           | 905    | 33            | 0.0           |
| 390    | 0             | 0.0           | 520    | 38610         | 61.4          | 650    | 53972         | 0.1           | 780    | 1025          | 0.0           | 910    | 30            | 0.0           |
| 395    | 0             | 0.0           | 525    | 40511         | 60.6          | 655    | 48369         | 0.0           | 785    | 874           | 0.0           | 915    | 23            | 0.0           |
| 400    | 48            | 0.0           | 530    | 42223         | 58.2          | 660    | 42641         | 0.0           | 790    | 747           | 0.0           | 920    | 24            | 0.0           |
| 405    | 201           | 0.0           | 535    | 44137         | 55.0          | 665    | 37602         | 0.0           | 795    | 639           | 0.0           | 925    | 22            | 0.0           |
| 410    | 457           | 0.0           | 540    | 46032         | 50.9          | 670    | 32798         | 0.0           | 800    | 547           | 0.0           | 930    | 22            | 0.0           |
| 415    | 925           | 0.1           | 545    | 48553         | 46.6          | 675    | 28558         | 0.0           | 805    | 473           | 0.0           | 935    | 17            | 0.0           |
| 420    | 1816          | 0.3           | 550    | 51408         | 42.0          | 680    | 24782         | 0.0           | 810    | 401           | 0.0           | 940    | 13            | 0.0           |
| 425    | 3217          | 0.8           | 555    | 54711         | 37.4          | 685    | 21386         | 0.0           | 815    | 351           | 0.0           | 945    | 6             | 0.0           |
| 430    | 5520          | 1.9           | 560    | 58847         | 32.9          | 690    | 18413         | 0.0           | 820    | 307           | 0.0           | 950    | 10            | 0.0           |
| 435    | 9225          | 4.1           | 565    | 63386         | 28.4          | 695    | 15721         | 0.0           | 825    | 261           | 0.0           | 955    | 11            | 0.0           |
| 440    | 15522         | 8.7           | 570    | 68196         | 24.1          | 700    | 13432         | 0.0           | 830    | 228           | 0.0           | 960    | 8             | 0.0           |
| 445    | 27642         | 18.5          | 575    | 73613         | 20.0          | 705    | 11513         | 0.0           | 835    | 193           | 0.0           | 965    | 12            | 0.0           |
| 450    | 36602         | 28.3          | 580    | 79207         | 16.3          | 710    | 9780          | 0.0           | 840    | 174           | 0.0           | 970    | 3             | 0.0           |
| 455    | 28292         | 24.7          | 585    | 84248         | 12.9          | 715    | 8356          | 0.0           | 845    | 151           | 0.0           | 975    | 8             | 0.0           |
| 460    | 21166         | 20.4          | 590    | 88397         | 9.8           | 720    | 7161          | 0.0           | 850    | 123           | 0.0           | 980    | 2             | 0.0           |
| 465    | 19092         | 20.1          | 595    | 91428         | 7.3           | 725    | 6067          | 0.0           | 855    | 106           | 0.0           | 985    | 13            | 0.0           |
| 470    | 14951         | 17.2          | 600    | 93452         | 5.3           | 730    | 5164          | 0.0           | 860    | 95            | 0.0           | 990    | 16            | 0.0           |
| 475    | 12606         | 15.7          | 605    | 93959         | 3.7           | 735    | 4393          | 0.0           | 865    | 82            | 0.0           | 995    | 20            | 0.0           |
| 480    | 13323         | 18.0          | 610    | 93079         | 2.5           | 740    | 3694          | 0.0           | 870    | 77            | 0.0           | 1000   | 0             | 0.0           |
| 485    | 15164         | 21.9          | 615    | 90707         | 1.7           | 745    | 3157          | 0.0           | 875    | 65            | 0.0           |        |               |               |

**Summary**

$R_f = 84.7$   
 $R_g = 94.6$   
 $CIE R_a = 80.9$   
 $R_g = -1.5$




**Color Vector Graphics**





Individual Sample Fidelity Index ( $R_{f,i}$ )

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 |            |





Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)